Clean Regulator

SRH Series





Clean Regulator

SRH Series


Contamination controlled stainless steel regulator

Outstanding corrosion resistance

All metal parts in contact with fluid use stainless steel 316

Oil free

diaphragm material







Designed to minimize residual fluid

- Design includes an intake/exhaust port in the diaphragm compartment which facilitates flow
- Valve springs are partitioned by the diaphragm


Pulsation suppressing design

Step response comparison






Circuit diagram



Consistent clean room production

Washed, assembled and inspected in a Class 100 environment, and sealed in double bags

Manufacturing process




Clean Regulator **SRH Series**





How to Order



Port size Made to Order
Refer to pages 1138 to 1140 for details.

notor to pages 1100 to 1110 for details.					
X210	EPDM seals				
X211	With relief port fittings (Applicable tube O.D.: ø4)				
X216	Machined relief port M5 thread				
X233	Knob operation product with reduced torque				
X234	Aluminum body				
X328	Pressure gauge included				

Symbol



Symbol SRH3000 SRH4000 Piping port size 01 02 1/4 03 3/8 • 04 1/2 A2 With metal gasket seal fitting URJF 1/4 А3 URJF 3/8 With metal gasket seal fitting

Note) Refer to page 1136 for pressure gauge details.


Note that SMC does not produce pressure gauges for port sizes A2 and A3.

Specifications

Model		SRH3□□0	SRH4□□0	SRH3□□1	SRH4□□1			
Relief mech	anism	Non-	relief	Re	elief			
Port size		1/8, 1/4 URJF 1/4	1/4, 3/8, 1/2 URJF 3/8	1/8, 1/4	1/4, 3/8, 1/2			
Fluid	Grade A	Clean air, N2, Ar,	CO2, Pure water	Clean	air, N2			
Fluid	Grade B	Air, N2, Ar,	CO2, Water	Air	, N2			
Proof press	Proof pressure		1.5 MPa					
Max. operating pressure		1 MPa						
Set	Low pressure type	0.02 to 0.2 MPa						
pressure	High pressure type	0.05 to 0.7 MPa						
Ambient and fluid temperatures		0 to 60°C (No freezing)						
Fluid-contact material (metal)		Stainless steel 316 (Body is stainless steel 316L)						
Diaphragm	Grade A	PTFE						
material	Grade B	Fluororubber						
Weight		360 g 730 g 360 g			730 g			

SRH Series


Flow Rate Characteristics (Representative Value)





Pressure Characteristics (Representative Value)


Fluid: Water/Air


Conditions/ Inlet pressure: 0.7 MPa, Outlet pressure: 0.2 MPa, Flow rate 2 L/min






















Construction



Component parts


Component parts							
No.	Description	Material					
NO.		Grade A	Grade B				
1	Body	Stainless steel 316L					
2	Diaphragm	PTFE	Fluororubber				
3	Diaphragm	PTFE Fluororubb					
4	Valve guide	PPS					
- 5	Bonnet	PPS					

Rc thread type



Dimensions inside () are for SRH4000.

Metal gasket seal fitting type



Dimensions inside () are for SRH4000.




SRH Series

Options

Pressure Gauge

Dimensions



Specifications

Item Model		G46-□-02-SRA	G46-□-02-SRB			
Port size		R	1/4			
Operating range	temperature	0 to 60°C (No freezing)				
Accuracy		± 3%	F.S.			
Scale rang	ge	27	'0°			
Parts washing (fluid-contact parts)		Precision wash	General degrease			
Assembly and adjustment environment		Clean room	General production line			
Oil free / V	Vater free	Non-lube / Non-wet				
	Fluid-contact parts	Stainless steel 316				
Materials	Case	Stainless steel 304 (Black melamine coating)				
wateriais	Clear cover	Polycarbonateca (Hard coated) Part No. G46-00-0				
	Internal parts	Brass				
Weight		80 g				


Models

Mandal	Pressure range	Indicator units		
Model	MPa			
G46-2-02-SRA	0 to 0.2			
G46-2-02-SRB	0 10 0.2			
G46-4-02-SRA	04-04	МРа		
G46-4-02-SRB	0 to 0.4			
G46-7-02-SRA	0 to 0.7			
G46-7-02-SRB	0 10 0.7			
G46-10-02-SRA	0 to 1 0			
G46-10-02-SRB	0 to 1.0			

Procedure for setting the limit gauge indicator


Before setting the limit indicator, turn the cover counterclockwise (approximately 6 to 7 mm) until it stops. Then, remove by pulling it towards you.

Count




Use a flat head screwdriver (with a 2.9 mm blade width) to set the limit indicator.

Be careful not to bend other needle or damage the dial plate.



3) After completing the setting, replace the cover.

Fit the cover by aligning the cutout in the cover to the groove on the top of the black case. Turn the cover clockwise (approximately 6 to 7 mm) and make sure that the matching mark on the cover is aligned with the groove on the top of the case.



⚠ Specific Product Precautions

Be sure to read this before handling the products. Refer to page 9 for safety instructions and pages 13 to 17 for precautions on every series.

Selection

- 1) Avoid use in locations with strong pressure pulsation or vibration.
- 2) Contact SMC if the product is to be used in an application with a high frequency of operation.

Mounting

- Do not subject the gauge to shocks, such as dropping during transportation and mounting, as this can cause loss of indication accuracy.
- 2) Do not use this gauge in a location with high temperature and humidity, as this may cause faulty operation.
- 3) When mounting the pressure gauge, be certain to use a wrench on the square wrench flats to screw it into place. If the wrench is applied on any other part, air leakage or other damage may occur.

Brackets

	For SRH3000	For SRH4000
Model	B21-1-T1	1350112-T1
Material	Rolled sheet steel (Ele	ectroless nickel plated)
Dimensions	8.5	30 50 50

SRH Series Made to Order Specifications 1



Please contact SMC for detailed dimensions, specifications and lead times.



Regulator with seals made of a different material.

SRH Standard model no. - X210

EPDM seals

Specifications

Model		SRH30-X210	SRH40-X210	SRH3_1-X210 SRH4_1-X210				
Relief me	chanism	Non-	relief	Re	lief			
Port size		1/8, 1/4 1/4, 3/8, 1/2 URJF 1/4 URJF 3/8		1/8, 1/4	1/4, 3/8, 1/2			
Fluid	Grade A	Clean air, N2, Ar,	CO ₂ , Pure water	Clean	air, N2			
i iuiu	Grade B	Air, N2, Ar,	CO ₂ , Water	Air,	N2			
Proof pressure			1.5 l	МРа				
Max. operatir	ng pressure	1.0 MPa						
Set tv		0.02 to 0.2 MPa						
pressure Hi	gh pressure pe	0.05 to 0.7 MPa						
Ambient and fluid temperatures		0 to 60°C (No freezing)						
Fluid-contact m	aterial (metal)	Stainless steel 316 (Body is stainless steel 316L)						
Diaphragm Grade A		PTFE						
material	Grade B		EP	DM				
Weight		360 g	730 g	360 g	730 g			



Regulator with a fitting in order to connect it to the relief port.

SRH Standard model no. — X211

Made to Order


Nil Standard


X211 With relief port fittings (Applicable tube O.D.: 04)

The specifications are the same as those of the standard model. Refer to page 1131 for details.

Dimensions

Dimensions other than below are the same as the standard type.






SRH Series Made to Order Specifications 2



Please contact SMC for detailed dimensions, specifications and lead times.

3 Machined Relief Port M5 Thread X216


Regulator with an M5 thread machined on the relief port in order to connect it to the relief port.




The specifications are the same as those of the standard model. Refer to page 1131 for details.

Dimensions


Dimensions other than below are the same as the standard type.





Fluoro grease is applied to an adjusting screw in order to make the knob operation easy.

* Oil is not used for the wetted parts.



The specifications are the same as those of the standard model. Refer to page 1131 for details.

5 Aluminum Body

Symbol X234

The body material has been changed to aluminum.

SRH Standard model no. — X234


• Aluminum Body

Specifications

	opeomodiono						
Model		SRH30-X234	SRH3 <u>□</u> 0-X234 SRH4 <u>□</u> 0-X234		SRH4_11-X234		
Relief me	chanism	Non-	relief	Relief			
Port size		1/8, 1/4	1/4, 3/8, 1/2	1/8, 1/4	1/4, 3/8, 1/2		
Fluid	Grade B	Air, N2,	Ar, CO2	Air,	N ₂		
Proof pre	ssure		1.5	MPa			
Max. operatin	g pressure		1.0	MPa			
Set Lo	ow pressure pe	0.02 to 0.2 MPa					
pressure Hi	gh pressure pe	0.05 to 0.7 MPa					
Ambient a temperatu	and fluid	0 to 60°C (No freezing)					
Fluid-contact m	aterial (metal)	(metal) A2017 (Surface treatment: Anodized)			lized)		
Diaphragm material	Grade B	Fluororubber					
Weight		230 g 360 g 230 g 360					

6 Pressure gauge included X328 (A, B, C, D)

Specification that includes a pressure gauge



Pressure gauge max. display pressure*1

Α	0.2 MPa
В	0.4 MPa
С	0.7 MPa
D	1.0 MPa

^{*1} Set the regulator pressure to the max. display pressure of the pressure gauge or lower.

About the included pressure gauge

an regulator shing grade	Pressure gauge model
Grade A	G46-□-02-SRA
Grade B	G46-□-02-SRB

The specifications are the same as those of the standard model. Refer to page 1131 for details.



SRH Series Made to Order Specifications 3



Please contact SMC for detailed dimensions, specifications and lead times.

7 Regulator (Stainless Steel 316) with Port Sizes Rc 3/4, Rc 1

- Regulator made of stainless steel 316 with port sizes Rc 3/4 and Rc 1.
- EPDM or FPM is used for valves (seals),
 O-rings and diaphragms.
- Oil-free

Oil is not used for any of the parts and all wetted parts are degreased.

Note) Products must be assembled under normal conditions.

Spe	cificatio	ns	
	Model	П	

Model	XT13-394-06	XT13-394-10	INA-48-1-06	INA-48-1-10	INA-48-58-06-H	INA-48-58-10-H	INA-48-16-06	INA-48-16-10
Port size	Rc3/4	Rc1	Rc3/4	Rc1	Rc3/4	Rc1	Rc3/4	Rc1
Relief mechanism	Non-relief Relief			Non-	Non-relief			
Fluid	Deionized water	er (Pure water)			Air	N ₂		
Proof pressure		1.5 MPa 1.9 MPa					MPa	
Max. operating pressure		1.0 MPa 1.3 MPa						MPa
Set pressure	0.05 to 0.5 MPa 0.1 to 1.0 MPa					.0 MPa		
Ambient and fluid temperatures		5 to 60°C						
Fluid-contact material (metal)		Stainless steel 316						
Diaphragm material	EPDM Fluororubber							
Weight	2100 g							


Note) The pressure gauge is optional. For details, refer to the Options on page 1136.

Flow Rate Characteristics


XT13-394-06, 10

---- Max. operating flow rate


(It is recommended to be used within the max.)
operating flow rate (negative) range.





INA-48-1-06, 10



Construction







Component parts

No.	Description	Material	
		XT13-394-06, 10	INA-48-1-06, 10
1	Body	Stainless steel 316	
2	Bonnet	ADC12	
3	Valve guide	Stainless steel 316	
4	Diaphragm Assembly	EPDM Stainless steel 316 (Wetted part metal)	Fluororubber Stainless steel 316 (Wetted part metal)
	Assembly	` ' '	` ' '
5	Valve	EPDM (Seals) Stainless steel 316 (Wetted part metal)	FPM (Seals) Stainless steel 316 (Wetted part metal)
6	O-ring	EPDM	Fluororubber



SRH Series Specific Product Precautions

Be sure to read this before handling the products. Refer to page 9 for safety instructions and pages 13 to 17 for precautions on every series.

Design and Selection

1. Confirm the fluid.

Because the fluid to be used differs depending on the product, be certain to confirm the specifications. If an incompatible fluid is used, special characteristics will change and this may cause improper operation.

2. Residual pressure relief is not possible without inlet pressure.

In the SRH series, if the inlet pressure is cut off while pressure still remains on the outlet side, it is not possible to eliminate the outlet pressure (residual pressure relief). If it will be necessary to eliminate pressure from the outlet side, a circuit should be provided for residual pressure relief.

- Oscillation (beat) may occur with some operating conditions even if the operation is within specification. Contact SMC for that case.
- 2. When operating at an inlet pressure lower than the inlet pressure used in the flow rate characteristics graph, the pressure drop on the outlet side may be greater. Therefore, be sure to conduct testing using the actual equipment.

For pressure control equipment selection, refer to the "Product Selection Guide."

Mounting

⚠ Caution

 Open the sealed package inside a clean room.

These products are packaged in sealed double packaging in a clean room. It is recommended that the inside packaging be opened in a clean room or other clean environment.

2. Flush out the piping.

Connect these products to piping only after it has been flushed and cleaned properly. If debris or scale etc. remains in the piping, this can cause faulty operation or failure.

Be certain that sealing material does not get inside the piping.

When screwing in pipes and joints etc., take care that cutting dust from the pipe threads, sealing material, and the like do not get inside the piping. If debris or scale etc. remain inside the piping, this may cause faulty operation or failure. Also, when thread tape is used, leave 1.5 to 2 threads exposed at the end of the pipe.

4. Confirm the mounted orientation of the product.

The side marked IN is the fluid inlet port, and the side marked OUT is the fluid exhaust port. If mounted backwards, the device will not operate properly.

Pressure Adjustment

⚠ Warning

1. Do not use tools when operating the pressure regulator knob.

If tools etc. are used to operate the pressure regulator knob, damage may occur. Operate this knob only by hand.

1. Perform pressure adjustments only after releasing the lock.

When the pressure regulator knob will not turn, it is locked. Release the lock by pulling the pressure regulator knob out. If the knob is turned by force damage will occur.

Lock again after adjusting the pressure by pressing the knob back

2. Adjust pressure in an upward direction.

A correct pressure setting cannot be achieved by adjusting the pressure downward. The outlet pressure is increased by turning the pressure regulator knob to the right, and decreased by turning the knob to the left.

In the case of the non-relief type, the pressure cannot be reduced by turning the pressure regulator knob to the left.

In the case of the non-relief type regulator, the outlet pressure will not decrease even if the knob is turned to the left, when there is no outlet fluid consumption. The knob will be damaged if it is turned by force.

In case the pressure setting is too high, reduce the pressure on the outlet side to less than the desired setting pressure by consuming fluid on the outlet side, and then reset to the desired pressure.

4. Confirm the inlet pressure.

Set the outlet pressure to no more than 85% of the inlet pressure. If the inlet pressure is too low, a correct setting pressure cannot be attained.

5. Do not use fluid containing solid matter.

This will cause faulty operation.

