
180° Angular Type Air Gripper


MHY2/MHW2 Series


ø10, ø16, ø20, ø25



MHZ MHF MHL MHR MHR MHK MHK MHY MHW -X MRHQ MA D-

180° Angular Type Air Gripper Cam Type Rack & Pinion Type MHY2/MHW2 Series






@SMC

MHF

-X□

MHY2/MHW2 Series Model Selection


Model Selection




Effective Gripping Force –


MHY2/MHW2 Series Double Acting


 Indication of effective gripping force The effective gripping force shown in the graphs to the right is expressed as F, which is the impellent force of one finger, when both fingers and attachments are in full contact with the workpiece as shown in the figure below.






MHY2-10D







MHY2-20D



MHY2-25D






SMC

MHY2/MHW2 Series Model Selection

Step 3 Confirmation of Moment of Inertia of Attachments -



Confirm the moment of inertia for the attachment at one side. Calculate the moment of inertia for A and B separately as shown in the figures on the right.



Procedure	Calculation	Calculation example		
. Check the operating conditions, dimensions of attachment, etc.	A part	Operating model: MHY2-16D Opening time: 0.15 s a = 40 (mm) b = 7 (mm) c = 8 (mm) d = 5 (mm) e = 10 (mm) f = 12 (mm)		
Calculate the moment of inertia of attachment.	A part z_1 z_1 z_2 Moment of inertia around Z1 axis $z_1 = \{m_1(a^2 + b^2)/12\} \times 10^{-6}$ Moment of inertia around Z axis $Ia = Iz_1 + m_1r_1^2 \times 10^{-6}$ B part z_2 z_2 Calculation of weight $m_2 = d \times e \times f \times Specific gravity$ Moment of inertia around Z axis $Iz_2 = \{m_2(d^2 + e^2)/12\} \times \frac{10^{-6}}{e}$ Moment of inertia around Z axis $Ib = Iz_2 + m_2r_2^2 \times \frac{10^{-6}}{16}$ Total moment of inertia I = Ia + IB (* Constant for unit conversion) MHY2-16D MHY2-16D MHY2-16D $u_{g_1}^{2,5}$ $u_{g_2}^{3,0}$ $u_{g_1}^{3,0}$ $u_{g_2}^{3,0}$ $u_{g_1}^{3,0}$ $u_{g_1}^{3,0}$ $u_{g_2}^{3,0}$ $u_{g_1}^{3,0}$ $u_{g_1}^{3,0}$ $u_{g_1}^{3,0}$ $u_{g_1}^{3,0}$ $u_{g_1}^{3,0}$ $u_{g_1}^{3,0}$ $u_{g_1}^{3,0}$ $u_{g_1}^{3,0}$ $u_{g_1}^{3,0}$ $u_{g_1}^{3,0}$ $u_{g_1}^{3,0}$ $u_{g_1}^{3,0}$ $u_{g_1}^{3,0}$ $u_{g_1}^{3,0}$ $u_{g_1}^{3,0}$ $u_{g_1}^{3,0}$ $u_{g_1}^{3,0}$ $u_{g_1}^{3,0}$ $u_{g_1}^{3,0}$ $u_{g_1}^{3,0}$ $u_{g_1}^{3,0}$ $u_{g_1}^{3,0}$ $u_{g_1}^{3,0}$ $u_{g_1}^{3,0}$ $u_{g_1}^{3,0}$ $u_{g_1}^{3,0}$ $u_{g_1}^{3,0}$ $u_{g_1}^{3,0}$ $u_{g_1}^{3,0}$ $u_{g_1}^{3,0}$ $u_{g_1}^{3,0}$ $u_{g_1}^{3,0}$ $u_{g_1}^{3,0}$ $u_{g_1}^{3,0}$ $u_{g_1}^{3,0}$ $u_{g_1}^{3,0}$ $u_{g_1}^{3,0}$ $u_{g_1}^{3,0}$ $u_{g_1}^{3,0}$ $u_{g_1}^{3,0}$ $u_{g_1}^{3,0}$ $u_{g_1}^{3,0}$ $u_{g_1}^{3,0}$ $u_{g_1}^{3,0}$ $u_{g_1}^{3,0}$ $u_{g_1}^{3,0}$ $u_{g_1}^{3,0}$ $u_{g_1}^{3,0}$ $u_{g_1}^{3,0}$ $u_{g_1}^{3,0}$ $u_{g_1}^{3,0}$ $u_{g_1}^{3,0}$ $u_{g_1}^{3,0}$ $u_{g_1}^{3,0}$ $u_{g_1}^{3,0}$ $u_{g_1}^{3,0}$ $u_{g_1}^{3,0}$ $u_{g_1}^{3,0}$ $u_{g_1}^{3,0}$ $u_{g_1}^{3,0}$ $u_{g_1}^{3,0}$ $u_{g_1}^{3,0}$ $u_{g_1}^{3,0}$ $u_{g_1}^{3,0}$ $u_{g_1}^{3,0}$ $u_{g_1}^{3,0}$ $u_{g_1}^{3,0}$ $u_{g_1}^{3,0}$ $u_{g_1}^{3,0}$ $u_{g_1}^{3,0}$ $u_{g_1}^{3,0}$ $u_{g_1}^{3,0}$ $u_{g_1}^{3,0}$ $u_{g_1}^{3,0}$ $u_{g_1}^{3,0}$ $u_{g_1}^{3,0}$ $u_{g_1}^{3,0}$ $u_{g_1}^{3,0}$ $u_{g_1}^{3,0}$ $u_{g_1}^{3,0}$ $u_{g_1}^{3,0}$ $u_{g_1}^{3,0}$ $u_{g_1}^{3,0}$ u_{g			
 Confirm the moment of inertia of one attachment is within the allowable range. 	Moment of inertia of attachment < Allowable moment of inertia	0.13 x 10 ⁻⁴ (kg·m ²) < 0.9 x 10 ⁻⁴ (kg·m ²) Possible to use this model MHY2-16D completely.		




180° Angular Type Air Gripper MHY2/MHW2 Series

Symbol

_		
Symbol	Definition	Unit
z	Finger rotation axis	—
Z 1	Axis on the center gravity of A part of attachment and parallel to Z	_
Z2	Axis on the center gravity of B part of attachment and parallel to Z	—
Ι	Total moment of inertia for attachment	kg∙m²
IZ1	Inertia moment around the Z1 axis of A part of attachment	kg⋅m²
IZ2	Inertia moment around the Z2 axis of B part of attachment	kg∙m²


Symbol	Definition	Unit
IA	Moment of inertia around the Z axis of A part of attachment	kg∙m²
IB	Moment of inertia around the Z axis of B part of attachment	kg.m ²
m 1	Weight of A part of attachment	kg
m 2	Weight of B part of attachment	kg
ľ1	Distance between Z and Z1 axis	mm
r 2	Distance between Z and Z2 axis	mm

Allowable Range of Moment of Inertia of Attachment -



SMC

180° Angular Type Air Gripper **Cam Type** MHY2 Series ø10, ø16, ø20, ø25



Applicable Auto Switches / Refer to pages 797 to 850 for further information on auto switches.

		Electrical Indicator				Load voltage		Auto switch model		Lead wire length (m)*					Applicable			
Туре	Type Special function Electrical Indicate function entry light			Wiring (Output)		Loud voltage		Electrical en	try direction	0.5	1	3	5	Pre-wired connector		ad ad		
		ingin	(Output)		DC	AC	Perpendicular	In-line	(Nil)	(M)	(L)	(Z)	connector	Ioau				
				3-wire(NPN)		5 V. 12 V		M9NV	M9N	۲	•	•	0	0	IC			
switch				3-wire(PNP)		5 V, 12 V		M9PV	M9P	٠	•	•	0	0	circuit			
svi				2-wire		12 V		M9BV	M9B	۲	•	•	0	0	—			
auto	Diagnosis			3-wire(NPN)	-	EV		5 V. 12 V		M9NWV	M9NW	۲	•	•	0	0	IC	
	(2-color	Grommet	Yes	3-wire(PNP)	24 V	5 V, 12 V	-	M9PWV	M9PW	٠	•	•	0	0	circuit	Relay, PLC		
state	indicator)			2-wire		12 V		M9BWV	M9BW	۲	•	•	0	0	—			
ids	Water			3-wire(NPN)		5 V. 12 V		M9NAV**	M9NA**	0	0	•	0	0	IC			
Solid	resistant (2-color			3-wire(PNP)		5 V, 12 V		M9PAV**	M9PA**	0	0	•	0	0	circuit			
	indicator)			2-wire		12 V		M9BAV**	M9BA**	0	0	•	0	0	-			

** Water resistant type auto switches can be mounted on the above models, but in such case SMC cannot guarantee water resistance. * Lead wire length symbols: 0.5 m Nil (Example) M9NW * Auto switches marked with a *O* symbol are produced upon receipt of order.

1 m M (Example) M9NWM

3 m L (Example) M9NWL

5 m Z (Example) M9NWZ

Note 1) When using the 2-color indicator type, please make the setting so that the indicator is lit in red to ensure the detection at the proper position of the air gripper.

180° Angular Type Air Gripper Cam Type **MHY2** Series



Fluid	Air
Operating pressure	0.1 to 0.6 MPa
Ambient and fluid temperature	-10 to 60°C
Repeatability	±0.2 mm
Max. operating frequency	60 c.p.m.
Lubrication	Not required
Action	Double acting
Auto switch (Option) Note)	Solid state auto switch (3-wire, 2-wire)

Note) Refer to pages 797 to 850 for further information on auto switches.

Model

Specifications

Model	Bore size (mm)	Effective gripping force (1) (N·m)	Opening Closing		Weight ⁽²⁾ (g)
MHY2-10D	10	0.16	180°	side	70
MHY2-16D	16	0.54		-3°	150
MHY2-20D	20	1.10			320
MHY2-25D	25	2.28			560

Note 1) At the pressure of 0.5 MPa Note 2) Except auto switch

· Refer to "How to Select the Applicable Model" on page 700.

• Refer to pages 700 and 701 for the details on effective holding force and allowable overhanging distance.

Symbol

1

Double acting: External grip



	Made to Order Order Click here for details									
Symbol	Specifications/Description									
-X4	Heat resistance (100°C)									
-X5	Fluororubber seal									
-X50	Without magnet									
-X53	EPDM for seals, Fluorine grease									
-X63	Fluorine grease									
-X79 Grease for food processing machines, Fluorine										
-X79A	Grease for food processing machines									
-X81A Anti-corrosive treatment of finger										

Moisture Control Tube IDK Series

When operating an actuator with a small diameter and a short stroke at a high frequency, the dew condensation (water droplet) may occur inside the piping depending on the conditions.

Simply connecting the moisture control tube to the actuator will prevent dew condensation from occurring. For details, refer to <u>the IDK series in the</u> <u>Best Pneumatics No.6</u>. MHZ

MHF


MHR Mhk Mhs


MHC MHT MHY -X MRHQ MRHQ D-

Construction

Closed condition


ø**10**







ø16

ø**20**, ø**25**



Open condition





Component Parts

No.	Description	Material	Note	
1	Body	Aluminum alloy	Hard anodized	
2	Piston	ø10: Stainless steel ø16 to 25: Aluminum alloy	ø16 to 25: Chromated	
3	Joint	Stainless steel	Heat treated	
4	Finger	Stainless steel	Heat treated	
5	Сар	Resin		
6	Wear ring	Resin		
7	Shaft	Stainless steel	Nitriding	
8	Bushing A	Sintered alloy steel		
9	Bushing B	Sintered alloy steel		
10	End plate	Stainless steel		

No.	Description	Material	Note
11	Bumper	Urethane rubber	
12	Needle roller	High carbon chrome bearing steel	
13	Joint roller	Carbon steel	Nitriding
14	Rubber magnet	Synthetic rubber	
15	Type C retaining ring	Carbon steel	Phosphate coated
16	Piston bolt	Stainless steel	
17	Piston seal	NBR	
18	Rod seal	NBR	
19	Gasket	NBR	
20	Gasket	NBR	

Replacement Parts


Description		MHY2-10	MHY2-16	MHY2-20	MHY2-25	Main parts	
Seal kit		MHY10-PS MHY16-PS MHY20-PS		MHY20-PS	MHY25-PS	<ø10> 171819 <ø16, ø20, ø25> 17181920	
Finger coombly	MHY2-□D	MHY-A1001	MHY-A1601	MHY-A2001	MHY-A2501		
Finger assembly	MHY2-DD2	MHY-A1001-2	MHY-A1601-2	MHY-A2001-2	MHY-A2501-2	49	
Joint assembly		MHY-A1002	MHY-A1602	MHY-A2002	MHY-A2502	<ø10, ø16> 312	
		WITT ATOOL	WITT ATOO2	WITT A2002	WITT A2302	<ø20, ø25> 31213	
Piston assembly		MHY-A1003	MHY-A1603	MHY-A2003	MHY-A2503	<ø10>26114	
			WITT ATOOD	WITT A2000	WITT A2300	<ø16, ø20, ø25> 26111416	

* Order 1 piece of finger assembly per one unit.

Replacement part/grease pack part no. : MH-G04 (30 g)

180° Angular Type Air Gripper Cam Type **MHY2 Series**

Dimensions




* Do not extend the attachment from limited area for mounting to avoid interference with the attachment or main body.

-X□

MHY2 Series

Dimensions




* Do not extend the attachment from limited area for mounting to avoid interference with the attachment or main body.



¢ 4

180° Angular Type Air Gripper Cam Type **MHY2 Series**





* Do not extend the attachment from limited area for mounting to avoid interference with the attachment or main body.



MHZ

MHF

MHL

MHR

MHK

MHS Mhc

MHT

MHW

-X□


MRHQ

MA

D-🗆

MHY2 Series

Dimensions



* Do not extend the attachment from limited area for mounting to avoid interference with the attachment or main body.