Pressure Gauge with Switch ()

GP46 Series










- A pressure switch function has been added to the gauge.
- The pressure switch is equipped with a light for verifying operation.
- The pressure gauge is equipped with a limit indicator.
- To be used for verifying the supply pressure.


Circuit Example



 Be sure to read the precautions for selection and mounting.

Circuit Diagram

Without indicator light




With indicator light

110, 220 VAC



24 VDC



The arrow in the diagram indicates the direction of the pressure increase. The light turns OFF when the pressure becomes higher than the set pressure and turns ON when the pressure becomes lower than the set pressure.

Standard Specifications

Standard Specifications						
	Model			GP46		
	Туре			Back side thread		
	Ambient and fluid temperature			-5 to 60°C (No freezing)		
Gauge	Indicated pressure rang			0 to 1.0 MPa		
g	Port size (1)			R 1/8, R 1/4 (Option M: with M5 female thread)		
	Fluid (2) (6)			Air		
	Indication precision (7)			±0.03 MPa		
	Setting range (3) (4)			0.1 to 0.8 MPa		
ج	Hysteresis			0.07 MPa		
switch	Pointer error (5)			±0.05 MPa (5 to 40°C)		
				±0.08 MPa (-5 to 60°C) No freezing		
Pressure	Contact			With light: 1a (Normally open)		
l ss				Without light: 1ab (Normally open/ Normally closed)		
ě	Wiring			Lead wire (Length: 300 mm)		
₽	Indicator light	AC		Neon light		
		DC		Light emitting diode (LED)		
	Clear cover			Part no.: G46-00-00-3		
	Attachment: C		С	Part no.: 1305104-4A		
	With cover ring assembly C ₂		C ₂	Part no.: 1305104-10A		
	Weight (kg)			0.12		

Note 1) When mounting a pressure gauge, use caution not to tighten excessively. Excessive tightening will cause product to be damaged. Use a pipe tape for sealing.

Note 2) Water is not an acceptable fluid. When using the other fluids, please consult with SMC for compatibility information concerning corrosion.

Note 3) Set value of pressure switch is indicated by pointer (green). It is the point where the circuit between N.O. (white) and COM (black) is turned off during pressure decrease. To set the value, turn needle in clockwise position to the correct value. When setting; if desired set position has been passed, turn needle in a counterclockwise direction back again beyond the desired value and then once again return needle in a clockwise direction stopping at the desired value. Value must be set while needle is traveling in a clockwise direction.

Note 4) Make sure to provide a minimum difference of 0.1 MPa between the set pressure and the operating pressure (including the pressure drop). If the difference is smaller, it could lead to improper operation. Refer to page 1298 for details on how to set the setting needle. Use caution: Operating pressure should be the sum of the pressure of the setting needle error (±0.03 MPa), the hysteresis (0.07 MPa), and the display accuracy (±0.05 MPa) on the set pressure value, or the circuit between N.O. (white) and COM (black) may not turn ON white pressure is increasing.

Note 5) Maximum error value: Add the pressure gauge indicator error of 0.03 MPa to the setting needle error.

Note 6) Avoid freezing as this may cause a malfunction. Note 7) The guaranteed temperature range is 23°C ±5°C.

Model (Standard)

Model	Pressure range (1) MPa	Indication unit	Connection thread	Note
GP46-10-01 to 02 (-Q)		MPa	R ¹ / ₈ R ¹ / ₄	_
GP46-10-01 to 02L2	0 to 1.0			
GP46-10-01 to 02L5 (-Q)				

Note 1) Do not apply pressure more than the maximum display pressure. This will cause a malfunction.

Model (Made to Order)

Other versions of this unit can be made on a Made-to-Order basis.

Please consult with SMC for details, as delivery times may be extended.

Model	Pressure range (1)		Indication	Connection	Note
Wodel	MPa	psi	unit	thread	Note
GP46-10-01 to 02-X201	0 to 1.0		MPa	R ½ R ½	Lead wire length 3 m
GP46-10-01 to 02L2-X201					
GP46-10-01 to 02L5-X201					
GP46-P10-01 to 02-X30 (2)		0 to 140	MPa, psi		
GP46-P10-01 to 02L5-X30 (2)					

Note 1) Do not apply pressure more than the maximum display pressure. This will cause a malfunction.

Note 2) Under the New Measurement Law, products for overseas use only (SI unit type for use in Japan)


Micro-switch Rated Voltage

Load	Load resistant		
Rated voltage	30 VDC	125 VAC	250 VAC
Operating current range	0.01 to 0.5 A	0.01 to 0.3 A	0.01 to 0.2 A



C E UK

How to Order



switc	ch •	•	2 9 9 5 6	-	
Symbo		Symbol	Description	GP46	
		+			
Δ,	Max. display pressure	10	1.0 MPa	•	
	wax. display pressure	P10 (1)	1.0 MPa, 150 psi	O (2)	
	+				
<u>a</u>	2 Connection thread		R 1/8	•	
9	Connection thread	02	R 1/4	•	
		+ Nil			
A	3 Option		_	•	
9			With M5 (Female thread)	•	
+					
	Suffix for	Nil	Without indicator light	•	
4	indicator light Note 4)	L2	Neon light (100 VAC/220 VAC)	•	
		L5	LED/24 VDC	•	
		+			
		Nil	Without cover ring assembly	•	
6	Attachment Note 5)	С	Clear cover has no protrusion. (Clear cover is irremovable.)	•	
		C2	Clear cover has protrusion. (Clear cover is removable.) The wrench flats protrude.	•	
+					
			_	•	
	Special specification	X30	Both MPa and psi	O (2)	
 0		X201	Lead wire length 3 m	•	
		Q (6)	Compliant with CE/UKCA marking	•	

Note 1) This symbol must be used with Special specification "X30."

Note 2) Under the New Measurement Law, products for overseas use only (SI unit type for use in Japan)

Note 3) To use the pressure gauge with M5 (female thread), attach the joint when piping the tube. For combinations with the special specification products, please consult SMC separately.

Note 4) Please consult with SMC for X30. 220 VAC is not available for -Q.


Note 5) For pressure gauges with the cover ring assembly, it is recommended to select the option M so as to perform the piping.

Note 6) The rated micro switch for CE/UKCA marked products is under the following conditions.

Load	Load resistant			
Rated voltage	30 VDC	125 VAC		
Operating current range	0.01 to 0.5 A	0.01 to 0.3 A		


Dimensions (-Q: With ground terminal on back side) * The dimensions in (): Connection thread R 1/4

GP46-10-01 to 02 (M) (L2,5)



With cover ring assembly (For panel mount) GP46-10-01 to 02 (M) (L2,5)-C

Type C (Clear cover is not removable.)



GP46-10-01 to 02 (M) (L2,5)-C2

Type C2 (Clear cover is removable. The wrench flats protrude.)

