

2-Color Display Digital Pressure Switch ISE70/75/75H Series



2-Color Display (E CA COUS Digital Pressure Switch: For Air RoHS ISE70 Series The ISE70 series has been remodeled. Click here for details.



Option/Part No.

When optional parts are required separately, use the following part numbers to place an order.

Option	Part no.	Note
Bracket	ZS-31-A	Bracket B and the bracket assembly make up one set. Note) Mounting screws are not included. Bracket assembly
Lead wire with M12 connector, straight	ZS-31-B	Lead wire length: 5 m
Lead wire with M12 connector, right-angled	ZS-31-C	Lead wire length: 5 m


2-Color Display Digital Pressure Switch For Air ISE70 Series

Specifications

Refer to pages 11 and 12 for Pressure Switch Precautions. For details about the Specific Product Precautions, refer to the Operation Manual on the SMC website, http://www.smcworld.com Click here for details.

	Model	ISE70	
Rated press	sure range	0 to 1 MPa	
Pressure disp	lay range/Set pressure range	-0.1 to 1 MPa	ZSE20
Withstand p	oressure	1.5 MPa	ISE20
Pressure display resolution/Set pressure resolution		0.01 MPa	ZSE30
Applicable fluid		Air, Non-corrosive gas, Non-flammable gas	ISE30
Power supp	ly voltage	12 to 24 VDC±10%, Ripple (p-p) 10% or less (with power supply polarity protection)	ZSE40
Current con	sumption	55 mA or less (at no load)	ISE40
Switch outp	put	Output -27: 2 settings; NPN open collector 2 outputs (Pin no.: 2, 4) Output -43: Fixed setting; NPN open collector 1 output (Pin no.: 4) + PNP open collector 1 output (Pin no.: 2) Note 1) Output -65: PNP open collector 1 output (Pin no.: 4) Output -67: 2 settings; PNP open collector 2 outputs (Pin no.: 2, 4)	ZSE10 ISE10 ISE70 ZSE80
	Max. load current	80 mA	ISE80
	Max. applied voltage	30 V (at NPN output)	PS
	Residual voltage	1 V or less (with load current of 80 mA)	го
	Response time	2.5 ms (with anti-chattering function: 20 ms, 160 ms, 640 ms, 1000 ms, 2000 ms)	ISA3
	Short circuit protection	With short circuit protection	
Repeatabilit	ty	±0.5%F.S.	ISA2
Hysteresis	Hysteresis mode Window comparator mode	Variable (0 or above)	ISE35
Display		3-digit, 7-segment indicator, 2-color display (Red/Green) can be interlocked with the switch output, Sampling cycle: 5 times/1 s	DOF
Display acc	uracy	2%F.S.±1 digit (at 25°C±3°C)	PSE
Indicator lig	ht	OUT1: Light up when output is turned ON. (Green) OUT2: Light up when output is turned ON. (Red: for output -27, -67)	IS
Functions		Anti-chattering function, Display unit switching function, Zero-clear function, Keylock function	ISG
	Enclosure	IP67 Note 2)	
	Fluid temperature range	0 to 50°C (No freezing or condensation)	ZSM1
Environ-	Operating temperature range	Operating: 0 to 50°C, Stored: -10 to 60°C (No freezing or condensation)	L
ment	Operating humidity range	Operating and stored: 35 to 85%RH (No condensation)	
	Withstand voltage	1000 VAC for 1 minute between terminals and housing	
	Insulation resistance	50 $\text{M}\Omega$ or more (500 VDC measured via megohmmeter) between terminals and housing	
	e characteristics within operating temperature range)	±2%F.S.	
Standards		CE/UKCA marking, UL/CSA (E216656)	
Wetted parts material		Fitting: C3604 (electroless nickel plating) Sensor pressure receiving area: Silicon, O-ring: NBR	
Port size		02: Rc1/4, N02: NPT1/4, F02: G1/4 (ISO 1179) Note 3)	
Lead wire w	rith connector	Oilproof cable with M12 4-pin pre-wired connector, 4 cores, ø4, 5 m, Conductor O.D.: 0.72 mm, Insulator O.D.: 1.14 mm	
Weight		190 g (excluding the lead wire with M12 4-pin pre-wired connector)	

Note 1) The NPN and PNP outputs function for a single set point. Note 2) An FKM gasket is used for the product case seal. Refer to the Operation Manual at SMC's website for details. Note 3) G1/4: Applicable to SD 1179-1



Option/Part No.

When optional parts are required separately, use the following part numbers to place an order.

Option	Part no.	Note
Bracket	ZS-31-A	Bracket B and the bracket assembly make up one set. Bracket B Bracket assembly Note) Mounting screws are not included.
Lead wire with M12 connector, straight	ZS-31-B	Lead wire length: 5 m
Lead wire with M12 connector, right-angled	ZS-31-C	Lead wire length: 5 m



2-Color Display Digital Pressure Switch For General Fluids ISE75/75H Series

Specifications

Refer to pages 11 and 12 for Pressure Switch Precautions. For details about the Specific Product Precautions, refer to the Operation Manual on the SMC website, http://www.smcworld.com Click here for details.

	Model	ISE75	ISE75H		
Rated press	sure range	0 to 10 MPa	0 to 15 MPa		
Pressure disp	ay range/Set pressure range*	0.4 to 10 MPa	0.5 to 15 MPa		
Withstand p	oressure	30 MPa	45 MPa		
Pressure display	resolution/Set pressure resolution	0.1	MPa		
Applicable	fluid	Fluid or gas that will not corrode	stainless steel 304, 430 and 630		
Power supp	ly voltage	12 to 24 VDC±10%, Ripple (p-p) 10% or lo	ess (with power supply polarity protection)		
Current con	sumption		s (at no load)		
Switch outp	ut	Output -27: 2 settings; NPN open collector 2 outputs (Pir	no.: 2, 4) Pin no.: 4) + PNP open collector 1 output (Pin no.: 2) Note 1)		
	Max. load current		mA		
	Max. applied voltage		PN output)		
	Residual voltage		ad current of 80 mA)		
	Response time	2.5 ms (with anti-chattering function: 20 r	,		
	Short circuit protection	· · · · ·	cuit protection		
Repeatabili	•		%F.S.		
	Hysteresis mode	20.0701 10.			
Hysteresis	Window comparator mode	Variable (0 or above)			
Display		3-digit, 7-segment indicator, 2-color display (Red/Green) can be	e interlocked with the switch output, Sampling cycle: 5 times/1 s		
Display accuracy		2%F.S.±1 digit			
		-	tput is turned ON. (Green)		
Indicator lig	Int	OUT2: Lights up when output is turned ON. (Red: for output -27, -67)			
Functions		Anti-chattering function, Display unit switching	function, Zero-clear function, Keylock function		
	Enclosure	IP67	Note 2)		
	Fluid temperature range	-5 to 80°C (No freez	ring or condensation)		
Environ-	Operating temperature range	Operating: -5 to 50°C, Stored: -10 to	o 60°C (No freezing or condensation)		
ment	Operating humidity range	Operating and stored: 35 to	85%RH (No condensation)		
	Withstand voltage	250 VAC for 1 minute betw	veen terminals and housing		
	Insulation resistance	50 M Ω or more (50 VDC measured via megohmmeter) between terminals and housing			
	e characteristics within operating temperature range)	±3%	F.S.		
Standards		CE/UKCA marking, UL/CSA (E216656)			
	Pressure sensor	Stainless	steel 630		
Wetted part material	s Fitting	Stainless steel 304	Stainless steel 304 (port size Rc1/4) Stainless steel 430 (port size NPT1/4, G1/4)		
Port size		02: Rc1/4, N02: NPT1/4, F02: G1/4 (ISO 1179) Note 3)			
Lead wire w	ith connector	Oilproof cable with M12 4-pin pre-wired connector, 4 cores,	ø4, 5 m, Conductor O.D.: 0.72 mm, Insulator O.D.: 1.14 mm		
Weight		225 g	225 g (port size Rc1/4) 210 g (port size NPT1/4, G1/4)		
		145 g (Lead wire with M12	4-pin pre-wired connector)		

Note 1) The NPN and PNP outputs function for a single set point.

Note 2) An FKM gasket is used for the product case seal. Refer to the Operation Manual at SMC's website for details.

Note 3) G1/4: Applicable to ISO 1179-1 * Refer to page 84 for the pressure display range.

ISE70/75/75H Series

Set Pressure Range and Rated Pressure Range


Set the pressure to within the rated pressure range.

The set pressure range is the range of pressure that is possible in setting.

The rated pressure range is the range of pressure that satisfies the specifications (accuracy, linearity, etc.) on the switch. Although it is possible to set a value outside the rated pressure range, the specifications will not be guaranteed even if the value stays within the set pressure range.


Switch		Pressure range						
		-100 kPa	0	0.4 MPa 0	.5 MPa	1 MPa	10 MPa	15 MPa
For 1 MPa (For Air)	ISE70	–100 kPa (–0.1 MPa)	0			1 MPa 1 MPa		
For 10 MPa (For General Fluids)	ISE75		0	4 MPa			10 MPa 10 MPa	
For 15 MPa (For General Fluids)	ISE75H		0	0.5 MF	Pa			15 MPa 15 MPa

* The ISE75(H) switch shows zero (0) when the pressure being applied goes below the lower limit of the set pressure range, when the zero-cut off display function is selected.




Internal Circuits and Wiring Examples

-27 NPN (2 outputs)




-65 PNP (1 output)




-43 NPN (1 output) + PNP (1 output)

(The pressure set point for switching the output signal is common to NPN and PNP.)




-67 PNP (2 outputs)



2-Color Display Digital Pressure Switch ISE70/75/75H Series

Dimensions




ø١

ISE70/75/75H Series

Functions

A Display calibration function

Fine adjustment of the indicated value of the pressure sensor can be made within the range of \pm 5% of the read value. (The scattering of the indicated value can be eliminated.)



Note) When the display calibration function is used, the set pressure value may change ± 1 digit.

B Peak/Bottom hold function

This function constantly detects and updates the maximum and minimum pressure values and allows the unit to hold the display value.

C Keylock function

Prevents operation errors such as accidentally changing setting values.

D Zero-clear function

The measured pressure reading can be adjusted to zero. More specifically, the factory-set reading can be corrected to within $\pm 7\%$ F.S.

E Display unit switching function

Display units can be switched with this function.

Unit/Reading resolution	ISE70	ISE75/75H
MPa	0.01	0.1
kgf/cm ²	0.1	1
bar	0.1	1
psi	1	1 (X10)

F Anti-chattering function

A large bore cylinder or ejector consumes a large amount of air in operation and may experience a temporary drop in the primary pressure. This function prevents detection of such temporary drops in primary pressure as abnormal pressure.

Response time selections: 20 ms, 160 ms, 640 ms, 1000 ms, 2000 ms

H Zero-cut off display function

With the ISE75 series, users can enable or disable a function (zero-cut off display function) that displays pressure values of 0.3 MPa or less as zero (0.4 MPa or less in the ISE75H series).

@SMC

Example pressure displays (shading indicates changed displays)

ISE75- (for 10 MPa)	
Zero-cut off display function "ON": $0 \rightarrow$	Displayed as 0 \rightarrow 0.4 \rightarrow 0.5 \rightarrow 0.6 \rightarrow \rightarrow 9.9 \rightarrow 10.0
Zero-cut off display function "OFF": 0 \rightarrow	$0.1 \rightarrow 0.2 \rightarrow 0.3 \rightarrow 0.4 \rightarrow 0.5 \rightarrow 0.6 \rightarrow \cdots \rightarrow 9.9 \rightarrow 10.0$

ISE75H-D (for 15 MPa)

Zero-cut off display function "ON":	$0 \rightarrow$	Displayed as 0	$\rightarrow 0.5 \rightarrow 0.6 \rightarrow \cdots \cdots \rightarrow$	→ 14.9→ 15.0
Zero-cut off display function "OFF"	$: 0 \rightarrow 0.1$	\rightarrow 0.2 \rightarrow 0.3 \rightarrow 0.4	$\rightarrow 0.5 \rightarrow 0.6 \rightarrow \cdots $	→ 14.9→ 15.0

Pressure Display Range

Series	Zero-cut off display function "ON"	Zero-cut off display function "OFF"
ISE75	0, 0.4 to 10.0 MPa	0 to 10.0 MPa
ISE75H	0, 0.5 to 15.0 MPa	0 to 15.0 MPa

* The set pressure range does not change when the zero-cut off display function is disabled.

G Error function

Take the following corrective actions when error occurs.

Error descri	Error description		Description	Action	
Over-	OUT1	Er l	Load current of switch	Eliminate the cause of the over current by turning off the	
error	Note 1) OUT2	٤r2	output exceeds 80 mA.	power supply, and then turn on it again.	
Residu pressu error		{r}	During zero-clear operation, pressure over ±7% F.S. is applied. After 3 second, the mode will reset to measurement mode. ±1% F.S. of the zero-clear range varies between individual products.	Perform zero-clear operation again after restoring the applied pressure to an atmospheric pressure condition.	
Applied		ннн	Supply pressure exceeds the maximum set pressure.	Reset applied pressure to a level	
error	pressure error		Supply pressure is below the minimum set pressure.	within the set pressure range.	
	ErY		Internal data error		
System	error	٤rð	Internal data error	Turn the power off	
Joystell	01101	Er٦	Internal data error	and turn it on again.	
			Internal data error		

 \ast If the failure cannot be solved after the above instructions are performed, please contact SMC for investigation.

Note 1) Output -27 and -67 only.

ISE75(H) Series Made to Order Specifications Please contact SMC for detailed dimensions, specifications and lead times.



1 Analog Voltage	e Output Specifications -X500	
This product is compatible v	vith NPN open collector 1 output + Analog voltage output.	ZSE20 ISE20
		ZSE30 ISE30
How to Order	* Refer to "How to Order" on page 82 for the standard specification	s. ZSE40 ISE40
ISE75(H) –	- <u>43</u>	ZSE10 ISE10
Piping*●		ISE70
Output	© Option* ●	ZSE80 ISE80
	·	PS
Note) The output is applicable t	3 43 only.	ISA3
		ISA2
Specifications		ISE35
	Output voltage: 1 to 5 V ±2.5% F.S. (In rated pressure range)	PSE
Analog voltage output	Output impedance: Approx. 1 kΩ Response time: 300 ms or less	IS
	2 <u>1</u> 1 Brown DC (+)	ISG
Connector pin number	3 4 4 2 2 4 2 2 4 2 2 4 2 2 4 2 4 2 4 2 4 2 4 2 4 2 4 2 4 2 4 2 4 2 4 2 4 2 4 2 2 4 2 2 2 2 2 2 2 2 2 2 2 2 2	ZSM1

Models other than above are the same specifications as standard.

