
#### Standard: Double Acting, Single Rod


Series 55-CP96 ø32, ø40, ø50, ø63, ø80, ø100





For the  $\emptyset$ 125, refer to page 50-1.

#### How to Order



Cylinder stroke (mm)

40 mm

50 mm

63 mm

80 mm

100 mm

40

50

63

80

100

| Bore size (mm) | Standard stroke (mm)  | Max. stroke* | XC65, XC68<br>Max. stroke |
|----------------|---|--------------|---------------------------|
| 32             | 25, 50, 80, 100, 125, 160, 200<br>250, 320, 400, 500                | 2000         | 1800                      |
| 40             | 25, 50, 80, 100, 125, 160, 200<br>250, 320, 400, 500                | 2000         | 1700                      |
| 50             | 25, 50, 80, 100, 125, 160, 200<br>250, 320, 400, 500, 600           | 2000         | 1700                      |
| 63             | 25, 50, 80, 100, 125, 160, 200<br>250, 320, 400, 500, 600           | 2000         | 1700                      |
| 80             | 25, 50, 80, 100, 125, 160, 200<br>250, 320, 400, 500, 600, 700, 800 | 2000         | 1700                      |
| 100            | 25, 50, 80, 100, 125, 160, 200<br>250, 320, 400, 500, 600, 700, 800 | 2000         | 1700                      |

Intermediate strokes are available.

All other specifications are the same as the standard products Series CP96.

Click here for details.




<sup>\*</sup> Please consult with SMC for longer strokes.

## ATEX Compliant ISO Cylinder Standard: Double Acting, Single Rod


# Series 55-CP96





For the  $\emptyset$ 32,  $\emptyset$ 40,  $\emptyset$ 50,  $\emptyset$ 63,  $\emptyset$ 80, and  $\emptyset$ 100, refer to page 50.

#### **How to Order**



1600

Intermediate strokes are available.

125\*\*

2000

All other specifications are the same as the standard products Series CP96.

Click here for details.



<sup>\*</sup> Please consult with SMC for longer strokes.

<sup>\*\*</sup> Ø125 are produced upon receipt of order.

### Standard: Double Acting, Double Rod

## Series 55-CP96W Ø32, Ø40, Ø50, Ø63, Ø80, Ø100



( (Ex) | II 2G h | IIC T6..T5 Gb | II 2D h | IIIC T80°C..T100°C Db

63

80

100


63 mm

80 mm

100 mm

For the Ø125, refer to page 51-1.

#### How to Order



Cylinder stroke (mm)

| Cylinder stroke (mm) |   |              |  |  |
|----------------------|---|--------------|--|--|
| Bore size (mm)       | Standard stroke (mm)  | Max. stroke* |  |  |
| 32                   | 25, 50, 80, 100, 125, 160, 200<br>250, 320, 400, 500                | 1000         |  |  |
| 40                   | 25, 50, 80, 100, 125, 160, 200<br>250, 320, 400, 500                | 1000         |  |  |
| 50                   | 25, 50, 80, 100, 125, 160, 200<br>250, 320, 400, 500, 600           | 1000         |  |  |
| 63                   | 25, 50, 80, 100, 125, 160, 200<br>250, 320, 400, 500, 600           | 1000         |  |  |
| 80                   | 25, 50, 80, 100, 125, 160, 200<br>250, 320, 400, 500, 600, 700, 800 | 1000         |  |  |
| 100                  | 25, 50, 80, 100, 125, 160, 200<br>250, 320, 400, 500, 600, 700, 800 | 1000         |  |  |

Intermediate strokes are available.


All other specifications are the same as the standard products Series CP96W. Click here for details.



<sup>\*</sup> Please consult with SMC for longer strokes


### Standard: Double Acting, Double Rod

# Series 55-CP96W



For the  $\emptyset$ 32,  $\emptyset$ 40,  $\emptyset$ 50,  $\emptyset$ 63,  $\emptyset$ 80, and  $\emptyset$ 100, refer to page 51.

#### **How to Order**



\*\* ø125 are produced upon receipt of order.


All other specifications are the same as the standard products Series CP96W. Click here for details.



Non-rotating Type: Double Acting, Single Rod

## Series 55-CP96K ø32, ø40, ø50, ø63, ø80, ø100





40

50

63

80

100

40 mm


50 mm

63 mm

80 mm

100 mm

#### **How to Order**



All other specifications are the same as the standard products Series CP96.


Click here for details.




Non-rotating Type: Double Acting, Double Rod

## Series 55-CP96KW

Ø32, Ø40, Ø50, Ø63, Ø80, Ø100





All other specifications are the same as the standard products Series CP96W. Click here for details.

