Flow Switch Diaphragm Type Flow Switch IFW5 Series



The flow switch, IFW series is used for detection and confirmation of the flow as a relaying device for the general water applications in some various equipment such as cooling water fixture in the industrial machinery.

- Low flow setting possible (1 L/min)
- Simple flow setting

Without removing the cover, you can set with a screwdriver from the outside.





How to Order

Note) Terminal box for 24 VDC is available for 5, 6 (LED light).

Specifications

Fluid	Water/Non-corrosive liquid *			
Operating pressure	0.1 to 0.6 MPa			
Water resistance	1.2 MPa			
Operating temperature range	-5 to	60°C (No freezing)		
Operation	[Diaphragm type		
Insulation resistance	100 MΩ or more (500	or more (500 VDC measured via megohmmeter)		
Withstand voltage	1500 VAC for one min.			
Contract	Without terminal box: 1ab			
Contact	With terminal box: 1a or 1b			
Port size	3/8, 1/2, 3/4			
	Body	CAC408		
Body material in contact with fluid material	Rod	C3604B		
	Diaphragm	NBR Note)		

About the use of *, please confirm SMC.

Note) For ozone environments, select the -X404.

Micro Switch Ratings

	Non inductive load (A)				Inductive load (A)			
Voltage	Load re	Load resistance Light load		Inductive load		Motor load		
	N.C.	N.O.	N.C.	N.O.	N.C.	N.O.	N.C.	N.O.
125 VAC	5	5	1.5	0.7	4	4	2.5	1.3
250 VAC	5	5	1	0.5	4	4	1.5	0.8
8 VDC	7	5	3	3	5	4	3	3
14 VDC	5	5	3	3	4	4	3	3
30 VDC	5	5	3	3	4	4	3	3
125 VDC	0.4	0.4	0.1	0.1	0.4	0.4	0.1	0.1
250 VDC	0.3	0.3	0.05	0.05	0.3	0.3	0.05	0.05

Construction/Working Principle



Working Principle

Liquid flow creates a pressure differential nearby the orifice of the port of the body ①. One set of diaphragms monitors the pressure differential and operates the micro switch through the rod 2 and operating lever 4.

The rod (2) moves downward with increased flow, and upward with decreased flow. Moving the gear (5) upward or downward by the adjusting gear (3) manually offers an electric signal at various flow rates.

Component Parts

No.	Description Material	
1	Body CAC408	
2	Rod	C3604B
3	Gear	POM

No.	Description	Material
4	Operating lever	SPCC
5	Adjusting gear	POM

Model

Model	Flow range (L/min)	Max. flow (L/min)	Hysteresis (L/min)
IFW510	1 to 10	20	1 or less
IFW520	10 to 20	25	1.5 or less
IFW550	20 to 50	60	3 or less

Note) Hysteresis is the flow rate that is necessary for moving the microswitch from the operation position (ON signal) to the return position (OFF signal).

Flow Rate Characteristics









IF

IFW5 Series

Dimensions

IFW500-00 to 04 (Without terminal box)





IFW500-0-10 to 24 (With terminal box)







Dimensions





PFM
PFMB
PFMC
PFMV
PF2A
PF3W
LFE
PF2D
IF

IFW5 Series

Internal Wiring Diagram

IFW50-0-00/10/20

<u>C (COM)</u> A (NO)	Symbol	Contact	Color of lead wire
	С	Common	Black
\rightarrow	Α	Normally Open	White
B (NC)	в	Normally Closed	Red

IFW500-001 to 04/11 to 14/21 to 24

C (COM)

A (NO) Color of Symbo Contact ad wire с Common Black Α Normally Open White R Red Normally Closed B (NC)

IFW500-00-55/56



Symbol		Contact	Color of lead wir
[1	Power supply (Common)	Black
	2	Terminal (Relay terminal)	Red
[3	Power supply (Light terminal)	Blue

IFW500-0-65/66

24 VDC NC NC Æ

Symbol	Contact	Color of lead wire
1	Power supply (Common)	Black
2	Terminal (Relay terminal)	White
3	Power supply (Light terminal)	Blue

IFW500-00-75/76



Symbol	Contact	Color of lead wire
1	Power supply (Common)	Black
2	Terminal (Relay terminal)	Red
3	Power supply (Light terminal)	Gray

IFW500-0-85/86



ł	Symbol	Contact	Color of lead wire
	1	Power supply (Common)	Black
	2	Terminal (Relay terminal)	White
l	3	Power supply (Light terminal)	Gray

@SMC

Precautions

----Be sure to read this before handling the products. н Refer to back page 50 for Safety Instructions and pages 202 and 203 for Flow Switch Precautions.

Mounting & Wiring

▲Caution

- 1. Mount a switch, so that the liquid flow is in the same direction as that of the arrow on the body.
- Be sure to fill the passage with the fluid.
- 3. The flow switch can be installed either horizontally or vertically.
- 4. Provide a straight pipe portion that corresponds to approximately 5 times the bore of the pipe before and after the area of the pipe on which the product is installed, thus keeping the product as far away as possible from the elements that disturb the flow, such as elbows or valves.
- 5. For wiring, refer to the internal wiring diagram.
- 6. If a terminal box is not available, wire by selecting the contact at 1a or 1b. At that time, insulate the lead wires that will not be used
- 7. Because this is an open type, it cannot be used where water or oil splashes
- 8. It cannot be used if a water hammer or pulsation pressure is applied to the fluid.
- 9. In order to prevent a malfunction or diaphragm damage caused by debris or cutting chips in the fluid, install a filter with approximately 100 mesh on the inlet side of a flow switch.

Adjusting

∆Caution

- 1. To adjust flow, remove grommet of the upper cover and rotate flow adjusting gear using a flat head screwdriver. Turning clockwise can increase the set flow and turning counterclock can decrease the set flow.
- 2. The flow rate setting point is set at the ON flow rate. Therefore, in the case of the 1a contact, the ON signal is output if fluid with a higher flow rate than the set flow rate has occurred. In the case of the 1b contact, the ON signal is output when the flow rate has decreased from the set flow rate for the amount that corresponds to the hysteresis.
- 3. To prevent the chattering that is associated with the fluctuation of the operating flow rate, set the difference between the set flow rate and the operating flow rate so that it is as large as possible
- 4. Use at or below the maximum operating pressure and maximum flow rate.
- 5. The indicator on the window name plate (Fig. 1) is only a guideline. For precise setting, mount a flow meter on the downstream side of the flow switch, and set the level.

Also, when setting levels with a low flow rate at pressures of 0.2 MPa or more, there may be interference between the indicator needle and the scale plate. In such cases, detach the indicator needle and scale plate before setting. After setting, the indicator needle and scale plate can be reattached in positions of your choice.



Fig. 1 Window name plate