## **Made to Order Common Specifications:** -XB20: Stroke Adjustment Unit with Adjustment Bolt



### Stroke Adjustment Unit with Adjustment Bolt

Symbol -XB20

Stroke adjustment unit with an adjustment bolt.

**Applicable Series** 

ı	Series	Description	Model	Action	Vol. no. (for std model)
I	MY2	Mechanically jointed	MY2H	Linear guide (Single axis)	Web Catalog
ı	IVI T Z	rodless cylinder	MY2HT	Linear guide (Double axes)	web Catalog

#### How to Order

MY2H MY2HT

Standard model no.

-XB20

#### Stroke Adjustment Unit Specifications


Bore size	e (mm)	1	6	2	5	4	40		
Unit symbol		L	Н	L	Н	L	Н		
Shock absorber	MY2H	RB0806	RB1007	RB1007	RB1412	RB1412	RB2015		
model	MY2HT	RB1007	RB1412	RB1412	RB2015	RB2015	RB2725		
Stroke adjustment	Without spacer	0 to	-5.6	0 to -	-11.5	0 to	-16		
range by intermediate fixing	With short spacer	−5.6 to	-11.2	-11.5	to -23	-16 to -32			
spacer (mm)	With long spacer	-11.2 t	o –16.8	-23 to	-34.5	−32 to −48			



<sup>\*</sup> Stroke adjustment range is applicable for one side when mounted on a cylinder.


#### Stroke adjustment unit mounting diagram





#### Stroke Adjustment Unit Model

Note) Stroke adjustment unit with adjusting bolt (-XB20) cannot be mounted on the standard cylinder.



#### Unit part no.

Symbol	Stroke adjustment unit	Mounting position
L1	L unit	For left
L2	L unit	For right
H1	H unit	For left
H2	n uniit	For right

#### With adjustment bolt Intermediate fixing

spacer

Without spacer Short spacer Long spacer

> Spacer shipping method Nil Assembled as a unit Spacer only Spacers for MY2HT are shipped


in 2 piece sets. \* Intermediate fixing spacers

are shipped together.


### Place the protruding section on the stroke adjustment unit side MY2HT (-XB20) Stroke adjustment unit mounting

mounting bracket


MY2H (-XB20)




#### **Components Parts**



#### MY2H-A25L2-6-XB20 (With short spacer)



#### MY2H-A25L2-7-XB20 (With long spacer)



Holder mounting bracket

#### MY2H-A25L2-6N-XB20 (Short spacer only)



MY2H-A25L2-7N-XB20 (Long spacer only)



Nuts are installed onto the cylinder body.

# Made to Order Common Specifications:

# -XB20: Stroke Adjustment Unit with Adjustment Bolt




# 12 Stroke Adjustment Unit with Adjustment Bolt

-XB20


#### Dimensions (Dimensions other than below are the same as standard type.)

#### MY2H L unit




Applicable cylinder	Е	EA	EC	ED	EY	FA	FB	h	S	Т	SD	TT	W	Shock absorber model	Adjusting bolt	Adjustment range
MY2H16	15.8	8.4	6.2	5	28	12.4	30	3.2	40.8	6	1.3	4.2 (Max. 9.8)	34.5	RB0806	M5 x 0.8 x 25L	5.6
MY2H25	19.6	10.6	10	5.5	37	19.3	44.8	4	46.7	7	_	5 (Max. 16.5)	47.3	RB1007	M8 x 1.0 x 35L	11.5
MY2H40	29	16	13	8	57	17	49	5	67.3	12	_	6 (Max. 22)	59	RB1412	M10 x 1.0 x 50L	16

#### MY2H H unit



Applicable cylinder	Е	EA	EC	ED	EY	FA	FB	h	S	SD	Т	TΤ	W	Shock absorber model	Adjustment bolt	Adjustment range
MY2H16	15.8	8.4	6.2	5	28	12.4	30	3.2	46.7	7.2	7	4.2 (Max. 9.8)	35.5	RB1007	M5 x 0.8 x 25L	5.6
MY2H25	19.6	10.6	10	5.5	37	19.3	44.8	4	67.3	18.2	12	5 (Max. 16.5)	52.8	RB1412	M8 x 1.0 x 35L	11.5
MY2H40	29	16	13	8	57	17	49	5	73.2	-	15	6 (Max. 22)	59	RB2015	M10 x 1.0 x 50L	16



#### **⚠** Caution

Since the dimension EY of the unit is greater than the table top height (dimension H), when a workpiece is loaded that is larger than the full length (dimension L) of the slide table, allow a clearance of size "a" or larger at the workpiece side.

Applicable cylinder	а	EY	Н
MY2H16 L/H Unit	1	28	28
MY2H25 L/H Unit	1	37	37
MY2H40 L/H Unit	0	57	58



# **Made to Order Common Specifications:**


# -XB20: Stroke Adjustment Unit with Adjustment Bolt



## 12 Stroke Adjustment Unit with Adjustment Bolt


Symbol -XB20

#### Dimensions (Dimensions other than below are the same as standard type.)




Applicable cylinde	r E	EA	EB	EC	ED	EY	FA	FB	h	S	SD	Т	TT	W	Shock absorber model	Adjustment bolt	Adjustment range
MY2HT16	15.8	8.4	21	9	5	28	46.5	67	3.2	46.7	7.2	7	4.2 (Max. 9.8)	40.6	RB1007	M5 x 0.8 x 25L	5.6
MY2HT25	19.6	10.6	26.6	12.2	5.5	37	64.8	93.6	4	67.3	18.2	12	5 (Max. 16.5)	57.2	RB1412	M8 x 1.0 x 35L	11.5
MY2HT40	29	16	37	18.2	8	58	74.5	110.5	5	73.2	_	15	6 (Max. 22)	71.6	RB2015	M10 x 1.0 x 50L	16

#### MY2HT H unit



Applicable cylinder	Е	EA	EB	EC	ED	EY	FA	FB	h	S	SD	Т	TT	W	Shock absorber model	Adjustment bolt	Adjustment range
MY2HT16	15.8	8.4	21	9	5	28	46.5	67	3.2	67.3	27.8	12	4.2 (Max. 9.8)	40.6	RB1412	M5 x 0.8 x 25L	5.6
MY2HT25	19.6	10.6	26.6	12.2	5.5	37	64.8	93.6	4	73.2	24.1	15	5 (Max. 16.5)	57.2	RB2015	M8 x 1.0 x 35L	11.5
MY2HT40	29	16	37	18.2	8	58	74.5	110.5	5	99	24.5	25	6 (Max .22)	71.6	RB2725	M10 x 1.0 x 50L	16



#### ♠ Caution

Since the dimension EY of the unit is greater than the table top height (dimension  $\mathbf{H}$ ), when a workpiece is loaded that is larger than the full length (dimension L) of the slide table, allow a clearance of size "a" or larger at the workpiece side.

Applicable cylinder	а	EY	Н
MY2HT16 L/H Unit	1	28	28
MY2HT25 L/H Unit	1	37	37
MY2HT40 L/H Unit	1	58	58

# Made to Order Common Specifications: -XB20: Stroke Adjustment Unit with Adjustment Bolt



### 12 Stroke Adjustment Unit with Adjustment Bolt

Symbol -XB20

#### XB20 (Stroke Adjustment Unit with Adjustment Bolt)

#### 

#### <Stroke adjustment with adjusting bolt>


1. Loosen the lock nut for the adjustment bolt and adjust a stroke by rotating the adjustment bolt.


After adjusting the stroke, secure the adjustment bolt by tightening the lock nut.

If the effective stroke of the shock absorber is shortened by the stroke adjustment, its absorption capacity will be drastically reduced. Therefore, the adjustment bolt should be secured at a position where it projects about 0.5 mm farther than the shock absorber.

(N1.m)

Tighten shock absorber holding bolts equally with the specified tightening torque.






Tightening Torque for Stroke Adjustment Unit Holding Bolt

	are its out the	, .ujuo		(14 111)					
Bore size	MY	/2H	H MY2HT						
(mm)	L unit	H unit	L unit	H unit					
16		0.6							
25		1.	.5						
40	5.0								

#### Tightening Torque for Shock Absorber Holding Bolt (N·m)

Bore size	MY	′2H	MY2HT				
(mm)	L unit	L unit H unit L unit					
16	0.6						
25	1.5	.5					
40	5.0	1.5	5.0				



2. Do not use the shock absorber and air cushion together.

