
Made to Order Common Specifications:

-XC71: Helical Insert Thread Specifications





52 Helical Insert Thread Specifications

Symbol -XC71

Helical insert thread specifications

The guide body mounting threads are helical insert threads.

Applicable Series

Series	Description	Model	Action	Note	Vol. no. (for std model)
MGG	Guide cylinder	MGG	Double acting		Web Catalog

How to Order

MGG Bearing type B

Stroke

Specifications

Applicable series	MGG□B	
Bore size (mm)	20, 25, 32, 40, 50	
Mounting type	Basic type	
Specifications other than above	Same as standard type	


Bore size

Basic type

Dimensions (Dimensions other than below are the same as standard type.)


Port thread type

ø20 to ø50



	(11111)		
Bore size (mm)	н	AF	
20	M6 x 1 depth 12	M5 x 0.8 depth 7.5	
25	M8 x 1.25 depth 16	M6 x 1 depth 9	
32	M8 x 1.25 depth 16	M6 x 1 depth 9	
40	M10 x 1.5 depth 20	M8 x 1.25 depth 12	
50	M12 x 1.75 depth 24	M10 x 1.5 depth 15	

Auto switch



Symbol

53 Without Built-in Auto Switch Magnet This cylinder type does not have built-in auto switch magnet.

Applicable Series

Series	Description	Model	Action	Note	Vol. no. (for std model)
MGG	Guide cylinder	MGG	Double acting		Web Catalog

How to Order

MGG Standard model no.

Without built-in auto switch magnet

Specifications

-p		
Applicable series	MGG	
Bore size (mm)	20, 25, 32, 40, 50	
Auto switch	Not mountable	
Specifications other than above and external dimensions	Same as standard type	

