Vacuum Flow

ZH□-□□-*X185, X341*

By supplying compressed air,


Large blow and vacuum flow rate available



A discharge flow rate 4 times the supply air can be generated. Contributes to reduction in flow consumption if discharge requires flow rate.




 Large passage diameter available for suction of machining chips, particles, etc.





RoHS

● A vacuum flow rate 3 times the supply air A suction flow rate 3 times the supply air can be generated.




New Body material is selectable.

(Aluminum alloy, Stainless steel)

- Dust bag available
- Mounting bracket available
- Maintenance free

No regular motor maintenance is necessary compared with an electric blower.




SMC does not guarantee the entire system. Please think the system shown above as an example. A workpiece that is harder than the body material may damage to the inside of the body, causing the performance to lower. The compatibility should be judged by the customer before adopting the product.



How to Order





⚠ Warning

1. Because suctioned matter is elected together with exhaust, do not direct an exhaust port at a person or equipment.

40 42

2. Do not use in an atmosphere having corrosive gases. chemicals, sea water, water steam, or where there is direct contact with any of these.

⚠Refer to back page 50 for Safety Instructions and pages 49 to 51 for Vacuum Equipment Precautions.

Specifications


| Model | ZH10 | ZH20 | ZH30 | ZH40 |
|---|---|-------------|-------------|--------------|
| Seal material | NBR | | | |
| Bracket material | Steel | | | |
| Hose band material | Stainless steel | | | |
| Dust bag material | Polyester | | | |
| Dust bag filtration [µm] | 10 | | | |
| Passage diameter [mm] | ø13 | ø21.6 | ø30 | ø42 |
| C [dm3/(s-bar)] (Effective area [mm2])Note 1) | 0.49 (2.46) | 1.04 (5.19) | 1.97 (9.86) | 3.69 (18.47) |
| Fluid | Air | | | |
| Supply pressure range [MPa] | 0 to 0.7 | | | |
| Ambient and fluid temperatures [°C] | -5 to 80 (with no freezing or condensation) | | | |
| Bracket assembly | ZH-BK1-10-A | ZH-BK1-20-A | ZH-BK1-30-A | ZH-BK1-40-A |
| Dust bag assembly | ZH-DB1-10-A | ZH-DB1-20-A | ZH-DB1-30-A | ZH-DB1-40-A |
| | | | | |


Note 1) The C value as well as the effective area is a theoretical value


Weight


| Model/Body material | Weight [g]Note 2) | | | | | | |
|---|-------------------|-------------|-------------|-------------|--|--|--|
| ZH - - X185 [Aluminum alloy] | 92 (101) | 417 (436) | 929 (990) | 1847 (1966) | | | |
| ZH□-□□-X341 [Stainless steel] | 271 (280) | 1230 (1250) | 2740 (2800) | 5440 (5560) | | | |
| Note 2) (): Weight including the bracket | | | | | | | |

Exhaust Characteristics









Note 4) The above characteristics are when the discharge outlet is under atmospheric pressure.

Note 5) Back pressure increase should be avoided if you mount a filter or some devices to catch the suctioned particles on the suction outlet side of this product

Note 3) Suction flow rate is a theoretical Recommended Sonic Conductance and Solenoid Valves (Reference)

| | Model | ZH10-□□ | ZH20-□□ | ZH30-□□ | ZH40-□□ |
|----|--------------------------------------|--|--|--|---|
| | C [dm ² /(s-bar)] Note 6) | 1.48 or more | 3.12 or more | 5.92 or more | 11.08 or more |
| е | Solenoid valve (Reference) | VQZ200 | VP300 | VP500 | VP700 |
| t. | | Sonic conductance C [dm³/(s-bar)]: 1.7 | Sonic conductance C [dm³/(s·bar)]: 4.2 | Sonic conductance C [dm³/(s·bar)]: 8.9 | Sonic conductance C [dm³/(s·bar)]: 15.3 |

Note 6) This is the total recommended value for all devices on the upstream side including the piping to the valve and vacuum flow

ZCUK AMJ

AFJ

AMV

ZH -X185

ZH □-□ □-*X185, X341*

Е

15 18.5 23.5

32

F

øB ØC D

73 34 19 10 12.2 16.2 69.8 31

119.5 55

G H

111

G H

25 27.2 33.5 196.8 74.5 6

48

(mm)

250

٧

310

10 500


UV

200

Т

8 400

Dimensions



Κ

35 27

56 48

M N

56.5 29

35 18

4.5

P Q R Sa

21.6 Rc1/4


44 M4 x 0.7

13 Rc1/8 28 M3 x 0.5 5 300 150 190

ZH₄₀-□□

ZH10-

ZH20-□□



Note 1) This thread portion is intended for use in manufacturing processes. Applying rotational torque to the thread or using it for mounting may result in a change in the characteristics of the product at the time of shipment. Therefore, do not apply rotational torque to the thread or use it for mounting.

Note 2) It is recommended that you use hoses that have an I.D. of øC and are made of a soft material as the hoses to be connected to the suction port and the discharge port. The use of commercially available hose bands to secure the hoses will ensure more reliable hose connections. Please note that the characteristics of the suction flow and discharge flow may change according to hose length.

5

90 78 6.5 92

N

47 2.3

Q R Sa Sb T

42 Rc3/8

Model

ZH30-□□

ZH40-□□

øB øC D