
## 39 With Coil Scraper

It gets rid of frost, ice, weld spatter, cutting chips adhered to the piston rod, and protects the seals, etc.

#### **Applicable Series**

Series	Description	Model	Action	Note	Vol. no. (for std model)
	Air cylinder	CM2-Z	Double acting, Single rod	Except with air cushion	
CM2	CM2W-Z		Double acting, Double rod	Except with air cushion	
	Cylinder with end lock	CBM2	Double acting, Single rod	Lock in head end only (Except with air cushion)	
CG1	Air cylinder	CG1-Z1	Double acting, Single rod		
cui	Air cylinder	CG1-Z	Double acting, Single rod		
мв	Air a diadar	MB-Z	Double acting, Single rod	Except ø125	
	Air cylinder	MBW-Z	Double acting, Double rod	Except ø125	
MD4	Air a diadar	MB1-Z	Double acting, Single rod	Except ø125	
MB1	Air cylinder	MBW-Z	Double acting, Double rod	Except ø125	
		CA2-Z	Double acting, Single rod		
CA2	Air cylinder	CA2W-Z	Double acting, Double rod		
	Cylinder with end lock	CBA2	Double acting, Single rod		
004		CS1	Double acting, Single rod		
CS1	Air cylinder	CS1W	Double acting, Double rod		_
CS2		CS2 Double acting, Single rod			_
052	Air cylinder	CS2W	Double acting, Double rod		
		CQ2-Z	Double acting, Single rod	Applicable to ø32 to ø100	Web Catalog
CQ2	Compact cylinder CQ2W		Double acting, Double rod	Applicable to ø32 to ø100	
CQ2		CQP2	Double acting, Single rod	Applicable to ø32 to ø100, Except with bracket	
	Long stroke	CQ2-Z	Double acting, Single rod	Applicable to ø32 to ø100	
RQ	Compact cylinder with air cushion	RQ	Double acting, Single rod	Applicable to ø32 to ø100	
	O dia da unida la alc	MWB	Double acting, Single rod		
MWB	Cylinder with lock	MWBW	Double acting, Double rod		
	Lock unit	MWB-UT	—	Both sides are equipped with a coil scraper	
CNA2	Cylinder with lock	CNA2	Double acting, Single rod		
CNG	Cylinder with lock	CNG	Double acting, Single rod		
CLS	Cylinder with lock	CLS	Double acting, Single rod	Applicable to ø125 to ø160 (ø180 to ø250 as standard)	
CLQ	Compact cylinder with lock	CLQ	Double acting, Single rod	Applicable to ø40 to ø100	
		MGPM-Z	Double acting	Applicable to ø20 to ø100	7
MGP	Compact guide cylinder MGPL-Z		Double acting	Applicable to ø20 to ø100	7
		MGPA-Z	Double acting	Applicable to ø20 to ø100	1
MGG	Guide cylinder	MGG	Double acting	Applicable to ø32 to ø100	1
MGC	Guide cylinder	MGC	Double acting	Applicable to ø32 to ø50	1

#### How to Order



\* For MGP series, refer to page 1542.

#### Specifications: Same as standard type



Symbol

-XC35


## 39 With Coil Scraper

Symbol -XC35

Made to Order


#### Dimensions (Dimensions other than below are the same as standard type.)

#### **MNB** series



Bore size (mm)	F	Н	ZZ
32	16	47	205
40	18	56	221
50	19	63	250
63	19	63	264
80	25	77	326
100	25	77	346


#### **CLS** series



Bore size (mm)	Н	ZZ	
125	120	355	
140	120	355	
160	130	398.5	

\* ø180 to ø250: A coil scraper is attached as standard.

#### **CLQ** series



Bore size	Stroke range		Α		
(mm)	(mm)	Without auto switch	With auto switch	<b>-</b>	T1 h9
40	10 to 50	75.5	85.5	12	28_0.052
40	75,100	85.5	65.5	12	20_0.052
50	10 to 50	78.5	88.5	13	35_0_02
50	75,100	88.5	00.5		35_0.062
63	10 to 50	87	97	13	35_0.062
63	75,100	97	97		35_0.062
80	10 to 50	101.5	111.5	15	43_0_02
80	75,100	111.5	111.5	15	43_0.062
100	10 to 50	120	130	17	59_0 074
100	75,100	130	130	17	09 <sub>-0.074</sub>

Creations


## 39 With Coil Scraper



fade 1


Orde

(mm)



Specificatio	JNS			
Applicabl	e series	MGPM	MGPL, MGPA	
Bearing type		Slide bearing	Ball bushing bearing	
Bore size (mm	1)	20, 25, 32, 40, 50, 63, 80, 100		
Minimum operating	With single end	0.12 MPa		
pressure	With both ends	0.14 MPa		
Specifications of	other than above	Same as standard type		

#### Dimensions (Dimensions other than below are the same as standard type.)



(mm)

# Construction of the stroke str

For cylinder with both sides scraper

MGPM	MGPM (Slide bearing) A, E, HT Dimensions								
Dana sina		Α			Е				
Bore size (mm)	50 st	Over 50 st	Over	50 st	Over 50 st	Over	HT		
((1111))	or less	to 200 st	200 st	or less	to 200 st	200 st			
20	63	87.5	120	0	24.5	57	80		
25	63.5	87.5	119.5	0	24	56	93		
32	85	103.5	139.5	15.5	34	70	110		
40	85	103.5	139.5	9	27.5	63.5	118		
50	98.5	119.5	160.5	16.5	37.5	78.5	146		
63	98.5	119.5	160.5	11.5	32.5	73.5	160		
80	114.5	141.5	190.5	8	35	84	199		
100	136.5	161.5	200.5	10.5	35.5	74.5	236		

#### MGPL, MGPA (Ball bushing bearing) A, E, HT Dimensions

	Α				E					
Bore size (mm)	30 st	Over 30 st	Over 100 st	Over	30 st	Over 30 st	Over 100 st	Over	HT	
()	or less	to 100 st	to 200 st	200 st	or less	to 100 st	to 200 st	200 st		
20	69	86	110	127.5	6	23	47	64.5	80	
25	75.5	91.5	110.5	127.5	12	28	47	64	93	
	Α			E						
Bore size	50 st	Over 50 st	Over 100 st	Over	50 st	Over 50 st	Over 100 st	Over	HT	
(mm)	or less	to 100 st	to 200 st	200 st	or less	to 100 st	to 200 st	200 st		
32	89.5	106.5	126.5	148.5	20	37	57	79	110	
40	89.5	106.5	126.5	148.5	13.5	30.5	50.5	72.5	118	
50	101.5	122.5	142.5	169.5	19.5	40.5	60.5	87.5	146	
63	101.5	122.5	142.5	169.5	14.5	35.5	55.5	82.5	160	
-										

	A				E				
Bore size	25 st	Over 25 st	Over 50 st	Over	25 st	Over 25 st	Over 50 st	Over	HT
(mm)	or less	to 50 st	to 200 st	200 st	or less	to 50 st	to 200 st	200 st	
80	114.5	138.5	168.5	201.5	8	32	62	95	199
100	129.5	155.5	188.5	211.5	3.5	29.5	62.5	85.5	236

#### Common Dimensions: MGPM, MGPL, MGPA

Bore size		B DA		FC		
(mm)	P			MGPM	MGPL MGPA	
20	63	10	18	5	5	
25	63.5	10	17	6	5	
32	69.5	14	22	6	5	
40	76	14	22	6	5	
50	82	20	26	6	5	
63	87	20	26	6	5	
80	106.5	25	34	8	6	
100	126	30	41	9	6	

With Both Sides Scraper Dimensions:


AW, EW, FD, WII (mm							
Bore size (mm)	AW	EW	FD	мт			
20	74	6	5	6			
25	74.5	6	5	7			
32	82.5	7	6	9			
40	89	7	6	8.5			
50	95	7	6	11			
63	100	7	6	11			
80	120.5	8	6	14			
100	143	8	9	16			



## 39 With Coil Scraper



#### How to Order




Specifications: Same as the standard type of each series Note 1) Except 020 and 025

Note 2) Coil scrapers are attached to the piston rod and guide rods (front and back).

#### Dimensions (Dimensions other than below and the MGG B series (Ø63 to Ø100) are the same as standard type.)


#### MGG B series



	(mm)
Bore size (mm)	AL
32	9
40	12
50	12

#### MGC□B series

ø32 to ø50




	(mm)
Bore size (mm)	AL
32	9
40	12
50	12

## 39 With Coil Scraper

Dimensions (Dimensions other than below are the same as standard type.)

#### CG1-Z1 series CG1-Z series




									(mm)
Bore	Str	oke range	FA	ŀ	-	ь.	м	Z	Z
size	CG1-Z1	CG1-Z	FA	Male thread	Female thread	12	IVI	Male thread	Female thread
20		Up to 200 (up to 1500)	6	39	27	26	4	110 (118)	98 (106)
25		Up to 1000 Up to 300 (up to 1500)	6	44	28	31	5	115 (123)	99 (107)
32	Up to		6	44	28	38	5	117 (125)	101 (109)
40	1000		7	54	29	47	3.5	134 (143)	109 (118)
50	1		7	62	30	58	4.5	154 (166)	122 (134)
63			7	62	30	72	5.5	154 (166)	122 (134)

Note) (): CG1-Z long stroke


 On the axial foot and rod side flange types, the mounting bracket is wedged and bolted between the cylinder and the scraper at the time of shipment. Others are shipped together (but not assembled).

#### The dimensions of the CS2 series are the same as the standard type.



Bore size	With	out auto s	switch	With auto switch		itch
(mm)	F	н	ZZ	F	н	ZZ
125	50	120	245	50	120	245
140	50	120	245	50	120	245
160	50	130	266.5	50	130	266.5
180	55	145	291	55	145	295
200	55	145	291	55	145	300
250	69	175	357.5	_	_	—
300	69	190	387.5	—	_	—

#### MB series




#### **MB1** series



		(mm)
Bore size	н	ZZ
32	47	135
40	58	146
50	67	165
63	67	165
80	81	199
100	81	199

		(mm)
Bore size	Н	ZZ
32	47	135
40	58	146
50	67	165
63	67	165
80	81	199
100	81	199

#### CQ2 series



		Α		L		
Bore size	Standard type, A	Axial piping type	Long stroke	Standard type, Axial piping type	Long stroke	т
	50 stroke or less	75, 100 stroke	125 to 300 stroke	100 stroke or less	125 to 300 stroke	
32	35 (45)	45	62.5	12	17	23 <sup>+0</sup> -0.052
40	41.5 (51.5)	51.5	72	12	17	28 <sup>+0</sup> -0.052
50	43.5 (53.5)	53.5	73.5	13	18	35+0 -0.062
63	49 (59)	59	75	13	18	35 <sup>+0</sup> -0.062
80	58.5 (68.5)	68.5	86	15	20	43-0.062
100	70 (80)	80	97.5	17	22	59 <sup>+0</sup> -0.074

\* (): Denotes the dimensions with auto switch magnet.



nade t


Order

(mm)


## 39 With Coil Scraper

#### Dimensions (Dimensions other than below are the same as standard type.)


#### CQ2W series




#### **RQ** series




#### **CBA2** series



#### **CNG** series







			(mm)	
Bore	A			
size	50 stroke or less	75, 100 stroke	<b>_</b>	
32	54.5 (64.5)	64.5	12	
40	64 (74)	74	12	
50	66.5 (76.5)	76.5	13	
63	68 (78)	78	13	
80	81 (91)	91	15	
100	94.5 (104.5)	104.5	17	

\* (): Denotes the dimensions with auto switch magnet.

			(mm)
Bore size (mm)	Α	В	Th9
32	49	37	23 _0_052
40	56	44	28 _0.052
50	62.5	49.5	35 _0.062
63	68	55	35 _0.062
80	78.5	63.5	43 _0.062
100	93	76	59 _0.074

(mm)

Dere size (mm)	øe	f
Bore size (mm)	Øe	With rod side locking, With both-side locking
40	28	14.5
50	32	16.5
63	32	14
80	37	16
100	44	17.5

The above diagram shows the rod side locking and manual releasing non-locking types.

The CBA2 series head side locking type is the same as the standard type. The dimensions of the manual releasing non-locking type are the same as indicated above.

Bore size (mm)	FA	M	12	Н	ZZ
20	6	4	26	39	182
25	6	5	31	44	197
32	6	5	38	44	200
40	7	3.5	47	54	225
					190
			Long	stroke	205
20					

type with a rubber bumper.)

\* On the axial foot and rod side flange types, the mounting bracket is wedged and bolted between the cylinder and the scraper at the time of shipment.

Bore size (mm)	е	f
40	28	12
50	32	12.5
63	32	12.5
80	37	16.5
100	44	17



Symbol

-XC35

**SMC**