21 Adjustable Stroke Cylinder/Adjustable Retraction Type

Symbol

The retract stroke of the cylinder can be adjusted by the adjustment bolt.

Applicable Series

Series	Description	Model	Action	Note	Vol. no. (for std mode
	Air cylinder	CJ2-Z	Double acting, Single rod	Except double-side bossed, double clevis type, double foot, head side flange and with air cushion	
CJ2	Non-rotating rod	CJ2K-Z	Double acting, Single rod	Except double-side bossed, double clevis type, double foot and head side flange	
	Direct mount type	CJ2R-Z	Double acting, Single rod		
	Non-rotating rod/Direct mount type	CJ2RK-Z	Double acting, Single rod		1
	Smooth cylinder	CJ2Y-Z	Double acting, Single rod	Except double-side bossed, double clevis type, double foot and head side flange	
	Air cylinder	CM2-Z	Double acting, Single rod	Except boss-cut and clevis types	
CM2	Non-rotating rod	CM2K-Z	Double acting, Single rod	Except boss-cut and clevis types	
	Direct mount type	CM2R-Z	Double acting, Single rod	Except the head cover with boss	
	Non-rotating rod/Direct mount type	CM2RK-Z	Double acting, Single rod	Except the head cover with boss	
	Smooth cylinder	CM2Y-Z	Double acting, Single rod	Except boss-cut and clevis types	1
	Air cylinder	CG1-Z	Double acting, Single rod	Except head side flange and clevis types, ø80, and ø100	
CG1	Non-rotating rod	CG1K-Z	Double acting, Single rod	Except head side flange, clevis types and with air cushion	
	Direct mount type	CG1R-Z	Double acting, Single rod	Except with air cushion	1
	Non-rotating rod/Direct mount type	CG1KR-Z	Double acting	Except with air cushion	
МВ	Air cylinder	MB-Z	Double acting, Single rod	Except ø125, with rubber bumper, with auto switch, head side flange and clevis types	
	Non-rotating rod	MBK-Z	Double acting, Single rod	Except ø125, with rubber bumper, with auto switch, head side flange and clevis types	1
MB1	Air cylinder	MB1-Z	Double acting, Single rod	Except ø125, with rubber bumper, with auto switch, head side flange and clevis types	Web Catalog
	Non-rotating rod	MB1K-Z	Double acting, Single rod	Except head side flange and clevis types	lies calaio
CA2	Air cylinder	CA2-Z	Double acting, Single rod	Except head side flange and clevis types	1
	Non-rotating rod	CA2K	Double acting, Single rod	Except head side flange and clevis types	1
	End lock cylinder	CBA2	Double acting, Single rod	Except head side flange and clevis types	
CS1	Air cylinder	CS1	Double acting, Single rod	Except head side flange and clevis types, ø125 to ø160	1
CS2	Air cylinder	CS2	Double acting, Single rod	Except head side flange and clevis types	1
032	Smooth cylinder	CS2Y	Double acting, Single rod	Except head side flange and clevis types	
cas	Compact cylinder	CQS	Double acting, Single rod	Except with rubber bumper and with mounting bracket	
cus	Non-rotating rod type	CQSK	Double acting, Single rod	Except with rubber bumper and with mounting bracket	1
CQ2	Compact cylinder	CQ2-Z	Double acting, Single rod	Except with rubber bumper and with mounting bracket	
Cuz	Non-rotating rod	CQ2K-Z	Double acting, Single rod	Except with rubber bumper and with mounting bracket	
		MGPM-Z	Double acting		
MGP	Compact guide cylinder	MGPL-Z	Double acting		
		MGPA-Z	Double acting		
MGG	Guide cylinder	MGG	Double acting		
MGC	Guide cylinder	MGC	Double acting		

How to Order

CJ2	Mounting type Bore size - Stroke Z- XC9
CM2	Mounting type Bore size - Stroke Cushion Rod end type symbol Z - XC9 Stroke adjustment symbol * Except boss-cut and clevis types
CM2R	Mounting type Bore size Stroke Rod end type symbol Z – XC9 Stroke adjustment symbol
CG1	Mounting type Type Bore size - Stroke Rod end type symbol Stroke adjustment symbol Z - XC9
МВ	* Except clevis type
MB1	Mounting type Bore size - Stroke Suffix Stroke adjustment symbol Z - XC9 * Except head side flange and clevis types
CA2	Mounting type Type Bore size - Stroke Suffix Stroke adjustment symbol Z - XC9
0/12	* Except head side flange and clevis types
CA2K	Mounting type Type Bore size - Stroke Suffix Stroke adjustment symbol - XC9
	* Except head side flange and clevis types
CBA2	Mounting type Type Bore size - Stroke Stroke adjustment symbol R Manual release type - XC9
CS1	Except head side flange and clevis types Mounting type Tubing material Type Bore size Stroke Suffix Stroke adjustment symbol XC9
651	Mounting type Tubing material Type Bore size - Stroke Suffix Stroke adjustment symbol - XC9 * Except head side flange and clevis types *
CS2	Mounting type Bore size Port suffix - Stroke Suffix Stroke adjustment symbol - XC9
	* Except head side flange and clevis types
CS2Y	Mounting type Bore size Port suffix - Stroke Suffix Stroke adjustment symbol - XC9
	* Except head side flange and clevis types
CQ2B	Bore size – Stroke D (M) (Z) <u>XC9</u>
CQSB	Bore size - Stroke D (M) XC9
MGP	Bearing type Bore size - Stroke Stroke adjustment symbol Z- XC9
MGG	Bearing type Mounting type Bore size Port thread type - Stroke Stroke adjustment symbol - XC9
MGC	Bearing type Mounting type Bore size Port thread type Stroke Stroke adjustment symbol - Euppeldreuppel tak pair - XC9
(After od	Adjustable stroke cylinder/Adjustable retract type

(After adjusting stroke, both-side cushion type is changed into single side cushion type. CQ2 is without cushion.) 1498





Symbol

-XC9

21 Adjustable Stroke Cylinder/Adjustable Retraction Type

Specifications

Series	Stroke adjustment symbol	Stroke adjustment range (mm)
CJ2	—	0 to 15
CM2 CG1 MB	A	0 to 25
MB1 CA2 CS1	В	0 to 50
CQ2 CQS	_	0 to 10

Series	Stroke adjustment symbol	Stroke adjustment range (mm)		
MGP	A	0 to 10		
WGP	В	0 to 25		
MGG	A	0 to 25		
MGC	В	0 to 50		
Specifications other than above	Same as standard type			

Precautions

∧Caution


- When air is supplied to the cylinder, if the stroke adjustment bolt is loosened in excess of the allowable stroke adjustment amount, be aware that the stroke adjustment bolt could fly out or air could be discharged, which could injure personnel or damage the peripheral equipment.
- Adjust the stroke when the cylinder is not pressurized.
 If it is adjusted in the pressurized state, the seal of the adjustment section could become deformed, leading to air leakage.




Symbol



Dimensions (Dimensions other than below are the same as standard type.)



		(mm)
Bore size (mm)	BM	ZZ
10	M5 x 0.8	74
16	M5 x 0.8	75




			(mm)
Bore size (mm)	BM	MH	ZZ
20	M10 x 1.25	26.5	142.5
25	M14 x 1.5	29	149
32	M14 x 1.5	29	151
40	M16 x 1.5	32	186

21 Adjustable Stroke Cylinder/Adjustable Retraction Type



Dimensions (Dimensions other than below are the same as standard type.)



CM2R					(mm)
Bore size (mm)	вм	MF	мн	NN	zz
20	M10 x 12.5	13	26.5	M20 x 1.5	142.5
25	M14 x 1.5	13	29	M26 x 1.5	149
32	M14 x 1.5	13	29	M26 x 1.5	151
40	M16 x 1.5	16	32	M32 x 2	186

CG1						(mm)
Bore size	вм	s	Rubber bumper		Air cushion	
(mm)	DIVI	3	MH	ZZ	MH	ZZ
20	M6 x 1	77	23	135	21	133
25	M6 x 1	77	23	140	21	138
32	M8 x 1.25	79	25	144	25	144
40	M12 x 1.75	87	40	177	39	176
50	M12 x 1.75	102	33	193	37	197
63	M16 x 2	102	40	200	44	204

* In the case of axial foot type, the cushion is shipped after mounting. On other types, it is placed in the same package (not assembled).

* Dimensions other than above are the same as the CG1 series, long stroke type.

MB, MB1 Common (mn								
Bore size (mm)			d	ka	мм	zz		
32	9	8	40	8	M12 x 1.25	171		
40	9	8	39.5	8	M12 x 1.25	174.5		
50	11	8	46	13	M16 x 1.5	198		
63	11	8	52	17	M20 x 1.5	204		
80	15	10	61	19	M24 x 1.5	247		
100	15	10	61.5	19	M24 x 1.5	247.5		

CA2-Z						(mm)
Bore size (mm)	b	с	d	ka	ММ	zz
40	9	8	36	8	M12 x 1.25	171
50	11	8	42	13	M16 x 1.5	190
63	11	8	44	17	M20 x 1.5	200
80	15	10	54	19	M24 x 1.5	241
100	15	10	55.5	19	M24 x 1.5	253.5
CA2K, CE	3A2 (With	lock o	n rod	side only)	(mm
Bore size (mm)	b	с	d	ka	ММ	ZZ
40	9	8	44	11	M16 x 1.5	179
50	11	8	42	11	M16 x 1.5	190
63	11	8	48	14	M20 x 1.5	204

CS1			(mm
Bore size (mm)	b	d	ZZ
125	19	66	274
140	19	66	274
160	22	62	288

M24 x 1.5

M24 x 1.5 255

242


80


100

15 10 55 19

15 10 57 19


21 Adjustable Stroke Cylinder/Adjustable Retraction Type Dimensions (Dimensions other than below are the same as standard type.)





CQS series

ø12, ø16




Setting nut

BL

						(mm)
Bore size (mm)	Α	в	L	BL	вм	Manufacturable stroke
12	50.5 (54.5)	22 (27)	3.5	25 (29)	M5 x 0.8	5 to 30
16	51 (56)	22 (27)	3.5	25.5	M6 x 1	5 10 30
20	61 (71)	26 (36)	4.5	30.5	M8 x 1.25	E 40 E0
25	63.5 (73.5)	29 (39)	5	29.5	M8 x 1.25	5 to 50

Note) When securing the adjustment bolt, clamp the width across flats of the adjustment collar with a tool, such as a spanner and tighten the setting nut with a tool, such as other spanner to secure the bolt firmly.


CQ2 series



A + Stroke

B + Stroke

ø20, ø25, ø32



(mm)									
Bore size		4	E	L BL	ВМ	Manufacturable			
(mm)	50 mm stroke or less	75, 100 mm stroke	50 mm stroke or less	75, 100 mm stroke	_			stroke	
12	52 (59.2)	—	25.2 (32.4)	—	3.5	23.3	M5 x 0.8	5 to 30	
16	53 (63)	—	26 (36)	—	3.5	23.5	M6 x 1	5 10 30	
20	61 (73)	—	26 (38)	—	4.5	30.5	M8 x 1.25	5 to 50	
25	63.5 (73.5)	—	29 (39)	—	5	29.5	M8 x 1.25	5 10 50	
32	65.5 (75.5)	75.5	30.5 (40.5)	40.5	7	28	M8 x 1.25	5 to 50	
40	84 (94)	94	40 (50)	50	7	37	M12 x 1.5	75,100	
50	84.5 (94.5)	94.5	40.5 (50.5)	50.5	8	36	M12 x 1.5		
63	88.5 (98.5)	98.5	42 (52)	52	8	38.5	M16 x 1.5	10 to 50	
80	109.5 (119.5)	119.5	51 (61)	61	10	48.5	M20 x 1.5	75,100	
100	125 (135)	135	60.5 (70.5)	70.5	12	52.5	M24 x 1.5		
Note 1) (): Depotes the dimensions with outs switch									

Note 1) (): Denotes the dimensions with auto switch. Note 2) Applicable stroke available in 5 mm increments.

SMC

Note 3) The symbol is X526 for the long stroke type.

Stroke adjustment bolt

Note) When securing the stroke adjustment bolt, clamp the width across flats of the adjustment collar with a tool, such as a spanner and tighten the setting nut with a tool, such as other spanner to secure the bolt firmly.





Made to Order

(11111)						Stroke			
12	50.5 (54.5)	22 (27)	3.5	25 (29)	M5 x 0.8	5 to 30			
16	51 (56)	22 (27)	3.5	25.5	M6 x 1	5 10 30			
20	61 (71)	26 (36)	4.5	30.5	M8 x 1.25	E to 50			
25	63.5 (73.5)	29 (39)	5	29.5	M8 x 1.25	5 to 50			
Note 1) (): Denotes the dimensions with auto switch. Note 2) Applicable stroke available in 5 mm increments.									

21 Adjustable Stroke Cylinder/Adjustable Retraction Type



Dimensions (Dimensions other than below are the same as standard type.)

BI


мн

MGP series

MGG series

ø20 to ø50

ø63




Front mounting flange

Common Dimensions: MGPM, MGPL, MGPA (mm)										
Bore size (mm)	BM	MA	MB	MC	МН					
12	M5 x 0.8	5	8	12.5	17					
16	M6 x 1	5	10	14	19					
20	M8 x 1.25	6.5	13	16	25					
25	M8 x 1.25	6.5	13	16	24					
32	M8 x 1.25	6.5	19	21	25					
40	M12 x 1.5	9	27	30	32.5					
50	M12 x 1.5	9	30	34	32.5					
63	M16 x 1.5	10	36	40	37					
80	M20 x 1.5	15	41	46	48.5					
100	M24 x 1.5	18	46	52	55.5					

mon Dimonoiono, MCDM, MCDL, MCDA

MGG Series (mm)										
Bore size	в	Y	вм	Adjustment	0 to 25 mm	Adjustment 0 to 50 mm				
(mm)	n	T	DIVI	MH	ZZ	МН	ZZ			
20	12	77	M6 x 1	48	164	73	189			
25	12	77	M6 x 1	48	171	73	196			
32	12	79	M8 x 1.25	50	175	75	200			
40	13	87	M12 x 1.75	65	208	90	233			
50	14	102	M12 x 1.75	58	227	83	252			
63	14	117	M16 x 2	65	236	90	261			


* The piston speed for the retraction side is 50 to 500 mm/s.



Y + Stroke

© ₽

MGC series ø20 to ø50



Front mounting flange

MGC Series (mm)										
Bore size	ize R Y BM				0 to 25 mm	Adjustment 0 to 50 mm				
(mm)	n	T	DIVI	MH	ZZ	МН	ZZ			
20	12	77	M6 x 1	46	162	71	187			
25	12	77	M6 x 1	46	169	71	194			
32	12	79	M8 x 1.25	50	175	75	200			
40	13	87	M12 x 1.75	64	207	89	232			
50	14	102	M12 x 1.75	62	231	87	256			

* The piston speed for the retraction side is 50 to 500 mm/s.