2-Color Display Digital Pressure Switch

ISE70/75/75H Series

- NPN/PNP open collector 2 outputs added.
- Zero-cut off display function added.

The ISE70/75 series has been remodeled. Click here for details.





ZSE20 ISE20

ZSE30 ISE30 ZSE40

ISE40

ZSE10

ISE70

ZSE80

ISE80

PS

ISA3

ISA2

ISE35

Metal Body Type (Die-cast aluminum)

For General **Fluids**

O MPa • **15**

For Air

(ISE70)



Rated Pressure







ISG ZSM1

2-Color Display (Green/Red)

· Selectable from four patterns

	ON	OFF
1	Red	Green
2	Green	Red
3	Red	Red
4	Green	Green

See abnormal values at a glance.




M12 Connector

- . Lead wire with M12 connector (5 m)
- · Straight and right-angled connectors

With Bracket

· User-selectable mounting orientation



- . Withstand pressure: 3 times the rated pressure
- . Model with initial display settings of psi is also available as standard.
- Port size Rc1/4, NPT1/4, G1/4 (ISO1179)





- Anti-chattering
- Display calibration
- Zero-clear
- Keylock
- Display unit switching (Fixed SI unit in Japan)

Fan Ain	For Air For General Fluids			
For Air	For Gene	rai Fiulus		
ISE70 (1 MPa)	ISE75 (10 MPa)	ISE75H (15 MPa)		
UP COMP	Gray	U D DOOD OT		


2-Color Display Digital Pressure Switch C & c Tu us

For Air





The ISE70 series has been remodeled.
Click here for details.



Option/Part No.

When optional parts are required separately, use the following part numbers to place an order.

Option	Part no.	Note	
Bracket	ZS-31-A	Bracket B and the bracket assembly make up one set. Note) Mounting screws are not included. Bracket assembly	
Lead wire with M12 connector, straight	ZS-31-B	Lead wire length: 5 m	
Lead wire with M12 connector, right-angled	ZS-31-C	Lead wire length: 5 m	



2-Color Display Digital Pressure Switch For Air ISE70 Series

Specifications

Refer to pages 11 and 12 for Pressure Switch Precautions. For details about the Specific Product Precautions, refer to the Operation Manual on the SMC website, http://www.smcworld.com Click here for details.

	Model	ISE70		
Rated pressure range		0 to 1 MPa		
Pressure display range/Set pressure range		-0.1 to 1 MPa		
Withstand p		1.5 MPa		
	resolution/Set pressure resolution	0.01 MPa		
Applicable	· ·	Air, Non-corrosive gas, Non-flammable gas		
Power supp		12 to 24 VDC±10%, Ripple (p-p) 10% or less (with power supply polarity protection)		
Current cor	nsumption	55 mA or less (at no load)		
Switch outp	out	Output -27: 2 settings; NPN open collector 2 outputs (Pin no.: 2, 4) Output -43: Fixed setting; NPN open collector 1 output (Pin no.: 4) + PNP open collector 1 output (Pin no.: 2) Note 1) Output -65: PNP open collector 1 output (Pin no.: 4) Output -67: 2 settings; PNP open collector 2 outputs (Pin no.: 2, 4)		
	Max. load current	80 mA		
	Max. applied voltage	30 V (at NPN output)		
	Residual voltage	1 V or less (with load current of 80 mA)		
	Response time	2.5 ms (with anti-chattering function: 20 ms, 160 ms, 640 ms, 1000 ms, 2000 ms)		
	Short circuit protection	With short circuit protection		
Repeatabili	ty	±0.5%F.S.		
Hysteresis	Hysteresis mode	Variable (0 or above)		
пувістевів	Window comparator mode			
Display		3-digit, 7-segment indicator, 2-color display (Red/Green) can be interlocked with the switch output, Sampling cycle: 5 times/1 s		
Display acc	uracy	2%F.S.±1 digit (at 25°C±3°C)		
Indicator lig	ght	OUT1: Light up when output is turned ON. (Green) OUT2: Light up when output is turned ON. (Red: for output -27, -67)		
Functions		Anti-chattering function, Display unit switching function, Zero-clear function, Keylock function		
	Enclosure	IP67 Note 2)		
	Fluid temperature range	0 to 50°C (No freezing or condensation)		
Environ-	Operating temperature range	Operating: 0 to 50°C, Stored: -10 to 60°C (No freezing or condensation)		
ment	Operating humidity range	Operating and stored: 35 to 85%RH (No condensation)		
	Withstand voltage	1000 VAC for 1 minute between terminals and housing		
Insulation resistance		50 $M\Omega$ or more (500 VDC measured via megohmmeter) between terminals and housing		
Temperature characteristics (25°C reference: within operating temperature range)		±2%F.S.		
Standards		CE , UL/CSA (E216656) RoHS		
Wetted parts material		Fitting: C3604 (electroless nickel plating) Sensor pressure receiving area: Silicon, O-ring: NBR		
Port size		02: Rc1/4, N02: NPT1/4, F02: G1/4 (ISO 1179) Note 3)		
Lead wire with connector		Oilproof cable with M12 4-pin pre-wired connector, 4 cores, ø4, 5 m, Conductor O.D.: 0.72 mm, Insulator O.D.: 1.14 mm		
Weight		190 g (excluding the lead wire with M12 4-pin pre-wired connector)		
	N and PNP autputs function for			

Note 1) The NPN and PNP outputs function for a single set point.

Note 2) An FKM gasket is used for the product case seal. Refer to the Operation Manual at SMC's website for details.

Note 3) G1/4: Applicable to ISO 1179-1

SMC

ZSE20 ISE20 ZSE30 ISE30 ZSE40 ISE40 ZSE10 ISE10

ISE70 ZSE80 ISE80 PS

ISA3

ISA2 ISE35

PSE

IS ISG


ZSM1

2-Color Display Digital Pressure Switch C & C Thus





ISE75/75H Series



Option/Part No.

when optional parts are required separately, use the following part numbers to place an order.			
Option	Part no.	Note	
Bracket	ZS-31-A	Bracket B and the bracket assembly make up one set. Bracket B Note) Mounting screws are not included.	
Lead wire with M12 connector, straight	ZS-31-B	Lead wire length: 5 m	
Lead wire with M12 connector, right-angled	ZS-31-C	Lead wire length: 5 m	

2-Color Display Digital Pressure Switch For General Fluids ISE75/75H Series

Specifications

Refer to pages 11 and 12 for Pressure Switch Precautions. For details about the Specific Product Precautions, refer to the Operation Manual on the SMC website, http://www.smcworld.com Click here for details.

Model		ISE75	ISE75H	
Rated pressure range		0 to 10 MPa	0 to 15 MPa	
Pressure display range/Set pressure range*		0.4 to 10 MPa	0.5 to 15 MPa	
Withstand p	ressure	30 MPa	45 MPa	
Pressure display	resolution/Set pressure resolution	0.1	MPa	
Applicable f	luid	Fluid or gas that will not corrode	stainless steel 304, 430 and 630	
Power supp	ly voltage	12 to 24 VDC±10%, Ripple (p-p) 10% or less (with power supply polarity protection)		
Current con	sumption	55 mA or less	s (at no load)	
Switch outp	ut	Output -27: 2 settings; NPN open collector 2 outputs (Pin no.: 2, 4) Output -43: Fixed setting; NPN open collector 1 output (Pin no.: 4) + PNP open collector 1 output (Pin no.: 2) Note 1) Output -65: PNP open collector 1 output (Pin no.: 4) Output -67: 2 settings; PNP open collector 2 outputs (Pin no.: 2, 4)		
	Max. load current	80	mA	
	Max. applied voltage	30 V (at N	PN output)	
	Residual voltage	1 V or less (with loa	d current of 80 mA)	
	Response time	2.5 ms (with anti-chattering function: 20 i	ms, 160 ms, 640 ms, 1000 ms, 2000 ms)	
	Short circuit protection	With short circ	cuit protection	
Repeatabilit	у	±0.5%	%F.S.	
Hysteresis	Hysteresis mode	Variable (0 or above)		
nysteresis	Window comparator mode			
Display		3-digit, 7-segment indicator, 2-color display (Red/Green) can be interlocked with the switch output, Sampling cycle: 5 times/1 s		
Display accuracy		2%F.S.±1 digit	(at 25°C±3°C)	
Indicator light		OUT1: Lights up when ou	tput is turned ON. (Green)	
indicator ng		OUT2: Lights up when output is turned ON. (Red: for output -27, -67)		
Functions		Anti-chattering function, Display unit switching	function, Zero-clear function, Keylock function	
	Enclosure	IP67	Note 2)	
	Fluid temperature range	−5 to 80°C (No freez	ing or condensation)	
Environ-	Operating temperature range	Operating: -5 to 50°C, Stored: -10 to 60°C (No freezing or condensation)		
ment	Operating humidity range	Operating and stored: 35 to	85%RH (No condensation)	
	Withstand voltage	250 VAC for 1 minute betw	veen terminals and housing	
	Insulation resistance	50 M Ω or more (50 VDC measured via meg	gohmmeter) between terminals and housing	
	e characteristics within operating temperature range)	±3%F.S.		
Standards		CE , UL/CSA (E216656) RoHS		
Pressure sensor		Stainless steel 630		
Wetted part	Fitting	Stainless steel 304	Stainless steel 304 (port size Rc1/4) Stainless steel 430 (port size NPT1/4, G1/4)	
Port size		02: Rc1/4, N02: NPT1/4, F02: G1/4 (ISO 1179) Note 3)		
Lead wire with connector		Oilproof cable with M12 4-pin pre-wired connector, 4 cores,	ø4, 5 m, Conductor O.D.: 0.72 mm, Insulator O.D.: 1.14 mm	
Weight		225 g	225 g (port size Rc1/4) 210 g (port size NPT1/4, G1/4)	
		145 g (Lead wire with M12 4-pin pre-wired connector)		

Note 1) The NPN and PNP outputs function for a single set point.

Note 2) An FKM gasket is used for the product case seal. Refer to the Operation Manual at SMC's website for details.

ZSE40 ISE40 ZSE10 ISE10 ISE70 ZSE80 ISE80 PS ISA3 ISA2 ISE35 PSE IS ISG ZSM1

ZSE20 ISE20 ZSE30 ISE30

Note 3) G1/4: Applicable to ISO 1179-1

* Refer to page 84 for the pressure display range.

ISE70/75/75H Series


Set Pressure Range and Rated Pressure Range

Set the pressure to within the rated pressure range.

The set pressure range is the range of pressure that is possible in setting.

The rated pressure range is the range of pressure that satisfies the specifications (accuracy, linearity, etc.) on the switch.

Although it is possible to set a value outside the rated pressure range, the specifications will not be guaranteed even if the value stays within the set pressure range.




^{*} The ISE75(H) switch shows zero (0) when the pressure being applied goes below the lower limit of the set pressure range, when the zero-cut off display function is selected.

Rated pressure range of switch


Set pressure range of switch

Internal Circuits and Wiring Examples

-27 NPN (2 outputs)




-65 PNP (1 output)




-43 NPN (1 output) + PNP (1 output)

(The pressure set point for switching the output signal is common to NPN and PNP.)




-67 PNP (2 outputs)



2-Color Display Digital Pressure Switch ISE70/75/75H Series

Dimensions





02: Rc1/4 N02: NPT1/4 F02: G1/4 (ISO 1179) Note) If it is predicted that the pressure, such as the water hammer or surge pressure fluctuates rapidly, refer to the Handling Precautions stated in the Operation Manual at SMC website (http://www.smcworld.com).

44.5

3.5

Note) The connector faces down (toward the piping). Do not attempt to rotate the connector, as it is not rotatable. ZSE20 ISE20 ZSE30

ISE30 ZSE40 ISE40

ZSE10 ISE10

ZSE80 ISE80

PS

ISA3

ISA2

ISE35

PSE

ıs

ISG ZSM1



Connector pin number

Output -43 (Color: Gray)

(,		
1	Brown	DC (+)
2	White	OUT1 (PNP)
3	Blue	DC (-)
4	Black	OUT1 (NPN)

Output -65 (Color: Black)

(,			
1	Brown	DC (+)	
2	White	NC	
3	Blue	DC (-)	
4	Black	OUT1 (PNP)	

Output -27 and -67

-	(Color: Gray)		
	1	Brown	DC (+)
	2	White	OUT2 (NPN or PNP)
	3	Blue	DC (-)
	4	Black	OUT1 (NPN or PNP)

Bracket mount

8


24	
	Piping port 02: Rc1/4 N02: NPT1/4 F02: G1/4 (ISO 1179)

46

60

Lead wire with connector ZS-31-B

Lead wire with connector ZS-31-C



(31)

(38.7)

5000


ISE70/75/75H Series

Functions

A Display calibration function

Fine adjustment of the indicated value of the pressure sensor can be made within the range of $\pm 5\%$ of the read value.

(The scattering of the indicated value can be eliminated.)



Note) When the display calibration function is used, the set pressure value may change ± 1 digit.

Peak/Bottom hold function

This function constantly detects and updates the maximum and minimum pressure values and allows the unit to hold the display value.

C Keylock function

Prevents operation errors such as accidentally changing setting values.

D Zero-clear function

The measured pressure reading can be adjusted to zero. More specifically, the factory-set reading can be corrected to within $\pm 7\%$ F.S.

E Display unit switching function

Display units can be switched with this function.

Unit/Reading resolution	ISE70	ISE75/75H
MPa	0.01	0.1
kgf/cm ²	0.1	1
bar	0.1	1
psi	1	1 (X10)

Anti-chattering function

A large bore cylinder or ejector consumes a large amount of air in operation and may experience a temporary drop in the primary pressure. This function prevents detection of such temporary drops in primary pressure as abnormal pressure.

Response time selections: 20 ms, 160 ms, 640 ms, 1000 ms, 2000 ms

G Error function

Take the following corrective actions when error occurs.

Error description		LCD display	Description	Action	
Over-	OUT1	Er 1	Load current of switch	Eliminate the cause of the over current by turning off the	
error	Note 1) OUT2	E-2	output exceeds 80 mA.	power supply, and then turn on it again.	
Residual pressure error		Er3	During zero-clear operation, pressure over ±7% F.S. is applied. After 3 second, the mode will reset to measurement mode. ±1% F.S. of the zero-clear range varies between individual products.	Perform zero-clear operation again after restoring the applied pressure to an atmospheric pressure condition.	
Applied pressure error		ннн	Supply pressure exceeds the maximum set pressure.	Reset applied pressure to a level	
		LLL	Supply pressure is below the minimum set pressure.	within the set pressure range.	
System error		ErY	Internal data error		
		Erb	Internal data error	Turn the power off	
		Er7	Internal data error	and turn it on again.	
		Er8	Internal data error		

^{*} If the failure cannot be solved after the above instructions are performed, please contact SMC for investigation.

Note 1) Output -27 and -67 only.

H Zero-cut off display function

With the ISE75 series, users can enable or disable a function (zero-cut off display function) that displays pressure values of 0.3 MPa or less as zero (0.4 MPa or less in the ISE75H series).

Example pressure displays (shading indicates changed displays)

ISE75-□ (for 10 MPa)

Zero-cut off display function "ON": $0 \rightarrow Displayed as 0 \rightarrow 0.4 \rightarrow 0.5 \rightarrow 0.6 \rightarrow \cdots \rightarrow 9.9 \rightarrow 10.0$ Zero-cut off display function "OFF": $0 \rightarrow 0.1 \rightarrow 0.2 \rightarrow 0.3 \rightarrow 0.4 \rightarrow 0.5 \rightarrow 0.6 \rightarrow \cdots \rightarrow 9.9 \rightarrow 10.0$

ISE75H-□ (for 15 MPa)

Zero-cut off display function "ON": $0 \rightarrow$ Displayed as $0 \rightarrow 0.5 \rightarrow 0.6 \rightarrow \cdots \rightarrow 14.9 \rightarrow 15.0$ Zero-cut off display function "OFF": $0 \rightarrow 0.1 \rightarrow 0.2 \rightarrow 0.3 \rightarrow 0.4 \rightarrow 0.5 \rightarrow 0.6 \rightarrow \cdots \rightarrow 14.9 \rightarrow 15.0$

Pressure Display Range

Series	Zero-cut off display function "ON"	Zero-cut off display function "OFF"
ISE75	0, 0.4 to 10.0 MPa	0 to 10.0 MPa
ISE75H	0, 0.5 to 15.0 MPa	0 to 15.0 MPa

^{*} The set pressure range does not change when the zero-cut off display function is disabled.



ISE75(H) Series Made to Order Specifications Please contact SMC for detailed dimensions, specifications and lead times.




1 Analog Voltage Output Specifications

Symbol -X500

This product is compatible with NPN open collector 1 output + Analog voltage output.

How to Order

* Refer to "How to Order" on page 82 for the standard specifications.



Note) The output is applicable to 43 only.

Specifications

Analog voltage output	Output voltage: 1 to 5 V $\pm 2.5\%$ F.S. (In rated pressure range) Output impedance: Approx. 1 k Ω Response time: 300 ms or less		
Connector pin number	3	1 Brown DC (+) 2 White Analogue output 3 Blue DC (-) 4 Black OUT1 (NPN)	

Models other than above are the same specifications as standard.

ZSE20 ISE20

ZSE30 ISE30 ZSE40 ISE40

ZSE10 ISE10

ISE70

ZSE80 ISE80 PS

ISA3

ISA2

ISE35

PSE IS

ISG

ZSM1