


Series LX Dedicated Stepper Motor Driver Series LC6D




- Can be mounted on a DIN rail
- Driver position controlled by pulse signal
- Can be controlled by a general positioning unit or controller



CE marking

- The combination of Series LC6D and Series LX has been certified for CE marking. When using Series LX with CE marking, use it in combination with Series LC6D with CE marking.
- 2. The combination of Series LC6D and Series LX has been certified for EMC conformity. EMC changes depending on the customer's control panel configuration, and the relationship between other electrical equipment and wiring. Therefore, conformity cannot be certified for the customer's equipment in the actual operating environment. As a result, it is necessary for the customer to verify final EMC conformity for the machinery and equipment as a whole.

Maximum speeds of actuators vary depending on the type. Observe the maximum speed of the actuator in use.



Applicable Actuators

Driver model	Applicable actuator		Motor type
LC6D-220AD-□	Guide rod type	LXPB2	2 phase stepper motor
	High rigidity slide table type	LXSH2	2 phase slepper motor
	Low profile slide table type	LXFH5	
LC6D-507AD-	- High rigidity slide table type		5 phase stepper motor
	Guide rod type	LXPB5	

Specifications

Part no.	LC6D-220AD-	LC6D-507AD-
Power supply	24 VDC ±10%, 3 A	24 VDC ±10%, 2.5 A
Energization (Step angle °)	Full step (1.8°) Half step (0.9°)	Full step (0.72°) Half step (0.36°)
Motor current	2.0 A/phase	0.75 A/phase
Input signal	Photo coupler input (Input impedance 330 Ω)	
Maximum input frequency	10 kHz for full step 20 kHz for half step	
Function	Auto current down, Power down input	
Connection method	Connector	
Ambient temperature	5° to 40°C	
Ambient humidity	35 to 85% (No condensation)	
Accessories	Connectors: LC6-1-C1 (Re Cable should be arr	eceptacle, female terminal) anged by customer.

Pulse input signal method

Part no.	Input signal method	
LC6D-□□AD LC6D-□□AD-Q	2 pulse input method	
LC6D-	1 pulse input method	



Pulse Signals

LC6D positioning is controlled by the number of pulse signal inputs to the CW(CK) and CCW(U/D) terminals, and speed is controlled by pulse frequencies.

Calculation for speed and pulse frequencies


Pulse frequency [pps] = (Speed [mm/s]/Lead [mm]) x Divisions per rotation


Calculation for moving distance and pulse numbers
 Pulse numbers = (Moving distance [mm]/Lead [mm]) x Divisions per rotation


• The divisions per rotation are as shown in the table below.


Driver	Energization type	Divisions per rotation	
LC6D-220AD-	Full step	200	
	Half step	400	
LC6D-507AD-	Full step	500	
	Half step	1000	


Dimensions












Connector



		-
Description	Part no.	Quantity
Receptacle	5557-14R	1
Female terminal	5556PBTL	14


• Wiring tools [Manufacturer: Molex Japan Co., Ltd.] Wiring tools should be arranged by the customer.

wiring tools should be arranged by the customer.				
Description	Part no.			
Crimping tool	57026-5000 (for UL1007) 57027-5000 (for UL1015)			
Puller	57031-6000			

Mounting

A Caution

Provide cooling so that the operating temperature of the body will be within the range shown in the specifications. For that reason, each face of the body should be separated by a sufficient amount of distance from other construction or components.





LJ1

LG1


LTF

LC1

Series LC6D

Connection Examples

Electrical wires




Functions

Function change-over switch

Use the function change-over switch to set each function. It is set as follows when shipped.

1. ON ····· Energization type: Half step 2. OFF ··· Auto current down function



Input signal terminal

- CW pulse input terminal (LC6D-DDAD, LC6D-DDAD-Q) By applying the pulse input, the actuator moves from the motor side to the end side.
- CCW pulse input terminal (LC6D- AD, LC6D- AD-Q) By applying the pulse input, the actuator moves from the end side to the motor side.
- CK pulse input terminal (LC6D-DDAD-P1-X316) By applying the pulse input, the actuator moves.
- UD direction input terminal (LC6D-DDAD-P1-X316) By switching ON/OFF, the movement direction of the actuator changes.
- · Power down input terminal

By applying the "H" level input, the motor current is shut off and the motor becomes de-eneraized.

Functions

Auto current down

This is a function that reduces the motor current to half when the motor stops. This will prevent the motor and driver from generating heat.

Although auto current down causes the holding torque to be reduced when the motor stops, the holding torque that supports the actuator transfer load is maintained.

Power down


This function shuts off the motor current and de-energizes the motor. Use this function to release the electric actuator for maintenance, etc.




Series LX Dedicated Positioning driver Series LC6C



- Built-in position control function added to LC6D
- Up to 28 patterns of movement data can be set.
- Point movement can be easily achieved with a PLC, etc.
- Compatible with Series LX two
 phase stepper motor





Applicable Actuators


Driver	Applicable actuator		Motor type	
LC6C-220AD	Guide rod type	LXPB2	0 phase stopper motor	
LC0C-220AD	High rigidity slide table type	LXSH2	2 phase stepper motor	

* Select a 3 wire NPN type when using an auto switch.


Specifications

Part no.	LC6C-220AD
Power supply	24 VDC ±10%, Max. 3.0 A
Number of position settings	28 patterns
Position setting method	Setting with dedicated teaching box (LC5-1-T1-02)
Position control method	Absolute and incremental moves Speed: 6 to 200 mm/s (with lead screw lead of 12 mm)
Input signal capacity	Photo coupler input 24 VDC, Max. 6 mA
Output signal capacity	Photo coupler output Max. 30 VDC or less, Max. 20 mA
Parameter setting	Position data setting, Speed/Acceleration setting, etc.
Indication LED	Power supply LED (Green), Alarm LED (Red)
Operating temperature	5° to 40°C
Accessories	Power connector: LC6-1-C2, Interface connector: LC6-1-C3 (Cables should be arranged by customer.)

Absolute and incremental moves for each movement pattern.



Eight speed patterns based on the speed number and acceleration number can be set, and a speed pattern can be selected for each movement pattern.




LG1 LTF LC1 LC7 LC8 LXF LXP LXS LC6 LXS LC5 LC3F2 X LC3F2 X LC3F2

LJ1


Series LC6C

Dimensions



Wiring to the teaching box

By connecting multiple drivers (maximum of 16), they can be set by one teaching box. (When the teaching box is in use, external input to the drivers becomes invalid.)



968

Interface connector wiring -

Connection Examples

Power connector wiring -


Connector: Power connector: LC6-1-C2 (included) Terminal part no. Manufacturer: Molex Japan, Co., Ltd. Part no.: Receptacle 5557-18R Female terminal 5556PBTL 23456 1213145 111213145 View from the wiring side

Switches

Home position switch: This switch indicates the home position. Connect this switch when returning to the origin point. This switch also acts as a sensor that detects overrun in the motor direction.

Limit switch:

This sensor detects overrun in the end direction. Connect this switch as needed.



Power connector input/output signal details

Connector no.	Signal description	Detail
1	24 V	Connect to power supply (24 VDC)
2	0 V	Connect to power supply (0 V)
3	FG	Connect to frame ground
4	Home position switch (+)	Connect to home position switch positive power supply (+) line
5	Home position switch (OUT)	Connect to home position switch output line
6	Home position switch (-)	Connect to home position switch 0 V power supply (-) line
7	Limit switch (+)	Connect to limit switch positive power supply(+) line
8	Limit switch (OUT)	Connect to limit switch output line
9	Limit switch (-)	Connect to limit switch 0 V power supply (-) line
10	N.C.	Do not connect.
11	N.C.	Do not connect.
12	N.C.	Do not connect.
13	b phase (Yellow)	Connect to actuator power line (Yellow)
14	B phase (Red)	Connect to actuator power line (Red)
15	a phase (Blue)	Connect to actuator power line (Blue)
16	A phase (Orange)	Connect to actuator power line (Orange)
17	COM (Black)	Connect to actuator power line (Black)
18	COM (White)	Connect to actuator power line (White)

▲ Caution

Use a 3 wire NPN type for each switch.

interface connector winnig				
Manufactu	Interface connector rer: OMRON Corpor onnector XG4M-203	ation	I-C3 (included) Terminal part no.	
	is located on the number 1 side.	Ŕ	Image: Second state Image: Second state	
			24 VDC	
	Input (+) COM	1		
	Point input A	2		
	Point input B	3		
	Point input C	4		
	Point input D	5		
	Bank input 1	6		
	Bank input 2	7		
	Bank input 3	8		
	Emergency stop input	9	<u> </u>	
	Alarm reset input	10		
	Output (-) COM	11	30 VDC or less	
	Point output A	12		
	Point output B	13		
	Point output C	14		
	Point output D	15		
	READY output	16		
	BUSY output	17		
	Home position return output	18		
	Alarm output	19		
	N.C	20		
			1 1 1	

Interface connector input/output signal details

Connector no.	Signal description	Details
1	Input (+) COM	Input COM signal
2	Point input A	Point setting input (point A)
3	Point input B	Point setting input (point B)
4	Point input C	Point setting input (point C)
5	Point input D	Point setting input (point D)
6	Bank input 1	Bank setting input (binary, first bit)
7	Bank input 2	Bank setting input (binary, second bit)
8	Bank input 3	Bank setting input (binary, third bit)
9	Emergency stop input	Emergency stop input
10	Alarm reset input	When an alarm occurs, this signal turns off the alarm after the cause is resolved.
11	Output (-) COM	Output COM signal (GND)
12	Point output A	This signal indicates move completion for point input A.
13	Point output B	This signal indicates move completion for point input B.
14	Point output C	This signal indicates move completion for point input C.
15	Point output D	This signal indicates move completion for point input D.
16	READY output	This signal indicates that the controller is ready.
17	BUSY output	This signal indicates motor control in progress.
18	Home position return output	This signal indicates that home position return is completed.
19	Alarm output	This signal indicates occurrence of alarm.
20	N.C.	Do not connect.

▲ Caution

If input is not provided as prescribed for the operation, this may cause malfunction or failure.



LJ1

LG1

LTF

LC1

LC7

LC8

LXF

LXP

LXS

LC6

LZ

LC3F2


X

D-🗆

E-MY

Series LC6C

Home Position Return



- ① Moves to the motor side at home position return speed
- Decelerates and stops at the home position sensor ON position
- Moves to the end side at low speed
- ④ Moves and stops at 16 pulse position from the home position sensor OFF position

2 Operating procedures

- 1. Confirm that both READY output and alarm output are ON.
- 2. Turn OFF bank inputs 1 to 3. [Specify bank 0.]
- 3. When point input A is turned ON, the actuator begins to return to the home position.
- 4. BUSY output is turned ON during home position return.
- 5. BUSY output is turned OFF when the actuator reaches the home position, and home position return output turns ON.
- 6. Turn OFF point input A.
- Note) The actuator stops if point input A is turned OFF when BUSY output is ON (home position return movement in progress).

3 Home position return speed

Speed is set by parameter number 0D.

,	
1.	015
Acceleration no.	Speed no.

4 Home position return signal

This signal output turns ON when the home position return movement completes. It turns OFF when an alarm occurs or when JOG movement takes place.

5 Time chart


Actuator speed	+		
Bank input 1	OFF		
Bank input 2	OFF		
Bank input 3	OFF		
Point input A	OFF	ON	
Point input B	OFF		
Point input C	OFF		
Point input D	OFF		
Emergency stop input	ON		
Alarm reset input	OFF		
i	i n	 	
Point output A	OFF	 	
Point output B	OFF	 	
Point output C	OFF	 	
Point output D	OFF	 	
Alarm output	ON	 	
READY output	ON	 	
BUSY output	OFF	ON	OFF
Home position return output	OFF		ON
·	J	 	

Point Movement

With this driver, a maximum of 28 point positions can be set by combining banks and points. With the combination of bank and point inputs, the actuator can move to the position indicated by each point.

Setting detail

To set point settings, use the parameter setting and teaching functions of the dedicated teaching box.



2 Operating procedures

- 1. Confirm that both READY output and alarm output are ON.
- 2. Set bank with bank inputs 1 to 3. [Bank 1 to 7.]
- 3. When points are specified with point inputs A to D, the actuator starts to move.
- 4. BUSY output is ON while the actuator is moving.
- 5. BUSY output turns OFF when the move completes and point outputs A to D turn ON. These correspond to point inputs A to D that are ON.
- 6. When point inputs A to D are turned OFF, point outputs A to D turn OFF.
- Note) The actuator stops moving if point inputs A to D are turned OFF or two or more of point inputs A to D are turned ON while BUSY output is ON (during movement).

3 Time chart (when specifying point B)

Actuator speed	+		 	
Bank input 1 Bank input 2			 	
Bank input 3			1	
Point input A	OFF		 	
Point input B	OFF	ON	1	OFF
Point input C	OFF		1	I I
Point input D	OFF			
Emergency stop input	ON		1	1
Alarm reset input	OFF			
	1		1	
Point output A	OFF		 	
Point output B	OFF		ON	OFF
Point output C	OFF		 	
Point output D	OFF			
Alarm output	ON		 	
READY output	ON		1	
BUSY output	OFF	ON	OFF	
Home position return output	ON		 	

Series LC6C Dedicated Teaching Box/LC5-1-T1-02



Performance/Specifications


General specifications

Part no.	LC5-1-T1-02	
Power supply	Supplied by LC6C-220AD	
Dimensions (mm)	130 x 50 x 21	
Mass (g)	110	
Body type	Resin body	
Indication unit	7 LED numerical indicators, 9 LED indicator lights	
Operation unit	Key switches	
Cable length	2 m	

Basic performance

	Performance/Specifications		
Applicable controller	LC6C-220AD		
Operating temperature range	e 5° to 40°C		
Communication method	n method Conforming to RS485		
Functions	Parameter change, JOG operation, alarm reset, teaching, test		
Protective function indication	Alarm code		

Dimensions



21


LJ1
LG1
LTF
LC1
LC7
LC8
LXF
LXP
LXS
LC6
LZ
LC3F2
X
D-🗆
E-MY

Series LC6C

Part Descriptions

Power supply LED (Green)			Alarm LED (Red)
	PARA AL-RES		Mode indication LED [7] (Orange)
ID number			Parameter (2 digits)
	7 <i>0. 0.0.</i> <i> </i>		Data indication (4 digits)
	• TANKING TOP		
)	
		$\left(\right)$	
			1

Key Arrangement and Functions



Mark	Key description	Function
\land	UP	Increases a numerical value.
\sim	DOWN	Reduces a numerical value.
<	L	Moves a numerical value place to the left. Rotates the motor counter clockwise during JOG operation.
>	R	Moves a numerical value place to the right. Rotates the motor clockwise during JOG operation.
STOP	STOP	Becomes the emergency stop key when the actuator is moving.
ESC/ MODE	ESC/ MODE	Selects a mode. Completes each mode and returns to the mode level.
RET	RET	Determines the mode and records data.


A Caution

STOP key only stops the driver that is in communication.

Alarm Details

Alarm no. Alarm description		Presumed cause and solution		
1	Emergency stop input	Emergency stop input is turned OFF (open).		
2	Temperature abnormality	The temperature inside the driver is high. Check the installation environment and operation frequency.		
3	Power supply abnormality	Operating beyond the range of the specified power supply. Adjust the power supply.		
4	Limit switch abnormality	Home position switch and limit switch are operating. Malfunction such as loss of synchronism may have occurred. Check the equipment.		

Operating Method



ESC/MODE


As shown above, 6 modes are available. (I/O mode and MON mode do not function with this driver.) When the communication mode is started by the teaching box, a menu can be selected with [ESC/MODE]. Select the mode indication LED for the mode to be implemented (all mode indication LEDs turn Off in the ID mode) and press [RET] to start each mode. Refer to the instruction manual for the operation of each mode.

SMC

Series LC6D/LC6C Options

▲ Caution

- Do not repeatedly apply bending stress or tension to the cables. Wiring that subjects cables to repeated bending stress and tension causes line breakage.
- Make connections based on each driver's connection example.



Wiring


Pin no.	Color	Cable description	Signal description		Pin no.	Color	Cable description	Signal description
1	Yellow		PD+		8	Brown		PD-
2	Red	Interface cable	CCW+ (U/D+)		9	Green	Interface cable	CCW- (U/D-)
3	Black	Cabic	CW+ (CK+)		10	White		CW- (CK-)
4	White	Motor cable	Motor B		11	Brown		Motor F
5	Black		Motor A		12	Yellow		Motor E
6	Black		GND		13	Green	Motor cable	Motor D
7	White	Power cable	+24 V		14	Red		Motor C


LC6D connector Model LC6-1-C1

Receptacle 5557-14R 1 pc. Female terminal 5556PBTL 14 pcs. Molex Japan, Co., Ltd.

LC6C Interface Connector Cable

Model LC6-1-C3-Q-X252





SMC

LC6C interface connector Model LC6-1-C3 Connector XG4M-2030-T Omron LJ1

LG1

LTF

LC1

LC7

LC8

LXF

LXP

LXS

LC6

LZ

LC3F2

X

D-🗆

E-MY