

ORIGINAL INSTRUCTIONS

# Instruction Manual

# Flow Controller for Air

# IN502-44-# / IN502-45-# / IN502-46-# series





The intended use of the flow controller is to monitor and display flow information with the optional connection to IO-Link communication.

#### 1 Safety Instructions

These safety instructions are intended to prevent hazardous situations and/or equipment damage. These instructions indicate the level of potential hazard with the labels of "Caution," "Warning" or "Danger." They are all important notes for safety and must be followed in addition

to International Standards (ISO/IEC)<sup>\*1</sup>, and other safety regulations.

- <sup>\*1)</sup> ISO 4414: Pneumatic fluid power General rules and safety requirements for systems and their components. ISO 4413: Hydraulic fluid power — General rules and safety
- requirements for systems and their components

IEC 60204-1: Safety of machinery - Electrical equipment of machines. Part 1: General requirements

ISO 10218-1: Robotics - Safety requirements - Part 1: Industrial robots. • Refer to product catalogue, Operation Manual and Handling

Precautions for SMC Products for additional information.
Keep this manual in a safe place for future reference.

A Danger	Danger indicates a hazard with a high level of risk which, if not avoided, will result in death or serious injury.
<b>A</b> Warning	Warning indicates a hazard with a medium level of risk which, if not avoided, could result in death or serious injury.
<b>A</b> Caution	Caution indicates a hazard with a low level of risk which, if not avoided, could result in minor or moderate injury.

#### Warning

- Always ensure compliance with relevant safety laws and standards.
- All work must be carried out in a safe manner by a qualified person in compliance with applicable national regulations.
- This product is class A equipment intended for use in an industrial environment. There may be potential difficulties in ensuring electromagnetic compatibility in other environments due to conducted or radiated disturbances.
- Refer to the operation manual on the SMC website (URL: <u>https://www.smcworld.com</u>) for more Safety instructions.
- Special products (-X) might have specifications different from those shown in the specifications section. Contact SMC for specific drawings.

# 1 Safety Instructions (continued)

# **Caution**

- 1. When selecting equipment, carefully consider the application, required specifications, and operating conditions (fluid, pressure, flow rate, filtration, and environment), making sure not to exceed the specification range.
- This product is provided for normally typical forms of use in the manufacturing industry. As such, to use the product for applications that may affect the human body directly or indirectly such as caisson shield is not foreseen.
- 3. When the product is used as an air blower for food, install an appropriate filter to eliminate foreign matter in compressed air for air blowing. (Refer to the following example of pneumatic circuit).



4. Quality management relating to hygiene for food and medical treatment is not implemented for the product.

The product is produced in same line that manufactures other product which uses other materials. In rare cases, some of these materials can be found as a residue.

- 5. Food grease used
- Fluid contact parts: NSF H1 grade grease
- Part other than fluid contact parts: NSF H1 grade grease or grease which is not NSF H1 grade
- 6. The grease used in the solenoid valves built into the product is not food grease.

Grease may drain out of the product from the solenoid valve EXH. If necessary, pipe it to the outside of the area.

- 7. The product generates particles from the wear of sliding parts inside. When the product is used as an air blower, install an appropriate filter on the outlet of the product to prevent foreign matter from flowing to the downstream. Filters require regular inspection, replacement of the element, and maintenance referring to the operation manual.
- 8. Flush the piping line before using the product for the first time and after it has been replaced. Also, if piping, etc., is to be connected, flush (air blow) before using the product for the first time in order to reduce the effects of the dust generated from the connection, etc. Flushing the line is also required to eliminate contamination resulting from the installation of piping lines. Therefore, be sure to flush the line before running the system.

# 2 Specification

	2 Specification				
Model			IN502-44 IN502-45 IN502-46		
ē	Applicable fluids			Air, Nitrogen	
Fluid	Fluid temperature range		0 to 50 °C		
		ed controlled	50 to 500	100 to 1000	200 to 2000
>		range	L/min	L/min	L/min
Flow		controlled flow range	25 to 525 L/min	50 to 1050 L/min	100 to 2100 L/min
	Mini	mum unit of set		/min	2 L/min
	cont ത	rolled flow rate	1 2/		2 2/11/11
ure	atin Ige	pressure		1.0 MPa or less	
Pressure	)per rar	Supply pressure Load pressure	(when th	0.1 to 0.6 MPa	
P.		stand pressure	(when th	<u>e flow rate is 10</u> 1.0 MPa	JU% F.3)
cal	Pow	er supply		24 VDC ±10%	
Electrical	volta	age ent consumption		0.2 A or less	
Ē		ection	P	olarity protectio	n
		trol accuracy		±5% F.S.	
		/ measurement iracy		±3% F.S.	
-	Tem	perature	15% ES (	0 to 50 °C, 25 °	C standard)
Control		acteristics sure			
ŏ		sure acteristics	±ɔ∞ F.S. ( standa	operating press ard pressure sta	ndard)
			Reaches th	e range of ±5%	F.S. of the
	Sett	ling time		ed flow rate in 0 standard press	
t	ge	Output type	Voltage outpu	it: Select from 1	to 5 V or 0 to
outp	Voltage	Output		10 V	
ne o		impedance		Approx. 1 kΩ	
Analogue output	Current	Output type	Curre	nt output: 4 to 2	20 mA
Ana	Curr	Load impedance	Ap	prox. 50 to 600	Ω
t a		Input type	Voltage input: Select from 0 to 5 V or 0 to		
Analogue input (in SIO mode)	Voltage	Input	10 V		
gue D m	٨٥	impedance	Αρρrox. 1 ΜΩ		
alog SIG	Current	Input type	Current input: 4 to 20 mA		
(ir An	Curr	Input impedance		Approx. 50 Ω	
			Select from NPN or PNP open collector		
	Output type		output Limit deviation tolerance, error output,		
	Outp	out mode	output OFF		
but de)	Swit	ch operation imum load	Normal output, reverse output		
out	curre		80 mA		
Switch output (in SIO mode)		applied	30 VDC (NPN only)		
Sw (in	volta Inter	age mal volt drop			
		sidual voltage)		ss (at 80 mA lo	
	Dela	ıy time	ວ ms or less,	variable from 0 increments	ເບ 60 s/0.01 s
	Prot	ection	Ove	er current protec	ction
	4	Reference condition	Select stan	dard or referen	ce condition
	Flow rate	Unit	L/	′min, cfm (ft³/mi	n)
	No	Display range	25 to 525	50 to 1050	100 to 2100
	ш	Minimum unit	L/min	L/min /min	L/min 2 L/min
	Pressure	Units			
		Display range	kPa, MPa, kgf/cm², bar, psi -50 to 1050 kPa		-
ay	Pre.	Minimum unit		1 kPa	
Display		lay method	LCD		
	Num	ber of displays	3 (1 main display and 2 Sub displays)		
	Disp	lay colour	Mair Si	n display: red/gi ib display: oran	een, ge
			Main dis	splay: 4-digit 7-s	segment
	Disn	layed digits		(left): 4 digits ( s. 7-segments	
	2.50	, <del>.</del>	segments, 7-segments for other) Sub display (right): 5 digits (partially 11-		
			segment	s, 7-segments t when switch ou	tor other)
	Operation LED		Turns ON when switch output is ON (OUT1: Orange)		

# 2 Specifications (continued)

Мо	dal	IN502-44	IN502-45	IN502-46
IVIO	del	111002-44	111002-40	111002-40
	Enclosure protection		IP65	
ıtal	Withstand voltage	1000 V AC for 1 minute between terminals and housing		
Environmental	Insulation resistance		een terminals 500 VDC meg	0
Enviro	Operating temperature range	nperature Operation: 0 to 50 °C, Storage: -10 to 60 °C (no condensation)		
	Operating humidity range	Operation a	ind storage: 38	5 to 85%RH
Pip	ing specification	Rc1/2		
Material in contact with fluid			lloy, POM, SU Si, NBR, HNB	, ,
Weight		eight 760 g approx. (excluding lead wire		lead wire)

#### 2.1 IO-Link specifications (for models with IO-Link)

IO-Link type	Device	
IO-Link version	V1.1	
Communication speed	COM2 (38.4 kbps)	
Min. cycle time	5.5 ms	
Process data length	Input data: 8 bytes, Output data: 2 bytes	
On request data communication	Available	
Data storage function	Available	
Event function	Available	
Vendor ID	131 (0x0083)	
Device ID	IN502-44-5/6/13/14: 575 (0x00023F) IN502-44-7/8/15/16: 576 (0x000240) IN502-45-5/6/13/14: 577 (0x000241) IN502-45-7/8/15/16: 578 (0x000242) IN502-46-5/6/13/14: 727 (0x0002D7) IN502-46-7/8/15/16: 726 (0x0002D6)	
Configuration file	IODD file (download from the SMC website)	

# 3 Name and function of parts

# 3.1 Body Connector Display Piping port (IN side) Solenoid valve EXH Body Piping port (OUT side)

Part	Description	
Connector	M12 connector for electrical connections.	
Piping port	Port for connecting piping (Rc 1/2). IN represents "inlet" and OUT represents "outlet".	
Body	Body of the product.	
Solenoid valve EXH	Exhaust port (M5 female thread) for the internal solenoid valve. Do not block the exhaust.	
Display	Displays the flow, settings and error codes (See below).	

#### IN502-TF222-147EN-C

## 3 Name and function of parts (continued)

# 3.2 Display Units display Units display Units display UP button UP button UP button Sub display FOR AIR Units display 2

Part	Description
Operation LED	LED is ON (orange) when OUT is ON.
Main display (red/green)	Displays the current controlled flow, setting mode status, selected display units and error codes.
UP button	Selects the mode and increases the ON/OFF set value.
SET button	Press this button to change the mode and to confirm settings.
DOWN button	Changes the sub display, selects the mode and decreases the ON/OFF set value.
Units display 1 (red/green)	LED turns ON when STD is selected for the reference condition.
Units display 2 (red/green)	LED indicates the selected flow rate units.
Sub display (left)	Displays (orange) the display item label.
Sub display	Displays (orange) the display item, setting value, peak/bottom value, etc.
IO-Link status indicator light	Displays OUT1 output communication status (SIO mode, start-up mode, Pre-operation mode, operation mode) and presence of communication data (for products with IO-Link only).

• Refer to the operation manual on the SMC website (URL: <u>https://www.smcworld.com</u>) for more details of the IO-Link status indicator light operation and display.

#### 4 Installation

#### 4.1 Installation

#### **Warning**

- Do not install the product unless the safety instructions have been read and understood.
- Use the product within the specified operating pressure and temperature range.

#### 4.2 Environment

#### Warning

- Do not use in an environment where corrosive gases, chemicals, salt water, water or steam are present.
- Do not use the product in an environment where the product is constantly exposed to water or oil splashes.
- Do not use in an explosive atmosphere.
- Do not expose to direct sunlight. Use a suitable protective cover.
   Do not install in a leasting subtractive to a suitable protective cover.
- Do not install in a location subject to vibration or impact in excess of the product's specifications.
   Do not mount in a location support to under the support of the support o
- Do not mount in a location exposed to radiant heat that would result in temperatures in excess of the product's specifications.
- Do not use in an area where electrical surges are generated.
- Prevent foreign matter such as remnant of wires from entering the product

# 4.3 Mounting

- Never mount the product in a location where it will be used as a foothold.
- Do not mount the product upside down.
- Mount the product so that the fluid flows in the direction indicated by the arrow on the side of the body.
- If the EXH port of the solenoid valve may be exposed to water or dust, connect a fitting and tube (sold separately) and route the tube to a safe place where it will not be affected by water or dust.

# 4 Installation (continued)

- Install the product using 4 screws suitable for the product, tightened according to the required tightening torque.
- Suitable screw: M5, Tightening torque: 3 N•m ±10%
- Screws should be prepared by the user.



Refer to the operation manual on the SMC website (URL: <u>https://www.smcworld.com</u>) for mounting hole details and outline dimensions.

# 4.4 Piping

- Caution
   Before connecting piping make sure to clean up chips, cutting oil, dust etc.
- When installing piping or fittings, ensure sealant material does not enter inside the port.
- Tighten the piping to the correct tightening torque: 20 to 25 N•m If the tightening torque is exceeded, the product can be damaged. If the tightening torque is insufficient, the connection threads and brackets may become loose.
- Confirm that there is no leakage after piping.
- When attaching a fitting, the attachment should be held with a wrench. Holding other parts with a wrench may damage the product.



#### 5 Wiring

#### 5.1 Wiring

# Caution

- Connections should only be made with the power supply turned off.
- Use a separate route for the product wiring. If wires and cables are routed together with power or high voltage cables, malfunction may result due to noise.
- If a commercially available switching power supply is used, be sure to ground the frame ground (FG) terminal. If a switch-mode power supply is connected for use, switching noise will be superimposed and the product will not be able to meet the specifications. In that case, insert a noise filter such as a line noise filter/ferrite between the switching power supply and the product, or change the switching power supply to a series power supply.

# 5 Wiring (continued)

#### 5.2 Connector installation / removal

- Align the lead wire M12 connector with the connector key groove on the controller, and insert it straight in. Turn the knurled part clockwise. Connection is complete when the knurled part is fully tightened. Check that the connection is not loose.
- To unplug the connector, loosen the knurled part and pull it straight out.

#### Connector pin layout

#### When used as a Switch output device

	· · · · · · · · · · · ·			
v 2	No.	Name	Wire colour	Function
$\bigcirc 50$	1	DC(+)	Brown	24 VDC
$\odot/$	2	An IN	White	Analogue input
3	3	DC(-)	Blue	0 V
	4	OUT	Black	Switch output
	5	An OUT	Grey	Analogue output

#### When used as an IO-Link device

No.	Name	Wire colour	Function
1	L(+)	Brown	24 VDC
2	N.C.	White	(Analogue input)
3	L(-)	Blue	0 V
4	C/Q	Black	IO-Link communication
5	N.C./ An OUT	Grey	Analogue output

\*: Do not connect pins 2 and 5 to the IO-Link master.



Refer to the operation manual on the SMC website (URL: <u>https://www.smcworld.com</u>) for further Setting details.

# 7 Initial Settings

- Configure the reference condition, unit of pressure display, and switch output PNP/NPN switch.
- Reference condition
   Standard condition or normal condition can be selected for the standard reference condition of flow rate.
   Standard condition: flow rate converted into volume at 20 °C and 101.3 kPa (absolute pressure).
   Normal condition: flow rate converted into volume at 0 °C and 101.3 kPa (absolute pressure).
   Units selection function
- Units selection function
   The flow rate display units selection function allows for selecting L/min or cfm (ft<sup>3</sup>/min) as the standard unit.
   The pressure units selection function allows for selecting kPa, MPa, kgf/cm<sup>2</sup>, bar, or psi as the standard unit.
   This setting is only available for models with the units selection function.
- Switch output type
   The switch output function can be toggled between PNP and NPN
   output

#### 8 Function Selection mode

In measurement mode, press the SET button for at least 1 second but no more than 3 seconds to display [F 0].

The mode in which  $[F_{\Box\Box}]$  is displayed and changes to the respective function settings are made is referred to as function selection mode. Press the SET button for 2 seconds or longer in function selection mode

to return to measurement mode.

Note: Some functions are not supported on models with specific product numbers. [---] will be displayed on the sub display (right) for functions that are not supported or cannot be selected due to other settings.

Measurement mode

Press the SET button between 1 and 3 seconds



# 8.1 Default settings

- The factory default settings are as follows. If these settings are acceptable, retain for use. To change a setting, enter function selection mode.
- [F 0] Reference condition, unit of pressure display, and switch output PNP/NPN.

Item	Default setting
Reference condition	Standard condition
Flow rate display unit	L/min
Pressure display unit	kPa
Switch output PNP/NPN switch	PNP

• [F 1] Setting of OUT1

Item	Description	Default setting
Output mode	Limit deviation tolerance mode, error output mode, or switch output off can be selected.	Limit deviation tolerance mode
Reverse output	Selects which switch output is used, Normal or Reverse.	Normal output
Limit deviation tolerance	Sets the switch output on or off when measured flow rate is within the limit deviation tolerance of set flow rate.	±2% F.S.
ON delay time	Delay time (rising) of switch output can be selected.	0.00 sec.
OFF delay time	Delay time of (falling) switch output can be selected.	0.00 sec.
Display colour	Select the display colour.	Output ON: Green Output OFF: Red

#### IN502-TF222-147EN-C

#### 8 Function Selection mode (continued)

•	Other	Function	Settings
---	-------	----------	----------

Item	Default setting	
[F10] Sub display setting	dEF (standard)	
[F14] Zero cut-off setting	5.0% F.S.	
[F21] Analogue input setting	Voltage input: 0 to 5 V Current input: No configurable items	
[F22] Analogue output setting	Voltage output: 1 to 5 V Current output: No configurable items	
[F32] Control parameter setting	0.000	
[F33] Output process data setting in the event of abnormal communication	Output process data: 0	
[F80] Power saving mode setting	OFF	
[F81] Security code	OFF	
[F90] Setting of all functions	OFF	
[F96] Input check	No configurable items	
[F98] Output check	N/A (normal output)	
[F99] Reset to default settings	OFF	

#### 9 Other Settings

- Peak / Bottom value display
- Zero clear
- Key-lock function

Refer to the operation manual on the SMC website (URL: <u>https://www.smcworld.com</u>) for setting these functions.

# 10 IO-Link parameter setting

#### • IODD file

IODD (I/O Device Description) is a definition file which provides all properties and parameters required for establishing functions and communication of the device.

IODD includes the main IODD file and a set of image files such as vendor logo, device picture and device icon.

The IODD file list is shown below.

Product No.	IODD file *1	
IN502-44-5/6/13/14	SMC-IN502-44-5_6_13_14-yyyymmdd-IODD1.1	
IN502-44-7/8/15/16	SMC-IN502-44-7_8_15_16-yyyymmdd-IODD1.1	
IN502-45-5/6/13/14	SMC-IN502-45-5_6_13_14-yyyymmdd-IODD1.1	
IN502-45-7/8/15/16	SMC-IN502-45-7_8_15_16-yyyymmdd-IODD1.1	
IN502-46-5/6/13/14	SMC-IN502-46-5_6_13_14-yyyymmdd-IODD1.1	
IN502-46-7/8/15/16	SMC-IN502-46-7_8_15_16-yyyymmdd-IODD1.1	

 $\ast 1:$  "yyyymmdd" indicates the file preparation date. yyyy is the year, mm is the month and dd is the date.

• The latest IODD file can be downloaded from the SMC website (<u>https://www.smcworld.com</u>).

## 11 How to Order

Refer to the SMC website (URL: <u>https://www.smcworld.com</u>) for more How to Order details.

#### 12 Outline Dimensions (mm)

Refer to the SMC website (URL: <u>https://www.smcworld.com</u>) for details of Outline dimensions.

#### 13 Troubleshooting

#### 13.1 Error indication

13.1 Error indication				
Error name	Error display	Description	Measures	
Over current error	Er 1	The switch output load current is 80 mA or more.	Turn the power off and remove the cause of the over current. Then supply the power again.	
Residual pressure error	Er 3	During a zero-clear operation, pressure greater than ±50 kPa is applied. The zero-clear range varies by ±10 kPa due to variation between individual products.	Adjust the applied pressure to atmospheric pressure and retry the zero-clear operation.	
Controlled flow rate not reached	ErSO	The controlled flow rate has not reached the set flow rate within 5 seconds.	<ol> <li>(1) Refer to the operation manual to use the product within the controllable flow rate range.</li> <li>(2) Review the installation space environment, including the piping diameter.</li> </ol>	
Connected load error	Ersi	The operating pressure range has been exceeded due to connected load.	Check that the load pressure is within the operating pressure range.	
Control error	Er 52 Er 53 Er 54	<ul> <li>(1) The internal solenoid valve or sensor is not operating normally.</li> <li>(2) The product is possibly mounted in the opposite orientation (IN- OUT).</li> </ul>	<ul> <li>(1) Check that the power supply voltage is 24 VDC ±10%.</li> <li>Turn the power off, then on again, then perform a zero-clear operation.</li> <li>(2) Mount the product in the correct orientation.</li> </ul>	
Excess flow rate error	XXX	The flow rate has exceeded the upper limit of the displayable flow range.	The flow display will resume when the flow rate is within the displayable flow range.	
System error	Er 0 Er 4 Er 6 Er 7 Er 8 Er 9 Er 40	Displayed if an internal data error has occurred.	Turn the power off and on again.	

If the error cannot be reset after the above measures are taken, or errors other than the above are displayed, please contact SMC.

#### 14 Maintenance

#### 14.1 General Maintenance

# **Caution**

- Not following proper maintenance procedures could cause the product to malfunction and lead to equipment damage.
- If handled improperly, compressed air can be dangerous.
  Maintenance of pneumatic systems should be performed only by qualified personnel
- Before performing maintenance, turn off the power supply and be sure to cut off the supply pressure. Confirm that the air is released to atmosphere.
- After installation and maintenance, apply operating pressure and power to the equipment and perform appropriate functional and leakage tests to make sure the equipment is installed correctly.
- If any electrical connections are disturbed during maintenance, ensure they are reconnected correctly and safety checks are carried out as required to ensure continued compliance with applicable national regulations.
- Do not make any modification to the product.
- Do not disassemble the product, unless required by installation or maintenance instructions.
- How to reset the product after a power cut or when the power has been unexpectedly removed
- The settings for the product are retained in memory prior to the power loss or de-energizing of the product.

The output condition is also recoverable to that prior to the power loss or de-energizing. However, this may change depending on the operating environment. Therefore, check the safety of the whole installation before operating the product.

If the installation is using accurate control, wait until the product has warmed up (approximately 10 to 15 minutes) before operation.

#### 15 Limitations of Use

**15.1 Limited warranty and Disclaimer/Compliance Requirements** Refer to Handling Precautions for SMC Products.

#### 16 Product disposal

This product should not be disposed of as municipal waste. Check your local regulations and guidelines to dispose of this product correctly, in order to reduce the impact on human health and the environment.

#### **17 Contacts**

Refer to <u>www.smcworld.com</u> or <u>www.smc.eu</u> for your local distributor / importer.

# **SMC** Corporation

URL: <u>https://www.smcworld.com</u> (Global) <u>https://www.smc.eu</u> (Europe) SMC Corporation, 1-5-5, Kyobashi, Chuo-ku, Tokyo 104-0031, JAPAN Specifications are subject to change without prior notice from the manufacturer. © SMC Corporation All Rights Reserved. Template DKP50047-F-085O