

ORIGINAL INSTRUCTIONS

Instruction Manual

Space Saving Vacuum Unit Series ZQ□A





Manifold



Single Unit

the operation of suction and release.

The intended use of the vacuum unit is to generate vacuum and control

1 Safety Instructions

These safety instructions are intended to prevent hazardous situations and/or equipment damage. These instructions indicate the level of potential hazard with the labels of "Caution," "Warning" or "Danger." They are all important notes for safety and must be followed in addition to International Standards (ISO/IEC) "1), and other safety regulations.

1) ISO 4414: Pneumatic fluid power - General rules relating to systems. ISO 4413: Hydraulic fluid power - General rules relating to systems. IEC 60204-1: Safety of machinery - Electrical equipment of machines. (Part 1: General requirements)

ISO 10218-1: Manipulating industrial robots -Safety. etc.

- Refer to product catalogue, Operation Manual and Handling Precautions for SMC Products for additional information.
- Keep this manual in a safe place for future reference.

A Caution	Caution indicates a hazard with a low level of risk which, if not avoided, could result in minor or moderate injury.
A Warning	Warning indicates a hazard with a medium level of risk which, if not avoided, could result in death or serious injury.
▲ Danger	Danger indicates a hazard with a high level of risk which, if not avoided, will result in death or serious injury.

Marning

- Always ensure compliance with relevant safety laws and standards.
- All work must be carried out in a safe manner by a qualified person in compliance with applicable national regulations.

2 Specifications

General Specifications

Ambient temperature range [°C]	5 to 50(no condensation)	
Fluid	Air	
Vibration resistance [m/s ²]*1)	20	
Impact resistance [m/s²] *2)	100	

Note *1) 10 to 150 Hz for 2 hours in each direction of X, Y and Z (De-energized, Initial valve).

Note *2) 3 times in each direction of X, Y and Z (De-energized, Initial valve).

2.2 Vacuum Eiector Specifications

ziz vacadii zjecici opecinicatione				
Model		ZQ05□A	ZQ07□A	ZQ10□A
Nozzle diameter [mm]		0.5	0.7	1.0
Standard supply pressure [MPa]		0.35	0.43	
Max vacuum pressure [kPa]*1)		-80		
Max suction flow rate [L/min(ANR)]*1)		5	10	22
Air consumption [L/min(ANR)]*1)		15	25	47
Supply pressure	P Port	0.3 to 0.5		
range [MPa]	PD Port*2)		0 to 0.45	

Note *1) Values are at the same standard supply pressure and based on SMC's measurement standards. They depend on atmospheric pressure (weather, altitude, etc.) and measurement method.

Note *2) Must be 0.05MPa or more, lower than P Port pressure.

Port Types: P: Air supply port, PD: Vacuum release port, PV: Common vacuum supply pressure port, PS: Common pilot pressure supply port

2.3 Vacuum Pump System Specifications

Model	ZQ000□A	
Flow rate	C [dm ³ /(s·bar)]	0.31
characteristics of V to	В	0.23
PV`	Cv	0.09
Flow rate	C [dm ³ /(s·bar)]	0.24
characteristics of PS	В	0.26
to V*1)	Cv	0.08
Supply pressure	PV port [kPa]	0 to -101.3
range	PS port [MPa]	0.3 to 0.5
	PD port [MPa] *2)	0 to 0.45

Note *1) When needle is fully open.

Note *2) Must be 0.05MPa or more, lower than PS Port pressure.

2.4 Vacuum Pressure Switch Specifications

Node Vacuum Compound Pressure Energy Saving Pressure Pressure Saving Pressure Node Pressure Pr	2.4 Yaddan Freddare Owner Opcomoditions					
Rated pressure range Rated pressure range O to -101 kPa -100 to 100 kPa Set pressure range Withstand pressure Minimum setting unit Power supply voltage Current consumption Max load current Max applied voltage Residual voltage Response time Short circuit protection Pressure Pressure 10 to - 100 to 100 kPa -105 to 105 kPa -105 to 105 kPa 105 kPa -105 to 105 kPa -105 kPa Power supply polarity protection A0 mA or less NPN or PNP open collector: 2 outputs (selectable) NPN or PNP. Output 1: General purpose, Output 2: Valve control A0 mA 26.4V(NPN output) Residual voltage 2V or less (with 80mA load current) 2.5 ms or less (Response time selections with anti-chattering function: 20, 100, 500, 1000 and 2000 ms) Short circuit protection With short-circuit protection			ZSE10			
Rated pressure range Rea	Model			•	saving	
Withstand pressure Minimum setting unit Power supply voltage Current consumption Max load current Max applied voltage Residual voltage Response time Short circuit protection Minimum setting unit 12 to 24 VDC ±10%, Ripple (p-p) 10% or less (with power supply polarity protection) 40 mA or less NPN or PNP open collector: 2 outputs (selectable) NPN or PNP. Output 1: General purpose, Output 2: Valve control 28V (NPN output) 26.4V(NPN output) 25 ms or less (with 80mA load current) 2.5 ms or less (Response time selections with anti-chattering function: 20, 100, 500, 1000 and 2000 ms) With short-circuit protection	Rated press	sure range		-100 to 100 kPa		
Minimum setting unit Power supply voltage Current consumption Switch output Max load current Max applied voltage Response time Short circuit protection A12 to 24 VDC ±10%, Ripple (p-p) 10% or less (with power supply polarity protection) 40 mA or less NPN or PNP open collector: 2 outputs (selectable) NPN or PNP. Output 1: General purpose, Output 2: Valve control A28V (NPN output) 26.4V(NPN output) 26.4V(NPN output) 25.5 ms or less (with 80mA load current) 2.5 ms or less (Response time selections with anti-chattering function: 20, 100, 500, 1000 and 2000 ms) Short circuit protection With short-circuit protection	Set pressure	e range		–105 to 105 kPa		
Power supply voltage 12 to 24 VDC ±10%, Ripple (p-p) 10% or less (with power supply polarity protection) Current consumption A0 mA or less NPN or PNP open collector: 2 outputs (selectable) Max load current Max applied voltage Residual voltage Response time Response time Short circuit protection 12 to 24 VDC ±10%, Ripple (p-p) 10% or less (with power supply polarity protection NPN or PNP open collector: 2 outputs (selectable) NPN or PNP. Output 1: General purpose, Output 2: Valve control 25 ensor less (NPN output) 26.4V(NPN output) 25.5 ms or less (Response time selections with anti-chattering function: 20, 100, 500, 1000 and 2000 ms) Short circuit protection With short-circuit protection	Withstand p	ressure				
Switch output Switch output	Minimum se	etting unit	0.1kPa			
Switch output NPN or PNP open collector: 2 outputs (selectable) NPN or PNP. Output 1: General purpose, Output 2: Valve control	Power supply voltage					
Switch output NPN or PNP open collector: 2 outputs (selectable) PNP. Output 1: General purpose, Output 2: Valve control	Current consumption		40 mA or less			
Max applied voltage Residual voltage 28V (NPN output) 26.4V(NPN output) 20.4V(NPN out	Switch output		collector: 2 outputs		PNP. Output 1: General purpose, Output 2:	
voltage 28V (NPN output) output) Residual voltage 2V or less (with 80mA load current) 2.5 ms or less (Response time selections with anti-chattering function: 20, 100, 500, 1000 and 2000 ms) Short circuit protection With short-circuit protection		Max load current	80mA			
Response time 2.5 ms or less (Response time selections with anti-chattering function: 20, 100, 500, 1000 and 2000 ms) Short circuit protection With short-circuit protection			28V (NF	PN output)		
Response time with anti-chattering function: 20, 100, 500, 1000 and 2000 ms) Short circuit protection With short-circuit protection			2V or less (with 80mA load current)			
protection With short-circuit protection			with anti-chattering function: 20, 100, 500,			
Repeatability +0.2% F.S. +1 digit		protection	With short-circuit protection		otection	
1.0.276 1.0. ±1 digit	Repeatability		±0.2% F.S. ±1 digit			

2 Specifications - continued

2.5 Vacuum Pressure Switch Specifications- continued

Hysteresis mode	Vacuum Pressure	Compound Pressure	Energy saving	
			pressure	
	Variable (0 or above) Note 1)			
Window comparator mode	Variable (o or above)		-	
Output voltage	1 to 5 V ±2.5% F.S.		-	
Linearity	±1% F.	S. or less	-	
Impendence	Appro	ox. 1 kΩ	-	
Display system		3 1/2-digit, 7 segment LED 1-color display (Red)		
Display accuracy		±2% F.S. ±1 digit (at ambient temperature of 25 ±3°C)		
Indicator light		Lights when ON, OUT1: Green, OUT2: Red		
Enclosure	IP40			
Ambient humidity range	Operating/Stored: 35 to 85% RH (with no condensation)			
Withstand voltage	1000 VAC for 1 min. between terminals and housing			
Insulation resistance	$50~\text{M}\Omega$ or more (500 VDC measured via megohmmeter) between terminals and housing			
Temperature Characteristics		±2% F.S. (at 25°C of ambient temperature range between –5 and 50°C)		
Lead wires		Oil-resistant cabtire cord Cross section: 0.15 mm² (AWG26), 5 cores, Conductor O.D.: 1.0 mm		
	Comparator mode Output voltage Linearity Impendence Enclosure Ambient humidity range Withstand voltage Insulation resistance	Comparator mode Output voltage Linearity ±1% F.: Impendence Approximate a series and a serie	comparator mode Variable (o or above) Output voltage 1 to 5 V ±2.5% F.S. Linearity ±1% F.S. or less Impendence Approx. 1 kΩ 3 1/2-digit, 7 segment LE display (Red) ±2% F.S. ±1 digit (at a temperature of 25 ± Lights when ON, OUT1 OUT2: Red Enclosure IP40 Ambient humidity range Operating/Stored: 35 to 85 no condensation Withstand voltage 1000 VAC for 1 min. b terminals and hous terminals and hous ing Insulation resistance 50 MΩ or more (500 VDC row and housing) ±2% F.S. (at 25°C of a temperature range between temperature range between temperature range between temperature range between temperature range temperature	

2.6 Vacuum Pressure Switch with IO-Link

Model		ZQ-ZSEL000-0-A	ZQ-ZSFL====-A	
Rated pressure range		0 to -101 kPa	100 to -100 kPa	
Set pressure range		10 to -105 kPa	105 to -105 kPa	
Proof pres	ssure	500	kPa	
Minimum	setting unit	0.1 l	кРа	
Power su	pply voltage	24VDC±10%, Ripple(P-P)10% or less (Protected against reverse connection)		
Current c	onsumption	40 mA or less		
Switch output		PNP open collector 2 outputs (For valves)		
	Residual voltage	2 V or less (at 80mA load current)		
	Short circuit protection			
Repeatab	ility	±0.2%F.5		
Hysteresis		Variable	from 0.1	
Display type		3 1/2 digit, 7 segment LED, 1-color display(red)		
Display accuracy		±2%F.S. ±1 digit(At ambient temperature 25±3 °C)		
Indication LED		Lights up when the valve is turned on. Release valve (OUT1): Green, Supply valve (OUT2): Red		
Digital filte	er	Variant from 0 to 10s (0.01s steps)		
Enclosure		IP4	40	
Withstand voltage		1000 VAC for 1 minutes between terminals and housing		
nvironmeni resistance	Insulation resistance	50 MΩ or more between (with 500 VDC me		
Environmental resistance	Ambient temperature	Operation: -5 to 50°C, S condensation or fi		
ш	Ambient	Operation/Storage:	35 to 85 %RH (No	
humidity		condensation)		
Temperature characteristics		±2%F.S. (25°C standard)		
Lead wire		Cable: 3 wires, φ3.4, 300 mm, Insulator O.D.: 1.0mm Valve connector lead wire: 100mm, Insulator O.D.: 1.5mm		

2 Specifications - continued

2.7 Supply and Release Valve Specifications

Туре	Normally Closed	Normally Open	
Model	Z1-V114-5LU ZQ1-V124-5MU-A		
Manual override	Non-locking push type/slotted locking type		
Rated coil voltage	24 [OCV	
Allowable voltage fluctuation	-10 to 10%		
Power consumption	0.4W at start-up, 0.1W at holding (power saving circuit)		
Lead wire entry	L-shaped plug connector (with light/surge voltage suppressor)	M-shaped plug connector (with light/surge voltage suppressor)	
Lead wire	Conductor effective area 0.2 to 0.33 mm², Maximum outer sheath O.D. 1.7 mm		
Pofor to catalogue for more datails			

Refer to catalogue for more details.

3 Installation

3.1 Installation

Marning

- Do not install the product unless the safety instructions have been read and understood.
- When mounting the product, tighten it with the recommended tightening torque (0.54 to 0.66 N•m).
- When mounting the manifold product, use the attached washers.
- When installing the product, secure the space required for maintenance and inspection of the product
- Do not drop, hit, or apply excessive impact to the product.

3.2 Environment

- Do not use in an environment where corrosive gases, chemicals, salt water or steam are present.
- Do not use in an explosive atmosphere.
- Do not expose to direct sunlight. Use a suitable protective cover.
- Do not install in a location subject to vibration or impact in excess of

the product's specifications.

- Do not mount in a location exposed to radiant heat that would result in temperatures in excess of the product's specifications
- The suction filter used in this product is a simple one. If there is a lot of dust in the usage environment, please consider using a suction filter (ZFC series, etc.).
- Do not use in place where static electricity build-up can occur.
- Do not use in an environment where surges occur.

3.3 Air Supply

A Caution

- Do not use air containing chemicals, synthetic oils containing organic solvents, salts, or corrosive gases.
- Recommended quality of the supplied air be equivalent to the compressed air cleanliness grade "2: 6: 3" according to ISO8573-1: 2010.
- Do not supply the pressure in excess of the product's specifications.

3.4 Piping

A Caution

- Before connecting piping make sure to clean up chips, cutting oil, dust, etc.
- When piping pipe fittings to the pilot pressure exhaust (PE) port (M3) of the single specification, fix the parts where the port is installed, tighten by hand, and then use an appropriate tool to make about 1/4 turn. (Recommended tightening torque: 0.4 to 0.5 Nm)
- When piping pipe fittings to the pilot pressure exhaust (P) port, etc. (M5) of the single specification, fix the parts where the port is installed, tighten by hand, and then use an appropriate tool to make about 1/6 to 1/4 turn. (Recommended tightening torque: 1.0 to 1.5 Nm)
- When piping the tube to the one-touch fitting, grasp the tube, slowly
 insert it into the one-touch fitting, and insert it all the way in. After
 inserting it all the way, pull the tube lightly and check that it does not
 come off.

Page 1 of 2

3 Installation - continued


3.5 Wiring to the solenoid valve and pressure switches

Refer to the operation manual of solenoid valve (V100 series) and pressure switch (ZSE10 series). Manuals can be found by the links below:

ZSE10: https://www.smcworld.com/manual/en-jp/?k=zse10 V100: https://www.smcworld.com/manual/en-jp/?k=V100

4 Settings

4.1 Manual Override (With supply valve and release valve)



Refer to the operation manual of the solenoid valve V100 series for the manual operation method.

4.2 Release flow adjusting needle

When the release valve is turned on, vacuum release air is let out.

The release flow adjusting needle allows to control the vacuum break air flow rate.

Loosen the lock nut and use a flat-blade screwdriver to adjust the release flow rate adjustment needle at the back of the lock nut.

The breaking flow rate adjustment needle can be turned clockwise to reduce the release flow rate, and counterclockwise to increase the release flow rate.

After adjusting the release flow rate adjustment needle, tighten the lock nut to fix the adjustment position.

5 How to Order

Refer to the catalogue for 'How to Order'

6 Outline Dimensions (mm)

Refer to the catalogue for outline dimensions.

7 Maintenance

7.1 General Maintenance


A Caution

- Not following proper maintenance procedures could cause the product to malfunction and lead to equipment damage.
- If handled improperly, compressed air can be dangerous.
- Maintenance of pneumatic systems should be performed only by qualified personnel.
- Before performing maintenance, turn off the power supply and be sure to cut off the supply pressure. Confirm that the air is released to atmosphere.
- After installation and maintenance, apply operating pressure and power to the equipment and perform appropriate functional and leakage tests to make sure the equipment is installed correctly.
- If any electrical connections are disturbed during maintenance, ensure they are reconnected correctly, and safety checks are carried out as required to ensure continued compliance with applicable national regulations.
- Do not make any modification to the product.
- Do not disassemble the product, unless required by installation or maintenance instructions
- Implement the maintenance and check shown below to use the space saving vacuum unit safely and in an appropriate way for a long period of time.
- Drain the air filter and mist separator regularly
- Replace the sound absorbing material (silencer) built into the ejector regularly
- Refer to the online operation manual for replacement parts.
- Do not use benzene or thinner for cleaning

7 Maintenance - continued


7.2 Sound absorbing material replacement method

- Single Unit
- Loosen the assembly screws (2 pieces) of the silencer plate and remove the silencer plate (2 pieces) and the sound absorbing material
- Replace the silencer plate (2 sheets) and the sound absorbing material
- Assemble the silencer plate with the assembly screws (recommended tightening torque: 0.028 to 0.032 Nm).




Manifold

- Loosen the two assembly screws of the silencer block and remove the silencer block.
- Replace the sound absorbing material built into the silencer block.
- Assemble the silencer block with the assembly screws (recommended tightening torque: 0.25 to 0.31 Nm).



7.3 Filter element replacement method

- · Loosen the tension bolt and remove the filter case.
- Replace the filter element built into the filter case.
- Assemble the filter case with tension bolts (recommended tightening torque: 0.12 to 0.18 Nm).



8 Limitations of Use

8.1 Limited warranty and Disclaimer/Compliance Requirements Refer to Handling Precautions for SMC Products.

↑ Caution

- Exhaust from Space saving vacuum unit (ejector system)
- For the silencer exhaust type, make sure that there is no obstruction around the exhaust port.
- In the case of port exhaust type, exhaust resistance may be affected depending on the pipe diameter and length, so make sure that the back pressure is 1 kPa or less.
- Do not block the exhaust port.

· Ejector exhaust noise

When the vacuum ejector generates a vacuum, an intermittent noise (abnormal noise) may be generated from the exhaust section near the standard supply pressure where the vacuum pressure peaks, and the vacuum pressure may not be constant. There is no problem in use as long as the vacuum pressure range is sufficient for adsorption, but if you are concerned about the sound or affect the setting of the pressure switch, slightly change the supply pressure and reduce the range of the intermittent sound. Please avoid it.

· About the release flow rate adjusting needle

- Leakage cannot be reduced to zero when the needle is fully closed.
- Since the release flow rate adjustment needle has a retaining mechanism, it will not rotate beyond the rotation stop position. If you try to turn the needle any further, it may be damaged.
- When tightening the lock nut, tighten it by hand to about 15 to 30 degrees, and be careful not to damage it due to overtightening.

About solenoid valve and pressure switch

For the solenoid valve (V100 series) and pressure switch (ZSE10 series), refer to each instruction manual.

9 Product disposal

This product should not be disposed of as municipal waste. Check your local regulations and guidelines to dispose this product correctly, in order to reduce the impact on human health and the environment.

10 Contacts

Refer to <u>www.smcworld.com</u> or <u>www.smc.eu</u> for your local distributor/importer.

SMC Corporation

URL: https://www.smcworld.com (Global) https://www.smc.eu (Europe) SMC Corporation, 4-14-1, Sotokanda, Chiyoda-ku, Tokyo 101-0021, Japan Specifications are subject to change without prior notice from the manufacturer. © 2021 SMC Corporation All Rights Reserved. Template DKP50047-F-085M