# ITV2-TFI12-A **SMC** Installation and Maintenance Manual

# Electro-Pneumatic Regulator Series ITV2000-Q, ITV2090-Q, ITV3000-Q €€

# 1 Safety Instructions

This manual contains essential information for the protection of users and others from possible injury and/or equipment damage.

- Read this manual before using the product, to ensure correct handling, and read the manuals of related apparatus before use.
- Keep this manual in a safe place for future reference.
- These instructions indicate the level of potential hazard by label of "Caution", "Warning" or "Danger", followed by important safety information which must be carefully followed.
- To ensure safety of personnel and equipment the safety instructions in this manual and the product catalogue must be observed, along with other relevant safety practices.

A	Caution	Indicates a hazard with a low level of risk, which if not avoided, could result in minor or moderate injury.
A	Warning	Indicates a hazard with a medium level of risk, which if not avoided, could result in death or serious injury.
A	Danger	Indicates a hazard with a high level of risk, which if not avoided, will result in death or serious injury.

· Electromagnetic compatibility:

This product is class A equipment intended for use in an industrial environment. There may be potential difficulties in ensuring electromagnetic compatibility in other environments due to conducted as well as radiated disturbances.

#### A Warning

• The compatibility of pneumatic equipment is the responsibility of the person who designs the pneumatic system or decides its specifications

Since the products specified here can be used in various operating conditions, their compatibility with the specific pneumatic system must be based on specifications or after analysis and/or tests to meet specific requirements

• Only trained personnel should operate pneumatically operated machinery and equipment.

Compressed air can be dangerous if an operator is unfamiliar with it. Assembly, handling or repair of pneumatic systems should be performed by trained and experienced personnel.

- Do not service machinery/equipment or attempt to remove components until safety is confirmed.
- Inspection and maintenance of machinery/equipment should only be performed after confirmation of safe locked-out control positions.
- When equipment is to be removed, confirm the safety process as mentioned above. Switch off air and electrical supplies and exhaust all residual compressed air in the system.
- Before machinery/equipment is re-started, ensure all safety measures to prevent sudden movement of cylinders etc. (Supply air into the system gradually to create back pressure, i.e. incorporate a soft-start valve).
- Do not use this product outside of the specifications. Contact SMC if it is to be used in any of the following conditions:
- · Conditions and environments beyond the given specifications, or if the product is to be used outdoors.
- Installations in conjunction with atomic energy, railway, air navigation, vehicles, medical equipment, food and beverage, recreation equipment, emergency stop circuits, press applications, or safety equipment.
- An application, which has the possibility of having negative effects on people, property, or animals, requiring special safety analysis.

	A	Caution		
--	---	---------	--	--

• Ensure that the air supply system is filtered to 5 microns.


Model		ITV2(3)01*	ITV2(3)03*	ITV2(3)05*	ITV209*	
Min. supply pressure		(Set pressure) + 0.1 MPa			(Set pressure) –13.3 kPa	
Max. supply	pressure	0.2 MPa	1.0 MPa		-101 kPa	
Set pressure	range	0.005 ~ 0.1 MPa	0.005 ~ 0.5 MPa	0.005 ~ 0.9 MPa	-1.3 ~ -80 kPa	
Max. flow rat	e	1500 l/min (ITV20*0), 4000 l/min (ITV30*0)				
Supply volta	ge	24 VDC±10%, 12 to 15 VDC				
Current	24 VDC	Max. 120 mA				
consumption	12 VDC	Max. 180 mA				
Input signal	Current type <sup>Note1</sup>	4-20 mADC, 0-20 mADC				
	Voltage type	0-5 VDC, 0-10 VDC				
Input	Current type	Max. 250 $\Omega^{\text{Note 4}}$				
impedance	Voltage type	Approx. 6.5 kΩ				
Output	Analogue	1-5 VDC (Load Impedance:1kΩ or more)				
signal <sup>Note2</sup>	Switch	NPN - Open collector type: 30 V 30 mA PNP - Open collector type: 30 mA				
Linearity	•	Max. ±1%F.S.				
Hysteresis		Max. 0.5%F.S.				
Repeatability	/	Max. ±0.5%F.S.				
Sensitivity		Max. 0.2%F.S.				
Temperature characteristics		Max. ±0.12%F.S./°C				
Operating temperature		0~50°C (without condensation)				
Pressure	Accuracy					
	Min. Unit	MPa: 0.01, kgf/cm <sup>2</sup> : 0.01, bar: 0.01, PSI: 0.1 <sup>Note 3</sup> , kPa: 1			kPa: 1	
Protection st	ructure	Main unit: IP65, Cable connector: IP67				

- Note 1: Two wire control, 4 to 20 mADC and 0 to 20 mADC are not available. Supply voltage of 12-15VDC or 24 VDC is required.
- Note 2: Make selection of analogue or switch output: also select NPN or PNP output when switch output is selected.
- Note 3: 1 PSI is the minimum unit on ITV\*05\*.
- Note 4: Value for the state with no over current included. If an allowance is provided for an over current circuit, the input impedance varies depending on the input current. This is 350  $\Omega$  or less for an input current of 20 mA DC.

# **3 Operation Principle**


- -

ITV2000, ITV3000: When the input signal increases the supply solenoid valve **0** turns on and the exhaust solenoid valve **2** turns off. Supply pressure is passed to the pilot valve **9** through the supply solenoid valve. The pilot valve will open the main valve allowing partial supply pressure to pass to the out port. The pressure sensor **3** will provide output pressure feedback to the control circuit . The control circuit will balance the input signal and output pressure to ensure that the output pressure remains proportional to the input signal.



# 3 Operation Principle (continued)


ITV2090: When the input signal increases, the vacuum solenoid valve 0 turns on and the atmospheric pressure solenoid valve Oturns off. Because of this, the VAC and pilot chamber 
e are connected; the pressure in the pilot chamber 6 becomes negative and acts on the top of the diaphragm. As a result, the vacuum pressure valve **9**, which is linked to the diaphragm (a), opens, VAC and OUT are connected, and the set pressure becomes negative. This negative pressure feeds back to the control circuit <sup>(3)</sup> via the pressure sensor **9**. Then, a correct operation works until a vacuum pressure proportional to the input signal is reached, and a vacuum pressure is obtained which is always proportional to the input signal.






#### **A** Caution

Connect the cable to the connector on the main unit as shown in the following diagram. Take precautions, as incorrect wiring will damage the unit. Use a DC power supply capable of supplying the necessary power requirements with minimal ripple.





0 to 10 VDC

Black

0 to 20 mADC

Fig. 5 - Wiring diagrams






Fig. 2 - Schematic diagram for ITV2000 & ITV3000 series

Fig. 6 – Connector types

## **5 Setting the Regulator**

A Caution

When the 'set' key is operated minimum/maximum pressure will be present at the outlet port. When primary pressure is applied to the regulator minimum pressure will be present at the outlet port.




Fig. 7 - Key features of the ITV.

• Release 'Key Lock 'as explained in section 'Function of Key-Lock' • After releasing key lock, SET needs to be pressed again to get to F-1 • To set minimum pressure (display shows F-1) use up/down keys and press 'Set' key to 'Lock' setting.

• To set maximum pressure (display shows F-2) use up/down keys and press 'Set' key to 'Lock' setting.

Note 1: If the above sequence has been followed correctly, the settings will complete automatically.

Note 2: If only setting minimum pressure, when pressure is 'Set', pressing the set button once more will 'skip' to the next step...

# 6 Function of Key-Lock

The keys are locked after connecting power and cannot be operated. 'Loc' is displayed when any keys are pushed.

Key-Lock Release

• Push 'Down' key for longer than 2 seconds.

Display will flash 'Loc' (locked).

Push 'Set' key to unlock.

Note: To cancel push 'Up' key.

• Key-Lock• Push 'Up' key for longer than 2 seconds. Display will flash 'unL' (unlocked). · Push 'Set' key to lock.

Note: To cancel push 'Down' key.

#### 7 Function of the 'Error' Display

If an abnormality is detected by the ITV the LED display will show 'Er' followed by a code number. Isolate the power supply and ascertain the problem and solve. Re-instate power supply after correcting fault. Error codes are as shown in the table below.

No	Content	Display
1	Input signal is outside specification	Er 1
2	EEProm read/write error	Er 2
3	Memory read/write error	Er 3
4	Solenoid valve fault	Er 4
5	Switch output over-current	Er 5

## **8 Reset Function**

• Push 'Up' and 'Down' keys (Fig 7) together for longer than 3 seconds. Display shows 'RES'.

• Release keys to reset minimum pressure and maximum pressure.

#### ITV2-TFI12-A

#### 9 Installation & Maintenance

A Caution

- If the electrical supply fails, settings are 'held' for a short period. • If the air pressure fails with power 'on' the solenoid will 'flutter'. Turn off the power.
- If the monitor output function is not used, ensure that the wire is totally insulated.
- This product is pre-set at the factory and must not be dismantled by the user. Contact your local SMC office for advice.
- Ensure, when installing this product, that it is kept clear of power lines to avoid noise interference.
- Ensure that load surge protection is fitted when inductive loads are present (i.e. solenoid, relay etc.).
- Ensure precautions are in place if the product is used in a 'free flow output 'condition. Air will continue to flow continuously.
- Do not use a lubricator on the input side of this product. If lubrication is necessary, place the lubricator on the 'output' side.
- Ensure all air is exhausted from the product before maintenance.
- Length of connector cable shall be 10 m maximum.

#### **10 Contacts**

AUSTRIA BELGIUM CZECH REP. DENMARK FINLAND FRANCE GERMANY GREECE HUNGARY IRELAND ITALY

NETHERLANDS NORWAY POLAND PORTUGAL SLOVAKIA SLOVENIA SPAIN SWEDEN SWITZERLAND UNITED KINGDOM

# SMC Corporation

URL: http://www.smcworld.com (Global) http://www.smceu.com (Europe) Specifications are subject to change without prior notice from the manufacturer. © 2009 SMC Corporation All Rights Reserved.