

Rotary Clamp Cylinder/Double Guide Type


MK2T Series

∅20, ∅25, ∅32
∅40, ∅50, ∅63

The Replacement Procedure is on p. 404

Construction

MK2T□20 to 63



In case of clamp stroke 50 mm

* The numbers correspond with those in the "Construction" of the MK2T series in the Best Pneumatics catalog.

Seal Kit List

No.	Description	Material	Note
19	Gasket	NBR	
20	Coil scraper	Bronze	
21	Piston seal	NBR	
22	Rod seal	NBR	

Replacement Parts: Seal Kit

Bore size (mm)	Part no.	Content
20	MK2T20-PS	Set of nos. 19, 20, 21, 22
25	MK2T25-PS	
32	MK2T32-PS	
40	MK2T40-PS	
50	MK2T50-PS	
63	MK2T63-PS	

* The seal kit includes 19, 20, 21, 22. Order the seal kit based on each bore size.

Actuators

Modular F.R.L.
Pressure Control Equipment

Air Preparation
Equipment

Industrial Filters

Replacement
Procedure

Actuators

Modular F.R.L.
Pressure Control Equipment

Industrial Filters