

ORIGINAL INSTRUCTIONS

Instruction Manual Digital Flow Switch – Modular type PF3A701H / PF3A702H

OIO-Link



The intended use of the digital flow switch is to monitor and display flow information while connected to the IO-Link communication protocol.

1 Safety Instructions

These safety instructions are intended to prevent hazardous situations and/or equipment damage. These instructions indicate the level of potential hazard with the labels of "Caution," "Warning" or "Danger." They are all important notes for safety and must be followed in addition to International Standards (ISO/IEC)⁽¹⁾, and other safety regulations.

⁽¹⁾ ISO 4414: Pneumatic fluid power - General rules relating to systems. ISO 4413: Hydraulic fluid power - General rules relating to systems. IEC 60204-1: Safety of machinery - Electrical equipment of machines. (Part 1: General requirements)

ISO 10218-1: Manipulating industrial robots -Safety. etc.

- Refer to product catalogue, Operation Manual and Handling Precautions for SMC Products for additional information.
- Keep this manual in a safe place for future reference.

A Caution	Caution indicates a hazard with a low level of risk which, if not avoided, could result in minor or moderate injury.
A Warning	Warning indicates a hazard with a medium level of risk which, if not avoided, could result in death or serious injury.
🛕 Danger	Danger indicates a hazard with a high level of risk which, if not avoided, will result in death or serious injury.

Warning

- Always ensure compliance with relevant safety laws and standards.
- All work must be carried out in a safe manner by a qualified person in compliance with applicable national regulations.
- This product is class A equipment intended for use in an industrial environment. There may be potential difficulties in ensuring electromagnetic compatibility in other environments due to conducted or radiated disturbances.
- Refer to the operation manual on the SMC website (URL: <u>https://www.smcworld.com</u>) for more safety instructions.

2 Specifications

Models		PF3A701H	PF3A702H			
Applicable fluid				Air, N ₂		
Op	Operating fluid temperature			0 to 50 °C		
	Detection method Rated flow range		Heating senso	r (branch flow)		
			inge	10 to 1000 L/min	20 to 2000 L/min	
	Set	Ins flov	tantaneous v	10 to 1050 L/min	20 to 2100 L/min	
	range	Acc flow	cumulated v	0 to 999,999,999,990 L		
Flow	Min.	Ins flov	tantaneous v	1 L/min	2 L/min	
	on	Acc flov	cumulated v	10 L		
	Accumulated volume per pulse (pulse width = 50 ms)		volume = 50 ms)	Select from 10 L/pu	lse and 100 L/pulse	
	Accumula	ated	value hold	2 minutes c	or 5 minutes	
	Rated pro	อรรเ	ire range	0 to 1.	0 MPa	
ure	Proof pre	essu	re	1.5	MPa	
ress	Pressure	loss	6	Refer to the pres	ssure loss graph	
đ	Pressure Characte	risti	cs	±5.0 %F.S. (0 to 7 stand	1.0 MPa, 0.5 MPa dard)	
rical	Power su	ipply	/ voltage	24 VDC ±10% as s 21.6 to 30 VDC a	witch output device as IO-Link device	
lect	Current of	ons	umption	150 mA	or less	
ш	Protectio	n		Polarity p	protection	
	Display a	iccu	racy	±3.0 %F.S.		
Y.	Analogue output accuracy		tput	±3.0 %F.S.		
urac	Repeatability			±1.0 9	%F.S.	
Acc	Tempera character	ture ristic	S	±5.0 %F.S. (Ambie 25 °C st	nt temp. 0 to 50 °C, andard)	
	Impact when modular devices are connected		modular connected	±5.0 %		
	Output ty	pe		NPN or PNP ope	n collector output	
	Output m	ode		Select one of output (hysteresis or window comparator mode), output for accumulated flow, accumulated pulse output.		
	Switch or	witch operation Normal or reversed output		versed output		
put	Maximun	n loa	ad current	80	mA	
tch out	Maximun voltage (l	n ap NPN	plied I output)	28 VDC as swite 30 VDC as IC	ch output device D-Link device	
Swi	Internal v (Residua	volta I vol	ge drop tage)	NPN: 1.5 V or less (PNP: 2.0 V or less (load current 80 mA) load current 80 mA)	
	Delay tim	ie		3.3 ms variable at 0 to	or less 60 s / 0.01 step	
	Response time Hysteresis Protection		ne	Select from	1 s, 2 s, 5 s.	
				Vari	able	
			Over currer	nt protection		
tput	Output type			Voltage output: 1 to 5 V (0 to 10 V can be selected), Current output: 4 to 20 mA		
jue Ou	Impedance Voltage output Current output		Voltage output	Output impedan	ce approx. 1 kΩ	
Analog			Current output	Max. load imp Min. load imp	edance 600 Ω bedance 50 Ω	
4	Response time		ne	Linked to response time of switch output (output with digital filter setting)		

2 Specifications (continued)

Models			PF3A701H	PF3A702H	
」 Input type		type	Input with no voltage: 0.4 V or less		
tt. inpu	Input	mode	Select from Reset Accumulated Value, Reset Peak and Reset Bottom values		
ш	Time for input		30 ms or more		
	Refe	ence condition	Normal or Stan	dard condition	
Display	Display		Display method: LCD Number of displays: 2 (main display and sub display) Colour (main display): Red and green Display colour (sub display): Orange Display - main display: 5 digits, 7 segment Display - sub display: 6 digits, 7 segment		
	Oper	ation LED	OUT LED: Red is ON	I when output is ON	
	Protection		IP65		
al	Withstand voltage		1000 V AC for 1 minute between terminals and housing		
nment	Insula	ation resistance	50 MΩ between terminals and housing (with 500 VDC megger)		
Envire	Operative temp	ating erature range	Operation: 0 to 50 °C, Storage: -10 to 60 °C (no condensation or freezing)		
Operating humidity range		ating humidity	Operation, Storage: 35 to 85%RH (no condensation)		
Piping specification		ecification	Modular (body size 30)	Modular (body size 40)	
Material in contact with fluid		n contact with	SUS304, Aluminium alloy, PPS, HNBR (Sensor: Pt, Au, Ni, Fe, lead glass (not RoHS compliant), Al ₂ O ₃)		
Lead wire with connector		with connector	3 r	n	
We	ight	Body	350 g	400 g	
vve	vveight Lead wire		90	a	

2.1 IO-Link specifications

IO-Link type	Device		
IO-Link version	V1.1		
Communication speed	COM2 (38.4 kbps)		
Min. cycle time	3.3 ms		
Process data length	Input Data: 4 bytes, Output Data: 0 byte		
On request data communication	Available		
Data storage function	Available		
Event function	Available		
Vendor ID	131 (0x0083)		
Device ID	PF3A701H-xx-Lx-xxx 0X018A (394) PF3A701H-xx-L3x-xxx 0X018B (395) PF3A701H-xx-L4x-xxx 0X018C (396) PF3A702H-xx-L4x-xxx 0X018D (397) PF3A702H-xx-L3x-xxx 0X018E (398) PF3A702H-xx-L4x-xxx 0X018E (398) PF3A702H-xx-L4x-xxx 0X018E (399)		
IODD file	SMC-PF3A7*H-**-L*-***-yyyymmdd-IODD1.1		

 The IODD configuration file can be downloaded from the SMC website (URL: <u>https://www.smcworld.com</u>).

Warning

• Special products (-X) might have specifications different from those shown in this section. Contact SMC for specific drawings.

3 Names of Individual parts



Element	Description		
Display	See below		
Connector	M12 4-pin connector for electrical connections.		
Lead wire with M12 connector	Lead wire for power supply and outputs.		
Piping port	For piping connections.		
Body	The body of the product.		

3.1 Display



• IO-Link specification



PF##-TF2Z092EN

3 Names of Individual parts (continued)

Element	Description	
Main display	Displays the instantaneous flow value and error codes. (2 colour display)	
Operation LED	Indicates the output status of OUT. When the output is ON: Orange LED is ON. When the accumulated pulse output mode is selected, the output display will turn off.	
Sub display	Displays the accumulated flow, set value, and peak/ bottom value when in measurement mode.	
▲ button (UP)	Selects the mode and the display shown on the Sub display or increases the switch point.	
S button (SET)	Press this button to change the mode and to set a value.	
▼ button (DOWN)	Selects the mode and the display shown on the Sub display or decreases the switch point.	
Units display (Instantaneous flow)	Indicates the flow measurement units currently selected.	
Units display (Accumulated flow)	Indicates the flow measurement units currently selected.	
IO-Link status indicator light	LED is ON when OUT1 is used in IO-Link mode. (LED is OFF in SIO mode)	

4 Installation (continued)

4.4 Piping

Caution

- Before connecting piping make sure to clean up chips, cutting oil, dust etc.
- When installing piping or fittings, ensure sealant material does not enter inside the port.
- Fit the raised part of the spacer to the recessed part (groove for the raised part) of the product.
- Temporarily tighten the retainer A with two hexagon socket head cap screws.
- Tighten the two hexagon socket head cap screws with a hexagonal wrench evenly.
- Refer to the table below for the screws tightening torque.

Applicable model	Hex wrench socket nominal size	Tightening torque
PF3A701H	2	1.2.005 Nam
PF3A702H	3	1.2 ±0.05 N•m





 The following options are required for coupling with modular F, R, and L combinations. They are separately prepared by the user.

Digital flow switch	Air combination	Spacer	Spacer with bracket	Pipe adapter
PF3A701H	AC30#-D	Y300-D	Y300T-D	E300-#03-D
PF3A702H	AC40#-D	Y400-D	Y400T-D	E400-#04-D

 Refer to the SMC website (URL: <u>https://www.smcworld.com</u>) for more details of options.

4 Installation

4.1 Installation

A Warning

- Do not install the product unless the safety instructions have been read and understood.
- Use the product within the specified operating pressure and temperature range.

4.2 Environment

Warning

- Do not use in an environment where corrosive gases, chemicals, salt water or steam are present.
- Do not use in an explosive atmosphere.
- Do not expose to direct sunlight. Use a suitable protective cover.
 Do not install in a location subject to vibration or impact in excess of
- the product's specifications.
- Do not mount in a location exposed to radiant heat that would result in temperatures in excess of the product's specifications.

4.3 Mounting

- Never mount the product in a location where it will be used as a mechanical support.
- Mount the product so that the fluid flows in the direction indicated by the arrow on the side of the body.
- Avoid mounting the product with the display facing upward.
- Do not mount the product upside down.
- The monitor with integrated display can be rotated. Rotating the display with excessive force will damage the end stop.



▲ Caution

 Do not apply torsion or bending moment other than the weight of the product itself. External piping needs to be supported separately as it may cause damage. If a moment applied to the equipment is unavoidable during operation, the moment should be lower than the maximum moment shown below. Non-flexible piping like steel tube is susceptible to excessive moment load or vibration. Insert flexible tubes to prevent this.



Models	PF3A701H	PF3A702H
Maximum moment (M): N•m	16	19.5

Max. moment (M) = Length (L) x Load (F)

4 Installation (continued)

4.5 Wiring

A Caution

- Do not perform wiring while the power supply is ON.
- Confirm proper insulation of wiring.
- Do not route wires and cables together with power or high voltage cables.

The product can malfunction due to interference of noise and surge voltage from power and high voltage cables. Route the wires of the product separately from power or high voltage cables.

 If a commercially available switching power supply is used, be sure to ground the frame ground (FG) terminal. If the product is connected to the commercially available switching power supply, switching noise will be superimposed and the product specifications will not be satisfied. In that case, insert a noise filter such as a line noise filter/ ferrite between the switching power supplies or change the switching power supply to the series power supply.

		7	
1	(0)	$\overline{0}$	2
4	\bigcirc] 0/	3

Pin numbers of connector

When used as switch output device

No.	Name	Wire colour	Function
1	DC(+)	Brown	24 VDC
2	FUNC	White	Analogue output or External input
3	DC(-)	Blue	0 V
4	OUT	Black	Switch output

When used as IO-Link device

No.	Name	Wire colour	Function	
1	DC(+)	Brown	21.6 to 30 VDC	
2	N.C/Other	White	Not connected / Analogue output or External input	
3	DC(-)	Blue	0 V	
4	C/Q	Black	IO-Link data / Switch output (SIO)	

5 Function Setting

5.1 Function selection mode

In measurement mode, press the SET button for 3 seconds or longer to display [F 0].

Press the UP or DOWN button to select the function to be changed. Press and hold the SET button for 2 seconds or longer in function selection mode to return to measurement mode.



Refer to the SMC website (URL: <u>https://www.smcworld.com</u>) for more setting details.

PF##-TF2Z092EN

5 Function Setting (continued)

5.1 Default settings

Function (Main display)		Default Cattings
(Main display)	(Left sub display)	(Right sub display)
	[rEF] Select display units	[Std] Standard condition
[F 0]	[Uni] ([Unit]) Units selection function	[L] L/min
	([NorP]) Select NPN/PNP	([PnP]) PNP output
[F 1]	[oUt] ([oUt1]) Select output mode	[HYS] Hysteresis mode
	[ot] ([1ot]) Select switch mode	[P] ([1_P]) Normal output
	[P] ([P_1]) Select input switch	[500] 500 L/min (PF3A701H)
	operation	[1000] 1000 L/min (PF3A702H)
	[H] ([H_1]) Setting of Hysteresis	[50] 50 L/min (PF3A701H)
		[100] 100 L/min (PF3A702H)
	([dt1]) Delay time setting	([0.00]) 0.00 s
	[CoL] Select display colour	[SoG] ([1SoG]) Green when
		ŐN
		Red when OFF (OUT1)
([F 2])	[oUt2] Select output mode	[HYS] Hysteresis mode
	[2ot] Select switch mode	[2_P] Normal output
	[P_2] Select input switch	[500] 500 L/min (PF3A701H)
	operation	[1000] 1000 L/min (PF3A702H)
	[H_2] Setting of Hysteresis	[50] 50 L/min (PF3A701H)
		[100] 100 L/min (PF3A702H)
	[dt2] Delay time setting	[0.00] 0.00 s
	[CoL] Select display colour	[1SoG] Green when ON Red when OFF (OUT1)
[F 3]	[FiL] Select digital filter	[1.0] 1 second
[F 5]	[FnC] ([FUnC]) Select FUNC (switching analogue output/external input)	[oUt] ([AoUt]) Analogue output
[F10]	[SUb] Select sub display (Line name setting)	[dEF] Default setting
[F13]	[rEv] Select Reverse display	[oFF] Reverse display OFF
[F14]	[CUt] Select Zero cut-off setting	[1.0] 1%F.S. cut
[F30]	[SAv] ([SAvE]) Accumulated value hold	[oFF] Not stored
[F80]	[dSP] ([diSP]) Display OFF mode	[on] Display ON
[F81]	[Pin]Security code	[oFF] Not used
[F90]	[ALL] Setting of all functions	[oFF] Not used
[F96]	[Sin] ([S_in]) Check of input signal	[] No input signal
[F98]	[tES] ([tESt]) Setting of output check	[n] Normal output
[F99]	[ini] Reset to the default settings	[oFF] Not used

*: Items in brackets are IO-Link specifications.

6 Other Settings

- Flow switch setting and functions
- IO-Link functions
- Zero cut off function

Refer to the operation manual on the SMC website (URL: <u>https://www.smcworld.com</u>) for setting these functions.

7 How to Order

Refer to the SMC website (URL: <u>https://www.smcworld.com</u>) for more How to Order details.

8 Outline Dimensions (mm)

Refer to the SMC website (URL: <u>https://www.smcworld.com</u>) for details of Outline dimensions..

9 Maintenance

9.1 General Maintenance

Caution

- Not following proper maintenance procedures could cause the product to malfunction and lead to equipment damage.
- If handled improperly, compressed air can be dangerous.
- Maintenance of pneumatic systems should be performed only by qualified personnel.
- Before performing maintenance, turn off the power supply and be sure to cut off the supply pressure. Confirm that the air is released to atmosphere.
- After installation and maintenance, apply operating pressure and power to the equipment and perform appropriate functional and leakage tests to make sure the equipment is installed correctly.
- If any electrical connections are disturbed during maintenance, ensure they are reconnected correctly and safety checks are carried out as required to ensure continued compliance with applicable national regulations.
- Do not make any modification to the product.
- Do not disassemble the product, unless required by installation or maintenance instructions.
- Remove condensate periodically.

If condensate enters the secondary side, it can cause operating failure of pneumatic equipment.

- Do not use solvents such as benzene, thinner etc. to clean the product. This may damage the surface of the body or erase the markings on the body.
- Use a soft cloth to remove stains.

For heavy stains, use a damp cloth that has been soaked with diluted neutral detergent and fully squeezed, then wipe up the stains again with a dry cloth.

• How to reset the product after a power cut or when the power has been unexpectedly removed

The settings of the product are retained from before the power cut or de-energizing.

The output condition also recovers to that before the power cut or deenergizing, but may change depending on the operating environment. Therefore, check the safety of the whole system before operating the product.

10 Limitations of Use

10.1 Limited warranty and Disclaimer/Compliance Requirements Refer to Handling Precautions for SMC Products.

11 Product disposal

This product should not be disposed of as municipal waste. Check your local regulations and guidelines to dispose of this product correctly, in order to reduce the impact on human health and the environment.

12 Contacts

Refer to <u>www.smcworld.com</u> or <u>www.smc.eu</u> for your local distributor / importer.

SMC Corporation

URL: https://www.smcworld.com (Global) https://www.smc.eu (Europe) SMC Corporation, 4-14-1, Sotokanda, Chiyoda-ku, Tokyo 101-0021, Japan Specifications are subject to change without prior notice from the manufacturer. © 2021 SMC Corporation All Rights Reserved. Template DKP50047-F-085M