

ORIGINAL INSTRUCTIONS

Instruction Manual

Vacuum Module





The intended use of the vacuum unit is to generate vacuum and control the operation of suction and release.

Ejector Unit Specifications

Unit No.		ZX1-W05 ¹ _{2(T)}		ZX1-W07 ¹ _{2(T)}	ZX1-W10 _{2(T)}	
Nozzle dia. (mm)		0.5		0.7	1.0	
Suction flow (L/min(ANR))		5		10	22	
Air consu (L/min(AN	•	13 23		23	46	
Vacuum preached	oressure	-84 kPa				
Max. operating pressure		0.7 MPa				
Supply pressure range		0.2 MPa to 0.55 MPa				
Standard supply pressure		0.45 MPa				
Operating temperature range		5 to 50°C				
Ejector exhaust		Code 1 Built-in silencer For single unit and manifold				
type*		Code 2 Port exhaust····· For single unit and manifold				
	33 g	ZX1-W□1□ (With bracket)		Built-in		
14/a:a:b.4	25 g	ZX1-W□1□-N (ZX1-W□1□-N (Without bracket)			
Weight	37 g	ZX1-W□2□ (With bracket)				
	29 g	ZX1-W□2□-N (Port exhaust			

^{*}Codes 1 and 2 are corresponding to the suffixes in "How to Order" to indicate the eiector exhaust method.

1 Safety Instructions

These safety instructions are intended to prevent hazardous situations and/or equipment damage. These instructions indicate the level of potential hazard with the labels of "Caution," "Warning" or "Danger." They are all important notes for safety and must be followed in addition to International Standards (ISO/IEC) *1), and other safety regulations. 1) ISO 4414: Pneumatic fluid power - General rules relating to systems.

ISO 4413: Hydraulic fluid power - General rules relating to systems. IEC 60204-1: Safety of machinery - Electrical equipment of machines. (Part 1: General requirements)

ISO 10218-1: Manipulating industrial robots -Safety. etc.

- Refer to product catalogue, Operation Manual and Handling Precautions for SMC Products for additional information.
- Keep this manual in a safe place for future reference.

Caution indicates a hazard with a low level of risk which, if not avoided, could result in minor or moderate injury.
Warning indicates a hazard with a medium level of risk which, if not avoided, could result in death or serious injury.
Danger indicates a hazard with a high level of risk which, if not avoided, will result in death or serious injury.

↑ Warning

- Always ensure compliance with relevant safety laws and
- All work must be carried out in a safe manner by a qualified person in compliance with applicable national regulations.

2.2 Valve Unit for Ejector System Specifications

Unit no.	ZX1-VA□□□□□-□ (-Q)							
Component		Supply valve			Release valve			
	Pilot operated			Direct operated				
	Solenoid		Air		Solenoid			Air
	valve		operated		valve			operated
Operation	N.C. V114	N.O. SYJ324M	N.C. ZX1A	N.O. SYJA324	N.C. SYJ314	N.C. V114	External release ZX1A	N.C. SYJA314
Cv factor	0.	17 Ma	in val	/e	0.08	0.008		
Supply pressure range of air pressure SUP (PV) port Supply pressure range of pilot	0.3 to 0.6 MPa							
pressure SUP (PA, PB) ports for supply and release _{Note}	PV port pressure to 0.6 MPa							
Max. operating frequency	5 Hz							
Operating temperature range	5 to 50°C							
Interface plate symbol	PV⇔ PS⇔ PD							

Note) Combination of supply valve and release valve: K4, K5, K6, K7, K8, J3, K4, D4. The supply and release valves of this product have a structure which uses the pressure of the air pressure SUP (PV) port to operate them. Be sure to supply a pressure that is the pressure of the air pressure SUP (PV) port or more, and 0.6MPa or less to the pilot pressure SUP (PA,PB) ports for supply and release.

2 Specifications - continued 2.3 Valve Unit for Pump System Specifications

Jnit no.	ZX1-VB 🗆 🗆 🖂 (-Q)							
Component	Supply valve			Release valve				
	Pilot operated				Direct operated			
	Solenoid		Air		Sole	enoid		Air
	valve		operated		va	lve		operate
Operation					N.C. SYJ314	N.C. V114	External release ZX1A	N.C. SYJA314
Cv factor	0.	.17 Ma	ain val	ve	0.08	0.008	•	3 1
Supply pressure range of vacuum pressure SUP (PV) port								
Supply pressure range of pilot pressure SUP (PS) port	0.3 to 0.6 MPa							
Supply pressure range of pilot pressure SUP (PA, PB) ports for supply and release Note)	PS port pressure to 0.6 MPa							
Max. operating requency	5 Hz							
Operating emperature ange	5 to 50°C							
nterface plate symbol	(PV)•(PS⇔PD)							
Standard accessory	Bracket B (ZX1-OBB)							

Note) The supply and release valves of this product have a structure which uses

the pressure of the pilot pressure SUP (PS) port to operate them. Be sure to supply a pressure that is the pressure of the pilot pressure SUP (PS) port or more, and 0.6 MPa or less to the pilot pressure SUP (PA,PB) ports for supply and release.

2.4 Solenoid Valve Specifications

Model	V114	SYJ314, SYJ324M		
Rated voltage	24, 12, 6, 5, 3 VDC/100,	,		
Electrical entry	L plug connector, grommet	L plug connector, M plug connector, grommet		
Light/surge voltage suppressor	With or Without			
Manual operation Non-locking push type/Locking slotted type				

^{*}Applicable to plug connector only.

2.5 Suction Filter Unit Specifications

Unit no.	-	ZX1-F		
Operating pressure ran	ge	-100 to 500 kPa		
Operating temperature	range	5 to 50°C		
Filtration efficiency		30µm		
Element		PVA		
Weight	37 g	ZX1-F-□ (with bracket A)		
vveignt	29 g	ZX1-F-□-N (without bracket A)		

2 Specifications - continued

2.6	Vacuum Pressure Switch Sp	pecifications		
Mode		ZSE2		
ivioue		For vacuum		
Rate	pressure/ set pressure range	0 to -101 kPa		
Proof	pressure	500 kPa		
Fluid		Air/non-corrosive, non-flammable		
riuia		gas		
		12 to 24 VDC±10%, Ripple (P-P)		
Powe	er supply voltage	10% or less (with power supply		
		polarity protection)		
Curre	ent consumption	17 mA or less at 24 VDC		
Resp	onse time	5 ms or less		
Repe	atability	±1% F.S. or less		
	Enclosure	IP40		
Ф		Operating: 0 to 60°C. Stored: -10 to		
uc	Operating temperature range	60°C (with no condensation and no		
Resistance		freezing)		
ses	Operating humidity range	Operating/stored: 35 to 85%RH (with		
		no condensation)		
Temp	perature characteristics (25°C)			
\^/i+bc	stand voltage	1000 VAC for 1 min. (between		
vviuis	stariu voitage	terminals and housing)		
		50 M Ω or more (500 VDC measu		
Insula	ation resistance	via megohmmeter) between		
		terminals and housing		
		01: R 1/8, M5 x 0.8. T1: NPTF 1/8.		
Port s	size	M5 x 0.8. 0X: with suction filter (for		
Oits	3120	mounting on ZX unit). 0R: based		
		mount type (for mounting on ZR uni		
Weig	ht	35 g (including 0.6m long lead wire)		
		Oil proof heavy-duty vinyl cable 3		
Lead	Grommet type	cores, Ø3.4. Conductor area:		
		0.2mm ² . Insulator O.D: 1.1mm		
wire		Heat resistant vinyl electric wire, 3		
	Connector type	wires. Conductor area: 0.31mm ² .		
l		Insulator O.D: 1.55mm		

2.7 Vacuum Pressure Switch Output Specifications

Model	Nil	55			
Switch output	NPN open collector 30 V, 80 mA or less	PNP open collector 80 mA or less			
Residual voltage	1 V or less (with load current of 80 mA)				
Number of outputs	1				
Hysteresis	3% F.S. or less (fixed)				
Indicator light	ON: when output is ON (red)				
Trimmer adjustment	200°				

3 Installation

3.1 Installation

▲ Warning

- Do not install the product unless the safety instructions have been read and understood.
- When mounting the product, tighten it with the recommended tightening torque (M3: 0.28~0.34 Nm. M5: 1.4~1.6 Nm)).
- When installing the product, secure the space required for maintenance and inspection of the product
- Do not drop, hit, or apply excessive impact to the product.

3.2 Environment

Marning

- Do not use in an environment where corrosive gases, chemicals, salt water or steam are present.
- Do not use in an explosive atmosphere.
- Do not expose to direct sunlight. Use a suitable protective cover.
- Do not install in a location subject to vibration or impact in excess of the product's specifications.
- Do not mount in a location exposed to radiant heat that would result in temperatures in excess of the product's specifications
- The suction filter used in this product is a simple one. If there is a lot of dust in the usage environment, please consider using a suction filter (ZFC series, etc.).
- Do not use in place where static electricity build-up can occur.
- . Do not use in an environment where surges occur.

3.3 Air Supply

↑ Caution

- Do not use air containing chemicals, synthetic oils containing organic solvents, salts, or corrosive gases.
- Recommended quality of the supplied air be equivalent to the compressed air cleanliness grade "2: 6: 3" according to ISO8573-1: 2010.
- Do not supply the pressure in excess of the product's specifications.

3.4 Piping

A Caution

- Before connecting piping make sure to clean up chips, cutting oil, dust, etc.
- When piping a joint to each port, fix the part where the port is attached and use the recommended torque (M3: 0.4 to 0.5 Nm, M5: 1.0 to 1.5 Nm, 1/8: 3 to 5 Nm)


3.5 Wiring to the solenoid valve and pressure switches

Refer to the operation manual of solenoid valve (V100, SYJ300 series) and pressure switch (ZSE2 series). Manuals can be found by the links below:


V100: https://www.smcworld.com/manual/en-jp/?k=V100
SYJ300: https://www.smcworld.com/manual/en-jp/?k=ZSE2
https://www.smcworld.com/manual/en-jp/?k=ZSE2

4 Settings

4.1 Manual Override (With supply valve and release valve)



4 Settings - continued



Refer to the operation manual of the solenoid valve V100, SYJ300 series for the manual operation method.

4.2 Release flow adjusting needle

When the release valve is turned on, vacuum release air is let out. The release flow adjusting needle allows to control the vacuum break air

flow rate.

For products with locknut, loosen the locknut and use a flat-blade screwdriver to adjust the release flow rate adjustment needle at the back

The breaking flow rate adjustment needle can be turned clockwise to reduce the release flow rate, and counterclockwise to increase the release flow rate.

For products with locknut, after adjusting the release flow rate adjustment needle, tighten the locknut to fix the adjustment position.

5 How to Order

Refer to the catalogue for 'How to Order'.

6 Outline Dimensions (mm)

Refer to the catalogue for outline dimensions.

7 Maintenance

7.1 General Maintenance

↑ Caution

- Not following proper maintenance procedures could cause the product to malfunction and lead to equipment damage.
- If handled improperly, compressed air can be dangerous.
- Maintenance of pneumatic systems should be performed only by qualified personnel.
- Before performing maintenance, turn off the power supply and be sure to cut off the supply pressure. Confirm that the air is released to atmosphere.
- After installation and maintenance, apply operating pressure and power to the equipment and perform appropriate functional and leakage tests to make sure the equipment is installed correctly.
- If any electrical connections are disturbed during maintenance, ensure they are reconnected correctly, and safety checks are carried out as required to ensure continued compliance with applicable national regulations.
- Do not make any modification to the product.
- Do not disassemble the product, unless required by installation or maintenance instructions
- Implement the maintenance and check shown below to use the space saving vacuum unit safely and in an appropriate way for a long period of time.
- Drain the air filter and mist separator regularly
- Replace the sound absorbing material (silencer) built into the ejector regularly
- Refer to the online operation manual for replacement parts.
- Do not use benzene or thinner for cleaning

7.2 Sound absorbing material replacement method

- Single Unit
- Loosen the two assembly screws of the silencer case and remove the silencer case assembly.
- Replace the sound absorbing material in the silencer case.
- Assemble the silencer case assembly with the replaced sound absorbing material, and assemble it with screws (recommended tightening torque: 0.2 to 0.3 Nm)

7 Maintenance - continued

7.3 Filter element replacement method

- Loosen the tension bolt and remove the filter case.
- Replace the filter element built into the filter case.
- Assemble the filter case with tension bolts (recommended tightening torque: 0.12 to 0.18 Nm).

8 Limitations of Use

8.1 Limited warranty and Disclaimer/Compliance RequirementsRefer to Handling Precautions for SMC Products.

A Caution

- Exhaust from vacuum module (ejector system)
- For the silencer exhaust type, make sure that there is no obstruction around the exhaust port.
- In the case of port exhaust type, exhaust resistance may be affected depending on the pipe diameter and length, so make sure that the back pressure is 1 kPa or less.
- Do not block the exhaust port.
- Ejector exhaust noise

When the vacuum ejector generates a vacuum, an intermittent noise (abnormal noise) may be generated from the exhaust section near the standard supply pressure where the vacuum pressure peaks, and the vacuum pressure may not be constant. There is no problem in use as long as the vacuum pressure range is sufficient for adsorption, but if you are concerned about the sound or affect the setting of the pressure switch, slightly change the supply pressure and reduce the range of the intermittent sound. Please avoid it.

· About the release flow rate adjusting needle

- Leakage cannot be reduced to zero when the needle is fully closed.
- The breaking flow rate adjustment needle changes from the fully closed state to the fully open state after two rotations. If it is turned more than that, it may come off, so please do not turn it more than 2 times
- For products with locknut, when tightening the locknut, tighten it by hand to about 15 to 30 degrees, and be careful not to damage it due to overtightening.

· About solenoid valve and pressure switch

For the solenoid valve (V100, SYJ300 series) and pressure switch (ZSE2 series), refer to each instruction manual.

9 Product disposal

This product should not be disposed of as municipal waste. Check your local regulations and guidelines to dispose this product correctly, in order to reduce the impact on human health and the environment.

10 Contacts

Refer to www.smc.eu for your local distributor/importer.

SMC Corporation

URL: https://www.smcworld.com (Global) https://www.smc.eu (Europe) SMC Corporation, 4-14-1, Sotokanda, Chiyoda-ku, Tokyo 101-0021, Japan Specifications are subject to change without prior notice from the manufacturer. © 2021 SMC Corporation All Rights Reserved.

Template DKP50047-F-085M