Magnetically Coupled Rodless Cylinder/Slider Type: Slide Bearing

CY1S-Z Series ^{06, 010, 015} ^{020, 025} ^{032, 040}



Construction

CY1S: Bilateral piping type





CY1SG: Centralized piping type



With bumper bolt

* The numbers correspond with those in the "Construction" of the CY1S-Z series in the Web Catalog.

Seal Kit List

004							
No.	Description	Material	Note	No.	Description	Material	Note
4	Piston seal	NBR		24)	Cylinder tube gasket	NBR	
5	Wear ring A	Special resin		25	Bumper bolt	Chromium molybdenum steel	
6	Lube-retainer A	Special resin		26	Bumper	Urethane rubber	
13	Slider gasket	NBR		33	Hexagon nut	Chromium molybdenum steel	
19	Wear ring B	Special resin		37	Switch spacer	Special resin	
20	Lube-retainer B	Special resin		39	Guide shaft gasket	NBR	

Benlacement Parts: Seal Kit

Bore size	Sea	al kit	Bumper bolt assembly		Switch spacer	
(mm)	Part no.	Contents	Part no.	Contents	Part no.	Contents
6	CY1S6-Z-PS	Set of nos. (4), (5), (3), (9), (2), (3)	CYS06-37-AJ024-R	Set of nos. 25, 26, 33	BMY3-016	No. 37
10	CY1S10-Z-PS	Set of nos. (4), (13, (19, 20, 24, 39	CYS10-37-AJ025-R			
15	CY1S15-Z-PS		01510-37-AJ025-R			
20	CY1S20-Z-PS	Set of nos. ④, ⑤, ⑥, 13, 19	CYS20-37-AJ027-R			
25	CY1S25-Z-PS		CYS25-37-AJ028-R			
32	CY1S32-Z-PS 20, 24, 39					
40	CY1S40-Z-PS		CYS32-37-AJ029-R			

Note 1) The seal kit includes 4, 5, 13, 19, 29, 39 for ø6. 4, 13, 19, 20, 29, 39 for ø10. 4, 5, 6, 13, 19, 20, 29, 39 are for ø15 to ø40. Order the seal kit based on each bore size.

Note 2) The seal kit includes a grease pack (10 g). Order with the following part number when only the grease pack is required. Grease pack part no.: GR-S-010

Note 3) A switch spacer, as specified in the table above will be required if an auto switch is mounted afterward. When ordering an additional auto switch, also order an additional switch spacer. Refer to "Auto Switch Mounting" for details.

