
Ejector System Vacuum Unit 25A-ZK2 A Series RoHS

Single Unit Ejector + With Valve + Without Energy Saving Function



The standard supply pressure of each nozzle diameter is the same as that of the corresponding standard product. For details, refer to the Web Catalog

Supply valve Release valve N.C. Self-holding N.C. •

R •*2 *2 Supply valve maintains vacuum by energization (20 ms or


more). Stopping the vacuum turns on the release valve.

6 Connector (Supply valve/Release valve/Pressure switch for vacuum)

	· · · ·	-		-	
Symbol	For supply valve/ release valve: 300 mm (Connector assembly)*4	For pressure switch for vacuum: 2 m (Lead wire with connector)		Note	
L	•	•		Cannot be selected	
L1	None	•		when ᠪ is N	
L2	•	None		Cannot be selected	
L3	None	None		when 🟮 is P or T	

*4 For the connector length other than 300 mm, select L1 or L3, and order the connector assembly on page 194 separately.

8 Option*5 (For details on the Function/Application, refer to page 195.)



*5 When more than one option is selected, list the option symbols in alphabetical order. (Example -BJ)

*6 Use a One-touch fitting or barb fitting for piping. (O.D.: Within ø6.2)

* The 25A- series specifications and dimensions are the same as those of the standard model.

The manifold type is available as a special order.

A		Silencer exhaust*1	Silencer exhaust
в	Single unit	Port exhaust	Port exhaust
G		High-noise reduction silencer exhaust	High-noise reduction silencer exhaust

*1 With exhaust port when 2 is 12 or 15

4 Rated voltage (Supply valve/Release valve)

Symbol	Voltage
5	24 VDC
6	12 VDC

• Pressure switch for vacuum/Pressure sensor

		_	Specifications		cifications
Symbol	Туре	Pressure range [kPa]	NPN	PNP	With unit selection
			2 ou	tputs	function*3
Α			•	—	•
В	for	0.1- 101	•	—	None (SI unit only)
С	Pressure switch for vacuum	0 to -101			•
D			—	•	None (SI unit only)
Ε			•	—	•
F		-100 to 100	•	—	None (SI unit only)
Н	Pre	-100 10 100		•	•
J			—		None (SI unit only)
Ρ	Pressure	0 to -101	- Analog output 1 to 5 V		Nutput 1 to 5 V
Т	sensor	-100 to 100			
Ν	Without pressure switch for vacuum/pressure sensor				

*3 The unit selection function is not available in Japan due to the New Measurement Law. The unit for the type without the unit selection function is fixed as kPa.


🕖 Vacuum (V) port

Symbol	Vacuum (V) port
06	ø6
08	ø8



Ejector System Vacuum Unit 25A-ZK2 A Series RoHS

Single Unit Ejector + With Valve + With Energy Saving Function



*3 When more than one option is selected, list the option symbols in alphabetical order. (Example -BJ) *4 Use a One-touch fitting or barb fitting for piping. (O.D.: Within ø6.2)

Screwdriver operation

type long lock nut

Round lock nut

Screwdriver

operation type

Ε

J

κ

flow

Vacuum break flov adjusting needle

Screwdriver operation

Lock nu

type long lock nut

Vacuum break

flow adjusting needle

For details, refer to the Web Catalog. 192

* The 25A- series specifications and dimensions are the same as those

The manifold type is available as a special order.

of the standard model.




Can be selected only for the

combination of J

and K


Ejector System Vacuum Unit 25A-ZK2 A Series RoHS

Single Unit Ejector + Without Valve + Without Energy Saving Function



Ν Without pressure switch for vacuum/pressure sensor

*2 The unit selection function is not available in Japan due to the New Measurement Law. The unit for the type without the unit selection function is fixed as kPa.



*3 When more than one option is selected, list the option symbols in alphabetical order. (Example -BW)

The manifold type is available as a special order.

* The 25A- series specifications and dimensions are the same as those of the standard model.



Symbol

06

08


Filter case

color

Smoke

Clear

Open collector 2 outputs



One check valve type

(All specifications other than vacuum switch with energy saving function and exhaust interference prevention valve)

Two check valve type

(Vacuum switch with energy saving function and exhaust interference prevention valve)

*1 When ZK2-BG5-2-A is mounted, the workpiece cannot be removed until

1

2

vacuum is released.

•Applicable nozzle size 4 For nozzle size 07, 10 6 For nozzle size 12, 15

Sound absorbing material for high-noise reduction silencer (5 pcs. per set)

ZK2 - SE4 - 6 - A

Release lever (10 pcs. per set)

ZK2 – RL1 – A


Lock nut (10 pcs. per set)

25A-ZK2 – LN1 – A


SMC

25A-ZK2 A Series

Optional Specifications/Functions/Applications







Symbol	Applicable tubing O.D.	Specification
Nil	Without port	Manifold
0	Without fitting (M5 x 0.8)	Single unit

Doption

	Bracket for single unit	
Single unit Manifold		Manifold
Nil	With	Without
Ν	Without	Not available

* The 25A- series specifications and dimensions are the same as those of the standard model.

For details, refer to the Web Catalog.



3111	For Manifold

6 Manual override

		Non-locking push type	
Nil Latching:		Latching:	
		Push-locking slotted type	
	B *2	Locking slotted type	

*2 When "Q1" is selected in
, the locking slotted type is only available in the release valve. This option cannot be chosen when "Q2" is

selected in **3**.

7 Vacuum pressure switch (With suction filter*3)

	• • • • • • • • • • • • • • • • • • •				
Symbol	Pressure range [kPa]	Output			
EA	0 to -100	NPN 2 outputs			
EB		PNP 2 outputs			
EC		NPN 1 output + Analog voltage			
EE		PNP 1 output + Analog voltage			
FA	-100 to 100	NPN 2 outputs			
FB		PNP 2 outputs			
FC		NPN 1 output + Analog voltage			
FE		PNP 1 output + Analog voltage			
F *4	Suction filter only				

*3 The filter used in this product is of a simple type, and will become clogged quickly in environments with high quantities of dust or particulates. Please consider using in combination with an air suction filter of the ZFC series, etc.

*4 It is not necessary to select the items for (3) and (9).

Nil	None	
K *7	With check valve	

*6 The check valve has a function to prevent the exhaust air from the exhaust unit overflowing to the vacuum port side when a manifold is used, but it cannot prevent overflow of the exhaust air completely. During usage, please inspect thoroughly with actual machine.

Also, in order to completely prevent the overflow of exhaust air, leave plenty of space between the check valve unit and adjacent ejector to avoid interference from the ejector's exhaust unit.

*7 Cannot be selected when ② is "1U" In addition, for the type with a check valve, the air in the adsorption part is not released to the atmosphere when vacuum is stopped. If "J1," "J2," or "Q2" is selected for ③, be sure to also install a circuit for vacuum release.

Warning

- · Cannot be used for vacuum retention
- Use a release valve. Without a release valve, a workpiece may not be released.

D Fitting (V port)

SymbolApplicable tubing O.D.**0**Without fitting (M5 x 0.8)

Fitting (P port)

8 Unit Nil*5

Μ

P*5

9 Lead wire

Nil

G

For Manifold (9: 3M)

With unit switching function

SI unit only (kPa) With unit switching function

(Initial value: psi)

Without lead wire with

connector

Lead wire with connector

(Length: 2 m) (Included)

*5 Under the New Measurement Act,

(implemented October 1999).

switches with the unit switching function are not permitted for use in Japan

	• • • • • • • • • • • • •		
Symbol	Applicable tubing O.D.	Specification	
Nil	Without port	Manifold	
0	Without fitting (M5 x 0.8)	Single unit	

Option Ear Single Unit (

For Single Unit (2: 1U)

			FUI IVIAI		
Symbol	Bracket assembly	Converter assembly for solenoid valve*8	Symbol		Converter assembly for solenoid valve*8
Nil	0	—	Nil	—	—
N	—	—	S	0	—
С	—	0	С	—	0
D	0	0	E	0	0


- *8 A converter assembly for attaching the VQ100 lead wire assembly with a connector to the ZQ-A is included. Refer to the "Converter assembly for solenoid valve" in the Web Catalog. "Q2" cannot be selected in ③. Select "LO" in ⑤.
- *9 Select "C" for (1) for the manifold part number on page 180-3. "J1", "J2", or "Q2" cannot be selected in (3). For a release pressure supply pressure of 0.3 MPa or lower, select "S" or "E."
- * The 25A- series specifications and dimensions are the same as those of the standard model.

For details, refer to the Web Catalog.



Ejector System Compact Vacuum Unit 25A-ZQ A Series Rolls Manifold Part Number





Series compatible with secondary batteries

Stations^{*1}

01	1 station	
02	2 stations	
:	:	
08	8 stations	

*1 Number of stations varies according to nominal nozzle size during simultaneous operation. (Table 1)

Table 1. Max. Number of Stations that Can Operate Simultaneously*2

Nominal nozzle size	Max. number of stations that can operate simultaneously
0.5	8 stations
0.7	6 stations
1.0	4 stations

*2 For any of the nominal nozzle sizes, the max. number of stations that can be mounted is 8. However, please ensure that the max. number of stations that are operated simultaneously comply with the values above.

2 A	Air pressure supply (P) port location
B	Both sides

Provide the second state of the second stat

в	None (Release pressure: Commonly supplied from the P port)	
C *3	Provided (Release pressure: Supplied from the PD port)	

*3 For a release pressure supply pressure of 0.3 MPa or lower (for an individual unit without the energy-saving function), select "S" or "E" for (B) for the single unit part number on page 198.

B Exhaust

-	
S	Silencer exhaust (Both sides)
Ρ	Port exhaust (Both sides)

5 Shipping configuration

Nil	Assembled as a vacuum unit	
A*4 Manifold unit only		
.4 4 9 9	t of and blocks and the alarma ra	

A set of end blocks and the clamp rod assembly is included in this manifold unit. (Used for the maintenance of the end block)

* The 25A- series specifications and dimensions are the same as those of the standard model.

For details, refer to the Web Catalog.

Manifold Order Example

∕⁄∂SMC

25A-ZZQ104A-BSB------ 1 pc.

* 25A-ZQ053MA-K15L-EAG-0 \cdots 2 pcs. \rightarrow Stations 1 and 2

* 25A-ZQ103MA-K15L-F-0 \cdots 2 pcs. \rightarrow Stations 3 and 4 When the manifold is viewed from the vacuum (V) port, the first station starts from the left.

25A-ZQ053MA-K15L-EAG-0 (2 pcs.) and 25A-ZQ103MA-K15L-F-0 (2 pcs.) are arranged from the first station.

Vacuum (V) port .7 Stations If "*" is not entered, the manifold and single unit will be shipped without being assembled.

- When the manifold and the units are not assembled, please assemble them by referring to
- "How to increase/decrease manifold stations" in the Web Catalog. There is nothing else to arrange additionally.


The asterisk (*) denotes the symbol for the assembly.

🗥 Caution when ordering manifold

Prefix it to the single unit part number.

I. I.

Vacuum Pump System Compact Vacuum Unit 25A-ZQ A Series RoHS Single Unit Part Number



state. Devise the circuit for the vacuum release additionally.

*2 Latching (+ common)

L	L plug connector (Lead wire length: 0.3 m) With light/surge voltage suppressor
LO	L plug connector (Without connector) With light/surge voltage suppressor

5 Manual override

Nil	Non-locking push type
INII	Latching: Push-locking slotted type
B *3	Locking slotted type

*3 When "Q1" is selected in 2, the locking slotted type is only available in the release valve. This option cannot be chosen when "Q2" is selected

in 🛛

6 Vacuum pressure switch (With suction filter^{*4})

Symbol	Pressure range [kPa]	Output
EA	0 to -100	NPN 2 outputs
EB		PNP 2 outputs
EC		NPN 1 output + Analog voltage
EE		PNP 1 output + Analog voltage
FA	100 1- 100	NPN 2 outputs
FB		PNP 2 outputs
FC	–100 to 100	NPN 1 output + Analog voltage
FE		PNP 1 output + Analog voltage
F * ⁵	Suction filter only	

- *4 The filter used in this product is of a simple type, and will become clogged quickly in environments with high quantities of dust or particulates. Please consider using in combination with an air suction filter of the ZFC series, etc.
- ∗5 It is not necessary to select the items for ⑦ and ⑧

🖸 Unit


Nil*6	With unit switching function	
М	SI unit only (kPa)	
P *6	With unit switching function (Initial value: psi)	

*6 Under the New Measurement Act, switches with the unit switching function are not permitted for use in Japan (implemented October 1999).

Fitting (PS/PV port)

Symbol	Applicable tubing O.D.	Specification
Nil	Without port	Manifold
0	Without fitting (M5 x 0.8)	Single unit

8 Lead wire



9 Fitting (V port)

Symbol	Applicable tubing O.D.	
0	Without fitting (M5 x 0.8)	

D Option

For Sing	gle Unit (0: U)		For Manifold (① : M)			
Symbol	Bracket assembly	Converter assembly for solenoid valve*7	y Symbol Low release pressure specification*8 Conv for s		Converter assembly for solenoid valve*7	
Nil	0	—	Nil	_	_	
Ν	—	—	S	0	—	
С	—	0	С	—	0	
D	0	0	E	0	0	

A converter assembly for attaching the VQ100 lead wire assembly with a connector to the ZQ-A is included. Refer to the "Converter Assembly for Solenoid Valve" in the **Web Catalog**. *7 Q2" cannot be selected in 2. Select "LO" in 4.

*8 Select "C" for (3) for the manifold part number on page 201. "J1", "J2", or "Q2" cannot be selected in 2. For a release pressure supply pressure of 0.3 MPa or lower, select "S" or "E."

The 25A- series specifications and dimensions are the same as those of the standard model.

For details, refer to the Web Catalog.






Table 1. Location of Each Port

	3 PD port	Left side with the V port facing the front			Right side with the V port facing the front		
PV port location	BPD port	PS port	PV port	PD port	PS port	PV port	PD port
	В	—	•	—	•	—	—
L	С	—	•	•	•	_	•
в	В	•	_	_	_	•	—
п	С	•	—	•	—	•	•

* The 25A- series specifications and dimensions are the same as those of the standard model.

3 4

Stations

For details, refer to the Web Catalog.

Manifold Order Example

25A-ZZQ104A-ROB 1 pc.

* 25A-ZQ000MA-K15L-EAG-0… 2 pcs. \rightarrow Stations 1 and 2 * 25A-ZQ000MA-K15L-F-0 …… 2 pcs. \rightarrow Stations 3 and 4

* When the manifold is viewed from the vacuum (V) port, the first station starts from the left.

25A-ZQ000MA-K15L-EAG-0 (2 pcs.) and 25A-ZQ000MA-K15L-F-0 (2 pcs.) are arranged from the first station.

Vacuum (V) port


∕⁄∂SMC

▲ Caution when ordering manifold

- The asterisk (*) denotes the symbol for the assembly.
- Prefix it to the single unit part number.
- I If "*" is not entered, the manifold and single unit will be shipped without being assembled.
- When the manifold and the units are not assembled, please assemble them by referring to
- I "How to increase/decrease manifold stations" in the Web Catalog.
- There is nothing else to arrange additionally.

Compact Vacuum Unit **25A-ZQ** A Series

Construction




nen replacing the late assembly.)
order.
order.
order.
order.
order.
order.



25A-ZQ A Series

How to Order Replacement Parts for Single Unit



Connector and Socket for Solenoid Valve

 For N.C.N.O. Pilot Valves,
 SY100-30-A
 * With connector and sockets only

 Pilot Valves
 (Number of sockets: 2)
 * With connector and sockets only

 For Latching
 AXT661-12A
 * Unumber of sockets: 3)

2 Vacuum Pressure Switch (With Suction Filter) (Recommended torque for replacement: 0.11 to 0.13 N·m)



Vacuum pressure switch

U 140	adin precedure eviteri				
Symbol	Pressure range [kPa]	Output			
EA		NPN 2 outputs			
EB	0 to -100	PNP 2 outputs			
EC	010-100	NPN 1 output + Analog voltage			
EE		PNP 1 output + Analog voltage			
FA		NPN 2 outputs			
FB		PNP 2 outputs			
FC	-100 to 100	NPN 1 output + Analog voltage			
FE	-10010100	PNP 1 output + Analog voltage			
VA *1		NPN 1 output + Energy saving control			
VB *1		PNP 1 output + Energy saving control			

*1 It is not possible to replace the vacuum pressure switch from the specification without energy saving function to the specification with energy saving function.

2 Unit

Nil*2 With unit switching function						
M SI unit only (kPa)						
P *2, *3	With unit switching function (Initial value: psi)					

*2 Under the New Measurement Act, switches with the unit switching function are not permitted for use in Japan (implemented October 1999).
*3 Cannot be selected when ① is "VA" or "VB"

3 Lead wire

Nil	Without lead wire with connector
G	Lead wire with connector (Length: 2 m) (Included)
W	Lead wire for switch with energy saving function (Length: 2 m) (Included)

4 Check valve*4

Nil	None
K *5	With check valve

*4 The check valve has a function to prevent the exhaust air from the exhaust unit overflowing to the vacuum port side when a manifold is used, but it cannot prevent overflow of the exhaust air completely. During usage, please inspect thoroughly with actual machine. Also, in order to completely prevent the overflow of exhaust air, leave

Also, in order to completely prevent the overnow of exhaust air, leave plenty of space between the check valve unit and adjacent ejector to avoid interference from the ejector's exhaust unit.

*5 When "VA" or "VB" is specified for $lackbda{0}$, the check valve is already built in.

\land Warning

1. Cannot be used for vacuum retention

2. Use a release valve. Without a release valve, a workpiece may not be released.

5 Fitting (V port)

Symbol	Applicable tubing O.D.
0	Without fitting (M5 x 0.8)

Lead Wire with Connector Assembly for Vacuum Pressure Switch

(When an individual lead wire is necessary, order with the part numbers below.)


\cdot Lead wire with connector for vacuum pressure switch

ZS – 39 – 5G

SMC


 \cdot Lead wire with connector for pressure switch with energy saving function





How to Order Replacement Parts for Single Unit

Compact Vacuum Unit/25A-ZQ A Series



How to increase/decrease manifold stations

Disassembly

- 1. Remove 2 clamp rods ①.
- 2. Remove end block L ②. (Be careful not to drop the gasket.)

Assembly


- Confirm that the body gasket for manifold (6) is attached to the gasket groove on each single unit and that the exhaust block gasket (7) is also attached to the outer side of the raised part. (See View b.)
- 2. Confirm that the body gasket for manifold (6) is attached to the gasket groove on end block R (3).
- 3. Confirm that the exhaust block gasket $(\overline{2})$ is attached to the outer side of the raised part on end block L $(\overline{2})$.

4. Put together the single units for manifold, end block R ③, and end block L ② using the positioning pins (at two "a" locations), and assemble them using the clamp rods ①. Tightening torque: 0.54 to 0.66 N·m

Component Parts

No.	Description	Material	Note	
1	Clamp rod assembly	Steel (Electroless nickel plating)	Refer to 1 below for how to order.	
2	End block L	PBT, POM, PET, Steel, Aluminum alloy, Stainless steel	Left side with the vacuum (V) port facing the front	
3	End block R	PBT, POM, PET, Steel, Aluminum alloy, Stainless steel	Right side with the vacuum (V) port facing the front	
4	Sound absorbing material (For Manifold)	Non-woven fabric (PET)	Refer to 2 below for how to order.	
5	Silencer block assembly	PBT	Refer to 3 below for how to order.	
6	Body gasket for manifold	NBR	Refer to 4 below for how to order.	
7	Exhaust block gasket	NBR	Refer to 5 below for how to order.	
8	Washer assembly	Stainless steel	Refer to 6 below for how to order.	
9	Port block assembly	Aluminum alloy, Steel (Electroless nickel plating), NBR	Refer to 7 below for how to order.	

How to Order Replacement Parts for Manifold



This product **(only the One-touch fitting port type)** is a secondary battery compatible product. For details, refer to the **Web Catalog**.

Vacuum Ejector Body Ported Type/Box Type (Built-in Silencer)


ZH Series


RoHS

Compact and lightweight

Body ported type

Port size: G threads have been added.






This product (only the One-touch fitting port type) is a secondary battery compatible product. For details, refer to the Web Catalog.

In-line Type Vacuum Ejector

ZU A Series


(RoHS)

Compact and Lightweight




Application Examples

For preventing pad adsorption failures from the vacuum source



Numerous pads can be used to adsorb workpieces with holes.







For mounting on the end of a Z-axis air cylinder

Variations

· an an o								
Model	Nozzle size Standard supply		Ultimate vacuum pressure [kPa]		Maximum suction flow rate [L/min (ANR)]		Air consumption	Port size
MOdel	[mm]	pressure [MPa]	Type S	Type L	Type S	Type L	[L/min (ANR)]	FUITSIZE
ZU03⊟A	0.3	0.35	-85	-40	1.8	3.4	4.2	ø4 One-touch fitting
ZU04⊟A	0.4	0.35	-87	-40	3.2	5.8	7.7	ø5/32"
ZU05⊟A	0.5	0.45	00	40	7	13	14	ø6 One-touch fitting
ZU07⊟A	0.7	0.45	-90	-48	11	16	28	Rc1/8
007								









Vertical

2 Vacuum inlet direction

Pad diameter

-			
02	ø2	16	ø16
04	ø4	20	ø20
06	ø6	25	ø25
08	ø8	32	ø32
10	ø10	40	ø40
13	ø13	50	ø50

With adapter

5 Vacu	uum inl	et					
Turne	Sumbol	Size	Pad diameter [mm]				
Туре	Symbol	Size	ø2 to ø8	ø10 to ø16	ø20 to ø32	ø40, ø50	
	A5	M5 x 0.8	O*1	—	—	—	
	AS5	NID X U.O	—	○*1	○*1	—	
Male	A6	M6 x 1	O*1	—	—	—	
thread	AS6		—	○*1	○*1	⊖*1	
	AG01	G1/8	—	O*1	O*1	—	
	AG02	G1/4	—	—	—	⊖*1	
	Nil	M3 x 0.5	_	○ (⑥ Connection thread: A5/A6)	○ (⑥ Connection thread: A6)	○ (⑤ Connection thread: A6)	
		M5 x 0.8	_	_	○ (⑥ Connection thread: A8)	○ (6 Connection thread: A8)	
F	B4	M4 x 0.7	O*1	_	—	—	
Female thread	B5	M5 x 0.8	O*1	O*1	O*1	—	
uneau	B6	M6 x 1	_	○*1	○*1	⊖*1	
	B8	M8 x 1.25	_	—	O*1	⊖*1	
	B01	Rc1/8	_	○*1	○*1	⊖*1	
	BG01	G1/8	_	O*1	O*1	_	
	BG02	G1/4	—	—	—	O*1	

*1 Use the connection thread.

6 Connection thread

Tuno	Sumbol	Size	Pad diameter [mm]			
Туре	Symbol	Size	ø2 to ø8	ø10 to ø16	ø20 to ø32	ø40, ø50
Mala	A5	M5 x 0.8	—	O*2	—	_
Male thread	A6	M6 x 1	—	O*2	O*2	O*2
lineau	A8	M8 x 1	_	—	⊖*2	○*2

4 Material


Ν	NBR	
S	S Silicone rubber*1 *2	
U	Urethane rubber	
F FKM		
GN Conductive NBR		
GS Conductive silicone rubber		


- *1 Compliant with the FDA (USA Food and Drug Administration) regulation 21CFR§177.2600 for "Rubber articles intended for repeated use"
- *2 Compliant with the standards for "Rubber apparatus (excluding baby drinking apparatus) and containers/packaging" (D3) (Partial revision: Ministry of Health, Labour, and Welfare Notification No. 595, 2012) in Section 3 "Apparatus and Containers/ Packaging" of the Food Sanitation Act, Article 18 "Specifications and Standards for Food and Food Additives, etc." (Ministry of Health and Welfare Notification No. 370, 1959)

Lock ring unit

	<u> </u>
Part no.	Pad diameter [mm]
ZPSL1	ø10 to ø16
ZPSL2	ø20 to ø32
ZPSL3	ø40, ø50







2 Vacuum inlet direction

B Pad diameter

D Pac	Pad diameter		
10	ø10		
13	ø13		
16	ø16		
20	ø20		
25	ø25		
32	ø32		
40	ø40		
50	ø50		

4 Material

Wateria		
Ν	NBR	
S	Silicone rubber*1 *2	
U	Urethane rubber	
F	FKM	
GN	Conductive NBR	
GS	Conductive silicone rubber	

- *1 Compliant with the FDA (USA Food and Drug Administration) regulation 21CFR§177.2600 for "Rubber articles intended for repeated use"
- *2 Compliant with the standards for "Rubber apparatus (excluding baby drinking apparatus) and containers/packaging" (D3) (Partial revision: Ministry of Health, Labour, and Welfare Notification No. 595, 2012) in Section 3 "Apparatus and Containers/ Packaging" of the Food Sanitation Act, Article 18 "Specifications and Standards for Food and Food Additives, etc." (Ministry of Health and Welfare Notification No. 370, 1959)

Lock ring unit

	guine		
Part no.	Pad diameter [mm]		
ZPSL1	ø10 to ø16		
ZPSL2	ø20 to ø32		
ZPSL3	ø40, ø50		

Vertical


5 Vacu	um inl	et				
Tuno	Cumple al	Cine	Pad diameter [mm]			
Туре	Symbol	Size	ø10 to ø16	ø20 to ø32	ø40, ø50	
	AS5	M5 x 0.8	O*2	O*2	—	
Male	AS6	M6 x 1	⊖*2	⊖*2	O*2	
thread	AG01	G1/8	O*2	O*2	—	
	AG02	G1/4	—	—	O*2	
	Nil	M3 x 0.5	○ (⑥ Connection thread: A5/A6)	○ (⑥ Connection thread: A6)	○ (6 Connection thread: A6)	
		M5 x 0.8	_	○ (⑥ Connection thread: A8)	○ (⑥ Connection thread: A8)	
Female	B5	M5 x 0.8	O*2	O*2	—	
thread	B6	M6 x 1	O*2	O*2	O*2	
	B8	M8 x 1.25	—	O*2	O*2	
	B01	Rc1/8	O*2	O*2	○*2	
	BG01	G1/8	O*2	O*2	—	
	BG02	G1/4	_	_	O*2	
*1 Use th	B01 BG01 BG02	Rc1/8 G1/8	<u> </u>			


*1 Use the connection thread.

6 Connection thread

Туре	Symbol	Symbol Size		Pad diameter [mm]		
Type	Symbol	Size	ø10 to ø16	ø20 to ø32	ø40, ø50	
	A5	M5 x 0.8	O*2	—	—	
Male thread	A6	M6 x 1	O*2	O*2	○*2	
uncau	A8	M8 x 1	—	O*2	⊜*2	

*2 With a (female) vacuum inlet





U Ad	apter (Lock ring) material
S	Stainless steel (Stainless steel 304)

Vertical

2 Vacuum inlet direction

A

B P	3 Pad diameter					
06	ø6	20	ø20			
08	ø8	25	ø25			
10	ø10	32	ø32			
13	ø13	40	ø40			
16	ø16	50	ø50			

With adapter

9 Vacuum inlet						
Tuno	e Symbol Size		Pad diameter [mm]			
Туре	Symbol	Size	ø6, ø8	ø10 to ø16	ø20 to ø32	ø40, ø50
	A5	M5 x 0.8	O*1	—	—	—
	AS5	IVIS X U.8	—	⊖*1	⊖*1	—
Male	A6	M6 x 1	O*1	—	—	—
thread	AS6		_	O*1	O*1	O*1
	AG01	G1/8	—	O*1	O*1	—
	AG02	G1/4	—	_	—	O*1
	Nil	M3 x 0.5	—	○ (⑥ Connection thread: A5/A6)	○ (⑥ Connection thread: A6)	○ (⑥ Connection thread: A6)
		M5 x 0.8	—	_	○ (⑥ Connection thread: A8)	○ (⑥ Connection thread: A8)
E	B4	M4 x 0.7	O*1	—	—	_
Female thread	B5	M5 x 0.8	O*1	O*1	()*1	_
uneau	B6	M6 x 1	—	O*1	O*1	O*1
	B8	M8 x 1.25	—	—	O*1	O*1
	B01	Rc1/8	—	O*1	O*1	O*1
	BG01	G1/8	—	O*1	O*1	_
	BG02	G1/4	—	—	—	O*1

*1 Use the connection thread.

6 Connection thread


Turne	Symbol	Cizo	Pad diameter [mm]			
Type Symbo		Size	ø6, ø8	ø10 to ø16	ø20 to ø32	ø40, ø50
Male thread	A5	M5 x 0.8	—	O*2	—	—
	A6	M6 x 1	—	O*2	O*2	O*2
	A8	M8 x 1		—	O*2	O*2

N	NBR	
S	S Silicone rubber*1 *2	
U	Urethane rubber	
F	FKM	
GN	Conductive NBR	
GS Conductive silicone rubber		


- *1 Compliant with the FDA (USA Food and Drug Administration) regulation 21CFR§177.2600 for "Rubber articles intended for repeated use"
- *2 Compliant with the standards for "Rubber apparatus (excluding baby drinking apparatus) and containers/packaging" (D3) (Partial revision: Ministry of Health, Labour, and Welfare Notification No. 595, 2012) in Section 3 "Apparatus and Containers/ Packaging" of the Food Sanitation Act, Article 18 "Specifications and Standards for Food and Food Additives, etc." (Ministry of Health and Welfare Notification No. 370, 1959)


Lock ring unit

Part no. Pad diameter [mm]	
ZPSL1 Ø10 to Ø16	
ZPSL2	ø20 to ø32
ZPSL3	ø40, ø50



How to Order





Vacuum inlet direction
 T
 Vertical

B Pa	d diameter
10	ø10
13	ø13
16	ø16

4 Material

-				
N	NBR			
S	Silicone rubber *1 *2			
U	Urethane rubber			
F	FKM			
GN	Conductive NBR			
GS	GS Conductive silicone rubber			

*1 Compliant with the FDA (USA Food and Drug Administration) regulation 21CFR§177.2600 for "Rubber articles intended for repeated use"

*2 Compliant with the standards for "Rubber apparatus (excluding baby drinking apparatus) and containers/packaging" (D3) (Partial revision: Ministry of Health, Labour, and Welfare Notification No. 595, 2012) in Section 3 "Apparatus and Containers/Packaging" of the Food Sanitation Act, Article 18 "Specifications and Standards for Food and Food Additives, etc." (Ministry of Health and Welfare Notification No. 370, 1959)

With adapter

6	Vacuum	inlet
---	--------	-------


Tuno	Sumbol	Size	Pad diameter
Туре	Symbol	Size	All sizes
Female	A5	M5 x 0.8	0
thread	A6	M6 x 1	0
One-touch	B4	M4 x 0.7	0
fitting	B5	M5 x 0.8	0




Basic Pad Thin Flat Type with Ribs **ZP Series**

For pad units and pads with an adapter (stainless steel type): The standard product is a secondary battery compatible product. For details on specifications and dimensions, refer to the **Web Catalog**.

How to Order





Vacuum inlet direction
 T Vertical

Pad diameter			
10	ø10		
13	ø13		
16	ø16		

4 Material

•			
Ν	NBR		
S	Silicone rubber*1 *2		
U	Urethane rubber		
F	FKM		
GN	Conductive NBR		
GS Conductive silicone rubber			


*1 Compliant with the FDA (USA Food and Drug Administration) regulation 21CFR§177.2600 for "Rubber articles intended for repeated use"

*2 Compliant with the standards for "Rubber apparatus (excluding baby drinking apparatus) and containers/packaging" (D3) (Partial revision: Ministry of Health, Labour, and Welfare Notification No. 595, 2012) in Section 3 "Apparatus and Containers/Packaging" of the Food Sanitation Act, Article 18 "Specifications and Standards for Food and Food Additives, etc." (Ministry of Health and Welfare Notification No. 370, 1959)


With adapter

5 Vacuum inlet

Turne	Sumbol	Size	Pad diameter
Туре	Symbol	Size	All sizes
Male	A5	M5 x 0.8	0
thread	A6	M6 x 1	0
Female	B4	M4 x 0.7	0
thread	B5	M5 x 0.8	0







Adapter (Lock ring) material		
S	Stainless steel (Stainless steel 304)	
	-	

3 Pad diameter

10	ø10	
16	ø16	
25	ø25	
40	ø40	

4 Material

N	NBR
S	Silicone rubber*1 *2
U	Urethane rubber
F	FKM
GN	Conductive NBR
GS	Conductive silicone rubber

*1 Compliant with the FDA (USA Food and Drug Administration) regulation 21CFR§177.2600 for "Rubber articles intended for repeated use"

*2 Compliant with the standards for "Rubber apparatus (excluding baby drinking apparatus) and containers/packaging" (D3) (Partial revision: Ministry of Health, Labour, and Welfare Notification No. 595, 2012) in Section 3 "Apparatus and Containers/ Packaging" of the Food Sanitation Act, Article 18 "Specifications and Standards for Food and Food Additives, etc." (Ministry of Health and Welfare Notification No. 370, 1959)

Lock ring unit

LOOKTII					
Part no.	Pad diameter [mm]				
ZPSL1	ø10, ø16				
ZPSL2	ø25				
ZPSL3	ø40				

2	Va	cuum	inlet	dir	ec	tio	on	
	_							

T Vertical

With adapter

6	Vacuum		inl	et

Туре	Symbol	Size	Pad diameter [mm]			
	Symbol	Size	ø10, ø16	ø25	ø40	
	AS5	M5 x 0.8	O*1	○*1	—	
Male	AS6	M6 x 1	⊖*1	⊖*1	O*1	
thread	AG01	G1/8	⊖*1	⊖*1	—	
	AG02	G1/4	—	—	O*1	
	Nil	M3 x 0.5	○ (ⓒ Connection thread: A5/A6)	○ (ⓒ Connection thread: A6)	○ (⑥ Connection thread: A6)	
		M5 x 0.8	—	○ (⑥ Connection thread: A8)	○ (ⓒ Connection thread: A8)	
Female	B5	M5 x 0.8	O*1	O*1	—	
thread	B6	M6 x 1	O*1	O*1	O*1	
	B8	M8 x 1.25	—	⊖*1	O*1	
	B01	Rc1/8	O*1	O*1	O*1	
	BG01	G1/8	O*1	O*1	—	
	BG02	G1/4	—	—	O*1	

*1 Use the connection thread.

6 Connection thread


Tuno	Symbol Size			Pad diameter [mm]	
Туре	pe Symbol	IDOI SIZE	ø10, ø16	ø25	ø40
Mala	A5	M5 x 0.8	O*2	—	—
Male thread	A6	M6 x 1	O*2	O*2	○*2
uneau	A8	M8 x 1	—	O*2	○*2

*2 With a (female) vacuum inlet





How to Order



3 Pad diameter 2 Vacuum inlet direction Adapter material S Stainless steel (Stainless steel 304) Nil Pad unit 015 т Vertical 02 γ Lateral 035

With adapter

5 Con	nection	h thread/	Vacuum inle	et	O: ZP3S-T/Vertical ●: Z	P3S-Y/Lateral
5 Connection thread		6 Vacuum inlet		Pad diameter		
Туре	Symbol	Size	Туре	Symbol	Size	All sizes
Male	A3	M3 x 0.5	—	Nil	*1	0
thread	A6	M6 x 0.75	Female thread	B3	M3 x 0.5	0
Female	B3	M3 x 0.5	—	Nil	*1	0
thread	БЗ	IVIS X 0.5	Female thread	B3	M3 x 0.5	

*1 Use the connection thread.

4 Material

ø1.5

ø2

ø3.5

N	NBR
S	Silicone rubber*1 *2
U	Urethane rubber
F	FKM
GN	Conductive NBR
GS	Conductive silicone rubber

- *1 Compliant with the FDA (USA Food and Drug Administration) regulation 21CFR§177.2600 for "Rubber articles intended for repeated use"
- *2 Compliant with the standards for "Rubber apparatus (excluding baby drinking apparatus) and containers/packaging" (D3) (Partial revision: Ministry of Health, Labour, and Welfare Notification No. 595, 2012) in Section 3 "Apparatus and Containers/ Packaging" of the Food Sanitation Act, Article 18 "Specifications and Standards for Food and Food Additives, etc." (Ministry of Health and Welfare Notification No. 370, 1959)



For pad units and pads with an adapter (stainless steel type): The standard product is a secondary battery compatible product. For details on specifications and dimensions, refer to the **Web Catalog**.

Pad diameter: Ø4, Ø6, Ø8, Ø10, Ø13, Ø16

How to Order

P3 Series

Pad unit ZP3 - 04 UM N * Pad unit's sales unit: 10 pcs. (Except material HS) With adapter ZP3 S - T 04 UM N - B5 - 0 2 3 0 0 5 6

Compact Type

Flat Type with Groove



2 Vacuum inlet direction		
Nil	Pad unit	
Т	Vertical	
Y	Lateral	

3 Pad diameter		
04	ø4	
06	ø6	
08	ø8	
10	ø10	
13	ø13	
16	ø16	

Flat type with groove

4 Material

-	
Ν	NBR
S	Silicone rubber*1*2
U	Urethane rubber
F	FKM
GN	Conductive NBR
GS	Conductive silicone rubber
HS	Semiconductive silicone rubber

*1 Compliant with the FDA (USA Food and Drug Administration) regulation 21CFR§177.2600 for "Rubber articles intended for repeated use"

*2 Compliant with the standards for "Rubber apparatus (excluding baby drinking apparatus) and containers/packaging" (D3) (Partial revision: Ministry of Health, Labour, and Welfare Notification No. 595, 2012) in Section 3 "Apparatus and Containers/ Packaging" of the Food Sanitation Act, Article 18 "Specifications and Standards for Food and Food Additives, etc." (Ministry of Health and Welfare Notification No. 370, 1959).

5 Con	Connection thread/ 6 Vacuum inlet O: ZP3S-T/Vertical •: ZP3S-Y/Lateral								
5 Connection thread			6 Vacuum inlet			Pad diameter [mm]			
Туре	Symbol	Size	Туре	Type Symbol Size ø			ø10 to ø16		
	A5	M5 x 0.8	—	Nil	Use the connection thread.	0	0		
Male thread	A10	M10 x 1	Female thread	B5	M5 x 0.8	0	—		
uneau	A12	M12 x 1	Female thread	B5	M5 x 0.8	—	0		
Female	B5	M5 x 0.8	—	Nil	Use the connection thread.	0	0		
thread	D 5	WD X 0.0	Female thread	B5	M5 x 0.8				




thread

Compact Type **Bellows Type** P3 Series Pad diameter: Ø4, Ø6, Ø8

For pad units and pads with an adapter (stainless steel type): The standard product is a secondary battery compatible product. For details on specifications and dimensions, refer to the Web Catalog.



How to Order



1 Ac	lapter material	2 Vac	uum inlet direction	3	Pad diameter	4	Material	
S	Stainless steel (Stainless steel 304)	Nil	Pad unit	04	ø4	N		NBF
		Т	Vertical	06	ø6	S	Si	icone rut
		Y	Lateral	08	ø8	U	ι ι	Jrethane
						F		FKN

M5 x 0.8

	With adapter								
6 Con	5 Connection thread/ 6 Vacuum inlet O: ZP3S-T/Vertical •: ZP3S-Y/Lateral								
5 Connection thread				6 Va	cuum inlet	Pad diameter			
Туре	Symbol	Size	Туре	Symbol	Size	All sizes			
Male	A5	M5 x 0.8	—	Nil	Use the connection thread.	0			
thread	A10	M10 x 1	Female thread	B5	M5 x 0.8	0			
Female	B5	M5 x 0.8	_	Nil	Use the connection thread.	0			
thread	D3	0.0 X CIVI	Female thread	B5	M5 x 0 8				

B5

Female thread

•						
N	NBR					
S	Silicone rubber*1 *2					
U	Urethane rubber					
F	FKM					
GN	Conductive NBR					
GS	Conductive silicone rubber					

- *1 Compliant with the FDA (USA Food and Drug Administration) regulation 21CFR§177.2600 for "Rubber articles intended for repeated use"
- *2 Compliant with the standards for "Rubber apparatus (excluding baby drinking apparatus) and containers/packaging" (D3) (Partial revision: Ministry of Health, Labour, and Welfare Notification No. 595, 2012) in Section 3 "Apparatus and Containers/ Packaging" of the Food Sanitation Act, Article 18 "Specifications and Standards for Food and Food Additives, etc." (Ministry of Health and Welfare Notification No. 370, 1959)



1 Adapter


Compact Type Bellows Type with Ribs

ZP3 Series



How to Order

Pad diameter: Ø10, Ø13, Ø16



Adapter material		2 Vac	uum inlet direction	3 Р	3 Pad diameter		
S	Stainless steel (Stainless steel 304)	Nil	Pad unit	10	ø10		
		Т	Vertical	13	ø13		
		Y	Lateral	16	ø16		

With adapter

5 Con	nection	thread/ 6	O: ZP3S-T/Vertical ●: ZP3	3S-Y/Lateral		
6	Connecti	on thread		6 Vacuum inlet		
Туре	Symbol	Size	Туре	Symbol	Size	All sizes
Male	A5	M5 x 0.8	—	Nil	Use the connection thread.	0
thread	A12	M12 x 1	Female thread	B5	M5 x 0.8	0
Female	e B5 M5 x 0.8		—	Nil	Use the connection thread.	0
thread	65	IVIO X 0.0	Female thread	B5	M5 x 0.8	

4 Material

Ν	NBR
S	Silicone rubber*1 *2
U	Urethane rubber
F	FKM
GN	Conductive NBR
GS	Conductive silicone rubber

For pad units and pads with an adapter (stainless steel type): The standard product is a secondary battery compatible product. For details on specifications and dimensions, refer to the Web Catalog.

> *1 Compliant with the FDA (USA Food and Drug Administration) regulation 21CFR§177.2600 for "Rubber articles intended for repeated use"

> *2 Compliant with the standards for "Rubber apparatus (excluding baby drinking apparatus) and containers/packaging" (D3) (Partial revision: Ministry of Health, Labour, and Welfare Notification No. 595, 2012) in Section 3 "Apparatus and Containers/Packaging" of the Food Sanitation Act, Article 18 "Specifications and Standards for Food and Food Additives, etc." (Ministry of Health and Welfare Notification No. 370, 1959)

For pad units and pads with an adapter (Excludes the M12 x 1.75 type): The standard product is a secondary battery compatible product. For details on specifications and dimensions, refer to the **Web Catalog**.

Pad unit ZP3P - 20 PT SF Vertical vacuum inlet With adapter ZP3P - T 20 PT SF - A5

Vacuum Pad

Adapter material							
Nil	Aluminum						
s	Stainless steel						
3	(Stainless steel 304)						

2 Pad diameter					
20	ø20				
25	ø25				
35	ø35				
50	ø50				

With adapter

4 Mounting thread size

Туре	Symbol	Size	ø 20	ø 25	ø 35	ø 50
	A5	M5 x 0.8			—	_
Male	AG1	G1/8		•	—	_
thread	AG2	G1/4	_	—		•
	AG3	G3/8	—	_	•	•
Female thread	B5	M5 x 0.8			—	_
	B8	M8 x 1.25	—	_		

Pad material SF

P3P-PT Series

Pad diameter: Ø20, Ø25, Ø35, Ø50

How to Order

*1 Compliant with the FDA (USA Food and Drug Administration) regulation 21CFR§177.2600 for "Rubber articles intended for repeated use"

Silicone rubber*1, *2

*2 Compliant with the standards for "Rubber apparatus (excluding baby drinking apparatus) and containers/packaging" (D3) (Partial revision: Ministry of Health, Labour, and Welfare Notification No. 595, 2012) in Section 3 "Apparatus and Containers/Packaging" of the Food Sanitation Act, Article 18 "Specifications and Standards for Food and Food Additives, etc." (Ministry of Health and Welfare Notification No. 370, 1959).



Vacuum Pad

2.5-Stage Bellows Type ZP3P-JT Series

For pad units and pads with an adapter (Vacuum inlet: Excludes the built-in One-touch fitting type): The standard product is a secondary battery compatible product. For details

on specifications and dimensions, refer to the Web Catalog.

	How to Order	
Pad unit ZP3P With adapter ZP3P	- 20 JT 2 SF - W - T 20 JT 2 SF - W Bellows type 2.5-stage • Silicone re	- AG01 -
Adapter material	Pad diameter	3 Attachment
Nil Aluminum	20 ø20	W With attachment
S Stainless steel (Stainless steel 304)	25 ø25	WM With mesh attachment
	32 Ø32	WF With flat attachment
	40 ø40	

ø50

4 Connection thread/**5** Vacuum inlet

4 Connection thread			S Vacuum inlet		Pad diameter [mm]										
Туре	Thread	Symbol	Size	Thread	Symbol	Size	ø20, ø25	ø32, ø40, ø50							
		AG01	G1/8				•	•							
	Male	AG02	G1/4	— Nil	Nii*1	•	•								
Direct	thread	AG03	G3/8			NI	_]] —		_			•
mounting		AG04	G1/2				—	•							
	Female	BG01	G1/8		NI:I	Nil	*1	•	_						
	thread	BG02	G1/4				_	•							
		A16	M16 x 1	Female	B01	Rc1/8									
Plate	late Male A	AIO	IVITOXI	thread	BN01	NPT1/8									
mounting	thread	A20	M20 x 1	Female B02	Rc1/4										
		AZU		thread	BN02	NPT1/4		-							

50

With adapter

*1 Use the connection thread.

Pad, adapter assembly, and mounting nuts are included but do not come assembled.



Vacuum Pad 5.5-Stage Bellows Type

For pad units and pads with an adapter (Vacuum inlet: Excludes the built-in One-touch fitting type): The standard product is a secondary battery compatible product. For details on specifications and dimensions, refer to the **Web Catalog**.

ZP3P-JT Series

Pad unit ZP3P -	How to O	<u>F-WG</u>		
With adapter ZP3P	2 Bellows type ●	With guide a Silicone rubber	GO1 – 3 4 ttachment	
Adapter materialNilAluminumSStainless steel (Stainless steel 304)	Pad diameter 20 020 25 025 32 032 40 040	5 2		

ø50

With adapter

50

3 Connection thread/**4** Vacuum inlet

Connection thread			4 Vacuum inlet		Pad diameter [mm]			
Туре	Thread	Symbol	Size	Thread	Symbol	Size	ø20, ø25	ø32 to ø50
	Male	AG01	G1/8		Nil	*1	•	
Direct	thread	AG02	G1/4] —				•
mounting	Female	BG01	G1/8		Nil	*1	•	—
	thread	BG02	G1/4] —				•
		A16	M16 x 1	Female	B01	Rc1/8		
Plate	Male	AIO	IVITOXI	thread	BN01	NPT1/8		
mounting	thread	A20	M20 x 1	Female	B02	Rc1/4		
		A20		thread	BN02	NPT1/4		-


*1 Use the connection thread.

Pad, adapter assembly, and mounting nuts are included but do not come assembled.



For pad units and pads with an adapter: The standard product is a secondary battery compatible product. For details on specifications and dimensions, refer to the **Web Catalog**.

Flat Type with Ribs Bellows Type ZP3C Series Flat type



Pad unit ZP3C - 20 C FS With adapter ZP3C - T 20 C FS - MF - A8 0 2 3 0 0 5 Pad material: FS61

Vacuum Pad

Vacuum inlet direction				
Nil Pad unit				
T Vertical				

Pad	Pad diameter			
20	ø20			
25	ø25			
32	ø32			
40	ø40			
50	ø50			

B Pad	d form
С	Flat

C B

lat type with ribs	
Bellows type	

Mesh	filter
MCOIL	me

(4

Nil Without mesh filter	
MF	With mesh filter

6 Connection thread

Turne	Type Thread Symbol		Size	Pad diameter [mm]	
Туре	Inreau	Symbol	Size	Ø20 to Ø32	ø 40 , ø 50
		A8	M8 x 1	•	—
		A10	M10 x 1	—	•
Direct		AG01	G1/8	•	—
mounting		AG02	G1/4	—	•
		BG01	G1/8	•	—
		BG02	G1/4	—	•

* Use the connection thread for the vacuum inlet.

Specifications

Pad/Mesh filter specifications

	Material	FS61 (Fluoro-based rubber)	
Pad	Color	Green	
	Hardness (Shore A: $\pm 5^{\circ}$)	60	
Mesh filter		Opening: 250 µm	

Adapter specifications


Connection	Male thread		Female thread			
Pad diameter	ø20 to ø32	ø 40 , ø 50	ø20 to ø32	ø 40, ø 50		
Connection thread	M8 x 1 G1/8	M10 x 1 G1/4	G1/8	G1/4		
Vacuum inlet	Use the connection thread.					


Vacuum Pad/Bowl Shape with Non-slip Feature **ZP3M** Series

For pads with an adapter: The standard product is a secondary battery compatible product. For details on specifications and dimensions, refer to the Web Catalog.



How to Order





т

Pad diameter

32	ø32
40	ø40
50	ø50
63	ø63
80	ø80
100	ø100

3 Material

Symbol	Material	Color
FS	FS61 (Fluoro-based rubber)	Green

4 Connection thread and type

Mounting		Symbol	Cine	Pad diameter	
Mounting	Туре	Symbol	Size	ø32 to ø50	ø63 to ø100
		A10	M10 x 1.0	•	—
	Male thread	A16	M16 x 1.5	—	•
Diversit		AG02	G1/4	•	•
Direct mounting		B14	M14 x 1.0	•	•
mounting	Female thread	BG02	G1/4	•	
		BG03	G3/8	•	•
	Square adapter	S32	□31.8	•	•

* The adapter and pad are adhered to each other and cannot be disassembled.

Specifications

Pad Material

Material	FS61 (Fluoro-based rubber)
Color of rubber	Green
Rubber hardness (Shore A: ±5°)	60
Operating temperature range*1	0°C to 200°C
Ambient temperature	0°C to 150°C

*1 Surface temperature of the workpiece to be adsorbed

Adapter Specifications

Connection	Male t	hread	d Female thread		Square adapter
Pad diameter	ø32 to ø50	ø63 to ø100	ø32 to ø50	ø63 to ø100	ø32 to ø100
Size	M10 x 1.0 G1/4	M16 x 1.5 G1/4	G	x 1.0 1/4 3/8	□31.8
Vacuum inlet	Use the connection thread and type.				

5 Mesh filter

Nil	None
MF	With mesh filter

Mesh filter unit

	-		
Part no.	Pad diameter		
Fait no.	ø32 to ø50	ø63 to ø100	
ZPMF-60-D13	•	—	
ZPMF-60-D18	—		

Pad Specifications

Part no.	Horizontal holding force [N]*1		Minimum curvature radius	
Part no.	Without oil	With oil	for adsorption [mm]*2	
ZP3M-T32RFS	47	21	14	
ZP3M-T40RFS	81	53	15	
ZP3M-T50RFS	111	74	20	
ZP3M-T63RFS	170	108	27.5	
ZP3M-T80RFS	231	178	36	
ZP3M-T100RFS	387	224	46	

*1 These are actual measurement values when flat workpieces were adsorbed and are not guaranteed values. (According to the SMC test) The values vary depending on the conditions (shape, surface roughness, oil type, oil amount, and other conditions) of the workpiece.

*2 These are actual measurement values when cylindrical workpieces were adsorbed and are not guaranteed values. (According to the SMC test)


Mesh Filter Specifications

Mesh filter	60
Opening	250 μm

Bernoulli Gripper ZNC Series

For grippers without a sensor: The standard product is a secondary battery compatible product. For details on specifications and dimensions, refer to the Web Catalog.

How to Order



Mounting plate (Size 20)

🕖 Body size 20

30

40

60

80

ø20 mm

ø30 mm

ø40 mm

ø60 mm

ø80 mm

<u> </u>	31		
Nil	Without moun	00	
т	With mounting	Aluminum	
TS	plate	Stainless steel	\mathcal{D} .

Mounting plate

material. Stoppers cannot be retrofitted.

Vibration suppression cover can be retrofitted to the basic type.


* The vibration suppression cover cannot be used with the type with stoppers.

- The mounting plate is shipped together with the product but does not come assembled. Single unit part nos. \Rightarrow Web Catalog *
- The piping methods for types with and without a mounting plate are shown in Table 2 below. *

Table 1. With Vibration Suppression Cover


Symbol	Material	Body size		Body material	
Symbol	waterial	symbol	Aluminum	Resin	Stainless steel
		20	—	—	—
		30	_	—	—
VP	Resin	40	•	•	—
		60	_	—	—
		80	—	—	—
		20	•	•	
		30	•	•	•
VS	Stainless steel	40	•	—	
		60	•	•	•
		80	•	•	

Table 2. Size 20 Piping (Refer to the Web Catalog for details on how to mount the product.)



An O-ring (5.7 x 3.7 x 1) and a plug are shipped together with the product as accessories. SMC

Attachments/Part Nos.




Stopper size 1: With 3 stoppers * Stopper size 2: With 3 stoppers and 3 spring pins For replacement instructions \Rightarrow Refer to the **Web Catalog**.

Vibration suppression cover ZNCM – 40 VP							
• Body	/ size				/later	rial	
20	ø20 mm	60	ø60 mm	1	VP	Resin	
30	ø30 mm	80	ø80 mm		vs	Stainless steel	
40	ø40 mm					ial: Resin is only able for body size 40	

For stainless steel:


Body sizes ø20mm and ø30 mm: With 2 mounting screws Body sizes ø40 mm, ø60 mm, and ø80 mm: With 3 mounting screws

Bernoulli Gripper With Coanda Grip **ZNC-C Series**





How to Order





20	ø20 mm			
30	ø30 mm			
40	ø40 mm			
60	ø60 mm			
80	ø80 mm			

Body material
 Nil Aluminum

Stainless steel

S

Nil	None			
Т	Aluminum			
TS	Stainless steel			
	mounting plate is ed together with the			


- shipped together with the product but does not come assembled. * The piping methods for
- types with and without a mounting plate are shown in Table 1 below.

4 Attachment

Nil	Without vibration suppression cover			
V	With vibration suppression cover			
. It is no	t possible to additionally install or remove			

It is not possible to additionally install or remove the vibration suppression cover.

Table 1. Piping




Coanda Grip Only / Part No.

ø40 mm

40

	Z		M − 4 dy size •	
20	ø20 mm	60	ø60 mm	
30	ø30 mm	80	ø80 mm	

Vacuum Regulator RoHS 25A-IRV10/20 Series



* This product cannot be used in environments containing chemical agents such as hydrofluoric acid, etc.

* The 25A- series specifications and dimensions are the same as those of the standard model.

For details, refer to the Web Catalog.