

Dual Rod Cylinder

CXSJ/CXS Series

Ø6, Ø10, Ø15, Ø20, Ø25, Ø32

Dual rod cylinder with guide function suitable for pick & place applications.







Compact Type


CXSJ Series


 Auto switch can be installed from 3 directions.



Symmetric mounting








Bore size	0		Note) Weight			
(mm)	Series	Width	Height	Full length	(kg)	
~6	CXSJ□6	13.4	32	42 + Stroke	0.057	
ø6	CXS□6	16	37	58.5 + Stroke	0.095	
~10	CXSJ□10	15	42	56 + Stroke	0.114	
ø10	CXS□10	17	46	72 + Stroke	0.170	
45	CXSJ□15	19	54	70 + Stroke	0.219	
ø15	CXS□15	20	58	79 + Stroke	0.280	
00	CXSJ□20	24	62	84 + Stroke	0.371	
ø20	CXS□20	25	64	94 + Stroke	0.440	
05	CXSJ□25	29	73	87 + Stroke	0.544	
ø25	CXS□25	30	80	96 + Stroke	0.660	
~20	CXSJ□32	37	94	100.5 + Stroke	1.078	
ø32	CXS□32	38	98	112 + Stroke	1.230	

Note) Slide bearing, 20 mm strokes

Axial piping available (ø6, ø10)




 Allowable kinetic energy, allowable load, and nonrotating accuracy are equivalent to those of CXS basic type.

With air cushion

CXS Series: Ø20, Ø25, Ø32

Air cushion only minimally adds to full length dimension, compared with the standard type cylinder.



1 Improved allowable kinetic energy:


Two to three times that of the standard type

2 Improved noise reduction:

Reduction of more than 6 dB is possible

Unique air cushion mechanism with no cushion ring

Elimination of the cushion ring used in current type air cushions has made it possible to reduce the overall length of the cylinder while retaining all the advantages of a compact profile.



- When the piston is retracting, air is exhausted through both A and A' until piston seal H passes air passage A.
- After piston seal H has passed air passage A, air is exhausted only through A'. The section marked with slanted lines becomes a cushion chamber, and an air cushion effect is achieved.
- When air is supplied for the piston extension, the check seal opens and the piston extends with no delay.



Glean Series

11-12- CXSJ Series/ø6, ø10

Series	Туре	Bearing type
11-CXSJ	Vacuum specifications	Slide bearing Ball bushing bearing
12-CXSJ	Relieving type Special treatment	Ball bushing bearing










CXS Series Ø6, Ø10, Ø15, Ø20, Ø25, Ø32



CXSJ Series **Model Selection**

⚠ Caution Theoretical output must be confirmed separately, referring to the table on page 822.

3

4

Model Selection

Vertical Mounting Mounting orientation Max. speed (mm/s) Up to 200 Up to 400 Up to 600 Up to 800 Stroke (mm) All strokes ø6 ø10

2


ø32 **Horizontal Mounting**

ø15

ø20 ø25

Selection

graph



^{*} The maximum speeds for ø6 to ø32 are: ø6, 10: up to 800 mm/s; ø15, 20: up to 700 mm/s; ø25, 32: up to 600 mm/s

Caution

If the cylinder is horizontally mounted and the plate end does not reach the load's center of gravity, use the formula below to calculate the imaginary stroke L' that includes the distance between the load's center of gravity and the plate end. Select the graph that corresponds to the imaginary stroke L'.

Imaginary stroke L' = (Stroke) + k + L

k: Distance between the center and end of the plate

2.75 mm
4 mm
5 mm
C
6 mm
8 mm


(Example)


1 When using CXSJM6-10 and L = 15 mm: Imaginary stroke L' = 10 + 2.75 + 15 = 27.75 Therefore, the graph used for your model selection should be the one for CXSJM6-30 6).


2 When using CXSJL25-50 and L = 10 mm: Imaginary stroke L' = 50 + 6 + 15 = 71 Therefore, the graph used for your model selection should be the one for CXSJL25-75 14).




Vertical Mounting












Note) V = 700 mm/s for ø15, ø20.


CXSJ Series


Horizontal Mounting





























CXS Series **Model Selection/Basic Type**


★ Caution Confirmation of theoretical output is required separately.

Basic Type: CXS

Vertica	al Moun	iting							
Mour orien	nting ntation								
Max. spe	eed (mm/s)	Up to 100	Up to 200	Up to 300	Up to 400	Up to 600	Up to 700 (Up to 800)		
Stroke	(mm)	All strokes							
	ø6	(1)		(2)					
	ø 10								
Selection	ø 15								
graph	ø 20		(3)		(4)	(5)	(6)		
	ø 25								
	ø 32								

Refer to "Theoretical Output" on page 835.

Horizontal Mounting



^{*} The maximum speeds for ø10 to ø32 are: ø10: up to 800 mm/s; ø15, 20: up to 700 mm/s; ø25, 32: Up to 600 mm/s

If the cylinder is horizontally mounted and the plate end does not reach the load's center of gravity, use the formula below to calculate the imaginary stroke L' that includes the distance between the load's center of gravity and the plate end. Select the graph that corresponds to the imaginary stroke L'.

Imaginary stroke L' = (Stroke) + k + L

k: Distance between the center and end of the plate

2.75 mm
4 mm
5 mm
0
6 mm
8 mm

(Example)


When using CXSM6-10 and L = 15 mm:


Imaginary stroke L' = 10 + 2.75 + 15 = 27.75


Therefore, the graph used for your model selection should be the one for CXSM6-30.





Vertical Mounting
















CXS Series


Horizontal Mounting


0







100














Horizontal Mounting












CXS Series

Model Selection/With Air Cushion


⚠ Caution Confirmation of theoretical output is required separately. Refer to "Theoretical Output Table" on page 847.

With Air Cushion: CXS

Vertical Mounting



Horizontal Mounting



Caution

If the cylinder is horizontally mounted and the plate end does not reach the load's center of gravity, use the formula below to calculate the imaginary stroke L' that includes the distance between the load's center of gravity and the plate end. Select the graph that corresponds to the imaginary stroke L'.

Imaginary stroke L' = (Stroke) + k + L

k: Distance between the center and the end of the plate


ø 20	6 mm
ø 25	0 111111
ø 32	8 mm




When using CXSM20-10 and L = 10 mm:


Imaginary stroke L' = 10 + 6 + 10 = 26


Therefore, the graph used for your model selection should be the one for CXSM20-30.





Vertical Mounting















CXS Series


Horizontal Mounting


















Dual Rod Cylinder/Compact Type CXSJ Series

Ø6, Ø10, Ø15, Ø20, Ø25, Ø32

How to Order



Applicable Auto Switches/Refer to pages 1289 to 1383 for detailed auto switch specifications.

				ndicator Wiring		Load voltage		Auto switch model		Lead wire length (m)*						
Туре	Special function	Electrical entry	Indicator	(output)	DC		AC			0.5	1	3	5	Pre-wired connector	Applicable load	
		ona y	"g".	,		DC	AC	Perpendicular	In-line	(Nil)	(M)	(L)	(Z)	Commodion		
				3-wire (NPN)		5 V. 12 V		M9NV	M9N	•	•	•	0	0	IC circuit	
듄	_			3-wire (PNP)		5 V, 12 V		M9PV	M9P	•	•	•	0	0	IC CIICUIL	
switch				2-wire	1	12 V		M9BV	M9B	•	•	•	0	0	_	
		on Grommet Yes		3-wire (NPN)	5 V. 12 V] [M9NWV	M9NW	•	•	•	0	0	IC circuit	Relay,	
	(2-color indication		Yes	3-wire (PNP) 24	24 V	4 V 5 V, 12 V	-	M9PWV	M9PW	•	•	•	0	0	TIC CIICUIL	PLC
Solid state	(2 color indicator)			2-wire	}	12 V		M9BWV	M9BW	•	•	•	0	0	_	
ğ				3-wire (NPN)		5 V. 12 V		M9NAV*1	M9NA*1	0	0	•	0	0	IC circuit	
So	Water resistant (2-color indicator)			3-wire (PNP)		5 V, 12 V		M9PAV*1	M9PA*1	0	0	•	0	0	IC CIICUII	
	(E dolor indidator)			2-wire		12 V		M9BAV*1	M9BA*1	0	0	•	0	0	_	
_ t			Yes	3-wire (NPN equiv.)	_	5 V	_	A96V	A96	•	_	•	_	_	IC circuit	
Reed auto switch	Grommet	et res		12 V	100 V	A93V*2	A93	•	•	•	•	_	_	Relay,		
		None	2-wire	24 V	5 V, 12 V	100 V or less	A90V	A90	•	_	•	_	_	IC circuit	PLC	

- *1 Water resistant type auto switches can be mounted on the above models, but in such case SMC cannot guarantee water resistance. Consult with SMC regarding water resistant types with the above model numbers.
- *2 1 m type lead wire is only applicable to D-A93.

Lead wire length symbols: 0.5 m Nil (Examp	ole) M9NW
1 m M	M9NWM
3 m L	M9NWL
5 m Z	M9NWZ

* Solid state auto switches marked with "O" are produced upon receipt of order.

- Since there are applicable auto switches other than listed, refer to page 832 for details.
- For details about switch with pre-wired connector, refer to pages 1358 and 1359.
- * Auto switches are shipped together (not assembled).



CXSJ Series



Symbol Rubber bumper

Operating Conditions

Non-rotating Accuracy


Non-rotating accuracy θ^o without a load should be less than or equal to the value provided in the table below as a guide. Housing



Bore size (mm)	ø6 to ø32
CXSJM (Slide bearing)	
CXSJL (Ball bushing bearing)	±0.1°

CXSJ□6 to 32 Deflection at the Plate End

An approximate plate-end deflection X without a load is shown in the graph below.



Specifications

Bore size (mm)	6	10	15	20	25	32		
Fluid			Air (No	n-lube)				
Proof pressure			1.05	MPa				
Maximum operating pressure	0.7 MPa							
Minimum operating pressure	0.15 MPa	0.1	MPa		0.05 MPa			
Ambient and fluid temperature		-	10 to 60°C	(No freezin	g)			
Piston speed	30 to 80	00 mm/s	30 to 70	00 mm/s	30 to 60	00 mm/s		
Cushion		R	ubber bump	er on both	ends			
Stroke adjustable range	0 to -5 mm compared to the standard stroke							
Port size	M3 x 0.5	M3 x 0.5 M5 x 0.8 Rc (NPT, PF)						
Allowable kinetic energy	0.016 J	0.064 J	0.095 J	0.17 J	0.27 J	0.32 J		

Standard Stroke

 Model
 Standard stroke
 Long stroke (-XB11)

 CXSJ□6
 10, 20, 30, 40, 50
 —

 CXSJ□10
 10, 20, 30, 40, 50, 75
 80 to 150

 CXSJ□15
 110 to 150

 CXSJ□20, 25, 32
 10, 20, 30, 40, 50, 75, 100
 110 to 200


Theoretical Output


											(N)
Bore size	Rod size	Operating	Piston area	Operating pressure (MPa)							
(mm)	(mm)	direction	(mm ²)	0.1	0.15	0.2	0.3	0.4	0.5	0.6	0.7
CXSJ□6	4	OUT	56	-	8.4	11.2	16.8	22.4	28.0	33.6	39.2
CVOT	*	IN	31	_	4.6	6.2	9.3	12.4	15.5	18.6	21.7
CXSJ□10	6	OUT	157	15.7	_	31.4	47.1	62.8	78.5	94.2	110
CV20	٠ ا	IN	100	10.0	_	20.0	30.0	40.0	50.0	60.0	70.0
CXSJ□15	8	OUT	353	35.3	_	70.6	106	141	177	212	247
CXSJ		IN	252	25.2	_	50.4	75.6	101	126	151	176
CXSJ□20	10	OUT	628	62.8	_	126	188	251	314	377	440
CASJ_20	10	IN	471	47.1	_	94.2	141	188	236	283	330
CXSJ□25	40	OUT	982	98.2	_	196	295	393	491	589	687
CXSJL25	12	IN	756	75.6	_	151	227	302	378	454	529
CXSJ□32	40	OUT	1608	161	_	322	482	643	804	965	1126
CXSJ_32	16	IN	1206	121	_	241	362	482	603	724	844

Note) Theoretical output (N) = Pressure (MPa) x Piston area (mm²)

Maximum Load Mass

When the cylinder is mounted as shown in the diagrams below, the maximum load mass W should not exceed the values illustrated in the graph.






Weight

							(kg)				
Model		Standard stroke (mm)									
iviodei	10	20	30	40	50	75	100				
CXSJM6	0.047	0.057	0.067	0.077	0.087	_	_				
CXSJL6	0.048	0.058	0.068	0.078	0.088	_	_				
CXSJM10	0.099	0.114	0.129	0.144	0.159	0.198	_				
CXSJL10	0.106	0.121	0.136	0.151	0.166	0.205	_				
CXSJM15	0.198	0.219	0.240	0.261	0.282	0.335	0.387				
CXSJL15	0.218	0.239	0.260	0.281	0.302	0.355	0.407				
CXSJM20	0.345	0.371	0.397	0.423	0.449	0.514	0.579				
CXSJL20	0.375	0.401	0.427	0.453	0.479	0.544	0.609				
CXSJM25	0.506	0.544	0.582	0.620	0.658	0.753	0.848				
CXSJL25	0.516	0.554	0.592	0.630	0.668	0.763	0.858				
CXSJM32	1.022	1.078	1.134	1.190	1.246	1.386	1.526				
CXSJL32	1.032	1.088	1.144	1.200	1.256	1.396	1.536				
letel Ferrendel eleter of CVC IDCD D and CVC ID10D D along add the											

Note) For axial piping of CXSJ□6P-□ and CXSJ□10P-□, please add the following weight. CXSJ□6P-□: 0.009 kg, CXSJ□10P-□: 0.014 kg


Construction: Standard Piping

CXSJM (Slide bearing)



схѕлм10







Rod cover

Piston rod B-side piston

CXSJL (Ball bushing bearing) CXSJL6



CXSJL10





Rod cover

Piston rod B-side piston

Component Parts: Standard Piping

No.	Description	Material	Note		
1	Housing	Aluminum alloy	Hard anodized		
2	Piston rod A	Carbon steel Note)	Hard chromium electroplated		
3	Piston rod B	Carbon steel Note)	Hard chromium electroplated		
4	Rod cover	Aluminum bearing alloy			
5	Head cover	Aluminum alloy	Anodized		
6	Plate	Aluminum alloy	Glossy, self-coloring hard anodized		
7	Piston A	Piston A Aluminum alloy			
8	Piston B	on B Aluminum alloy			
9	Magnet	_			
10	Bumper bolt	Carbon steel	Nickel plated		
11	Hexagon nut	Carbon steel	Zinc chromated		
12	Bumper	Urethane			
13	Hexagon socket head cap screw	Chromium steel	Zinc chromated		
14	Hexagon socket head set screw	Chromium steel	Zinc chromated		
15	Retaining ring	Special steel	Phosphate coated		

Note) Stainless steel for CXSJM6.

Replacement Parts/Seal Kit

neplacemen	i Paris/Sear Kii					
Model	Seal kit no.	Contents				
CXSJM6	CXSJM6-PS					
CXSJL6	CXSJL6-PS	Set of nos. above ①, ⑧, and ②				
CXSJM10	CXSJM10-PS	Set of hos. above (1), (8), and (2)				
CXSJL10	CXSJL10-PS					
	0 0 - 10 - 1					

^{*} Seal kit includes (7), (8), and (2). Order the seal kit, based on each bore size.

Grease pack part no.: GR-S-010 (10 g)

No.	Description	Material	Note
16	Bumper B	Urethane	
17	Piston seal	NBR	
18	Rod seal	NBR	
19	O-ring	NBR	
20	O-ring	NBR	
21	Seal retainer	Stainless steel	
22	Retaining ring B	Special steel	Phosphate coated
23	Bolt holder	Stainless steel	
24	Bearing spacer	Aluminum bearing alloy	
25	Ball bushing	_	
26	Piston rod A	Special steel	Hard chromium electroplated
27	Piston rod B	Special steel	Hard chromium electroplated
28	O-ring	NBR	
29	Piston C	Stainless steel	
30	Bumper holder	Resin	


^{*} Since the seal kit does not include a grease pack, order it separately.

CXSJ Series


Construction: Standard Piping

CXSJM (Slide bearing)

схѕлм15



CXSJM20 to 32



Head cover

Rod cover Component Parts: Standard Piping

Component i arts. Ctandard i iping									
No.	Description	Material	Note						
1	Housing	Aluminum alloy	Hard anodized						
2	Piston rod A	Carbon steel	Hard chromium electroplated						
3	Piston rod B	Carbon steel	Hard chromium electroplated						
4	Rod cover	Aluminum bearing alloy							
5	Head cover	Special steel							
6	Plate	Aluminum alloy	Glossy, self-coloring hard anodized						
7	Piston A	Chromated							
8	Piston B	Stainless steel							
9	Magnet	_							
10	Bumper bolt	Carbon steel	Nickel plated						
11	Hexagon nut	Carbon steel	Zinc chromated						
12	Bumper	Urethane							
13	Hexagon socket head cap screw	Chromium steel	Zinc chromated						
14	Hexagon socket head set screw	Chromium steel	Zinc chromated						
15	Retaining ring	Special steel	Phosphate coated						

Replacement Parts/Seal Kit											
Model	Seal kit no.	Contents									
CXSJM15	CXSM15-PS										
CXSJM20	CXSM20-PS										
CXSJM25	CXSM25-PS										
CXSJM32	CXSM32-PS	Set of nos. above 17, 18, and 19									
CXSJL15	CXSL15APS	Set of nos. above (//, (ii), and (ii)									
CXSJL20	CXSL20APS										
CXSJL25	CXSL25APS										
CXSJL32	CXSL32APS										


^{*} Seal kit includes ①, ⑬, and ⑬. Order the seal kit, based on each bore size.

* Since the seal kit does not include a grease pack, order it separately.


Grease pack part no.: GR-S-010 (10 g)

CXSJL (Ball bushing bearing)

CXSJL15



CXSJL20 to 32




Rod cover Head cover

No.	Description	Material	Note
16	Bumper B	Urethane	
17	Piston seal	NBR	
18	Rod seal	NBR	
19	O-ring	NBR	
20	O-ring	NBR	
21	Seal retainer	Stainless steel	
22	Retaining ring B	Special steel	Phosphate coated
23	Bolt holder	Stainless steel	
24	Bearing spacer	Resin	
25	Ball bushing	-	
26	Piston rod A	Special steel	Hard chromium electroplated
27	Piston rod B	Special steel	Hard chromium electroplated
28	O-ring	NBR	
29	Piston C	Stainless steel	
30	Bumper holder	Resin	

Construction: Axial Piping

CXSJ□6P, CXSJ□10P



Component Parts: Axial Piping


••••	omponent i arter / tatar i iping									
No.	Description	Material	Note							
1	Cover	Aluminum alloy	Hard anodized							
2	Adapter	Aluminum alloy	Anodized							
3	Hexagon socket head cap screw	Chromium steel	Zinc chromated							
4	Hexagon socket head plug		Nickel plated							
5	O-ring	NBR								
6	O-ring	NBR								
7	Steel ball	Special steel	Hard chromium electroplated							
8	Steel ball	Special steel	Hard chromium electroplated							
9	Steel ball	Special steel	Hard chromium electroplated							

^{*} Parts other than those listed above are the same as those of CXSJ basic type.

Clean Series

There are two types of cylinders, relieving type and vacuum type, available for a clean room environment. The relieving type specification with the double-seal construction of the rod section allows the cylinder to channel exhaust through the relief port directly to the outside of a clean room environment. The vacuum type specification allows for the application of a vacuum on the rod section while forced exhaust of air takes place through the vacuum port to the outside of a clean room environment.

How to Order



^{*} Refer to the Web Catalog for dimensions.



Cylinder with Stable Lubrication Function (Lube-retainer)

How to Order

 $\textbf{CXSJ} \ \boxed{\textbf{Bearing type}} \ \boxed{\textbf{Bore size}} \ \underline{\underline{\textbf{M}}} - \boxed{\textbf{Stroke}} - \boxed{\textbf{Auto switch}} \ \boxed{\textbf{Number of auto switches}}$

Cylinder with Stable Lubrication Function (Lube-retainer)




Specifications

Bore size [mm]	6	10	15	20	25	32			
Min. operating pressure	0.2 MPa	0.15	MPa	Pa 0.1 MPa					
Piston speed	50 to 80	00 mm/s	50 to 70	00 mm/s	50 to 600 mm/s				

^{*} Specifications other than the above are the same as the standard type.

Dimensions (Dimensions other than those shown below are the same as those of the standard model.)


CXSJ□6, 10M




ZZ + Stroke

SS + Stroke









				[HIIIII]
Model	R	RR	SS	ZZ
CXSJ□6M	25	13.5	36.5	46.5
CXSJ□10M	33.5	17	49.5	61
CXSJ□15M	44	_	63.5	76
CXSJ□20M	51	_	73.5	90
CXSJ□25M	52	_	76.5	93
CXSJ□32M	66	_	90.5	110.5


							[mm]	
Symbol				Z				
Model Stroke	10	20	30	40	50	75	100	
CXSJ□6M	19.5	29.5	39.5	39.5 49.5		_	_	
CXSJ□10M	23	33	43	53	63	88	_	
CXSJ□15M	3	1		41	51	61		
CXSJ□20M	3	6		46		66		
CXSJ□25M	3	7		47		67		
CXSJ□32M	5	0		60	80			

For details, refer to the Web Catalog.


Dimensions: ø6 Standard Piping













* For bolt holder, refer to page 833, "Mounting".

CXSJ Series


Dimensions: Ø10 Standard Piping






* For bolt holder, refer to page 833, "Mounting".

Dimensions: Ø6, Ø10 Axial Piping



CXSJ Series

Dimensions: Ø15 to 32 Standard Piping





Bore size (mm)	Α	В	ZZ	С	D	E	F	G	Н	Т	J	K	L	М	N	NN	Q	R	Т	U	SS
15	54	19	70	52	17	8.5	2 x M5 x 0.8	42	25	5	10	2.5	20	2 x 2 x ø8 counterbore	2 x M4 x 0.7 with thread depth 6	ø8	9.5	38	9	2 x M5 x 0.8 with thread depth 4	57.5
20	62	24	84	60	22	11	2 x M5 x 0.8	50	29	6	12	4.5	25	2 x 2 x a9.5 counterbore	2 x M4 x 0.7 with thread depth 6	ø10	12	45	9	2 x M5 x 0.8 with thread depth 4	67.5
25	73	29	87	71	27	13.5	2 x M6 x 1.0	60	35	6	12	4.5	30	2 x 2 x ø11 counterbore	2 x M5 x 0.8 with thread depth 7.5	ø12	14.5	46	9	2 x M5 x 0.8 with thread depth 4	70.5
32	94	37	100.5	92	35	17.5	2 x M6 x 1.0	75	45	8	16	4	30	2 x 2 x ø11 counterbore	2 x M5 x 0.8 with thread depth 7.5	ø16	18.5	56	10	2 x Rc1/8 with thread depth 5	80.5

Symbol				
Oymbor		Z		
Bore size (mm)	10, 20	30, 40, 50	75	100
15	25	35	45	55
20	30	40	60	60
25	30	40	60	60
32	40	50	70	70

CXSJ Series Auto Switch Mounting

Auto Switch Proper Mounting Position for Stroke End Detection





Operating Range						(mm)				
Auto quitab madal	Bore size									
Auto switch model		10	15	20	25	32				
D-A9□, D-A9□V	5	6	6	7.5	8	9				
D-M9□, D-M9□V										
D-M9□A, D-M9□AV	2.5	3	3.5	4.5	4.5	5				
D-M9□W, D-M9□WV										

The operating ranges are provided as guidelines including hystereses and are not guaranteed values (assuming approximately ±30% variations). They may vary significantly with ambient environments.

Auto Switch Proper Mounting Position

Bore size (mm)	D-/	490,	D-A	96		D-A93 D-M9□, D-M9□W D-M9□AV										
(11111)	Α	В	С	D	Α	В	С	D	Α	В	С	D	Α	В	С	D
6	15.5	_	13.5	5.5	15.5	_	11	8	19.5	0.5	9.5	9.5	19.5	0.5	11.5	7.5
10	25.5	_	23.5	3	25.5	—	21	5.5	29.5	3	19.5	7	29.5	3	21.5	5
15	31.5	6	29.5	4	31.5	6	27	1.5	35.5	10	25.5	0	35.5	10	27.5	2
20	39	9	37	7	39	9	34.5	4.5	43	13	33	3	43	13	35	5
25	40	11	38	9	40	11	35.5	6.5	44	15	34	5	44	15	36	7
32	49	11.5	47	9.5	49	11.5	44.5	7	53	15.5	43	5.5	53	15.5	45	7.5

Bore size		9□A	Α				
(mm)	Α	В	С	D			
6	19.5	0.5	7.5	11.5			
10	29.5	3	17.5	9			
15	35.5	10	23.5	2			
20	43	13	31	5			
25	44	15	32	7			
32	53	15.5	41	7.5			


Note 1) ø6: D-A90, A96, A93, F9BA ø10: D-A90, A96, A93


Only outward electrical entry (D dimension) is available.

Note 2) Minus value in D column (ø15, ø20, ø25, ø32) means that the auto switches are to be mounted beyond the cylinder body edges.

Note 3) When setting an auto switch, confirm the operation and adjust its mounting position.


Auto switch mounting dimensions






			(mm)		
Auto switch model	Symbol	Bore size			
Auto Switch model	Symbol	6	10		
D-A9□	A 1	1	1		
D-M9□, D-M9□W	B ₁	1	1		
D-M9□A	B ₁	2	2		
D-A9□V	C1, D1	5.5	5.5		
D-A9⊟V	C2, C3, D2	4	4		
D-M9□V, D-M9□WV	C1, D1	8	8		
D-M9□AV	C2, C3, D2	6	6		
-					


CXSJ□15 to 32





					(mm)			
Auto switch model	0	Bore size						
Auto switch model	Symbol	15	20	25	32			
D-M9□, D-M9□W	A 1	1	1	1	1			
D-M9□A	A 1	2	2	2	2			
D-A9□V	C ₁	5.5	5.5	5.5	5.5			
D-M9□WV	C ₂	4.5	4.5	4.5	4.5			
D-M9□AV	C ₃	1	_	_	_			

Auto Switch Mounting




Tightening Torque of Auto Switch Mounting Screw (N-m)


Tightening Torque of Auto Switch Mounting Screw (N-III									
Auto switch model	Tightening torque								
D-M9□(V)									
D-M9□W(V)	0.05 to 0.15								
D-A93									
D-M9□A(V)	0.05 to 0.10								
D-A9□(V) (Excludes the D-A93)	0.10 to 0.20								

⚠Caution

Avoid proximity to magnetic objects.

When magnetic substances such as iron (including flange brackets) are in close proximity to an auto switch cylinder (auto switch mounting side), be sure to provide a clearance between the magnetic substance and the cylinder body as shown in the drawing below. If the clearance is less than 10 mm, the auto switch may not function properly.







Other than the applicable auto switches listed in "How to Order," the following auto switches can be mounted.

* Normally closed (NC = b contact) solid state auto switches (D-M9 \square E(V)) are also available. For details, refer to page 1308.



CXSJ Series Specific Product Precautions

Be sure to read this before handling the products. Refer to page 8 for safety instructions and pages 9 to 18 for actuator and auto switch precautions.

Mounting

 Make sure that the surface on which the cylinder is to be mounted is flat (reference value for flatness: 0.05 or less).


Dual-rod cylinders can be mounted from 3 directions, however, make sure that the surface on which the cylinder is to be mounted is flat (reference value for flatness: 0.05 or less). Otherwise, the accuracy of the piston rod operation is not achieved, and malfunctioning can occur.

2. The piston rod must be retracted when mounting the cylinder.

Scratches or gouges in the piston rod may lead to damaged bearings and seals and cause malfunctions or air leakage.

3. CXSJ (ø6. ø10)

Adjust the bolt holder using a hexagon wrench 3 mm in width across flats so that it does not protrude from the cylinder surface (approx. 0.5 mm depth from the cylinder surface to the top of the holder). If the bolt holder is not properly adjusted, it can interfere with the switch rail, hindering the auto switch mounting. The required length of the mounting bolt for a bolt holder and mounting hole in the rod cover side varies depending on the bearing surface position for the mounting bolt. Refer to dimensions L_1 and L_2 provided below to select the appropriate mounting bolt length.



	L1 (mm)	L2 (mm)	Applicable mounting bolt size
CXSJ□6	5	8.4	M3
CXSJ□10	5	9.5	M3

Be sure to mount the cylinder to the bolt holder. If it is operated without using the bolt holder, the bolt holder may drop.

Piping

1. For axial piping, the side port of the standard cylinder is plugged. However, a plugged port can be switched according to the operating conditions. When changing the port position, use the removed plug or a new plug. If reusing the removed plug, apply sealant, etc., before reassembly. If using a new M5 plug, apply a thin layer of grease all the way around the male thread before use. In addition, clear any foreign matter adhered to the port the plug was removed from before piping. After reassembly, be sure to check for air leakage before operating the product.

Plug part no.: (ø6) MTS08-08-P6830

(ø10) CXS10-08-R8601

Stroke Adjustment

⚠ Caution

1. After adjusting the stroke, make sure to tighten the hexagon nut to prevent it from loosening.

Dual-rod cylinders have a bolt to adjust 0 to -5 mm strokes on the retracted end (IN).

Loosen the hexagon nut to adjust the stroke; however, make sure to tighten the hexagon nut after making an adjustment.

Never operate a cylinder with its bumper bolt removed. Also, do not attempt to tighten the bumper bolt without using a nut.

If the bumper bolt is removed, the piston hits the head cover causing damage to the cylinder. Therefore, do not use a cylinder without a bumper bolt.

Furthermore, if the bumper bolt is tightened without a nut, the piston seal is caught in the leveled part, damaging the seal.

A bumper at the end of the bumper bolt is replaceable.

In case of a missing bumper, or a bumper has a permanent settling, use the

right part numbers for ordering.

Bore size (mm)	6, 10, 15	20, 25	32
Part no.	CXS10-34A	CXS20-34A	CXS32-34A
Part no.	28747	28749	28751
Qty.		1	

Disassembly and Maintenance

⚠ Caution

1. Never use a cylinder with its plate removed.

When removing the hexagon socket head cap screw on the end plate, the piston rod must be secured to prevent from rotating. However, if the sliding parts of the piston rod are scratched and gouged, a malfunction may occur.

When disassembling and reassembling the cylinder, contact SMC or refer to the separate operation manual.

⚠ Warning

 Take precautions when your hands are near the plate and housing.

When the cylinder is operated, take extra precautions to avoid getting your hands and fingers caught between the plate and housing, that can cause a bodily injury.

Operating Environment

⚠ Caution

- Do not operate the cylinder in a pressurized environment.
 The pressurized air may flow inside the cylinder due to its construction.
- Do not use as a stopper. This may cause malfunction. When using as a stopper, select a stopper cylinder (RS series) or a compact guide cylinder (MGP series).

Speed Adjustment

⚠ Caution


A sudden extension may occur with CXSJ□6.

CXSJ\(\subseteq 6\) has a low internal volume and sudden extension/erratic movement may occur particularly when it is used at low speed. This sudden extension can be mitigated by combining the use of meter-in and meter-out speed controllers.



Dual Rod Cylinder Basic Type CXS Series Ø6, Ø10, Ø15, Ø20, Ø25, Ø32

How to Order



Applicable Auto Switches/Refer to pages 1289 to 1383 for further information on auto switches.

			ight	VAC		Load volta	age	A		Lead wire le	ngth	(m) *												
Type	pe Special function Electrical entry	Wiring (Output)	. 3, 1		AC	Auto switch model		0.5	3	5	Pre-wired connector		cable load											
		Citity	Indi	(Output)		DC	AC	Perpendicular In-line		(Nil) (L)		(Z)	COLLIGECTOL											
5	_			3-wire (NPN)		5 V, 12 V		Y69A	Y59A	•	•	0	0	IC										
switch				3-wire (PNP)		5 V, 12 V		Y7PV	Y7P	•	•	0	0	circuit										
ě				2-wire		12 V		Y69B	Y59B	•	•	0	0	_	Deless									
a =	Diagnostic indication (2-color indicator)	Grommet	Grommet	Grommet	Grommet	Grommet	Grommet	Grommet	Grommet	Grommet	Grommet	Yes	3-wire (NPN)	24 V	5 1/ 40 1/	_	Y7NWV	Y7NW	•	•	0	0	IC	Relay,
tat					>	3-wire (PNP)	5 V, 12 V		Y7PWV	Y7PW	•	•	0	0	circuit	PLC								
Solid state auto	` ,			2-wire	1 [12 V	12 V		Y7BWV	Y7BW	•	•	0	0										
	Water resistant (2-color indicator)			2-wire				12 V	12 V	12 V	12 V	12 V	12 V	12 V	12 V	12 V		_	Y7BA**	_	•	0	0	1 - 1
Reed auto switch		Grommet	res	3-wire (NPN equivalent)	_	5 V	_	_	Z 76	•	•	-	_	IC circuit	_									
S G	_	Gioillilet		2-wire	24 V	12 V	100 V	_	Z73	•	•	•	_	_	Relay,									
arı			None	∠-wire	24 V	12 V	100 V or less	_	Z80	•	•	<u> </u>	_	IC circuit	PLĊ									

- ** Water resistant type auto switches can be mounted on the above models, but in such case SMC cannot guarantee water resistance. Consult with SMC regarding water resistant types with the above model numbers.
- * Lead wire length symbols: 0.5 m Nil (Example) Y59A * Solid state auto switches marked with "O" are produced upon receipt of order.

 - 3 m L (Example) Y59AL 5 m Z (Example) Y59AZ
- Since there are other applicable auto switches than listed, refer to page 843 for details.
- For details about auto switches with pre-wired connector, refer to pages 1358 and 1359.
- · Auto switches are shipped together (not assembled).

Symbol Rubber bumper



Made to Order: Individual Specifications (For details, refer to page 844.)

			-	-	•	
Symbol		Specificat	ions	S		
-X593	Without plate					

Made to Order Specifications

Click here for details

Symbol	Specifications					
-XB6	Heat resistant cylinder (-10 to 150°C)					
-XB9	ow speed cylinder (10 to 50 mm/s)					
-XB11	Long stroke type					
-XB13	Low speed cylinder (5 to 50 mm/s)					
-XB19	High speed specification					
-XC22	Fluororubber seals					
-XC85	Grease for food processing equipment					

Moisture Control Tube IDK Series

Weight

When operating an actuator with a small diameter and a short stroke at a high frequency, the dew condensation (water droplet) may occur inside the piping depending on the conditions. Simply connecting the moisture control tube to the actuator will prevent dew condensation from occurring. For details, refer to the Web Catalog.

Specifications

Bore size (mm)	6	10	15	20	25	32		
Fluid	Air (Non-lube)							
Proof pressure	1.05 MPa							
Maximum operating pressure	0.7 MPa							
Minimum operating pressure	0.15 MPa	0.15 MPa 0.1 MPa 0.05 MPa						
Ambient and fluid temperature	-10 to 60°C (No freezing)							
Piston speed	30 to 300 mm/s 30 to 800 mm/s 30 to 700 mm/s 30 to 600 mm/s							
Cushion			Rubber	bumper				
Stroke adjustable range	C) to -5 mm	compared	to the star	ndard strok	е		
Port size	M5 x 0.8 Rc 1/8							
Bearing type	Slide bearing, Ball bushing bearing (Same dimensions for both)							
Allowable kinetic energy	0.0023 J	0.064 J	0.095 J	0.17 J	0.27 J	0.32 J		

Standard Stroke

		(mm)
Model	Standard stroke	Long stroke
CXS□6	10, 20, 30, 40, 50	60, 70, 75, 80, 90, 100
CXS□10	10, 15, 20, 25, 30, 35, 40, 45, 50, 60, 70, 75	80, 90, 100, 110, 120, 125, 150
CXS□15		110, 120, 125, 150
CXS□20	10, 15, 20, 25, 30, 35, 40, 45, 50,	
CXS□25	60, 70, 75, 80, 90, 100	110, 120, 125, 150, 175, 200
CXS□32		

^{*} Refer to "Made to Order Specifications" for stroke which exceeds the standard stroke length. Non-standard strokes for a size ø6 cylinder are available as a special order.

Theoretical Output

										(N
Rod size	Operating		Operating pressure (MPa)							
(mm)	direction	(mm ²)	0.1	0.15	0.2	0.3	0.4	0.5	0.6	0.7
	OUT	56	_	8.4	11.2	16.8	22.4	28.0	33.6	39.2
4	IN	31	_	4.6	6.2	9.3	12.4	15.5	18.6	21.7
,	OUT	157	15.7	_	31.4	47.1	62.8	78.5	94.2	110
6	IN	100	10.0	_	20.0	30.0	40.0	50.0	60.0	70.0
8	OUT	353	35.3	_	70.6	106	141	177	212	247
	IN	252	25.2	_	50.4	75.6	101	126	151	176
40	OUT	628	62.8	_	126	188	251	314	377	440
10	IN	471	47.1	_	94.2	141	188	236	283	330
10	OUT	982	98.2	_	196	295	393	491	589	687
12	IN	756	75.6	_	151	227	302	378	454	529
10	OUT	1608	161	_	322	482	643	804	965	1126
16	IN	1206	121	_	241	362	482	603	724	844
	(mm) 4 6	(mm) direction 4 OUT IN 6 IN 8 OUT IN 10 OUT IN 10 IN 112 IN 16 OUT 16	4 OUT 56 IN 31 6 OUT 157 IN 100 8 IN 252 10 OUT 628 10 IN 471 12 IN 756 OUT 1608	(mm) direction (mm²) 0.1 4 OUT 56 — IN 31 — 6 IN 157 15.7 IN 100 10.0 8 OUT 353 35.3 IN 252 25.2 OUT 628 62.8 IN 471 471 OUT 982 98.2 IN 756 75.6 IN 756 75.6 OUT 1608 161	(mm) direction (mm²) 0.1 0.15 4 OUT 56 — 8.4 IN 31 — 4.6 OUT 157 15.7 — IN 100 10.0 — OUT 353 35.3 — IN 252 25.2 — OUT 628 62.8 — IN 471 47.1 — 12 IN 756 75.6 — 16 OUT 1608 161 —	(mm) direction (mm²) 0.1 0.15 0.2 4 OUT 56 — 8.4 11.2 1N 31 — 4.6 6.2 157 15.7 — 31.4 1N 100 10.0 — 20.0 20 353 35.3 — 70.6 1N 252 25.2 — 50.4 10 0UT 628 62.8 — 126 1N 47.1 47.1 — 94.2 12 IN 756 75.6 — 151 16 OUT 1608 161 — 322	(mm) direction (mm²) 0.1 0.15 0.2 0.3 4 OUT 56 — 8.4 11.2 16.8 6 IN 31 — 4.6 6.2 9.3 6 IN 157 15.7 — 31.4 47.1 8 OUT 353 35.3 — 70.6 106 1N 252 25.2 — 50.4 75.6 10 OUT 628 62.8 — 126 188 1N 471 47.1 — 94.2 141 20 OUT 982 98.2 — 196 295 1N 756 75.6 — 151 227 16 OUT 1608 161 — 322 482	Marchin Marc	(mm) direction (mm²) 0.1 0.15 0.2 0.3 0.4 0.5 4 OUT 56 — 8.4 11.2 16.8 22.4 28.0 6 IN 31 — 4.6 6.2 9.3 12.4 15.5 6 IN 157 15.7 — 31.4 47.1 62.8 78.2	Mathematical Color Mathematical Color


Note) Theoretical output (N) = Pressure (MPa) x Piston area (mm²)

															(kg)
Model		Standard stroke (mm)													
iviouei	10	15	20	25	30	35	40	45	50	60	70	75	80	90	100
CXSM 6	0.081	_	0.095	_	0.108	_	0.122	_	0.135	_	_	_	_	_	_
CXSL 6	0.081	_	0.095	_	0.108	_	0.122	_	0.135	_	_	_	_	_	_
CXSM10	0.15	0.16	0.17	0.18	0.19	0.20	0.21	0.22	0.23	0.25	0.27	0.28	_	_	_
CXSL 10	0.15	0.16	0.17	0.18	0.19	0.20	0.21	0.22	0.23	0.25	0.27	0.28	_	_	_
CXSM15	0.25	0.265	0.28	0.29	0.30	0.315	0.33	0.345	0.36	0.39	0.42	0.435	0.45	0.48	0.51
CXSL 15	0.27	0.285	0.30	0.31	0.32	0.335	0.35	0.365	0.38	0.41	0.44	0.455	0.47	0.50	0.53
CXSM20	0.40	0.42	0.44	0.46	0.48	0.495	0.51	0.53	0.55	0.585	0.62	0.64	0.66	0.70	0.74
CXSL 20	0.43	0.445	0.46	0.48	0.50	0.515	0.53	0.55	0.57	0.605	0.64	0.66	0.68	0.715	0.75
CXSM25	0.61	0.635	0.66	0.69	0.72	0.745	0.77	0.80	0.83	0.89	0.95	0.97	0.995	1.06	1.10
CXSL 25	0.62	0.645	0.67	0.70	0.73	0.755	0.78	0.81	0.84	0.895	0.955	0.98	1.005	1.065	1.11
CXSM32	1.15	1.19	1.23	1.275	1.32	1.36	1.40	1.45	1.49	1.58	1.665	1.71	1.755	1.84	1.93
CXSL 32	1.16	1.205	1.25	1.295	1.34	1.38	1.42	1.465	1.51	1.595	1.68	1.72	1.765	1.855	1.94

Operating Conditions

Non-rotating Accuracy


Non-rotating accuracy θ° at the retracted end and without a load should be less than or equal to the value provided in the table below as a guide.



Bore size (mm)	Ø6 to Ø32		
CXSM (Slide bearing)	+0.1°		
CXSL (Ball bushing bearing)	±0.1°		


CXS□6 to 32 Deflection at the Plate End


An approximate plate-end deflection \boldsymbol{X} without a load is shown in the graph below.



Maximum Load Mass

When the cylinder is mounted as shown in the diagrams below, the maximum load mass W should not exceed the values illustrated in the graph.






Clean Series

There are two types of cylinders, relieving type and vacuum type, available for a clean room environment. The relieving type specification with the double-seal construction of the rod section allows the cylinder to channel exhaust through the relief port directly to the outside of a clean room environment. The vacuum type specification allows for the application of a vacuum on the rod section while forced exhaust of air takes place through the vacuum port to the outside of a clean room environment.

How to Order



Specifications

Bore size (mm)	6	10	15	20	25	32	
Proof pressure	1.05 MPa						
Maximum operating pressure	0.7 MPa						
Minimum operating pressure	0.15 MPa	0.1	МРа	0.05 MPa			
Ambient and fluid temperature		-10	to 60°C	(No free:	zing)		
Piston speed			30 to 40	00 mm/s			
Stroke adjustable range	0 to -5 mm compared to the standard stroke						
Bearing type	Ball bushing bearing						

Refer to the Web Catalog for dimensions.

Series Applicable to Operating Environments that Do Not Accept Copper

- Copper (Cu) and Zinc (Zn)-free 25A- series
- Copper and Fluorine-free----20- series
- * For details, refer to the Web Catalog

Cylinder with Stable Lubrication Function (Lube-retainer)

How to Order

CXS□6



Cylinder with Stable Lubrication Function (Lube-retainer)





Specifications

Bore size (mm)	6	10	15	20	25	32		
Action		Double acting						
Minimum operating pressure	0.2 MPa	0.15	0.15 MPa 0.1 MPa					
Piston speed	50 to 300 mm/s	50 to 800 mm/s	50 to 70	00 mm/s	50 to 60) to 600 mm/s		
Cushion			Rubber bumper					


st Specifications other than the above are the same as the standard model.


Dimensions (Dimensions other than those shown below are the same as the standard model.)





CXS□10 to 32





			(,
Model	K	L	R
CXS□10	4	25	35
CXS□15	3	36	44.5
CXS□20	6	36	50.5
CXS□25	6	36	52
CXS□32	4	40	66

Symbol								SS							
Model Stroke	10	15	20	25	30	35	40	45	50	60	70	75	80	90	100
CXS□10	70	75	80	85	90	95	100	105	110	120	130	135	_	_	_
CXS□15	76	81	86	91	96	101	106	111	116	126	136	141	146	156	166
CXS□20	86	91	96	101	106	111	116	121	126	136	146	151	156	166	176
CXS□25	88	93	98	103	108	113	118	123	128	138	148	153	158	168	178
CXS 32	102	107	112	117	122	127	132	137	142	152	162	167	172	182	192

For details, refer to the **Web Catalog**.


(mm)

(mm)


CXS Series

Construction: Slide Bearing

CXSM6



CXSM10 to 32



Component Parts

<u></u>	Component Parts								
No.	Description	Material	Note						
1	Housing	Aluminum alloy	Hard anodized						
2	Piston rod A	Carbon steel (1)	Hard chrome plated						
3	Piston rod B	Carbon steel (1)	Hard chrome plated						
4	Rod cover	Aluminum bearing alloy							
5	Plate	Aluminum alloy	Anodized						
6	Piston A	Aluminum alloy	Chromated						
7	Piston B	Aluminum alloy	Chromated						
8	Bumper	Urethane							
9	Magnet	_							
10	Bumper bolt	Carbon steel	Nickel plated						
11	Hexagon nut	Carbon steel	Zinc chromated						
12	Hexagon socket head cap screw	Chromium steel	Zinc chromated						
13	Hexagon socket head set screw	Chromium steel	Zinc chromated						
14	Retaining ring	Special steel	Phosphate coating						

Note 1) Stainless steel for CXSM6.

Component Parts

No.	Description	Material	Note					
15	Bumper	Urethane						
16	Plug	Chromium steel	Nickel plated					
17	Piston seal	NBR						
18	Rod seal	NBR						
19	O-ring	NBR						
20	Seal retainer	Aluminum alloy						
21	Port spacer	Aluminum alloy						
22	Steel ball	Special steel	Hard chrome plated					

Replacement Parts/Seal Kit


Bore size (mm)	Kit no.	Contents
6	CXSM6-PS	
10	CXSM10APS	
15	CXSM15-PS	Set of nos. above
20	CXSM20-PS	17, 18 and 19
25	CXSM25-PS	
32	CXSM32-PS	

^{*} Seal kit includes ①, ® and ⑨. Order the seal kit, based on each bore size.
* Since the seal kit does not include a grease pack, order it separately.


Grease pack part no.: GR-S-010 (10 g)

Construction: Ball Bushing Bearing

CXSL6



CXSL10 to 32



Component Parts: Standard Piping

No.	Description	Material	Note
1	Housing	Aluminum alloy	Hard anodized
2	Piston rod A	Special steel	Hard chrome plated
3	Piston rod B	Special steel	Hard chrome plated
4	Rod cover	Aluminum bearing alloy	
5	Plate	Aluminum alloy	Anodized
6	Piston A	Aluminum alloy	Chromated
7	Piston B	Aluminum alloy	Chromated
8	Bumper	Urethane	
9	Magnet	_	
10	Bumper bolt	Carbon steel	Nickel plated
11	Hexagon nut	Carbon steel	Zinc chromated
12	Hexagon socket head cap screw	Chromium steel	Zinc chromated
13	Hexagon socket head set screw	Chromium steel	Zinc chromated
14	Retaining ring	Special steel	Phosphate coating
15	Bumper holder	Synthetic resin	

Component Parts

00.	iiponent i uito		
No.	Description	Material	Note
16	Ball bushing	_	
17	Bearing spacer	Synthetic resin(1)	
18	Bumper	Urethane	
19	Plug	Chromium steel	Nickel plated
20	Piston seal	NBR	
21	Rod seal	NBR	
22	O-ring	NBR	
23	Seal retainer	Aluminum alloy	
24	Port spacer	Aluminum alloy	
25	Steel ball	Special steel	Hard chrome plated
	45. A1	(0)(0) 0	

Note 1) Aluminum bearing alloy for CXSL6.

Rep	lacement	Parts/9	Seal Kit
-----	----------	---------	----------


Bore size (mm)	Kit no.	Contents
6	CXSL6-PS	
10	CXSL10BPS	
15	CXSL15APS	Set of nos. above
20	CXSL20APS	20, 21 and 22
25	CXSL25APS	
32	CXSL32APS	

^{*} Seal kit includes @, @ and @. Order the seal kit, based on each bore size.

^{*} Since the seal kit does not include a grease pack, order it separately. Grease pack part no.: GR-S-010 (10 g)


CXS Series

Dimensions: Ø6



					(mm)
Model	Stroke	Z	S	SS	ZZ
CXS□6-10	10	15	23	55	68.5
CXS□6-20	20	20	33	65	78.5
CXS□6-30	30	25	43	75	88.5
CXS□6-40	40	30	53	85	98.5
CXS□6-50	50	35	63	95	108.5

Dimensions: Ø10, Ø15



																				(mm)
Model	Α	В	С	D	Е	F	G	Н	Τ	J	L	M	N	NN	Р	Q	QQ	R	U	V
CXS□10	46	17	44	15	7.5	2 x M4 x 0.7	35	20	4	8	20	12 x a6 5 counter-	2 x M3 x 0.5 thread depth 5	ø6	33.6	8.5	7		2 x M4 x 0.7 thread depth 7	4 x M3 x 0.5 thread depth 4.5
CXS□15	58	20	56	18	9	2 x M5 x 0.8	45	25	5	10	30	12 x ø8 counter-	2 x M4 x 0.7 thread depth 6	ø8	48	10	10	38.5	2 x M5 x 0.8 thread depth 8	4 x M4 x 0.7 thread depth 5


Dimensions by Stroke

Symbo Symbo			SS															Z										ΖZ							
Model	10	15	20	25	30	35	40	45	50	60	70	75	80	90	100	10, 15 20, 25	30, 35, 40, 45, 50	60, 70, 75	80	90, 100	10	15	20	25	30	35	40	45	50	60	70	75	80	90	100
CXS□10	65	70	75	80	85	90	95	100	105	115	125	130	-	-	-	30	40	50	-	-	82	87	92	97	102	107	112	117	122	132	142	147	-	-	[-
CXS□15	70	75	80	85	90	95	100	105	110	120	130	135	140	150	160	25	35	45	45	55	89	94	99	104	109	114	119	124	129	139	149	154	159	169	179

SMC

CXS Series

Dimensions: Ø20, Ø25, Ø32



																(mm)
Model	Α	В	С	D	Е	F	G	н	1	J	K	L	М	N	NN	Р
CXS□20	64	25	62	23	11.5	2 x M5 x 0.8	50	28	6	12	12	30	2 x ø5.5 through 2 x ø9.5 counterbore depth 5.3	2 x M4 x 0.7 thread depth 6	ø10	53
CXS□25	80	30	78	28	14	2 x M6 x 1.0	60	35	6	12	12	30		2 x M5 x 0.8 thread depth 7.5	ø12	64
CXS□32	98	38	96	36	18	2 x M6 x 1.0	75	44	8	16	14	30		2 x M5 x 0.8 thread depth 8	ø16	76


Model	Q	QQ	R	T	TT	U	UU	v	w
CXS□20	7 75	12.5	45	9.5	6.5	8	4 x M5 x 0.8	8 x M4 x 0.7	2 x M6 x 1.0
CA3⊟20	7.75	12.5	7	5.	0.5	۰	thread depth 4.5	thread depth 5.5	thread depth 10
CXS□25	8.5	15	46	13	9	9	4 x Rc 1/8	8 x M5 x 0.8	2 x M8 x 1.25
CA3⊟25	0.5	13	40	2	9	9	thread depth 6.5	thread depth 7.5	thread depth 12
CXS□32	9	19	56	20	11.5	10	4 x Rc 1/8	8 x M5 x 0.8	2 x M8 x 1.25
UN3∟32		19	50	20	11.3	'0	thread depth 6.5	thread depth 7.5	thread depth 12


Dimensions by Stroke

Symbol			SS															ZZ															
Model	10	15	20	25	30	35	40	45	50	60	70	75	80	90	100	10, 15, 20, 25	30, 35, 40, 45, 50	60, 70, 75, 80, 90, 100	10	15	20	25	30	35	40	45	50	60	70	75	80	90	100
CXS□20	80	85	90	95	100	105	110	115	120	130	140	145	150	160	170	30	40	60	104	109	114	119	124	129	134	139	144	154	164	169	174	184	194
CXS□25	82	87	92	97	102	107	112	117	122	132	142	147	152	162	172	30	40	60	106	111	116	121	126	131	136	141	146	156	166	171	176	186	196
CXS□32	92	97	102	107	112	117	122	127	132	142	152	157	162	172	182	40	50	70	122	127	132	137	142	147	152	157	162	172	182	187	192	202	212

CXS Series **Auto Switch Mounting**

Auto Switch Proper Mounting Position (Detection at Stroke End)





Bore size (mm)	A B		D-Z7/Z8, D-Y5□, D	D-Y6□, D-Y7□V	D-Y7□V /V	D-Y7BA		
(111111)			С	D	С	D	С	D
6	15.5	4.5	11.5 (10)	0.5 (-1)	13	2	5.5	-5.5
10	22.5	7.5	18.5 (17)	3.5 (2)	20	5	12.5	-2.5
15	30.5	4.5	26.5 (25)	0.5 (-1)	28	2	20.5	-5.5
20	38	7	34 (32.5)	3 (1.5)	36	4.5	28	ا
25	38	9	34 (32.5)	5 (3.5)	36	6.5	28	-1
32	48	9	44 (42.5)	5 (3.5)	46	6.5	38	-1
Note 1) Negative	efigures	in the tab	ole D indicate	how much th	e load wir	es protru	de from	the cylin-

der body

Note 3) Adjust the auto switch after confirming the operating conditions in the actual setting.

Note 2) (): Denotes the dimensions of D-Z73.


Operating Range

	Bore size (mm)									
Auto switch model	6	10	15	20	25	32				
D-Z7□/Z80	9	7	9	9	9	11				
D-Y59□, D-Y69□ D-Y7P/Y7PV D-Y7□W/Y7□WV D-Y7BA	3	3	3.5	3.5	4	4.5				

* Since this is a guideline including hysteresis, not meant to be guaranteed.

(assuming approximately ±30% dispersion.) There may be the case it will vary substantially depending on an ambient environment

Dimensions for Mounting of Auto Switch



A Dimension

Auto switch model	Bore size (mm)								
Auto switch model	6	10	15	20	25	32			
D-Y59A/Y7P/Y59B									
D-Y69A/Y7PV/Y69B									
D-Y7NWV/Y7PWV/Y7BWV	0.7 0.2			.2					
D-Y7NW/Y7PW/Y7BW									
D-Y7BA									
D-Z7, D-Z8	1.2 0.7								

Auto Switch Mounting

When mounting and securing auto switches, they should be inserted into the cylinder's auto switch mounting rail from the direction shown in the drawing

After setting in the mounting position, use a flat head watchmaker's screwdriver to tighten the auto switch mounting screw that is included.

Note) When tightening an auto switch mounting screw, use a watchmakers' screwdriver with a handle of approximately 5 to 6 mm in diameter. Also, tighten with a torque of about 0.05 to 0.1 N·m. As a guide, turn about 90° past the point at which tightening can first be felt




Auto switch mounting screw

(Included with auto switch)

M2.5 x 4 L

1. Avoid proximity to magnetic objects

When magnetic substances such as iron (including flange brackets) are in close proximity to a cylinder body with an auto switch, be sure to provide a clearance between the magnetic substance and the cylinder body as shown in the drawing below. If the clearance is less than the values noted in the table below, the auto switch may not function properly.



Bore size	X (mm)
ø 6	0
ø10	0
ø15	10
ø 20	10
ø 25	0
ø 32	0

Other than the applicable auto switches listed in "How to Order", the following auto switches can be mounted. For detailed specifications, refer to pages 1289 to 1383.

* Normally closed (NC = b contact), solid state auto switch (D-Y7G/Y7H type) are also available. For details, refer to page 1310.

CXS Series


Made to Order: Individual Specifications

Please contact SMC for detailed dimensions, specifications and lead times.




1 Without Plate





This specification is for the cylinder without a plate. This cylinder is suitable for mounting your own plate. Please note that the rod end dimensions of this cylinder are different from those of the standard cylinder.



																				(mm)
Model	а	b	С	d	е	f	g	h	i	j	k	L ₁	m	n	0	р	q	r	s	t
CXS□ 6	16 ^{±0.1}	ø4 +0.013 +0.001	M3 x 0.5	ø4	ø3.5	1	3	ø5.5	ø6 _0.2	2.75	2.8 +0.2	3.5 +0.1	0.5 +0.2	3.5 ^{-0.05} _{-0.15}	M2.5 x 0.45		4.5	3.5	4.75	C0.5
CXS□10	20 ±0.1	ø6 +0.016 +0.001	M5 x 0.8	ø6	ø5.5	1.25	4.5	ø6.5	ø3.5 _{-0.2}	4	3.2 +0.2	5 +0.1	1 +0.2	5 -0.05 -0.15	M3 x 0.5		8	5	6.5	C0.5
CXS□15	25 ^{±0.1}	Ø8 +0.016 +0.001	M6 x 1.0	ø8	ø7.5	2	5	ø9.5	ø5.5 _{-0.2}	5	5.2 +0.3	6 +0.2	1.5 +0.2	6 -0.05 -0.15	M5 x 0.8	3	8	7	8	C0.5
CXS□20	28 ^{±0.1}	ø10 +0.016 +0.001	M8 x 1.25	ø10	ø9.5	2	7	ø11	ø6.6 _{-0.2}	6	6.2 +0.3	8 +0.2	2 +0.2	8 -0.05 -0.15	M6 x 1.0	3	10	8	9.5	C0.5
CXS□25	35 ^{±0.1}	ø12 +0.019 +0.001	M8 x 1.25	ø12	ø11.5	2	7	ø11	ø6.6 _{_0.2}	6	6.2 +0.3	10 +0.2	2 +0.2	10 -0.05 -0.15	M6 x 1.0		12	8.5	9.5	C0.7
CXS□32	44 ±0.1	ø16 +0.019 +0.001	M10 x 1.5	ø16	ø15.5	3.5	8	ø14	ø9 _0.2	8	8.2 +0.4	13 +0.2	2 +0.2	13 -0.05 -0.15	M8 x 1.25		12.5	11	13.5	C0.7

Note 1) Unless indicated otherwise, the dimensional tolerance conforms to the ordinary dimensional difference (matching) per JIS B 0405.

Note 2) Pistorn rod A and B must be extended in order to install a plate. Apply presure (0.2 MPa or more) from the supply port of the extended end when installing a plate.

To secure the plate to the rods, attach it first to piston rod B, and then to piston rod A. Make sure to apply Loctile to the threaded portion.

After anchoring the plate, operate the cylinder to check for proper operation (e.g., the cylinder operates smoothly when moved by hand or at least operates properly at the minimum operating pressure).



CXS Series Specific Product Precautions

Be sure to read this before handling the products. Refer to page 8 for safety instructions and pages 9 to 18 for actuator and auto switch precautions.

Mounting

 Make sure that the surface on which the cylinder is to be mounted is flat (reference value for flatness: 0.05 or less).

Dual rod cylinders can be mounted from 3 directions, however, make sure that the surface on which the cylinder is to be mounted is flat (reference value for flatness: 0.05 or less). Otherwise, the accuracy of the piston rod operation is not achieved, and malfunctioning can occur.

Piston rod must be retracted when mounting the cylinder.

Scratches or gouges in the piston rod may lead to damaged bearings and seals and cause malfunctions or air leakage.

Piping

⚠ Caution

 Plug the appropriate supply port(s) according to the operating conditions.

Dual-rod cylinders have 2 supply ports for each operating direction (3 supply ports for ø6 only). Plug the appropriate supply port according to the operating conditions. When changing the port position, use the removed plug or a new plug. If reusing the removed plug, apply sealant, etc., before reassembly. If using a new M5 plug, apply a thin layer of grease all the way around the male thread before use. In addition, clear any foreign matter adhered to the port the plug was removed from before piping.

After reassembly, be sure to check for air leakage before operating the product.

Plug part no.: (ø6)CXS10-08-28747B

(ø10 to ø20)CXS20-08-28749A

(ø25 to ø32)CYP025-08B29449A(Rc 1/8)

CXS25-08-A3025B(NPT 1/8) CXS25-08-A3911A(G 1/8)

Stroke Adjustment

1. After adjusting the stroke, make sure to tighten the hexagon nut to prevent it from loosening.

Dual rod cylinders have a bolt to adjust 0 to -5 mm strokes on the retracted end (IN).

Loosen the hexagon nut to adjust the stroke; however, make sure to tighten the hexagon nut after making an adjustment.

Never operate a cylinder with its bumper bolt removed. Also, do not attempt to tighten the bumper bolt without using a nut.

If the bumper bolt is removed, the piston hits the head cover causing damage to the cylinder. Therefore, do not use a cylinder without a bumper bolt.

Furthermore, if the bumper bolt is tightened without a nut, the piston seal is caught in the leveled part, damaging the seal.

Stroke Adjustment

⚠ Caution

3. A bumper at the end of the bumper bolt is replaceable. In case a missing bumper, or a bumper has a permanent settling, use following part numbers for ordering.

Bore size (mm)	6, 10, 15	20, 25	32
Part no.	CXS10-34A 28747	CXS20-34A 28749	CXS32-34A 28751
Qtv.		1	

Disassembly and Maintenance

⚠ Caution

1. Never use a cylinder with its plate removed.

When removing the hexagon socket head cap screw on the end plate, the piston rod must be secured to prevent from rotating. However, if the sliding parts of the piston rod are scratched and gouged, a malfunction may occur. If the plate is not required for your application, use the cylinder that does not come with a plate, available through made-to-order (-X593) on page 844.

When disassembling and reassembling the cylinder, please contact SMC or refer to the separate operation manual.

⚠ Warning

 Take precautions when your hands are near the plate and housing.

Take sufficient care to avoid getting your hands or fingers caught when the cylinder is operated.

Operating Environment

- Do not operate the cylinder in a pressurized environment.
 The pressurized air may flow inside the cylinder due to its construction.
- Do not use as a stopper. This may cause malfunction. When using as a stopper, select a stopper cylinder (RS series) or a compact guide cylinder (MGP series).

Speed Adjustment


⚠ Caution

A sudden extension may occur with CXS□6.

CXS\(\sigma\)6 has a low internal volume and sudden extension/erratic movement may occur particularly when it is used at low speed. This sudden extension can be mitigated by combining the use of meter-in and meter-out speed controllers.



Dual Rod Cylinder With Air Cushion CXS Series



Applicable Auto Switches/Refer to pages 1289 to 1383 for further information on auto switches.

			light			Load volta	age			Lead wire ler	ngth (m) *									
Type	Special function	Electrical entry	dicator	Wiring (Output)		DC AC		Auto switch model		0.5	3	5	Pre-wired	Applic	able load						
	·	entry	ligi	(Output)		DC	AC	Perpendicular	In-line	(Nil)	(L)	(Z)	connector								
등				3-wire (NPN)		5 V. 12 V		Y69A	Y59A	•	•	0	0	IC							
Swit	auto switch			3-wire (PNP)		5 V, 12 V		Y7PV	Y7P	•	•	0	0	circuit							
\$				2-wire		12 V	_	Y69B	Y59B	•	•	0	0	_	Delevi						
an	(2-color indicator)	Grommet	es	3-wire (NPN)	24 V	5 V, 12 V		Y7NWV	Y7NW	•	•	0	0	IC	Relay, PLC						
state			~	3-wire (PNP)				Y7PWV	Y7PW	•	•	0	0	circuit	PLC						
Solids				0				Y7BWV	Y7BW	•	•	0	0								
	Water resistant (2-color indicator)			2-wire			v		Y7BA**	_	•	0	0								
Reed auto switch	,	0	0	0	0	0	0		se,	3-wire (NPN equivalent)	_	5 V	_	1	Z 76	•	•	_	_	IC circuit	_
Bee to s	_	Grommet		0	24 V	12 V	100 V	_	Z73	•	•	•	_	_	Relay,						
ari			None	2-wire 24 \	24 V	12 V	100 V or less	_	Z80	•	•	_	_	IC circuit	PLC						

- ** Water resistant type auto switches can be mounted on the above models, but in such case SMC cannot guarantee water resistance.

 Consult with SMC regarding water resistant types with the above model numbers.
- * Lead wire length symbols: 0.5 m Nil (Example) Y59A
 - 3 m L (Example) Y59AL
 - 5 m Z (Example) Y59AZ
- * Solid state auto switches marked with "O" are produced upon receipt of order.
- Since there are other applicable auto switches than listed, refer to page 843 for details.
 For details about auto switches with pre-wired connector, refer to pages 1358 and 1359.
- Auto switches are shipped together (not assembled).

Moisture Control Tube IDK Series

When operating an actuator with a small diameter and a short stroke at a high frequency, the dew condensation (water droplet) may occur inside the piping depending on the conditions.

Simply connecting the moisture control tube to the actuator will prevent dew condensation from occurring. For details, refer to the Web Catalog.





⚠ Precautions

I Be sure to read this before handling I the products.

Refer to page 8 for safety instructions and pages 9 to 18 for actuator and auto switch precautions.

Selection

- Operate the cylinder until the stroke end.
 If the stroke is restricted by the external
 stopper and clamp workpiece, effective
 cushioning and noise reduction will not be
 achieved.
- Adjust the cushion needles to absorb the kinetic energy during the cushion stroke so that excessive kinitic energy does not remain when the piston reaches the stroke end.

If the piston reaches the stroke end with excessive kinetic energy remaining (more than the values given in table (1) below) due to an improper adjustment, excessive impact will occur, causing damage to machinery.

Table (1) Allowable Value at Piston Impact

Bore size (mm)	20	25	32
Piston speed (mm/s)	50 to 700	50 to 600	50 to 600
Kinetic energy (J)	0.17	0.27	0.32

Cushion Needle Adjustment

⚠ Caution

 Keep the adjusting range for the cushion needle between the fully closed position and the rotations shown below.

Bore size (mm)	20	25	32
Rotations	2.5 rotatio	ns or less	3 rotations or less

Use a 3 mm flat head watchmakers screwdriver to adjust the cushion needles to the fully closed position, as this will cause damage to the seals. The adjusting range for the cushion needles must be between the fully closed position and the open position ranges indicated in the table above. A retaining mechanism prevents the cushion needles from slipping out; however, they may spring out during operation if they are rotated beyond the ranges shown above.

Precautions for selection standard, mounting, piping, and operating environment are same as for the standard series.

Specifications

Bore size (mm)	20	25	32						
Fluid		Air (Non-lube)							
Proof pressure		1.05 MPa							
Maximum operating pressure	re 0.7 MPa								
Minimum operating pressure	0.1 MPa								
Ambient and fluid temperature	-1	0 to 60°C (No freezing	ıg)						
Piston speed		50 to 1000 mm/s							
Port size	M5 x 0.8 Rc 1/8 (NPT 1/8, G 1/8)								
Bearing type	Slide bearing, Ball bu	Slide bearing, Ball bushing bearing (Same dimensions for both)							
Cushion	A	ir cushion (Both ends	s)						

Cushion mechanism

	Bore size (mm)	Effective cushion length (mm)	Absorbable kinetic energy (J)					
	20	5.9	0.40					
	25	5.7	0.75					
[32 5.6		1.0					

^{*} Maximum load mass is the same as the standard type.

Standard Stroke

 Model
 Standard stroke

 CXS□20
 20, 25, 30, 35, 40, 45, 50, 60, 70, 75, 80, 90, 100

 CXS□25
 25, 30, 35, 40, 45, 50, 60, 70, 75, 80, 90, 100

 CXS□32
 25, 30, 35, 40, 45, 50, 60, 70, 75, 80, 90, 100

Theoretical Output

										(N)	
Model	Rod size	Operating	Piston area	Operating pressure (MPa)							
Model	(mm)	direction	(mm ²)	0.1	0.2	0.3	0.4	0.5	0.6	0.7	
CXS□20	10	OUT	628	62.8	126	188	251	314	377	440	
CASUZU	10	IN	471	47.1	94.2	141	188	236	283	330	
CXS□25	12	OUT	982	98.2	196	295	393	491	589	687	
CA3L23	12	IN	756	75.6	151	227	302	378	454	529	
CXS□32	10	OUT	1608	161	322	482	643	804	965	1126	
CASU32	16	IN	1206	121	241	362	482	603	724	844	

Note) Theoretical output (N) = Pressure (MPa) x Piston area (mm²)

Weight


	(KÇ														
Model		Standard stroke (mm)													
iviodei	20	25	30	35	40	45	50	60	70	75	80	90	100		
CXSM20-□A	0.50	0.52	0.54	0.56	0.58	0.60	0.62	0.66	0.70	0.715	0.735	0.755	0.815		
CXSL20-□A	0.52	0.54	0.56	0.58	0.60	0.62	0.64	0.68	0.72	0.735	0.755	0.775	0.835		
CXSM25-□A	_	0.78	0.80	0.82	0.84	0.86	0.88	0.92	0.96	0.98	1.00	1.04	1.08		
CXSL25-□A	_	0.79	0.81	0.83	0.85	0.87	0.89	0.93	0.97	0.99	1.01	1.05	1.09		
CXSM32-□A	_	1.48	1.53	1.575	1.62	1.67	1.72	1.82	1.92	1.96	2.06	2.14	2.20		
CXSL32-□A	_	1.51	1.55	1.60	1.64	1.69	1.74	1.84	1.94	1.98	2.08	2.16	2.22		



CXS Series

Construction

CXSM/With air cushion





Close-up of A


Component Parts: CXSM

No.	Description	Material	Note
1	Housing	Aluminum alloy	Hard anodized
2	Piston rod A	Carbon steel	Hard chrome plated
3	Piston rod B	Carbon steel	Hard chrome plated
4	Rod cover	Aluminum bearing alloy	
5	Plate	Aluminum alloy	Anodized
6	Piston A	Aluminum alloy	Chromated
7	Piston B	Aluminum alloy	Chromated
8	Bumper B	Urethane	
9	Magnet	_	
10	Bumper bolt	Carbon steel	Nickel plated
11	Hexagon nut	Carbon steel	Zinc chromated
12	Bumper	Urethane	
13	Hexagon socket head cap screw	Chromium steel	Zinc chromated
14	Hexagon socket head set screw	Chromium steel	Zinc chromated
15	Retaining ring	Special steel	Phosphate coated
16	Steel ball	Special steel	Nickel plated
17	Piston seal	NBR	
18	Rod seal	NBR	
19	O-ring	NBR	
20	O-ring	NBR	
21	Cushion needle	Stainless steel	
22	Check seal retainer	Copper alloy	-
23	Check seal	NBR	
	Mandle manical	NBR	
24	Needle gasket	I NOW	

Replacement Parts/Seal Kit

Bore size (mm)	Kit no.	Contents
20	CXS□20A-PS	CYCM: C-+ -4 @ @4 @
25	CXS□25A-PS	CXSM: Set of nos. (7), (8) and (9) CXSL: Set of nos. (19, 20) and (21)
32	CXS□32A-PS	OXOL: Oct of flos. (9, 69 and 6)

CXSL/With air cushion






Close-up of A

Component Parts: CXSL

No.	Description	Material	Note
1	Housing	Aluminum alloy	Hard anodized
2	Piston rod A	Special steel	Hard chrome plated
3	Piston rod B	Special steel	Hard chrome plated
4	Bearing spacer	Aluminum alloy	
5	Ball bushing	_	
6	Bumper holder	Aluminum alloy	
7	Plate	Aluminum alloy	Anodized
8	Piston A	Aluminum alloy	Chromated
9	Piston B	Aluminum alloy	Chromated
10	Bumper B	Urethane	
11	Magnet	_	
12	Bumper bolt	Carbon steel	Nickel plated
13	Hexagon nut	Carbon steel	Zinc chromated
14	Bumper	Urethane	
15	Hexagon socket head cap screw	Chromium steel	Zinc chromated
16	Hexagon socket head set screw	Chromium steel	Zinc chromated
17	Retaining ring	Special steel	Phosphate coated
18	Steel ball	Special steel	Nickel plated
19	Piston seal	NBR	
20	Rod seal	NBR	
21	O-ring	NBR	
22	O-ring	NBR	
23	Cushion needle	Stainless steel	
24	Check seal retainer	Copper alloy	
25	Check seal	NBR	
26	Needle gasket	NBR	
27	Check gasket	NBR	


* Seal kit includes ①, ① and ①. Order the seal kit, based on each bore size. * Since the seal kit does not include a grease pack, order it separately. Grease pack part no.: GR-S-010 (10 g)


Dimensions: Ø20




CXS Series

Dimensions: Ø25








				(111111)
Part no.	S	SS	ZZ	Z
CXS□25-25A	25	100	124	30
CXS□25-30A	30	105	129	
CXS□25-35A	35	110	134	
CXS□25-40A	40	115	139	40
CXS□25-45A	45	120	144	
CXS□25-50A	50	125	149	
CXS□25-60A	60	135	159	
CXS□25-70A	70	145	169	
CXS□25-75A	75	150	174	60
CXS□25-80A	80	155	179	60
CXS□25-90A	90	165	189	
CXS□25-100A	100	175	199	

Note) For port threads TN and TF, only the piping port type varies.



Dimensions: Ø32




				(mm)
Part no.	S	SS	ZZ	Z
CXS□32-25A	25	112	142	40
CXS□32-30A	30	117	147	
CXS□32-35A	35	122	152	
CXS□32-40A	40	127	157	50
CXS□32-45A	45	132	162	
CXS□32-50A	50	137	167	
CXS□32-60A	60	147	177	
CXS□32-70A	70	157	187	
CXS□32-75A	75	162	192	70
CXS□32-80A	80	167	197	70
CXS□32-90A	90	177	207	
CXS□32-100A	100	187	217	

Note) For port threads TN and TF, only the piping port type varies.


CXS Series Auto Switch Mounting

Auto Switch Proper Mounting Position (Detection at Stroke End)

Electrical entry direction: Inward



Electrical entry direction: Outward




Bore size (mm)	Α	В	D-Z7/Z8, D-Y5□, I	D-Y7□W D-Y7□	D-Y6□, D-Y7□\	D-Y7□V VV	D-Y7BA		
			С	D	С	D	С	D	
20	40.5	6.5	36.5(35)	2.5(1)	38.5	4	30.5	-3.5	
25	42	8	38(36.5)	4(2.5)	40	5.5	32	-2	
32	52.5	9.5	48.5(47)	5.5(4)	50.5	7	42.5	-0.5	

Note) Adjust the auto switch after confirming the operating conditions in the actual setting.

As for auto switch mounting dimensions, auto switch mounting method and its operating range, those are the same as basic type. Refer to page 843.

Dual Rod CylinderWith End Lock for Retraction Side CXS Series Ø6, Ø10, Ø15, Ø20, Ø25, Ø32

How to Order



Applicable Auto Switches/Refer to pages 1289 to 1383 for further information on auto switches.

		Electrical	ight			Load volta	age	Auto quit	ah maadal	Lead wire ler	ngth ((m) *				
Type	Special function	Electrical entry	ndicator light	Wiring (Output)		DC	AC	Auto switch model		0.5	3 5		Pre-wired Applie		cable load	
	•	Citaly	Indic	(Output)		DC AC		Perpendicular In-line		(Nil)	(L)	(Z)	COTTRECTOR			
5				3-wire (NPN)		5 V. 12 V		Y69A	Y59A	•	•	0	0	IC		
switch	_			3-wire (PNP)		J V, 12 V		Y7PV	Y7P	•	•	0	0	circuit		
anto				2-wire		12 V	_	Y69B	Y59B	•	•	0	0	_	Delen	
	Diagnostic indication	Grommet	es 8	3-wire (NPN)	24 V	5 V, 12 V		Y7NWV	Y7NW	•	•	0	0	O	Relay, PLC	
tat	(2-color indication		>	3-wire (PNP)	-			Y7PWV	Y7PW	•	•	0	0	circuit	PLC	
Solid state	(2-color indicator)			2-wire		40.1/		Y7BWV	Y7BW	•	•	0	0			
	Water resistant (2-color indicator)			2-wire		12 V		_	Y7BA**	_	•	0	0	_		
Reed auto switch			Yes	3-wire (NPN equivalent)	_	5 V	_	_	Z 76	•	•	-	_	IC circuit	_	
e s	_	Grommet	Ĺ	0	24 V	12 V	100 V	_	Z73	•	•	•	_		Relay,	
atto			None	2-wire	24 V		100 V or less	_	Z80	•	•	_	_	IC circuit	PLC	

- ** Water resistant type auto switches can be mounted on the above models, but in such case SMC cannot guarantee water resistance. Consult with SMC regarding water resistant types with the above model numbers.
- * Lead wire length symbols: 0.5 m Nil (Example) Y59A 3 m L (Example) Y59AL * Solid state auto switches marked with "O" are produced upon receipt of order. 5 m Z (Example) Y59AZ
- Since there are other applicable auto switches than listed, refer to page 843 for details.
- For details about auto switches with pre-wired connector, refer to pages 1358 and 1359.
 Auto switches are shipped together (not assembled).





Symbol Rubber bumper

Specifications

Bore size (mm)	6	10	15	20	25	32			
Fluid			Air (No	n-lube)					
Proof pressure			1.05	MPa					
Maximum operating pressure			0.7 N	/IPa					
Minimum operating pressure	0.3 MPa								
Ambient and fluid temperature	-10 to 60°C (No freezing)								
Piston speed	30 to 300mm/s	30 to 800mm/s	30 to 7	00mm/s	30 to 6	00mm/s			
Cushion		Bump	er is standa	ard on both	ends				
Port size	M5 x 0.8 Rc 1/8								
Bearing type	Slide bear	Slide bearing, Ball bushing bearing (Same dimensions for both)							
Allowable kinetic energy	0.0023 J	0.064 J	0.095 J	0.17 J	0.27 J	0.32 J			

Lock Specifications

Lock specifications	Rear end lock									
Bore size (mm)	6	10	15	20	25	32				
Maximum holding force (N)	14.7	39.2	98.1	157	235	382				
Manual release	Non-lock type									

^{*} Maximum load mass is the same as the standard type.

Standard Stroke

	(mm)
Model	Standard stroke
CXS□ 6	
CXS□10	10, 20, 30, 40, 50
CXS□15	
CXS□20	
CXS□25	10, 20, 30, 40, 50, 75, 100
CXS□32	

^{*} Strokes which exceed the standard stroke length will be available as special goods.

Theoretical Output

											(N)		
Model	Rod size	Operating	Piston area	Operating pressure (MPa)									
iviodei	(mm)	direction	(mm ²)	0.1	0.15	0.2	0.3	0.4	0.5	0.6	0.7		
CXS□ 6	4	OUT	56	_	8.4	11.2	16.8	22.4	28.0	33.6	39.2		
	4	IN	31	I	4.6	6.2	9.3	12.4	15.5	18.6	21.7		
CXS□10	6	OUT	157	15.7	_	31.4	47.1	62.8	78.5	94.2	110		
CXSLIU	0	IN	100	10.0	_	20.0	30.0	40.0	50.0	60.0	70.0		
CXS□15	8	OUT	353	35.3	_	70.6	106	141	177	212	247		
CASLIS	0	IN	252	25.2	_	50.4	75.6	101	126	151	176		
CXS□20	10	OUT	628	62.8	_	126	188	251	314	377	440		
CX5U20	10	IN	471	47.1	_	94.2	141	188	236	283	330		
CXS□25	12	OUT	982	98.2	_	196	295	393	491	589	687		
CXSU25	12	IN	756	75.6	_	151	227	302	378	454	529		
CXS□32	40	OUT	1608	161	_	322	482	643	804	965	1126		
CXSU32	16	IN	1206	121	_	241	362	482	603	724	844		

Note) Theoretical output (N) = Pressure (MPa) x Piston area (mm²)

Weight


							(kg)
Model			Stan	dard stroke	(mm)		
Widdei	10	20	30	40	50	75	100
CXSM6-□R	0.105	0.12	0.135	0.15	0.165	_	_
CXSL6-□R	0.105	0.12	0.135	0.15	0.165	_	_
CXSM10-□R	0.18	0.2	0.225	0.25	0.27	_	_
CXSL10-□R	0.18	0.2	0.225	0.25	0.27	_	_
CXSM15-□R	0.3	0.33	0.355	0.38	0.41	_	_
CXSL15-□R	0.32	0.35	0.375	0.4	0.43	_	_
CXSM20-□R	0.465	0.5	0.54	0.58	0.62	0.715	0.815
CXSL20-□R	0.485	0.52	0.56	0.60	0.64	0.735	0.835
CXSM25-□R	0.72	0.76	0.8	0.84	0.88	0.98	1.08
CXSL25-□R	0.73	0.77	0.81	0.85	0.89	0.99	1.09
CXSM32-□R	1.33	1.43	1.53	1.62	1.72	1.96	2.2
CXSL32-□R	1.35	1.45	1.55	1.64	1.74	1.98	2.22


Moisture Control Tube IDK Series

When operating an actuator with a small diameter and a short stroke at a high frequency, the dew condensation (water droplet) may occur inside the piping depending on the conditions.

Simply connecting the moisture control tube to the actuator will prevent dew condensation from occurring. For details, refer to the Web Catalog.

Construction





Component Parts

	-		
No.	Description	Material	Note
1	Housing	Aluminum alloy	Hard anodized
2	Piston rod B	Carbon steel	Hard chrome plated
3	O-ring	NBR	
4	Lock rod	Special steel	
5	Retaining ring	Special steel	
6	Lock holder	Aluminum alloy	
7	Lock pin	Special steel	
8	Lock spring	Piano wire	
9	O-ring	NBR	
10	Rod seal	NBR	
11	Manual lever	Special steel	

^{*} Parts other than those listed above are the same as those for standard type.

Replacement Parts/Seal Kit

neplacement Pa						
Bore size (mm)	Kit no.	Contents				
6	CXSRM6-PS					
U	CXSRL6APS]				
10	CXSRM10-PS					
10	CXSRL10APS	Includes the kit				
15	CXSRM15-PS	components of the sea				
10	CXSRL15APS	kit featured on page				
20	CXSRM20-PS	839 plus items (9) and				
20	CXSRL20APS	10 from the parts list				
25	CXSRM25-PS	above.				
	CXSRL25APS					
32	CXSRM32-PS]				
32	CXSRL32APS					

^{*} Seal kits includes the basic type seal (page 839), (9) and (10). Order the seal kit, based on each bore size.





^{*} Since the seal kit does not include a grease pack, order it separately. Grease pack part no.:GR-S-010 (10 g)

CXS Series

Dimensions: Ø6, Ø10, Ø15

CXS□6-□R






		(mm)
Model	SS	ZZ
CXS□6-10R	75	88.5
CXS□6-20R	85	98.5
CXS□6-30R	95	108.5
CXS□6-40R	105	118.5
CXS□6-50R	115	128.5

* Dimensions other than those listed above are the same as for the standard type.

CXS□10-□R




		(mm)
Model	K	0
CXS□10-□R	6.5	Width across flats 12
CXS□15-□R	8.5	Width across flats 13


																									(mm)
Symbol			KK					R					SS					Z					ZZ		
Model	10	20	30	40	50	10	20	30	40	50	10	20	30	40	50	10	20	30	40	50	10	20	30	40	50
CXS□10-□R		19.5		24	1.5			20			80	90	100	115	125	30	4	0	5	0	97	107	117	132	142
CXS□15-□R			20.5			20 30		90	100	110	120	130	35 45		5	109	119	129	139	149					


^{*} Dimensions other than those listed above are the same as for the standard type.

φ

Dimensions: Ø20, Ø25, Ø32







	(mm
Model	0
CXS□20-□R	Width across flats13
CXS□25-□R	Width across flats16
CXS□32-□R	Width across flats19


																												(mm)
Symbol				KK							SS							Z							ZZ			
Model Stroke	10	20	30	40	50	75	100	10	20	30	40	50	75	100	10	20	30	40	50	75	100	10	20	30	40	50	75	100
CXS□20-□R			22			27	22	100	110	120	130	140	170	190		40			60		80	124	134	144	154	164	194	214
CXS□25-□R	24	1.5	29	.5		24.5		107	117	132	142	147	172	197	4	10		6	0		80	131	141	156	166	171	196	221
CXS□32-□R			29			34	49	122	132	142	152	162	192	232	5	0		70		9	10	152	162	172	182	192	222	262

* Dimensions other than those listed above are the same as for the standard type.


CXS Series Auto Switch Mounting

Auto Switch Proper Mounting Position (Detection at Stroke End)

Electrical entry direction: Inward



Electrical entry direction: Outward



Bore size (mm)	Α	В	D-Z7/Z8, D-Y5□, D	D-Y7□W D-Y7□	D-Y6□, D-Y7□V		D-Y7	BAL
(11111)			С	D	С	D	C	D
6	15.5	24.5	11.5 (10)	20.5 (19)	13	22	5.5	14.5
10	22.5	22.5	18.5 (17)	18.5 (17)	20	20	12.5	12.5
15	30.5	24.5	26.5 (25)	20.5 (19)	28	22	20.5	14.5
20	38	27	34 (32.5)	23 (21.5)	36	24.5	28	17
25	38	34	34 (32.5)	30 (28.5)	36	31.5	28	24
32	48	39	44 (42.5)	35 (33.5)	46	6.5	38	29

Note) Adjust the auto switch after confirming the operating conditions in the actual setting.

As for auto switch mounting dimensions, auto switch mounting method and its operating range, those are the same as basic type. Refer to page 843.




CXS Series With End Lock for Retraction Side Specific Product Precautions

Be sure to read this before handling the products.
Refer to page 8 for safety instructions and pages 9 to 18 for actuator and auto switch precautions.

Recommended Pneumatic Circuit

This is necessary for the proper operation and release of the lock.



Handling Precautions

∧ Caution

1. Do not use 3 position solenoid valves.

Avoid using in combination with 3 position solenoid valves (especially closed center metal seal types). If pressure is trapped in the port on the head side, the cylinder cannot be locked. Even after being locked, the lock may be released after some time, due to air leakage from the solenoid valve entering the cylinder.

- 2. Back pressure is required to release the end lock. Be sure that air is supplied to the rod side before starting operation, as shown in the drawing on the left. The lock may not be released. (♠Refer to the section on releasing the lock.)
- Release the lock when mounting and adjusting the cylinder. An attempt to mount or adjust a cylinder while it is locked can damage the lock.
- 4. Operate with a load ratio of 50% or less. If the load ratio exceeds 50%, this may cause problems such as failure of the lock to release, or damage to the lock unit.
- 5. Do not operate multiple cylinders in synchronization. Avoid applications in which two or more end lock cylinders are synchronized to move one workpiece, as one of the cylinder locks may not be able to release when required.
- Install speed controllers as they will be meter-out control.
 When they are used under meter-in control, the lock may not be released.
- Never adjust the retracting stroke using a bumper bolt or external stopper. The lock will not function.

Operating Pressure

Apply a pressure more than 0.3 MPa to the port on the head side.
 The pressure is necessary to release the lock.

Exhaust Speed

Caution

1. Locking will occur automatically if the pressure applied to the port on the head side falls to 0.05 MPa or less. In cases where the piping on the head side is long and thin, or the speed controller is separated at some distance from the cylinder port, the exhaust speed will be reduced. Note that some time may be required for the lock to engage. In addition, clogging of a silencer mounted on the solenoid valve exhaust port can produce the same effect.

Releasing the lock

⚠ Warning

1. Before releasing the lock, be sure to supply air to the rod side, so that there is no load applied to the lock mechanism when it is released. (Refer to the Recommended Pneumatic Circuit.) If the lock is released when the rod side is in an exhaust state, and with a load applied to the lock unit, the lock unit may be subjected to an excessive force and be damaged. Furthermore, sudden movement of the slide table is extremely dangerous.

Manual Release

Manual release (Non-locking type)

Insert the manual lever and screw it into the lock holder assembly.
 If the lever is screwed in sidelong, it may damage the lock spring.



2. To unlock, pull the manual lever in the direction of the arrow. Release the manual lever to return the cylinder to a ready-to-lock state.



 The manual lever (ø1.6 x 35 L, tip part: M1.6 x 0.35 x 3 L) is included with the cylinder. If additional manual levers are required, use the following part number to place an order: CXS06-48BK2777 (for all series).


⚠ Caution

Do not use the cylinder while the manual lever is screwed in. It may damage the lock mechanism.



Dual Rod Cylinder Double Rod Type CXSW Series ø6, ø10, ø15, ø20, ø25, ø32

How to Order



Applicable Auto Switches/Refer to pages 1289 to 1383 for further information on auto switches.

			ight			Load volt	age			Lead wire ler	igth (m) *				
Type	Special function	Electrical entry	dicator light	Wiring (Output)		DC	AC	Auto swite	cn model	0.5	3	5	Pre-wired	Appli	cable load	
	·	entry	puqic	(Output)		DC	C AC		Perpendicular In-line		(L)	(Z)	connector			
switch				3-wire (NPN)		5 V. 12 V		Y69A	Y59A	•	•	0	0	IC		
SK.	_			3-wire (PNP)		5 V, 12 V		Y7PV	Y7P	•	•	0	0	circuit		
皂				2-wire		12 V		Y69B	Y59B	•	•	0	0	_	Deless	
ಹ	Diagnostic indication	Grommet	es	3-wire (NPN)	24 V	5 V 10 V	_	Y7NWV	Y7NW	•	•	0	0	IC	Relay, PLC	
gg	(2-color indicator)		>	3-wire (PNP)		5 V, 12 V		Y7PWV	Y7PW	•	•	0	0	circuit	PLC	
Solid state auto	,,			0		40.1/	1	Y7BWV	Y7BW	•	•	0	0			
	Water resistant (2-color indicator)			2-wire		12 V			Y7BA**	_	•	0	0			
Reed auto switch		Grommet	sə,	3-wire (NPN equivalent)	_	5 V	_	_	Z 76	•	•	-	_	IC circuit	_	
8 g	_	Grommet	_	0	24 V	12 V	100 V	_	Z73	•	•	•	_	_	Relay,	
art			None	2-wire	24 V	12 V	100 V or less	_	Z80	•	•	_	_	IC circuit	PLC	

- ** Water resistant type auto switches can be mounted on the above models, but in such case SMC cannot guarantee water resistance.
- Consult with SMC regarding water resistant types with the above model numbers.

 * Lead wire length symbols: 0.5 m ·········· Nii (Example) Y59A

 * Solid state auto switches marked with "O" are produced upon receipt of order.
 - 3 m L (Example) Y59AL
 - 5 m ······ Z (Example) Y59AZ
- Since there are other applicable auto switches than listed, refer to page 843 for details.
- For details about auto switches with pre-wired connector, refer to pages 1358 and 1359
- · Auto switches are shipped together (not assembled).

Dual Rod Cylinder CXSW Series



Symbol Rubber bumper

Specifications

Bore size (mm)	6	10	15	20	25	32				
Fluid	Air (Non-lube)									
Proof pressure			1.05	MPa						
Maximum operating pressure			0.7	MPa						
Minimum operating pressure		0.15 MPa			0.1 MPa					
Ambient and fluid temperature		-1	0 to 60°C	(No freezir	ng)					
Piston speed			50 to 50	00 mm/s						
Cushion		Bumpe	er is stand	ard on bot	h ends					
Stroke adjustable range	0 to -10 mm compared to the standard stroke (Extended end: 5 mm, Retracted end: 5 mm)									
Port size		1/8								
Bearing type	Slide bear	ring, Ball bu	ıshing beaı	ing (Same	dimension	s for both)				

Standard Stroke

		(mm)
Model	Standard stroke	Long stroke
CXSW□ 6	10, 20, 30, 40, 50	_
CXSW□10	10, 20, 30, 40, 50	75 100 105 150
CXSW□15	10, 20, 30, 40, 50	75, 100, 125, 150
CXSW□20		
CXSW□25	10, 20, 30, 40, 50, 75, 100	125, 150, 175, 200
CXWS□32		

^{*} For long strokes, it will be made-to-order. (-XB11)

Made to Order Specifications Click here for details



Theoretical Output

									(14)
Model	Rod size	Piston area	ston area Operating pressure (MPa)						
Model	(mm)	(mm²)	0.1	0.2	0.3	0.4	0.5	0.6	0.7
CXSW□ 6	4	31	4.6	6.2	9.3	12.4	15.5	18.6	21.7
CXSW□10	6	100	10	20	30	40	50	60	70
CXSW□15	8	252	25.2	50.4	75.6	101	126	151	176
CXSW□20	10	471	47.1	94.2	141	188	236	283	330
CXSW□25	12	756	75.6	151	227	302	378	454	529
CXSW□32	16	1206	121	241	362	482	603	724	844

Note) Theoretical output (N) = Pressure (MPa) x Piston area (mm 2)

Weight

							(kg
Model	Standard stroke (mm)						
Model	10	20	30	40	50	75	100
CXSWM 6	0.11	0.13	0.14	0.16	0.17	_	_
CXSWL 6	0.12	0.13	0.15	0.16	0.18	_	_
CXSWM10	0.24	0.26	0.28	0.30	0.32	0.37	0.42
CXSWL 10	0.25	0.27	0.29	0.31	0.33	0.38	0.43
CXSWM15	0.43	0.45	0.48	0.51	0.54	0.61	0.68
CXSWL 15	0.47	0.50	0.52	0.55	0.58	0.65	0.42
CXSWM20	0.71	0.74	0.78	0.82	0.85	0.95	1.04
CXSWL 20	0.75	0.79	0.82	0.86	0.90	0.99	1.08
CXSWM25	1.06	1.11	1.17	1.22	1.28	1.41	1.55
CXSWL 25	1.07	1.12	1.18	1.23	1.29	1.42	1.56
CXSWM32	2.04	2.12	2.21	2.29	2.38	2.59	2.81
CXSWL 32	2.06	2.15	2.23	2.32	2.41	2.62	2.83

Moisture Control Tube IDK Series

When operating an actuator with a small diameter and a short stroke at a high frequency, the dew condensation (water droplet) may occur inside the piping depending on the conditions.


Simply connecting the moisture control tube to the actuator will prevent dew condensation from occurring. For details, refer to the Web Catalog.




Operating Conditions

Maximum Load Mass

When the cylinder is mounted as shown in the diagrams below, the maximum load mass W should not exceed the values illustrated in the graph immediately following the diagrams.






Note) Please consult with SMC regarding the maximum load mass for long strokes depending on your specific usage conditions.

Allowable Kinetic Energy -

Operate a vertically mounted cylinder with a load mass and cylinder speed not exceeding the ranges shown in the graph below. A horizontally mounted cylinder should also be operated with a load weight less than the ranges given in the graph at left. Cylinder speed should be adjusted using a speed controller.



Deflection at the Plate End -


An approximate plate-end deflection X without a load is shown in the table below.



Bore size (mm)	6 to 32	
CXSWM (Slide bearing)	10.00	
CXSWL (Ball bushing bearing)	±0.03 mm	

Non-rotating accuracy


Non-rotating accuracy θ° without a load should be less than or equal to the value provided in the table below as a guide.




Bore size (mm)	6 to 32	
CXSWM (Slide bearing)	10.10	
CXSWL (Ball bushing bearing)	±0.1°	

Construction

CXSWM (Slide bearing)



CXSWL (Ball bushing bearing)



(Piston part)








CXSW□25, 32

19 4

CXSWM6



CXSWL6



CXSWL10, 15

Component Parts

00	omponent i arts						
No.	Description	Material	Note				
1	Housing	Aluminum alloy	Hard anodized				
2	Piston rod A	Carbon steel	Hard chrome plated				
3	Piston rod B	Carbon steel	Hard chrome plated				
4	Rod cover	Aluminum bearing alloy					
5	Plate	Aluminum alloy	Hard anodized				
6	Piston A	Aluminum alloy	Chromated				
7	Piston B	Aluminum alloy	Chromated				
8	Magnet	_					
9	Bumper bolt	Carbon steel	Nickel plated				
10	Hexagon nut	Carbon steel	Zinc chromated				
11	Hexagon socket head cap screw	Chromium steel	Zinc chromated				
12	Hexagon socket head set screw	Chromium steel	Zinc chromated				

Note) Piston rod for CXSL is quenched.

Replacement Parts/Seal Kit

riopiacomoni i artorocai itit					
Bore size (mm)	Kit no.	Contents			
6	CXSWM6-PS				
U	CXSWL6-PS				
10	CXSWM10-PS				
10	CXSWL10APS				
15	CXSWM15-PS				
13	CXSWL15APS	Set of nos. above			
20	CXSWM20-PS	20, 21 and 22			
20	CXSWL20APS				
25	CXSWM25-PS				
25	CXSWL25APS				
20	CXSWM32-PS				
32	01/01/1/ 00 4 DO	1			

CXSWL32APS

Component Parts

CU	Joinponent Parts					
No.	Description	Material	Note			
13	Retaining ring	Special steel	Phosphate coated			
14	Bumper holder	Synthetic resin				
15	Ball bushing	_				
16	Bearing spacer	Synthetic resin				
17	Bumper	Urethane				
18	Plug	Chromium steel	Nickel plated			
19	Seal retainer	Aluminum alloy				
20°	Piston seal	NBR				
21°	Rod seal	NBR				
22°	O-ring	NBR				
23	O-ring	NBR				


^{*} For CXSWL6, aluminum bearing alloy is used for 16.

^{*} Seal kit includes @ to @. To order them, use the order number given in the left table.

^{*} Since the seal kit does not include a grease pack, order it separately. Grease pack part no.: GR-S-010 (10 g)

CXSW Series


Dimensions: Ø6, Ø10



Opposite side interceptible with

(mm) s SS ZZ Z w Model CXSW□6-10 CXSW□6-20 CXSW□6-30 CXSW□6-40 CXSW□6-50

 Only the CXSW□6-10 and the CXSW□6-20 have a groove cut out for installing auto switches.
 (The dimensions are marked "*".)



2 x M4 x 0.7

thread depth 7

	Model	S	SS	ZZ
æ	CXSW□10-10	10	92	136
Standard stroke	CXSW□10-20	20	102	156
p.	CXSW□10-30	30	112	176
and	CXSW□10-40	40	122	196
ਲ	CXSW□10-50	50	132	216
ě	CXSW□10-75	75	157	266
stro	CXSW□10-100	100	182	316
Long stroke (-XB11)	CXSW□10-125	125	207	366
2 -	CXSW□10-150	150	232	416
* Onl	the CYSW□10-10 a	nd the	CXSW	/m10-2

^{*} Only the CXSW□10-10 and the CXSW□10-20 have a groove cut out for installing auto switches. (The dimensions are marked "*".)

(mm)


Z

4 x M3 x 0.5 thread depth 5

F02

Dual Rod Cylinder CXSW Series


Dimensions: Ø15, Ø20




					(mm)
	Model	s	SS	ZZ	Z
ě	CXSW□15-10	10	105	153	55
Standard stroke	CXSW□15-20	20	115	173	65
ğ	CXSW□15-30	30	125	193	75
and	CXSW□15-40	40	135	213	85
St	CXSW□15-50	50	145	233	95
Long stroke (-XB11)	CXSW□15-75	75	170	283	120
	CXSW□15-100	100	195	333	145
	CXSW□15-125	125	220	383	170
۲	CXSW□15-150	150	245	433	195

* Only the CXSW□15-10 and the CXSW□15-20 have a groove cut out for installing auto switches. (The dimensions are marked "*".)

CX5WU20



4





	30 (Z) (30)
6.5	2 x 4 x M4 x 0.7 thread depth 6 (Opposite side: Same)
±	
	• / + † •
12.5	44.5
-	2 x 2 x M5 x 0.8 thread depth 4.5 (Piping port)

(Opposite side: Same)

		with plug at time on side not equipped	
x M4 x 0.7 thread depth 66_	(30) (Z)	(30) 2 x	M6 x 1 thread depth 10
50±02	•	- 10	•


					(mm)
	Model	S	SS	ZZ	Z
	CXSW□20-10	10	120	178	60
ô	CXSW□20-20	20	130	198	70
Standard stroke	CXSW□20-30	30	140	218	80
<u>p</u>	CXSW□20-40	40	150	238	90
ğu	CXSW□20-50	50	160	258	100
Ste	CXSW□20-75	75	185	308	125
	CXSW□20-100	100	210	358	150
ъ _	CXSW□20-125	125	235	408	175
ong stroke (-XB11)	CXSW□20-150	150	260	458	200
	CXSW□20-175	175	285	508	225
ے ت	CXSW□20-200	200	310	558	250
ا د	CXSW 20-200		310		250

*Only the CXSW□20-10 has a groove cut out for installing auto switches.

(The dimensions are marked "*".)

CXSW Series


Dimensions: ø25, ø32



ΖZ

					(mm)
$\overline{}$	Model	S	SS	ZZ	Z
Standard stroke	CXSW□25-10	10	122	180	62
	CXSW□25-20	20	132	200	72
	CXSW□25-30	30	142	220	82
	CXSW□25-40	40	152	240	92
	CXSW□25-50	50	162	260	102
	CXSW□25-75	75	187	310	127
	CXSW□25-100	100	212	360	152
Long stroke (-XB11)	CXSW□25-125	125	237	410	177
	CXSW□25-150	150	262	460	202
	CXSW□25-175	175	287	510	227
	CXSW□25-200	200	312	560	252

Only the CXSW 25-10 has a groove cut out for installing auto switches. (The dimensions are marked "".)



(30)

2 x M8 x 1.25 thread depth 12

SMC

ΖZ

mm)						
z	.	ZZ	SS	S	Model	
83	3	213	143	10	CXSW□32-10	Standard stroke
93	3	233	153	20	CXSW□32-20	
03	3	253	163	30	CXSW□32-30	
13	3	273	173	40	CXSW□32-40	
23	3	293	183	50	CXSW□32-50	
48	3	343	208	75	CXSW□32-75	
73	3	393	233	100	CXSW□32-100	
98	3	443	258	125	CXSW□32-125	Long stroke (-XB11)
23	3	493	283	150	CXSW□32-150	
48	3	543	308	175	CXSW□32-175	
73	3 T	593	333	200	CXSW□32-200	
2	3 3 3	393 443 493 543	233 258 283 308	100 125 150 175 200	CXSW□32-100 CXSW□32-125 CXSW□32-150 CXSW□32-175	

^{*} Only the CXSW 32-10 has a groove cut out for installing auto switches.

(The dimensions are marked "*".)


4 x M5 x 0.8 thread depth 8

 75 ± 0.2


CXSW Series Auto Switch Mounting

Auto Switch Proper Mounting Position (Detection at Stroke End)

Electrical entry direction: Inward



Electrical entry direction: Outward



Bore size (mm)	Α	D-Z7/Z8, D-Y7□W D-Y5□, D-Y7□	D-Y6□, D-Y7□V D-Y7□WV	D-Y7BA
(11111)		В	В	В
6	13.8	9.8(8.3)	11.3	3.8
10	28.5	24.5(23)	26	_
15	35	31(29.5)	32.5	_
20	42.5	38.5(37)	40.5	_
25	43.5	39.5(38)	41.5	33.5
32	54	50(48.5)	52	44

Note) Adjust the auto switch after confirming the operating conditions in the actual setting.

As for auto switch mounting dimensions, auto switch mounting method and its operating range, those are the same as basic type. Refer to page 843