
Basic Type/Direct Mount Type

CY3B/CY3R Series

Ø6, Ø10, Ø15, Ø20, Ø25, Ø32, Ø40, Ø50, Ø63



Improved durability


Improved bearing performance

A 70% longer wear ring length achieving an improvement in bearing performance compared to the CY1B.


Improved lubrication by using a Lube-retainer

A special resin Lube-retainer is installed on the dust seal to achieve ideal lubrication on the external surface of the cylinder tube.

Direct mount type CY3R Series



Series Variations



Note) The ● mark indicates the available combination of bore size and standard stroke.

Availability of Made to Order products varies with the series and the bore size. For more information, please refer to pages 1419 to 1585.


Upgraded version of space saving magnetically rodless cylinder!


Reduction of sliding resistance

■ Minimum operating pressure reduced by 30%

By using a Lube-retainer, the minimum operating pressure is reduced by 30%.

(CY3B40 compared with CY1B40)






Small auto switches are mountable.

Small auto switches can be mounted on the currrent auto switch mounting groove of the CY3R25 to 63. So, they can be mounted to all of the cylinder sizes in the CY3R series, making inventory control of the product easy.

Lightweight

The body weight has been reduced by approximately 10% by eliminating unnecessary body weight and by reducing the outer diameter of the cylinder tube. (Compared with previous ø50 and ø60 models)


CY3B/CY3R Series Model Selection



Selection Procedure

Selection procedure

- 1. Find the drive resisting force Fn (N) when moving the load horizontally.
- 2. Find the distance Lo (cm) from the point of the load where driving force is applied, to the center of the cylinder shaft.
- 3. Select the bore size from Lo and Fn. based on data A.



Selection example


Given a load drive resisting force of Fn = 100 (N) and a distance from the cylinder shaft center to the load application point of Lo = 8 cm, find the intersection point by extending upward from the horizontal axis of data (A) where the distance from the shaft center is 8 cm, and then extending to the side, find the allowable driving force on the vertical axis.

Models suitable in satisfying the requirement of 100 (N) are CY3 32 or CY3 40.


* The Lo point from the cylinder shaft center is the moment working point between the cylinder and the load section.

<Data (A): Distance from cylinder shaft center —— Allowable driving capacity>







CY3B10




CY3B15




CY3B20




CY3B25




CY3B32




CY3B40



CY3B50




CY3B63




<Data (A): Distance from cylinder shaft center —— Allowable driving capacity>


CY3R6




CY3R32




CY3R10




CY3R40




CY3R15




CY3R50




CY3R20



CY3R63




CY3R25



Cylinder Dead Weight Deflection

When the cylinder is mounted horizontally, deflection appears due to its own weight as shown in the data, and the longer the stroke is, the greater the amount of variation in the shaft center. Therefore, a connection method should be considered which can assimilate this deflection.



The above clearance amount is a reference value.


Note 1) According to the dead weight deflection in the figure on the right, provide clearance so that the cylinder does not touch the mounting surface or the load, etc., and is able to operate smoothly within the minimum operating pressure range for a full stroke. For more information, refer to operation manual.

Note 2) In case of the CY3R, install a shim, etc. to eliminate clearance between the body and the switch rail. For more information, refer to the CY3R operation manual.

Note 3) The amount of deflection differs from the CY1B/CY1R. Adjust the clearance value by referring to the dead weight deflection as shown in the table on the right.

When CY1B/CY1R are replaced with CY3B/CY3R, install a cylinder after confirming a full stroke and clearance are allowed.

CY3B CY3R




* The above deflection data represent values at the time when the external sliding part moves to the middle of the stroke.

Vertical Operation

It is recommended that the load is guided by a ball type bearing (linear guide, etc.). If a slide bearing is used, sliding resistance increases due to the load mass and moment, which may cause malfunctions

When the cylinder is mounted vertically or on an angle and is to make intermediate stops, use an external stopper, etc., for positioning. In addition, as the slider may move downwards toward the stroke end due to self-weight or the mass of the workpiece, use an external stopper, etc., for positioning if accurate positioning is required.



| Bore size (mm) | Model | Mass (Wv) (kg) | pressure (Pv) (MPa) | |
|-------------------|--------|-------------------|------------------------|--|
| 6 | CY3□6 | 1.0 | 0.55 | |
| 10 | CY3□10 | 2.7 | 0.55 | |
| 15 | CY3□15 | 7.0 | 0.65 | |
| 20 | CY3□20 | 11.0 | 0.65 | |
| 25 | CY3□25 | 18.5 | 0.65 | |
| 32 | CY3□32 | 30.0 | 0.65 | |
| 40 | CY3□40 | 47.0 | 0.65 | |
| 50 | CY3□50 | 75.0 | 0.65 | |
| 63 | CY3□63 | 115.0 | 0.65 | |

 Use caution, as there is a danger of breaking the magnetic coupling if operated above the maximum operating pressure.

Maximum Weight of Connection Bracket to the Body

The CY3B series is guided by an external axis such as a linear guide) without directly mounting the load. When designing a metal bracket to connect the load, make sure that its weight will not exceed the value in the table below. Basically, guide the CY3R direct mounting type also with an external axis. (For connection methods, refer to the Operation Manual.)

Max. Connection Bracket Weight


| Model | Max. connection bracket weight (Wamax) (kg) |
|--------|---|
| CY3□6 | 0.2 |
| CY3□10 | 0.4 |
| CY3□15 | 1.0 |
| CY3□20 | 1.1 |
| CY3□25 | 1.2 |
| CY3□32 | 1.5 |
| CY3□40 | 2.0 |
| CY3□50 | 2.5 |
| CY3□63 | 3.0 |

Consult with SMC in case a bracket with weight exceeding the above value is to be mounted.

<CY3R> Maximum Load Mass when Loaded Directly on Body

When the load is applied directly to the body, it should be no greater than the maximum values shown in the table below.

| Model | Max. load weight (Wsmax) (kg) |
|--------|-------------------------------|
| CY3R6 | 0.2 |
| CY3R10 | 0.4 |
| CY3R15 | 1.0 |
| CY3R20 | 1.1 |
| CY3R25 | 1.2 |
| CY3R32 | 1.5 |
| CY3R40 | 2.0 |
| CY3R50 | 2.5 |
| CY3R63 | 3.0 |



Intermediate Stop

(1) Intermediate stopping of load with an external stopper, etc.

When stopping a load in mid-stroke using an external stopper, etc., operate within the operating pressure limits shown in the table below. Use caution, as operation at a pressure exceeding these limits can result in breaking of the magnetic coupling.

| Bore size (mm) | Model | Operating pressure limit for intermediate stop (Ps) (MPa) |
|-------------------|--------|---|
| 6 | CY3□6 | 0.55 |
| 10 | CY3□10 | 0.55 |
| 15 | CY3□15 | 0.65 |
| 20 | CY3□20 | 0.65 |
| 25 | CY3□25 | 0.65 |
| 32 | CY3□32 | 0.65 |
| 40 | CY3□40 | 0.65 |
| 50 | CY3□50 | 0.65 |
| 63 | CY3□63 | 0.65 |

(2) Intermediate stopping of load with an air pressure circuit

When performing an intermediate stop of a load using an air pressure circuit, operate at or below the kinetic energy shown in the table below. Use caution, as operation when exceeding the allowable value can result in breaking of the magnetic coupling.


(Reference values)

| Bore size (mm) | Model | Allowable kinetic energy for intermediate stop (Es) (J) |
|-------------------|--------|---|
| 6 | CY3□6 | 0.007 |
| 10 | CY3□10 | 0.03 |
| 15 | CY3□15 | 0.13 |
| 20 | CY3□20 | 0.24 |
| 25 | CY3□25 | 0.45 |
| 32 | CY3□32 | 0.88 |
| 40 | CY3□40 | 1.53 |
| 50 | CY3□50 | 3.12 |
| 63 | CY3□63 | 5.07 |

Stroke End Stopping Method

When stopping a load having a large inertial force at the stroke end, tilting of the body and damage to the bearings and cylinder tube may occur. (Refer to the left hand drawing below.)

As shown in the right hand drawing below, a shock absorber should be used together with the stopper, and thrust should also be transmitted from the center of the body so that tilting will not occur.




<CY3R>

Body Non-rotating Accuracy and Maximum Allowable Moment (with Switch Rail)

(Reference values)

Reference values for non-rotating accuracy and maximum allowable moment at stroke end are indicated below.

| Bore size (mm) | Non-rotating accuracy (°) | Max. allowable moment (M₀) (N⋅m) | Allowable stroke (mm) | | |
|-------------------|---------------------------|--|--------------------------|--|--|
| 6 | 7.3 | 0.02 | 100 | | |
| 10 | 6.0 | 0.05 | 100 | | |
| 15 | 4.5 | 0.15 | 200 | | |
| 20 | 3.7 | 0.20 | 300 | | |
| 25 | 3.7 | 0.25 | 300 | | |
| 32 | 3.1 | 0.40 | 400 | | |
| 40 | 2.8 | 0.62 | 400 | | |
| 50 | 2.4 | 1.00 | 500 | | |
| 63 | 2.2 | 1.37 | 500 | | |
| | | | | | |




- Note 1) Avoid operations where rotational torque (moment) is applied. In such a case, the use of an external guide is recommended.
- Note 2) The above reference values will be satisfied within the allowable stroke ranges, but caution is necessary, because as the stroke becomes longer, the inclination (rotation angle) within the stroke can be exceeded to increase.
- Note 3) When a load is applied directly to the body, the loaded weight should be no greater than the allowable load weight on page 1180.

Magnetically Coupled Rodless Cylinder/ Basic Type

CY3B Series

Ø6, Ø10, Ø15, Ø20, Ø25, Ø32, Ø40, Ø50, Ø63

How to Order



Standard Stroke

| Bore size (mm) | Standard stroke (mm) | Maximum available stroke (mm) | | |
|-------------------|---|-------------------------------|--|--|
| 6 | 50, 100, 150, 200 | 300 | | |
| 10 | 50, 100, 150, 200, 250, 300 | 500 | | |
| 15 | 50, 100, 150, 200, 250, 300, 350, 400, 450, 500 | 1000 | | |
| 20 | | 1500 | | |
| 25 | 100, 150, 200, 250, 300, 350, 400, 450, 500, 600, 700, 800 | 2000 | | |
| 32 | 700, 000 | 3000 | | |
| 40 | | 3000 | | |
| 50 | 100, 150, 200, 250, 300, 350, 400, 450, 500, 600, 700, 800, 900, 1000 | 5000 | | |
| 63 | 700, 000, 300, 1000 | 5000 | | |

Note 1) Long stroke type (XB11) applies to the strokes exceeding 2000 mm. (Refer to page 1456.)

Note 2) The longer the stroke, the larger the amount of deflection in a cylinder tube. Pay attention to the mounting bracket and clearance value.

Note 3) Intermediate stroke is available in 1 mm increments



Specifications



Symbol

Rubber bumper (Magnet type)





Made to Order: Individual Specifications (For details, refer to pages 1194 to 1196.)

| Symbol | Specifications |
|--------|---|
| -X116 | Hydro specifications |
| -X132 | Axial ports |
| -X160 | High speed specifications |
| -X168 | Helical insert thread specifications |
| -X206 | Added mounting tap positions for slider |
| -X210 | Non-lubricated exterior specifications |
| -X322 | Outside of cylinder tube with hard chrome plating |
| -X324 | Non-lubricated exterior specifications (with dust seal) |
| -Y1/68 | Interchangeable specification with CV1 G |

Made to Order

| Click here for details | | | | | |
|------------------------|--|--|--|--|--|
| Symbol | Specifications | | | | |
| -XB6 | Head resistant cylinder (-10 to 150°C) | | | | |
| -XB9 | Low-speed cylinder (15 to 50mm/s) | | | | |
| -XB11 | Long stroke type | | | | |
| -XB13 | Low-speed cylinder (7 to 50mm/s) | | | | |
| -XC24 | With magnetic shielding plate | | | | |
| -XC57 | With floating joint | | | | |

For clean specifications, refer to the Web Catalog.


| Bore size (mm) | 6 | 10 | 15 | 20 | 25 | 32 | 40 | 50 | 63 |
|-------------------------------|---|------|------|---------|---------|---------|------|------|------|
| Fluid | | | | | Air | | | | |
| Proof pressure | | | | 1. | .05 MP | а | | | |
| Max. operating pressure | | | | C |).7 MPa | a | | | |
| Min. operating pressure | 0.16 | 0.16 | 0.16 | 0.16 | 0.15 | 0.14 | 0.12 | 0.12 | 0.12 |
| Ambient and fluid temperature | | | -1 | 0 to 60 | °C (No | freezir | ng) | | |
| Piston speed | 50 to 500 mm/s | | | | | | | | |
| Cushion | | | | Rubl | oer bur | nper | | | |
| Lubrication | Not required (Non-lube) | | | | | | | | |
| Stroke length tolerance (mm) | 0 to 250 st: +1.0 , 251 to 1000 st: +1.4 , 1001 st to: +1.8 | | | | | | | | |
| Mounting orientation | Horizontal, Inclined, Vertical Note) | | | | | | | | |
| Mounting nut (2 pcs.) | Standard equipment (accessory) | | | | | | | | |
| Magnet holding force (N) | 19.6 | 53.9 | 137 | 231 | 363 | 588 | 922 | 1471 | 2256 |

Note) When vertically mounting, it is impossible to perform an intermediate stop by means of a pneumatic circuit.


Theoretical Cylinder Thrust

When calculating the actual thr-


ø6, ø10



Ø15, Ø20, Ø25, Ø32, Ø40



ø50, ø63



Weight

| | | | | | | | | | Unit: kg |
|---------------------------------------|-------|-------|-------|-------|-------|-------|------|-------|----------|
| Bore size (mm) | 6 | 10 | 15 | 20 | 25 | 32 | 40 | 50 | 63 |
| Basic weight (at 0 st) | 0.052 | 0.08 | 0.275 | 0.351 | 0.672 | 1.287 | 2.07 | 3.2 | 5.3 |
| Additional weight per 50 mm of stroke | 0.004 | 0.014 | 0.015 | 0.02 | 0.023 | 0.033 | 0.04 | 0.077 | 0.096 |

Calculation method/Example: CY3B32-500

Cylinder stroke 500 st

 $1.287 + 0.033 \times 500 \div 50 = 1.617 \text{ kg}$




CY3B Series


Construction

Basic type **CY3B6**







CY3B10, 15





CY3B20 to 40





CY3B50, 63





Component Parts

| | • | | | | | |
|-----|--------------------------------|----------------|----------------|------------------|-----------------------|--|
| No. | Description | Material | | Note | | |
| 1 | Body | Aluminum alloy | | Hard anodized | | |
| 2 | Head cover | ø6, ø10 | Brass | | | |
| 2 | neau cover | ø15 to ø63 | Aluminum alloy | | | |
| 3 | End collar | Alumii | num alloy | ø20 to | ø40 only | |
| 4 | Cylinder tube | Stainl | ess steel | | | |
| 5 | Piston | ø6 | Brass | ø6 | Electroless Ni plated | |
| · · | Piston | ø10 to ø63 | Aluminum alloy | ø10 to ø63 | Chromated | |
| 6 | Shaft | Stainl | ess steel | | | |
| 7 | Piston side yoke | Rolle | ed steel | Zinc c | hromated | |
| 8 | External slider side yoke | Rolle | ed steel | Zinc c | hromated | |
| 9 | Magnet A | | _ | | | |
| 10 | Magnet B | | _ | | | |
| 11 | Spacer | Aluminum alloy | | ø6: no | t available | |
| 12 | Bumper | Uretha | ne rubber | | | |
| 13 | Piston nut | Carb | on steel | ø6 to ø15: | not available | |
| 14 | C type retaining ring for hole | Carbor | tool steel | Phosphate coated | | |
| 15 | Wear ring A | Special resin | | | | |
| 16 | Wear ring B | Spec | ial resin | | | |
| 17 | Piston seal | 1 | NBR | | | |
| 18 | Lube-retainer | Spec | ial resin | ø6: no | t available | |
| 19 | Cylinder tube gasket | NBR | | ø6, ø10 only | | |

Replacement Parts/Seal Kit

| riopiacoment i arto/ocar itit | | | | | | | | |
|-------------------------------|-----------|----------------------------------|--|--|--|--|--|--|
| Bore size (mm) | Kit no. | Contents | | | | | | |
| 6 | CY3B6-PS | Set of nos. above 16, 17, 19 | | | | | | |
| 10 | CY3B10-PS | Set of nos. above 16, 17, 18, 19 | | | | | | |
| 15 | CY3B15-PS | | | | | | | |
| 20 | CY3B20-PS | | | | | | | |
| 25 | CY3B25-PS | Set of nos, above | | | | | | |
| 32 | CY3B32-PS | | | | | | | |
| 40 | CY3B40-PS | 15, 16, 17, 18 | | | | | | |
| 50 | CY3B50-PS | | | | | | | |
| 63 | CY3B63-PS | | | | | | | |

Note 1) Seal kits are sets consisting of numbers 15 through 19. Order using the kit number corresponding to each bore size.

Note 2) Adhesive glue is applied to the thread fixed section of the head cover and cylinder tube. Contact SMC if the head cover removal is difficult.

Note 3) For replacement of the ø10 wear ring A, contact SMC or your nearest sales representative.

* Seal kit includes a grease pack (ø6, ø10: 5 and 10 g, ø15 to ø63: 10 g). Order with the following part number when only the grease pack is

Grease pack part number for ø6, ø10: GR-F-005 (5 g) For external sliding sections GR-S-010 (10 g) For tubing


interior

Grease pack part number for ø15 to ø63: GR-S-010 (10 g)

Dimensions

Basic type

CY3B6 to 63




| | | | | | | | | | | | | | | | | | | | | | | (mm) |
|--------|----|-----|----|----------|-------|-----|----|------|-------|-----|-----|----|-----|-----------|-------|-----|-----------|-----------|-------|-----|-----|-----------|
| Model | Α | В | С | СС | D | Е | F | G | Н | ı | J | K | L | MM | N | NA | NN | Q | R | S | Т | V |
| CY3B6 | 4 | 17 | 8* | — | 7.6 | 4 | 8* | 5 | 13.5* | - | 4.5 | 5 | 35 | M3 x 0.5 | 9.5* | 10* | M6 x 1* | _ | _ | 62* | 6.5 | _ |
| CY3B10 | 4 | 25 | 14 | - | 12 | 1.5 | 9 | 5 | 12.5 | - | 4.5 | 4 | 38 | M3 x 0.5 | 11 | 14 | M10 x 1 | | _ | 63 | 7.5 | _ |
| CY3B15 | 4 | 35 | 14 | _ | 16.6* | 2 | 10 | 5.5 | 13 | _ | 6 | 11 | 57 | M4 x 0.7 | 11 | 17 | M10 x 1 | _ | _ | 83 | 8 | _ |
| CY3B20 | 8 | 36 | 26 | _ | 21.6* | 2* | 13 | 7.5* | 20 | 28 | 6 | 8 | 66 | M4 x 0.7 | 18* | 24 | M20 x 1.5 | _ | 12* | 106 | 10 | _ |
| CY3B25 | 8 | 46 | 32 | _ | 26.4* | 2* | 13 | 7.5* | 20.5 | 34 | 8 | 10 | 70 | M5 x 0.8 | 18.5* | 30 | M26 x 1.5 | _ | 15* | 111 | 10 | _ |
| CY3B32 | 8 | 60 | 32 | _ | 33.6* | 2* | 16 | 8* | 22 | 40 | 8 | 15 | 80 | M6 x 1 | 20* | 36 | M26 x 1.5 | _ | 18* | 124 | 13 | _ |
| CY3B40 | 10 | 70 | 41 | — | 41.6* | 3* | 16 | 11 | 29 | 50 | 10 | 16 | 92 | M6 x 1 | 26* | 46 | M32 x 2 | _ | 23* | 150 | 13 | _ |
| CY3B50 | _ | 86 | _ | 32 | 52.4* | 8 | 2 | 14 | 33 | 58* | 12 | 25 | 110 | M8 x 1.25 | 25 | 55 | _ | 30 -0.007 | 27.5* | 176 | _ | M8 x 1.25 |
| CY3B63 | _ | 100 | _ | 38 | 65.4* | 8 | 2 | 14 | 33 | 72* | 12 | 26 | 122 | M8 x 1.25 | 25 | 69 | | 32 -0.007 | 34.5* | 188 | _ | M10 x 1.5 |

| Mandal | w | x | γ | ZZ | F | (Piping port | :) |
|--------|----|----|----|-----|-----------|--------------------------------|-------|
| Model | w | ^ | T | | Nil | TN* | TF* |
| CY3B6 | 25 | 10 | I | 78* | M3 x 0.5* | _ | _ |
| CY3B10 | 30 | 16 | _ | 81 | M5 x 0.8 | _ | _ |
| CY3B15 | 35 | 19 | _ | 103 | M5 x 0.8 | _ | _ |
| CY3B20 | 50 | 25 | I | 132 | Rc 1/8 | NPT 1/8 | G 1/8 |
| CY3B25 | 50 | 30 | _ | 137 | Rc 1/8 | NPT 1/8 | G 1/8 |
| CY3B32 | 50 | 40 | I | 156 | Rc 1/8 | NPT 1/8 | G 1/8 |
| CY3B40 | 60 | 40 | _ | 182 | Rc 1/4 | NPT 1/4 | G 1/4 |
| CY3B50 | 60 | 60 | 16 | 180 | Rc 1/4 | NPT 1/4 | G 1/4 |
| CY3B63 | 70 | 70 | 16 | 192 | Rc 1/4 | NPT 1/4 | G 1/4 |

Note 2) The astrisk denotes the dimensions which are different from the CY1B series.

Note 3) Mounting nuts can be screwed on only for the effective thread length of the head cover (T dimension). When mounting a cylinder, consider the thickness of flange, etc.

Mounting Nut/Included in the package (2 pcs).



| Part no. | Applicable bore size (mm) | d | Н | B | C |
|----------|---------------------------|-----------|----|----|------|
| SNJ-006B | 6 | M6 x 1.0 | 4 | 8 | 9.2 |
| SNJ-016B | 10, 15 | M10 x 1.0 | 4 | 14 | 16.2 |
| SN-020B | 20 | M20 x 1.5 | 8 | 26 | 30 |
| SN-032B | 25, 32 | M26 x 1.5 | 8 | 32 | 37 |
| SN-040B | 40 | M32 x 2.0 | 10 | 41 | 47.3 |

Note) Mounting nuts are not available for ø50 and ø63.




Magnetically Coupled Rodless Cylinder/ **Direct Mount Type**

CY3R Series

Ø6, Ø10, Ø15, Ø20, Ø25, Ø32, Ø40, Ø50, Ø63

How to Order



Cylinder stroke (mm)

Refer to page 1187 for standard stroke.

Applicable Auto Switches/Refer to pages 1289 to 1383 for further information on auto switches.


| | | Electrical | ō | Wiring | L | oad volta | ge | Auto | Lead v | wire le | ngth | (m) | D | | | | |
|------------------|-------------------|----------------------|-----------|------------------------|-------------|----------------|---------------|-----------------|--------------|----------|----------|----------|---------------------|------------|------------|---------------|--------|
| Туре | Special function | entry | Indicator | (output) | D | C | AC | switch model | 0.5 (Nil) | 1 (M) | 3 (L) | 5 (Z) | Pre-wired connector | Applica | ble load | | |
| | | | | 3-wire (NPN) | | 5 V. 12 V | | M9N | • | • | • | 0 | 0 | | | | |
| | | | | 3-wire (PNP) | | 5 V, 12 V | | M9P | • | • | • | 0 | 0 | IC circuit | iit | | |
| ~ = | | | | 2-wire | | 12 V | | M9B | • | • | • | 0 | 0 | _ | | | |
| switch | Diagnostic |] | | 3-wire (NPN) | EV 10 | 5 V, 12 V |] [| M9NW | • | • | • | 0 | 0 | IC circuit | | | |
| s p | indication | Grommet | Yes | 3-wire (PNP) | 24 V | 24 V 5 V, 12 V | 3 V, 12 V | - L | M9PW | • | • | • | 0 | 0 | IC circuit | Relay, PLC | |
| Solid auto s | (2-color display) | | | 2-wire | | | ĺ | 12 V |] [| M9BW | • | • | • | 0 | 0 | _ | 1 1 20 |
| 0, 6 | Water resistant | | | 3-wire (NPN) | | 5 V, 12 V |] [| M9NA*1 | 0 | 0 | • | 0 | 0 | IC circuit | | | |
| | (2-color display) | | | 3-wire (PNP) | | | | M9PA*1 | 0 | 0 | • | 0 | 0 | IC circuit | | | |
| | (2-color display) | | | 2-wire | | 12 V |] [| M9BA*1 | 0 | 0 | • | 0 | 0 | _ | | | |
| ed switch | | | Yes | 3-wire (NPN equiv.) | _ | 5 V | _ | A96 | • | - | • | _ | _ | IC circuit | _ | | |
| Reed auto swi | | Grommet No 2-wire 24 | 24.1/ | 5 V. 12 V | 100 V | A93 | • | • | • | • | _ | _ | Relay, | | | | |
| an | | | No | ∠-wire | 2-wire 24 V | 5 V, 12 V | 100 V or less | A90 | • | _ | • | _ | _ | IC circuit | PLĆ | | |


- *1 Water resistant type auto switches can be mounted on the above models, but in such case SMC cannot guarantee water resistance. Consult with SMC regarding water resistant types with the above model numbers.
- * Lead wire length symbols: 0.5 m...... Nil (Example) M9NW * Solid state auto switches marked "O" are produced upon receipt of order.

1 m M (Example) M9NWM 3 m..... L (Example) M9NWL 5 m..... Z (Example) M9NWZ

- * Other than the applicable auto switches listed in "How to Order", the other auto switches can be mounted. For detailed specifications, refer to page 1193.
- * With pre-wired connector is also available in solid state auto switches. For specifications, refer to pages 1358 and 1359
- * The auto switch is shipped together, but not assembled.

Specifications





Note 2) When vertically mounting, it is impossible to perform an intermediate stop by means of a pneumatic circuit.

Symbol

Rubber bumper (Magnet type)





Made to Order: Individual Specifications (For details, refer to pages 1194 to 1196.)

| Symbol | Specifications | | | | | | |
|--------|---|--|--|--|--|--|--|
| -X116 | Hydro specifications | | | | | | |
| -X160 | High speed specifications | | | | | | |
| -X322 | Outside of cylinder tube with hard chrome plating | | | | | | |
| -X1468 | Interchangeable specification with CV1 6 | | | | | | |

Made to Order

ø6. ø10

90

80

70

60

50

40

30

20

2 100

Theoretical thrust (holding force)

Click here for details

| Symbol | Specifications |
|--------|---------------------|
| -XC57 | With floating joint |

For clean specifications, refer to the Web Catalog


Standard Stroke


| Bore size (mm) | Standard stroke (mm) | Max. stroke without switch (mm) | Max. stroke with switch (mm) | | |
|----------------|--|---------------------------------|------------------------------|--|--|
| 6 | 50, 100, 150, 200 | 300 | 300 | | |
| 10 | 50, 100, 150, 200, 250, 300 | 500 | 500 | | |
| 15 | 50, 100, 150, 200, 250, 300 350, 400, 450, 500 | 1000 | 750 | | |
| 20 | | 1500 | 1000 | | |
| 25 | 100, 150, 200, 250, 300, 350 400, 450, 500, 600, 700, 800 | 1500 | 1200 | | |
| 32 | 400, 430, 300, 600, 700, 600 | | | | |
| 40 | 100, 150, 200, 250, 300, 350 | 2000 | 1500 | | |
| 50 | 400, 450, 500, 600, 700, 800 | 2000 | 1500 | | |
| 63 | 900, 1000 | | | | |

Note 1) The longer the stroke, the larger the amount of deflection in a cylinder tube. Pay attention to the mounting bracket and clearance value.

Note 2) Intermediate stroke is available in 1 mm increments.


Theoretical Cylinder Thrust





 ★ Caution
 When calculating the actual thrust, design should consider the minimum actuating pressure.

 332 α40
 α50 α63



Weight Unit: kg


| Bore size | 6 | 10 | 15 | 20 | 25 | 32 | 40 | 50 | 63 | |
|-----------------------------|---------------------|-------|-------|-------|-------|-------|-------|-------|-------|-------|
| Donie weight (at 0 at) | With switch rail | 0.086 | 0.111 | 0.272 | 0.421 | 0.622 | 1.217 | 1.98 | 3.54 | 5.38 |
| Basic weight (at 0 st) | Without switch rail | 0.069 | 0.08 | 0.225 | 0.351 | 0.542 | 1.097 | 1.82 | 3.25 | 5.03 |
| Additional weight per 50 mm | With switch rail | 0.016 | 0.034 | 0.040 | 0.051 | 0.056 | 0.076 | 0.093 | 0.159 | 0.188 |
| of stroke | Without switch rail | 0.004 | 0.014 | 0.015 | 0.020 | 0.023 | 0.033 | 0.040 | 0.077 | 0.096 |

Calculation method/Example: CY3R25-500 (with switch rail) Basic weight...0.622 (kg), Additional weight...0.056 (kg/50 st), Cylinder stroke...500 (st) $0.622 + 0.056 \times 500 \div 50 = 1.182$ (kg)



CY3R Series

Construction



Component Parts

| omponent Parts | | | | | | | | |
|----------------------------------|---|----------------|---|-----------------------------|--|--|--|--|
| Description | Ma | terial | 1 | Note | | | | |
| Body | Alumin | um alloy | Hard | anodized | | | | |
| End cover A | Alumin | um alloy | | | | | | |
| End cover C | Alumin | um alloy | | | | | | |
| End cover B | Alumin | um alloy | | | | | | |
| End cover D | Alumin | um alloy | | | | | | |
| Cylinder tube | Stainle | ss steel | | | | | | |
| Distan | ø6 | Brass | ø6 | Electroless nickel plated | | | | |
| Piston | ø10 to ø63 | Aluminum alloy | ø10 to ø63 | Chromate | | | | |
| Shaft | Stainle | ss steel | | | | | | |
| Piston side yoke | Rolled s | teel plate | Zinc c | hromated | | | | |
| External slider side yoke | Rolled s | teel plate | Zinc chromated | | | | | |
| Magnet A | - | _ | | | | | | |
| Magnet B | | _ | | | | | | |
| Spacer | Alumin | um alloy | ø6: not available | | | | | |
| Bumper | Urethar | ne rubber | | | | | | |
| Piston nut | Carbo | n steel | Zinc chromate (ø6 to ø15: not available) | | | | | |
| Type C retaining ring for hole | Carbon | tool steel | Phosphate coated | | | | | |
| Attachment ring | Alumin | um alloy | Chromate | | | | | |
| Type C retaining ring for shaft | Hard s | teel wire | | | | | | |
| Magnetic shielding plate | Rolled s | teel plate | Chromated (ø6 | i, ø10: not available) | | | | |
| Switch rail (both sides piping) | Alumin | um alloy | White | anodized | | | | |
| Switch rail (centralized piping) | Alumin | um alloy | White | anodized | | | | |
| Magnet | | _ | | | | | | |
| Hexagon socket head plug | Chromi | um steel | Nicke | el plated | | | | |
| Stool balls | Chromi | um staal | ø40 | Hexagon socket head plug | | | | |
| Sieci balls | | | | | | | | |
| Hexagon socket head screw | Chromi | um steel | Nickel plated | | | | | |
| Hexagon socket head set screw | Chromi | um steel | Nickel plated | | | | | |
| | Description Body End cover A End cover A End cover B End cover B End cover B Cylinder tube Piston Shaft Piston side yoke External slider side yoke Magnet A Magnet A Magnet B Spacer Bumper Piston nut Type C retaining ring for hole Attachment ring Type Cretaining ring for shaft Switch rail both sides piping Switch rail centralized piping Magnets Magnets Switch rail centralized piping | Description | Description Material Body Aluminum alloy End cover A Aluminum alloy End cover C Aluminum alloy End cover B Aluminum alloy End cover B Aluminum alloy Cylinder tube Stainless steel Piston of Brass O10 to 663 Aluminum alloy Shaft Stainless steel Piston side yoke Rolled steel plate External sider side yoke Rolled steel plate Magnet A — Magnet B — Spacer Aluminum alloy Bumper Urethane rubber Piston nut Carbon tool steel Attachment ring Aluminum alloy Type Cretaining ring for hole Attachment ring Aluminum alloy Type Cretaining ring for shaft Hard steel wire Magnetic shielding plate Switch rail (both sides piping) Aluminum alloy Switch rail (centralized piping) Aluminum alloy Magnet Steel balls Chromium steel Steel balls Chromium steel Hexagon socket head plug Chromium steel | Description Material In | | | | |

| No. | Description | Material | Note | | |
|------------|----------------------|---------------|---------------------------------|--|--|
| 24 Note 2) | Cylinder tube Gasket | NBR | | | |
| | Wear ring A | Special resin | ø6: not available | | |
| 26 Note 2) | Wear ring B | Special resin | | | |
| 27 Note 2) | Wear ring C | Special resin | | | |
| 28 Note 2) | Piston seal | NBR | | | |
| 29 Note 2) | Lubretainer | Special resin | ø6: not available | | |
| 30 Note 2) | Switch rail gasket | NBR | Both sides piping type: None | | |

Replacement Parts/Seal Kit

| Bore size (mm) | Kit no. | Contents | | | |
|----------------|-----------|---|--|--|--|
| 6 | CY3R6-PS | Set of nos. above 24, 26, 27, 28 | | | |
| 10 | CY3R10-PS | Set of nos. above 24, 26, 27, 28, 29, 3 | | | |
| 15 | CY3R15-PS | | | | |
| 20 | CY3R20-PS | | | | |
| 25 | CY3R25-PS | Set of nos. above | | | |
| 32 | CY3R32-PS | 24, 25, 26, 27, 28, 29, 30 | | | |
| 40 | CY3R40-PS | | | | |
| 50 | CY3R50-PS | | | | |
| 63 | CY3R63-PS | | | | |

Note1) Seal kits are the same for both the both sides piping type and the centralized piping type.

Note2) Seal kits are sets consisting of numbers 24 through 30. Order using the kit number corresponding to each bore size.

Note3) For replacement of the ø10 wear ring A, contact SMC or your nearest sales representative.

* Seal kit includes a grease pack (ø6, ø10: 5 and 10 g, ø15 to ø63: 10 g). Order with the following part number when only the grease pack is needed.

Grease pack part number for ø6, ø10: GR-F-005 (5 g) For external


sliding sections GR-S-010 (10 g) For tubing




Construction

Centralized piping type


CY3RG10







Switch Rail Accessory



Switch Rail Accessory Kit

| E | Bore size | Kit | no. | Contents |
|----|------------------------|-------------------|--------------------|--|
| | (mm) | Both sides piping | Centralized piping | Contents |
| | 6 | CYR6EB-□ | _ | Numbers (18a), (18b), (19, (2), (2) above |
| | 10 | CYR10EB-□ | CYR10E-□ | Numbers (18a), (18b), (19, 20, 20, 20 above |
| | 15 | CYR15EB-□ | CYR15E- | Numbers 17, 18a, 18b, 20, 22, 27 above Note 2) |
| 20 | For reed switch | CYR20EB-□ | CYR20E-□ | |
| 20 | For solid state switch | CYR20EBN-□ | CYR20EN-□ | |
| | 25 | CYR25EB-□ | CYR25E-□ | Numbers |
| | 32 | CYR32EB-□ | CYR32E-□ | (7), (8a), (18b), (19), (20), (22), (27) above |
| | 40 | CYR40EB-□ | CYR40E-□ | |
| | 50 | CYR50EB- | CYR50E-□ | |
| | 63 | CYR63EB-□ | CYR63E-□ | |

Note 1) \square indicates the stroke.

Note 2) A magnet is already built in for ø15.

Note 3) (18a) is attached on both sides piping.

Note 4) (18b) and (20 are attached on centralized piping.


CY3R Series

Dimensions

Both sides piping type: Ø6 to Ø63

Note) This figure shows types with switch rail (Nil).

CY3R10 to 20



| | | | | | | | | | | | | | | | | | | | | (mm) |
|--------|------|-----|-----|----|-----|-------|------|-----|----|------|----|----|------|----|-------|----|-----|-------|----------------|------|
| Model | Α | В | С | СВ | CR | D | F | G | GP | GW | Н | HA | НВ | HC | HP | HR | HS | HT | JxE | K |
| CY3R6 | 7* | -* | -* | 2 | 0.5 | 7.6 | 5.5 | 3* | 20 | 18.5 | 19 | 17 | 10.5 | 18 | 10.5* | 17 | 6 | 10.5* | M4 x 0.7 x 6 | 7 |
| CY3R10 | 9 | 6.5 | 3.2 | 2 | 0.5 | 12 | 6.5 | 4 | 27 | 25.5 | 26 | 24 | 14 | 25 | 14 | 24 | 5 | 14 | M4 x 0.7 x 6 | 9 |
| CY3R15 | 10.5 | 8 | 4.2 | 2 | 0.5 | 16.6* | 8 | 5 | 33 | 31.5 | 32 | 30 | 17 | 31 | 17 | 30 | 8.5 | 17 | M5 x 0.8 x 7 | 14 |
| CY3R20 | 9 | 9.5 | 5.2 | 3 | 1 | 21.6* | 9 | 6 | 39 | 37.5 | 39 | 36 | 21 | 38 | 24 | 36 | 7.5 | 24 | M6 x 1 x 8 | 11 |
| CY3R25 | 8.5 | 9.5 | 5.2 | 3 | 1 | 26.4* | 8.5 | 6 | 44 | 42.5 | 44 | 41 | 23.5 | 43 | 23.5 | 41 | 6.5 | 23.5 | M6 x 1 x 8 | 15 |
| CY3R32 | 10.5 | 11 | 6.5 | 3 | 1.5 | 33.6* | 10.5 | 7 | 55 | 53.5 | 55 | 52 | 29 | 54 | 29 | 51 | 7 | 29 | M8 x 1.25 x 10 | 13 |
| CY3R40 | 10 | 11 | 6.5 | 5 | 2 | 41.6* | 13 | 7 | 65 | 63.5 | 67 | 62 | 36 | 66 | 36 | 62 | 8 | 36 | M8 x 1.25 x 10 | 15 |
| CY3R50 | 14 | 14 | 8.2 | 5 | 2 | 52.4* | 17 | 8.5 | 83 | 81.5 | 85 | 80 | 45 | 84 | 45 | 80 | 9 | 45 | M10 x 1.5 x 15 | 25 |
| CY3R63 | 15 | 14 | 8.2 | 5 | 3 | 65.4* | 18 | 8.5 | 95 | 93.5 | 97 | 92 | 51 | 96 | 51 | 90 | 9.5 | 51 | M10 x 1.5 x 15 | 24 |

| Model | L | LD | M | MM | N | PW | Q | QW | Т | TC | W | WP | ws | Х | Υ | Z |
|--------|-----|-----|-----|-----------|-----|----|-----|----|-------|------|----|------|----|----|------|-----|
| CY3R6 | 34 | 3.5 | 3.5 | M3 x 0.5 | 3.5 | 19 | 60* | 10 | 14.5* | 10.5 | 20 | 9.5 | 6 | 10 | 35.5 | 66* |
| CY3R10 | 38 | 3.5 | 4 | M3 x 0.5 | 4.5 | 26 | 68 | 14 | 17.5 | 14 | 20 | 13 | 8 | 15 | 39.5 | 76 |
| CY3R15 | 53 | 4.3 | 5 | M4 x 0.7 | 6 | 32 | 84 | 18 | 19 | 17 | 25 | 16 | 7 | 18 | 54.5 | 94 |
| CY3R20 | 62 | 5.4 | 5 | M4 x 0.7 | 7 | 38 | 95 | 17 | 20.5 | 20 | 40 | 19 | 7 | 22 | 64 | 107 |
| CY3R25 | 70 | 5.4 | 6 | M5 x 0.8 | 6.5 | 43 | 105 | 20 | 21.5 | 22.5 | 40 | 21.5 | 7 | 28 | 72 | 117 |
| CY3R32 | 76 | 7 | 7 | M6 x 1 | 8.5 | 54 | 116 | 26 | 24 | 28 | 50 | 27 | 7 | 35 | 79 | 130 |
| CY3R40 | 90 | 7 | 8 | M6 x 1 | 11 | 64 | 134 | 34 | 26 | 33 | 60 | 32 | 7 | 40 | 93 | 148 |
| CY3R50 | 110 | 8.6 | 10 | M8 x 1.25 | 15 | 82 | 159 | 48 | 30 | 42 | 60 | 41 | 10 | 50 | 113 | 176 |
| CV3R63 | 118 | 8.6 | 10 | M8 v 1 25 | 16 | 94 | 171 | 60 | 32 | 48 | 70 | 47 | 10 | 60 | 121 | 188 |

| | F | (Piping port |) |
|--------|-----------|--------------|-------|
| Model | Nil | TN* | TF* |
| CY3R6 | M3 x 0.5* | _ | _ |
| CY3R10 | M5 x 0.8 | _ | _ |
| CY3R15 | M5 x 0.8 | _ | _ |
| CY3R20 | Rc 1/8 | NPT 1/8 | G 1/8 |
| CY3R25 | Rc 1/8 | NPT 1/8 | G 1/8 |
| CY3R32 | Rc 1/8 | NPT 1/8 | G 1/8 |
| CY3R40 | Rc 1/4 | NPT 1/4 | G 1/4 |
| CY3R50 | Rc 1/4 | NPT 1/4 | G 1/4 |
| CY3R63 | Rc 1/4 | NPT 1/4 | G 1/4 |


Note 2) The astrisk denotes the dimensions which are different from the CY1R series.

1190



Dimensions

Centralized piping type: ø10 to ø63



| | | | | | | | | | | | | | | | | | | | | (mm) |
|---------|-----|-----|----|-----|-------|------|-----|----|------|----|----|------|----|------|----|-----|------|----------------|----|------|
| Model | В | С | СВ | CR | D | F | G | GP | GW | Н | HA | НВ | нс | HP | HR | HS | HT | JxE | K | L |
| CY3RG10 | 6.5 | 3.2 | 2 | 0.5 | 12 | 6.5 | 4 | 27 | 25.5 | 26 | 24 | 14 | 25 | _ | 24 | 5 | _ | M4 x 0.7 x 6 | 9 | 38 |
| CY3RG15 | 8 | 4.2 | 2 | 0.5 | 16.6* | 8 | 5 | 33 | 31.5 | 32 | 30 | 17 | 31 | _ | 30 | 8.5 | _ | M5 x 0.8 x 7 | 14 | 53 |
| CY3RG20 | 9.5 | 5.2 | 3 | 1 | 21.6* | 9 | 6 | 39 | 37.5 | 39 | 36 | 21 | 38 | 11 | 36 | 7.5 | 28 | M6 x 1 x 8 | 11 | 62 |
| CY3RG25 | 9.5 | 5.2 | 3 | 1 | 26.4* | 8.5 | 6 | 44 | 42.5 | 44 | 41 | 23.5 | 43 | 14.5 | 41 | 6.5 | 33.5 | M6 x 1 x 8 | 15 | 70 |
| CY3RG32 | 11 | 6.5 | 3 | 1.5 | 33.6* | 10.5 | 7 | 55 | 53.5 | 55 | 52 | 29 | 54 | 20 | 51 | 7 | 41 | M8 x 1.25 x 10 | 13 | 76 |
| CY3RG40 | 11 | 6.5 | 5 | 2 | 41.6* | 13 | 7 | 65 | 63.5 | 67 | 62 | 36 | 66 | 25 | 62 | 8 | 50 | M8 x 1.25 x 10 | 15 | 90 |
| CY3RG50 | 14 | 8.2 | 5 | 2 | 52.4* | 17 | 8.5 | 83 | 81.5 | 85 | 80 | 45 | 84 | 32 | 80 | 9 | 56 | M10 x 1.5 x 15 | 25 | 110 |
| CY3RG63 | 14 | 8.2 | 5 | 3 | 65.4* | 18 | 8.5 | 95 | 93.5 | 97 | 92 | 51 | 96 | 35 | 90 | 9.5 | 63.5 | M10 x 1.5 x 15 | 24 | 118 |

| Model | LD | М | ММ | N | PW | Q | QW | Т | TC | W | WP | ws | Х | Υ | Z |
|---------|-----|----|-----------|-----|----|-----|----|------|------|----|------|----|----|------|-----|
| CY3RG10 | 3.5 | 4 | M3 x 0.5 | 4.5 | 26 | 68 | 14 | 17.5 | 14 | 20 | 13 | 8 | 15 | 39.5 | 76 |
| CY3RG15 | 4.3 | 5 | M4 x 0.7 | 6 | 32 | 84 | 18 | 19 | 17 | 25 | 16 | 7 | 18 | 54.5 | 94 |
| CY3RG20 | 5.4 | 5 | M4 x 0.7 | 7 | 38 | 95 | 17 | 20.5 | 20 | 40 | 19 | 7 | 22 | 64 | 107 |
| CY3RG25 | 5.4 | 6 | M5 x 0.8 | 6.5 | 43 | 105 | 20 | 21.5 | 22.5 | 40 | 21.5 | 7 | 28 | 72 | 117 |
| CY3RG32 | 7 | 7 | M6 x 1 | 8.5 | 54 | 116 | 26 | 24 | 28 | 50 | 27 | 7 | 35 | 79 | 130 |
| CY3RG40 | 7 | 8 | M6 x 1 | 11 | 64 | 134 | 34 | 26 | 33 | 60 | 32 | 7 | 40 | 93 | 148 |
| CY3RG50 | 8.6 | 10 | M8 x 1.25 | 15 | 82 | 159 | 48 | 30 | 42 | 60 | 41 | 10 | 50 | 113 | 176 |
| CY3RG63 | 8.6 | 10 | M8 x 1.25 | 16 | 94 | 171 | 60 | 32 | 48 | 70 | 47 | 10 | 60 | 121 | 188 |


| Model | F | (Piping port |) | | |
|---------|----------|--------------------------------|-------|--|--|
| Model | Nil | TN* | TF* | | |
| CY3RG10 | M5 x 0.8 | _ | _ | | |
| CY3RG15 | M5 x 0.8 | _ | _ | | |
| CY3RG20 | Rc 1/8 | NPT 1/8 | G 1/8 | | |
| CY3RG25 | Rc 1/8 | NPT 1/8 | G 1/8 | | |
| CY3RG32 | Rc 1/8 | NPT 1/8 | G 1/8 | | |
| CY3RG40 | Rc 1/4 | NPT 1/4 | G 1/4 | | |
| CY3RG50 | Rc 1/4 | NPT 1/4 | G 1/4 | | |
| CY3RG63 | Rc 1/4 | NPT 1/4 | G 1/4 | | |

Note 2) The astrisk denotes the dimensions which are different from the CY1RG series.



CY3B/CY3R Series **Auto Switch Mounting**

Auto Switch Proper Mounting Position for Stroke End Detection



(Reference dimension)

Auto Switch Proper Mounting Position

ø6 to ø20

Auto switch mode В С n D-M9□ D-M9□W D-M9□ D-M9□ D-M9□ Bore size (mm) D-M9□W D-M9□W D-A9□ D-A9□ D-A9□ D-M9 W D-A9□ D-M9□A D-M9
A D-M9□A D-M9□A 46 26 10 28 32 48 44 48 44 32 15 17.5 21.5 76.5 72.5 56.5 60.5

23.5 Note 1) Auto switches cannot be installed in Area C in the case of ø15

Note 2) D-A9□ type cannot be mounted on the section D of ø10.

Note 3) The above values are a guideline of the auto switch mounting position when detected at the stroke end. Adjust the auto switch after confirming the operating conditions in the actual setting.

87.5

Note 4) D-Z7□ and D-Y□ types cannot be mounted.

19.5

ø25 to ø63 (mm)

35.5

67.5

71.5

39.5

| Auto switch | | Α | | | В | | | С | | D | | |
|----------------|-------|---------------------------|---|-------|---------------------------|---|-------|---------------------------|---|-------|---------------------------|---|
| Bore size (mm) | D-A9□ | D-M9 D-M9 W D-M9 | D-Z7 D-Z80 D-Y59 D-Y7P D-Y7 W D-Y7BA | D-A9□ | D-M9 D-M9 W D-M9 | D-Z7 D-Z80 D-Y59 D-Y7P D-Y7 W D-Y7BA | D-A9□ | D-M9□ D-M9□W D-M9□A | D-Z7 D-Z80 D-Y59 D-Y7P D-Y7 W D-Y7BA | D-A9□ | D-M9□ D-M9□W D-M9□A | D-Z7□ D-Z80 D-Y59□ D-Y7P D-Y7□W D-Y7BA |
| 25 | 19 | 23 | 18 | 98 | 94 | 99 | 42 | 38 | 43 | 75 | 79 | 74 |
| 32 | 22.5 | 26.5 | 21.5 | 107.5 | 103.5 | 108.5 | 45.5 | 41.5 | 46.5 | 84.5 | 88.5 | 83.5 |
| 40 | 24.5 | 28.5 | 23.5 | 123.5 | 119.5 | 124.5 | 47.5 | 43.5 | 48.5 | 100.5 | 104.5 | 99.5 |
| 50 | 28.5 | 32.5 | 27.5 | 147.5 | 143.5 | 148.5 | 51.5 | 47.5 | 52.5 | 124.5 | 128.5 | 123.5 |
| 63 | 30.5 | 34.5 | 29.5 | 157.5 | 153.5 | 158.5 | 53.5 | 49.5 | 54.5 | 134.5 | 138.5 | 133.5 |

Note 1) 50 mm is the minimum stroke available with 2 auto switches mounted.

Note 2) Figures in the table above are used as a reference when mounting the auto switches for stroke end detection. In the case of actually setting the auto switches,

adjust them after confirming their operation. Note 3) Auto switch brackets are required when ordering D-A9□/M9□/M9□W/M9□A types and cylinders separately. (Refer to the auto switch mounting bracket: part no. on page 1193.)



Auto Switch Mounting CY3B/CY3R Series

Auto Switch Operation Range


| Auto switch model | Bore size (mm) | | | | | | | | | | | |
|---|----------------|-----|-----|----|----|-----|-----|-----|----|--|--|--|
| Auto switch model | 6 | 10 | 15 | 20 | 25 | 32 | 40 | 50 | 63 | | | |
| D-A9 | 8 | 11 | 8 | 6 | 6 | 7 | 9 | 8 | 8 | | | |
| D-M9□ | | | | | | | | | | | | |
| D-M9□W | 4.5 | 6.5 | 4.5 | 5 | 5 | 5.5 | 5.5 | 6.5 | 7 | | | |
| D-M9□A | | | | | | | | | | | | |
| D-Z7□/Z80 | _ | _ | _ | _ | 9 | 9 | 11 | 9 | 10 | | | |
| D-Y59\(\textstyre{Y7P/Y7}\(\textstyre{W/Y7BA}\) | _ | _ | _ | _ | 5 | 5 | 6 | 6 | 6 | | | |

^{*} The auto switches cannot be mounted in some cases.

Auto Switch Mounting Bracket/Part No.

| Auto switch model | Bore size (mm) |
|------------------------------------|----------------|
| Auto switch model | ø25 to ø63 |
| D-A9□ D-M9□ D-M9□W D-M9□A | BMG2-012 |

$D-A9 \square /M9 \square /M9 \square W/M9 \square A$



Other than the applicable auto switches listed in "How to Order", the following auto switches can be mounted. For detailed specifications, refer to pages 1289 to 1383.

| Туре | Model | Electrical entry | Features | Applicable bore size | |
|-------------------------|--------------------|-------------------|--|----------------------|--|
| Danid auto auditali | D-Z73, Z76 | Grommet (In-line) | _ | | |
| Reed auto switch | D-Z80 | Grommet (m-ine) | Without indicator light | | |
| | D-Y59A, Y59B, Y7P | | _ | | |
| Solid state auto switch | D-Y7NW, Y7PW, Y7BW | Grommet (In-line) | Diagnostic indication (2-color display) | ø25 to ø63 | |
| | D-Y7BA | | Water resistant (2-color display) | | |

^{*} With pre-wired connector is also available in solid state auto switches. For specifications, refer to pages 1358 and 1359

ı

ı ı ī

^{*} Since the operating range is provided as a guideline including hysteresis, it cannot be guaranteed (assuming approximately ±30% dispersion). It may vary substantially depending on an ambient environment.

^{*} Normally closed (NC = b contact) solid state switches (D-M9□E(V)/Y7G/Y7H) are also available. For details, refer to pages 1308 and 1310.

^{*} Applicable bore sizes are ø25 to ø63.

CY3B/CY3R Series Made to Order: Individual Specifications 1





Applicable Series

| No. | Symbol | Specifications/Description | Basic type CY3B | Direct mount type CY3R |
|-----|--------|---|-----------------|---------------------------|
| 1 | -X116 | Hydro specifications | ●(ø25 to ø63) | ●(ø25 to ø63) |
| 2 | -X132 | Air supply port relocated in axial direction | ●(ø6 to ø63) | _ |
| 3 | -X160 | High speed specifications | ●(ø20 to ø63) | ●(ø20 to ø63) |
| 4 | -X168 | Helical insert thread specifications | ●(ø20 to ø63) | _ |
| 5 | -X206 | Added mounting tap positions for slider | ●(ø6 to ø63) | _ |
| 6 | -X210 | Non-lubricated exterior specifications | ●(ø6 to ø63) | _ |
| 7 | -X322 | Outside of cylinder tube with hard chrome plated | ●(ø15 to ø63) | ●(ø15 to ø63) |
| 8 | -X324 | Non-lubricated exterior specifications (with dust seal) | ●(ø10 to ø63) | _ |
| 9 | -X1468 | Interchangeable with CY1□6 | ●(ø6) | ●(ø6) |

1 Hydro Specifications

Symbol -X116

This type is applicable for precision constant speed feed, intermediate stop and skip feed.

| [Basic type] [Direct mount type] | | | | | |
|----------------------------------|-----------|------------------|---|--------|--------|
| CY3B | Bore size | Port thread type | - | Stroke | – X116 |
| 0.0 | | | | | |

Specifications

| opcomodions | | |
|--------------|---------------------------------------|--|
| Туре | Basic type, Direct mount type | |
| Bore size | Basic type CY3B25 to 63, CY3R25 to 63 | |
| Fluid | Turbine oil | |
| Piston speed | 15 to 300mm/s | |

Note) Piping is from each plate on both sides.

2 Air Supply Port Relocated in Axial Direction


Hydro specifications


Symbol

-X132



The air supply port has been changed to an axial position on the head cover.






The port size is the same as the standard type.

1194

Made to Order: Individual Specifications CY3B/CY3R Series



This makes a high speed piston drive of 1,500 mm/s possible (basic type, without load), but it is not applicable for all conditions. Consult with SMC for the operating conditions, etc.

Specifications

| Applicable series | CY3B/CY3R |
|------------------------|-----------------|
| Bore size | ø20 to ø63 |
| Piston speed (no load) | 1500 mm/s (MAX) |

Note 1) When operating this cylinder at high speed, a shock absorber must be provided. Note 2) For the CY3R, only the piping on both sides can be made.


Note 2) For the CY3H, only the piping on both sides can be made.

Note 3) The piston speed may vary depending on the operating conditions. For details, con-

tions. Apply grease periodically if necessary.

tact SMC or your nearest sales representative.

Note 4) Speed tends to decrease over a period of time depending on the operating condi-




Added mounting tap positions for slider

Mounting taps have been added on the surface opposite the standard positions.

Specifications

| Applicable series | СҮЗВ | |
|-------------------|-----------|--|
| Bore size | ø6 to ø63 | |




* Dimensions are the same as the standard product.



Helical insert thread is used for standard mounting thread.

Specifications

| Applicable series | СҮЗВ | |
|-------------------|------------------|--|
| Bore size | CY3B: ø20 to ø63 | |



Suitable for environments where oil is not tolerated. It is recommended to use this type in a special environment where standard product causes lubrication failure.

Non-lubricated exterior specifications


Note) Consider installing a protective cover if the product is used in an environment where foreign matter such as paper powder might be caught in the sliding parts of the cylinder.

Specifications

| Applicable series | СҮЗВ | |
|-------------------|-----------|--|
| Bore size | ø6 to ø63 | |

Construction

CY3B (Basic type)






CY3B/CY3R Series Made to Order: Individual Specifications 2

Please contact SMC for detailed dimensions, specifications and lead times.





The cylinder tube outer circumference is plated with hard chrome, which further reduces bearing abrasion.

- * Be sure to install a shock absorber to the stroke end.
- Note 1) The maximum stroke is 3,500 st, or the maximum stroke for the standard type.
- CY3R is compatible with the maximum stroke for the standard type.

 Note 2) When exceeding 2,000 strokes, contact SMC separately.

8 Non-lubricated Exterior Specifications (with Dust Seal) CY3B Bore size Port thread type Stroke X324 Non-lubricated exterior specifications (with dust seal)

No grease is applied to the external surface of the cylinder. Suitable for environments where oil is not tolerated.

A felt dust seal is mounted to the external sliding part of the cylinder tube. Note) Although a felt dust seal is installed, foreign matter might be caught in the sliding parts of the cylinder. In that instance, consider installing a protective cover.

Specifications


| Applicable series | Bore size (mm) |
|-------------------|----------------|
| *CY3B-3R | ø15 to ø63 |


Specifications

| Applicable series | Bore size (mm) |
|-------------------|----------------|
| СҮЗВ | ø10 to ø63 |


Construction/Dimensions







Construction



9 Interchangeable with CY1□6 -X1468



Can be interchanged with CY1□6.



CY3B/CY3R Series Specific Product Precautions 1

Be sure to read this before handling the products.

Refer to page 8 for safety instructions and pages 9 to 18 for actuator and auto switch precautions.

Handling

⚠ Warning

 Pay attention to the space between the head cover and the body.

Take sufficient care to avoid getting your hands or fingers caught when the cylinder is operated.

2. Do not apply a load to a cylinder which is greater than the allowable value stated in the Model Selection.

Applying an improper load may cause malfunctions.

- 3. Do not use the cylinder in an environment where the cylinder is expose to moisture, adhesive foreign matter, dust or liquid such as water or cutting fluid. If the cylinder is used in an environment where the lubrication of the cylinders sliding parts is compromised, please consult SMC.
- When applying grease to the cylinder, use the grease that has already been applied to the product. Contact SMC for available grease packs.

Mounting

 Take care to avoid nicks or other damage on the outside surface of the cylinder tube.

This can lead to damage of the wear ring and lubretainer, which in turn can cause malfunction.

2. Take care regarding rotation of the external slider.

Even when the rotation is controlled by connecting the external slider to other shaft (linear guide, etc.), keep it in the floating connection status.

Do not operate with the magnetic coupling out of position.

In case the magnetic coupling is out of position, push the external slider back into the correct position by hand at the end of the stroke (or correct the piston slider with air pressure).

- The cylinder is mounted with bolts through the mounting holes in the end covers. Be sure they are tightened securely. (CY3R)
- If gaps occur between the mounting surface and the end covers when mounting with bolts, perform shim adjustment using spacers, etc. so that there is no unreasonable stress. (CY3R)
- 6. Be sure that both end covers are secured to the mounting surface before operating the cylinder.


Avoid operation with the external slider secured to the surface.

Mounting

⚠ Caution

7. Do not apply a lateral load to the external slider.

When a load is mounted directly to the cylinder, variations in the alignment of each shaft center cannot be assimilated, which results in the generation of a lateral load that can cause malfunction. (Figure 1) The cylinder should be operated using a connection method which allows for assimilation of shaft alignment variations and deflection due to the cylinder's own weight. A drawing of a recommended mounting is shown in Figure 2.



Variations in the load and cylinder shaft alignment cannot be assimilated, resulting in malfunction.

Shaft alignment variations are assimilated by providing clearance for the mounting bracket and cylinder. Moreover, the mounting bracket is extended above the cylinder shaft center, so that the cylinder is not subjected to moment.

Figure 1. Incorrect mounting
Note) The drawing shows the
CY3B series

Figure 2. Recommended mounting

Use caution regarding the allowable load mass when operating in a vertical direction.

The allowable load mass when operating in a vertical direction (reference values on page 1180) is determined by the model selection method, however, if a load greater than the allowable value is applied, the magnetic coupling may break and there is a possibility of dropping the load. When using this type of application, contact SMC regarding the operating conditions (pressure, load, speed, stroke, frequency, etc.).

Careful alignment is necessary when connecting to a load having an external guide mechanism.

As the stroke becomes longer, variations in the center axis become larger. Consider using a connection method (floating mechamism) that is able to absorb these variations. Furthermore, use the special floating brackets (XC57) which have been provided for the CY3B and CY3R series (page 1552).





CY3B/CY3R Series Specific Product Precautions 2

Be sure to read this before handling the products.

Refer to page 8 for safety instructions and pages 9 to 18 for actuator and auto switch precautions.


Disassembly & Maintenance

⚠ Warning

 Use caution as the attractive power of the magnets is very strong.

When removing the external slider and piston slider from the cylinder tube for maintenance, etc., handle with caution, since the magnets installed in each slider have very strong attractive power.

- When reattaching the head covers after disassembly, confirm that they are tightened securely. (CY3B)
 When disassembling, hold the wrench flat section of one head cover with a vise, and remove the other cover using a spanner or
 - cover with a vise, and remove the other cover using a spanner or adjustable angle wrench on its wrench flat section. When retightening, first coat with Locktight (No. 542 red), and retighten 3 to 5° past the original position prior to removal.
- 2. Special tools are necessary for disassembly. (CY3R)



Special Tool Number List

| | Applicable bore size (mm) |
|--------|---------------------------|
| CYRZ-V | |
| CYRZ-W | |
| CYRZ-X | |
| CYRZ-Y | 63 |

Use caution when taking off the external slider, as the piston slider will be directly attracted to it.

When removing the external slider or piston slider from the cylinder tube, first force the sliders out of their magnetically coupled positions and then remove them individually while there is no longer any holding force. If they are removed when still magnetically coupled, they will be directly attracted to one another and will not come apart.

Do not disassemble the magnetic components (piston slider, external slider).

This can cause a loss of holding force and malfunction.

When disassembling to replace the seals and wear ring, refer to the separate disassembly instructions.

Disassembly & Maintenance

⚠ Caution

Note the direction of the external slider and piston slider.

Since the external slider and piston slider are directional for ø6 and ø10, refer to the figures below when performing disassembly or maintenance. Put the external slider and piston slider together, and insert the piston slider into the cylinder tube so that they will have the correct positional relationship as shown in Figure 3. If they align as shown in Figure 4, insert the piston slider after turning it around 180°. If the direction is not correct, it will be impossible to obtain the specified holding force.





Figure 3. Correct position Figure 4. Incorrect position

For ø6 and ø10