Compact Guide Cylinder

MGP Series

Ø12, Ø16, Ø20, Ø25, Ø32, Ø40, Ø50, Ø63, Ø80, Ø100

Up to 24% Weight reduced!

Weight reduced by up to 24% with a shorter guide rod and thinner plate



3 types of bearing can be selected.

Slide bearing


MGPM series

Ball bushing

MGPL series

High precision ball bushing

MGPA series










With air cushion


Water resistant cylinder



Basic Type

■Weight reduced by up to 17% ■Guide rod shortened

Bore size [mm]	Reduction rate [%]	Weight [kg]
ø12	11	0.25
ø16	3	0.37
ø 20	12	0.59
ø 25	12	0.84
ø 32	17	1.41
ø 40	16	1.64
ø 50	17	2.79
ø 63	17	3.48
ø 80	17	5.41
ø100	13	9.12



iicu		[mm]
Bore size	Guid	e rod
Dore Size	Shortened by	New dimension
ø 32	22	15.5
ø 40	22	9
ø 50	18	16.5
ø 63	18	11.5
ø 80	10.5	8
ø100	10.5	10.5
0 1 20	the service of the service of	05 1 1 (00

*: Compared with the slide bearing type, 25 stroke (ø32 to ø100) (No projection for ø12 to ø25-25 stroke)


- *: Compared with the slide bearing type, ø12 to ø25-20 stroke
- *: Compared with the slide bearing type, ø32 to ø100-25 stroke
- **Performance and strength (rigidity) are equivalent to the current MGP series.**
- Mounting dimensions are equivalent to the current MGP series.

MGP Series (Basic Type), Stroke Variations

	Bore size	Stroke [mm]	
Bearing type	[mm]	10 20 25 30 40 50 75 100 125 150 175 200 250 300 350 400	Made to Order
MGPM Slide bearing MGPL Ball bushing MGPA High precision ball bushing	12 16 20 25 32 40 50 63 80		-XA C: Change of guide rod end shape -XB6: Heat resistant cylinder (-10 to 150°C) -XB10: Intermediate stroke (Using exclusive body) -XB13: Low speed cylinder (5 to 50 mm/s) -XC6: Made of stainliess steel -XC8: Adjustable stroke cylinder/ -Adjustable extension type -XC22: Flutorroutber seal -XC35: With coil scraper -XC79: Tappet hote, drilled hole and pinned hole machined additionally -XC82: Bottom mounting type -X144: Symmetrical port position -X867: Side porting type (Plug location changed)

Compact Guide Cylinder MGP Series






With Air Cushion

• Weight reduced by up to 24%

Bore size [mm]	Reduction rate [%]	Weight [kg]
ø16	12	1.28
ø 20	18	1.91
ø 25	22	2.52
ø32	24	3.57
ø 40	23	4.13
ø 50	23	6.56
ø 63	22	8.04
ø 80	21	11.35
ø100	19	17.72

*: Compared with the current MGPM with air cushion, 200 stroke

● Guide rod shortened by up to 35.5 mm (MGPM100-50 stroke)



Bore size	Guid	Guide rod					
Bore size	Shortened by	New dimension					
ø 32	33.5	9					
ø 40	33.5	2.5					
ø 50	22	12.5					
ø 63	22	7.5					
ø 80	35.5	10					
ø 100	35.5	10.5					
a. Compored wit	h the ourrent MCD	Musith air aughian					

- Compared with the current MGPM with air cushion, 50 stroke
- Performance and strength are equivalent to the current MGP series with air cushion.
- •Mounting dimensions are equivalent to the current MGP series with air cushion.

MGP Series (With Air Cushion), Stroke Variations

Bearing type	Bore size						Stroke	e [mm]						Made to Order		
bearing type	[mm]	25	50	75	100	125	150	175	200	250	300	350	400	Made to Order		
MGPM-□A Slide bearing MGPL-□A Ball bushing MGPA-□A High precision	16 20 25 32 40 50 63	••••••	••••••	••••••	••••••	••••••	••••••	••••••	••••••	••••••	•••••	•••••	••••••	-XC19: Intermediate stroke (Spacer type) -XC79: Tapped hole, drilled hole, pinned hole machined additionally -X867: Side porting type (Plug location changed)		
ball bushing	100		-5	-5	-5	-5	-5	-5	-5	-5	-5	-5	ŏ	1.		

529

With End Lock

- Holds the cylinder's home position even if the air supply is cut off.
- Compact body ø20 to ø63 ······ Standard + 25 mm body length ø80, ø100 Standard + 50 mm body length



■Stroke Variations

Bearing type	Bore size						Stroke	[mm]						Intermediate	Lock	Manual
веатінд туре	[mm]	25	50	75	100	125	150	175	200	250	300	350	400	stroke	direction	release
MGPM Slide bearing	20 25	•	•	•	•	•	•	•	•	•	•	•	•		Rod end	Non-lock
MGPL Ball bushing	32 40	•	•	•	•	•	•	•	•	•	•		•	Spacer type available in 5 mm	lock	type
bearing MGPA	50 63	•	•	•	•	•	•	•	•	•	•		•	stroke increments.	Head end	Lock
High precision ball bushing	100	-			-	-	-	-	-		•	•	•	-	lock	type

Heavy duty quide rod type with improved load

■Stroke Variations

Bearing type	Bore size				Stroke	[mm]			
bearing type	[mm]	25	50	75	100	125	150	175	200
MGPS	50	-		-	-				
Slide bearing	80	-	-	-	-	-	-	-	-



 Anti-lateral load : 10% increase

• Eccentric load resistance: 25% increase

 Impact load resistance : 140% increase

(Compared with MGPM50 compact guide cylinder)

Bore size	Guide rod diameter [mm]						
[mm]	MGPS	MGPM					
50	30	25					
80	45	30					

Proposals for Improving Product Life


SMC offers a wide range of models suitable for various applications and operating environments. This includes models that can be used in environments that the basic model cannot, such as those where coolant liquid, water droplets/splashing, dust, etc., are present. When using in environments where the above are present, it is possible to improve the service life of the product by selecting a model ideal for use in such environments.

- →For details, refer to the Web Catalog.
- Environmental Resistance
- Measures Against Moisture/Drainage
- Measures Against Condensation
- Preventive and Predictive Maintenance
- High Rigidity



Compact Guide Cylinder MGP Series

■Compact Guide Cylinders, Series Variations



Combinations of Standard and Made to Order Specifications

MGP Series

•:	Standard

[:] Made to Order

Туре		Basic type		
Bearing type	Slide bearing	Ball bushing	High precision ball bushing	
Model	МСРМ	MGPL	MGPA	
Page		536		
Applicable		10.1 100		

Symbol Specifications Standard Stan			Page		536		
12-, 13- Clean series	Symbol	Specifications	Applicable bore size		ø12 to ø100		
25.4- Copper (Cu) and Zinc (Zn)-free *1 20- Copper and Fluorine-free *1 R/V Water resistant (NBR sealsuFKM *2) R/P Water resistant (NBR sealsuFKM *2) MGP□M Cylinder with stable lubrication function (Lube-retainer) MGP□M Guide unit with Lube-retainer MGP□M Guide unit with Lube-retainer MGP□M Change of guider od end shape -XA□ Change of guider od end shape -XBB Heat resistant cylinder (-10 to 150*C) *2 -XB10 Intermediate stroke (Using exclusive body) -XB13 Low speed cylinder (5 to 50 mm/s) -XB2 Shock absorber soft type RJ series type -XC4(W) With heavy duty scraper -XC6 Made of stainless steel -XC8 Adjustable stroke cylinder/Adjustable extension type -XC9 Adjustable stroke (Spacer type) -XC9 Rich Stroke sprinder/Adjustable retraction type *2 -XC35(W) With cold scraper -XC68 With shock absorber -XC89 With shock absorber -XC89 With shock absorber -XC89 Stroke mounting type -XC85 Grease for food processing equipment -XC88 Grease for food processing equipment -XC89 Subtra residant coll scraper, Libe-ristine, Cease for widing (Rod parts: S45C) -XC92(W) Dust resistant actuator *4 -XC91(W) Spatter residant coll scraper, Grease for widing (Rod parts: S45C) -XC92(W) Dust resistant actuator *4 -XC91(W) Spatter residant coll scraper, Grease for widing (Rod parts: S45C) -XC92(W) Dust resistant actuator *4 -XC91(W) Spatter residant coll scraper, Grease for widing (Rod parts: S45C) -XC92(W) Dust resistant actuator *4 -XC91(W) Spatter residant coll scraper, Grease for widing (Rod parts: S45C) -XC92(W) Dust resistant actuator *4 -XC91(W) Spatter residant coll scraper, Grease for widing (Rod parts: S45C) -XC92(W) Dust resistant actuator *4 -XC91(W) Spatter residant coll scraper, Grease for widing (Rod parts: S45C) -XC92(W) Dust resistant actuator *4 -XC91(W) Spatter resident coll scraper, Grease for widing (Rod parts: S45C) -XC92(W) Dust resistant actuator *4 -XC91(W) Spatter resident coll scraper, Grease for widing (Rod parts: S45C) -XC92(W) Dust resistant actuator *4 -XC91(W) Spatter resident coll scraper, Grease for widing (R	Standard	Basic type		•	•	•	
2-0 Copper and Fluorine-free *1 R/V Water resistant (NBR seale/FKM *2) MGP□M Oylinder with stable lubrication function (Lube-retainer) MGP□F With flange	12-, 13-	Clean series	ø12 to ø63	_	•	_	
20- Copper and Fluorine-free *1 R/V Water resistant (NBR sealer/FKM *2) MGP□M Cylinder with stable lubrication function (Lube-retainer) MGP□M Guide unit with Lube-retainer MGP□M Cylinder with stable lubrication function (Lube-retainer) MGP□M Cylinder with stable lubrication function (Lube-retainer) MGP□M Cylinder with stable lubrication function (Lube-retainer) MGP□M Cylinder (Stude unit with Lube-retainer MGP□M Cylinder (Stude ord and shape - XAB□ Change of guide rod end shape - XB6 Heat resistant cylinder (-10 to 150°C)*2 - XB10 Intermediate stroke (Using exclusive body) - XB11 Low speed cylinder (5 to 50 mm/s) - XB22 Shock absorber soft type RJ series type - XC84 Made of stainless steel - XC8 Adjustable stroke cylinder/Adjustable extension type - XC8 Adjustable stroke cylinder/Adjustable extension type - XC9 Adjustable stroke cylinder/Adjustable extension type - XC9 Intermediate stroke (Spacer type) - XC10 Intermediate stroke (Spacer type) - XC20 Fluororubber seal *2 - XC35(W) With coil scraper - XC69 With shock absorber - XC69 With shock absorber - XC69 With shock absorber - XC89 Softom mounting type - XC82 Grease for food processing equipment - XC88 Grease for food processing equipment - XC88 W Spilm resistent coil scraper, Libe-ritaine, Grease for welding (Rod parts SEQ) - XC89(W) Spilm resistent coil scraper, Libe-ritaine, Grease for welding (Rod parts SEQ) - XC89(W) Spilm resistent coil scraper, Libe-ritaine, Grease for welding (Rod parts SEQ) - XC89(W) Spilm resistent coil scraper, Libe-ritaine, Grease for welding (Rod parts SEQ) - XC89(W) Spilm resistent coil scraper, Libe-ritaine, Grease for welding (Rod parts SEQ) - XC89(W) Spilm resistent coil scraper, Libe-ritaine, Grease for welding (Rod parts SEQ) - XC89(W) Spilm resistent coil scraper, Libe-ritaine, Grease for welding (Rod parts SEQ) - XC89(W) Spilm resistent coil scraper, Grease for welding (Rod parts SEQ) - XC89(W) Spilm resistent coil scraper, Grease for welding (Rod parts SEQ) - XC89(W) Spilm resistent coil scraper, Grease for welding (Rod	25A-	Copper (Cu) and Zinc (Zn)-free *1	~10 to ~100	•	•	0	
MGPCM Cylinder with stable lubrication function (Lube-retainer)	20-	Copper and Fluorine-free *1	012100100	•	● *3	●*3	
MGPMIG Guide unit with Lube-retainer	R/V	Water resistant (NBR seals/FKM *2)		•	_	_	
MGPM□G Suide unit with Lube-retainer	MGP□M	Cylinder with stable lubrication function (Lube-retainer)	a20 to a100	•	•	0	
XAD	МСРМ□С	Guide unit with Lube-retainer	920 10 9 100	•	_	_	
ABB	MGP□F	With flange		● *5	•	•	
XB6	-XA□	Change of guide rod end shape	a12 to a100	0	0	0	
AB13	-XB6	Heat resistant cylinder (-10 to 150°C) *2	912109100	0	_	_	
-XB13	-XB10	Intermediate stroke (Using exclusive body)	a12 to a100	0	0	0	
-XC4(W) With heavy duty scraper -XC6 Made of stainless steel -XC8 Adjustable stroke cylinder/Adjustable extension type -XC9 Adjustable stroke cylinder/Adjustable retraction type *2 -XC19 Intermediate stroke (Spacer type) -XC22 Fluororubber seal *2 -XC35(W) With coil scraper -XC69 With shock absorber -XC69 With shock absorber -XC79 Tapped hole, drilled hole, pinned hole machined additionally -XC82 Bottom mounting type -XC83 Grease for food processing equipment -XC88 Grease for food processing equipment -XC89W Spatter resistant coil scraper, Lube-retainer, Grease for welding [Rod parts: Skifc) -XC91(W) Spatter resistant coil scraper, Lube-retainer, Grease for welding [Rod parts: Skifc) -XC92(W) Dust resistant coil scraper, Grease for welding (Rod parts: Skifc) -XC92(W) Dust resistant actuator *4 Symmetrical port position -X144 Symmetrical port position -XC81 Enlarged plate and body gap dimensions -XC81 Enlarged plate and body gap dimensions -XC81 Enlarged plate and body gap dimensions	-XB13	Low speed cylinder (5 to 50 mm/s)	812 10 8 100	0	0	_	
-XC6 Made of stainless steel -XC8 Adjustable stroke cylinder/Adjustable extension type -XC9 Adjustable stroke cylinder/Adjustable retraction type *2 -XC19 Intermediate stroke (Spacer type) -XC22 Fluororubber seal *2 -XC35(W) With coil scraper -XC69 With shock absorber -XC79 Tapped hole, drilled hole, pinned hole machined additionally -XC82 Bottom mounting type -XC85 Grease for food processing equipment -XC88(W) Spatter resistant coil scraper, Lube-retainer, Grease for welding (Rod parts: Stainless steel 34) -XC90(W) Dust resistant actuator *4 Symmetrical port position -X471 Enlarged plate and body gap dimensions **O 12 to 0100 **O 12 to 0100 **O 12 to 0100 **O 12 to 0100 **O 2 **O 12 to 0100 **O 12 to 0100	-XB22	Shock absorber soft type RJ series type	ø12 to ø100	0	0	0	
-XC8 Adjustable stroke cylinder/Adjustable extension type -XC9 Adjustable stroke (Spacer type) -XC19 Intermediate stroke (Spacer type) -XC22 Fluororubber seal *2 -XC35(W) With coil scraper -XC35(W) With shock absorber -XC69 With shock absorber -XC79 Tapped hole, drilled hole, pinned hole machined additionally -XC82 Bottom mounting type -XC85 Grease for food processing equipment -XC88(W) Spatter resistant coil scraper, Lube-retainer, Grease for welding (Rod parts: Starios sted 304) -XC89W Spatter resistant coil scraper, Lube-retainer, Grease for welding (Rod parts: S45C) -XC91(W) Dust resistant actuator *4 Symmetrical port position -X471 Enlarged plate and body gap dimensions	-XC4(W)	With heavy duty scraper	ø20 to ø100	0	0	0	
-XC9 Adjustable stroke cylinder/Adjustable retraction type *2 -XC19 Intermediate stroke (Spacer type) -XC22 Fluororubber seal *2 912 to 9100 -XC35(W) With coil scraper -XC35(W) With shock absorber -XC69 With shock absorber -XC79 Tapped hole, drilled hole, pinned hole machined additionally -XC82 Bottom mounting type -XC85 Grease for food processing equipment -XC88(W) Spatter resistant coil scraper, Lube-retainer, Grease for welding (Rod parts: S45C) -XC91(W) Spatter resistant coil scraper, Grease for welding (Rod parts: S45C) -XC92(W) Dust resistant actuator *4 Symmetrical port position 912 to 9100 912 to 9100 912 to 9100 913 to 9100 914 to 9100 915 to 9100 915 to 9100 916 to 9100 915 to 9100 916 to 9100 917 to 9100 918 to 9100 918 to 9100 919 to 9100 910 to 91000 910	-XC6	Made of stainless steel		0	0	_	
-XC19 Intermediate stroke (Spacer type)	-XC8	Adjustable stroke cylinder/Adjustable extension type	ø12 to ø100	0	0	0	
-XC22 Fluororubber seal *2 012 to 0100 ○ ─ ─ ─ -XC35(W) With coil scraper 020 to 0100 ○ ○ ○ -XC69 With shock absorber 050 to 0100 ○ ○ ○ -XC79 Tapped hole, drilled hole, pinned hole machined additionally ○ ○ ○ ○ -XC82 Bottom mounting type 012 to 0100 ○ ─ ─ -XC85 Grease for food processing equipment ○ ○ ○ ─ -XC88(W) Spatter resistant coil scraper, Lube-retainer, Grease for welding (Rod parts: Stainless steel 304) ○ ─ ─ -XC89W Spatter resistant coil scraper, Lube-retainer, Grease for welding (Rod parts: StSC) ○ ○ ─ -XC91(W) Spatter resistant coil scraper, Grease for welding (Rod parts: StSC) ○ ○ ○ -XC92(W) Dust resistant actuator *4 012 to 0100 ○ ─ ─ -X144 Symmetrical port position 012 to 0100 ○ ○ ○ -X471 Enlarged plate and body gap dimensions 012 to 063 ○ ○ ○	-XC9	Adjustable stroke cylinder/Adjustable retraction type *2		0	0	0	
-XC35(W) With coil scraper -XC69 With shock absorber -XC79 Tapped hole, drilled hole, pinned hole machined additionally -XC82 Bottom mounting type -XC85 Grease for food processing equipment -XC88(W) Spatter resistant coil scraper, Lube-retainer, Grease for welding (Rod parts: Staffor) -XC89W Spatter resistant coil scraper, Lube-retainer, Grease for welding (Rod parts: Staffor) -XC91(W) Spatter resistant coil scraper, Grease for welding (Rod parts: Staffor) -XC92(W) Dust resistant actuator *4 Symmetrical port position ### Spatter resistant coil scraper for welding (Rod parts: Staffor) ### Spatter resistant coil scraper for welding (Rod parts: Staffor) ### Spatter resistant actuator *4 ### Symmetrical port position ### Spatter resistant coil scraper for welding (Rod parts: Staffor) ### Spatter resistant actuator *4 ### Symmetrical port position ### Spatter resistant coil scraper for welding (Rod parts: Staffor) ### Spatter resistant actuator *4 ### Symmetrical port position ### Spatter resistant actuator *4 ### Symmetrical port position ### Spatter resistant actuator *4 ### Symmetrical port position ### Spatter resistant actuator *4 ### Spatter resistant actuator *4	-XC19	Intermediate stroke (Spacer type)	ø16 to ø100	_	_	_	
-XC69 With shock absorber	-XC22	Fluororubber seal *2	ø12 to ø100	0	_	_	
-XC79 Tapped hole, drilled hole, pinned hole machined additionally -XC82 Bottom mounting type -XC85 Grease for food processing equipment -XC86(W) Spatter resistant coll scraper, Lube-retainer, Grease for welding (Rod parts: Stainless steel 3M) -XC89W Spatter resistant coll scraper, Lube-retainer, Grease for welding (Rod parts: Stainless steel 3M) -XC91(W) Spatter resistant coll scraper, Grease for welding (Rod parts: Stafc) -XC92(W) Dust resistant actuator *4	-XC35(W)	With coil scraper	ø20 to ø100	0	0	0	
-XC82 Bottom mounting type -XC85 Grease for food processing equipment -XC88(W) Spatter resistant coil scraper, Lube-retainer, Grease for welding (Rod parts: Starilor Starilor) -XC89W Spatter resistant coil scraper, Lube-retainer, Grease for welding (Rod parts: Starilor) -XC91(W) Spatter resistant coil scraper, Grease for welding (Rod parts: StSC) -XC92(W) Dust resistant actuator *4 -X144 Symmetrical port position -X471 Enlarged plate and body gap dimensions	-XC69	With shock absorber	ø50 to ø100	0	0	0	
-XC85 Grease for food processing equipment -XC88(W) Spatter resistant coil scraper, Lube-retainer, Grease for welding (Rod parts: Stainless steel 304) -XC99W Spatter resistant coil scraper, Lube-retainer, Grease for welding (Rod parts: S45C) -XC91(W) Spatter resistant coil scraper, Grease for welding (Rod parts: S45C) -XC92(W) Dust resistant actuator *4 012 to 0100 0 0 0 -X144 Symmetrical port position 012 to 0100 0 0 -X471 Enlarged plate and body gap dimensions 012 to 063 0 0 0 0 0 0 0 0	-XC79	Tapped hole, drilled hole, pinned hole machined additionally		0	0	0	
-XC88(W) Spatter resistant coil scraper, Lube-retainer, Grease for welding (Rod parts: Stariless steel 304) -XC89W Spatter resistant coil scraper, Lube-retainer, Grease for welding (Rod parts: S45C) -XC91(W) Spatter resistant coil scraper, Grease for welding (Rod parts: S45C) -XC92(W) Dust resistant actuator *4	-XC82	Bottom mounting type	ø12 to ø100	0	_	_	
-XC89W Spatter resistant coil scraper, Lube-retainer, Grease for welding (Rod parts: S45C) -XC91(W) Spatter resistant coil scraper, Grease for welding (Rod parts: S45C) -XC92(W) Dust resistant actuator *4 Symmetrical port position ### 12 to ### 100 ###	-XC85	Grease for food processing equipment		0	0	0	
-XC91(W) Spatter resistant coil scraper, Grease for welding (Rod parts: S45C) -XC92(W) Dust resistant actuator *4 -X144 Symmetrical port position -X471 Enlarged plate and body gap dimensions ### 12 to ### 10 #	-XC88(W)	Spatter resistant coil scraper, Lube-retainer, Grease for welding (Rod parts: Stainless steel 304)		0	_	_	
-XC92(W) Dust resistant actuator *4	-XC89W	Spatter resistant coil scraper, Lube-retainer, Grease for welding (Rod parts: S45C)	ø32 to ø100	0	_	_	
-X144 Symmetrical port position Ø12 to Ø100 © ©	-XC91(W)	Spatter resistant coil scraper, Grease for welding (Rod parts: S45C)		0	0	0	
-X471 Enlarged plate and body gap dimensions ø12 to ø63 © O	-XC92(W)	Dust resistant actuator *4	ø12 to ø100	0	_	_	
	-X144	Symmetrical port position	ø12 to ø100	0	0	0	
-X867 Side porting type (Plug location changed) Ø12 to Ø100 © ©	-X471	Enlarged plate and body gap dimensions	ø12 to ø63	0	0	0	
	-X867	Side porting type (Plug location changed)	ø12 to ø100	0	0	0	

^{*1:} For details, refer to the Web Catalog.

^{*5:} This product cannot be used as a stopper.



O: Special product (Please contact SMC for details.)

^{-:} Not available

^{*2:} Without cushion

^{*3:} Copper and fluorine-free are available as standard products.

^{*4:} The shape is the same as the current product.

	Heavy duty guide *4 rod type	With air cushion With end lock *4									
	Slide bearing	Ball bushing High precision ball bushing		Slide bearing	High precision ball bushing	Ball bushing	Slide bearing				
	MGPS	MGPA	MGPL	МСРМ	MGPA	MGPL	МСРМ				
	584		575		558						
Symbol	ø50, ø80		ø20 to ø100		ø16 to ø100						
Standard	•	•	•	•	•	•	•				
12-, 13-	_	_	0	_	_	0	_				
25A-	0	0	0	0	0	0	0				
20-	0	0	0	0	●*3	•*3	•				
R/V	0	_	_	0	_	_	0				
MGP□M	0	0	0	0	0	0	0				
МСРМ□С	_	_	_	_	_	_	0				
MGP□F	0	0	0	0	0	0	0				
-XA□	_	0	0	0	0	0	0				
-XB6	0	_	_	0	_	_	0				
-XB10	0	0	0	0	0	0	0				
-XB13	0	_	0	0	_	_	_				
-XB22	0	0	0	0	_	_	_				
-XC4(W)	0	0	0	0	0	0	0				
-XC6	0	_	0	0	_	0	0				
-XC8	0	_	_	_	_	_	_				
-XC9	0	_	_	_	_	_	_				
-XC19	_	_	_	_	0	0	0				
-XC22	0	_	_	0	_	_	0				
-XC35(W)	0	0	0	0	0	0	0				
-XC69	0	0	0	0	_	_	_				
-XC79	0	0	0	0	0	0	0				
-XC82	0	_	_	0	_	_	0				
-XC85	0	0	0	0	0	0	0				
-XC88(W)	0	_	_	0	_	_	0				
-XC89W	0	_	_	0	_	_	0				
-XC91(W)	0	0	0	0	0	0	0				
-XC92(W)	0	_	_	0	_	_	0				
-X144	0	0	0	0	0	0	0				
-X471	0	0	0	0	0	0	0				
-X867	0	0	0	0	0	0	0				



CONTENTS

Compact Guide Cylinder MGP Series









■Compact Guide Cylinder/Basic	Туре	MGP-Z	Series
-------------------------------	------	-------	--------

How to Order ·····	Page 536
Specifications	Page 537
Clean Series ·····	Page 539
Water Resistant Cylinder	Page 540
Cylinder with Stable Lubrication Function (Lube-retainer)	Page 541
Guide Unit with Lube-retainer	Page 541
Model Selection	Page 545
Construction	Page 553
Dimensions	Page 555

Compact Guide Cylinder/With Air Cushion MGP-AZ Series

How to Order ·····	Page 558
Specifications	Page 559
Model Selection	Page 562
Construction	Page 570
Dimensions	Page 572

● Compact Guide Cylinder/With End Lock MGP Series

How to Order ·····	Page 575
Specifications	Page 576
Construction	Page 578
Dimensions ·····	Page 580
Specific Product Precautions	Page 583

Compact Guide Cylinder/Heavy Duty Guide Rod Type MGPS Series

How to Order ·····	Page 584
Specifications	Page 585
Model Selection	Page 586
Construction	Page 590
Dimensions	Page 59
Auto Switch Mounting	Page 592
Specific Braduot Bragautions	Dogo FOO



Compact Guide Cylinder

MGP Series


Ø12, Ø16, Ø20, Ø25, Ø32, Ø40, Ø50, Ø63, Ø80, Ø100

Water resistant cylinder (→ Refer to page 540.)

Dust resistant cylinder ⇒(Web Catalog)

Cylinder with stable lubrication function (Lube-retainer) (➡ Refer to page 541.)

How to Order



Applicable Auto Switches/Refer to pages 1289 to 1383 for further information on auto switches

P- P-	Applicable Auto Switches/heler to pages 1269 to 1363 to future information of auto switches.																																						
			Floatrical	Electrical	턆	Wiring	Load voltage		Auto switch model		Lead wire length [m]				Pre-wired	Applicable																							
Туре	e Special function Electrical entry		Indicator	(Output)	D	C	AC	Perpendicular	In-line	0.5 (Nil)	1 (M)	3 (L)	5 (Z)	connector		ad																							
				3-wire (NPN)		5 V. 12 V		M9NV	M9N	•	•	•	0	0	IC																								
등	_			3-wire (PNP)		5 V, 12 V		M9PV	M9P	•	•	•	0	0	circuit																								
switch				2-wire	5 V, 12 V 24 V 12 V 5 V, 12 V	12 V		M9BV	M9B	•	•	•	0	0	_]																							
]		3-wire (NPN)		5 V 40 V		VWN6W	M9NW	•	•	•	0	0	IC																								
anto	Diagnostic indication (2-color indicator)			3-wire (PNP)			[_			24 V		- 1			5 V, 12 V		M9PWV	M9PW	•	•	•	0	0	circuit	l									
	(2-color maicator)	Grommet	Yes	2-wire																24 V	12 V	12 V —	M9BWV	M9BW	•	•	•	0	0		Relay,								
state			3-wire (NPN)	514.4		5 V 40 V		M9NAV*1	M9NA*1	0	0	•	0	0	IC	1																							
	Water resistant (2-color indicator)			3-wire (PNP)		NP)]		5 V, 12 V		M9PAV*1	M9PA*1	0	0	•	0	0	circuit																				
Solid	(2-color indicator)			2-wire 2-wire (Non-polar)			12 V		M9BAV*1	M9BA*1	0	0	•	0	0]																						
တိ	Magnetic field resistant (2-color indicator)						_		1	P3DWA*2	•	_	•	•	0	_																							
Reed auto switch	anto Ich	Grommet	Yes	3-wire (NPN equivalent)	_	5 V	_	A96V	A96	•	_	•	_	_	IC circuit	_																							
ĕ.ĕ	_	Grommet		2-wire	24 V	12 V	100 V	A93V*3	A93	•	•	•	•	_	_	Relay,																							
8 "			No	2-wire	24 V	12 V	100 V or less	A90V	A90	•	-	•	_	_	IC circuit	PLĆ																							

- *1: Water resistant type auto switches are mountable on the above models, but in such case SMC cannot guarantee water resistance. A water resistant type cylinder is recommended for use in an environment which requires water resistance.
- However, please contact SMC for water resistant products of ø12 and ø16. *2: The D-P3DWA□ is mountable on bore size ø25 to ø100.
- *3: 1 m type lead wire is only applicable to the D-A93.
- *: Lead wire length symbols: 0.5 mNil (Example) M9NW
 - 1 m----- M (Example) M9NWM
 - (Example) M9NWL
 - 3 m L 5 m..... Z (Example) M9NWZ
- *: Solid state auto switches marked with " O " are produced upon receipt of order.
- *: Other than the auto switches listed above, the D-P4DW type can be mounted. Refer to page 595 for details.
- *: For details about auto switches with pre-wired connector, refer to pages 1358 and 1359.
- *: Auto switches are shipped together, (but not assembled).





Symbol Rubber bumper





Made to Order: Individual Specifications (For details, refer to pages 597 and 598.)

Symbol	Specifications
-X144	Symmetrical port position
-X471	Enlarged plate and body gap dimensions
-X867	Side porting type (Plug location changed)



Made to Order Click here for details

Symbol	Specifications
-ХА□	Change of guide rod end shape
-XB6	Heat resistant cylinder (-10 to 150°C)
-XB10	Intermediate stroke (Using exclusive body)
-XB13	Low speed cylinder (5 to 50 mm/s)
-XB22	Shock absorber soft type RJ series type
-XC4	With heavy duty scraper
-XC6	Made of stainless steel
-XC8	Adjustable stroke cylinder/Adjustable extension type
-XC9	Adjustable stroke cylinder/Adjustable retraction type
-XC22	Fluororubber seal
-XC35	With coil scraper
-XC69	With shock absorber
-XC79	Tapped hole, drilled hole, pinned hole machined additionally
-XC82	Bottom mounting type
-XC85	Grease for food processing equipment
-XC88	Spatter resistant coil scraper, Lube-retainer, Grease for welding (Rod parts: Stainless steel 304)
-XC89W	Spatter resistant coil scraper, Lube-retainer, Grease for welding (Rod parts: S45C)
-XC91	Spatter resistant coil scraper, Grease for welding (Rod parts: S45C)
-XC92	Dust resistant actuator *1

*1: The shape is the same as the current product.

Refer to pages 592 to 596 for cylinders with auto switches.

- Auto switch proper mounting position (detection at stroke end) and its mounting height
- Minimum stroke for auto switch mounting
- Operating range
- Auto switch mounting brackets/Part no.
- · Auto Switch Mounting

Specifications

Bore size [mm]	12	16	20	25	32	40	50	63	80	100
Action		Double acting								
Fluid		Air								
Proof pressure	1.5 MPa									
Maximum operating pressure	1.0 MPa									
Minimum operating pressure	0.12 MPa 0.1 MPa									
Ambient and fluid temperature	-10 to 60°C (No freezing)									
Piston speed *1	50 to 500 mm/s 50 to					50 to 40	00 mm/s			
Cushion	Rubber bumper on both ends									
Lubrication	Not required (Non-lube)									
Stroke length tolerance					+1.5 0	mm				

^{*1:} Maximum speed with no load. Depending on the operating conditions, the piston speed may not be satisfied.

Make a model selection, considering a load according to the graph on pages 545 to 551.

Standard Strokes

Bore size [mm]	Standard stroke [mm]
12, 16	10, 20, 30, 40, 50, 75, 100, 125, 150, 175, 200, 250
20, 25	20, 30, 40, 50, 75, 100, 125, 150, 175, 200, 250, 300, 350, 400
32 to 100	25, 50, 75, 100, 125, 150, 175, 200, 250, 300, 350, 400

Manufacture of Intermediate Strokes

Description	ø12 to ø32: Available	i type e standard stroke cylinder. in 1 mm stroke increments. e in 5 mm stroke increments.		B10) making an exclusive body. lable in 1 mm increments.		
Model no.	Refer to How to Order for t	he standard model numbers.	Add "-XB10" to the end of standard model number. For details, refer to Made to Order.			
	ø12, ø16	1 to 249	ø12, ø16	11 to 249		
Applicable stroke [mm]	ø20, ø25, ø32	1 to 399	ø20, ø25	21 to 399		
Stroke [mm]	ø40 to ø100	5 to 395	ø32 to ø100	26 to 399		
Example	Part no.: MGPM20 A spacer 1 mm in widi MGPM20-40. C dimer	th is installed in the	Part no.: MGPM20-39Z-XB10 Special body manufactured for 39 stroke. C dimension is 76 mm.			

Theoretical Output

								OL	JT _		IN	
									→ [-	_	[N
Bore size	Rod size	Operating	Piston area			Op	erating	press	ure [MF	Pa]		
[mm]	[mm]	direction	[mm²]	0.2	0.3	0.4	0.5	0.6	0.7	0.8	0.9	1.0
12	6	OUT	113	23	34	45	57	68	79	90	102	113
12		IN	85	17	25	34	42	51	59	68	76	85
16	8	OUT	201	40	60	80	101	121	141	161	181	201
10	٥	IN	151	30	45	60	75	90	106	121	136	151
20	10	OUT	314	63	94	126	157	188	220	251	283	314
20	10	IN	236	47	71	94	118	141	165	188	212	236
25	10	OUT	491	98	147	196	245	295	344	393	442	491
20	10	IN	412	82	124	165	206	247	289	330	371	412
32	14	OUT	804	161	241	322	402	483	563	643	724	804
32	14	IN	650	130	195	260	325	390	455	520	585	650
40	14	OUT	1257	251	377	503	628	754	880	1005	1131	1257
40	14	IN	1103	221	331	441	551	662	772	882	992	1103
50	18	OUT	1963	393	589	785	982	1178	1374	1571	1767	1963
50	10	IN	1709	342	513	684	855	1025	1196	1367	1538	1709
63	18	OUT	3117	623	935	1247	1559	1870	2182	2494	2806	3117
US	10	IN	2863	573	859	1145	1431	1718	2004	2290	2576	2863
80	22	OUT	5027	1005	1508	2011	2513	3016	3519	4021	4524	5027
80		IN	4646	929	1394	1859	2323	2788	3252	3717	4182	4646
100	26	OUT	7854	1571	2356	3142	3927	4712	5498	6283	7069	7854
100	20	IN	7323	1465	2197	2929	3662	4394	5126	5858	6591	7323

^{*:} Theoretical output [N] = Pressure [MPa] x Piston area [mm²]




Weights

Slide Bearing	ng: MC	3PM1	2 to 1	00												[kg]
Bore size							St	andard s	troke [m	m]						
[mm]	10	20	25	30	40	50	75	100	125	150	175	200	250	300	350	400
12	0.22	0.25	_	0.29	0.33	0.36	0.46	0.55	0.66	0.75	0.84	0.93	1.11	_	_	_
16	0.32	0.37	_	0.42	0.46	0.51	0.66	0.78	0.94	1.06	1.18	1.31	1.55	_	_	_
20	_	0.59	_	0.67	0.74	0.82	1.06	1.24	1.43	1.61	1.80	1.99	2.42	2.79	3.16	3.53
25	-	0.84	_	0.94	1.04	1.14	1.50	1.75	2.00	2.25	2.50	2.75	3.35	3.85	4.34	4.84
32	_	_	1.41	_	_	1.77	2.22	2.57	2.93	3.29	3.65	4.00	4.90	5.61	6.33	7.04
40	_	_	1.64	_	_	2.04	2.52	2.92	3.32	3.71	4.11	4.50	5.47	6.26	7.06	7.85
50	-	_	2.79	_	_	3.38	4.13	4.71	5.30	5.89	6.47	7.06	8.55	9.73	10.9	12.1
63	_	_	3.48	_	_	4.15	4.99	5.67	6.34	7.02	7.69	8.37	10.0	11.4	12.7	14.1
80	l –	_	5.41	_	_	6.26	7.41	8.26	9.10	9.95	10.8	11.6	13.9	15.6	17.3	19.0
100	_	_	9.12	_	_	10.3	12.0	13.2	14.4	15.6	16.9	18.1	21.2	23.6	26.1	28.5


Ball Bushin	g: MG	iPL12	to 10	0, Hig	jh Pre	cisio	า Ball	Bush	ing: N	IIGPA	12 to	100				[kg]
Bore size							St	andard s	stroke [m	m]						
[mm]	10	20	25	30	40	50	75	100	125	150	175	200	250	300	350	400
12	0.21	0.24	_	0.27	0.32	0.35	0.43	0.50	0.59	0.67	0.75	0.83	0.99	_	_	_
16	0.31	0.35	_	0.40	0.47	0.51	0.62	0.72	0.85	0.96	1.06	1.17	1.38	_	_	_
20	-	0.60	_	0.66	0.79	0.85	1.01	1.17	1.36	1.52	1.68	1.84	2.17	2.49	2.81	3.13
25	I -	0.87	_	0.96	1.12	1.20	1.41	1.62	1.86	2.06	2.27	2.48	2.92	3.33	3.75	4.16
32	-	_	1.37	_	_	1.66	2.08	2.37	2.74	3.03	3.31	3.60	4.25	4.82	5.39	5.97
40	-	_	1.59	_	_	1.92	2.38	2.70	3.11	3.44	3.77	4.09	4.81	5.46	6.11	6.76
50	I -	_	2.65	_		3.14	3.85	4.34	4.97	5.47	5.96	6.45	7.57	8.56	9.54	10.5
63	I -	_	3.33	_	_	3.91	4.71	5.29	6.01	6.59	7.17	7.75	9.05	10.2	11.4	12.5
80	I -	_	5.27	_	_	6.29	7.49	8.21	8.92	9.64	10.4	11.1	12.9	14.3	15.7	17.2
100		_	8.62	_		10.1	11.8	12.9	13.9	15.0	16.0	17.1	19.6	21.7	23.8	25.9

Compact Guide Cylinder MGP Series

1)Clean Series



How to Order




Specifications

Applicable series				MG	iPL			
Bearing type			Ball	bushi	ng bea	ring		
Bore size [mm]	12	16	20	25	32	40	50	63
Stroke [mm]	10 to	250	20 to	400		25 to	400	

*: Specifications other than above are the same as standard, basic type.

*: For bore sizes 12 and 16,

Dimensions



*: For details, refer to the Web Catalog.

*: Other dimensions are the same as standard products. *: The dimensions in () are the same as standard type. [mm]

D i			Α				
Bore size [mm]	30 st or less	Over 30 st and up to 100 st	Over 100 st and up to 200 st	Over 200 st	В	DA	FB
12	56	68	97.5	97.5	55	(6)	19
16	62	78	107.5	107.5	59	(8)	19
20	72	89	113	130.5	66	(10)	21
25	78.5	94.5	113.5	130.5	66.5	(10)	20

*: For bore size ø12 and ø16, only M5 x 0.8 port is available.

*: For bore size ø20 or more, choice of Rc, NPT, G port is available. (Refer to page 536.)


D			Α				
Bore size [mm]	50 st		В	DA	FB		
32	91.5	108.5	128.5	150.5	71.5	(14)	24
40	91.5	108.5	128.5	150.5	78	(14)	24
50	102.5	123.5	143.5	170.5	83	20	27
63	102.5	123.5	143.5	170.5	88	20	27

*: Choice of Rc, NPT, G port is available. (Refer to page 536.)

2 Water Resistant Cylinder

Ideal for use in a machine tool environment exposed to coolants. Applicable for use in an environment with water splashing such as food processing and car wash equipment, etc.

How to Order



- *: Piston rod and guide rod are made of stainless steel.
- *: Please contact SMC when using liquids that contain sulfur.

Made to Order




Specifications

Applica	ble series	MGPM				
Bearing type		Slide bearing				
Bore size [mm]		20, 25, 32, 40, 50, 63, 80, 100				
Cushion MGPM□□R		Rubber bumper				
MGPM□□V		Without cushion				
Minimum operating pressure		0.13 MPa				
Made to Order XC6A		Specified parts made of stainless steel				

- *: Bore sizes 12 and 16 mm are only available as a special order. Contact SMC for further details.
- *: Specifications other than above are the same as standard, basic type.
- *: For details on the made-to-order XC6A with specified parts made of stainless steel, refer to page 1488.

Dimensions



Water resistant

Danie sie s		Α					
Bore size [mm]	50 st or less	Over 50 st and up to 200 st	Over 200 st	В	DA	FA	FB
20	66	90.5	123	66	(10)	(8)	21
25	67.5	91.5	123.5	67.5	(10)	(9)	21
32	87	105.5	141.5	71.5	(14)	(10)	24
40	87	105.5	141.5	78	(14)	(10)	24
50	99.5	120.5	161.5	83	20	(12)	27
63	99.5	120.5	161.5	88	20	(12)	27
80	110.5	137.5	186.5	102.5	25	(16)	30
100	130.5	155.5	194.5	120	30	(19)	35

Water resistant + XC6A

Гn	or	'n

[mm]

David diam		Α					
Bore size [mm]	50 st or less	Over 50 st and up to 200 st		В	DA	FA	FB
20	66	90.5	123	66	(10)	9	20
25	67.5	91.5	123.5	67.5	(10)	10	20
32	87	105.5	141.5	71.5	(14)	12	22
40	87	105.5	141.5	78	(14)	12	22
50	99.5	120.5	161.5	83	20	16	23
63	99.5	120.5	161.5	88	20	16	23
80	110.5	137.5	186.5	102.5	25	19	27
100	130.5	155.5	194.5	120	30	22	32

- *: Other dimensions are the same as standard products.
- *: The dimensions in () are the same as standard type.

Click here for details.

3Cylinder with Stable Lubrication Function (Lube-retainer)

Improves durability in environments with micro-powder. (Compared with the standard model) In addition, the overall length and mounting are the same as those of the standard model.

How to Order

MGP Bearing type Bore size Port thread type M - Stroke Z - Auto switch


Cylinder with stable lubrication function (Lube-retainer)

Specifications

Bore size [mm]	20, 25, 32, 40, 50, 63, 80, 100
Minimum operating pressure	0.15 MPa

- *: Bore sizes 12 and 16 mm are only available as a special order. Contact SMC for further details.
- *: Specifications other than above are the same as standard, basic type.






Click here for details.

4 Guide Unit with Lube-retainer

How to Order




Specifications

Bore size [mm]	20, 25, 32, 40, 50, 63, 80, 100
Bearing type	Slide bearing

- *: Bore sizes 12 and 16 mm are only available as a special order. Contact SMC for further details.
- *: Specifications other than above are the same as standard, basic type.

Dimensions (Dimensions other than below are the same as standard type.)



						[mm]
D		Α			E	
Bore size [mm]	50 st or less	Over 50 st to 200 st	Over 200 st	50 st or less	Over 50 st to 200 st	Over 200 st
20	(53)	83	115.5	(0)	30	62.5
25	(53.5)	83.5	115.5	(0)	30	62
32	82	100.5	136.5	22.5	41	77
40	82	82 100.5		16	34.5	70.5
50	95.5	116.5	157.5	23.5	44.5	85.5
63	95.5	116.5	157.5	18.5	39.5	80.5
80	113.5	140.5	189.5	17	44	93
100	135.5	160.5	199.5	19.5	44.5	83.5


The dimensions in () are the same as standard type.



5With Flange

Plate side flange type is added.

How to Order




Specifications: Same as standard type

∆ Caution

This product cannot be used as a stopper.


 $\label{eq:Dimensions} \textbf{Dimensions} \mbox{ (Dimensions other than below are the same as standard type.)}$



												(111111)	
Bore size	В	С	FA	FB	FC	FD	FE	FF	FG	FH	G	Н	Flange weight (kg)
12	42	29	7	6	80	89	18	25	4.5	5	26	58	0.08
16	46	33	7	6	88	98	22	32	5.5	5	30	64	0.11
20	53	37	8	8	102	112	24	38	5.5	6	36	83	0.17
25	53.5	37.5	9	7	114	126	30	40	6.6	6	42	93	0.20
32	59.5	37.5	10	12	138	154	34	50	9	9	48	112	0.46
40	66	44	10	12	146	162	40	60	9	9	54	120	0.60
50	72	44	12	16	178	198	46	65	11	10	64	148	0.87
63	77	49	12	16	192	212	58	75	11	10	78	162	1.09
80	96.5	56.5	16	24	238	262	54	90	13.5	16	91.5	202	2.59
100	116	66	19	31	280	308	62	100	15.5	22	111.5	240	4.63




Allowable Rotational Torque of Plate



T [N·m]

Bore size	Descring tons		Stroke [mm] 10 20 25 30 40 50 75 100 125 150 175 200 250 300 350 400														
[mm]	Bearing type	10	20	25	30	40	50	75	100	125	150	175	200	250	300	350	400
12	MGPM	0.39	0.32	_	0.27	0.24	0.21	0.43	0.36	0.31	0.27	0.24	0.22	0.19	_	_	_
12	MGPL/A	0.61	0.45	_	0.35	0.58	0.50	0.37	0.29	0.24	0.20	0.18	0.16	0.12	_	_	_
16	MGPM	0.69	0.58	_	0.49	0.43	0.38	0.69	0.58	0.50	0.44	0.40	0.36	0.30	_	_	_
16	MGPL/A	0.99	0.74	_	0.59	0.99	0.86	0.65	0.52	0.43	0.37	0.32	0.28	0.23	_	_	_
20	MGPM	_	1.05	_	0.93	0.83	0.75	1.88	1.63	1.44	1.28	1.16	1.06	0.90	0.78	0.69	0.62
20	MGPL/A	_	1.26	_	1.03	2.17	1.94	1.52	1.25	1.34	1.17	1.03	0.93	0.76	0.65	0.56	0.49
25	MGPM	_	1.76	_	1.55	1.38	1.25	2.96	2.57	2.26	2.02	1.83	1.67	1.42	1.24	1.09	0.98
25	MGPL/A	_	2.11	_	1.75	3.37	3.02	2.38	1.97	2.05	1.78	1.58	1.41	1.16	0.98	0.85	0.74
32	MGPM	_	_	6.35	_	_	5.13	5.69	4.97	4.42	3.98	3.61	3.31	2.84	2.48	2.20	1.98
32	MGPL/A	_	_	5.95	_	_	4.89	5.11	4.51	6.34	5.79	5.33	4.93	4.29	3.78	3.38	3.04
40	MGPM	_	_	7.00	_	_	5.66	6.27	5.48	4.87	4.38	3.98	3.65	3.13	2.74	2.43	2.19
40	MGPL/A	_	_	6.55	_	_	5.39	5.62	4.96	6.98	6.38	5.87	5.43	4.72	4.16	3.71	3.35
50	MGPM	_	_	13.0	_	_	10.8	12.0	10.6	9.50	8.60	7.86	7.24	6.24	5.49	4.90	4.43
30	MGPL/A	_	_	9.17	_	_	7.62	9.83	8.74	11.6	10.7	9.83	9.12	7.95	7.02	6.26	5.63
63	MGPM	_	_	14.7	I	_	12.1	13.5	11.9	10.7	9.69	8.86	8.16	7.04	6.19	5.52	4.99
03	MGPL/A	_	_	10.2	_	_	8.48	11.0	9.74	13.0	11.9	11.0	10.2	8.84	7.80	6.94	6.24
80	MGPM	_	_	21.9	_	_	18.6	22.9	20.5	18.6	17.0	15.6	14.5	12.6	11.2	10.0	9.11
30	MGPL/A	_	_	15.1	I	_	23.3	22.7	20.6	18.9	17.3	16.0	14.8	12.9	11.3	10.0	8.94
100	MGPM	_	_	38.8	_	_	33.5	37.5	33.8	30.9	28.4	26.2	24.4	21.4	19.1	17.2	15.7
100	MGPL/A	_	_	27.1	_	_	30.6	37.9	34.6	31.8	29.3	27.2	25.3	22.1	19.5	17.3	15.5

Non-rotating Accuracy of Plate



Non-rotating accuracy θ when retracted and when no load is applied should be not more than the values shown in the table.


Bore size	N	on-rotating accuracy	θ
[mm]	MGPM	MGPL	MGPA
12	10.070	10.050	
16	±0.07°	±0.05°	
20	±0.06°	±0.04°	
25	±0.06	10.04	
32	±0.05°	±0.03°	±0.01°
40	±0.05	10.03	±0.01
50	±0.04°	±0.03°	
63	±0.04	±0.03	
80	±0.03°	±0.03°	
100	±0.03	±0.03	

High Precision Ball Bushing/MGPA

∧ Caution

Positioning accuracy for pin hole on the plate


Dispersion of dimensions when machining each component will be accumulated in the plate pin hole positioning accuracy when mounting this cylinder. Values below are referred as a guide.



 $A = Catalog dimension \pm (0.1 + L_1 \times 0.0008) [mm]$

*: To be 0.15 for ø80, ø100


Note) Displacement by load and self-weight deflection by plate and guide rod are not included.




 $\mathbf{B} = \pm (0.045 + \mathbf{L}_2 \times 0.0016) \text{ [mm]}$




High Precision Ball Bushing/MGPA Plate Displacement Amount (Reference Values)




MGPA12




MGPA32, 40




MGPA16




MGPA50, 63




MGPA20




MGPA80



MGPA25




MGPA100



- *: The guide rod and self-weight for the plate are not included in the above displacement values.
- *: Allowable rotating torque, and operating range when used as a lifter, are the same as those of the MGPL series.

Basic Type MGP Series **Model Selection**

Selection Conditions



Selection Example 1 (Vertical Mounting)

Selection conditions

Mounting: Vertical

Bearing type: Ball bushing

Stroke: 30 stroke


Maximum speed: 200 mm/s

Load mass: 3 kg Eccentric distance: 90 mm

Find the point of intersection for the load mass of 3 kg and the eccentric distance of 90 mm on graph (5), based on vertical mounting, ball bushing, 30 stroke, and the speed of 200 mm/s.

→ MGPL25-30Z is selected.

(5) 30 stroke or less, V = 200 mm/s or less



Selection Example 2 (Horizontal Mounting)

Selection conditions

Mounting: Horizontal

Bearing type: Slide bearing

Distance between plate and load center of gravity: 50 mm


Maximum speed: 200 mm/s

Load mass: 2 kg Stroke: 30 stroke

Find the point of intersection for the load mass of 2 kg and 30 stroke on graph (13), based on horizontal mounting, slide bearing, the distance of 50 mm between the plate and load center of gravity, and the speed of 200 mm/s.

→ MGPM20-30Z is selected.

(13) L = 50 mm, V = 200 mm/s or less



· When the maximum speed exceeds 200 mm/s, the allowable load mass is determined by multiplying the value shown in the graph at 400 mm/s by the coefficient listed in the table below.

Max. speed	Up to 300 mm/s	Up to 400 mm/s	Up to 500 mm/s
Coefficient	1.7	1	0.6


[·] Use the Guide Cylinder Selection Software, when the eccentric distance is 200 mm or more.





Vertical Mounting Slide Bearing


Operating pressure 0.4 MPa ---- Operating pressure 0.5 MPa or more

MGPM12 to 100










 $[\]cdot$ Use the Guide Cylinder Selection Software, when the eccentric distance is 200 mm or more.





Model Selection MGP Series

Operating pressure 0.4 MPa
---- Operating pressure 0.5 MPa or more

Vertical Mounting Ball Bushing


MGPL12 to 25, MGPA12 to 25






MGPL32 to 100, MGPA32 to 100

(7) 50 stroke or less, V = 200 mm/s or less



10

Eccentric distance L [mm]



Eccentric distance L [mm]

(8) Over 50 stroke, V = 200 mm/s or less

100 200




 $[\]cdot$ Use the Guide Cylinder Selection Software, when the eccentric distance is 200 mm or more.


L m m m

Vertical Mounting Ball Bushing


Operating pressure 0.4 MPa


MGPL12 to 25, MGPA12 to 25






MGPL32 to 100, MGPA32 to 100







 $[\]cdot$ Use the Guide Cylinder Selection Software, when the eccentric distance is 200 mm or more.





Horizontal Mounting Slide Bearing

MGPM12 to 100











(15) L = 50 mm, V = 400 mm/s




(16) L = 100 mm, V = 400 mm/s




Horizontal Mounting Ball Bushing


(17) L = 50 mm, V = 200 mm/s or less




MGPL32 to 63, MGPA32 to 63




MGPL80/100, MGPA80/100




(18) L =100 mm, V = 200 mm/s or less



MGPL32 to 63, MGPA32 to 63




MGPL80/100, MGPA80/100






Horizontal Mounting Ball Bushing

(19) L = 50 mm, V = 400 mm/s




Stroke [mm]


MGPL32 to 63, MGPA32 to 63




MGPL80/100, MGPA80/100




(20) L =100 mm, V = 400 mm/s




MGPL32 to 63, MGPA32 to 63





Operating Range when Used as Stopper

Bore Size: Ø12 to Ø25/MGPM12 to 25 (Slide Bearing)




*: When selecting a model with a longer L dimension, be sure to choose a bore size which is sufficiently large.

△ Caution


Caution on handling

- When using as a stopper, select a model with 30 stroke or less.
- The MGPL (Ball bushing) and the MGPA (High precision ball bushing) cannot be used as a stopper.

MGPM12 to 25 (Slide Bearing)



Bore Size: Ø32 to Ø100/MGPM32 to 100 (Slide Bearing)




*: When selecting a model with a longer L dimension, be sure to choose a bore size which is sufficiently large.

⚠ Caution

Caution on handling

- When using as a stopper, select a model with 50 stroke or less.
- The MGPL (Ball bushing) and the MGPA (High precision ball bushing) cannot be used as a stopper.


MGPM32 to 100 (Slide Bearing)





*: Refer to graphs (13) and (15) if line pressure is applied by a roller conveyor after the workpiece is stopped.

Construction/MGPM Series


MGPM12 to 25








MGPM32 to 100





Component Parts

Description	Material		Note		
Body	Aluminum alloy	Hard	anodized		
Piston	Aluminum alloy				
Distance and	Stainless steel	ø1:	2 to ø25		
Piston roa	Carbon steel	ø32 to ø100	Hard chrome plating		
Collar	Aluminum alloy	Ch	romated		
Head carrer	Alumainum allau	ø12 to ø63	Chromated		
nead cover	Aluminum alloy	ø80, ø100	Painted		
Guide rod	Carbon steel	Hard ch	rome plating		
Plate	Carbon steel	Nick	el plating		
Plate mounting bolt	Carbon steel	Nick	el plating		
Guide bolt	Carbon steel	Nick	el plating		
Retaining ring	Carbon tool steel	Phosp	hate coated		
Retaining ring	Carbon tool steel	Phosp	hate coated		
Bumper A	Urethane				
Bumper B	Urethane				
Magnet	_				
Plug	Carbon atool	ø12, ø16 Nickel plating			
Hexagon socket head plug	Carbon Steel	ø20 to ø100			
Slide bearing	Bearing alloy				
	Body Piston Piston rod Collar Head cover Guide rod Plate Plate mounting bolt Guide bolt Retaining ring Retaining ring Bumper A Bumper B Magnet Plug Hexagon socket head plug	Body Aluminum alloy Piston Aluminum alloy Piston rod Stainless steel Carbon steel Collar Aluminum alloy Head cover Aluminum alloy Guide rod Carbon steel Plate Carbon steel Plate Manufinum alloy Carbon steel Guide bolt Carbon steel Guide bolt Carbon steel Retaining ring Carbon tool steel Bumper A Urethane Bumper B Urethane Magnet — Plug Hexagon socket headplug Carbon steel Carbon steel	Body		

^{*:} A felt is not installed on the slide bearing.

Component Parts

No.	Description	Material		Note
17	Ball bushing			
18	Spacer	Aluminum alloy		
19	Steel ball	Carbon steel	ø12	2 to ø50
20	Plug	Carbon steel	ø63 to ø100	Nickel plating
21*	Piston seal	NBR		
22*	Rod seal	NBR		
23*	Gasket A	NBR		
24*	Gasket B	NBR		

Replacement Parts/Seal Kit

Bore s		Kit no.	Contents	Bore size [mm]	Kit no.	Contents
12	- 1	MGP12-Z-PS	Set of	40	MGP40-Z-PS	Set of
16		MGP16-Z-PS	nos.	50	MGP50-Z-PS	nos.
20		MGP20-Z-PS	above	63	MGP63-Z-PS	above
25		MGP25-Z-PS	21), 22,	80	MGP80-Z-PS	21), 22,
32		MGP32-Z-PS	23, 24	100	MGP100-Z-PS	23, 24


- *: Seal kit includes ② to ②. Order the seal kit, based on each bore size.
- *: Since the seal kit does not include a grease pack, order it separately.


 Grease pack part number: GR-S-010 (10 g)




Construction/MGPL Series, MGPA Series

MGPL12 to 25 MGPA12 to 25






MGPL32 to 100 MGPA32 to 100










Ø32 to Ø63 Over 100 stroke Ø80, Ø100 Over 200 stroke


Ø12 to Ø25/MGPM, MGPL, MGPA






Bottom view







- *1: Refer to Section EE details for the shape of ø12 to ø25 with stroke of 50 or less.
- *: The use of a slot (width XA, length XB, depth 3) allows for a relaxed pin pitch tolerance, with the pin hole (øXAH9, depth 6) as the reference, without affecting mounting accuracy.
- *: For intermediate strokes other than standard strokes, refer to Manufacture of Intermediate Strokes on page 537.
- *: For bore size Ø12 and Ø16, only M5 x 0.8 port is available.
- *: For bore size ø20 or more, choice of Rc, NPT, G port is available. (Refer to page 536.)

MGPM	MGPM, MGPL, MGPA Common Dimensions [mm]																								
Bore size	Standa	rd stroke	[mm]	В	С	DA	FA	FB	G	GA	GВ	н	на	J	к	L	мм	ML	NN	ОА	ов	OL		P	
[mm]																							Nil	TN	TF
12	10, 20, 3	0, 40, 50,	75, 100	42	29	6	7	6	26	10	7	58	M4	13	13	18	M4 x 0.7	10	M4 x 0.7	4.3	8	4.5	M5 x 0.8	_	-
16	125, 15	0, 175, 20	0, 250	46	33	8	7	6	30	10.5	7.5	64	M4	15	15	22	M5 x 0.8	12	M5 x 0.8	4.3	8	4.5	M5 x 0.8	_	_
20	20, 30, 40,	50, 75, 100,	125, 150	53	37	10	8	8	36	11.5	9	83	M5	18	18	24	M5 x 0.8	13	M5 x 0.8	5.4	9.5	5.5	Rc1/8	NPT1/8	G1/8
25	175, 200	250, 300, 3	50, 400	53.5	37.5	10	9	7	42	11.5	10	93	M5	21	21	30	M6 x 1.0	15	M6 x 1.0	5.4	9.5	5.5	Rc1/8	NPT1/8	G1/8
D :											W	/Δ					,	ΝR							

Bore size					_	_	_	١					WA					WB					V-	vv		_
[mm]	PA	PB	PW	Q	R	S	'	U	VA	VB		Over 30 st 100 st or less	Over 100 st 200 st or less	Over 200 st 300 st or less	Over 300 st	30 st or less	Over 30 st 100 st or less	Over 100 st 200 st or less	Over 200 st 300 st or less	Over 300 st	X	XA	XB	YY	YL	
12	13	8	18	14	48	22	56	41	50	37	20	40	110	200	_	15	25	60	105		23	3	3.5	M5 x 0.8	10	5
16	14.5	10	19	16	54	25	62	46	56	38	24	44	110	200	_	17	27	60	105	_	24	3	3.5	M5 x 0.8	10	5
20	13.5	10.5	25	18	70	30	81	54	72	44	24	44	120	200	300	29	39	77	117	167	28	3	3.5	M6 x 1.0	12	17
25	12.5	13.5	30	26	78	38	91	64	82	50	24	44	120	200	300	29	39	77	117	167	34	4	4.5	M6 x 1.0	12	17

MGPM (Slide bearing) A, DB, E Dimensions

Bore size			4						
[mm]	50 st or less		Over 100 st 200 st or less		DB	50 st or less		Over 100 st 200 st or less	Over 200 st
12	42	60.5	82.5	82.5	8	0	18.5	40.5	40.5
16	46	64.5	92.5	92.5	10	0	18.5	46.5	46.5
20	53	77.5	77.5	110	12	0	24.5	24.5	57
25	53.5	77.5	77.5	109.5	16	0	24	24	56


MGPL (Ball bushing)


1]	MGPA (High p	recisio	n ball l	oushin	ıg) /	A, DB,	E Dime	ensions	[mm]
	Bore size			4				Е	•	
	[mm]	30 st or less	Over 30 st 100 st or less	Over 100 st 200 st or less		DB	30 st or less	Over 30 st 100 st or less	Over 100 st 200 st or less	Over 200 st
	12	43	55	84.5	84.5	6	1	13	42.5	42.5
	16	49	65	94.5	94.5	8	3	19	48.5	48.5
_	20	E0.	76	100	1175	10	-	22	47	64 5


65.5 81.5 100.5 117.5 13


47

Ø32 to Ø63/MGPM, MGPL, MGPA









- *: The use of a slot (width XA, length XB, depth XC) allows for a relaxed pin pitch tolerance, with the pin hole (øXAHe, depth XL) as the reference, without affecting mounting accuracy.
- *: For intermediate strokes other than standard strokes, refer to Manufacture of Intermediate Strokes on page 537.
- *: Choice of Rc, NPT, G port is available. (Refer to page 536.)

MGPM	, MGPL, MG	ŝΡΑ	Co	mn	non	Dir	ner	nsic	ns														[mm]
Bore size		В	С	ПΔ	FΔ	FR	G	GΔ	GB	н	на	.1	к		мм	мь	NN	OA	OB	OI		P	
[mm]	stroke [mm]	-	•		. ~		_	~ _	u.	١		Ŭ	l '``	-			''''		"	-	Nil	TN	TF
32	25, 50, 75	59.5	37.5	14	10	12	48	12	9	112	M6	24	24	34	M8 x 1.25	20	M8 x 1.25	6.7	11	7.5	Rc1/8	NPT1/8	G1/8
40	100, 125, 150	66	44	14	10	12	54	15	12	120	M6	27	27	40	M8 x 1.25	20	M8 x 1.25	6.7	11	7.5	Rc1/8	NPT1/8	G1/8
50	175, 200, 250	72	44	18	12	16	64	15	12	148	M8	32	32	46	M10 x 1.5	22	M10 x 1.5	8.6	14	9	Rc1/4	NPT1/4	G1/4
63	300, 350, 400	77	49	18	12	16	78	15.5	13.5	162	M10	39	39	58	M10 x 1.5	22	M10 x 1.5	8.6	-	9	Rc1/4	NPT1/4	G1/4

Bore si	zel 🕳 .	. I.		-	_		_	- 1						WA					WD			· ·		VD	\v_0		vv	\/ı	-
[mm]	P/	4	РВ	PW	Q	н	S	'	U	VA	VВ	25 st or less	Over 25 st 100 st or less	Over 100 st 200 st or less	Over 200 st 300 st or less	Over 300 st	25 st or less	Over 25 st 100 st or less	Over 100 st 200 st or less	Over 200 st 300 st or less	Over 300 st	X	XA	XB	хс	XL	YY	YL	
32	6.	.5 1	16	35.5	30	96	44	110	78	98	63	24	48	124	200	300	33	45	83	121	171	42	4	4.5	3	6	M8 x 1.25	16	21
40	13	1	18	39.5	30	104	44	118	86	106	72	24	48	124	200	300	34	46	84	122	172	50	4	4.5	3	6	M8 x 1.25	16	22
50	9	2	21.5	47	40	130	60	146	110	130	92	24	48	124	200	300	36	48	86	124	174	66	5	6	4	8	M10 x 1.5	20	24
63	13	2	28	58	50	130	70	158	124	142	110	28	52	128	200	300	38	50	88	124	174	80	5	6	4	8	M10 x 1.5	20	24


MGPM (Slide bearing) A, DB, E Dimensions


Bore size		Α				E	
[mm]	50 st or less	Over 50 st 200 st or less	Over 200 st	DB	50 st or less	Over 50 st 200 st or less	Over 200 st
32	75	93.5	129.5	20	15.5	34	70
40	75	93.5	129.5	20	9	27.5	63.5
50	88.5	109.5	150.5	25	16.5	37.5	78.5
63	88.5	109.5	150.5	25	11.5	32.5	73.5


MGPL (Ball bushing) MGPA (High precision ball bushing) A, DB, E Dimensions [mm]

	Bore size			4				- 1		
	[mm]	50 st or less	Over 50 st 100 st or less	Over 100 st 200 st or less		DB		Over 50 st 100 st or less	Over 100 st 200 st or less	Over 200 st
-	32	79.5	96.5	116.5	138.5	16	20	37	57	79
	40	79.5	96.5	116.5	138.5	16	13.5	30.5	50.5	72.5
	50	91.5	112.5	132.5	159.5	20	19.5	40.5	60.5	87.5
	63	91.5	112.5	132.5	159.5	20	14.5	35.5	55.5	82.5

Ø80, Ø100/MGPM, MGPL, MGPA







- *: The use of a slot (width X6, length 7, depth 5) allows for a relaxed pin pitch tolerance, with the pin hole (ø6H9, depth 10) as the reference, without affecting mounting accuracy.
- *: For intermediate strokes other than standard strokes, refer to Manufacture of Intermediate Strokes on page 537.
- *: Choice of Rc, NPT, G port is available. (Refer to page 536.)

MGPM	, M	GPI	L, N	ИGI	PA	Cor	nm	on I	Dim	ens	ions	;																[mm]
Bore size	St	anda	rd	В	С	DΛ	ΕΛ	FB	G	GA	GB G	د اء	на		14	п	JC	v		ММ	ML	NN	ο,	ов	OI.		Р	
[mm]	stro	ke [n	nm]	-	`	DA		FB	٦	GA	ав с	"	luw.	٦	JA	100	30		-	IVIIVI	IVIL	1414	UA	ОБ	OL.	Nil	TN	TF
80		50, 75, 1 150, 175		96.5	56.5	22	16	24	91.5	19	16.5 1	4.5 202	M12	45.5	38	7.5	15	46	54	M12 x 1.7	5 25	M12 x 1.75	10.6	17.5	3	Rc3/8	NPT3/8	G3/8
100	250,	300, 350	400	116	66	26	19	31	111.5	22.5	20.5 1	8 240	M14	55.5	45	10.5	10	56	62	M14 x 2.0	31	M14 x 2.0	12.5	20	8	Rc3/8	NPT3/8	G3/8
Bore size		Ī						Τ		1			- 1	NΑ							WB				.,		T.,,	
Bore size [mm]	PA	РВ	PW	Q	R	s	T	U	VA	VB	25 st or less	Over 25 100 st or l	st Over ess 200 s	100 st or less	Over 20 300 st or	0 st less :	Over 300 st	25 or le	st C	Over 25 st 0 0 st or less 2	Over 100 s 00 st or les	t Over 200 s s 300 st or les	t O	ver 0 st	Х	YY	YL	. Z
80	14.5	25.5	74	52	174	1 75	198	156	180	140	28	52	1	28	200)	300	42	2	54	92	128	1	78	100	M12 x 1	75 24	28
100	17.5	32.5	89	64	210	90	236	188	210	166	48	72	1	48	220)	320	35	5	47	85	121	1	71	124	M14 x 2	.0 28	11

MGPM (Slide bearing) A, DB, E Dimensions

W C W	(Onac i	ocui iiig)	, ~, 00,		Dilliciis	10113	[IIIIII]
Bore size		Α				E	
[mm]	50 st	Over 50 st 200 st or less	Over 200 st	DB		Over 50 st 200 st or less	Over 200 st
80	104.5	131.5	180.5	30	8	35	84
100	126.5	151.5	190.5	36	10.5	35.5	74.5

MGPL (Ball bushing)

MGPA (High precision ball bushing) A, DB, E Dimensions [mm] Bore size DB 200 st or less 200 st 104.5 128.5 158.5 191.5 25 8 32 62 95 100 119.5 145.5 178.5 201.5 30 3.5 29.5 62.5 85.5

Compact Guide Cylinder With Air Cushion MGP Series

Ø16, Ø20, Ø25, Ø32, Ø40, Ø50, Ø63, Ø80, Ø100

How to Order MGPM32 50 AZ-M9BW Made to Order For details, refer to page 559. Compact Guide Cylinder Bearing type Number of auto switches M Slide bearing 2 pcs. L Ball bushing S 1 pc High precision ball bushing n n pcs. Bore size Auto switch 16 mm 50 50 mm Without auto switch 20 mm 63 63 mm (Built-in magnet) 25 25 mm 80 80 mm *: For applicable auto switches, 32 32 mm 100 mm refer to the table below. 40 40 mm With air cushion Port thread type M5 x 0.8 Cylinder stroke [mm] Ro Refer to Standard Strokes on page 559. ΤN NPT TF G *: For bore size 16.

Applicable Auto Switches/Refer to pages 1289 to 1383 for further information on auto switches.


only M5 x 0.8 is

- 1P F	ilicable Auto Swit			o pagoo 1200												
			동		L	oad volta	ge	Auto swit	tch model	Lead	wire	lengt	h [m]			
Туре	Special function	Electrical entry	Indicator light	Wiring (Output)	D	С	AC	Perpendicular	In-line	0.5 (Nil)	1 (M)	3 (L)	5 (Z)	Pre-wired connector	Applica	ble load
				3-wire (NPN)		5 V,12 V		M9NV	M9N	•		•	0	0	IC	
ے				3-wire (PNP)		5 V, 12 V		M9PV	M9P	•	•	•	0	0	circuit	
switch				2-wire		12 V]	M9BV	M9B	•	•	•	0	0	_	
S		1		3-wire (NPN)		5 V.12 V	1	M9NWV	M9NW	•	•	•	0	0	IC	
anto	Diagnostic indication (2-color indicator)			3-wire (PNP)		5 V, 12 V		M9PWV	M9PW	•	•	•	0	0	circuit	D. I.
	(2-color maicator)	Grommet	Yes	2-wire	24 V	12 V	1 –	M9BWV	M9BW	•	•	•	0	0	_	Relay, PLC
state]		3-wire (NPN)		5 V.12 V		M9NAV*1	M9NA*1	0	0	•	0	0	IC	1 20
	Water resistant (2-color indicator)			3-wire (PNP)		5 V, 12 V		M9PAV*1	M9PA*1	0	0	•	0	0	circuit	
Solid	(2-color maicator)			2-wire		12 V]	M9BAV*1	M9BA*1	0	0	•	0	0		
	Magnetic field resistant (2-color indicator)			2-wire (Non-polar)		_		_	P3DWA*2	•	_	•	•	0	_	
Reed auto switch		C	Yes	3-wire (NPN equivalent)	_	5 V	_	A96V	A96	•	_	•	-	_	IC circuit	_
× ed		Grommet		0	041/	12 V	100 V	A93V*3	A93	•	•	•	•	_	_	Relay,
ag s			No	2-wire	24 V	12 V	100 V or less	A90V	A90	•	_	•	_	_	IC circuit	PLĆ

- *1: Water resistant type auto switches are mountable on the above models, but in such case SMC cannot guarantee water resistance.
 - A water resistant type cylinder is recommended for use in an environment which requires water resistance. However, please contact SMC for water resistant products of ø12 and ø16.
- *2: The D-P3DWA□ is mountable on bore size ø25 to ø100.
- *3: 1 m type lead wire is only applicable to the D-A93.
- *: Lead wire length symbols: 0.5 m-----Nil (Example) M9NW
 - 1 m······· M (Example) M9NWM 3 m······ L (Example) M9NWL
 - 3 m······· L (Example) M9NWL 5 m······ Z (Example) M9NWZ
- * : Solid state auto switches marked with "O" are produced upon receipt of order.
- *: Other than the auto switches listed above, the D-P4DW type can be mounted. Refer to page 595 for details. *: For details about auto switches with pre-wired connector, refer to pages 1358 and 1359.
- *: Auto switches are shipped together, (but not assembled).



Specifications



satisfied. Make a model selection, considering a load according to the graph on pages 562 to 568.

Air cushion Standard Strokes

Bore size [mm]	Standard stroke [mm]
16	25, 50, 75, 100, 125, 150, 175, 200, 250
20 to 63	25, 50, 75, 100, 125, 150, 175, 200, 250, 300, 350, 400
80, 100	50, 75, 100, 125, 150, 175, 200, 250, 300, 350, 400

Manufacture of Intermediate Strokes

Description	standard stroke cylinder. Minimum manufacturable stroke ø16	ts are available by replacing collars of a 6 to e63: 15 mm), ø100: 20 mm ne cushion effect is not obtainable for
Model no.	Add "-XC19" to the end of standard part	number.
	ø16	15 to 249
Applicable stroke [mm]	ø20 to ø63	15 to 399
Stroke [mm]	ø80, ø100	20 to 399
Example	Part no.: MGPM20-35AZ-XC19 A collar 15 mm in width is installed in the	MGPM20-50AZ. C dimension is 112 mm.

^{*:} Intermediate stroke (in 1 mm increments) based on an exclusive body will be available upon request for special.

Refer to pages 592 to 596 for cylinders

· Auto switch proper mounting position (detection at stroke end) and its mounting

Symbol

Made to Order: Individual Specifications

(For details, refer to pages 597 and 598.) Specifications

Side porting type (Plug location changed)

Specifications

Tapped hole, drilled hole, pinned hole machined additionally -XC85 Grease for food processing equipment

Made to Order

Click here for details

Change of guide rod end shape

Intermediate stroke (Spacer type)

Made to

Order

-X867

Made to

Order

Symbo -XA□

-XC19

-XC79


- · Minimum stroke for auto switch mounting
- · Operating range

with auto switches.

- · Auto switch mounting brackets/Part no.
- · Auto Switch Mounting

	Intermediate strokes in 1 mm increm standard stroke cylinder.	ents are available by replacing collars of a
Description		16 to ø63: 15 mm 80. ø100: 20 mm
	Select a rubber bumper type, because less than this stroke.	e the cushion effect is not obtainable for
Model no.	Add "-XC19" to the end of standard pa	rt number.
	ø16	15 to 249
Applicable stroke [mm]	ø20 to ø63	15 to 399
Stroke [min]	ø80, ø100	20 to 399
Example	Part no.: MGPM20-35AZ-XC19 A collar 15 mm in width is installed in the	ne MGPM20-50AZ. C dimension is 112 mm.

Theoretical Output



^{*:} Theoretical output [N] = Pressure [MPa] x Piston area [mm2]



Weights


Slide Bearing: MGPM16 to 100

Bore size					Sta	ndard s	troke [r	nm]				
[mm]	25	50	75	100	125	150	175	200	250	300	350	400
16	0.48	0.62	0.74	0.86	1.01	1.14	1.26	1.38	1.62	_	_	_
20	0.78	1.02	1.20	1.39	1.57	1.75	1.94	2.12	2.55	2.92	3.29	3.65
25	1.07	1.43	1.67	1.92	2.17	2.41	2.66	2.91	3.50	4.00	4.49	4.99
32	1.65	2.10	2.45	2.81	3.16	3.52	3.87	4.23	5.11	5.82	6.53	7.24
40	1.95	2.43	2.83	3.22	3.61	4.00	4.40	4.79	5.75	6.54	7.32	8.10
50	3.28	4.03	4.63	5.22	5.82	6.41	7.00	7.60	9.10	10.29	11.48	12.67
63	4.13	4.97	5.65	6.34	7.02	7.71	8.39	9.07	10.76	12.13	13.50	14.86
80	_	7.48	8.36	9.24	10.12	11.00	11.88	12.76	15.06	16.82	18.58	20.33
100	_	12.13	13.40	14.67	15.94	17.21	18.48	19.75	22.92	25.46	28.00	30.55

Ball Bushing: MGPL16 to 100, High Precision Ball Bushing: MGPA16 to 100 [kg]

Bore size					Sta	ndard s	troke [r	nm]				
[mm]	25	50	75	100	125	150	175	200	250	300	350	400
16	0.48	0.59	0.69	0.84	0.94	1.05	1.15	1.25	1.46	_	_	_
20	0.82	0.98	1.14	1.35	1.51	1.67	1.82	1.98	2.34	2.65	2.97	3.29
25	1.16	1.36	1.57	1.83	2.03	2.24	2.44	2.65	3.11	3.52	3.93	4.34
32	1.59	2.01	2.29	2.67	2.95	3.24	3.53	3.81	4.48	5.05	5.61	6.18
40	1.87	2.33	2.65	3.07	3.39	3.71	4.04	4.36	5.10	5.74	6.38	7.03
50	3.10	3.82	4.32	4.93	5.43	5.93	6.43	6.93	8.10	9.10	10.10	11.09
63	3.95	4.75	5.35	6.06	6.66	7.25	7.84	8.44	9.79	10.98	12.17	13.36
80	_	7.63	8.38	9.12	9.87	10.62	11.37	12.11	14.03	15.52	17.02	18.51
100	_	12.07	13.17	14.28	15.38	16.49	17.59	18.70	21.32	23.53	25.74	27.95

Allowable Rotational Torque of Plate



													[IN-M
Bore size	Bearing	Stroke											
[mm]	type	25	50	75	100	125	150	175	200	250	300	350	400
16	MGPM	0.53	0.84	0.69	0.58	0.50	0.44	0.40	0.36	0.30	_	_	_
	MGPL/A	1.27	0.86	0.65	0.52	0.43	0.37	0.32	0.28	0.23	_	_	_
20	MGPM	0.99	2.23	1.88	1.63	1.44	1.28	1.16	1.06	0.90	0.78	0.69	0.62
20	MGPL/A	2.66	1.94	1.52	1.57	1.34	1.17	1.03	0.93	0.76	0.65	0.56	0.49
05	MGPM	1.64	3.51	2.96	2.57	2.26	2.02	1.83	1.67	1.42	1.24	1.09	0.98
25	MGPL/A	4.08	3.02	2.38	2.41	2.05	1.78	1.58	1.41	1.16	0.98	0.85	0.74
32	MGPM	6.35	6.64	5.69	4.97	4.42	3.98	3.61	3.31	2.84	2.48	2.20	1.98
32	MGPL/A	5.95	5.89	5.11	6.99	6.34	5.79	5.33	4.93	4.29	3.78	3.38	3.04
40	MGPM	7.00	7.32	6.27	5.48	4.87	4.38	3.98	3.65	3.13	2.74	2.43	2.19
40	MGPL/A	6.55	6.49	5.62	7.70	6.98	6.38	5.87	5.43	4.72	4.16	3.71	3.35
50	MGPM	13.0	13.8	12.0	10.6	9.50	8.60	7.86	7.24	6.24	5.49	4.90	4.43
50	MGPL/A	9.17	11.2	9.80	12.8	11.6	10.7	9.80	9.10	7.95	7.02	6.26	5.63
63	MGPM	14.7	15.6	13.5	11.9	10.7	9.69	8.86	8.16	7.04	6.19	5.52	4.99
03	MGPL/A	10.2	12.5	11.0	14.3	13.0	11.9	11.0	10.2	8.84	7.80	6.64	6.24
80	MGPM	_	26.0	22.9	20.5	18.6	17.0	15.6	14.5	12.6	11.2	10.0	9.11
60	MGPL/A	_	25.2	22.7	20.6	18.9	17.3	16.0	14.8	12.9	11.3	10.0	8.94
100	MGPM	_	41.9	37.5	33.8	30.9	28.4	26.2	24.4	21.4	19.1	17.2	15.7
100	MGPL/A	_	41.7	37.9	34.6	31.8	29.3	27.2	25.3	22.1	19.5	17.3	15.5


High Precision Ball Bushing/MGPA

∴ Caution

[kg]


Positioning accuracy for pin hole on the plate

Dispersion of dimensions when machining each component will be accumulated in the plate pin hole positioning accuracy when mounting this cylinder. Values below are referred as a guide.




- $\mathbf{A} = \boxed{\text{Catalog dimension}} \pm (0.1 + \mathbf{L}_1 \times 0.0008) \text{ [mm]}$
- *1: To be 0.15 for ø80, ø100
- Displacement by load and self-weight deflection by plate and guide rod are not included.

[Bottom mounting]



 $\mathbf{B} = \pm (0.045 + \mathbf{L}_2 \times 0.0016) \text{ [mm]}$


Non-rotating Accuracy of Plate




Non-rotating accuracy θ when retracted and when no load is applied should be not more than the values shown in the table.

Bore size	Non-rotating accuracy θ						
[mm]	MGPM	MGPL	MGPA				
16	±0.07°	±0.05°					
20	±0.06°	±0.04°					
25	±0.06	±0.04					
32	±0.05°	±0.03°					
40	±0.05	±0.03°	±0.01°				
50	+0.04°	±0.03°					
63	±0.04	±0.03					
80	±0.03°	±0.03°					
100	±0.03	±0.03					


High Precision Ball Bushing/MGPA Plate Displacement Amount (Reference Values)




MGPA16




MGPA50, 63




MGPA20




MGPA80




MGPA25



MGPA100




MGPA32, 40



- *: The guide rod and self-weight for the plate are not included in the above displacement values.
- *: Allowable rotating torque, and operating range when used as a lifter, are the same as those of the MGPL series.

With Air Cushion MGP Series **Model Selection**

Selection Conditions



Selection Example 1 (Vertical Mounting)

Selection conditions

Mounting: Vertical

Bearing type: Ball bushing


Stroke: 75 stroke Maximum speed: 200 mm/s

Load mass: 7 kg

Eccentric distance: 70 mm

Find the point of intersection for the load mass of 7 kg and the eccentric distance of 70 mm on graph (5), based on vertical mounting, ball bushing, 75 mm stroke, and the speed of 200 mm/s.

→MGPL25-75AZ is selected.



Selection Example 2 (Horizontal Mounting)

Selection conditions

Mounting: Horizontal

Bearing type: Slide bearing

Distance between plate and load center of gravity: 40 mm

Maximum speed: 400 mm/s


Load mass: 8 kg

Stroke: 100 stroke

Find the point of intersection for the load mass of 8 kg and 100 stroke on graph (17), based on horizontal mounting, slide bearing, the distance of 40 mm between the plate and load center of gravity, and the speed of 400 mm/s.

→MGPM32-100AZ is selected

(17) L = 50 mm, V = 400 mm/s



[·] When the maximum speed exceeds 200 mm/s, the allowable load mass is determined by multiplying the value shown in the graph at 400 mm/s by the coefficient listed in the table below.


Maximum	Up to 300 mm/s	Up to 400 mm/s	Up to 500 mm/s
Coefficient	1.7	1	0.6

[·] Use the Guide Cylinder Selection Software, when the eccentric distance is 200 mm or more,


Vertical Mounting Slide Bearing


Operating pressure 0.4 MPa
---- Operating pressure 0.5 MPa or more


MGPM16 to 100












(4) Over 25 stroke, V = 400 mm/s





 $[\]cdot$ Use the Guide Cylinder Selection Software, when the eccentric distance is 200 mm or more.

Vertical Mounting Ball Bushing

Operating pressure 0.4 MPa - - - - Operating pressure 0.5 MPa or more

MGPL16 to 25






50


Eccentric distance L [mm]

200


10

MGPL32 to 63





MGPL80/100





· Use the Guide Cylinder Selection Software, when the eccentric distance is 200 mm or more. **SMC**

Vertical Mounting Ball Bushing

Operating pressure 0.4 MPa

MGPL16 to 25







MGPL32 to 63


(12) 25 stroke, V = 400 mm/s







MGPL80/100





[·] Use the Guide Cylinder Selection Software, when the eccentric distance is 200 mm or more.





Horizontal Mounting Slide Bearing

MGPM16 to 100
















Horizontal Mounting Ball Bushing


(19) L = 50 mm, V = 200 mm/s or less




MGPL32 to 63




MGPL80/100




(20) L = 100 mm, V = 200 mm/s or less



MGPL32 to 63




MGPL80/100




Horizontal Mounting Ball Bushing


(21) L = 50 mm, V = 400 mm/s




MGPL32 to 63




MGPL80/100




(22) L = 100 mm, V = 400 mm/s



MGPL32 to 63




MGPL80/100



Operating Range when Used as Stopper

Bore Size Ø16 to Ø25/MGPM16 to 25 (Slide Bearing)




*: When selecting a model with a longer L dimension, be sure to choose a bore size which is sufficiently large.

△ Caution

Caution on handling

- When using as a stopper, select a model with 25 stroke or less.
- The MGPL (Ball bushing) and the MGPA (High precision ball bushing) cannot be used as a stopper.

MGPM16 to 25 (Slide Bearing)



Bore Size Ø32 to Ø100/MGPM32 to 100 (Slide Bearing)

m m m m


*: When selecting a model with a longer L dimension, be sure to choose a bore size which is sufficiently large.

△ Caution

Caution on handling

- When using as a stopper, select a model with 50 stroke or less.
- The MGPL (Ball bushing) and the MGPA (High precision ball bushing) cannot be used as a stopper.


MGPM32 to 100 (Slide Bearing)



*: Refer to graphs (15) and (17) if line pressure is applied by a roller conveyor after the workpiece is stopped.

Construction (With Air Cushion)/MGPM Series

MGPM



Component Parts

iiponent raits	•						
Description	Material		Note				
Body	Aluminum alloy	Hard	anodized				
Piston A	Aluminum alloy		ø16				
Piston B	Aluminum alloy		ø16				
Piston	Aluminum alloy	ø20	to ø100				
Dieten ved	Stainless steel	ø10	6 to ø25				
Piston rou	Carbon steel	ø32 to ø100	Hard chrome plating				
Collar	Aluminum alloy	Ch	romated				
Head cover	Aluminum alloy	Chromated Hard chrome plating					
Guide rod	Carbon steel	Hard chrome plating Nickel plating					
Plate	Carbon steel	l Nickel plating					
Plate mounting bolt	Carbon steel	Nickel plating Nickel plating					
Guide bolt	Carbon steel	Nickel plating Nickel plating					
Retaining ring	Carbon tool steel	Phosp	hate coated				
Retaining ring	Carbon tool steel	Phosp	hate coated				
Magnet	_						
Plug	Carbon stool	ø16	Nickel plating				
Hexagon socket head plug	Carbon Steel	ø20 to ø100	Nickei plating				
Slide bearing	Bearing alloy						
Ball bushing	_						
Spacer	Aluminum alloy						
Cushion ring	Aluminum alloy	ø25 to ø100	Anodized				
Cuchion volve		ø16 to ø32	Electroless nickel plating				
Cusinon valve		ø50 to ø100	Chromated				
Cushion needle		ø40 only	Electroless nickel plating				
	Description Body Piston A Piston B Piston rod Collar Head cover Guide rod Plate Plate mounting bolt Guide bolt Retaining ring Magnet Plug Hexagon socket head plug Slide bearing Ball bushing Spacer Cushion ring Cushion valve	Description Material Body Aluminum alloy Piston A Aluminum alloy Piston B Aluminum alloy Piston A Aluminum alloy Piston A Aluminum alloy Piston Aluminum alloy Piston Aluminum alloy Piston Aluminum alloy Stainless steel Carbon steel Carbon steel Aluminum alloy Head cover Aluminum alloy Guide rod Carbon steel Plate Carbon steel Plate Carbon steel Retaining ring Carbon tool steel Retaining ring Carbon tool steel Retaining ring Carbon tool steel Retaining ring Carbon steel Sampent Plug Carbon steel Retaining ring Carbon steel Silde bearing Bearing alloy Ball bushing — Spacer Aluminum alloy Cushion valve	Description Material Hard				

*: A felt is not installed on the slide bearing.

Component Parts

No.	Description	Material		Note
21	Gasket	NBR		ø16
22	Gasket	NBR		
23	Retaining ring	Carbon tool steel	ø50, ø63	Phosphate coated
24	Steel ball	Carbon steel	ø16	6 to ø50
25	Plug	Carbon steel	ø63 to ø100	Nickel plating
26*	Piston seal	NBR		
27*	Rod seal	NBR		
28*	Cushion seal	Urethane		
29*	Gasket A	NBR		
30*	Gasket B	NBR		
	•			

Replacement Parts/Seal Kit


Bore size [mm]	Kit no.	Contents	Bore size [mm]	Kit no.	Contents
16	MGP16-AZ-PS		50	MGP50-AZ-PS	Set of nos.
20	MGP20-AZ-PS	Set of nos.	63	MGP63-AZ-PS	above
25	MGP25-AZ-PS	above 26, 27, 28,	80	MGP80-AZ-PS	26, 27, 28,
32	MGP32-AZ-PS	29, 30	100	MGP100-AZ-PS	29, 30
40	MGP40-AZ-PS] , ,			

^{*:} Seal kit includes 26 to 30. Order the seal kit, based on each bore size.


^{*:} Since the seal kit does not include a grease pack, order it separately. Grease pack part no.: GR-S-010 (10 g)


Construction (With Air Cushion)/MGPL Series

MGPL




Ø16 to Ø25/MGPM, MGPL, MGPA (With Air Cushion)





Bottom view



- *: The use of a slot (width XA, length XB, depth 3) allows for a relaxed pin pitch tolerance, with the pin hole (øXAHe, depth 6) as the reference, without affecting mounting accuracy.
- *: For intermediate strokes other than standard strokes, refer to Manufacture of Intermediate Strokes on page 559.
- *: For bore size ø16, only M5 x 0.8 port is available.
- *: For bore size ø20 or more, choice of Rc, NPT, G port is available. (Refer to page 558.)

MGPM	, M	GPL	_ Co	ımc	mon	Dir	nen	sio	ns																		[mm]
Bore size		Stand	dard s	strok	(e	В	С	DΛ	E 4	ЕВ	<u>ر</u>	G۸	GB	н	на	J	к		мм	ML	NN	Ω.	ов	OI.		Р	
[mm]			[mm]]		-	٦	DA	-	гь	٦	GA	GB	"	ПА	"	``	-	IVIIVI	IVIL	IVIV	04	ОВ	OL	Nil	TN	TF
16	25, 50,	75, 100,	125, 15	0, 175,	200, 250	71	58	8	7	6	30	10.5	7.5	64	M4	15	15	22	M5 x 0.8	12	M5 x 0.8	4.3	8	4.5	M5 x 0.8	-1	_
20	25, 5	0, 75,	100, 12	25, 15	50, 175	78	62	10	8	8	36	11.5	9	83	M5	18	18	24	M5 x 0.8	13	M5 x 0.8	5.4	9.5	5.5	Rc1/8 N	IPT1/8	G1/8
25	20	0, 250	, 300,	350,	400	78.5	62.5	10	9	7	42	11.5	10	93	M5	21	21	30	M6 x 1.0	15	M6 x 1.0	5.4	9.5	5.5	Rc1/8 N	IPT1/8	G1/8
		_			_				_	_							_						_			_	_
Bore size			DW.	١,	R	s	-			VВ			١	٧A					W	3		l v	V.	VD	YY	\ _V ,	-
[mm]	PA	РВ	PW	Q	н	3	'	U	VA	VB	75 st or	r less 10	0 to 175	st 200,	250 st	300 st or n	nore 75	st or less	100 to 175 st	200, 250	st 300 st or more	X	XA	ХВ	* * *	YL	'
	00 5	4.0		1.0		25	-00		=-					_	00			~=		105		~ .	_	0.5	145 0	0 40	TE


Bore size	D.	-	PW	_	R	_	-	١	VA	VВ		W	Α			W	В		v	XA	хв	vv	vı	-
[mm]	PA	РВ	PW	Q	н	3	'	U	VA	VB	75 st or less	100 to 175 st	200, 250 st	300 st or more	75 st or less	100 to 175 st	200, 250 st	300 st or more	^	XA	ХB	11	YL	
16	39.5	10	19	16	54	25	62	46	56	38	44	110	200	_	27	60	105	_	24	3	3.5	M5 x 0.8	10	5
20	38.5	10.5	25	18	70	30	81	54	72	44	44	120	200	300	39	77	117	167	28	3	3.5	M6 x 1.0	12	17
25	37.5	13.5	30	26	78	38	91	64	82	50	44	120	200	300	39	77	117	167	34	4	4.5	M6 x 1.0	12	17


MGPL (Ball bushing)

MGPM	(Slide I	bearing)/A, DB,	E	Dimens	ions	[mm]
Bore size		Α		DB		E	
[mm]	25 to 100 st	125 to 200 st	250 st or more	סט	25 to 100 st	125 to 200 st	250 st or more
16	71	92.5	92.5	10	0	21.5	21.5
20	78	78	110	12	0	0	32
25	78.5	78.5	109.5	16	0	0	31

1]	MGPA (High pre	cision ba	all bushir	1g)/	A, DB, E	Dimensi	ons [mm]
	Bore size		Α		DB		Е	
е	[mm]	25 to 75 st	100 to 200 st	250 st or more	סט	25 to 75 st	100 to 200 st	250 st or more
	16	71	94.5	94.5	8	0	23.5	23.5
	20	78	100	117.5	10	0	22	39.5
_	25	81.5	100.5	117.5	13	3	22	39

Ø32 to Ø63/MGPM, MGPL, MGPA (With Air Cushion)





- *: The use of a slot (width XA, length XB, depth XC) allows for a relaxed pin pitch tolerance, with the pin hole (øXAHe, depth XL) as the reference, without affecting mounting accuracy.
- *: For intermediate strokes other than standard strokes, refer to Manufacture of Intermediate Strokes on page 559.
- *: Choice of Rc, NPT, G port is available. (Refer to page 558.)

MGPM	, M	GPL	. Co	mr	non	Dir	nen	sio	ns																			[mm]
Bore size	Sta	ındar	d stro	oke	В	С	cv	DA	ΕΛ.	ЕВ	G	GA	GB	н	на	J	ĸ		мм	ML	l N	IN	ОА	ΛВ	Λ.		Р	
[mm]		[m	m]		-		CV	DA	FA	гь	G	GA	GB	"	ПА	J	\ <u>`</u>	_	IVIIVI	IVIL	14	114	UA	ОВ	OL	Nil	TN	TF
32	25	, 50,	75, 1	00	84.5	62.5	1.5	14	10	12	48	12	9	112	M6	24	24	34	M8 x 1.25	20	M8 x	1.25	6.7	11	7.5	Rc1/8	NPT1/8	G1/8
40	12	25, 1	50, 17	75	91	69	1.5	14	10	12	54	15	12	120	M6	27	27	40	M8 x 1.25	20	M8 x	1.25	6.7	11	7.5	Rc1/8	NPT1/8	G1/8
50	20		50, 30	00	97	69	3	20	12	16	64	15	12	148	M8	32	32	46	M10 x 1.5	22	M10	x 1.5	8.6	14	9	Rc1/4	NPT1/4	G1/4
63		350,	400		102	74	3	20	12	16	78	15.5	13.5	162	M10	39	39	58	M10 x 1.5	22	M10	x 1.5	8.6	<u> </u>	9	Rc1/4	NPT1/4	G1/4
Bore size													W			Т			NB									
[mm]	PA	РВ	PW	Q	R	s	Т	U	VA	VB	75 st or le	ss 100 to		-	300 st or n	nore 75	st or less		st 200, 250 st 3	00 st or more	X	XA	ХВ	хc	XL	YY	YL	. Z
32	31.5	16	35.5	30	96	44	110	78	98	63	48	12	24	200	300	7	45	83	121	171	42	4	4.5	3	6	M8 x 1.	25 16	21
40	38	18	39.5	30	104	44	118	86	106	72	48	12	24	200	300		46	84	122	172	50	4	4.5	3	6	M8 x 1.	25 16	22
50	34	21.5	47	40	130	60	146	110	130	92	48	12	24	200	300)	48	86	124	174	66	5	6	4	8	M10 x 1	.5 20	24
63	38	28	58	50	130	70	158	124	142	110	52	12	28	200	300)	50	88	124	174	80	5	6	4	8	M10 x 1	.5 20	24


MGPM (Slide bearing)/A, DB, E Dimensions [n

	(040	Douini	9,,,,	٠-,			U [iiiiiii]
Bore size		Α		DB		E	
[mm]	25 st	50 to 200 st	250 st or more	פט	25 st	50 to 200 st	250 st or more
32	84.5	93.5	129.5	20	0	9	45
40	91	93.5	129.5	20	0	2.5	38.5
50	97	109.5	150.5	25	0	12.5	53.5
63	102	109.5	150.5	25	0	7.5	48.5


MGPL (Ball bushing)

MGPA	(High	precisi	on ball	bushi	ng)/	A, DB,	E DIM	ensior	IS [mm]
Bore size			١		DB				
[mm]	25 st	50, 75 st	100 to 200 st	250 st or more	סט	25 st	50, 75 st	100 to 200 st	250 st or more
32	84.5	96.5	116.5	138.5	16	0	12	32	54
40	91	96.5	116.5	138.5	16	0	5.5	25.5	47.5
50	97	112.5	132.5	159.5	20	0	15.5	35.5	62.5
63	102	112.5	132.5	159.5	20	0	10.5	30.5	57.5

Ø80, Ø100/MGPM, MGPL, MGPA (With Air Cushion)



Bottom view



- *: The use of a slot (width X6, length 7, depth 5) allows for a relaxed pin pitch tolerance, with the pin hole (e6Hs, depth 10) as the reference, without affecting mounting accuracy.
- *: For intermediate strokes other than standard strokes, refer to Manufacture of Intermediate Strokes on page 559.

10.5

*: Choice of Rc, NPT, G port is available. (Refer to page 558.)

MGPM	, M	GPL	_ Cc	mr	nor	Di	me	nsio	ns																			[mm]
Bore size	Stan	dard s	stroke	В	С	Δ.	ΕΛ	ЕВ	م ا م	٠, ۱	BGC		шл		1.	п	ıc	к	L	ММ	ML	NN	OA	ΛВ	Λı		Р	
[mm]		[mm]		-	•		FA	FB	٦	ואי	ы	1"	ll'A	٦	JA	JB	30	^	-	IVIIVI	IVIL	INIA	0 4	ОВ	OL	Nil	TN	TF
80	50, 75,	100, 125,	150, 175	121.5	81.5	25	16	24	91.5 1	9 1	6.5 14.5	202	M12	45.5	38	7.5	15	46	54	M12 x 1.75	25	M12 x 1.75	10.6	17.5	3	Rc3/8	NPT3/8	G3/8
100	200, 25	50, 300, 3	150, 400	141	91	30	19	31 1	11.5 2	2.5 2	0.5 18	240	M14	55.5	45	10.5	10	56	62	M14 x 2.0	31	M14 x 2.0	12.5	20	8	Rc3/8	NPT3/8	G3/8
Bore size	ВΛ	DD	PW	a	R	s	Ι,	U	V/A	VB				WA	١						W	В			x	YY	YL	7
[mm]	- ~	гь	F VV	۳	l n	3	١.	"	٧^	VB	50, 7	5 st	100 to 17	75 st 2	00, 25	i0 st 3	300 st or	more	50, 7	5 st 100 to	175 st	200, 250 st	300 st o	r more	^	'''	''	- -
80	39.5	25.5	74	52	174	75	198	3 156	180	140	52	: [128	3	200)	300)	54	9	2	128	17	8	100	M12 x 1.	75 24	28
100	42.5	32.5	89	64	210	90	236	6 188	210	166	72	. [148	3	220) [320) [47	8	5	121	17	1	124	M14 x 2	2.0 28	11

MGPM	(Slide bear	ring)/A, DB,	ΕI	Dimensions	[mm]
Bore size		4	DB	i i	
[mm]	50 to 200 st	250 st or more	υБ	50 to 200 st	250 st or more
80	131.5	180.5	30	10	59

36

190.5


•	L (Ball bushing) A (High precision ball bushing)/A, DB, E Dimensions [mn										
Bore size		4	DВ	E							
[mm]	50 to 200 st	250 st or more	סט	50 to 200 st	250 st or more						
80	158.5	191.5	25	37	70						
100	178.5	201.5	30	37.5	60.5						

151.5

49.5

Compact Guide Cylinder/With End Lock *MGP Series* Ø20, Ø25, Ø32, Ø40, Ø50, Ø63, Ø80, Ø100

How to Order



Applicable Auto Switches/Refer to pages 1289 to 1383 for further information on auto switches.

	Thousie Hate Ciri		light			oad volta		Auto swit		Lead	wire	ength	[m]										
Туре	Special function	Electrical entry	Indicator	Wiring (Output)	С	С	AC	Perpendicular	In-line	0.5 (Nil)	1 (M)	3 (L)	5 (Z)	Pre-wired connector	Applical	ble load							
				3-wire (NPN)		5 V.12 V		M9NV	M9N	•	•	•	0	0	IC								
ج ا	_			3-wire (PNP)		5 V, 12 V		M9PV	M9P	•	•	•	0	0	circuit								
switch				2-wire		12 V		M9BV	M9B	•	•	•	0	0	_								
	Diagnostic indication			3-wire (NPN)		5 V.12 V		M9NWV	M9NW	•	•	•	0	0	IC								
울	Diagnostic indication (2-color indicator)			3-wire (PNP)	3-wire (PNP) 2-wire 24 V	5 V, 12 V		M9PWV	M9PW	•	•	•	0	0	circuit	Relay,							
□ C	(2-color indicator)	Grommet	Yes	2-wire		12 V	_	M9BWV	M9BW	•	•	•	0	0	_	PLC							
state	Water resistant			3-wire (NPN)		5 V,12 V		M9NAV*1	M9NA*1	0	0	•	0	0	IC	PLC							
	(2-color indicator)			3-wire (PNP) 2-wire	2-wire	J V, 12 V		M9PAV*1	M9PA*1	0	0	•	0	0	circuit								
Solid	(2-color indicator)					12 V		M9BAV*1	M9BA*1	0	0	•	0	0									
	Magnetic field resistant (2-color indicator)			2-wire (Non-polar)		_		_	P3DWA	•	-	•	•	0	_								
o switch			a . Y							. Yes	3-wire (NPN equivalent)	_	5 V	_	A96V	A96	•	_	•	_	_	IC circuit	_
dauto	_	Grommet	No	2 wire	24.1/	10.1/	100 V	A93V*2	A93	•	•	•	•	_	_	Relay,							
Reed				2-wire	24 V	12 V	100 V or less	A90V	A90	•	_	•	_	_	IC circuit	PLC							

- *1: Water resistant type auto switches can be mounted on the above models, but in such case SMC cannot guarantee water resistance.
- Please consult with SMC regarding water resistant types with the above model numbers.
- *2: 1 m type lead wire is only applicable to the D-A93.
- *: Lead wire length symbols: 0.5 m········Nii (Example) M9NW *: Solid state auto switches marked with "O" are produced upon receipt of order.

 1 m········· M (Example) M9NWM *: Bore sizes 32 to 100 are available for D-P4DW.

*: Bore sizes 25 to 100 are available for D-P3DWA

- 3 m----- L (Example) M9NWL 5 m---- Z (Example) M9NWZ
- *: Since there are other applicable auto switches than listed above, refer to page 595 for details.
- *: For details about auto switches with pre-wired connector, refer to pages 1358 and 1359.
- *: Auto switches are shipped together, (but not assembled).





Symbol Rubber bumper





Made to Order: Individual Specifications (For details, refer to pages 597 and 598.)

Symbol	
-X867	Side porting type (Plug location changed) *1

*1: The shape is the same as the current product



Made to Order Click here for details

Symbol	Specifications
-XB13	Low speed cylinder (5 to 50 mm/s)
-XC79	Tapped hole, drilled hole, pinned hole machined additionally *1
-XC85	Grease for food processing equipment

*1: The shape is the same as the current product.

Refer to pages 592 to 596 for cylinders with auto switches.

- . Minimum stroke for auto switch mounting
- · Auto switch proper mounting position (detection at stroke end) and its mounting height
- Operating range
- · Auto switch mounting brackets/Part no.
- Auto switch mounting

Specifications

				40			80	400			
Bore size [mm]	ore size [mm] 20 25 32 40 50 63							100			
Action	Double acting										
Fluid	Air										
Proof pressure				1.5	MPa						
Maximum operating pressure	1.0 MPa										
Minimum operating pressure				0.15 N	/IPa *1						
Ambient and fluid temperature	-10 to 60°C (No freezing)										
Piston speed *2	50 to 500 mm/s 50 to 400 i										
Cushion Rubber bumper on both ends											
Lubrication	Not required (Non-lube)										
Stroke length tolerance	m										

- *1: 0.1 MPa except the lock unit.
- *2: Maximum speed with no load. Depending on the operating conditions, the piston speed may not be satisfied. Make a model selection, considering a load according to the graph on pages 545 to 551.

Lock Specifications

Lock position Head end, Rod end										
Holding force	ø20	ø25	ø32	ø40	ø50	ø63	ø80	ø100		
(Max.) N	215	330	550	860	1340	2140	3450	5390		
Backlash 2 mm or less										
Manual release		Non-lock type, Lock type								

Adjust switch positions for operation at both the stroke end and backlash (2 mm) movement positions.

Standard Strokes

Bore size [mm]	Standard stroke [mm]
20, 25, 32, 40, 50, 63, 80, 100	25, 50, 75, 100, 125, 150, 175, 200, 250, 300, 350, 400


Manufacture of Intermediate Stroke

Description	Spacer installation type. Dealing with the stroke in 5 mm increments is available by installing spacer with standard stroke cylinder. When a spacer is mounted on the cylinder with an end lock on the rod side, use a special piston rod.
Part no.	Refer to "How to Order" for the standard model numbers on page 575.
Applicable stroke [mm]	5 to 395
Example	Part no.: MGPM50-35-HN A spacer 15 mm in width is installed in a MGPM50-50-HN. C dimension is 119 mm.

*: The minimum stroke for mounting auto switches is 10 stroke or more for two switches, and 5 stroke or more for one switch. *: Intermediate stroke (in 1 mm increments) based on an exclusive body will be available upon request for special.

IN

Theoretical Output



^{*:} Theoretical output [N] = Pressure [MPa] x Piston area [mm2]



Weights

Slide Bearing: MGPM20 to 100 (Basic weight)

[kg]

Bore size				Standard stroke [mm]										
[mm]	25	50	75	100	125	150	175	200	250	300	350	400		
20	0.86	1.12	1.32	1.52	1.71	1.91	2.11	2.31	2.78	3.18	3.57	3.97		
25	1.18	1.56	1.83	2.10	2.38	2.65	2.92	3.19	3.85	4.39	4.94	5.48		
32	1.92	2.32	2.70	3.09	3.47	3.85	4.23	4.61	5.56	6.32	7.09	7.85		
40	2.20	2.66	3.08	3.51	3.93	4.36	4.78	5.20	6.24	7.10	7.95	8.80		
50	3.73	4.46	5.10	5.74	6.38	7.02	7.66	8.30	9.91	11.2	12.5	13.8		
63	4.61	5.45	6.21	6.96	7.72	8.47	9.23	9.99	11.8	13.3	14.8	16.3		
80	7.88	8.70	9.49	10.3	11.2	12.0	12.8	13.9	15.5	17.2	18.8	20.5		
100	12.1	13.2	14.4	15.6	16.8	18.0	19.1	20.6	22.9	25.3	27.6	30.0		

Ball Bushing, High Precision Ball Bushing: MGPA20 to 100 (Basic weight)

Ball Bushir	Ball Bushing, High Precision Ball Bushing: MGPA20 to 100 (Basic weight) [kg]												
Bore size	Standard stroke [mm]												
[mm]	25	50	75	100	125	150	175	200	250	300	350	400	
20	0.93	1.10	1.27	1.48	1.65	1.83	2.00	2.17	2.55	2.90	3.25	3.60	
25	1.27	1.50	1.74	2.01	2.24	2.47	2.70	2.94	3.44	3.91	4.37	4.83	
32	1.74	2.19	2.51	2.88	3.20	3.51	3.83	4.15	4.84	5.47	6.10	6.73	
40	2.02	2.51	2.87	3.29	3.65	4.01	4.37	4.73	5.51	6.23	6.95	7.67	
50	3.46	4.21	4.76	5.40	5.95	6.50	7.05	7.60	8.83	9.92	11.1	12.2	
63	4.33	5.20	5.86	6.62	7.28	7.95	8.61	9.27	10.7	12.1	13.4	14.7	
80	8.05	8.87	9.66	10.5	11.4	12.2	13.0	14.1	15.7	17.4	19.0	20.7	
100	12.4	13.5	14.7	15.9	17.1	18.3	19.4	20.9	23.2	25.6	27.9	30.3	

Lock Unit Additional Weight


	Head e	nd lock	Rod end lock			
Bore size [mm]	HN	HL	RN	RL		
20	0.05	0.07	0.05	0.06		
25	0.06	0.07	0.05	0.07		
32	0.09	0.10	0.09	0.10		
40	40 0.15		0.14	0.18		
50	0.24	0.27	0.23	0.27		

				[Kg]		
	Head e	nd lock	Rod end lock			
Bore size [mm]	HN	HL	RN	RL		
63	0.36	0.40	0.35	0.39		
80	0.90	0.97	1.03	1.10		
100	1.52	1.60	1.60	1.68		

Calculation: (Example) MGPM50-100-HN · Basic Weight + Lock unit additional weight


• 5.74 + 0.24 = 5.98 kg

Allowable Rotational Torque of Plate



													i [iz.tii]
Bore size	Bearing						Stroke	[mm]					
[mm]	type	25	50	75	100	125	150	175	200	250	300	350	400
20	MGPM	0.99	0.75	1.88	1.63	1.44	1.28	1.16	1.06	0.90	0.78	0.69	0.62
20	MGPL/A	2.66	1.94	1.52	1.25	1.34	1.17	1.03	0.93	0.76	0.65	0.56	0.49
25	MGPM	1.64	1.25	2.96	2.57	2.26	2.02	1.83	1.67	1.42	1.24	1.09	0.98
25	MGPL/A	4.08	3.02	2.38	1.97	2.05	1.78	1.58	1.41	1.16	0.98	0.85	0.74
32	MGPM	6.35	5.13	5.69	4.97	4.42	3.98	3.61	3.31	2.84	2.48	2.20	1.98
32	MGPL/A	5.95	4.89	5.11	4.51	6.34	5.79	5.33	4.93	4.29	3.78	3.38	3.04
40	MGPM	7.00	5.66	6.27	5.48	4.87	4.38	5.98	3.65	3.13	2.74	2.43	2.19
40	MGPL/A	6.55	5.39	5.62	4.96	6.98	6.38	5.87	5.43	4.72	4.16	3.71	3.35
50	MGPM	13.0	10.8	12.0	10.6	9.50	8.60	7.86	7.24	6.24	5.49	4.90	4.43
50	MGPL/A	9.17	7.62	9.83	8.74	11.6	10.7	9.83	9.12	7.95	7.02	6.26	5.63
63	MGPM	14.7	12.1	13.5	11.9	10.7	9.69	8.86	8.16	7.04	6.19	5.52	4.99
03	MGPL/A	10.2	8.48	11.0	9.74	13.0	11.9	11.0	10.2	8.84	7.80	6.94	6.24
80	MGPM	21.9	18.6	22.9	20.5	18.6	17.0	15.6	14.5	12.6	11.2	10.0	9.11
30	MGPL/A	15.1	23.3	22.7	20.6	18.9	17.3	16.0	14.8	12.9	11.3	10.0	8.94
100	MGPM	38.8	33.5	37.5	33.8	30.9	28.4	26.2	24.4	21.4	19.1	17.2	15.7
100	MGPL/A	27.1	30.6	37.9	34.6	31.8	29.3	27.2	25.3	22.1	19.5	17.3	15.5

Non-rotating Accuracy of Plate



For non-rotating accuracy θ without load, use a value no more than the values in the table as a guide.


Bore size	Non-re	otating accu	ігасу θ
[mm]	MGPM	MGPL	MGPA
20	+0.07°	±0.09°	
25	10.07	±0.09	
32	+0.06°	±0.08°	
40	±0.00	±0.00	+0.01°
50	+0.05°	±0.06°	_±0.01
63	±0.05	±0.00	
80	+0.04°	±0.05°	
100	±0.04	±0.03	

Model selection


Model selection is the same as MGP/ standard type. Refer to pages 545 to 552.



Construction/MGPM Series




Non-locking type



Component Parts

No.	Description	Mat	erial		Note					
1	Body	Alumin	um alloy	Hard	anodized					
2	Piston	Alumin	um alloy							
3	B*-1	Stainless steel	ø20, ø25	Hard chrome plati	ng with rod end lock only					
3	Piston rod	Carbon steel	ø32 to ø100	Hard ch	rome plating					
4	Collar	Alumin	um alloy	Chi	romated					
5	Bushing	Bearin	ng alloy							
6	Head cover	Alumin	um alloy	Chr	romated					
7	Guide rod	Carbo	n steel	Hard ch	rome plating					
8	Plate	Carbo	n steel	Nickel plating						
9	Plate mounting bolt	Carbo	n steel	Nick	el plating					
10	Guide bolt	Carbo	n steel	Nickel plating						
11	Retaining ring	Carbon	tool steel	Phosphate coated						
12	Retaining ring	Carbon	tool steel	Phospi	nate coated					
13	Bumper A	Uret	hane							
14	Bumper B	Uret	hane							
15	Magnet	-	_							
16	Hexagon socket head cap plug		n steel	Nick	el plating					
17	Slide Bearing	Bearin	ng alloy							
18	Felt	F	elt							
19	Holder	Re	esin							
20	Ball bushing									
21	Spacer	Alumin	um alloy							
22	Steel ball	Carbo	n steel	ø20) to ø50					
23	Plug	Carbo	n steel	ø63 to ø100	Nickel plating					
24*		N	BR		· ·					
25*	Rod seal	N	BR							
26*	Gasket A	N	BR							
27*	Gasket B	N	BR							

(Rod end lock)



Component Parts

00.	iiponent i an	.5	
No.	Description	Material	Note
28	Piston gasket	NBR	ø32 to ø100 only
29	Lock bolt	Carbon steel	Zinc chromated
30	Lock holder	Brass	Electroless nickel plating
31	Lock piston	Carbon steel	Hard chrome plating
32	Lock spring	Stainless steel	
33	Seal retainer	Carbon steel	Zinc chromated (ø80, ø100 only)
34	Bumper	Urethane	
35*	Hexagon socket head cap screw	Carbon steel	Black zinc chromated
36*	Hexagon socket head cap screw	Carbon steel	Zinc chromated (ø50, ø63 only)
37	Cap A	Aluminum die-casted	Black painted
38	Cap B	Carbon steel	SQ treated
39	Rubber cap	Synthetic rubber	
40	M/O knob	Zinc die-casted	Black painted
41	M/O bolt	Alloy steel	Black zinc chromated
42	M/O spring	Steel wire	chromated
43	Stopper ring	Carbon steel	chromated
44*	Lock piston seal	NBR	
45*	Lock holder gasket	NBR	

Replacement Parts/Seal Kit


Ī	Bore size [mm]	Kit no.	Contents	Bore size [mm]	Kit no.	C	ontents
	20	MGP20-B-PS	Set of nos.	50	MGP50-B-PS	Set of nos.	24, 25, 26, 27,
	25	MGP25-B-PS	above	63	MGP63-B-PS	above	35, 36, 44, 45
	32	MGP32-B-PS	24, 25, 26, 27,	80	MGP80-B-PS	Set of nos.	24, 25, 26, 27,
	40	MGP40-B-PS	35, 44, 45	100	MGP100-B-PS	above	44, 45


- *: Each seal kit includes the parts listed above. Order the seal kit based on each bore size.
- *: Since the seal kit does not include a grease pack, order it separately.

 Grease pack part no.: GR-S-010 (10 g)




Construction/MGPL, MGPA Series






Lock type



SMC

Dimensions: Ø20, Ø25



- *: For intermediate strokes other than standard strokes, refer to the Manufacture of Intermediate Stroke on page 576. *: Rc, NPT and G ports can be selected. (Refer to page 575.)

MGPM,	MGPM, MGPL, MGPA Common Dimensions																[mm]								
Bore size	Sta	ndard	stroke	E	зС	DA	G	GA	GB	н	J	к		мм	МГ	. NI			Р		РВ	PW	G	R	s
[mm]		[mm			, -	בט	3	un.	G.D.		١	١.	_	IVIIVI	IVIL	1	`	Nil	N	TF	1.0	. **	3	"	
20			100, 12: 00. 250		62	10	36	10.5	8.5	83	18	18	24	M5 x 0.8	13	M5 x	0.8 R	Rc 1/8	NPT 1/8	G 1/8	10.5	25	18	70	30
25		00, 350		78	.5 62.	12	42	11.5	9	93	21	21	30	M6 x 1.0	15	M6 x	1.0 R	Rc 1/8	NPT 1/8	G 1/8	13.5	30	26	78	38
Bore size	т	U	VA	VB		1	WA					WB			х	ХА	хв								
[mm]	'	١ ٠	VA	VD	75 st or les	Over 75 to 175 s	t Over	175 st i0 st 0	er 250 st	75 st or less	Over 75 to 175	st Ove	er 175 st 250 st	Over 250 st	^	^A	^ P								
20	81	54	72	44	44	120	20	00	300	39	77	-	117	167	28	3	3.5	_							
25	91	64	82	50	44	120	20	00	300	39	77	1	117	167	34	4	4.5								

MGPM (Slide bearing)/A, DB, E Dimensions [mm]

Bore size		Α		DB		E	
[mm]	25 st or less	Over 25 st to 175 st	Over 175 st	υв	25 st or less	Over 25 st to 175 st	Over 175 st
20	78	84.5	122	12	0	6.5	44
25	78.5	85	122	16	0	6.5	43.5
	•						


MGPL (Ball bushing),		
MGPA (High precision ball bushing)/A, DB, E Dimensions	[mm]	

Bore size		Α				E	
[mm]	75 st or less	Over 75 st to 175 st	Over 175 st	DB	75 st or less	Over 75 st to 175 st	Over 175 st
20	80	104	122	10	2	26	44
25	85.5	104.5	122	13	7	26	43.5


End Lock Mechanism

Dimens	sions			[mm]
Bore size [mm]	DL	DM	HR	HN
20	21	19	10.5	22
25	26.5	16	8	19.5

Dimensions: Ø32 to Ø63



With rod end lock



End lock mechanism (Manual release lock type)



1	-slot o	dime	nsic	ons		[mm]				
8	Bore size		T-slot	dimer	nsions					
	[mm]	а	b	С	d	е				
	32	6.5	10.5	5.5	3.5	9.5				
	40	6.5	10.5	5.5	4	11				
Ξ	50	8.5	13.5	7.5	4.5	13.5				
Г	63	11	17.8	10	7	18.5				

- *: For intermediate strokes other than standard strokes, refer to the Manufacture of Intermediate Stroke on page 576.
- *: Rc, NPT and G ports can be selected. (Refer to page 575.)

MGPM,	IGPM, MGPL Common Dimensions [mm]															[mm]										
Bore size [mm]		dard st [mm]	roke	В	С	DA	FA	FB	G	GA	GB	н	на	J	к	L	ММ	ML	NN	ОА	ов	OL	Nil	P	Τ.	TF
32	0.5		_	84.5	62.5	16	12	10	48	12.5	9	112	M6	24	24	34	M8 x 1.25	20	M8 x 1.25	6.6	11	7.5	Rc1/	8 NPT1	/8 G	1/8
40	100,	, 50, 7 125, 1	150	91	69	16	12	10	54	14	10	120	M6	27	27	40	M8 x 1.25	20	M8 x 1.25	6.6	11	7.5	Rc1/	8 NPT1	/8 G	1/8
50		200, 2 350, 4		97	69	20	16	12	64	14	11	148	M8	32	32	46	M10 x 1.5	22	M10 x 1.5	8.6	14	9	Rc1/	4 NPT1	/4 G	1/4
63	500,	550, -	100	102	74	20	16	12	78	16.5	13.5	162	M10	39	39	58	M10 x 1.5	22	M10 x 1.5	8.6	14	9	Rc1/	4 NPT1	/4 G	1/4
Bore size [mm]	РА	РВ	PW	Q	R	s	Т	U	VA	νв	75 st Or or less to		/A Over 175 st to 250 st	Over 250	st 75 st or less	Over 7: to 175	WB 5 st Over 175 to 250	5 st Over 2	50 st X	ХА	хв	хс	XL	YY	YL	z
32	32	15	35.5	30	96	44	110	78	98	63		124	200	300	45	83	121	17	1 42	4	4.5	3	6	M8 x 1.25	16	21
40	38	18	39.5	30	104	44	118	86	106	72	48	124	200	300	46	84	122	2 17	2 50	4	4.5	3	6	M8 x 1.25	16	22
50	34	21.5	47	40	130	60	146	110	130	92	48	124	200	300	48	86	124	1 17	4 66	5	6	4	8	M10 x 1.5	20	24
63	39	28	58	50	130	70	158	124	142	110	52	128	200	300	50	88	124	1 17	4 80	5	6	4	8	M10 x 1.5	20	24


MGPM (Slide bear Bore size [mm] 25 st or less 32 97 102 40 97 102 50 106.5 118 63 106.5 118


ring)/A, DB, E Dimensions [mm]						MGPL (Bal	l bushing	j), MGPA	(High pr	ecision b	all bu	ushing)/A	, DB, E D	imensio	ns [mm]		
١		DB		E		Bore size		Α				E					
25 st '5 st	Over 175 st	υБ	25 st or less	Over 25 st to 175 st	Over 175 st	[mm]	25 st or less	Over 25 st to 75 st	Over 75 st to 175 st	Over 175 st	DB	25 st or less	Over 25 st to 75 st	Over 75 st to 175 st	Over 175 st		
)2	140	20	12.5	17.5	55.5	32	84.5	98	118	140	16	0	13.5	33.5	55.5		
)2	140	20	6	11	49	40	91	98	118	140	16	0	7	27	49		
8	161	25	9.5	21	64	50	97	114	134	161	20	0	17	37	64		
8	161	25	4.5	16	59	63	102	114	134	161	20	0	12	32	59		

End Loc	End Lock Mechanism Dimensions [mm]									
Bore size [mm]	DL	DM	HR	HN	LL	МО				
32	22	22	9.5	21	15	15				
40	26	23	11.5	25.5	21	19				
50	24	23	13	27	21	19				
63	25	25.5	11	25	21	19				



Dimensions: Ø80, Ø100





- *: For intermediate strokes other than standard strokes, refer to the Manufacture of Intermediate Stroke on page 576.
- *: Rc, NPT and G ports can be selected. (Refer to page 575.)

MGPM,	MG	PL C	omi	mor	า Di	me	nsi	ons																		[mm]
Bore size [mm]	Sta	ndard str [mm]	oke	В	С	D.	A F	A	FВ	G	GA	GB	GC	Н	на	۲	JA	JB	K	L	ММ	N	IL	NN	ОА	ОВ
80), 75, 100 175, 200		146.5	106	5 2	5 2	2	18	91.5	19	15.5	14.5	202	M12	45.5	38	7.5	46	54	M12 x 1.	75 2	5 N	Л12 x 1.75	10.6	17.5
100		0, 350, 4		166	116	3	0 2	5	25 1	111.5	23	19	18	240	M14	55.5	45	10.5	5 56 62 M14 x 2.0			.0 3	1 N	M14 x 2.0	12.5	20
Bore size		P		Б.	nn.	DW		_		T -	l	\/A	VD		١	VA			WB v vv			W	YL	7		
[mm]	Nil	N	TF	PA	РВ	PW	Q	R	s	'	U	VA	VB	50 st or less	Over 50 s to 150 st	t Over 15 to 250	Ost C	over 50 st o	50 st or less	Over 50 st to 150 st	Over 150 st to 250 st	Over 250 st	^	YY	I YL	
80	Rc3/8	NPT3/8	G3/8	64.5	25.5	74	52	174	75	198	156	180	140	52	128	20	0 3	00	54	92	128	178	100	M12 x 1.75	24	28
100	Rc3/8	NPT3/8	G3/8	67.5	32.5	89	64	210	90	236	188	210	166	72	148	22	0 3	20	47	85	121	171	124	M14 x 2.0	28	11

MGPM (Slide bearing)/A. DB. E Dimensions [mm]

		0, ,						
Bore size	Į.	١	DB	E				
[mm]	150 st or less	Over 150 st	06	150 st or less	Over 150 st			
80	146.5	193	30	0	46.5			
100	166	203	36	0	37			

MGPL (Ball bushing),

SMC

MGPA (High precision ball bushing)/A, DB, E Dimensions [n	nm]
---	-----

Bore size		4	DB	E	
[mm]	150 st or less	Over 150 st	סט	150 st or less	Over 150 st
80	160	193	25	13.5	46.5
100	180	203	30	14	37

End Lock Mechanism

582

Dimens	Dimensions [mm]										
Bore size [mm]	DL	DM	HR	HN							
80	45.5	40.5	24	38.5							
100	49	43.5	26.5	41							





MGP Series With End Lock Specific Product Precautions

Be sure to read this before handling the products. Refer to page 8 for safety instructions and pages 9 to 18 for actuator and auto switch precautions.

Use Recommended Air Pressure Circuit.

· It is necessary for proper locking and unlocking.





Handling

1. Do not use a 3 position solenoid valve.

Avoid using this cylinder in combination with a 3 position solenoid valve (particularly the closed center metal seal type). If air pressure becomes sealed inside the port on the side that contains the lock mechanism, the lock will not engage. Even if the lock is engaged at first, the air that leaks from the solenoid valve could enter the cylinder and cause the lock to disengage as time elapses.

2. Back pressure is necessary for unlocking.

Before starting, make sure that air is supplied to the side that is not equipped with a lock mechanism as shown in the diagram above. Otherwise, the lock may not disengage. (Refer to "Rock Disengagement".)

3. Disengage the lock before installing or adjusting the cylinder.

The lock could become damaged if the cylinder is installed with its lock engaged.

Operate the cylinder at a load ratio of 50% or less.
 The lock might not disengage or might become damaged if a load ratio of 50% is exceeded.

5. Do not synchronize multiple cylinders.

Do not operate two or more end lock cylinders synchronized to move a single workpiece because one of the cylinder locks may not be able to disengage when required.

Operate the speed controller under meterout control.

If operated under meter-in control, the lock might not disengage.

7. On the side that has a lock, make sure to operate at the stroke end of the cylinder.

The lock might not engage or disengage if the piston of the cylinder has not reached the stroke end.

- 8. Do not use the air cylinder as an air-hydro cylinder. This may result in oil leak.
- The position adjustment of the auto switch should be performed at two positions; a position determined by the stroke and a position after the backlash movement (by 2 mm).

When a 2-color indicator auto switch is adjusted to show green at the stroke end, the indication may turn red when the cylinder returns by the backlash. This, however, is not an error.

Operating Pressure

⚠Caution

 Supply air pressure of 0.15 MPa or higher to the port on the side that has the lock mechanism, as it is necessary for disengaging the lock

Exhaust Air Speed

1. The lock will engage automatically if the air pressure at the port on the side that has the lock mechanism becomes 0.05 MPa or less. Be aware that if the piping on the side that has the lock mechanism is narrow and long, or if the speed controller is located far from the cylinder port, the exhaust air speed could become slower, involving a longer time for the lock to engage. A similar result will ensure if the silencer that is installed on the exhaust port of the solenoid valve becomes cloqued.

Lock Disengagement

△Warning

1. To disengage the lock, make sure to supply air pressure to the port on the side without a lock mechanism, thus preventing the load from being applied to the lock mechanism. (Refer to the recommended air pressure circuit.) If the lock is disengaged when the port on the side that does not contain a lock mechanism is in the exhausted state and the load is being applied to the lock mechanism, undue force will be applied to the lock mechanism, and it may damage the lock mechanism. Also, it could be extremely dangerous, because the piston rod could move suddenly.

Manual Disengagement

** ∴** Caution

1. Non-locking type manual release

Insert the bolt, which is provided as an accessory part, through the rubber cap (it is not necessary to remove the rubber cap). Screw the bolt into the lock piston and pull the bolt to disengage the lock. Releasing the bolt will re-engage the lock.



The bolt size, pulling force, and the stroke are listed below.


Bore size [mm]	Thread size	Pulling force	Stroke [mm]
20, 25, 32	M2.5 x 0.45 x 25 L or more	4.9 N	2
40, 50, 63	M3 x 0.5 x 30 L or more	10 N	3
80, 100	M5 x 0.8 x 40 L or more	24.5 N	3

Bolt should be detached under normal operation, otherwise it may cause malfunction of the locking feature.

2. Locking type manual release

Turn 90° counterclockwise while pushing the M/O knob. Lock is released when ▲ on the cap and ▼ OFF mark on the M/O knob correspond. (Lock remains released.)


When locking is desired, turn 90° clockwise while fully pushing the M/O knob and correspond ▲ on the cap and ▼ ON mark on the M/O knob. Confirm the correct position by click sound "click". Otherwise, lock may not be engaged.



583

Compact Guide Cylinder/ Heavy Duty Guide Rod Type MGPS Series \$50, \$80

How to Order



Applicable Auto Switches/Refer to pages 1289 to 1383 for further information on auto switches.

API	DIICADIE AUTO SWI	CHES/Re	_	o pages 1289	10 1383	tor turtne	er intorma	tion on auto	switches.							
			light	145.	L	oad volta	ge	Auto swit	ch model	Lead	wire I	ength	[m]	D		
Туре	Special function	Electrical entry	Indicator	Wiring (Output)			AC	Perpendicular	endicular In-line		1 (M)	3 (L)	5 (Z)	Pre-wired connector	Applicable load	
			П	3-wire (NPN)		5 V.12 V		M9NV	M9N	•	•	•	0	0	IC	
ڃ	_			3-wire (PNP)		5 V, 12 V		M9PV	M9P	•	•	•	0	0	circuit	
switch				2-wire		12 V]	M9BV	M9B	•	•	•	0	0	_	
	Disappostic indication			3-wire (NPN)		5 V,12 V		M9NWV	M9NW	•	•	•	0	0	IC	
육	Diagnostic indication (2-color indicator)			3-wire (PNP)				M9PWV	M9PW	•	•	•	0	0	circuit	Relay,
<u>a</u>	(2-color indicator)	Grommet	Yes	2-wire	24 V] —	M9BWV	M9BW	•	•	•	0	0	_	PLC
state	Mater registent			3-wire (NPN)		5 V.12 V		M9NAV*1	M9NA*1	0	0	•	0	0	IC	[[
	Water resistant (2-color indicator)			3-wire (PNP)		J V, 12 V		M9PAV*1	M9PA*1	0	0	•	0	0	circuit	
Solid	(2-color indicator)			2-wire		12 V		M9BAV*1	M9BA*1	0	0	•	0	0		
	Magnetic field resistant (2-color indicator)			(Non-polar)		_		_	P3DWA	•	_	•	•	0	_	
o switch		Grommet	Yes	3-wire (NPN equivalent)	_	5 V	_	A96V	A96	•	_	•	_	_	IC circuit	-
dart		Grommet			12 V	100 V	A93V*2	A93	•	•	•	•	_	_	Relay,	
Se	Reed auto		No	2-wire	24 V	12 V	100 V or less	A90V	A90	•	—	•	_	_	IC circuit	PLC

- *1: Water resistant type auto switches can be mounted on the above models, but in such case SMC cannot guarantee water resistance. Please consult with SMC regarding water resistant types with the above model numbers.
- *2: 1 m type lead wire is only applicable to the D-A93.
- *: Lead wire length symbols: 0.5 m········Nii (Example) M9NW *: Solid state auto switches marked with "O" are produced upon receipt of order. 1 m········ M 3 m········ L (Example) M9NWM L
- *: Since there are other applicable auto switches than listed above, refer to page 595 for details.

(Example) M9NWZ

- *: For details about auto switches with pre-wired connector, refer to pages 1358 and 1359.
- *: Auto switches are shipped together, (but not assembled).

5 m.-

Compact Guide Cylinder Heavy Duty Guide Rod Type MGPS Series



Symbol Rubber bumper





Made to Order: Individual Specifications (For details, refer to pages 597 and 598.)

Symbol	Specifications
-X867	Side porting type (Plug location changed) *1

*1: The shape is the same as the current product.



Symbol	Specifications
-XB13	Low speed cylinder (5 to 50 mm/s)
-XC85	Grease for food processing equipment

Refer to pages 592 to 596 for cylinders with auto switches.

- Minimum stroke for auto switch mounting
- Auto switch proper mounting position (detection at stroke end) and its mounting height
- Operating range
- · Auto switch mounting brackets/Part no.
- · Auto switch mounting

Specifications

Bore size [mm]	50	80				
Action	Double	acting				
Fluid	А	ir				
Proof pressure	1.5	MPa				
Maximum operating pressure	1.0	MPa				
Minimum operating pressure	0.1	MPa				
Ambient and fluid temperature	−10 to 60°C	(No freezing)				
Piston speed *1	50 to 40	00 mm/s				
Cushion	Rubber bumper on both ends					
Lubrication	Not required (Non-lube)					
Stroke length tolerance	+1.5 +0 mm					

*1: Maximum speed with no load. Depending on the operating conditions, the piston speed may not be satisfied. Make a model selection, considering a load according to the graph on pages 586 to 588.

Standard Strokes

Bore size [mm]	Standard stroke [mm]
50, 80	25, 50, 75, 100, 125, 150, 175, 200

Manufacture of Intermediate Stroke

Description	Spacer installation type Spacers are installed in the standard stroke cylinder. Available in 5 mm stroke increments.
Part no.	Refer to "How to Order" for the standard model numbers on page 584.
Applicable stroke [mm]	5 to 195
Example	Part no.: MGPS50-35 A spacer 15 mm in width is installed in a MGPS50-50. C dimension is 94 mm.

intermediate stroke (in 1 mm increments) based on an exclusive body will be available upon request for special.

Theoretical Output




Bore size	Rod size [mm]	ize Operating direction	Piston area	Operating pressure [MPa]									
[mm]			[mm ²]	0.2	0.3	0.4	0.5	0.6	0.7	0.8	0.9	1.0	
50		OUT	1963	393	589	785	982	1178	1374	1571	1767	1963	
50	20	IN	1649	330	495	660	825	990	1155	1319	1484	1649	
00	05	OUT	5027	1005	1508	2011	2513	3016	3519	4021	4524	5027	
80	25	IN	4536	907	1361	1814	2268	2721	3175	3629	4082	4536	

^{*:} Theoretical output [N] = Pressure [MPa] x Piston area [mm2]

Weights


									[kg]			
Bore size		Standard stroke [mm]										
[mm]	25	50	75	100	125	150	175	200				
	50	3.90	4.68	5.74	6.52	7.30	8.08	8.86	9.64			
ſ	80	9.21	10.7	13.0	14.5	15.9	17.9	18.9	20.3			

Allowable Rotational Torque of Plate



							I [IN-III]				
Standard stroke [mm]											
25	50	75	100	125	150	175	200				
15	12	16	15	13	12	11	9.8				
49	41	51	45	41	38	35	32				
	15	15 12	25 50 75 15 12 16	25 50 75 100 15 12 16 15	25 50 75 100 125 15 12 16 15 13	25 50 75 100 125 150 15 12 16 15 13 12	25 50 75 100 125 150 175 15 12 16 15 13 12 11				

Non-rotating Accuracy of Plate




For non-rotating accuracy θ without load, use a value no more than the values in the table as a guide.

Bore size [mm]	Non-rotating accuracy θ
50	±0.05°
80	±0.04°



MGPS Series **Model Selection**

Selection Conditions



Selection Example 1 (Vertical Mounting)

Selection conditions

Mounting: Vertical

Stroke: 50 stroke


Maximum speed: 200 mm/s Load mass: 100 kg

Eccentric distance: 100 mm

Find the point of intersection for the load mass of 100 kg and the eccentric distance of 100 mm on graph 1, based on vertical mounting, 50 mm stroke, and the speed of 200 mm/s.

→ MGPS80-50 is selected.

(1) 50 stroke or less, V = 200 mm/s or less



Selection Example 2 (Horizontal Mounting)

Selection conditions

Mounting: Horizontal

Distance between plate and load center of gravity: 50 mm


Maximum speed: 200 mm/s

Load mass: 30 kg Stroke: 100 stroke

Find the point of intersection for the load mass of 30 kg and 100 stroke on graph 5, based on horizontal mounting, the distance of 50 mm between the plate and load center of gravity, and the speed of 200 mm/s.

→MGPS80-100 is selected.

(5) L = 50 mm, V = 200 mm/s or less




· When the maximum speed exceeds 200 mm/s, the allowable load mass is determined by multiplying the value shown in the graph at 400 mm/s by the coefficient listed in the table below


Maximum	Up to 300 mm/s	Up to 400 mm/s	Up to 500 mm/s
Coefficient	1.7	1	0.6


[·] Use the Guide Cylinder Selection Software, when the eccentric distance is 200 mm or more.


- Operating pressure 0.4 MPa ---- Operating pressure 0.5 MPa or more

MGPS50, 80











[·] Use the Guide Cylinder Selection Software, when the eccentric distance is 200 mm or more.





Horizontal Mounting Slide Bearing

MGPS50, 80











Operating Range when Used as Stopper



- When selecting a model with a longer L dimension, be sure to choose a bore size which is sufficiently large.
 Refer to the horizontal mounting selection graph if line
- *: Refer to the horizontal mounting selection graph if line pressure is to be applied by a roller conveyor after the workpiece is stopped.




⚠ Caution

Caution on handling

When using as a stopper, select a model with 50 stroke or less.

Construction



50 stroke or less

Component Parts

No.	Description	Material	Note				
1	Body	Aluminum alloy	Hard a	anodized			
2	Piston	Aluminum alloy					
3	Piston rod	Carbon steel	Hard chrome plating				
4	Collar	Aluminum alloy casted	Painted				
5	Bushing	Bearing alloy					
6	Head cover	Aluminum alloy	ø50	Chromated			
	neau cover	Aluminum alloy	ø80	Painted			
7	Guide rod	Carbon steel	Hard chr	ome plating			
8	Plate	Carbon steel	Nickel plating				
9	Plate mounting bolt A	Carbon steel	Nickel plating	For piston rod			
10	Plate mounting bolt B	Carbon steel	Nickel plating	For guide rod			

Component Parts

No.	Description	Material	Note
11	Retaining ring	Carbon tool steel	Phosphate coated
12	Bumper A	Urethane	
13	Bumper B	Urethane	
14	Magnet	_	
15	Hexagon socket head taper plug	Carbon steel	Nickel plating
16	Slide Bearing	Bearing alloy	
17*	Piston seal	NBR	
18*	Rod seal	NBR	
19*	Gasket A	NBR	
20*	Gasket B	NBR	

Replacement Parts/Seal Kit


Bore size [mm]	Kit no.	Contents						
50	MGP50-PS	Set of nos. above ①, ⑧, ⑨, ②						
80	MGP80-PS	Set of flos. above (f), (g), (g), (g)						


^{*:} Seal kit includes $\ensuremath{\mathfrak{D}}$ to $\ensuremath{\mathfrak{D}}$. Order the seal kit, based on each bore size.

^{*:} Since the seal kit does not include a grease pack, order it separately.

Grease pack part no.: GR-S-010 (10 g)

Dimensions





- *: For intermediate strokes other than standard strokes, refer to the Manufacture of Intermediate Stroke on page 585.
- *: Rc, NPT and G ports can be selected. (Refer to page 584.)


Dimer	nsio	ns																							[mm]
Bore size [mm]		lard stro [mm]		25,		A Ove	r 50 st	В	С	DA	DB	25, 50 st Ove		er 50 st	FA	FB	G	GA	GB	GC	н	на	J	κ	L
50		0, 75, 10			86	1	10	86	44	20	30	0 24 2		29.5	12.5	72	14	11	12	160	M10	35	37	50	
80	125, 1	50, 175, 2	200	1	118	1	51	118	65	25	45	0	0 33 3		35	18	95	19	24	14.5	242	M12	47	48	66
Bore size [mm]	М	M	МІ	L	NN	ı	NL	OA	ОВ	ос	OL	P Nil N T			TF	PA	РВ	PW	Q	QA	QB	RA	RB	RR	
50	M12:	x 1.75	20)	M10 x	1.5	20	10.6	17.5	59	13	Rc 1/4	NPT	1/4	1/4	9	24.5	50	32	16	7	48	140	M8 x	1.25
80	M16	x 2.0	32	2 1	V112 x	1.75	24	12.5	20	72	17.5	Rc 3/8	NPT	3/8	3/8	14.5	29	77	40	18	9	80	200	M10:	x 1.5
Bore size [mm]	RL	s	Т		U	VA	VВ	25 s	st 50	WA 0, 75, 100 st	Over 1	WB 100 st 25 st 50.75.100 s				er 100 st	х	XA	хв	хс	XL	Y	Y	YL	z
50	14	50	15	6	116	140	100	24		48	12	4 36		48		86	68	5	6	4	8	M12 x	1.75	24	24
80	20	65	22	8	170	214	138	28		52	12	8 4	12	54		92	100	6	7	5	10	M14	x 2.0	28	28

Auto Switch Mounting

Auto Switch Proper Mounting Position (Detection at stroke end) and Its Mounting Height/MGP-Z (Basic type), MGP-AZ (Air cushion), MGPS (Heavy duty guide rod type)

D-M9□/M9□V D-M9□W/M9□WV D-M9□A/M9□AV


D-A9□/A9□V ø12 to ø100







D-P3DWA

ø25 to ø63











D-P4DW



*: The MGP-Z (Basic type) is shown as a representative example.

ø80, ø100



Applicable Cylinder: MGP-Z (Basic type) Auto Switch Proper Mounting Position

Auto Switch Proper Mounting Position [mm												
Auto switch model	D-M9 D-M9 D-M9 D-M9 D-M9	□V □W □WV □A	D-A	DWA	D-P4DW *1							
Bore size	A B		Α	В	Α	В	Α	В				
12	7.5	9.5	3.5	5.5	_	_	_	_				
16	10.5 10.5		6.5	6.5	_	_	_	_				
20	12.5	12.5	8.5	8.5	_	_ _		_				
25	11.5	14	7.5	10	7	9.5	_	_				
32	12.5	13	8.5	9	8	8.5	5.5	6				
40	15.5	16.5	11.5	12.5	11	12	8.5	9.5				
50	14.5	17	10.5	13	10	12.5	7.5	10				
63	16.5	20	12.5	16	12	15.5	9.5	13				
80	18	26	14	22	13.5	21.5	11	19				
100	21.5	32.5	17.5	28.5	17	28	14.5	25.5				

^{*1:} The auto switch mounting bracket BMG7-032 is used.

Applicable Cylinder: MGP-AZ (Air cushion) Auto Switch Proper Mounting Position

Auto switch model	D-M9 \ V \\ D-M9 \ W \\ D-M9 \ A \\ R \\ R		D-A		D-P3	DWA	D-P4DW *1		
Bore size	A B		Α	В	Α	В	Α	В	
16	25	20.5	21	16.5	_	_	_	_	
20	27	23	23	19				_	
25	27	23	23	19	22.5	18.5	_	_	
32	21	29	17	25	16.5	24.5	14	22	
40	25.5	31.5	21.5	27.5	21	27	18.5	24.5	
50	26	30.5	22	26.5	21.5	26	19	23.5	
63	30	31.5	26	27.5	25.5	27	23	24.5	
80	30.5 38.5		26.5	34.5	26	26 34		31.5	
100	34.5	44	30.5	40	30	30 39.5		37	

^{*1:} The auto switch mounting bracket BMG7-032 is used.

Applicable Cylinder: MGPS (Heavy duty guide rod) Auto Switch Proper Mounting Position

\	D-M9 D-M9 D-M9 D-M9 D-M9	M9 U				7' 30 59 7P 69 7PV 7' W 7' V	D-P3	DWA	D-P4	↓DW *2
size \	Α	В	Α	В	Α	В	Α	В	Α	В
50	12.5	16.5	8.5	12.5	7.5	11.5	8	12	7	11
80	18	23.5	14	19.5	13	18.5	13.5	19	12.5	18

^{*1:} The auto switch mounting bracket BMG2-012 is used.

Applicable Cylinder: MGP-Z (Basic type)

Auto Switc	h Pro	per N	/lount	ting H	leight	t		[mm]	
Auto switch model	D-M9	D-M9□V D-M9□WV D-M9□AV		D-A9□V		DWA	D-P4DW*1		
Bore size \	Hs	Ht	Hs	Ht	Hs	Ht	Hs	Ht	
12	19.5	_	17	_	_	_	_	_	
16	22	_	19.5	_	_	_	_	_	
20	24.5	_	22	_	_	_	_	_	
25	26	_	24	_	32.5	_	_	_	
32	29	_	26.5	_	35.5	_	40	_	
40	33	_	30.5	_	39	_	44	_	
50	38.5	_	36	_	44.5	_	49.5	_	
63	45.5	_	43	_	51.5	_	56.5	_	
80	45	74	43	71.5	49.5	80.5	61	74	
100	55	85.5	53	83	59.5	92	71.5	86	

^{*1:} The auto switch mounting bracket BMG7-032 is used.

Applicable Cylinder: MGP-AZ (Air cushion)

Auto Switch Proper Mounting Height [mm]												
Auto switch model	D-M9 D-M9 D-M9	□WV	v		D-P3	DWA	D-P4DW*1					
Bore size \	Hs	Ht	Hs	Ht	Hs	Ht	Hs	Ht				
16	22	_	19.5	_	_	_	_	_				
20	24.5	_	22	_	_	_	_	_				
25	26	_	24	_	32.5	_	_	_				
32	29	_	26.5	_	35.5	_	40	_				
40	33	_	30.5	_	39	_	44	_				
50	38.5	_	36	_	44.5	_	49.5	_				
63	45.5	_	43	_	51.5	_	56.5	_				
80	45	74	43	71.5	49.5	80.5	61	74				
100	55	85.5	53	83	59.5	92	71.5	86				

^{*1:} The auto switch mounting bracket BMG7-032 is used.

Applicable Cylinder: MGPS (Heavy duty guide rod)

Auto S	witch Pi	ope	r M	oun	tıng	Hei	ght				[mm]
Auto switch model	*1 D-M9	D-M9 D-M9 D-M9	□WV	D-A	*2	D-Y6 D-Y7 D-Y7	P۷	D-P3	*2 DWA	D-P4	*3 4 DW
size \	Hs	Hs	Ht	Hs	Ht	Hs	Ht	Hs	Ht	Hs	Ht
50	32.5	38.5	_	36	_	34	_	44.5	_	50	-
80	40	45	74	43	71.5	41	70	49.5	78.5	61	84.5

^{*1:} For the D-M9 \square , the auto switch mounting bracket BMG2-012 is used.

[mm]

^{*:} Adjust the auto switch after confirming the operating conditions in the actual setting.

^{*2:} The auto switch mounting bracket BMG1-040 is used.

^{*:} Adjust the auto switch after confirming the operating conditions in the actual setting.

^{*2:} The auto switch mounting bracket BMG2-012 is used.

^{*3:} The auto switch mounting bracket BMG1-040 is used.

Auto Switch Proper Mounting Position (Detection at stroke end) and Its Mounting Height/MGP (With end lock)

Applicable cylinder: MGP series, With end lock

With rod end lock

D-M9□ D-M9□A **D-Z7**□ D-Y7P D-M9□V D-M9□AV D-Z80 D-Y7PV D-M9□W D-A9□ D-Y59□ D-Y7□W D-M9□WV D-A9□V D-Y69□ D-Y7□WV D-Y7BA

Auto Switch Proper Mounting Position

Auto Switch Proper Mounting Position [mm]											
Auto switch model Bore	D-M9 \\ D-M9 \		D-Y590 D-Y690 D-Y70 D-Y70	D-Z7□/Z80 D-Y59□/Y7P D-Y69□/Y7PV D-Y7□W D-Y7□WV D-Y7BA		*3, *4 DWA	D-P4DW*2				
size \	Α	В	Α	В	Α	В	Α	В	Α	В	
20	40	7	36	3	35	2	_	_	_	_	
25	40.5	7	36.5	3	35.5	2	36	2.5*5	_	_	
32	37.5	10	33.5	6	32.5	5	33	6	32	4.5	
40	43.5	10.5	39.5	6.5	38.5	5.5	39	6	38	5	
50	44.5	9.5	40.5	5.5	39.5	4.5	40	5	39	4	
63	47	12	43	8	42	7	42.5	7.5	41.5	6.5	
80	68	23.5	64	19.5	63	18.5	63.5	19	62.5	18	
100	72.5	28.5	68.5	24.5	67.5	23.5	68	24	67	23	

- *1: The auto switch mounting bracket BMG2-012 is used.
- *2: The auto switch mounting bracket BMG1-040 is used.
- *3: The auto switch mounting bracket BMG10-025 is used.
- *4: This shows the top end position of the mounting bracket when the auto switch is put in contact with the mounting bracket.
- *5: When mounted on the head end of ø25, the tip of the BMG2-012 protrudes 3.5 mm from the cylinder body
- *: Adjust the auto switch after confirming the operating conditions in the actual setting.

Auto Switch Proper Mounting Height

(D-P3DWA)		[mm]
Bore size	Hs	Ht
25	32	_
32	35	_
40	39	_
50	44.5	_
63	51.5	_
80	49.5	78.5
100	60	90

Auto Switch Proper Mounting Height

(D-P4DW)		[mm]
Bore size	Hs	Ht
32	41.5	_
40	44.5	_
50	50	_
63	57	_
80	61	84.5
100	71	96.5

With head end lock

D-M9□	D-M9□A	D-Z7 □	D-Y7P
D-M9□V	D-M9□AV	D-Z80	D-Y7PV
D-M9□W	D-A9□	D-Y59□	D-Y7□W
D-M9□WV	D-A9□V	D-Y69□	D-Y7□WV
			D V7DA


uto Switch Proper Mounting Position

Auto St	vitcn	Prop	er w	ounti	ng Po	ositio	n			
Auto switch model	D-M9 D-M9 D-M9 D-M9	M9 U M9 W M9 WV M9 A M9 AV B 38 5 38 5 37 5 39.5	D-A9 D-Y7 D-Y7 D-Y7 D-Y7 D-Y7 D-Y7 D-Y7 D-Y7		D-P3	*3, *4 DWA	D-P4DW *2			
size \	Α	В	Α	В	Α	В	Α	В	Α	В
20	9	38	5	34	4	33			_	_
25	9.5	38	5.5	34	4.5	33	6	33.5	_	_
32	10.5	37	6.5	33	5.5	32	6	32.5	5	31.5
40	14.5	39.5	10.5	35.5	9.5	34.5	10	35	9	34
50	12.5	41.5	8.5	37.5	7.5	36.5	8	37	7	36
63	15	44	11	40	10	39	10.5	39.5	9.5	38.5
80	18	73.5	14	69.5	13	68.5	13.5	69	12.5	68
100	22.5	78.5	18.5	74.5	17.5	73.5	18	74	17	73


- *1: The auto switch mounting bracket BMG2-012 is used.
- *2: The auto switch mounting bracket BMG1-040 is used.
- *3: The auto switch mounting bracket BMG10-025 is used.
- *4: This shows the top end position of the mounting bracket when the auto switch is put in contact with the mounting bracket.
- *: Adjust the auto switch after confirming the operating conditions in the actual setting.


Auto switch

For D-P3DWA (*: Cannot be mounted on bore size Ø20.)



For D-P4DW (*: Cannot be mounted on bore size ø25 or less.)






ø80, ø100

For 25 stroke

*: For bore sizes ø40 to ø63 with two auto switches, one switch is mounted on each side.





Mounting of Auto Switch

. Caution

In the case of 25 st or less with head side end lock type, it might not insert auto switch from the rod side.

In this case, install it after removing the plate temporarily.

Regarding the plate removal and the way of assembly, please consult





[mm]

Minimum Stroke for Auto Switch Mounting

											[mm]
Auto switch model	Number of auto switches	ø 12	ø 16	ø 20	ø 25	ø 32	ø 40	ø 50	ø 63	Ø 80	ø100
D-M9□V	1 pc.						5				
D-IVI9 V	2 pcs.						5				
D-M9□	1 pc.		5	5 *1					5		
D-IVI3	2 pcs.	10 *1					10				
D-M9□W	1 pc.					5	*2				
D-IVI3 UV	2 pcs.	10 *2					10				
D-M9□WV	1 pc.						*2				
D-M9□AV	2 pcs.						10				
D-M9□A	1 pc.						*2				
D-IVI3	2 pcs.					10) *2				
D-A9□	1 pc.			5 *1					5		
D-A3	2 pcs.		10	0 *1					10		
D-A9□V	1 pc.						5				
-	2 pcs.					1	10				
D-Z7□	1 pc.	-	_	5	*1				5		
D-Z80	2 pcs.	-	_				1	0			
D-Y59□	1 pc.			5	*1				5		
D-Y7P	2 pcs.	-	_					0			
D-Y69□	1 pc.	-	_					5			
D-Y7PV	2 pcs.	-						5			
D-Y7□W	1 pc.	-	_					*2			
D-Y7□WV	2 pcs.	-	_					*2			
D-Y7BA	1 pc.	-						*2			
D-17DA	2 pcs.	-	_				10) *2			
D-P3DWA	1 pc.							15 *2			
D-I ODWA	2 pcs.							15 *2			
	1 pc.			_					*2		
D-P4DW	2 pcs. (Different surfaces)) *2	,	
	2 pcs. (Same surface)			_		1	7	75		1 1	10

^{*1:} Confirm that it is possible to secure the minimum bending radius of 10 mm of the auto switch lead wire before use.

Operating Range

										[mm]
Auto switch model					Bore	size				
Auto switch model	12	16	20	25	32	40	50	63	80	100
D-M9□/M9□V D-M9□W/M9□WV D-M9□A/M9□AV	3.5	5	5	5	6	6	6	6.5	6	7
D-A9□/A9□V	7	9	9	9	9.5	9.5	9.5	11	10.5	10.5
D-Z7□/Z80	_	_	10	10	10.5	10.5	10.5	11.5	11.5	12
D-Y59□/Y69□ D-Y7P/Y7PV D-Y7□W/Y7□WV D-Y7BA	_	_	7.5	7	6.5	6	7	8	9.5	10
D-P3DWA	_	_	_	5.5	6.5	6	6	6.5	6	7
D-P4DW	_	_	_	_	5	4	4	5	4	4

^{*:} Values which include hysteresis are for guideline purposes only, they are not a guarantee (assuming approximately ±30% dispersion) and may change substantially depending on the ambient environment.

Other than the applicable auto switches listed in How to Order, the following auto switches are mountable. *: The auto switches other than the D-P4DW are mountable on the models with end lock and heavy duty guide rod type only.

Refer to pages 1289 to 1383 for the detailed specifications.

Туре	Model	Electrical entry	Features
Reed	D-Z73, Z76	Grommet (In-line)	_
need	D-Z80	Grommet (m-line)	Without indicator light
	D-P4DW	Grommet (In-line)	Magnetic field resistant (2-color indicator) Bore size: ø32 to ø100
Solid state	D-Y69A, Y69B, Y7PV	Crammat (Darmandiaular)	_
	D-Y7NWV, Y7PWV, Y7BWV	Grommet (Perpendicular)	Diagnostic indication (2-color indicator)
	D-Y59A, Y59B, Y7P		_
	D-Y7NW, Y7PW, Y7BW	Grommet (In-line)	Diagnostic indication (2-color indicator)
	D-Y7BA		Water resistant (2-color indicator)

^{*:} With pre-wired connector is also available for solid state auto switches.

^{*:} When installing the D-P4DW, use the BMG7-032 auto switch mounting bracket.



^{*2:} Confirm that it is possible to securely set the auto switch(es) within the range of indicator green light ON range before use. For in-line entry type, also consider *1 shown above.

For details, refer to pages 1358 and 1359.

^{*:} Normally closed (NC = b contact) solid state auto switches (D-M9□E(V)) are also available.

For details, refer to page 1308.

Auto Switch Mounting

Applicable Cylinder: MGP-Z (Basic type), MGP-AZ (Air cushion)

Applicable auto switches	D-M9□/M9□V D-M9□W/M9□WV D-M9□A/M9□AV D-A9□/A9□V		D-P3DWA
Bore size [mm]	ø12 to ø100		ø25 to ø100
Auto switch tightening torque	Auto switch model D-M9□(V) D-M9□W(V) D-A93 D-M9□A(V) D-A9□(V) (Excludes the D-A93)	[N·m] Tightening torque 0.05 to 0.15 0.05 to 0.10 0.10 to 0.20	0.2 to 0.3 N·m


Applicable auto switches	D-P4DW
Bore size [mm]	ø32 to ø100
Auto switch mounting bracket part no.	BMG7-032
Auto switch mounting bracket/ Quantity	Auto switch mounting bracket x 1 pc. Auto switch mounting nut x 1 pc. Hexagon socket head cap screw x 2 pcs. Hexagon socket head cap screw x 2 pcs. (With spring washer x 2 pcs.)
Auto switch mounting surface	
Mounting of auto switch	1. Attach the auto switch to the auto switch mounting bracket with the hexagon socket head cap screw (M3 x 14 L). The tightening torque for the M3 hexagon socket head cap screw is 0.5 to 0.8 N-m. 2. Fix the auto switch mounting nut and the auto switch mounting bracket temporarily by tightening the hexagon socket head cap screw (M2.5 x 5 L). 3. Insert the temporarily fixed auto switch mounting bracket into the auto switch mounting groove, and slide the auto switch through the auto switch mounting groove. 4. Check the detecting position of the auto switch and fix the auto switch firmly with the hexagon socket head cap screw (M2.5 x 5 L). The tightening torque for the M2.5 hexagon socket head cap screw is 0.2 to 0.3 N-m. 5. If the detecting position is changed, go back to step 3. Auto switch Hexagon socket head cap screw Auto switch mounting bracket Auto switch mounting pracket Auto switch mounting pracket Auto switch mounting pracket Auto switch mounting pracket Auto switch mounting pracket

Applicable Cylinder: MGP (With end lock), MGPS

(Heavy duty guide rod type)

(******)	3 , - , 	
Bore size [mm]		
ø 25	ø32 to ø100	
BMG2-012		
BMG10-025 (With end lock)		
BMG2-012 (Heavy duty guide rod type)		
— BMG1-040		
	Bore si: Ø 25 BMG	

- *: Cylinders with an end lock are available in ø25 to ø100.
- *: The heavy duty guide rod type is available in ø50 and ø80.



^{*:} Auto switch mounting brackets and auto switches are enclosed with the cylinder for shipment. For an environment that needs the water-resistant auto switch, select the D-M9□A(V) type.

Made to Order: Individual Specifications

Please contact SMC for detailed dimensions, specifications and lead times.



-X144

1 Symmetrical Port Position

Ports are mounted symmetrically.


Applicable Series

Description	Model	Action
	MGPM-Z	Double acting
Standard type	MGPL-Z	Double acting
	MGPA-Z	Double acting


How to Order


MGP A Standard model no. -X144

This makes it easy to remove and rotate piping when it is mounted on a wall where mounting space is limited.



Dimensions (Dimensions other than below are the same as standard type.)





MGPM-Z, MGPL-Z, MGPA-Z Common Dimensions				
Bore size [mm]	GA	PA	PB	
12	10	13	8	
16	10.5	14.5	10	
20	11.5	13.5	10.5	
25	11.5	12.5	13.5	
32	12	6.5	16	
40	15	13	18	
50	15	9	21.5	
63	15.5	13	28	
80	19	14.5	25.5	
100	22.5	17.5	32.5	

Symbol


-X867


Ports on the top plugged in order to use the piping port on the side.

Applicable Series

Description	Model	Action
	MGPM-Z	Double acting
Standard type	MGPL-Z	Double acting
	MGPA-Z	Double acting
	MGPM-AZ	Double acting
With air cushion	MGPL-AZ	Double acting
	MGPA-AZ	Double acting
	MGPM	Double acting
With end lock	MGPL	Double acting
	MGPA	Double acting
Heavy duty guide rod type	MGPS	Double acting

2 Side Porting Type (Plug location changed)





How to Order

MGP A Standard model no. -X867

Side porting type (Plug location changed)

Symbol

-X471


3 Enlarged Plate and Body Gap Dimensions

This specification increases the gap between the plate and body when the cylinder is retracted (Standard: 7 to 16 mm) to 28 to 31 mm. (Features a safety measure to protect fingers from being caught in the gap)


Applicable series

Description	Model	Action	
Standard type	MGPM-Z	Double Acting	

Specifications: Same as standard type



Dimensions (Dimensions other than below are the same as standard type.)



						[mm]
Bore size [mm]	50 st or less	Over 50 st 100 st or less	Over 100 st 200 st or less	Over 200 st	В	FB
12	64	82.5	104.5	104.5	64	28
16	68	86.5	114.5	114.5	68	28
20	74	98.5	98.5	131	74	29
25	74.5	98.5	98.5	130.5	74.5	28

					[mm]
		Α			
Bore size [mm]	50 st or less	Over 50 st 200 st or less	Over 200 st	В	FB
32	92	110.5	146.5	76.5	29
40	92	110.5	146.5	83	29
50	103.5	124.5	165.5	87	31
63	103.5	124.5	165.5	92	31



MGP Series Specific Product Precautions 1

Be sure to read this before handling the products. Refer to page 8 for safety instructions and pages 9 to 18 for actuator and auto switch precautions.

Mounting

⚠ Warning

 Never place your hands or fingers between the plate and the body.

Be very careful to prevent your hands or fingers from getting caught in the gap between the cylinder body and the plate when air is applied.



⚠ Caution

1. Use cylinders within the piston speed range.

An orifice is set for this cylinder, but the piston speed may exceed the operating range if the speed controller is not used. If the cylinder is used outside the operating speed range, it may cause damage to the cylinder and shorten the service life. Adjust the speed by installing the speed controller and use the cylinder within the limited range.

Pay attention to the operating speed when the product is mounted vertically.

When using the product in the vertical direction, if the load factor is large, the operating speed can be faster than the control speed of the speed controller (i.e. quick extension). In such cases, it is recommended to use a dual speed controller.

- When used near the lower limit of the operating piston speed, stick-slip may occur depending on the operating conditions. To counter this, it is recommended to use an operating pressure with margin.
- Do not use the product if an air leaks occurs.

If an air leak does occurs, this may result in the speed being increased beyond the speed controller's adjustment capability, which may further lead to the products speed becoming impossible to control. If the speed is increased excessively, internal components and quide sections may be damaged.

Do not scratch or gouge the sliding portion of the piston rod and the guide rod.

Damaged seals etc. will result in leakage or malfunction.


Do not dent or scratch the mounting surface of the body and the plate.

The flatness of the mounting surface may not be maintained, which would cause an increase in sliding resistance.

Make sure that the cylinder mounting surface has a flatness of 0.05 mm or less.

If the flatness of the workpieces and brackets mounted on the plate is not appropriate, sliding resistance may increase.

If it is difficult to maintain a flatness of 0.05 or less, put a thin shim ring (prepared by user) between the plate and workpiece mounting surface to prevent the sliding resistance from increasing.



Mounting

⚠ Caution


Be sure that the piston rods are retracted when mounting workpieces on the plate.

If workpieces are mounted on the plate when the piston rods are extended, it can lead to distortion of the guide unit, resulting in a malfunction.

9. Bottom of cylinder

The guide rods protrude from the bottom of the cylinder at the end of the retracting stroke, and therefore, in cases where the cylinder is to be bottom mounted, it is necessary to provide bypass ports in the mounting surface for the guide rods, as well as holes for the hexagon socket head cap screws which are used for mounting.

Moreover, in applications where impact occurs from a stopper etc., the mounting screws should be inserted to a depth of 2d or more.



Bore size	Α	В	С	C D [mm]		Hexagon socket
[mm]	[mm]	[mm]	[mm]	MGPM	MGPL/A	head cap screw
12*	50	18	41	10	8	M4 x 0.7
16	56	22	46	12	10	M5 x 0.8
20	72	24	54	14	12	M5 x 0.8
25	82	30	64	18	15	M6 x 1.0
32	98	34	78	22	18	M8 x 1.25
40	106	40	86	22	18	M8 x 1.25
50	130	46	110	27	22	M10 x 1.5
63	142	58	124	27	22	M10 x 1.5
80	180	54	156	33	28	M12 x 1.75
100	210	62	188	39	33	M14 x 2.0

^{*:} Air cushions are not available for bore size 12.



MGP Series Specific Product Precautions 2

Be sure to read this before handling the products. Refer to page 8 for safety instructions and pages 9 to 18 for actuator and auto switch precautions.

Piping

∧ Caution

Depending on the operating conditions, piping port positions can be changed by using a plug.

1. M5


After tightening by hand, tighten additional 1/6 to 1/4 rotation with a tightening tool.

2. Tapered thread for Rc port (MGP) and NPT port (MGP□□TN)

Tighten with proper tightening torque below. Also, use sealant tape on the plug. With regard to the sunk dimension of a plug ("a" dimension in the drawing), use the stipulated figures as a guide and confirm the air leakage before operation.

If tightening plugs on the top mounting port with more than the proper tightening torque, plugs will be screwed much deeply and air passage will be squeezed. Consequently, the cylinder speed will be restricted.

Connection thread (plug) size	Proper tightening torque [N·m]	a dimension
1/8	7 to 9	0.5 mm or less
1/4	12 to 14	1 mm or less
3/8	22 to 24	1 mm or less



3. Parallel pipe thread for G port (MGP□□TF)

Screw in the plug to the surface of the body (dimension "a" in the drawing) by checking visually instead of using the tightening torque shown in the table. Cushion

With air cushion

⚠ Warning

1. Do not open the cushion valve excessively.

Air leakage will occur if operated after opening by 4 rotations or more. Furthermore, a stopper mechanism is provided for the cushion valve, and it should not be forced open beyond that position. Be aware that the cushion valve may jump up from the cover when the air is supplied.

⚠ Caution

 Be sure to use the cylinder after the air cushion has been adjusted appropriately.

First, fully close the cushion valve. Start the operation at the cylinder speed to be used with the load applied, and then open the cushion valve gradually to make the adjustment. The optimal adjustment is that the piston reaches its stroke end and the collision sound is minimized. If the cushion valve is used without adjusting the air cushion appropriately, this may cause damage to the retaining ring or piston.

Bore size [mm]	Applicable tool
16, 20, 25, 32, 40	JIS B4648 hexagon wrench key 1.5
50, 63, 80, 100	JIS B4648 hexagon wrench key 3

2. Be sure to operate a cylinder equipped with air cushion to the end of the stroke.

If it is not operated to the end of the stroke, the effect of the air cushion will not be fully exhibited. Consequently, in cases where the stroke is regulated by an external stopper etc., caution must be exercised, as the air cushion may become completely ineffective.

3. Do not open the cushion needle after rotating it numerous times in a row.

Though uncommon, there are cases in which the cushion needle may leak air.

The cushion needle should be adjusted by gradually opening it while checking the operation of the cylinder cushion.





MGP Series Specific Product Precautions 3


Be sure to read this before handling the products. Refer to page 8 for safety instructions and pages 9 to 18 for actuator and auto switch precautions.

Allowable Kinetic Energy


⚠ Caution

Load mass and a maximum speed must be within the ranges shown in the graph below.

MGP with Rubber Bumper



MGP with Air Cushion



MGP without Cushion (MGP-□V (Water resistant), XB6, XC9, XC22)

