
3-Color Display



Digital Flow Switch for Large Flow Applicable fluid Air, N2



Flow ratio 100:1 A wide range of flow measurement is possible with 1 product.





♦ IO-Link Compatible

The measured value and the device status can be figured out easily via the process data. p. 3

Improved resistance to moisture and foreign matter

The bypass construction reduces sensor accuracy deterioration and damage. p. 1

PF3A H(-L) Series

Modular type

Can be connected to the air combination p.5



3-Screen Display Digital Flow Monitor




Allows for the monitoring of remote lines p. 7



Improved resistance to moisture and foreign matter

The bypass construction reduces the moist air or foreign matter in contact with the sensor, reducing sensor accuracy deterioration and damage.



* The figure shows the PF3A703/6/12H(-L).

Through bore construction*


- Pressure loss: 75% reduction*2 $(20 \text{ kPa} \rightarrow 5 \text{ kPa})$
- Maintenance-free fluid passage
- *1 Excludes the modular type *2 Compared with the existing model (PF2A7□H/ Large flow type)



3-color/2-screen display * 2-screen display: 2-row display of main screen and sub screen

Upper Main display: Green At set point

Upper Main display: Red At set point



Set value Orange (Lower Sub display)

The lower/sub display can be changed by pressing the up/down buttons.

* Either "Input of line name" or "Display OFF" can be added via the function settings.








Display rotates 90° and can be reversed.



Easy operation, improved visibility The display can be rotated in increments of 90° according to the installation. The display can be reversed for easy operation.



<u>Installation</u> **Example**



Smallest settable increment: 2 L/min

- * For the PF3A703H
- * 5 L/min for the existing model (PF2A703H/Large flow type)


Functions pp. 37 to 39

- Output operation
- Simple setting mode
- Display color
- Reference condition
- Response time (Digital filter)
- FUNC output switching function (Analog output ⇔ External input)
- Selectable analog output function
- External input function
- Forced output function
- Accumulated value hold
- Peak/Bottom value display
- Display OFF mode

- Setting of a security code
- Kev-lock function
- Reset to the default settings
- Reversible display mode
- Zero cut-off function
- Delay time setting
- Selection of the display on the sub screen
- Analog output free range function
- Error display function
- Zero-clear function
- Display fine adjustment function
- Measurement display setting

Grease-free

Application



Select a digital flow switch to increase energy savings!

Flow control is necessary for promoting energy saving in any application. Saving energy starts from numerical control of the flow consumption of equipment and lines and clarification of the purpose and effect.

- Digital display allows visualization.
- 3-color/2-screen display, Improved visibility
- Remote control is possible with accumulated pulse.




Energy Saving Program

🥦 IO-Link Compatible PF3A□□H-□□-L□-□□ 🛼 15

Supports the IO-Link communication protocol

0

IO-Link Master



Configuration File (IODD File*1)

· Manufacturer · Product part no. · Set value

*1 IODD File: IODD is an abbreviation of IO Device Description. This file is necessary for setting the device and connecting it to a master. Save the IODD file on the PC to be used to set the device prior to use.



IO-Link is an open communication interface technology between the sensor/actuator and the I/O terminal that is an international standard: IEC 61131-9.

Device settings can be set by the master.

- · Threshold value
- · Operation mode,



- \cdot Switch ON/OFF signal and analog value
- · Device information:

Manufacturer, Product part number, Serial number, etc.

- · Normal or abnormal device status
- · Cable breakage

-0



IO-Link Compatible Device: Digital Flow Switch for Large Air Flow PF3A7□H-L Series



IO-Link Compatible Device: Digital Flow Switch for Large Air Flow PF3A8□H-L Series

Display function

Displays the output communication status and indicates the presence of communication data









Operation and Display

peration and i						
Communication with master	IO-Link status indicator light	Status		Screen display* ²	Description	
	* 1		_	Operate	ModE oPE	Normal communication status (readout of measured value)
Yes			Normal	Start up	ModE Strt	At the start of communication
				Preoperate	ModE PrE	At the start of communication
	(Flacking)	IO-Link mode	<u>a</u>	Version does not match	Er 15 # (1)	The IO-Link version does not match that of the master. * The applicable IO-Link version is 1.1.
No	(Flashing)		Abnormal	Communication disconnection	ModE oPE ModE Strt ModE PrE	Normal communication was not received for 1 s or longer.
	OFF	SIO mode			MadE Sia	General switch output

^{*1} In IO-Link mode, the IO-Link indicator is ON or flashing. *2 When the lower line (sub screen) is set to mode display (Upper line for the PF3A8□H-L)

Implement diagnostic bits in the process data.

The diagnostic bit in the cyclic process data makes it easy to find problems with the equipment. It is possible to find problems with the equipment in real time using the cyclic (periodic)

data and to monitor such problems in detail with the noncyclic (aperiodic) data.

For the PF3A7□H-L

Р	ro	cess	Data	

Bit offset	Item	Note				
0	OUT1 output	0: OFF 1: ON				
1	OUT2 output	0: OFF 1: ON				
8	Flow rate diagnosis	0: OFF 1: ON				
14	Fixed output	0: OFF 1: ON				
15	Error (Failure)	0: OFF 1: ON				
16 to 31 Measured flow rate va		Signed 16 bit				

Diagnosis items

Over current error
Rated flow error
Accumulated flow error
Flow sensor failure
Internal product malfunction

dat	a.		SCMC =		109	P	500 500	
	00	00	0.1	00	10	40	4-	40

Bit offset	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16
Item	Item Measured flow rate value (PD)															
Bit offset	15	14	13	12	11	10	9	8	7	6	5	4	3	2	1	0
Item	Error Fixed output Reservation Flow ralls diagnosis Reservation						OUT2	OUT1								
	(Failure)														Switch	output

For the PF3A8□H-L

Process Data

Bit offset	Item	Not	е
0	Accumulated flow SW1	0: OFF	1: ON
1	Accumulated flow SW2	0: OFF	1: ON
2	Flow rate SW1	0: OFF	1: ON
3	Flow rate SW2	0: OFF	1: ON
4	Temperature SW1	0: OFF	1: ON
5	Temperature SW2	0: OFF	1: ON
6	Pressure SW1	0: OFF	1: ON
7	Pressure SW2	0: OFF	1: ON
8	Flow rate unit	0: L	1: ft3
9	Flow rate criteria	0: STD	1: nor
10	10 Flow rate diagnosis		1: HHH

Bit offset	Item	Note
11	Temperature diagnosis	0: Normal 1: HHH/LLL
12	Pressure diagnosis	0: Normal 1: HHH/LLL
13	Fixed output	0: Normal output 1: Fixed output
14	Error	0: Normal 1: Abnormal
15	System error	0: Normal 1: Abnormal
16 to 31	Measured pressure value	Signed 16 bit
32 to 47	Measured temperature value	Signed 16 bit
48 to 63	Measured flow rate value	Signed 16 bit
64 to 79	Accumulated flow rate lower limit	Unsigned 32 bit
80 to 95	Accumulated flow rate upper limit	Orisigned 32 bit




Diagnosis item

- · Rated flow error
- Above/Below the rated pressure range
 Above/Below the rated temperature range
- Error (Over current, Outside of zero-clear range, Version does not match)
- System error (Flow/Temperature sensor failure, Internal malfunction)

Bit offset	95	94	93	92	91	90	89	88	87	86	85	84	83	82	81	80
Item		Accumulated flow rate upper limit (PD)														
Bit offset	79	78	77	76	75	74	73	72	71	70	69	68	67	66	65	64
Item		Accumulated flow rate lower limit (PD)														
Bit offset	63	62	61	60	59	58	57	56	55	54	53	52	51	50	49	48
Item							Mea	sured flow	rate value	(PD)						
Bit offset	47	46	45	44	43	42	41	40	39	38	37	36	35	34	33	32
Item							Measu	red tempe	rature valu	e (PD)						
Bit offset	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16
Item							Mea	sured pres	sure value	(PD)						
Bit offset	15	14	13	12	11	10	9	8	7	6	5	4	3	2	1	0
Item	System error	Error	Fixed output	Pressure diagnosis	Temperature diagnosis	Flow rate diagnosis	Flow rate criteria	Flow rate unit	Pressure 2	Pressure 1	Temperature 2	Temperature 1	Flow rate 2	Flow rate 1	Accumulated flow 2	Accumulated flow 1

Application Example






3-Color Display Modular Type Digital Flow Switch PF3A701H/702H(-L) Series

рр. **17, 19**

Can be connected to the air combination







A right to left (-R) flow direction is also available.




■ 90° rotation




■ The flow switch can be installed/removed without removing the piping.

Reduced maintenance time for inspection, cleaning, replacement, etc.







4-Screen Display Modular Type Digital Flow Switch with Pressure/Temperature Sensor PF3A801H/802H-L Series p.21 Can be connected to the air combination



■ 3-color/4-screen display

Simultaneous measurement of the instantaneous flow rate, accumulated flow rate, pressure, and temperature

Pressure sensor

Rated pressure range: 0 to 1 MPa


Temperature sensor


Rated temperature range: 0 to 50°C

■ Space-saving design, Reduced labor

Both the flow rate and pressure can be measured with 1 product.


The installation of a digital pressure switch and a cross spacer is not necessary, thus reducing the face-to-face and depth dimensions. In addition, only 1 cable is required for wiring. This reduces the required installation space, piping, and wiring work.






3-Screen Display Digital Flow Monitor **PFG300** Series p.31


Allows for the monitoring of remote lines




Visualization of settings









Easy screen switching




The sub screen can be switched by pressing the up/down buttons.




* Either "Input of line name" or "Display OFF" can be added via the function settings.

Simple 3-step setting

When the S button is pressed and the set value (P_1) is being displayed, the set value (threshold value) can be set. When the S button is pressed and the hysteresis (H_1) is being displayed, the hysteresis value can be set.






NPN/PNP switch function

The number of stock items can be reduced.



Input range selection (for Pressure/Flow rate)



The displayed value to the sensor input can be set as required. (Voltage input: 1 to 5 V/Current input: 4 to 20 mA)

Pressure switch/Flow switch can be displayed.


A is displayed for 1 V (or 4 mA). B is displayed for 5 V (or 20 mA). The range can be set as required.

Analog output of 0 to 10 V is also available.

Voltage	1 to 5 V	Switchable	
output	0 to 10 V	Switchable	
Current output	4 to 20 mA	Fixed	

■ Pressure Sensor for General Fluids/PSE570





	Α	В
PSE570	0	1000
PSE573	-100	100
PSE574	0	500
0 . 4		

Set A and B to the values shown

Convenient functions

Copy function

The set values of the monitor can be copied.





Copy destination

Security code

The key locking function keeps unauthorized persons from tampering with the settings.

Power saving mode

Power consumption is reduced by turning off the monitor.


Current consumption*1	Reduction rate*2
25 mA or less	Approx. 50% reduction
*1 During normal operation	*2 In nower saving mode

External input function

The accumulated value, peak value, and bottom value can be reset remotely.

Compact & Lightweight

- Compact: Max. 6 mm shorter
- Lightweight: Max. 5 g lighter (30 g → 25 g)




Functions pp. 40 to 42

- Output operation
- Simple setting mode
- Display color
- Delay time setting
- Digital filter setting
- FUNC output switching function
- Selectable analog output function
- External input function
- Forced output function
- Accumulated value hold
- Peak/Bottom value display
- Setting of a security code
- Key-lock function
- Reset to the default settings
- · Display with zero cut-off setting
- Selection of the display on the sub screen
- Analog output free range function
- Error display function
- Copy function
- Selection of power saving mode

Mounting

The bracket configuration allows for mounting in four orientations.





Panel mounting

Mountable side by side both vertically and horizontally

One opening!


- · Reduced panel fitting labor
- · Space saving







Flow Switch Flow Rate Variations



Flow Switch Variations / Basic Performance Table

1 10						
Series	PFMV3	PF2M7(-L)	PFMB PFG300	PF2MC7(-L) PFG300	PF2A	PFG300 p. 31
Enclosure	IP40	IP40	IP40	IP65 [Monitor unit: IP40]	IP65	IP65 [Monitor unit: IP40]
Fluid	Dry air, N₂	Dry air, N ₂ , Ar, CO ₂	Dry air, N₂	Dry air, N₂	Air, N₂	Air, N ₂
Setting	Digital	Digital	Digital	Digital	Digital	Digital
Rated flow range [L/min]	0 to 0.5 -0.5 to 0.5 0 to 1 -1 to 1 0 to 3 -3 to 3	0.01 to 1 0.02 to 2 0.05 to 5 0.1 to 10 0.3 to 25 0.5 to 50 1 to 100 2 to 200	5 to 500 10 to 1000 20 to 2000	5 to 500 10 to 1000 20 to 2000	1 to 10 5 to 50 10 to 100 20 to 200 50 to 500	30 to 3000 60 to 6000 120 to 12000 20 to 2000
Power supply voltage	12 to 24 VDC ±10%	PF2M7	12 to 24 VDC ±10%	PFMC 12 to 24 VDC ±10% PFMC-L 18 to 30 VDC ±10%	12 to 24 VDC ±10%	PF3A7□H-L 24 VDC ±10% PF3A7□H-L 18 to 30 VDC ±10% PF3A701H/ 702H-L 21.6 to 30 VDC PF3A8□H-L 21.6 to 30 VDC
Temperature characteristics (25°C standard)	±2% F.S. (15 to 35°C) ±5% F.S. (0 to 50°C) [Monitor unit:] ±0.5% F.S. (0 to 50°C)	±3% F.S. ±1 digit (15 to 35°C) ±5% F.S. ±1 digit (0 to 50°C)	±2% F.S. (15 to 35°C) ±5% F.S. (0 to 50°C) Monitor unit: ±0.5% F.S. (0 to 50°C)	±2% F.S. (15 to 35°C) ±5% F.S. (0 to 50°C) Monitor unit: ±0.5% F.S. (0 to 50°C)	±3% F.S. (15 to 35°C) ±5% F.S. (0 to 50°C)	±5% F.S. (0 to 50°C) Monitor unit: ±0.5% F.S. (0 to 50°C)
Repeatability	±2% F.S. (Fluid: Dry air) Analog output: ±5% F.S. Monitor unit: ±0.1% F.S. Analog output: ±0.3% F.S.	±1% F.S. ±1 digit (Fluid: Dry air)	±1% F.S. [Monitor unit:] (Fluid: Dry air) ±0.1% F.S.]	±1% F.S. [Monitor unit:] (Fluid: Dry air) ±0.1% F.S.]	±1% F.S. (PF2A7□0) ±2% F.S. (PF2A7□1)	\pm 1% F.S. Monitor unit: \pm 0.1% F.S.
Hysteresis	Hysteresis mode: Variable Window comparator mode: Variable	Hysteresis mode: Variable Window comparator mode: Variable	Hysteresis mode: Variable Window comparator mode: Variable	Hysteresis mode: Variable Window comparator mode: Variable	Hysteresis mode: Variable Window comparator mode: Fixed (3 digits)	Hysteresis mode: Variable Window comparator mode: Variable
Output	NPN/PNP open collector Analog voltage output Analog current output	NPN/PNP open collector Accumulated pulse output Analog voltage output Analog current output IO-Link	NPN/PNP open collector Accumulated pulse output Analog voltage output Analog current output	NPN/PNP open collector Accumulated pulse output Analog voltage output Analog current output IO-Link	NPN/PNP open collector Accumulated pulse output	NPN/PNP open collector Accumulated pulse output Analog voltage output Analog current output IO-Link
Display	Monitor unit: 2-color LCD display	2-color LCD display	2-color LED 2-color LCD display display Monitor unit: 3-color LCD display	3-color LCD display	LED display	3-color LCD display

CONTENTS

Thu	100	
	II.	
		W. Taraba

3-Color Display Digital Flow Switch *PF3A7*□*H* Series

Body Ported Type IO-Link Compatible

3-Color Display Digital Flow Switch PF3A7 H-L Series



Modular Type

3-Color Display Digital Flow Switch PF3A7 H Series

Modular Type IO-Link Compatible

3-Color Display Digital Flow Switch PF3A7 H-L Series

Modular Type IO-Link Compatible

4-Screen Display Digital Flow Switch with Pressure/Temperature Sensor **PF3A8** H-L Series



3-Screen Display Digital Flow Monitor *PFG300 Series*

Body Ported T	ype	
3-Color Display	Digital Flow Switch	
	PF3A7⊟H Series	
	How to Order ······	n 10
`	Specifications	p. 14
Body Ported T	ype IO-Link Compatible	
	Digital Flow Switch	
	PF3A7□H-L Series	
	How to Order ······	n 15
	Specifications	•
`	Specifications	ρ. ι
Modular Type		
	,	
	Digital Flow Switch	
l	PF3A7□H Series	
ŀ	How to Order	p. 17
9	Specifications	p. 18
	IO-Link Compatible	
3-Color Display	Digital Flow Switch	
I	PF3A7□H-L Series	
I	How to Order	p. 19
	Specifications	•
	•	

Modular Type IO-Link Compatible			
4-Screen Display Digital Flow Switch			
with Pressure/Temperature Sensor			
PF3A8□H-L Series			
How to Order p. 21			
Specifications p. 22			
Flow Rangep. 23			
Analog Output p. 23			
Pressure Lossp. 24			
Flow Rate Characteristicsp. 24			
IN Side Straight Section and Accuracyp. 25			
Temperature Accuracyp. 25			
Internal Circuits and Wiring Examples p. 26			
Construction: Parts in Contact with Fluid p. 28			
Dimensions p. 28			
Optional Accessoriesp. 30			


3-Screen Display Digital Flow Monitor PFG300 Series

How to Order	ρ.	JΙ
Specifications	p.	32
Internal Circuits and Wiring Examples	p.	33
Dimensions ·····	p.	34
LVE unation Dataila		07
-L) /Function Details	p.	3/

PF3A□H(-L)/Function Details ······	p. 37
PFG300/Function Details ······	p. 40
Safety Instructions Back	cover

Body Ported Type

3-Color Display Digital Flow Switch (E CA PF3A7 H Series RoHS)



FS

PNP

default setting is 1 to 5 V.

Analog current output ⇔ External input*4

buttons. Analog output is set as default setting.

*2 Analog output or external input can be selected by pressing the

*4 The accumulated value, peak value, and bottom value can be reset.

1 to 5 V or 0 to 10 V can be selected by pressing the button. The

PFG310 series

Option/Part No.

When only optional parts are required, order with the part number listed below

Trion only optional parts are required, order with the part named herea select				
Part no. Option		Note		
ZS-37-A	Lead wire with M12 connector	Length: 3 m		

Specifications

For flow switch precautions and specific product precautions, refer to the "Operation Manual" on the SMC website.

	Model		DESAZOSH	DESAZOGU	DE2 A 740U	
	Model		PF3A703H	PF3A706H	PF3A712H	
Fluid Applicable fluid*1		Air, Nitrogen				
Fluid temperature		0 to 50°C				
	Detection method	ı	001.0000111	Thermal type	100 10000 /	
	Rated flow range	lastastas	30 to 3000 L/min	60 to 6000 L/min	120 to 12000 L/min	
	Set point range*2	Instantaneous flow	30 to 3150 L/min	60 to 6300 L/min	120 to 12600 L/min	
		Accumulated flow	0 to 999,999,990 L		9,999,900 L	
Flow	Smallest settable		2 L/min	5 L/min	10 L/min	
	increment	Accumulated flow	10 L	10	0 L	
	Accumulated volum		Select from 100 L/pulse or 1000 L/pulse.			
	(Pulse width = 50 ms	,		· · · · · · · · · · · · · · · · · · ·		
	Accumulated value hol		Intervals of 2 or 5 minutes can be selected.			
	Rated pressure ra	inge		0.1 to 1.5 MPa		
Pressure	Proof pressure			2.25 MPa		
	Pressure loss			r to the "Pressure Loss" graph on page		
	Pressure characte		±2.5% F.S. (0.1 to 1.0 MPa, 0.5 MPa standard)			
	Power supply vol			24 VDC ±10%		
Electrical	Current consump	tion		150 mA or less		
	Protection			Polarity protection		
	Display accuracy			±3.0% F.S.		
	Analog output acc	curacy		±3.0% F.S.		
Accuracy	Repeatability			Switch output/Display: ±1.0% F.S.		
				Analog output: ±1.0% F.S.		
	Temperature chara	acteristics	±5.0% F.S. (Ambient temperature of 0 to 50°C, 25°	C standard)	
	Output type			NPN open collector		
				PNP open collector		
	Output mode		Select from Instantaneous output (Hysteresis			
	Switch operation		<u> </u>	Select from Normal or Reversed output		
0 11.1	Max. load current			80 mA		
Switch output	Max. applied voltage			28 VDC		
	Internal voltage d			put type: 1 V or less (at load current of		
	(Residual voltage)	PNP out	put type: 2 V or less (at load current of	ou ma)	
	Response time*5			Select from 1 s, 2 s, or 5 s.		
	Hysteresis*6		Variable from 0			
	Protection		Over current protection			
	Output type	W. B.	Voltage output: 1 to 5 V (0 to 10 V can be selected*8), Current output: 4 to 20 mA			
Analog output*7	Impedance	Voltage output	Output impedance: Approx. 1 kΩ			
- •	- Current output					
	Response time*9		Linked to the response time of the switch output			
External input*10	Input type Input mode		No-voltage input: 0.4 V or less Select from Accumulated value external reset or Peak/Bottom value reset.			
External input	Input mode Input time		Select from Accumulated value external reset or Peak/Bottom value reset. 30 ms or longer			
	Reference conditi	on*11				
		Instantaneous flow	Select from Standard conditions or Normal conditions. L/min, CFM (ft³/min)			
	Unit*12 Instantaneous flow Accumulated flow			L. ft ³		
	Display range*13	Accumulated HOW	0 to 3150 L/min	0 to 6300 L/min	0 to 12600 L/min	
		Instantaneous flow	(Flow under 30 L/min is displayed as "0")			
	Pishiah talihe	Accumulated flow*14	0 to 999,999,990 L		9,999,900 L	
Display	Minimum	Instantaneous flow	2 L/min	5 L/min	10 L/min	
	display unit	Accumulated flow	10 L			
	a.opiaj aint	Accumulated IIOW	10 L 100 L LCD, 2-screen display (Main screen/Sub screen)			
	Display			screen: Red/Green, Sub screen: Ora		
	2.Spiuy			5 digits, 7 segment, Sub screen: 6 digi		
	Indicator LED			ndicator: Red LED is ON when output		
	Enclosure		IP65			
	Withstand voltage	9	1000 VAC for 1 minute between terminals and housing			
Environmental	Insulation resista			asured via megohmmeter) between te		
resistance Operating tempera				0°C, Stored: -10 to 60°C (No freezing		
Operating humidity range		Operating/Stored: 35 to 85% RH (No condensation)				
Standards		CE/UKCA marking				
Piping Piping specification		Rc1, NPT1, G1	Rc1 1/2, NPT1 1/2, G1 1/2	Rc2, NPT2, G2		
Main materials of parts in contact with fluid			sor: Pt, Au, Fe, Lead glass (exempted			
Length of lead wir			, ,	3 m		
J		Rc	610 g	1190 g	1680 g	
147.1.1.1	Piping	NPT	610 g	1190 g	1680 g	
Weight	specification	G	630 g	1220 g	1720 g	
	Lead wire with co		9	+90 g	9	
				· - * y		

- *1 Air quality grade is JIS B 8392-1:2012 [4:6:-] and ISO 8573-1:2010 [4:6:-].
- Set point range will change according to the setting of the zero cut-off function.
- When using the accumulated value hold function, use the operating conditions to calculate the product life, and do not exceed it. The maximum update limit of the memory device is 1.5 million times. If the product is operated 24 hours per day, the product life will be as follows:

 • 5 min interval: life is calculated as 5 min x 1.5 million = 7.5 million min = 14.3 years


 - 2 min interval: life is calculated as 2 min x 1.5 million = 3 million min = 5.7 years If the accumulated value external reset is repeatedly used, the product life will be shorter than the calculated life.
- When the pressure range is 1.0 to 1.5 MPa, the pressure characteristics will be $\pm 5\%$ F.S. (standard pressure is 0.5 MPa). Do not release the OUT side piping port of the product to the atmosphere without connecting piping. If the product is used with the piping port re-
- leased to atmosphere, accuracy may vary.

 *5 The time from when the flow is changed by a step input (when the flow rate changes from 0 to the maximum value of the rated flow range instantaneously) until the switch output turns ON (or OFF) when set to be 90% of the rated flow rate
- *6 If the flow fluctuates around the set value, the width for setting more than the fluctuating width needs to be set. Otherwise, chattering will occur.
- Analog output or external input can be selected by pressing the buttons. Refer to the graph for analog output.

 When selecting 0 to 10 V, refer to the analog output graph for the allowable load current.
- The time from when the flow is changed by a step input (when the flow rate changes from 0 to the maximum value of the rated flow range instantaneously) until the analog output reaches 90% of the rated flow rate *10 Analog output or external input can be selected by pressing the buttons.
- The flow rate given in the specifications is the value under standard conditions.
- *12 Setting is only possible for models with the units selection function.
- *13 Display range will change according to the setting of the zero cut-off function. *14 The accumulated flow display is the upper 6-digit and lower 6-digit (total of 12 digits) display. When the upper digits are displayed, x 106 lights up.
- * Products with tiny scratches, marks, or display color or brightness variations which do not affect the performance of the product are verified as conforming products.







Options/Part Nos.

When only optional parts are required, order with the part numbers listed below.

20

2

Part no.	Option	Note	
ZS-37-A	Lead wire with M12 connector	Length: 3 m	
ZS-49-A	Lead wire with M12-M12 connector	Male/female conversion, Length: 3 m	

- Output specification

Symbol	OUT	FUNC*2	Applicable monitor unit model
L	IO-Link: Switch output (N/P)	_	_
L3	IO-Link: Switch output (N/P)	Analog voltage output*3 ⇔ External input*4	PFG300 series
L4	IO-Link: Switch output (N/P)	Analog current output ⇔ External input*4	PFG310 series

- *2 Analog output or external input can be selected by pressing the buttons. Analog output is set as default setting. Output symbol "L" cannot be used as the FUNC terminal is not connected.
- *3 1 to 5 V or 0 to 10 V can be selected by pressing the button. The default setting is 1 to 5 V.
- *4 The accumulated value, peak value, and bottom value can be reset.

Specifications

For flow switch precautions and specific product precautions, refer to the "Operation Manual" on the SMC website.

					55661
Model		PF3A703H-L	PF3A706H-L	PF3A712H-L	
Electrical	Power output device		24 VDC ±10%		
	supply voltage	When used as an IO-Link device	18 to 30 VDC ±10%		
	Output typ	oe e	Select	from NPN or PNP open collector	output.
Output mode		Select from Hysteresis, Window comparator, Accumulated output, Accumulated pulse output, Error output, or Switch output OFF modes.			
Switch output	Switch output Max. applied voltage		30 V (NPN output)		
Internal voltage drop (Resi		tage drop (Residual voltage)	1.5 V or less (at load current of 80 mA)		nA)
	Delay time*1		3.3 ms or less, variable from 0 to 60 s/0.01 s increments		
Analog output	nalog output Response time*2		Linked to the set value of the digital filter		
Display		LCD, 2-screen display (Main screen/Sub screen) Main screen: Red/Green, Sub screen: Orange Main screen/Sub screen: 9 digits (7 segments 7 digits, 11 segments 2 digits)		Drange [']	
	Digital filt	er*3	Select from 1 s, 2 s, or 5 s.		
Standards		CE/UKCA marking			

- *1 The time from when the instantaneous flow reaches the set value to when the switch output operates can be set.
- *2 The time from when the flow is changed by a step input (when the flow rate changes from 0 to the maximum value of the rated flow range instantaneously) until the analog output reaches 90% of the rated flow rate
- *3 The time for the digital filter can be set to the sensor input. The response time indicates when the set value is 90% in relation to the step input.

Communication Specifications (IO-Link mode)

Communication Specifications (IO-Link mode)			
IO-Link type	Device		
IO-Link version	V 1.1		
Communication speed	COM2 (38.4 kbps)		
Configuration file	IODD file*1		
Minimum cycle time	3.3 ms		
Process data length	Input data: 4 bytes, Output data: 0 byte		
On request data communication	Yes		
Data storage function	Yes		
Event function	Yes		
Vendor ID	131 (0 x 0083)		
	PF3A703H-□□-L□-□□ : 400 (0 x 0190)		
	PF3A703H-□□-L3□-□□: 401 (0 x 0191)		
	PF3A703H-□□-L4□-□□: 402 (0 x 0192)		
	PF3A706H-□□-L□-□□ : 403 (0 x 0193)		
Device ID*2	PF3A706H-□□-L3□-□□: 404 (0 x 0194)		
	PF3A706H-□□-L4□-□□: 405 (0 x 0195)		
	PF3A712H-□□-L□-□□ : 406 (0 x 0196)		
	PF3A712H-□□-L3□-□□: 407 (0 x 0197)		
	PF3A712H-□□-L4□-□□: 408 (0 x 0198)		

- *1 The configuration file can be downloaded from the SMC website, https://www.smcworld.com
- *2 The device ID differs according to each product type (output specification).

Other specifications that are not listed are the same as those of the standard product. For details, refer to page 14.



Modular Type

3-Color Display Digital Flow Switch (E CAPPED A 7 H Series ROHS



How to Order

PF3A 7 01 H-CS

Integrated display

Rated flow range

Symbol	Rated flow range	Applicable air combination model
01	10 to 1000 L/min	AC30-D
02	20 to 2000 L/min	AC40-D

Large flow type •

Output specification •

Symbol	OUT	FUNC*1	Applicable monitor unit model
CS	NPN	Analog voltage output*2 ⇔ External input*3	PFG300 series
DS	NPN	Analog current output ⇔ External input*3	PFG310 series
ES	PNP	Analog voltage output*2 ⇔ External input*3	PFG300 series
FS	PNP	Analog current output ⇔ External input*3	PFG310 series

- *1 Analog output or external input can be selected by pressing the buttons. Analog output is set as default setting.
- *2 1 to 5 V or 0 to 10 V can be selected by pressing the button. The default setting is 1 to 5 V.
- *3 The accumulated value, peak value, and bottom value can be reset.

Options/Part Nos.

When only optional parts are required, order with the part numbers listed below.

	The confermal parts are required, order than are part names or meter serious				
Part no. Option		Note			
ZS-37-A	Lead wire with M12 connector	Length: 3 m			
7S-49-A	Lead wire with M12-M12 connector	Male/female conversion Length: 3 m			

Flow direction

Nil	Left to right	
R	Right to left	

Calibration certificate*8

Nil	None
A *9	Yes

- *8 The certificate is in both English and Japanese.
- *9 Made to order

Unit specification

Nil	Units selection function*6
М	SI units only*7

- *6 This product is for overseas use only. (The SI unit type is provided for use in Japan in accordance with the New Measurement Act.)
- *7 Fixed units: Instantaneous flow: L/min Accumulated flow: L

Option*4


N	lil	With lead wire with connector (3 m)	
N Without lead wire with connector			
(Q	Lead wire with M12-M12 connector (3 m)*5	

- *4 Options are shipped together with the product but do not come assembled.
- *5 The lead wire has an M12 (female) connector on one side and an M12 (male) connector on the other side.

Caution on Mounting

Pipe threads are not provided for this product. If the product is to be used as a single unit, order a spacer (or spacer with bracket) and a piping adapter separately. Refer to page 30 for details on attachments.

Assembly Example



- * Avoid mounting the lubricator on the inlet side.
- If a pressure relief 3-port valve is installed on the inlet side of the digital flow switch, causing a backflow of air, the measured value will change.

Assembly example

- Digital flow switch PF3A701H-CS-M ·······1 pc.
- ② Air combination AC30B-03E-D · · · · · · · 1 pc.
- Spacer with bracket Y300T-D · · · · · · · · · · · 2 pcs.
- Piping adapter E300-03-D1 pc.

Products do not come assembled. They should be ordered separately and assembled by the customer.



Simple Specials System

A system designed to respond quickly and easily to your special ordering needs

Please contact your local sales representative for more details.



Specifications

For flow switch precautions and specific product precautions, refer to the "Operation Manual" on the SMC website.

	Model		PF3A701H	PF3A702H	
Fluid	Applicable fluid*1		Air, Nit	rogen	
riula	Fluid temperature		0 to 50°C		
	Detection method		Thermal type (Bypass flow type)		
l	Rated flow range		10 to 1000 L/min	20 to 2000 L/min	
ļ	Cot maint warman	Instantaneous flow	10 to 1050 L/min	20 to 2100 L/min	
	Set point range*2	Accumulated flow	0 to 999,999	9,999,990 L	
Flow	Smallest settable	Instantaneous flow	1 L/min	2 L/min	
	increment	Accumulated flow	10	L	
	Accumulated volume	me per pulse	Oplant from 40 L/miles on 400 L/miles		
	(Pulse width = 50 ms)		Select from 10 L/pulse or 100 L/pulse.		
	Accumulated value	e hold function*3	Intervals of 2 or 5 minutes can be selected.		
	Rated pressure rar	nge	0 to 1.0 MPa		
Pressure	Proof pressure		1.5 MPa		
riessuie	Pressure loss		Refer to the "Pressure L		
	Pressure character	ristics*4	±5.0% F.S. (0 to 1.0 MPa, 0.5 MPa standard)		
	Power supply volta	age	24 VDC	5 ±10%	
Electrical	Current consumpt	ion	150 mA	or less	
	Protection		Polarity p		
	Display accuracy*		±3.0%		
l	Analog output acc	uracy*5	±3.0%		
Accuracy	Repeatability		±1.0%		
	Temperature chara		±5.0% F.S. (Ambient temperatu		
		ng modular products*6			
l	Output type		NPN open collector,		
	Output mode		Select from Instantaneous output (Hysteresis mode or Window comparator mode), Accumulated output, or Accumulated pulse output.		
ļ	Switch operation		Select from Normal		
Switch output	Max. load current		80 mA		
Switch output	Max. applied voltage (NPN only)		28 V		
			NPN output type: 1 V or less (at load current of 80 mA),		
	Response time*7		Select from 1		
	Hysteresis*8		Variable		
	Protection		Over curren		
	Output type		Voltage output: 1 to 5 V (0 to 10 V can be		
Analog output*9	Impedance Voltage output		Output impedance		
3		Current output	Maximum load impedance: 600 Ω , Minimum load impedance: 50 Ω		
	Response time*11			Linked to the response time of the switch output No-voltage input: 0.4 V or less	
-	Input type				
External input*12	Input mode		Select from Accumulated value extern		
	Input time	. +12	30 ms o		
	Reference condition*13		Select from Standard condi		
	Unit*14	Instantaneous flow	L/min, CFI		
l		Accumulated flow	0 to 1050 L/min	0 to 2100 L/min	
l	Display range*15	Instantaneous flow	(Flow under 10 L/min is displayed as "0")		
	Display range	Accumulated flow*16		(Flow under 20 L/min is displayed as "0")	
Display	Minimum	Instantaneous flow	0 to 999,999	9,999,990 L 2 L/min	
l	display unit	Accumulated flow	1 L/min	<u> </u>	
ļ	uispiay uiiit	Accumulated now	LCD, 2-screen display (N		
	Display				
ļ	Display		Main screen: Red/Green, Sub screen: Orange Main screen: 4 digits, 7 segment, Sub screen: 6 digits, 7 segment		
1	Indicator I ED		OUT indicator: Red LED is ON when output is ON IP65		
	Indicator LED				
	Enclosure		IPe	55	
Environmental	Enclosure Withstand voltage		IPG 1000 VAC for 1 minute betw	55 veen terminals and housing	
Environmental resistance	Enclosure Withstand voltage Insulation resistan	ce	IP0 1000 VAC for 1 minute betw 50 MΩ (500 VDC measured via megohr	65 veen terminals and housing nmeter) between terminals and housing	
	Enclosure Withstand voltage Insulation resistan Operating tempera	ce Iture range	IP0 1000 VAC for 1 minute betw 50 MΩ (500 VDC measured via megohn Operating: 0 to 50°C, Stored: -10 to	65 veen terminals and housing nmeter) between terminals and housing 60°C (No freezing or condensation)	
resistance	Enclosure Withstand voltage Insulation resistan	ce Iture range	IP0 1000 VAC for 1 minute betw 50 MΩ (500 VDC measured via megohn Operating: 0 to 50°C, Stored: –10 to Operating/Stored: 35 to 85	present terminals and housing the same terminals and the same term	
resistance Standards	Enclosure Withstand voltage Insulation resistan Operating tempera Operating humidity	ce iture range y range	IP0 1000 VAC for 1 minute betw 50 MΩ (500 VDC measured via megohn Operating: 0 to 50°C, Stored: -10 to Operating/Stored: 35 to 85 CE/UKCA	peen terminals and housing nmeter) between terminals and housing 60°C (No freezing or condensation) RH (No condensation)	
resistance	Enclosure Withstand voltage Insulation resistan Operating tempera	ce iture range y range	IP0 1000 VAC for 1 minute betw 50 MΩ (500 VDC measured via megohn Operating: 0 to 50°C, Stored: -10 to Operating/Stored: 35 to 85 CE/UKCA Modular (Body size: 30)	65 /een terminals and housing nmeter) between terminals and housing 60°C (No freezing or condensation) 60°RH (No condensation)	
resistance Standards Piping Main materials of	Enclosure Withstand voltage Insulation resistan Operating tempera Operating humidity Piping specificatio parts in contact with	ce iture range y range n	IPG 1000 VAC for 1 minute betw 50 MΩ (500 VDC measured via megohn Operating: 0 to 50°C, Stored: –10 to Operating/Stored: 35 to 85 CE/UKCA Modular (Body size: 30) Stainless steel 304, Alum [Sensor: Pt, Au, Ni, Fe, Lead glass (exen	preed from the RoHS application), Al ₂ O ₃	
resistance Standards Piping	Enclosure Withstand voltage Insulation resistan Operating tempera Operating humidity Piping specification parts in contact with	ce iture range y range n	IPG 1000 VAC for 1 minute betw 50 MΩ (500 VDC measured via megohn Operating: 0 to 50°C, Stored: -10 to Operating/Stored: 35 to 85 CE/UKCA Modular (Body size: 30) Stainless steel 304, Alum [Sensor: Pt, Au, Ni, Fe, Lead glass (exen	preed from the RoHS application), Al ₂ O ₃	
resistance Standards Piping Main materials of	Enclosure Withstand voltage Insulation resistan Operating tempera Operating humidity Piping specificatio parts in contact with	ce Iture range y range In h fluid	IPG 1000 VAC for 1 minute betw 50 MΩ (500 VDC measured via megohn Operating: 0 to 50°C, Stored: –10 to Operating/Stored: 35 to 85 CE/UKCA Modular (Body size: 30) Stainless steel 304, Alum [Sensor: Pt, Au, Ni, Fe, Lead glass (exen	present the form the Rohs application), Al ₂ O ₃ meter) between terminals and housing 60°C (No freezing or condensation) and Rohs Rh (No condensation) a marking Modular (Body size: 40) and Rh (Body size:	

- *1 Air quality grade is JIS B 8392-1:2012 [4:6:-] and ISO 8573-1:2010 [4:6:-].
- Set point range will change according to the setting of the zero cut-off function.
- *3 When using the accumulated value hold function, use the operating conditions to calculate the product life, and do not exceed it. The maximum update limit of the memory device is 1.5 million times. If the product is operated 24 hours per day, the product life will be as follows:
 - 5 min interval: life is calculated as 5 min x 1.5 million = 7.5 million min = 14.3 years
 - 2 min interval: life is calculated as 2 min x 1.5 million = 3 million min = 5.7 years If the accumulated value external reset is repeatedly used, the product life will be shorter than the calculated life.
- *4 Do not release the OUT side piping port of the product to the atmosphere without connecting piping. If the product is used with the piping port re-
- leased to atmosphere, accuracy may vary.

 *5 The value when connecting a product with a port size of 3/8 (PF3A701H) or 1/2 (PF3A702H)


 *6 The value when the port size of the modular product is 3/8 (PF3A701H) or 1/2 (PF3A702H) and the product is operated at a supply pressure of 0.5 MPa
- *7 The time from when the flow is changed by a step input (when the flow rate changes from 0 to the maximum value of the rated flow range instantaneously) until the switch output turns ON (or OFF) when set to be 90% of the rated flow rate

- *8 If the flow fluctuates around the set value, the width for setting more than the fluctuating width needs to be set. Otherwise, chattering will occur.
- Analog output or external input can be selected by pressing the buttons. Refer to the graph for analog output.
- *10 When selecting 0 to 10 V, refer to the analog output graph for the allowable load current.
- *11 The time from when the flow is changed by a step input (when the flow rate changes from 0 to the maximum value of the rated flow range instantaneously) until the analog output reaches 90% of the rated flow rate
- *12 Analog output or external input can be selected by pressing the buttons.
- *13 The flow rate given in the specifications is the value under standard conditions.
- Setting is only possible for models with the units selection function.
- *15 Display range will change according to the setting of the zero cut-off function.
- The accumulated flow display is the upper 6-digit and lower 6-digit (total of
- 12 digits) display. When the upper digits are displayed, x 10° lights up.

 * Products with tiny scratches, marks, or display color or brightness variations which do not affect the performance of the product are verified as conforming products.



Modular Type | **O**-Link 3-Color Display Digital Flow Switch (E CAPPED A 7 H-L Series Rohs



Options/Part Nos.


When only optional parts are required, order with the part numbers listed below.

Part no. Option		Note
ZS-37-A	Lead wire with M12 connector	Length: 3 m
ZS-49-A	Lead wire with M12-M12 connector	Male/female conversion, Length: 3 m

Caution on Mounting

Pipe threads are not provided for this product. If the product is to be used as a single unit, order a spacer (or spacer with bracket) and a piping adapter separately. Refer to page 30 for details on attachments.

Assembly Example



- * Avoid mounting the lubricator on the inlet side.
- If a pressure relief 3-port valve is installed on the inlet side of the digital flow switch, causing a backflow of air, the measured value will change.

Assembly example

other side.

*5 The lead wire has an M12 (female) connector on

one side and an M12 (male) connector on the

- Digital flow switch PF3A701H-L-M ······· 1 pc. ② Air combination AC30B-03E-D · · · · · · 1 pc.
- Spacer with bracket Y300T-D ······2 pcs.
- Piping adapter E300-03-D1 pc.

Products do not come assembled. They should be ordered separately and assembled by the customer.



Simple Specials System

A system designed to respond quickly and easily to your special ordering needs

Please contact your local sales representative for more details



Specifications

For flow switch precautions and specific product precautions, refer to the "Operation Manual" on the SMC website.

	Mod	del	PF3A701H-L	PF3A702H-L
Electrical	Power	When used as a switch output device	24 VDC ±10%	
Electrical	supply voltage	When used as an IO-Link device	21.6 to 30 VDC	
	Output typ	pe	Select from NPN or PN	P open collector output.
	Output mode		Select from Hysteresis, Window comparator, Accumulated output, Accumulated pulse output, Error output, or Switch output OFF modes.	
Switch output	Max. applied voltage		30 V (NPN output)	
	Internal voltage drop (Residual voltage)		1.5 V or less (at load current of 80 mA)	
	Delay time*1		3.3 ms or less, variable from 0 to 60 s/0.01 s increments	
Analog output	utput Response time*2		Linked to the set value of the digital filter	
Display	Display		LCD, 2-screen display (Main screen/Sub screen) Main screen: Red/Green, Sub screen: Orange Main screen/Sub screen: 9 digits (7 segments 7 digits, 11 segments 2 digits)	
	Digital filter*3		Select from 1 s, 2 s, or 5 s.	
Standards			CE/UKCA marking	

- *1 The time from when the instantaneous flow reaches the set value to when the switch output operates can be set.
- *2 The time from when the flow is changed by a step input (when the flow rate changes from 0 to the maximum value of the rated flow range instantaneously) until the analog output reaches 90% of the rated flow rate
- *3 The time for the digital filter can be set to the sensor input. The response time indicates when the set value is 90% in relation to the step input.

Communication Specifications (IO-Link mode)

10 Link hors		
IO-Link type	Device	
IO-Link version	V 1.1	
Communication speed	COM2 (38.4 kbps)	
Configuration file	IODD file*1	
Minimum cycle time	3.3 ms	
Process data length	Input data: 4 bytes, Output data: 0 byte	
On request data communication	Yes	
Data storage function	Yes	
Event function	Yes	
Vendor ID	131 (0 x 0083)	
	PF3A701H-□□-L□-□□ : 394 (0 x 018A)	
	PF3A701H-□□-L3□-□□: 395 (0 x 018B)	
Device ID*2	PF3A701H-□□-L4□-□□: 396 (0 x 018C)	
Device ID -	PF3A702H-□□-L□-□□ : 397 (0 x 018D)	
	PF3A702H-□□-L3□-□□: 398 (0 x 018E)	
	PF3A702H-□□-L4□-□□: 399 (0 x 018F)	

- *1 The configuration file can be downloaded from the SMC website, https://www.smcworld.com
- *2 The device ID differs according to each product type (output specification).


Other specifications that are not listed are the same as those of the standard product. For details, refer to page 18.



Modular Type **O IO**-Link **C E UK** RoHS

4-Screen Display Digital Flow Switch with Pressure/Temperature Sensor

PF3A8 H-L Series



*1 Options are shipped together with the product but do not come assembled.

Options/Part Nos.


When only optional parts are required, order with the part numbers listed below.

Part no. Option		Note
ZS-37-A Lead wire with M12 connector		Length: 3 m
ZS-49-A	Lead wire with M12-M12 connector	Male/female conversion, Length: 3 m

Caution on Mounting

Pipe threads are not provided for this product. If the product is to be used as a single unit, order a spacer (or spacer with bracket) and a piping adapter separately. Refer to page 30 for details on attachments.

Assembly Example



- * Avoid mounting the lubricator on the inlet side.
- If a pressure relief 3-port valve is installed on the inlet side of the digital flow switch, causing a backflow of air, the measured value will change.

Assembly example

 ● Digital flow switch PF3A801H-L2-M
 1 pc.

 ② Air combination AC30B-03E-D
 1 pc.

 ⑤ Spacer with bracket Y300T-D
 2 pcs.

 ④ Piping adapter E300-03-D
 1 pc.

Pressure Temperature

Products do not come assembled. They should be ordered separately and assembled by the customer.



Simple Specials System

A system designed to respond quickly and easily to your special ordering needs

: kPa, MPa

:°C

Please contact your local sales representative for more details.



^{*2} The lead wire has an M12 (female) connector on one side and an M12 (male) connector on the other side.

Specifications

For flow switch precautions and specific product precautions, refer to the "Operation Manual" on the SMC website.

	Model		PF3A801H	PF3A802H
Fluid	Applicable fl	uid*1		litrogen
	Fluid temper		0 to	50°C
	Detection me			Bypass flow type)
<u> </u>	Rated flow ra		10 to 1000 L/min	20 to 2000 L/min
	Set point	Instantaneous flow	10 to 1050 L/min	20 to 2100 L/min
	range*2	Accumulated flow		9,999,990 L
	increment	Instantaneous flow Accumulated flow	1 L/min	2 L/min 0 L
		pulse (Pulse width = 50 ms)	Soloot from 10 L/r	oulse or 100 L/pulse.
		ue hold function*3	Intervals of 2 or 5 mi	nutes can be selected.
	Rated pressi			1.000 MPa
	Set pressure			1.050 MPa
		able increment		1 MPa
	Proof pressu	ıre		MPa
	Pressure los			Loss" graph on page 24.
		rature range		50.0°C
	Set temperat			o 60.0°C
		able increment		1°C 30 VDC
	Power suppl Current cons			A or less
	Protection	zampuon		protection
+		Flow rate*4		% F.S.
	Accuracy	Pressure		% F.S.
L		Temperature*5		000 L/min, 200 to 2000 L/min)
		ow rate/Pressure)		% F.S.
		stics (Flow rate/Pressure)		ure of 0 to 50°C, 25°C standard)
		ristics (Flow rate)*6 ular products (Flow rate)*7		MPa, 0.5 MPa standard)
	Output type	ular products (Flow rate)*/		% F.S. open collector. (2 outputs)
				parator mode, Error output, Output
	Output mode	•		ulated pulse output (Only flow rate
Г	Switch opera	ation	Select from Norma	l or Reversed output.
	Max. load cu			mA
output		Itage (NPN only)		VDC
		p (Residual voltage)		ad current of 80 mA)
	Response til			or less
	Delay time*8 Hysteresis*9			0 s/0.01 s increments le from 0
	Protection	·		nt protection
	Reference co	ondition*10		ditions or Normal conditions.
		Instantaneous flow		FM (ft³/min)
	Unit*11	Accumulated flow		, ft ³
	O.I.I.	Pressure		gf/cm², bar, psi
		Temperature		, ∘F
		*12 Instantaneous flow	0 to 1050 L/min (Flow under 10 L/min is displayed as "0")	0 to 2100 L/min
	Display	Accumulated		D ⁶ L (6-digit display)
	Display range	flow	0 to 9,999,999.99 x	⁰⁶ L (6-digit display) 10 ³ L (9-digit display)
		flow Pressure*12	0 to 9,999,999.99 x -0.050 to	⁾⁶ L (6-digit display) 10³L (9-digit display) 1.050 MPa
		flow Pressure*12 Temperature	0 to 9,999,999.99 x -0.050 to -10.0 t	0 ⁶ L (6-digit display) 10 ³ L (9-digit display) 1.050 MPa o 60.0°C
Display		flow Pressure*12	0 to 9,999,999.99 x -0.050 to -10.0 t 1 L/min	⁾⁶ L (6-digit display) 10³L (9-digit display) 1.050 MPa
Display	range	flow Pressure*12 Temperature Instantaneous flow	0 to 9,999,999.99 x -0.050 to -10.0 t 1 L/min 1 0.00	0 ⁶ L (6-digit display) 10 ³ L (9-digit display) 1.050 MPa 0 60.0°C 2 L/min 0 L 1 MPa
Display	range Min. display	Fressure*12 Temperature Instantaneous flow Accumulated flow	0 to 9,999,999.99 x -0.050 to -10.0 t 1 L/min 1 0.00	0 ⁶ L (6-digit display) 10 ³ L (9-digit display) 1.050 MPa 0 60.0°C 2 L/min 0 L
Display	range Min. display	Flow Pressure*12 Temperature Instantaneous flow Accumulated flow Pressure	0 to 9,999,999.99 x -0.050 to -10.0 t 1 L/min 1 0.00 LCD, 4-sc Upper line: Red/Gret	0 ⁶ L (6-digit display) 10 ³ L (9-digit display) 1.050 MPa 0.60.0°C 2 L/min 0 L 1 MPa 1°C reen display en, Lower line: Orange
Display	range Min. display unit	flow Pressure*12 Temperature Instantaneous flow Accumulated flow Pressure Temperature	0 to 9,999,999.99 x -0.050 to -10.0 t 1 L/min 1 0.00 0. LCD, 4-sc Upper line: Red/Greu Upper/Lower line: 10 digits (7 segr	06 L (6-digit display) 103 L (9-digit display) 1.050 MPa 0 60.0°C 2 L/min 0 L 1 MPa 1°C reen display en, Lower line: Orange ments 5 digits, 11 segments 5 digits)
Display	Min. display unit Display Indicator LE	flow Pressure*12 Temperature Instantaneous flow Accumulated flow Pressure Temperature	0 to 9,999,999.99 x -0.050 to -10.0 t 1 L/min 1 0.00 0. LCD, 4-sc Upper line: Red/Gre Upper/Lower line: 10 digits (7 segr	D ⁶ L (6-digit display) 10³ L (9-digit display) 10³ L (9-digit display) 1.050 MPa 0 60.0°C 2 L/min 0 L 1 MPa 1°C reen display en, Lower line: Orange ments 5 digits, 11 segments 5 digits) ED is ON when output is ON
Display -	Min. display unit Display Indicator LE Flow rate	flow Pressure*12 Temperature Instantaneous flow Accumulated flow Pressure Temperature	0 to 9,999,999.99 x -0.050 to -10.0 t 1 L/min 1 0.00 0. LCD, 4-sc Upper line: Red/Gre Upper/Lower line: 10 digits (7 segr	06 L (6-digit display) 108 L (9-digit display) 108 L (19-digit display) 109
Display Digital filter*13	Min. display unit Display Indicator LE Flow rate Pressure	flow Pressure*12 Temperature Instantaneous flow Accumulated flow Pressure Temperature	0 to 9,999,999.99 x -0.050 to -10.0 t 1 L/min 1 0.00 0.0 LCD, 4-sc Upper line: Red/Gree Upper/Lower line: 10 digits (7 segr OUT indicator: Orange LE 1 s (2 s or 5 s o	0 ⁶ L (6-digit display) 10 ³ L (9-digit display) 1.050 MPa 0.60.0°C 2 L/min 0 L 1 MPa 1°C reen display en, Lower line: Orange nents 5 digits, 11 segments 5 digits) D is ON when output is ON can be selected.) 0 30 s/0.01 s increments)
Digital filter*13	Min. display unit Display Indicator LE Flow rate Pressure Temperature	flow Pressure*12 Temperature Instantaneous flow Accumulated flow Pressure Temperature	0 to 9,999,999.99 x -0.050 to -10.0 t 1 L/min 1 0.00 LCD, 4-sc Upper line: Red/Gre Upper/Lower line: 10 digits (7 segr OUT indicator: Orange LE 1 s (2 s or 5 sc 0.1 s (Variable from 0 t	D ⁶ L (6-digit display) 10³ L (9-digit display) 1.050 MPa 0.60.0°C 2 L/min 0 L 1 MPa 1°C reen display en, Lower line: Orange ments 5 digits, 11 segments 5 digits) D is ON when output is ON can be selected.) 0.30 s/0.01 s increments)
Digital filter*13	Min. display unit Display Indicator LE Flow rate Pressure	flow Pressure*12 Temperature Instantaneous flow Accumulated flow Pressure Temperature	0 to 9,999,999.99 x -0.050 to -10.0 t 1 L/min 1 0.00 0. LCD, 4-sc Upper line: Red/Gre Upper/Lower line: 10 digits (7 segr	0 ⁶ L (6-digit display) 10 ³ L (9-digit display) 1.050 MPa 0.60.0°C 2 L/min 0 L 1 MPa 1°C reen display en, Lower line: Orange nents 5 digits, 11 segments 5 digits) D is ON when output is ON can be selected.) 0 30 s/0.01 s increments)
Digital filter*13	Min. display unit Display Indicator LE Flow rate Pressure Temperature Enclosure Withstand vid	flow Pressure*12 Temperature Instantaneous flow Accumulated flow Pressure Temperature Doltage sistance	0 to 9,999,999.99 x -0.050 to -10.0 t 1 L/min 1 0.00 0.0 LCD, 4-sc Upper line: Red/Gree Upper/Lower line: 10 digits (7 seg OUT indicator: Orange LE 1 s (2 s or 5 s o 0.1 s (Variable from 0 to	D ⁶ L (6-digit display) 10³ L (9-digit display) 10³ L (9-digit display) 10³ L (9-digit display) 1.050 MPa 0 60.0°C 2 L/min 0 L 1 MPa 1°C reen display en, Lower line: Orange ments 5 digits, 11 segments 5 digits) D is ON when output is ON can be selected.) 0 30 s/0.01 s increments) 1 s 0 505 ween terminals and housing
Digital filter*13	Min. display unit Display Indicator LE Flow rate Pressure Temperature Enclosure Withstand vid	flow Pressure*12 Temperature Instantaneous flow Accumulated flow Pressure Temperature	0 to 9,999,999.99 x -0.050 to -10.0 t 1 L/min 1 0.00 0.00 LCD, 4-sc Upper line: Red/Gree Upper/Lower line: 10 digits (7 segr OUT indicator: Orange LE 1 s (2 s or 5 s s 0.1 s (Variable from 0 to	D ⁶ L (6-digit display) 10³ L (9-digit display) 1.050 MPa 0.60.0°C 2 L/min 0 L 1 MPa 1°C reen display en, Lower line: Orange nents 5 digits, 11 segments 5 digits) D is ON when output is ON can be selected.) 0.30 s/0.01 s increments) 1 s 0.65 ween terminals and housing
Digital filter*13	Min. display unit Display Indicator LE Flow rate Pressure Temperature Enclosure Withstand vo Insulation re Operating tem	flow Pressure*12 Temperature Instantaneous flow Accumulated flow Pressure Temperature Doltage sistance	0 to 9,999,999.99 x -0.050 to -10.0 t 1 L/min 1 0.00 LCD, 4-sc Upper line: Red/Gre Upper/Lower line: 10 digits (7 segr OUT indicator: Orange LE 1 s (2 s or 5 sc 0.1 s (Variable from 0 to If 1000 VAC for 1 minute bet 50 ΜΩ (500 VDC measured via megor) Operating: 0 to 50°C, Stored: -10 to Operating: Stored: 35 to 6	D ⁶ L (6-digit display) 10 ³ L (9-digit display) 10 ³ L (9-digit display) 10 ³ L (9-digit display) 1 0.50 MPa 0 60.0°C 2 L/min 0 L 1 MPa 1°C reen display en, Lower line: Orange ments 5 digits, 11 segments 5 digits) ED is ON when output is ON can be selected.) 0 30 s/0.01 s increments) 1 s 0 60°C (No freezing or condensation) 0 60°C (No freezing or condensation)
Display Digital filter*13 Environmental resistance Standards	Min. display unit Display Indicator LE Flow rate Pressure Temperature Enclosure Withstand vollasulation re Operating tem Operating he	flow Pressure*12 Temperature Instantaneous flow Accumulated flow Pressure Temperature D D Ditage sistance perature range umidity range	0 to 9,999,999.99 x -0.050 to -10.0 t 1 L/min 1 0.00 0.0 LCD, 4-sc Upper line: Red/Gree Upper/Lower line: 10 digits (7 segr OUT indicator: Orange LE 1 s (2 s or 5 s o 0.1 s (Variable from 0 to 1000 VAC for 1 minute bet 50 MΩ (500 VDC measured via megor Operating: 0 to 50°C, Stored: -10 to Operating/Stored: 35 to 8 CE/UKC	D ⁶ L (6-digit display) 10³ L (9-digit display) 10³ L (9-digit display) 10³ L (9-digit display) 10° L (9-digit display) 10° C (9-digit display) 10° C (10°
Digital filter*13 Environmental resistance Standards Piping	Min. display unit Display Indicator LE Flow rate Pressure Temperature Enclosure Withstand vi Insulation re Operating tem Operating tem	flow Pressure*12 Temperature Instantaneous flow Accumulated flow Pressure Temperature D D Doltage sistance perature range umidity range fication	0 to 9,999,999.99 x -0.050 to -10.0 t 1 L/min 1 0.00 LCD, 4-sc Upper line: Red/Gree Upper/Lower line: 10 digits (7 segr OUT indicator: Orange LE 1 s (2 s or 5 s s 0.1 s (Variable from 0 to Iff 1000 VAC for 1 minute bet 50 MΩ (500 VDC measured via megor Operating: 0 to 50°C, Stored: -10 to Operating/Stored: 35 to 8 CE/UKC Modular (Body size: 30)	D ⁶ L (6-digit display) 10³L (9-digit display) 1.050 MPa 0.060.0°C 2 L/min 0 L 1 MPa 1°C reen display en, Lower line: Orange nents 5 digits, 11 segments 5 digits) D is ON when output is ON can be selected.) 0.30 s/0.01 s increments) 1 s 0.60 C (No freezing or condensation) 0.50 RH (No condensation) 0.40 marking 0.40 Modular (Body size: 40)
Display Digital filter*13 Environmental resistance Standards Piping Main materia fluid	Min. display unit Display Indicator LE Flow rate Pressure Temperature Enclosure Withstand w Operating tem	flow Pressure*12 Temperature Instantaneous flow Accumulated flow Pressure Temperature D Doltage sistance perature range umidity range fication contact with	0 to 9,999,999.99 x -0.050 to -10.0 t 1 L/min 1 0.00 LCD, 4-sc Upper line: Red/Gre Upper/Lower line: 10 digits (7 segr OUT indicator: Orange LE 1 s (2 s or 5 sc 0.1 s (Variable from 0 tr 1000 VAC for 1 minute bet 50 MΩ (500 VDC measured via megor Operating: 0 to 50°C, Stored: -10 tr Operating: 0 to 50°C, Stored: -10 tr CE/UKC Modular (Body size: 30) Stainless steel 304, Alu [Sensor: Pt, Au, Ni, Fe, Lead glass (exe	D ⁶ L (6-digit display) 10³ L (9-digit display) 10³ L (9-digit display) 10³ L (9-digit display) 10° C 0 L 1
Display Digital filter*13 Environmental resistance Standards Piping Main materia fluid Length of lea	Min. display unit Display Indicator LE Flow rate Pressure Temperature Enclosure Withstand vo Insulation re Operating tem Operating tem Operating to perating to perating to perating specials of parts in ad wire with o	flow Pressure*12 Temperature Instantaneous flow Accumulated flow Pressure Temperature D Doltage sistance perature range umidity range fication contact with	0 to 9,999,999.99 x -0.050 to -10.0 t 1 L/min 1 0.00 0.00 LCD, 4-sc Upper line: Red/Gree Upper/Lower line: 10 digits (7 segr OUT indicator: Orange LE 1 s (2 s or 5 s o 0.1 s (Variable from 0 to 1000 VAC for 1 minute bet 50 MΩ (500 VDC measured via megor Operating: 0 to 50°C, Stored: -10 to Operating/Stored: 35 to 8 CE/UKC Modular (Body size: 30) Stainless steel 304, Alu [Sensor: Pt, Au, Ni, Fe, Lead glass (exe	De L (6-digit display) 10³ L (9-digit display) 10³ L (9-digit display) 10³ L (9-digit display) 10³ L (9-digit display) 10° L (9-digit display) 10.500 MPa 10.600 L 1 MPa 10° C 10 L
Display Digital filter*13 Environmental resistance Standards Piping Main materia fluid Length of lea	Min. display unit Display Indicator LE Flow rate Pressure Temperature Enclosure Withstand vides and operating tem Operating tem Operating tem Operating specials of parts in ad wire with of Body	flow Pressure*12 Temperature Instantaneous flow Accumulated flow Pressure Temperature D Doltage sistance perature range umidity range fication contact with	0 to 9,999,999.99 x -0.050 to -10.0 t 1 L/min 1 0.00 LCD, 4-sc Upper line: Red/Gree Upper/Lower line: 10 digits (7 segr Upper/Lower line: 10 digits (7 segr OUT indicator: Orange LE 1 s (2 s or 5 s o 0.1 s (Variable from 0 to Iff 1000 VAC for 1 minute bet 50 MΩ (500 VDC measured via megor Operating: 0 to 50°C, Stored: -10 to Operating/Stored: 35 to 8 CE/UKC Modular (Body size: 30) Stainless steel 304, Alu [Sensor: Pt, Au, Ni, Fe, Lead glass (exe	D ⁶ L (6-digit display) 10 ³ L (9-digit display) 10 ³ L (9-digit display) 10 ³ L (9-digit display) 10,050 MPa 0 60.0°C 2 L/min 0 L 1 MPa 1°C reen display en, Lower line: Orange ments 5 digits, 11 segments 5 digits) ED is ON when output is ON can be selected.) 0 30 s/0.01 s increments) 1 s 0 60°C (No freezing or condensation) ED o°C (No freezing or condensation) A marking Modular (Body size: 40) minum alloy, PPS, HNBR mpted from the RoHS application), Al ₂ O ₃

Communication Specifications (IO-Link mode)

Communication Specification	
IO-Link type	Device
IO-Link version	V 1.1
Communication speed	COM2 (38.4 kbps)
Configuration file	IODD file*14
Minimum cycle time	5.8 ms
Process data length	Input data:12 bytes, Output data: 0 byte
On request data communication	Yes
Data storage function	Yes
Event function	Yes
Vendor ID	131 (0 x 0083)
Device ID*15	PF3A801H-L2□-□□□: 562 (0 x 0232)
Device ID. 10	PF3A802H-L2□-□□□: 563 (0 x 0233)

- *1 Air quality grade is JIS B 8392-1:2012 [4:6:-] and ISO 8573-1:2010 [4:6:-].
- *2 Set point range will change according to the setting of the zero cut-off function.
- *3 When using the accumulated value hold function, use the operating conditions to calculate the product life, and do not exceed it. The maximum update limit of the memory device is 1.5 million times. If the product is operated 24 hours per day, the product life will be as follows:
 - · 5 min interval: life is calculated as 5 min x 1.5 million = 7.5 million min = 14.3 years
 - · 2 min interval: life is calculated as 2 min x 1.5 million = 3 million min = 5.7 years
 - If the accumulated value external reset is repeatedly used, the product life will be shorter than the calculated life.
- *4 The value when connecting a product with a port size of 3/8 (PF3A801H) or 1/2 (PF3A802H)
- *5 In the low flow rate range, the temperature value fluctuates (rises). Refer to the "Temperature Accuracy" graph on page 25.
- *6 Do not release the OUT side piping port of the product to the atmosphere without connecting piping. If the product is used with the piping port released to atmosphere, accuracy may vary.
- *7 The value when the port size of the modular product is 3/8 (PF3A801H) or 1/2 (PF3A802H) and the product is operated at a supply pressure of 0.5
- *8 The time from when the measured value reaches the set value to when the switch output operates can be set.
- *9 If the measured value fluctuates around the set value, the width for setting more than the fluctuating width needs to be set. Otherwise, chattering will occur.
- *10 The flow rate given in the specifications is the value under standard conditions
- *11 Setting is only possible for models with the units selection function
- *12 Display range will change according to the setting of the zero cut-off function.
- *13 The time for the digital filter can be set to the sensor input. The response time indicates when the set value is 90% in relation to the step input.
- *14 The configuration file can be downloaded from the SMC website, https://www.smcworld.com
- *15 The device ID differs according to each product type (output specification).
- * Products with tiny scratches, marks, or display color or brightness variations which do not affect the performance of the product are verified as conforming products.



PF3A□**H(-L)** Series

Flow Range

Model				Flow range		
iviodei	0 L/	min 1000	L/min 3000	L/min 600	D L/min 1:	2000 L/min
PF3A701H(-L) PF3A801H-L	10 L/min 10 L/min 0 L/min	i	1000 L/min 1050 L/min 1050 L/min			
PF3A702H(-L) PF3A802H-L	20 L/min 20 L/min 0 L/min		2000 L/min 2100 L/mi 2100 L/mi	n		
PF3A703H(-L)	30 L/min 30 L/min 0 L/min			3000 L/min ■ 3150 L/min ■ 3150 L/min		
PF3A706H(-L)	60 L/min 60 L/min 0 L/min				6000 L/min 6300 L/min 6300 L/min	
PF3A712H(-L)	120 L/mii 120 L/mii 0 L/min	1				12000 L/min 12600 L/min 12600 L/min
	Į.			Rated flo	ow range Set point range	Display range


Analog Output


Flow/Analog Output

0 L/min	A *2	В
1 V	1.04 V	5 V
4 mA	4.16 mA	20 mA
0 I /min	C*2	
O L/IIIIII	U -	U
0 V	0.1 V	10 V
	1 V 4 mA 0 L/min	1 V 1.04 V 4 mA 4.16 mA

- *1 Analog output accuracy is within $\pm 3\%$ F.S. *2 A and C will change according to the setting of the zero cutoff function.
- *3 The analog output current from the connected equipment should be 20 μA or less when selecting 0 to 10 V. When more than 20 μA current flows, it is possible that the accuracy is not satisfied below 0.5 V.
- *4 The minimum value of the rated flow range will change according to the setting of the zero cut-off function.

Model	Min. value of the rated flow range*4	Max. value of the rated flow range
PF3A701H(-L)	10 L/min	1000 L/min
PF3A702H(-L)	20 L/min	2000 L/min
PF3A703H(-L)	30 L/min	3000 L/min
PF3A706H(-L)	60 L/min	6000 L/min
PF3A712H(-L)	120 L/min	12000 L/min






Voltage output (0 to 10 V)

Inlet pressure: 1.0 MPa


Large Flow Type 3-Color Display Digital Flow Switch PF3A H(-L) Series

Pressure Loss (Reference Data)


PF3A701H(-L) (for 1000 L/min)




PF3A702H(-L) (for 2000 L/min) PF3A802H-L




PF3A703H(-L) (for 3000 L/min)



PF3A706H(-L) (for 6000 L/min)




PF3A712H(-L) (for 12000 L/min)




Rc3/8

Flow Rate Characteristics (Reference Data)


AC30B-D + PF3A701H/PF3A801H-L








AW30-D + PF3A701H/PF3A801H-L



AW40-D + PF3A702H/PF3A802H-L




^{*} This product cannot be used for applications in which the flow exceeds the rated flow range. Use caution when selecting a product.




PF3A□**H(-L)** Series

IN Side Straight Section and Accuracy (Reference Data)


PF3A703H(-L) (for 3000 L/min)



PF3A706H(-L) (for 6000 L/min)




PF3A712H(-L) (for 12000 L/min)




- Do not connect equipment or piping which may generate fluctuations in the flow or drift on the IN side of the product. When installing a regulator on the IN side of the product, make sure that chatter is not generated.
- · The piping on the IN side must have a straight section of piping whose length is more than 8 times the piping I.D.

If a straight section of piping is not installed, the accuracy may vary by $\pm 3\%$ F.S. or more.


The "straight section" refers to a section of piping without any bends or rapid changes in the cross sectional area.





Temperature Accuracy (Reference Data)

PF3A801H/802H-L



Model	А	В
PF3A801H-L	100 L/min	1000 L/min
PF3A802H-L	200 L/min	2000 L/min

< Temperature Measurement >

When there is no (low) fluid flow, the heat of the platinum sensor heated for flow detection is transmitted to the temperature sensor, so the temperature measurement value in the low flow range (less than 10% of the rated flow rate) tends to increase in relation to the fluid temperature.


< Detection Principle (Flow) >

When a heated platinum sensor is installed in the branch passage, and fluid flows through it, the fluid removes heat from the platinum sensor. The resistance value of the platinum sensor decreases as it loses heat. As the resistance value decrease ratio has a uniform relationship to the fluid flow, the flow rate can be detected by measuring the resistance value.



Internal Circuits and Wiring Examples

NPN + Analog output selected PF3A7□□H-□□-CS/DS□-□□




Max. applied voltage: 28 V, Max. load current: 80 mA, Internal voltage drop: 1 V or less

CS: Analog output: 1 to 5 V or 0 to 10 V

Output impedance: 1 k Ω DS: Analog output: 4 to 20 mA Max. load impedance: 600 Ω Min. load impedance: 50 Ω

PNP + Analog output selected PF3A7 - H- - ES/FS - -




Max. load current: 80 mA, Internal voltage drop: 2 V or less

ES: Analog output: 1 to 5 V or 0 to 10 V


Output impedance: 1 k Ω FS: Analog output: 4 to 20 mA Max. load impedance: 600 Ω Min. load impedance: 50 Ω

NPN + External input selected PF3A7 - H- - CS/DS - -




Max. applied voltage: 28 V, Max. load current: 80 mA, Internal voltage drop: 1 V or less External input: Input voltage 0.4 V or less (Reed or Solid state input) for 30 ms or longer

PNP + External input selected PF3A7 - H- - ES/FS - - -




Max. load current: 80 mA, Internal voltage drop: 2 V or less External input: Input voltage 0.4 V or less (Reed or Solid state input) for 30 ms or longer

Accumulated pulse output wiring examples




PF3A7□□**H-**□□**-ES/FS**□**-**□□



PF3A□H(-L) Series

Internal Circuits and Wiring Examples


PF3A7 H- H- L- - NPN output type



Max. applied voltage: 30 V, Max. load current: 80 mA, Internal voltage drop: 1.5 V or less

PF3A7 - H- - L3/L4 - - -

NPN + Analog output selected




Max. applied voltage: 30 V, Max. load current: 80 mA, Internal

voltage drop: 1.5 V or less

L3: Analog output: 1 to 5 V or 0 to 10 V $\,$

Output impedance: 1 k Ω L4: Analog output: 4 to 20 mA Max. load impedance: 600 Ω Min. load impedance: 50 Ω

PF3A7 H- L3/L4 - NPN + External input selected




Max. applied voltage: 30 V, Max. load current: 80 mA, Internal

voltage drop: 1.5 V or less


External input voltage: 0.4 V or less (Reed or Solid state input) for 30 ms or longer

PF3A8□-L2□-□ NPN 2 output type




Max. applied voltage: 30 V, Max. load current: 80 mA, Internal voltage drop: 1.5 V or less

When used as an IO-Link device




* The numbers in the diagram show the connector pin layout.

PNP output type



Max. load current: 80 mA, Internal voltage drop: 1.5 V or less

PNP + Analog output selected




Max. load current: 80 mA, Internal voltage drop: 1.5 V or less

L3: Analog output: 1 to 5 V or 0 to 10 V $\,$


Output impedance: 1 k Ω L4: Analog output: 4 to 20 mA Max. load impedance: 600 Ω Min. load impedance: 50 Ω

PNP + External input selected



Max. load current: 80 mA, Internal voltage drop: 1.5 V or less External input voltage: 0.4 V or less (Reed or Solid state input) for 30 ms or longer

PNP 2 output type



Max. load current: 80 mA, Internal voltage drop: 1.5 V or less




۵

Large Flow Type 3-Color Display Digital Flow Switch PF3A H(-L) Series

Construction: Parts in Contact with Fluid


PF3A703H(-L)/706H(-L)/712H(-L)




Component Parts

No.	Description	Material	Note
1	Body	Aluminum alloy	Anodized
2	Branch passage	PPS	_
3	Gasket	HNBR	_
4	Sensor base	PPS	_
5	Gasket	HNBR	_
6	Sensor	Au, Pt, Al ₂ O ₃	_

PF3A701H(-L)/702H(-L)




PF3A801H-L/802H-L





Component Parts


<u> </u>	iponent i arts		
No.	Description	Material	Note
1	Body	ADC	
2	Branch passage	PPS	
3	Gasket	HNBR	
4	Sensor base	PPS	
5	Gasket	HNBR	
6	Sensor	Au, Pt, Al ₂ O ₃	
7	Attachment	ADC	
8	O-ring	HNBR	
9	O-ring	HNBR	
10	Mesh	Stainless steel 304	_
11	Spacer	PPS	
12	Pressure sensor	Silicon, PPS	
13	O-ring	HNBR	
	•	*	


Dimensions












_	•	**
z –	•	ф

Model Symbol	Port size	Α	В	D	E	F	Н	K	L	N	Р
PF3A703H	Rc1, NPT1, G1	130	45	79.1	55.3	22.5	25	35	60	30	M4 x 0.7 depth 7
PF3A706H	Rc1 1/2, NPT1 1/2, G1 1/2	170	60	94.1	70.3	30	68	45	80	40	M5 x 0.8 depth 8
PF3A712H	Rc2, NPT2, G2	200	70	104.1	80.3	35	85	50	100	50	M6 x 1.0 depth 9

PF3A□**H(-L)** Series


Dimensions

PF3A701H/702H PF3A801H/802H



Model Symbol	Α	В	D	E	F
PF3A701H/PF3A801H	68.3	43	64.4	55.4	28.9
PF3A702H/PF3A802H	72.3	51	73	71	35.5

Lead wire with M12 connector (Part no.: ZS-37-A)



	I -:	T
Pin no.	Pin name	Wire color
1	DC(+)	Brown
2	ELINIC	\A/bita


Cable Specifications

Conductor	Nominal cross section	AWG23
Insulator	Outside diameter	Approx. 1.1 mm
insulator	Color	Brown, Blue, Black, White
Sheath	Finished outside diameter	ø4


DC(-) Blue

* 4-wire type lead wire with M12 connector used for the PF3A series

Lead wire with M12-M12 connector (Part no.: ZS-49-A)







Wiring diagram

^{*} For wiring, refer to the "Operation Manual" on the SMC website, https://www.smcworld.com




PF3A□**H**(-**L**) Series

Optional Accessories

Piping Adapter: 1/4, 3/8, 1/2, 3/4

A piping adapter allows for the installation/removal of the component without removing the piping and thus makes maintenance easier.





Model	Р	Α	В	С	D	Applicable air combination model
E300-□02-D	1/4					
E300-□03-D	3/8	27	43	53	30	AC30-D
E300-□04-D	1/2					
E400-□02-D	1/4					
E400-□03-D	3/8	30	51	71	36	AC40-D
E400-□04-D	1/2	30	31	'	36	
E400-□06-D	3/4					

- * \square in model numbers indicates a pipe thread type. No indication is necessary for Rc; however, indicate N for NPT, and F for G.
- * Separate spacers are required for modular unit.


Spacer/Spacer with Bracket

Spacer






Model	A	В	С	D	E	Applicable air combination model
Y300-D	4.2	43	16.2	53	_	AC30-D
Y400-D	5.2	51	19.2	71	_	AC40-D



Model	Α	В	С	D	E	EE	F	G	н	J	K	Applicable air combination model
Y300T-D	4.2	85	42.5	67.5	35	_	14	7	20	6	41	AC30-D
Y400T-D	5.2	115	50	85.5	40	55	18	9	26	7	50	AC40-D

Mounting Position Example



Applicable air combination model	Α	В	С	D	E
AC30-D	55.1	57.2	104.2	245.6	46.8
AC40-D	72.6	75.2	105.2	285.6	46.8

3-Screen Display

Digital Flow Monitor

PFG300 Series



How to Order



PFG 3 0 0 - RT - M - L

Type

3 Remote type monitor unit

Input specification

Sym	nbol	Description	Applicable flow switch model
C)	Voltage input	PF3A7□H-CS/ES/L3 series
1	ı	Current input	PF3A7□H-DS/FS/L4 series

 The PFG3 (monitor unit) cannot be used as an IO-Link communication device.

Output specification •

RT	2 outputs (NPN/PNP switching type) + Analog voltage output*1, 2			
sv	2 outputs (NPN/PNP switching type) + Analog current output*2			
ΧY	2 outputs (NPN/PNP switching type) + Copy function			

- *1 Can switch between 1 to 5 V and 0 to 10 V
- *2 Can be switched to external input or copy function

Unit specification

Nil	Units selection function*3
M	SI units only*4

- *3 This product is for overseas use only. (The SI unit type is provided for use in Japan in accordance with the New Measurement Act.)
- *4 Fixed units: Instantaneous flow: L/min Accumulated flow: L

Option 4

	Operation manual	Calibration certificate
Nil	0	_
Υ	_	_
K	0	0
T	_	0

Option 3

Optio	แบบง					
Nil	None					
	ZS-28-CA-4					
С	Sensor connector					

Option 1


		Option 1 -
Symbol	De:	scription
Nil	Without lead wire	
L	Power supply/output connection lead wire (Lead wire length: 2 m)	Power supply/output connection lead wire

Options/Part Nos.

When only optional parts are required, order with the part numbers listed below.

Part no.	Option	Note
ZS-28-CA-4	Sensor connector	For PF3A7□H
ZS-46-A1	Bracket A	Tapping screw: Nominal size 3 x 8 L (2 pcs.)
ZS-46-A2	Bracket B	Tapping screw: Nominal size 3 x 8 L (2 pcs.)
ZS-46-B	Panel mount adapter	
ZS-46-D	Panel mount adapter + Front protection cover	
ZS-46-5L	Power supply/output connection lead wire	5-core, 2 m
ZS-27-01	Front protection cover	

Connection Example



•	Option 2				
	Symbol	[Description		
	Nil	None			
	A 1	Bracket A (Vertical mounting)	ZS-46-A1		
	A2	Bracket B (Horizontal mounting)	ZS-46-A2		
	В	Panel mount adapter	ZS-46-B		
	D	Panel mount adapter + Front protection cover	ZS-46-D		



3-Screen Display Digital Flow Monitor **PFG300** Series

For flow switch precautions and specific product precautions, refer to the "Operation Manual" on the SMC website.

Specifications

	Model				PFG300 series		
Applicable SMC	Model		PF3A701H	PF3A702H	PF3A703H	PF3A706H	PF3A712H
flow switch	Rated flow range	e*1	10 to 1000 L/min	20 to 2000 L/min	30 to 3000 L/min	60 to 6000 L/min	120 to 12000 L/min
	Cat maint warms	Instantaneous flow	-50 to 1050 L/min	-100 to 2100 L/min	-150 to 3150 L/min	-300 to 6300 L/min	-600 to 12600 L/min
	Set point range	Accumulated flow	0 to 999,999	9,999,990 L	0 to 999,999,999,990 L	0 to 999,99	9,999,900 L
	Smallest settable	Instantaneous flow	1 L/	min	2 L/min	5 L/min	10 L/min
Flow	increment	Accumulated flow	10	L	10 L	10	0 L
	Accumulated volum	ne per pulse	401/		401/2012	400.1	le de e
	(Pulse width = 50 m	ns)	10 L/	10 L/pulse 100 L/pulse 100 L/pulse		/puise	
	Accumulated value ho	old function*3	Intervals of 2 or 5 minu	tes can be selected. Th	e stored accumulated flo	w is held even when th	e power supply is OFF.
	Power supply vo	oltage		12 to 24 VDC ±10% (24 VDC when the PF	3A7 H is connected)	
Electrical	Current consum	nption	25 mA or less				
	Protection	•	Polarity protection				
	Display accurac	V	<u>+</u>	0.5% F.S. ± Minimun	n display unit (Ambien	t temperature of 25°C	()
_	Analog output a	-			. (Ambient temperatur		,
Accuracy	Repeatability				F.S. ± Minimum displ		
	Temperature char	racteristics			nt temperature: 0 to 50		
	Output type				NPN or PNP open coll		
			Select from Hi		nparator, Accumulate		d pulse output
	Output mode		20.000 11011111)		ut, or Switch output Ol		a paido darpar,
	Switch operation	n			om Normal or Reverse		
	Max. load currer			30,000 110	80 mA		
Switch output	Max. applied voltage				30 VDC		
			NPN output: 1 V or	less (at load current	of 80 mA), PNP outpu	t: 1.5 V or less (at loa	d current of 80 mA)
	Internal voltage drop (Residual voltage) Response time*2			1000 (41.1044 04.10111	3 ms or less		
	Delay time*2		Select from 0.00, 0.05 to 0.1	s (increment of 0.01 s), 0.1	to 1.0 s (increment of 0.1 s), 1	to 10 s (increment of 1 s), 2	0 s. 30 s. 40 s. 50 s. or 60 s.
	Hysteresis*4			(Variable from 0	10 10 0 (3 3, 33 3, 13 3, 33 3, 31 33
	Protection				Short circuit protection	 1	
	Output type		Voltage		<u> </u>		24 VDC)
			Voltage output: 1 to 5 V, 0 to 10 V (only when the power supply voltage is 24 VDC) Current output: 4 to 20 mA				
			(0 L/min to maximum value of the rated flow)				
Analog output*5	. Voltage output			· .	Output impedance: 1 kg	Ω	
	Impedance		Maximum load impeda	ance: 300 Ω (at power	supply voltage of 12 V)	. 600 Ω (at power sup	olv voltage of 24 VDC)
	Response time*			· · ·	50 ms or less	, , , , , , , , , , , , , , , , , , , ,	,
	External innut		Input voltage: 0.4 V or less (Reed or Solid state) for 30 ms or longer				
External input*6	Input mode		Select from Accumulated value external reset or Peak/Bottom value reset.				
	•		Voltage input: 1 to 5 VDC (Input impedance: 1 M Ω), Current input: 4 to 20 mA DC (Input impedance: 51 Ω)				
Concer law	Input type		(0 L/min to maximum value of the rated flow)				
Sensor input	Connection method		Connector (e-CON)				
	Protection		Over voltage protection (Up to 26.4 VDC)				
	Display mode		Select from Instantaneous flow or Accumulated flow.				
		Instantaneous flow			L/min, cfm (ft ³ /min)		
	Unit*7	Accumulated flow			L, ft ³ , L x 10 ⁶ , ft ³ x 10 ⁶	3	
	Dienlay ranga	Instantaneous flow	-50 to 1050 L/min	-100 to 2100 L/min	-150 to 3150 L/min	-300 to 6300 L/min	-600 to 12600 L/min
	Display range	Accumulated flow*9	0 to 999,999	9,999,990 L	0 to 999,999,999,990 L	0 to 999,99	9,999,900 L
Display	Minimum	Instantaneous flow	1 L/	min	2 L/min	5 L/min	10 L/min
Display	display unit	Accumulated flow	10	L	10 L	10	0 L
	Display type				LCD		
	Number of displ	lays			splay (Main screen, S		
	Display color		1) Main screen: Red/Green, 2) Sub screen: Orange				
	Number of display digits		1) Main screen: 5 digits (7 segments), 2) Sub screen: 9 digits (7 segments)				
	Indicator LED		LED ON when switch output is ON. OUT1/2: Orange				
Digital filter*8			Select from 0.00, 0.05 to 0.1 s (increment of 0.01 s), 0.1 to 1.0 s (increment of 0.1 s), 1 to 10 s (increment of 1 s), 20 s, or 30 s.				
	Enclosure		IP40				
	Withstand voltage		1000 VAC for 1 minute between terminals and housing				
Environment	Insulation resist		50 M Ω or more (500 VDC measured via megohmmeter) between terminals and housing				
	Operating temperature rang						
	Operating humid	dity range					
Standards					CE/UKCA marking		
Weight	Body			25 g (Excluding the	power supply/output c	onnection lead wire)	
weigilt	Lead wire with o	connector			+39 g		
4 D-4	ange of the applicable flow switch		*4 If the flow fluctuates around the set value, the width for setting more than				

- *1 Rated flow range of the applicable flow switch
- *2 Value without digital filter (at 0.00 s)
- *3 When using the accumulated value hold function, use the operating conditions to calculate the product life, and do not exceed it. The maximum access limit of the memory device is 1.5 million times. If the product is operated 24 hours per day, the product life will be as follows:
 - 5 min interval: life is calculated as 5 min x 1.5 million = 7.5 million min = 14.3 years
 - \cdot 2 min interval: life is calculated as 2 min x 1.5 million = 3 million min = 5.7 years If the accumulated value external reset is repeatedly used, the product life will be shorter than the calculated life.
- *4 If the flow fluctuates around the set value, the width for setting more than the fluctuating width needs to be set. Otherwise, chattering will occur.
- *5 Setting is only possible for models with analog output.
- *6 Setting is only possible for models with external input.
- *7 Setting is only possible for models with the units selection function.
- *8 The response time indicates when the set value is 90% in relation to the step input.
- The accumulated flow display is the upper 6-digit and lower 6-digit (total of 12 digits) display. When the upper digits are displayed, $x\ 10^6$ lights up.
- * Products with tiny scratches, marks, or display color or brightness variations which do not affect the performance of the product are verified as conforming products.




PFG300 Series

Internal Circuits and Wiring Examples

-XY


-RT -SV

NPN (2 outputs) + Copy function




-RT -SV PNP (2 outputs) + Copy function


-XY




-RT: NPN (2 outputs) + Analog voltage output -SV: NPN (2 outputs) + Analog current output




-RT: PNP (2 outputs) + Analog voltage output -SV: PNP (2 outputs) + Analog current output




-RT: NPN (2 outputs) + External input -SV: NPN (2 outputs) + External input




-RT: PNP (2 outputs) + External input -SV: PNP (2 outputs) + External input




Accumulated pulse output wiring examples





PNP (2 outputs) type




Dimensions










Bracket A (Part no.: ZS-46-A1)












Bracket configuration allows for mounting in four orientations.


Bracket B (Part no.: ZS-46-A2)








Bracket configuration allows for mounting in four orientations.




PFG300 Series


Dimensions


Panel mount adapter (Part no.: ZS-46-B)






Panel mount adapter + Front protection cover (Part no.: ZS-46-D)





Power supply/output connection lead wire (Part no.: ZS-46-5L)



Sensor connector (Part no.: ZS-28-CA-4)

Pin no.	Terminal	
1	DC (+)	
2	N.C.	
3	DC (-)	
4	IN*1	
*1 1 to 5 V or 4 to 20 mA		






Cable Specifications

Cable Specifications			
Conductor cross section		0.15 mm ² (AWG26)	
Inquilator	Outside diameter	1.0 mm	
Insulator	Color	Brown, Blue, Black, White, Gray (5-core)	
Sheath	Finished outside diameter	ø3.5	




Dimensions


Panel fitting dimensions




Multiple (2 pcs. or more) secure mounting <Horizontal>



Panel mount example <Horizontal>




<Vertical>



Panel mount example <Vertical>

SMC



PF3A□H(-L) Series Function Details

* The pressure and temperature settings are only available for the PF3A8□H-L series.

For the setting of functions and operation methods, refer to the "Operation Manual" on the SMC website.

■ Output operation

The output operation can be selected from the following:

Output (hysteresis mode and window comparator mode) corresponding to instantaneous flow, pressure, and temperature, or output (accumulated output and pulse output) corresponding to accumulated flow

(Default setting: Hysteresis mode, Normal output)

■ Simple setting mode

Only the set values for instantaneous flow, accumulated flow, pressure, and temperature can be changed. The output mode, output type, display color, and accumulated pulse output cannot be changed.

■ Display color

The display color can be selected for each output status. The selection of the display color provides visual identification of abnormal values.

Green for ON, Red for OFF
Red for ON, Green for OFF
Red all the time
Green all the time

■ Reference condition

The display unit can be selected from standard conditions or normal conditions.

Standard conditions: Flow rate converted to a volume at 20°C and 101.3 kPa (absolute pressure)

Normal conditions: Flow rate converted to a volume at 0°C and 101.3 kPa (absolute pressure)

■ Response time (Digital filter)

The response time (digital filter) can be set to suit the application.

(Default setting: Flow rate: 1 s, Pressure: 0.1 s)

The effects of fluctuation and the flickering of the display can be reduced by changing the response time (digital filter).

Flow rate	Pressure	Temp.
1 s	0 to 30 s	
2 s	(Increments of	1 s
5 s	0.01 s)	

■FUNC output switching function -

Analog output or external input can be selected. (Default setting: Analog output)

■ Selectable analog output function

1 to 5 V or 0 to 10 V can be selected for the analog voltage output type. (Default setting: 1 to 5 V)

■ External input function

The accumulated flow, peak value, and bottom value can be reset remotely.

Accumulated value external reset: The accumulated flow value is reset via external input signal.

In accumulated increment mode, the accumulated value will reset to and increase from zero.

In accumulated decrement mode, the accumulated value will reset to and decrease from the set value.

* When the accumulated value is stored to memory, every time the accumulated value external reset is activated, the memory will be accessed. Take into consideration that the max. number of times the memory can be accessed is 1.5 million times. The total number of external inputs and the accumulated value memorizing time interval should not exceed 1.5 million times.

Peak/Bottom value reset: The peak value and bottom value are reset.

■ Forced output function

The output is forced ON/OFF when starting the system or during maintenance. This enables confirmation of the wiring and prevents system errors due to unexpected output.

For the analog output type: When ON, the output will be 5 V or 20 mA, and when OFF, 1 V or 4 mA.

For the IO-Link compatible PF3A \square H-L series, diagnostic bit (error and flow rate) and process data (PD) flow measurement can be checked.

* Also, the increase or decrease of the flow will not change the ON/OFF status of the output while the forced output function is activated.

■ Accumulated value hold

The accumulated value is not cleared even when the power supply is turned OFF. The accumulated value is memorized every 2 or 5 minutes during measurement and continues from the last memorized value when the power supply is turned ON again.

The max. writable limit of the memory device is 1.5 million times, which should be taken into consideration.

■ Peak/Bottom value display

The max. (min.) flow rate is detected and updated from when the power supply is turned ON. In peak (bottom) value display mode, this max. (min.) flow rate as well as the pressure and temperature are displayed.

■ Display OFF mode

This function will turn the display OFF.

In the display OFF mode, three digits " $_$ $_$ " on the right side of the sub display will flash.

If any button is pressed during this mode, the display reverts to normal for 30 seconds to allow the flow, pressure, temperature, etc., to be quickly checked. When a flow monitor (PFG300 series) is connected, the displayed values might be different due to an error. When a flow monitor display is to be used, it is

■ Setting of a security code

The user can select whether a security code must be entered to release the key lock. At the time of shipment from the factory, it is set such that a security code is not required.

■ Key-lock function

Prevents operation errors such as accidentally changing setting values


■ Reset to the default settings

The product can be returned to its factory default settings.

recommended that this product be set to the display OFF mode.

■ Reversible display mode


When the switch is used upside down, the orientation of the display can be rotated to make it easier to read by using the reversible display function.



■Zero cut-off function

When the flow is close to 0 L/min, the product will round the value down and zero will be displayed. A flow value may be displayed even when the flow rate is 0 L/min due to high pressure or depending on the installation. The zero cut-off function will force the display to zero. The range to display zero can be changed. (For the PF3A8 \square H-L series, the pressure is also subject to this function.)

Example) Vertical mounting, Fluid direction: Bottom to top



■ Delay time setting

(PF3A□H-L series only)

The time from when the instantaneous flow, pressure, and temperature reach the set values to when the switch output operates can be set. Setting the delay time can prevent the switch output from chattering.

The total switching time is the switch operation time and the set delay time. (Default setting: 0 s)

0 to 60 s (Increments of 0.01 s)



Function Details **PF3A** H(-L) Series

■ Selection of the display on the sub screen

The display on the sub screen in measuring mode can be set.




	Accumulated value display	Set value display	Peak value display
Sub screen	Displays the accumulated value	Displays the set value	Displays the peak value
Switch output/Communication mode display	Bottom value display	Line name display	OFF
Displays the current mode (Only for the IO-Link compatible products)	Displays the bottom value	Displays the line name	Displays nothing
Mode ope 0	Lo 1800 0	2000 A B PF 3 R D	0


■ Analog output free range function

This function allows a flow that generates an output of 5 V (or 10 V when 0 to 10 V is selected) or 20 mA to be changed.

The value can be changed between 10% of the max. value of the rated flow and the max. value of the display range.

For analog voltage output of 0 to 10 V





■ Error display function

ality arises, the location and contents are displayed

Display	Error name	Description	Action
Er 1 Er 2	OUT over current error * Er2: PF3A8 - L series only	A load current of 80 mA or more has been applied to the switch output (OUT).	Eliminate the cause of the over current by turning OFF the power supply and then turning it ON again.
ннн	Instantaneous flow error Pressure/Temperature error*1 *1 PF3A8□-L series only	The flow rate, pressure, or temperature exceeds the upper limit of the setting range.	Decrease the flow rate, pressure, or temperature.
LLL	Pressure/Temperature error * PF3A8□-L series only	The pressure or temperature exceeds the lower limit of the setting range.	Increase the pressure or temperature.
999999 (Flashing)	Accumulated flow error	The accumulated flow has exceeded the accumulated flow range. (For accumulated increment)	Reset the accumulated flow.
☐ (Flashing)	Accumulated flow error	The accumulated flow has reached the set accumulated flow value. (For accumulated decrement)	
Er3	Outside of zero-clear range * PF3A8□-L series only	During zero-clear operation, a pressure of 7% F.S. or more has been applied. (The mode is returned to measurement mode after 1 s.)	Retry the zero-clear operation without pressure.
ErO Er4 Er6 Er0 Er0 Er10 Er12 Er14 Er16	System error	An internal data error has occurred.	Turn the power OFF and then ON again.
Er 15	Version does not match * Only for the IO-Link compatible products	The IO-Link version does not match that of the master.	Ensure that the master IO-Link version matches the device version.

If the error cannot be solved after the instructions above are performed, please contact SMC for investigation.



PF3A□**H(-L)** Series

■Zero-clear function (PF3A8□H-L series only) -

This function clears and resets the zero value on the display of the measured pressure. The indicated value can be adjusted within $\pm7\%$ F.S. of the pressure at the time of shipment from the factory.

■ Display fine adjustment function (PF3A8□H-L series only) -

Fine adjustment of the indicated value of the pressure sensor can be made within the range of $\pm 5\%$ of the read value. (This eliminates wide variations of the indicated value.)

■Measurement display setting (PF3A8□H-L series only)

Display/hide the measured accumulated flow rate, pressure, and temperature.

Normal display	Accumulated flow display OFF	Pressure display OFF
Displays the instantaneous flow, accumulated flow, pressure, and temperature	Displays items other than the accumulated flow	Displays items other than the pressure
0500 1000 S S S 385000 V	STORY AND THE ST	350 385000 V
Temperature display OFF	Accumulated flow, pressure, and temperature display OFF	
Displays items other than the temperature The accumulated flow display changes from 6 digits to 9 digits.	Displays the instantaneous flow	
0500 1000 S S		

PFG300 Series Function Details

■ Output operation -

The output operation can be selected from the following: Output (hysteresis mode and window comparator mode) corresponding to instantaneous flow or output (accumulated output and pulse

output) corresponding to accumulated flow (Default setting: Hysteresis mode, Normal output)

■ Simple setting mode

Only the set values for instantaneous flow and accumulated flow can be changed. The output mode, output type, display color, and accumulated pulse output cannot be changed.

■ Display color

The display color can be selected for each output status. The selection of the display color provides visual identification of abnormal values.

G	ireen for ON, Red for OFF
R	ed for ON, Green for OFF
	Red all the time
	Green all the time

■ Delay time setting

The time from when the instantaneous flow reaches the set value to when the switch output operates can be set. Setting the delay time can prevent the switch output from chattering.

(Default setting: 0 s)

0.00 s
0.05 to 0.1 s (Increments of 0.01 s)
0.1 to 1.0 s (Increments of 0.1 s)
1 to 10 s (Increments of 1 s)
20 s
30 s
40 s
50 s
60 s

0.00 s

0.05 to 0.1 s (Increments of 0.01 s)

■ Digital filter setting

The time for the digital filter can be set to the sensor input. Setting the digital filter can reduce chattering of the switch output and flickering of the analog output and the display.

and	0.1 to 1.0 s (Increments of 0.1 s)	
the	1 to 10 s (Increments of 1 s)	
	20 s	
set	30 s	

The response time indicates when the set value is 90% in relation to the step input.

(Default setting: 0 s)

■ FUNC output switching function

Analog output, external input, or copy function can be selected. (Default setting: Analog output)

■ Selectable analog output function

1 to 5 V or 0 to 10 V can be selected for the analog voltage output type. (Default setting: 1 to 5 V)

■ External input function

The accumulated flow, peak value, and bottom value can be reset remotely.

Accumulated value external reset: The accumulated flow value is reset via external input signal.

In accumulated increment mode, the accumulated value will reset to and increase from zero.

In accumulated decrement mode, the accumulated value will reset to and decrease from the set value.

* When the accumulated value is stored to memory, every time the accumulated value external reset is activated, the memory will be accessed. Take into consideration that the max. number of times the memory can be accessed is 1.5 million times. The total number of external inputs and the accumulated value memorizing time interval should not exceed 1.5 million times.

Peak/Bottom value reset: The peak value and bottom value are reset.

For the setting of functions and operation methods, refer to the "Operation Manual" on the SMC website.

■ Forced output function

The output is forced ON/OFF when starting the system or during maintenance. This enables confirmation of the wiring and prevents system errors due to unexpected output.

For the analog output type: When ON, the output will be 5 V (or 10 V when 0 to 10 V is selected) or 20 mA, and when OFF, 1 V (or 0 V when 0 to 10 V is selected) or 4 mA.

* Also, the increase or decrease of the flow will not change the ON/OFF status of the output while the forced output function is activated.

■ Accumulated value hold

The accumulated value is not cleared even when the power supply is turned OFF. The accumulated value is memorized every 2 or 5 minutes during measurement and continues from the last memorized value when the power supply is turned ON again.

The max. writable limit of the memory device is 1.5 million times, which should be taken into consideration.

■ Peak/Bottom value display

The max. (min.) flow rate is detected and updated from when the power supply is turned ON. In peak (bottom) value display mode, this max. (min.) flow rate is displayed.

■ Setting of a security code

The user can select whether a security code must be entered to release the key lock. At the time of shipment from the factory, it is set such that a security code is not required.

■ Key-lock function

Prevents operation errors such as accidentally changing setting values

■ Reset to the default settings

The product can be returned to its factory default settings.

■ Display with zero cut-off setting

When the flow is close to 0 L/min, the product will round the value down and zero will be displayed. A flow value may be displayed even when the flow rate is 0 L/min due to high pressure or depending on the installation. The zero cut-off function will force the display to zero. The range to display zero can be changed.



PFG300 Series

■ Selection of the display on the sub screen


The display on the sub screen in measuring mode can be set.





Set value display	Accumulated value display	Peak value display
Displays the set value	Displays the accumulated value	Displays the peak value
SNC IIIIIIIIIIIIIIIIIIIIIIIIIIIIIIIIIIII	GSMC ()	GSMC WIND IND A B V
Bottom value display	Line name display	OFF
Displays the bottom value	Displays the line name (Up to 5 alphanumeric characters can be input.)	Displays nothing
SNC IIIIIIIIIIIIIIIIIIIIIIIIIIIIIIIIIIII		9 SMC

■ Analog output free range function

This function allows a flow that generates an output of 5 V (or 10 V when 0 to 10 V is selected) or 20 mA to be changed. The value can be changed between 10% of the max. value of the rated flow and the max. value of the display range.








■ Error display function

When an error or abnormality arises, the location and contents are displayed.

Display	Error name	Description	Action
Er I Er Z	OUT over current error	A load current of 80 mA or more has been applied to the switch output (OUT).	Eliminate the cause of the over current by turning OFF the power supply and then turning it ON again.
HHH	Instantaneous flow error	The flow rate exceeds the max. value of the display range.	Decrease the flow rate.
LLL	Reverse flow error	There is a reverse flow equivalent to −5% or more. (Except PF3A7□H series)	Change the flow to the correct direction.
999999 flashes x 10 ⁶	Accumulated flow error	The flow rate exceeds the accumulated flow rate range.	Clear the accumulated flow rate.
Er U Er B Er B Er 14 Er 40	System error	An internal data error has occurred.	Turn the power OFF and then ON again.
Er 13	Copy error	The copy function does not operate properly.	After clearing the error by pressing the and buttons simultaneously for a minimum of 1 second, check the wiring and the model, and then attempt to copy again.






Function Details **PFG300** Series


■ Copy function

The set values of the monitor can be copied.

This can reduce setting labor and minimize the risk of setting mistakes.

The set value can be copied to up to 10 flow monitors simultaneously. (Maximum transmission distance: 4 m)





- 1) Wire as shown in the figure on the left.
- 2) All monitors are set to copy destination when first purchased. (Default condition is the monitor to be copied to.)
- 3) Press the source monitor to start copying.

■ Selection of power saving mode

The power saving mode can be selected.

With this function, if no buttons are pressed for 30 s, it shifts to power saving mode.

At the time of shipment from the factory, the product is set to the normal mode (the power saving mode is turned off).

(During power saving mode, [ECo] will flash in the sub screen and the operation light will be ON (only when the switch is ON).)

* There may be a difference in the displayed value on the connected flow switch and the flow monitor. When the flow monitor display is being used, it is recommended to set the flow switch display to OFF mode.

⚠ Safety Instructions

These safety instructions are intended to prevent hazardous situations and/or equipment damage. These instructions indicate the level of potential hazard with the labels of "Caution," "Warning" or "Danger." They are all important notes for safety and must be followed in addition to International Standards (ISO/IEC)*1), and other safety regulations.

Caution: Caution indicates a hazard with a low level of risk which, if not avoided, could result in minor or moderate injury.

Warning: Warning indicates a hazard with a medium level of risk which, if not avoided, could result in death or serious injury.

⚠ Danger: Danger indicates a nazaru wiun a nigin level on the first avoided, will result in death or serious injury. **Danger** indicates a hazard with a high level of risk which, *1) ISO 4414: Pneumatic fluid power - General rules relating to systems.

ISO 4413: Hydraulic fluid power – General rules relating to systems.

IEC 60204-1: Safety of machinery - Electrical equipment of machines. (Part 1: General requirements)

ISO 10218-1: Manipulating industrial robots - Safety.

⚠Warning

1. The compatibility of the product is the responsibility of the person who designs the equipment or decides its specifications.

Since the product specified here is used under various operating conditions, its compatibility with specific equipment must be decided by the person who designs the equipment or decides its specifications based on necessary analysis and test results. The expected performance and safety assurance of the equipment will be the responsibility of the person who has determined its compatibility with the product. This person should also continuously review all specifications of the product referring to its latest catalog information, with a view to giving due consideration to any possibility of equipment failure when configuring the equipment.

2. Only personnel with appropriate training should operate machinery and equipment.

The product specified here may become unsafe if handled incorrectly. The assembly, operation and maintenance of machines or equipment including our products must be performed by an operator who is appropriately trained and experienced.

3. Do not service or attempt to remove product and machinery/ equipment until safety is confirmed.

- 1. The inspection and maintenance of machinery/equipment should only be performed after measures to prevent falling or runaway of the driven objects have been confirmed.
- 2. When the product is to be removed, confirm that the safety measures as mentioned above are implemented and the power from any appropriate source is cut, and read and understand the specific product precautions of all relevant products carefully.
- 3. Before machinery/equipment is restarted, take measures to prevent unexpected operation and malfunction.
- 4. Contact SMC beforehand and take special consideration of safety measures if the product is to be used in any of the following conditions.
 - 1. Conditions and environments outside of the given specifications, or use outdoors or in a place exposed to direct sunlight.
 - 2. Installation on equipment in conjunction with atomic energy, railways, air navigation, space, shipping, vehicles, military, medical treatment, combustion and recreation, or equipment in contact with food and beverages, emergency stop circuits, clutch and brake circuits in press applications, safety equipment or other applications unsuitable for the standard specifications described in the product catalog.
 - 3. An application which could have negative effects on people, property, or animals requiring special safety analysis.
 - 4. Use in an interlock circuit, which requires the provision of double interlock for possible failure by using a mechanical protective function, and periodical checks to confirm proper operation.

⚠ Caution

1. The product is provided for use in manufacturing industries.

The product herein described is basically provided for peaceful use in manufacturing industries.

If considering using the product in other industries, consult SMC beforehand and exchange specifications or a contract if necessary.

If anything is unclear, contact your nearest sales branch.

Limited warranty and Disclaimer/ **Compliance Requirements**

The product used is subject to the following "Limited warranty and Disclaimer" and "Compliance Requirements".

Read and accept them before using the product.

Limited warranty and Disclaimer

- 1. The warranty period of the product is 1 year in service or 1.5 years after the product is delivered, whichever is first.*2)
 - Also, the product may have specified durability, running distance or replacement parts. Please consult your nearest sales branch.
- 2. For any failure or damage reported within the warranty period which is clearly our responsibility, a replacement product or necessary parts will be provided. This limited warranty applies only to our product independently, and not to any other damage incurred due to the failure of the product.
- 3. Prior to using SMC products, please read and understand the warranty terms and disclaimers noted in the specified catalog for the particular products.
 - 2) Vacuum pads are excluded from this 1 year warranty.

A vacuum pad is a consumable part, so it is warranted for a year after it is delivered.

Also, even within the warranty period, the wear of a product due to the use of the vacuum pad or failure due to the deterioration of rubber material are not covered by the limited warranty.

Compliance Requirements

- 1. The use of SMC products with production equipment for the manufacture of weapons of mass destruction (WMD) or any other weapon is strictly prohibited.
- 2. The exports of SMC products or technology from one country to another are governed by the relevant security laws and regulations of the countries involved in the transaction. Prior to the shipment of a SMC product to another country, assure that all local rules governing that export are known and followed.

⚠ Caution

SMC products are not intended for use as instruments for legal metrology.

Measurement instruments that SMC manufactures or sells have not been qualified by type approval tests relevant to the metrology (measurement) laws of each country. Therefore, SMC products cannot be used for business or certification ordained by the metrology (measurement) laws of each country.

Revision History

Edition B * The digital flow monitor PFG300 series has been added.

Number of pages has been increased from 16 to 28.

٧Z

Edition C * IO-Link compatible products (PF3A7□H-L) have been added. * The modular type has been added.

YX

Number of pages has been increased from 28 to 40.

Edition D * The 4-screen display PF3A8 series has been added. * Number of pages has been increased from 40 to 44.

↑ Safety Instructions Be sure to read the "Handling Precautions for SMC Products" (M-E03-3) and "Operation Manual" before use.