

Compact Type High Purity Air Operated Chemical Liquid Valve

LVD Series



Compact Type High Purity Air Operated Chemical Liquid Valve LVD Series

Guide ring Piston bumper Eliminates lateral motion of the poppet which Absorbs piston momentum to minimize reduces internal leakage. impact-induced particle generation. **Diaphragm (PTFE)** Buffer Special diaphragm construction ensures gentle opening Protects diaphragm from deformation and closing that prevents the formation of micro-bubbles. and damage due to back pressure. Minimal residual liquid Pilot port Residual liquid is minimized by the tapered shape and Integral clean One-touch fitting construction integrated fitting construction, allowing liquid to flow smoothly, Can select female thread (M5 x 0.8). achieving improved swept flow rate characteristics. Integrated fitting construction Body (New PFA) Offers quadruple seal construction. Nut lock mechanism. Compatible with chemicals such as acids, High flexural strength. Different tubing sizes can be selected. bases and ultrapure water. Dimension across inlet/outlet ports: Reduced by up to 29% Actuator section Piping from 4 directions are possible. LVD LVC



With bypass

Class 3 Class 4 Class 2 LVD20 LVC30 LVD30 LVC40 LVD40 Α 54.5 54.5 79 79.5 96 82 в 79 67 106 83 131 93 Suck Back

1



в

[mm]

Class 5

LVC50 LVD50

129 105.5

154 114

With flow rate adjustment Variations


Options

[Integrated fittings]... Page 740

Orifice	Flow rate								Applica	ble tubi	ing O.D						
diameter	characteristics	Model				Metri	c size							nch siz	e		
diameter	Kv (Cv)		3	4	6	8	10	12	19	25	1/8	3/16	1/4	3/8	1/2	3/4	1
2	0.07 (0.09)	LVD10	-0-	-0-							-0-						
4	0.3 (0.35)	LVD20		-•-	-0-								-0-				_
8	1.1 (1.3)	LVD30		_			-0-						-	-0-			
10	1.6 (1.9)	LVD40		_			-+-	-0-							-0-		_
16	4.2 (5)	LVD50	\vdash						-0-							-0-	

[Tube extensions]... Page 747

[Tube ext	ensions]…	Page 74	7									With reducer OBasic size
Orifice	Flow rate characteristics	Model		Applicable tubing O.D. Metric size Inch size								
diameter	Kv (Cv)	model	6	8	10	12	19	1/4	3/8	1/2	3/4	
4	0.3 (0.35)	LVD20	-0-			-		0			—	
8	1.1 (1.3)	LVD30		_	-Ò-	_	_	-	-Ò-	_	_	
10	1.6 (1.9)	LVD40	\vdash	_		-0-			_	-0-	_	
16	4.2 (5)	LVD50]				-0-			_	-0-	~
738							⁄⁄ s	VIC				



SMC

1.1 (1.3)

1.6 (1.9)

4.2

6.8

8

10

16

22


I VD30-F/FN

LVD40-F/FN

LVD50-F/FN

LVD60-F/FN

Air Operated Insert Bushing, Integrated Fittings LVD Series



@SMC

Standard Specifications



N	Nodel		LVD10	LVD20	LVD30	LVD40	LVD50		
Tubles O.D.	Note)	Metric	3, 4	3, 4, 6	6, 8, 10	10, 12	12, 19		
Tubing O.D.	14018)	Inch	1/8	1/8, 3/16, 1/4	1/4, 3/8	3/8, 1/2	1/2, 3/4		
Orifice diam	eter		ø2	ø4	ø8	ø10	ø16		
Flow rate	low rate Kv		0.07	0.3	1.1	1.6	4.2		
characteristics Cv			0.09	0.35	1.3	1.9	5		
Withstand p	ressu	ire [MPa]			1				
Operating pressure A→B flow			0 to						
[MPa]		B→A flow	0 to	0 to 0.2 0 to 0.1					
Back pressu	ıre [M	Pa]	0.3 or less 0.2 or less						
Valve leakag	ge [cn	n³/min]	0 (With water pressure)						
Pilot air pres	ssure	[MPa]	0.3 to 0.5						
Pilot port	One-t	touch fitting	ø4 x ø3 tubing ø6 x ø4 tubing						
size	Threa	aded			M5 x 0.8				
Fluid tempe	rature	e [°C]			0 to 100				
Ambient ten	npera	ture [°C]	0 to 60						
Weight [kg]			0.04 0.09 0.16 0.19 0.40						
Note) Refer to	page	769 for detail	s of the appli	icable tubing	sizes.				

Different Diameter Tubing Applicable with Reducer

Different diameter tubing can be selected (within a body class) by using a nut and insert bushing (reducer). Different diameter tubing cannot be selected for the body size 1. • • With reducer

		Tubing O.D.												
Body class		Metric size								Inch size				
	3	4	6	8	10	12	19	1/8	3/16	1/4	3/8	1/2	3/4	
1	0	0	—	-	-	—	-	0	-	—	—	—	—	
2	•	•	0	-	-	—	-	•	•	0	-	—	_	
3	-	-	٠	٠	0	—	_	-	-	٠	0	—	_	
4	-	-	—	-	٠	0	-	-	-	—	٠	0	—	
5	-	-	—	-	-	٠	0	-	-	_	_	•	0	

Note) Refer to page 766 for information on changing tubing sizes.

A Precautions


Be sure to read this before handling the products. Refer to back page 50 for Safety Instructions, and pages 768 and 769 for Compact Type High Purity Air Operated Chemical Liquid Valve Precautions.

LVD Series

Suck Back

A change of volume inside the suck back valve pulls in liquid at the end of the nozzle to prevent dripping.

Pilot port with One-touch fittings




Standard Specifications

N	lodel	LVD13U		
Tubing O.D. Note)	Metric size	3, 4		
Tubing O.D.	Inch size	1/8		
Orifice diameter		ø2		
Flow rate	Kv	0.07		
characteristics	Cv	0.09		
Withstand press	ure [MPa]	1		
Operating pressu	ire [MPa]	0 to 0.2		
Maximum suck b	ack volume [cm ³]	0.03		
Pilot air pressure	e [MPa]	0.3 to 0.5		
	One-touch fitting	ø4 x ø3 tubing		
Pilot port size	Threaded	M5 x 0.8		
Fluid temperatur	e [°C]	0 to 100		
Ambient tempera	ture [°C]	0 to 60		
Weight [kg]		0.07		

Note) Refer to page 769 for details on the applicable tubing sizes.


How to Order



Pilot port threaded type



Construction




Component Parts


No.	Description	Material
1	Actuator section	PPS
2	Body	PFA
3	Diaphragm	PTFE
4	End plate	PPS
5	Insert bushing	PFA
6	Nut	PFA
7	Collar	PFA
8	Flow rate adjuster section	PPS


LVD Series


Dimensions


Basic type
















Pilot port threaded type


Dimensions	;																[mm]
Model	A	В	С	D	E	F	G	н	J	ĸ	L	М	N	Р	Q	R	V
LVD1 -S	20	20	45	39	9.5	46	23	11.5	4.5	11	30	5	21	ø4 (5/32")	28	22.5	M5 x 0.8
LVD2□-S□	30	30	54.5	56	11	67	28.5	13	4	20	44	7	23.5	ø6	31.5	17.5	M5 x 0.8
LVD3□-S□	35	35	79.5	62	17.5	83	42.4	17.5	6	22	50	7	36.8	ø6	36	21	M5 x 0.8
LVD4□-S□	35	35	82	62	20	93	44.9	17.5	6	22	50	7	39.3	ø6	36	21	M5 x 0.8
LVD5□-S□	45	45	105.7	76	25	114	65.2	17.5	8	32	64	7	52.2	ø6	38.5	25	M5 x 0.8
744								(୍ରିମ	MC							



With flow rate adjustment & bypass

Dimensions	5		[mm]
Model	S	Т	U
LVD2□-S□	12.5	28	9.6
LVD3D-SD	26	34	17.5
LVD4□-S□	26	35	20
LVD5 -S	29.5	57	25







LVD Series


Dimensions

Suck back valve unit: Pilot port with One-touch fittings




Pilot port threaded type





SMC

Air Operated Tube Extensions LVD-T Series



Variations

	N	Nodel	LVD20-T	LVD30-T	LVD40-T	LVD50-T
	Orifice diar Tubing O.D.	neter	ø4	ø8	ø10	ø16
		Vetric	6	10	12	19
Туре	Symbol Valve type	Inch	1/4	3/8	1/2	3/4
Basic	¢PA ∳PB ∳PA	N.C.	0	0	0	0
	вцавдавца	N.O.	0	0	0	0
	N.C. N.O. Double acting	Double acting	0	0	0	0
With flow rate adjustment		N.C.	0	0	0	0
	N.C. Double acting	Double acting	0	0	0	0



RoHS

LVD-T Series



A Precautions

Be sure to read this before handling the products. Refer to back page 50 for Safety Instructions, and pages 768 and 769 for Compact Type High Purity Air Operated Chemical Liquid Valve Precautions.


N.C.


Standard Specifications

	Mode	əl	LVD20	LVD30	LVD40	LVD50				
Tuble o D		Metric	6	10	12	19				
Tubing O.D	•	Inch	1/4	3/8	1/2	3/4				
Orifice diar	neter		ø4	ø8	ø10	ø16				
Flow rate			0.3	1.1	1.6	4.2				
characteris	tics	Cv	0.35	1.3	1.9	5				
Withstand	press	ure [MPa]		1						
Operating pre	Dperating pressure A→B flow		0 to 0.5	0 to 0.3						
[MPa]		$B {\rightarrow} A \text{ flow}$	0 to 0.2		0 to 0.1					
Back press	ure [l	MPa]	0.3 or less	0.2 or less						
Valve leaka	ige [c	m³/min]		0 (With wa	ter pressure)					
Pilot air pre	essure	e [MPa]	0.3 to 0.5							
Pilot port	One	-touch fitting		ø6 x ø	4 tube					
size	Thre	aded		M5 :	x 0.8					
Fluid tempe	eratur	e [°C]		0 to	100					
Ambient te	Ambient temperature [°C]			0 to 60						
Weight [kg]			0.09	0.15 0.17 0.3						

Construction


Basic type






N.O.

Double acting



With flow rate adjustment (5)



PB PA

Component Parts

No.	Description	Material
1	Actuator section	PPS
2	Body	PFA
3	Diaphragm	PTFE
4	End plate	PPS
5	Flow rate adjuster section	PPS



Air Operated Tube Extensions **LVD-T** Series


Dimensions

Basic type

LVD5
-T

45

45 105.7 76 25



17.5

32 64 7 52.2


169.5 65

38.5 25

ø6

M5 x 0.8

Air Operated Insert Bushing, Integrated Fittings LVD-F/FN Series (ROHS)



Air Operated Insert Bushing, Integrated Fittings LVD-F/FN Series

,... I Bo Ве i

ı for ı I

ı

ı

ı .

Standard Specifications

	Mode		LVD20	LVD30	LVD40	LVD50	LVD60			
Tubing	<u> </u>	Metric	3, 4, 6	6, 8, 10	10, 12	12, 19	19, 25			
Tubing O	. D .	Inch	1/8, 3/16, 1/4	1/4, 3/8	3/8, 1/2	1/2, 3/4	3/4, 1			
Orifice dia	ameter		ø4	ø8	ø10	ø16	ø22			
Flow rate	Κv		0.3	1.1	1.6	4.2	6.8			
characteristics	Cv		0.35	1.3	1.9	5	8			
Withstand	d pressu	re [MPa]			1					
Operating Standard A→B flow			0 to 0.5		0 to 0.3		0 to 0.4			
Operating pressure	Stanuaru	$B \rightarrow A$ flow	0 to 0.2		0 to	0.1				
[MPa]	High back	A→B flow			0 to 0.5					
[ווור מ]	pressure	$B \rightarrow A$ flow			0 to 0.4					
Death	Standard	N.C./N.O.	0.3 or less		0.2 or less		0.2 or less			
Back	Stanuaru	Double acting	0.3 01 less		0.3 or less					
pressure [MPa]	High back pressure	N.C./N.O./ Double acting	0.5 or less							
Valve leal	kage [cn	n³/min]		0 (Wi	th water pres	sure)				
Pilot air p	ressure	[MPa]	0.	.3 to 0.5 (Hig	h back press	ure: 0.5 to 0.	8)			
Pilot port	size		Rc1/8, NPT1/8							
Fluid tem	perature	• [°C]	0 to 100							
Ambient t	tempera	ture [°C]	0 to 60							

Different Diameter Tubing Applicable with Reducer

Different diameter tubing can be selected (within a body class) by using a nut and insert bushing (reducer). With reducer

														within	Jaaoon
Deater		Tubing O.D.													
Body class				Metri	c size						Ir	nch siz	ze		
Ciass	3	4	6	8	10	12	19	25	1/8	3/16	1/4	3/8	1/2	3/4	1
2	٠	•	0	_	_	-	_	_	٠	•	0	_	—	_	-
3	_	-	٠	٠	0	-	-	—	—	—	٠	0	—	—	—
4	—	-	-	—	•	0	—	—	-	-	—	٠	0	-	—
5	_	-	-	—	_	•	0	—	—	-	—	—	•	0	—
6	_	-	-	_	-	-	•	0	—	-	_	—	—	•	0


Note) Refer to page 766 for information on changing tubing sizes.


APrecautions


Be sure to read this before handling the products. Refer to back page 50	
for Safety Instructions, and pages 1 768 and 769 for Compact Type High	LVC
Purity Air Operated Chemical Liquid Valve Precautions.	1.1/0
	LVH
	LVD
	LVQ
	LVP
	LVW
	LQ1
	LQ3
	LVN
	LQHB
	TL
	TLM
	TD TID
	TH Tih


LVD-F/FN Series


Dimensions
















Dimensions															[mm]
Model	Α	В	С	D	E	F	G	Н	J	ĸ	L	M	N	Р	Q
LVD2-V-F	30	30	54.5	56	11	67	28.5	11.5	4	20	44	7	23.5	Rc1/8 NPT1/8	24
LVD3-V-F	35	35	79.5	62	17.5	83	42.4	17.5	6	22	50	7	36.8	Rc1/8 NPT1/8	25
LVD4□-V□-F□	35	35	82	62	20	93	44.9	17.5	6	22	50	7	39.3	Rc1/8 NPT1/8	25
LVD50-V0-F0	45	45	105.7	76	25	114	65.2	17.5	8	32	64	7	52.2	Rc1/8 NPT1/8	27.5
LVD6□-V□-F□	58	74	137.8	84	32	164	76.8	27.5	8	56	71	6.5	70.8	Rc1/8 NPT1/8	44

Air Operated Insert Bushing, Integrated Fittings LVD-F/FN Series

Dimensions


With flow rate adjustment, High back pressure with flow rate adjustment





Dimensions	[mm]
Model	S
LVD2□-V□-F1	18.5
LVD3 -V -F1	28.5
LVD4□-V□-F1	28.5
LVD5 -V -F1	30.1
LVD6□-V□-F1	38


With bypass, High back pressure with bypass




Dimensions [mm]										
Model	Т	U								
LVD3□-V□-F2	36.9	17.5								
LVD4□-V□-F2	37.9	20								
LVD5 -V -F2	60.6	25								

With indicator.	Hiah	back	pressure	with	indicator

Dimensions	[mm]
Model	w
LVD20-V□-F4	56.4
LVD30-VD-F4	87.3
LVD40-V□-F4	89.8
LVD50-VD-F4	114.6
LVD60-VD-F4	149.4






(Max.T)

LVA
LVH
LVD
LVQ
LVP
LVW
LQ1
LQ3
LVN
LQHB
tl Til
TLM TILM
TD TID
TH Tih

LVC

Air Operated Flare, Integrated Fittings LVD-F/FN Series (RoHS)



Standard Specifications

	Mode	1	LVD20	LVD30	LVD40	LVD50	LVD60					
This and Metric			6	8, 10	12	19	25					
Tubing O	.D.	Inch	1/4									
Orifice di	ameter		ø4	ø8	ø10	ø16	ø22					
Flow rate	Kv		0.3	1.1	1.6	4.2	6.8					
characteristics	Cv		0.35	1.3	1.9	5	8					
Withstand	d pressu	ire [MPa]			1							
• "	Chandard	A→B flow	0 to 0.5		0 to 0.3		0 to 0.4					
Operating pressure			0 to 0.2 0 to 0.1									
[MPa]			0 to 0.5									
נואור מן	pressure	B→A flow	0 to 0.4									
Deals	Standard	N.C./N.O.	0.3 or less		0.2 or less	0.2 or less						
Back	Stanuaru	Double acting	0.3 01 1855		0.3 or less							
pressure [MPa]	High back pressure	N.C./N.O./ Double acting	0.5 or less									
Valve leal	kage [cn	n³/min]	0 (With water pressure)									
Pilot air p	ressure	[MPa]	0.3 to 0.5 (High back pressure: 0.5 to 0.8)									
Pilot port	size		Rc1/8, NPT1/8									
Fluid tem	perature	• [°C]	0 to 100									
Ambient	tempera	ture [°C]	0 to 60									


▲Precautions


Be sure to read this before handling the products. Refer to back page 50 for Safety Instructions, and pages 768 and 769 for Compact Type High Purity Air Operated Chemical Liquid Valve Precautions.




Air Operated Flare, Integrated Fittings **LVD-F/FN** Series


Dimensions







LVC
LVA
LVH
LVD
LVQ
LVP
LVW
LQ1
LQ3
LVN
LQHB
TL TIL
TLM TILM
TD TID
TH Tih




Dimensions															[mm]
Model	Α	В	С	D	E	F	G	н	J	ĸ	L	М	N	Р	Q
LVD2-Z-F	30	30	56.5	56	13	77	30.5	11.5	4	20	44	7	25.5	Rc1/8 NPT1/8	24
LVD3-Z-F	35	35	79.5	62	17.5	103	42.4	17.5	6	22	50	7	36.8	Rc1/8 NPT1/8	25
LVD4-Z-F	35	35	82	62	20	112	44.9	17.5	6	22	50	7	39.3	Rc1/8 NPT1/8	25
LVD5-Z-F	45	45	105.7	76	25	134	65.2	17.5	8	32	64	7	52.2	Rc1/8 NPT1/8	27.5
LVD6□-Z□-F□	58	74	137.8	84	32	181	76.8	27.5	8	56	71	6.5	70.8	Rc1/8 NPT1/8	44



LVD-F/FN Series


Dimensions


With flow rate adjustment, High back pressure with flow rate adjustment



Dimensions	[mm]
Model	S
LVD2□-Z□-F1	18.5
LVD3 -Z -F1	28.5
LVD4□-Z□-F1	28.5
LVD5 -Z -F1	30.1
LVD6□-Z□-F1	38


With indicator, High back pressure with indicator





Dimensions	[mm]
Model	w
LVD20-Z□-F4	58.4
LVD30-ZD-F4	87.3
LVD40-Z□-F4	89.8
LVD50-ZD-F4	114.6
LVD60-Z□-F4	149.4

Air Operated Tube Extensions LVD-T-F/FN Series RoHS



Standard Specifications


	Mode		LVD20	LVD30	LVD40	LVD50	LVD60		
A Metric		6	10	12	19	25			
Tubing O	Tubing O.D. Inch		1/4	3/8	1/2	3/4	1		
Orifice diameter			ø4	ø8	ø10	ø16	ø22		
Flow rate	Kv		0.3	1.1	1.6	4.2	6.8		
characteristics	Cv		0.35	1.3	1.9	5	8		
Withstand pressure [MPa]					1		-		
0	Operating Standard A→B flow		0 to 0.5	0 to 0.3 0 to 0					
Operating pressure	Statiuaru	B→A flow	0 to 0.2 0 to 0.1						
[MPa]	High back	A→B flow	0 to 0.5						
լաւаյ	pressure	B→A flow	0 to 0.4						
Back	Standard	N.C./N.O.	0.3 or less	0.2 or less					
pressure	Statiuaru	Double acting	0.3 01 1855		0.2 01 1855		0.3 or less		
[MPa]	High back press.	N.C./N.O./Double acting	0.5 or less						
Valve leal	kage [cn	n³/min]	0 (With water pressure)						
Pilot air p	Pilot air pressure [MPa]			0.3 to 0.5 (High back pressure: 0.5 to 0.8)					
Pilot port	Pilot port size			Rc1/8, NPT1/8					
Fluid tem	perature	• [°C]	0 to 100						
Ambient t	empera	ture [°C]	0 to 60						


APrecautions

Be sure to read this before handling the products. Refer to back page 50 for Safety Instructions, and pages 768 and 769 for Compact Type High Purity Air Operated Chemical Liquid Valve Precautions.

LVD-T-F/FN Series

Dimensions






Dimensions [mm]															
Model	Α	В	С	D	E	F	G	Н	J	ĸ	L	M	N	Р	Q
LVD2-T-F	30	30	61	56	14.5	103	35	11.5	4	20	44	7	30	Rc1/8 NPT1/8	24
LVD3-T-F	35	35	79.5	62	17.5	136	42.4	17.5	6	22	50	7	36.8	Rc1/8 NPT1/8	25
LVD4-T-F	35	35	82	62	20	137	44.9	17.5	6	22	50	7	39.3	Rc1/8 NPT1/8	25
LVD50-T0-F0	45	45	105.7	76	25	169.5	65.2	17.5	8	32	64	7	52.2	Rc1/8 NPT1/8	27.5
LVD6□-T□-F□	58	74	137.8	84	32	210	76.8	27.5	8	56	71	6.5	70.8	Rc1/8 NPT1/8	44

Air Operated Tube Extensions LVD-T-F/FN Series

Dimensions


With flow rate adjustment, High back pressure with flow rate adjustment




	_
	ן

Dimensions	[mm]
Model	S
LVD2□-T□-F1	18.5
LVD3 -T -F1	28.5
LVD4□-T□-F1	28.5
LVD5 -T -F1	30.1
LVD6□-T□-F1	38

With indicator, High back pressure with indicator





Dimensions	[mm]
Model	W
LVD20-T□-F4	62.9
LVD30-TD-F4	87.3
LVD40-T□-F4	89.8
LVD50-TD-F4	114.6
LVD60-TD-F4	149.4

LVC	
LVA	
LVH	
LVD	
LVQ	
LVP	
LVW	
LQ1	
LQ3	
LVN	
LQHB	
TL TIL	
TLM TILM	
TD TID	
TH Tih	

Manually Operated **Insert Bushing, Integrated Fittings** LVDH-F/FN Series ROHS

How to Order Valves

LVDH 2 0-V 07 FN Material Fitting type Actuator section Body Diaphragm Seal Buffer Symbol End plate F PFA PVDF PTFE FKM FN PFA PVDF PTFF FPDM Port B (OUT) different diameter size

Symbol	Application
Nil	Ports A & B same size
Refer to the applicable	Different diameter tubings can be
tubing table to the left.	selected within the same body class.

Body class

Symbol	Body class	Orifice dia.
2	2	ø4
3	3	ø8
4	4	ø10
5	5	ø16
6	6	ø22

		וג	LC	V	
	<u> </u>		_	Applicable	
		Body of		Connecting	Symbol
5 6	4 5	3 4	2	tubing size	Symbol
				: size	Metric
			۲	3 x 2	03
			۲	4 x 3	04
			0	6 x 4	06
				8 x 6	08
		\circ		10 x 8	10
	0	0		12 x 10	12
0	0			19 x 16	19
0				25 x 22	25
				ize	Inch s
			۲	1/8" x 0.086"	03
			۰	3/16" x 1/8"	05
		•	0	1/4" x 5/32"	07
		0		3/8" x 1/4"	11
•	0	0		1/2" x 3/8"	13
0	0			3/4" x 5/8"	19
0				1" x 7/8"	25
		With		3/4" x 5/8"	19

Symbol Mod

Standard Specifications

Model		LVDH20	LVDH30	LVDH40	LVDH50	LVDH60			
Tubing O.D. Metric		3, 4, 6	6, 8, 10	10, 12	12, 19	19, 25			
		Inch	1/8, 3/16, 1/4	1/4, 3/8	3/8, 1/2	1/2, 3/4	3/4, 1		
Orifice diameter			ø4	ø8	ø10	ø16	ø22		
Flow rate	Kν		0.3	1.1	1.6	4.2	6.8		
characteristics	characteristics Cv		0.35	1.3	1.9	5	8		
Withstand press	Withstand pressure [MPa]			1					
Operating pressure [MPa]	A→E	8 flow	0 to 0.5						
Valve leakage [c	cm³/m	in]	0 (With water pressure)						
Fluid temperatu	re [°C]	0 to 100						
Ambient temper	rature	[°C]	0 to 60						

Different Diameter Tubing Applicable with Reducer

Different diameter tubing can be selected (within a body class) by using a nut and insert bushing (reducer).

With reducer

Dashi							Tu	bing C).D.						
Body class				Metri	c size						Ir	nch siz	re		
Ciass	3	4	6	8	10	12	19	25	1/8	3/16	1/4	3/8	1/2	3/4	1
2	٠	•	0		-	-	-	-	•	•	0	-	-	-	-
3	_	—	٠	٠	0	-	-	—	—	-	۲	0	-	—	—
4	_	—	-	—	•	0	—	—	-	-	—	٠	0	-	-
5	_	-	-	-	-	•	0	-	_	-	_	—	•	0	-
6	-	—	_	_	_	_	•	0	—	—	-	—	_	•	0

Note) Refer to page 766 for information on changing tubing sizes.

100	7	6	0
-----	---	---	---



APrecautions

- Be sure to read this before handling
- the products. Refer to back page 50 for Safety Instructions, and pages
- 768 and 769 for Compact Type High
- Purity Air Operated Chemical Liq-
- uid Valve Precautions.
 - -----

Handle Operation

In order to prevent valve breakage due to excessive handle operation, the number of handle rotations is shown in the table below as a guide for handle operation when opening or closing the valve.


Number of Handle Rotations


(from fully open to fully closed)


Body class	Number of rotations
2	6 to 7
3	3 to 4
4	3104
5	5 to 6
6	5106


Manually Operated Insert Bushing, Integrated Fittings LVDH-F/FN Series

Dimensions












LVC
LVA
LVH
LVD
LVQ
LVP
LVW
LQ1
LQ3
LVN
LQHB
TL TIL
TLM TILM
TD TID
TH TIH



Dimensions

Dimensions														[mm]
Model	Α	В	С	D	E	F	J	K	L	М	N	Q	S	Y
LVDH20-VD-FD	30	30	54.5	56	11	67	4	20	44	7	23.5	24	18.5	-
LVDH30-VD-FD	35	35	79.5	62	17.5	83	6	22	50	7	36.8	25	34.6	50
LVDH40-V□-F□	35	35	82	62	20	93	6	22	50	7	39.3	25	34.6	50
LVDH50-VD-FD	45	45	105.7	76	25	114	8	32	64	7	52.2	27.5	36.2	50
LVDH60-V□-F□	58	74	137.8	84	32	164	8	56	71	6.5	70.8	44	39	50



Manually Operated **Flare, Integrated Fittings** LVDH-F/FN Series ROHS

How to Order Valves

LVDH 2 0 - Z 07 - FN Motorial Deduceles a

• 1110	cornar				
Sumbol	Body	Actuator section	Diaphragm	Seal	Buffer
Symbol	Бойу	End plate	Diaphragm	Sear	Duller
F	PFA	PVDF	PTFE	F۲	M
FN	PFA	PVDF	PTFE	EPDM	
F FN		PVDF			

	БС	2 Ø4 3 Ø8 4 Ø10					
Symbol	2 51						
2	Body classOrifice dia.2ø43ø8						
3	3 ø8						
4	4						
5	5	ø16					
6	6	ø22					

Fit	ting type					
Symbol	Model					
Ζ	LQ3					

Applicable tubing size

Symbol	Connecting			ly c		
Synbol	tubing size	2	3	4	5	6
Metric	: size					
06	6 x 4	0				
08	8 x 6		0			
10	10 x 8		0			
12	12 x 10			0		

Inch s	size			
25	25 x 22			
19	19 x 16			0
12	12 X 10		0	

07	1/4" x 5/32"	0				
11	3/8" x 1/4"		0			
13	1/2" x 3/8"			Ο		
19	3/4" x 5/8"				0	
25	1" x 7/8"					0

Standard Specifications

Mod	el		LVDH20	LVDH30	LVDH40	LVDH50	LVDH60		
Tubing O.D. Metric		Metric	6	8, 10	12	19	25		
Tubing O.D.		Inch	1/4	3/8	1/2	3/4	1		
Orifice diameter			ø4	ø8	ø10	ø16	ø22		
Flow rate	Κv		0.3	1.1	1.6	4.2	6.8		
characteristics	Cv		0.35	1.3	1.9	5	8		
Withstand press	sure [l	MPa]			1				
Operating pressure [MPa]	A→E	3 flow			0 to 0.5				
Valve leakage [c	:m³/m	in]		0 (Wi	th water pres	sure)			
Fluid temperatu	re [°C]	0 to 100						
Ambient temperature [°C] 0 to 60									

Precautions

Be sure to read this before handling the products. Refer to back page 50 for Safety Instructions, and pages 768 and 769 for Compact Type High Purity Air Operated Chemical Liquid Valve Precautions. -----**Handle Operation**

In order to prevent valve breakage due to excessive handle operation, the number of handle rotations is shown in the table below as a guide for handle operation when opening or closing the valve.

Number of Handle Rotations


(from fully open to fully closed)

Body class	Number of rotations				
2	6 to 7				
3	0 4= 4				
4	3 to 4				
5	5 40 0				
6	5 to 6				



Manually Operated Flare, Integrated Fittings LVDH-F/FN Series

Dimensions



Dimensions	Dimensions														
Model	Α	В	С	D	E	F	J	K	L	М	N	Q	S	Y	
LVDH20-ZD-FD	30	30	56.5	56	13	77	4	20	44	7	25.5	24	18.5	-	
LVDH30-ZD-FD	35	35	79.5	62	17.5	103	6	22	50	7	36.8	25	34.6	50	
LVDH40-Z□-F□	35	35	82	62	20	112	6	22	50	7	39.3	25	34.6	50	
LVDH50-ZD-FD	45	45	105.7	76	25	134	8	32	64	7	52.2	27.5	36.2	50	
LVDH60-ZD-FD	58	74	137.8	84	32	181	8	56	71	6.5	70.8	44	39	50	

Manually Operated Tube Extensions LVDH-T-F/FN Series RoHS

How to Order Valves

LVDH 2 0 - T 07 - FN Body class

	Symbol	Body	Actuator section	Diaphragm	Seal	Buffer	
		BOUY	End plate	Diaphragm	Sear	Duller	
	F	PFA	PVDF	PTFE	FKM		
	FN	PFA	PVDF	PTFE	EPDM		

Fitting	type

α4

ø8

ø10

ø16

ø22

Symbol Type

T Tube extensions

Tubing	0	n	

Svmbol			lass	s		
Symbol	Tubing O.D.	2	3	4	5	6
Metric	size					
06	ø6	0				
10	ø10		0			
12	ø12			0		
19	ø19				0	
25	ø25					0
Inch s	ize					
07	1/4	0				
11	3/8		0			
13	1/2			0		
19	3/4				Ο	
25	1					0

Standard Specifications

Mod	el		LVDH20	LVDH30	LVDH40	LVDH50	LVDH60			
Tubian O D Metric		6	6 10 12 19							
Tubing O.D.		Inch	1/4	3/8	1/2	3/4	1			
Orifice diameter			ø4	ø8	ø10	ø16	ø22			
Flow rate	Kν		0.3	1.1	1.6	4.2	6.8			
characteristics	Cv		0.35	8						
Withstand press	ure [l	MPa]	1							
Operating pressure [MPa]	A→E	3 flow		0 to 0.5						
Valve leakage [c	:m³/m	in]		0 (Wi	th water pres	sure)				
Fluid temperatu	re [°C]	0 to 100							
Ambient temperature [°C]					0 to 60					

2

3

4

5

6

2

3

4

5

6

APrecautions

Be sure to read this before handling the products. Refer to back page 50 for Safety Instructions, and pages 768 and 769 for Compact Type High Purity Air Operated Chemical Liquid Valve Precautions. Handle Operation

In order to prevent valve breakage due to excessive handle operation, the number of handle rotations is shown in the table below as a guide for handle operation when opening or closing the valve.

Number of Handle Rotations


(from fully	open to	o fully	closed)
-------------	---------	---------	---------


Body class	Number of rotations				
2	6 to 7				
3	3 to 4				
4	3104				
5	5 to 6				
6	5106				





Manually Operated Tube Extensions LVDH-T-F/FN Series

Dimensions










LVC
LVA
LVH
LVD
LVQ
LVP
LVW
LQ1
LQ3
LVN
LQHB
TL TIL
TLM TILM
TD TID
TH Tih

c



Dim		

Dimensions														[mm]
Model	Α	В	С	D	E	F	J	K	L	М	N	Q	S	Y
LVDH20-TD-FD	30	30	61	56	14.5	103	4	20	44	7	30	24	18.5	-
LVDH30-TD-FD	35	35	79.5	62	17.5	136	6	22	50	7	36.8	25	34.6	50
LVDH40-TD-FD	35	35	82	62	20	137	6	22	50	7	39.3	25	34.6	50
LVDH50-TD-FD	45	45	105.7	76	25	169.5	8	32	64	7	52.2	27.5	36.2	50
LVDH60-TD-FD	58	74	137.8	84	32	210	8	56	71	6.5	70.8	44	39	50

LVD Series Fittings and Special Tools

Fittings

Changing Tubing Sizes

The tubing size can be changed within the same body class (body size) by replacing the nut and insert bushing.

Dech							Tul	oing C).D.						
Body class		Metric size							Inch size						
class	3	4	6	8	10	12	19	25	1/8	3/16	1/4	3/8	1/2	3/4	1
1	0	0	—	—	_	—	—	—	0	—	_	—	-	—	—
2	•	٠	0	—	—	—	—	—	٠	•	0	—	-	—	—
3	—	-	•	٠	0	-	—	-	—	-	٠	0	—	—	—
4	_	—	-	_	٠	0	_	_	_	-	_	٠	0	—	_
5	—	—	-	—	—	٠	0	—	—	-	_	—	•	0	—
6	—	-	—	-	—	-	٠	0	—	-	—	—	—	٠	0

Changing tubing sizes

Example) Changing the tubing from an outside diameter of 1/4" to 1/8" in body class 2.

Prepare an insert bushing and nut for tubing O.D. $1/8^{\prime\prime}$ (LQ1-2U03) and change the tubing size. (Refer to the section on how to order fitting parts.)

Insert bushing

Tubing O.D. 1/4" LQ1-2U07

(Basic size)

Nut

1 Q1-2N07

Tubing


Note) Tubing is sold separately.



\backslash	Component parts				
	Nut	Insert	Collar (Insert assembly)		
○ Basic size	Yes	Yes	No		
 Reducer type 	Yes	Yes	Yes		

A Caution

1. Connect tubing with special tools. Refer to the pamphlet "High-Purity Fluoropolymer Fittings Hyper Fitting/Series LQ1, 2 Work Procedure Instructions" (M-E05-1) for connecting tubing and special tools.



How to Order Fitting Parts

			* Type U is reco	mmended w	hen changing tubing	sizes.	
LQ1-1		J U.	3	-• Tubing	g size Note)		
				Symbol	Tubing size	Body class (fittings)]
		Туре с	of part	03	1/8" x 0.086", 3 x 2	4	1
		Symbol	Type of part	04	4 x 3	1	
		U	Nut & Insert bushing	03	1/8" x 0.086"		1
		в	Insert bushing	04	4 x 3]	
		Ν	Nut	05	3/16" x 1/8"	2	
				06	6 x 4		
	Body	y class	s fittings	07	1/4" x 5/32"		
	Symbo	Body c	class (fittings)	06	6 x 4		
	1		1	08	8 x 6		
	2		2	10	10 x 8	3	
	3		3	07	1/4" x 5/32"		
	4		4	11	3/8" x 1/4"		
	5		5	10	10 x 8		
	6		6	12	12 x 10	4	
				11	3/8" x 1/4"		
				13	1/2" x 3/8"		
				12	12 x 10		
				13	1/2" x 3/8"	5	
				19	3/4" x 5/8", 19 x 16		
				19	3/4" x 5/8", 19 x 16	6	Note) Refer to
				25	1" x 7/8", 25 x 22		on the a

SMC

te) Refer to page 769 for details on the applicable tubing sizes.

Applicable Fluids

High Purity Air Operated Chemical Liquid Valve Material and Fluid Compatibility Check List

Chemical		Compatibility	
Acetone		O Note 1) 2)	
Ammonium hydroxide		O Note 2)	
Isobutyl alcohol		O Note 1) 2)	
Isopropyl alcohol		O Note 1) 2)	
Hydrochloric acid		0	
Ozone (dry)		0	
Hydrogen peroxide	Concentration 5% or less, Temperature 50°C or less	0	
Ethyl acetate		O Note 1) 2)	
Butyl acetate		O Note 1) 2)	
Nitric acid (except fuming nitric acid)	Concentration 10% or less	O Note 2)	
DI water (deionized water)		0	
Sodium hydroxide (caustic soda)	Concentration 50% or less	0	
Nitrogen gas		0	
Ultrapure water		0	
Toluene		O Note 1) 2)	
Hydrofluoric acid		×	
Sulfuric acid (except fuming sulfuric ac	id)	O Note 2)	Table symbols Can be used. C: Can be used under certain conditions.
Phosphoric acid	Concentration 80% or less	0	\bigcirc : Can be used under certain conditions. X : Cannot be used.

LVC
LVA
LVH
LVD
LVQ
LVP
LVW
LQ1
LQ3
LVN
LQHB
tl Til
TLM
TD TID
TH Tih

The material and fluid compatibility check list provides reference values as a guide only.

Note 1) Since static electricity may be generated, implement suitable countermeasures.

Note 2) Use caution as permeation may occur. The permeated fluid may effect the parts of other materials.

• Compatibility is indicated for fluid temperatures of 100°C or less.

• The material and fluid compatibility check list provides reference values as a guide only, therefore we do not guarantee the application to our product.

. The data above is based on the information presented by the material manufacturers.

· SMC is not responsible for its accuracy and any damage happened because of this data.



Compact Type High Purity Air Operated Chemical Liquid Valve Precautions 1

Be sure to read this before handling the products.

Design / Selection

Warning

1. Check the specifications.

Give careful consideration to operating conditions such as the application, fluid and environment, and use within the operating ranges specified in this catalog.

2. Fluids

Operate after confirming the compatibility of the product's component materials with fluids, using the check list on page 767. Please contact SMC regarding fluids other than those in the check list. Operate within the indicated fluid temperature range.

3. Maintenance space

Ensure the necessary space for maintenance and inspections.

4. Fluid pressure range

Keep the supplied fluid pressure within the operating pressure range shown in the catalog.

5. Ambient environment

Install the product in an environment where there is no effect from radiant heat caused by heat sources, etc., and use within the ambient operating temperature range. After confirming the compatibility of the product's component materials with the ambient environment, operate so that fluid does not adhere to the product's exterior surfaces.

6. Liquid seals

When circulating fluid:

Provide a relief valve in the system so that fluid does not get into the liquid seal circuit.

7. Countermeasures for static electricity

Since static electricity may be generated depending on the fluid being used, implement suitable countermeasures.

Mounting

Warning

1. If air leakage increases or equipment does not operate properly, stop operation.

After mounting, perform suitable function and leak tests to confirm that the mounting is correct.

2. Operation Manual

Mount and operate the product after reading the manual carefully and understanding its contents. Also, keep the manual where it can be referred to as necessary.

Piping

▲ Caution

1. Preparation before piping

Before piping is connected, it should be thoroughly blown out with air (flushing) or washed to remove chips, cutting oil and other debris from inside the pipe.

Install piping so that it does not apply pulling, pressing, bending or other forces on the valve body. Piping

▲ Caution

2. Use the tightening torques shown below for the threaded pilot port.

Tightening Torque for Operating Port

Operating port	Torque [N·m]
M5	1/6 turn with a tightening tool after first tightening by hand
Rc, NPT1/8	0.8 to 1.0


3. Use pilot ports and sensor (breathing) ports as indicated below.

	PA port	PB port	Sensor (breathing) port
N.C.	Pressure	Breathing	Breathing
N.O.	Breathing	Pressure	Breathing
Double acting	Pressure	Pressure	Breathing

In the case of N.C. and N.O. types, the port which does not receive operating pressure is released to atmosphere. When intake and exhaust directly from the valve is not desired due to problems with the ambient environment or scattering of dust, etc., install piping and perform intake and exhaust at a location which does not present a problem.

4. Connect tubing with special tools.

Refer to the pamphlet "High-Purity Fluoropolymer Fittings Hyper Fitting/Series LQ1, 2 Work Procedure Instructions" (M-E05-1) or "High Purity Fluoropolymer Fittings Hyper Fitting/ Flare Type Series LQ3 Fitting Procedure" (M-E06-4) for connecting tubing and special tools. (Downloadable from our web site.)



5. Tighten the nut until it touches the end surface of the body, and then tighten it an additional 1/8 turn. If the nut won't turn any further, then it means a sufficient tightening has occurred. Refer to the proper tightening torques shown below.

Tightening Torque for Piping

Body class	Torque [N·m]				
class	LQ1	LQ3			
2	0.3 to 0.4	1.6 to 1.8			
3	0.8 to 1.0	3.2 to 3.5			
4	1.0 to 1.2	5.0 to 5.3			
5	2.5 to 3.0	10.0 to 10.5			
6	5.5 to 6.0	22.5 to 23.0			

Operating Air Supply

Warning Use clean air.

Do not use compressed air which includes chemicals, synthetic oils containing organic solvents, salt, or corrosive gases, etc., as this may cause damage or malfunction.





Compact Type High Purity Air Operated Chemical Liquid Valve Precautions 2

Be sure to read this before handling the products.

Installation and Removal of Tubing for Pilot Port Section

▲ Caution

1. Installation of tubing

- Using tube cutters TK-1, 2 or 3, take a tube having no flaws on its periphery and cut it off at a right angle. Do not use pinchers, nippers or scissors, etc. The tubing might be cut diagonally or flattened, making installation impossible or causing problems such as disconnection and leakage.
- Hold the tube and push it in slowly, inserting it securely all the way into the fitting.
- 3) After inserting the tubing, pull on it tightly to confirm that it will not come out. If it is not installed securely all the way into the fitting, problems such as leakage or disconnection of the tubing can occur.
- 4) Grease is not used due to the KP series oil-free specification. For this reason, greater insertion force is required when tubing is installed. In particular, polyurethane tubing may fold when inserted due to its softness. Hold the end of the tubing, and insert it all the way in slowly and securely. Refer to dimension "M" in the dimension drawings for guidance on the insertion depth of tubing.

2. Removal of tubing

- 1) Push in the release button sufficiently, pressing the collar evenly around its circumference.
- 2) Pull out the tubing while holding down the release button so that it does not pop out. If the release button is not pressed down sufficiently, there will be increased bite on the tubing and it will become more difficult to pull it out.
- 3) When the removed tubing is to be used again, first cut off the section of the tubing which has been chewed. Using the chewed portion of the tube as it is can cause problems such as leakage or difficulty in removing the tubing.

Precautions on Use of Other Tubing Brands

▲ Caution

 When using tubing brands other than SMC, confirm that the tubing outside diameter tolerances satisfy the following specifications.

1) Polyolefin tubing:	Within ±0.1 mm
2) Polyurethane tubing:	Within ±0.15 mm,
	Within –0.2 mm
Nylon tubing:	Within ±0.1 mm
Soft nylon tubing:	Within ±0.1 mm

Do not use tubing if the outside diameter tolerance is not satisfied. It may not be possible to connect the tubing, or leakage or disconnection may occur after connection.

Polyolefin tubing is recommended for use with clean room fittings. Note that while other types of tubing will satisfy performance standards for leakage and tubing pull-out strength, etc., the degree of cleanliness will deteriorate.

Operating Environment

A Warning

- 1. Do not use in a location having an explosive atmosphere.
- Do not operate in locations where vibration or impact occurs.

Operating Environment

\land Warning

\land Warning

- 3. Do not use in locations where radiated heat will be received from nearby heat sources.
- 4. Do not use in environments which exceed the ambient temperature specifications of the product.

<u>Maintenance</u>

1. Maintenance should be performed in accordance with the procedures in the Operation Manual.

Incorrect handling can cause damage or malfunction of machinery and equipment, etc.

2. Before removing equipment or compressed air supply/ exhaust devices, shut off the air and power supplies, and exhaust compressed air from the system. Further, when restarting equipment after remounting

or replacement, first confirm safety and then check the equipment for normal operation.

- 3. Perform work after removing residual chemicals and carefully replacing them with DI water or air, etc.
- 4. Do not disassemble the product. Products which have been disassembled cannot be guaranteed. If disassembly is necessary, please contact SMC.
- 5. In order to obtain optimum performance from valves, perform periodic inspections to confirm that there are no leaks from valves or fittings, etc.

▲ Caution

1. Removal of drainage

Flush drainage from filters regularly.

Handling

A Caution

1. To adjust the flow rate with flow rate adjustment, open gradually starting from the fully closed state.

Opening is accomplished by turning the adjustment knob counterclockwise. Additionally, do not apply excessive force to the adjustment knob when nearing a fully open or closed state. This may result in deformation of the orifice sheet surface or damage to the threaded portion of the adjustment knob.

It is in the closed state when the product is shipped from the factory.

In addition, do not apply excessive force to the adjustment knob even when the lock nut is in a tightened state. Operate the adjustment knob when the lock nut is in a loosened state.

SMC



Compact Type High Purity Air Operated Chemical Liquid Valve Precautions 3

Be sure to read this before handling the products.

Use of Tubing

▲Caution

1. Refer to the applicable tubing sizes shown below for tubing to be used.

Applicable Tubing Sizes

	Connection	O.D. [n	nm]	Internal thick	ness [mm]	
	tubing size	Standard size Tolerance		Standard size	Tolerance	
	ø3 x ø2	3.0		0.5	±0.06	
	ø4 x ø3	4.0		0.5	10.00	
	ø6 x ø4	6.0	+0.2	1.0	±0.1	
Metric	ø8 x ø6	8.0	-0.1			
size	ø10 x ø8	10.0			10.1	
	ø12 x ø10	12.0				
	ø19 x ø16	19.0	+0.3	1.5	±0.15	
	ø25 x ø22	25.0	-0.1	1.5	±0.15	
	1/8" x 0.086"	3.18		0.5	10.4	
	3/16" x 1/8"	4.75		0.8	±0.1	
	1/4" x 5/32"	6.35	+0.2 -0.1	1.2	±0.12	
Inch size	3/8" x 1/4"	9.53	-0.1			
3120	1/2" x 3/8"	12.7			10.45	
	3/4" x 5/8"	19.0	+0.3	1.6	±0.15	
	1" x 7/8"	25.4	-0.1			

Return of Product

Warning

If the product to be returned is contaminated or is possibly contaminated with substances that are harmful to humans, for safety reasons, please contact SMC beforehand and then employ a specialist cleaning company to decontaminate the product. After the decontamination prescribed above has been carried out, submit a Product Return Request Sheet or the Detoxification/Decontamination Certificate to SMC and await SMC's approval and further instructions before attempting to return the item.

Please refer to the International Chemical Safety Cards (ICSC) for a list of harmful substances.

If you have any further questions, please don't hesitate to contact your SMC sales representative.

LVC
LVA
LVH
LVD
LVQ
LVP
LVW
LQ1
LQ3
LVN
LQHB
tl Til
TLM Tilm
TD TID
TIL TLM TILM TD TID TH TH