Vacuum System Peripherals

| Vacuum Regulator/Electronic Vacuum Regulator |
|---|
| Vacuum regulator: IRV10/20 P.867 Electronic vacuum regulator: ITV009□/ITV209□ P.867 |
| Directional Control Valve |
| Selection guide of directional control valve (Ejector system/Vacuum pump system) P.868 V100, SYJ, VQZ, VK, VX2, VX3 P.870 VT/VP, VG342, VNB, VEX3 P.871 VQD, VQD1000-V, SJ3A6, SY3A□R, SY5A□R, SY5A2R P.872 |
| Vacuum Pressure Switch |
| ZSE20(F), ZSE20A(F), ZSE20B(F), ZSE10(F), ZSE20C(F) PS1100/1200, PSE200A/300A/530/540, PF2M7, PFMV |
| Pressure Gauge for Vacuum |
| Pressure gauge for vacuum: GZ46/GZ46E P.874 |
| Flow Control Equipment |
| Speed controller: AS-X214 P.876 Check valve: AK P.876 Check valve with One-touch fitting: AKH P.876 Check valve, Bushing type: AKB P.876 |
| |
| Made to Order |



Vacuum System Peripherals: RoHS Vacuum Regulator/Electronic Vacuum Regulator

Vacuum Regulator

| Series | Model | Set pressure range | Port size | Catalog |
|------------|-------|--------------------|-------------------------------------|-------------|
| IRV series | IRV10 | | ø6, ø8 ø1/4", ø5/16" | |
| | IRV20 | –100 to –1.3 kPa | ø6, ø8, ø10 ø1/4", ø5/16", ø3/8" | Web Catalog |

Electronic Vacuum Regulator

Stepless control of vacuum pressure proportional to an electrical signal

| Series | Model | Set pressure range | Input signal | Port size | Catalog |
|----------------|---------|--------------------|---|---|-------------|
| ITV009□ series | ITV009□ | -1 to -100 kPa | Current type: 4 to 20 mA DC (Sink type) Current type: 0 to 20 mA DC (Sink type) Voltage type: 0 to 5 VDC Voltage type: 0 to 10 VDC | Built-in One-touch fittings Metric size: ø4 Inch size: ø5/32 | Web Catalog |
| ITV209□ series | ITV209□ | −1.3 to −80 kPa | Current type: 4 to 20 mA DC (Sink type) Current type: 0 to 20 mA DC (Sink type) Voltage type: 0 to 5 VDC Voltage type: 0 to 10 VDC Preset input: (4 points/16 points) 10 bit digital input CC-Link DeviceNet* PROFIBUS DP RS-232C communication | 1/4 | Web Catalog |

Vacuum System Peripherals: Directional Control Valve

| | | | | | | | | i |
|---|--------------------|-----------------|--------------------|---------------------|-----------------|--------------------|---------------------|---|
| A guide for selecting the solenoid valve model to accommodate the system | System | | E | jector | Syste | m | | |
| An array of solenoid valves (2/3 port valve) for controlling the ejector/external vacuum supply system | | Vacuu | m releas | e valve | Sı | upply val | ve | |
| How to read the chart | | | | Ŧ | | | | |
| The solenoid valves are available in the following constructions: the standard product (for general use), the external pilot specification, and the | Circuit | | | | 1(P | | _ | |
| vacuum specification. Select the optimal model in accordance with your circuit configuration and the effective area. For detailed specifications of | construction |] : | 1(P) H 3(R) X | ≠ (A) | 3(R) | 2(A) | <u> </u> | |
| these products, refer to the respective catalog that is available separately. | | (Bla | inking) | `` <u>`</u> | | Euternal | ` | |
| Solenoid valve | Valve construction | Standard | pilot spec. (R) | Vacuum spec. (V) | Standard | pilot spec. (R) | Vacuum spec. (V) | |
| Compact 3 port solenoid valve V100, SYJ | V100 | • | - | - | • | - | - | |
| Compact 3 port solenoid valve V100, SYJ Compact size: 10 mm (V100, SYJ300) 18 mm (SYJ500) 18 mm (SYJ500) Low power consumption: 0.1 W | SYJ300/500/700 | - | • | - | - | • | - | |
| 3 port solenoid valve VQZ 10 mm: VQZ100 15 mm: VQZ200 | VQZ100/ 200/300 | - | • | - | - | • | - | |
| 18 mm: VQZ300 | | | | | | | | |
| 3 port solenoid valve VK | | • | - | • | • | - | - | |
| Direct operated 2 port solenoid valve VX2 | | • | - | • | • | - | - | |
| Direct operated 3 port solenoid valve VX31/32/33 | | • | - | • | • | - | _ | |
| 3 port solenoid valve VT VT307/317/325 | | • | - | • | • | - | - | |
| 3 port solenoid valve VP VP300/500/700 | | - | • | - | - | • | - | |
| 3 port solenoid valve VG342 | | - | • | - | - | • | - | |
| Vacuum pilot 2 port valve VNB□□□V | | _ | • | • | - | • | • | |
| 3 position valve VEX3 | | - | • | • | - | • | • | |
| 3/4 port solenoid valve VQD | VQD1000 | - | - | - | • | - | - | |
| VQD1000/VQD100 | VQD100 | - | - | • | • | - | • | |
| Vacuum/release unit VQD1000-V | | _ | - | - | - | - | - | |
| Vacuum release valve with throttle valve SJ3A6 | | - | • | - | - | • | - | |
| Vacuum release valve with restrictor SY3A□R/SY5A□R | Co-ososo Co | _ | • | - | - | • | - | |
| Vacuum release valve with restrictor/Body ported SY5A2R | | (Made to Order) | _ | _ | (Made to Order) | - | - | |
| 919AZR | | (Made to Order) | | | (Made to Order) | | | |

Directional Control Valve/Vacuum System Peripherals

Caution on Model Selection Vacuum Pump System Vacuum switching valve | Divider valve of vacuum supply air • Use a plug cap at R port of 2 port valve and 3 port valve for vacuum release valve and vacuum switching valve. (Except VEX3) 1) Applications are different from vacuum holding valve. 2) Refer to the Web Catalog for flow rate characteristics. 3(R) x (Blanking) External pilot spec. (R) Standard External pilot spec. (R) Standard Port size Catalog M3 x 0.5 Web M5 x 0.8 Catalog 1/8,1/4 M5 x 0.8 Web 1/8, 1/4 Catalog Web M5 x 0.8 1/8 Catalog Web 1/8 to 3/8 Catalog Web 1/8 to 3/8 Catalog Web 1/8 to 3/8 Catalog Web 1/8 to 1/2 Catalog 1/2 to 3/4 Web Catalog 1 Web 3/8 to 2 Catalog Web 1/8 to 1/2 Catalog Web M5 x 0.8 Catalog Web M5 x 0.8 Catalog Web M5 x 0.8 Catalog Web ø6, ø8 Catalog Web

(Made to Order

(Made to Order

ø6, ø8

Catalog

Vacuum System Peripherals: Directional Control Valve/Solenoid Valve

Compact 3 Port Solenoid Valve V100, SYJ



Possible to use with vacuum up to at -100 kPa Compact size: Width 10 mm (V100, SYJ300) Width 15 mm (SYJ500) Width 18 mm (SYJ700)

Low power consumption 0.1W (With energy saving circuit)

Body ported Base mounted

Refer to the Web Catalog for details.

| woaei | | |
|-----------------------|----------------|-----------|
| Piping specifications | Solenoid valve | Port size |
| | SYJ312/322 | M3 x 0.5 |
| Pody ported | SYJ512/522 | M5 x 0.8 |
| Body ported | SYJ712/722 | 1/8 |
| | V114UT | M5 x 0.8 |
| | V114/124 (A) | M5 x 0.8 |
| Base mounted | SYJ314/324 | M5 x 0.8 |
| (With sub-plate) | SYJ514/524 | 1/8 |
| | SYJ714/724 | 1/8, 1/4 |

3 Port Solenoid Valve VK





Compact size: Width 18 mm Possible to use with vacuum

Body ported Base mounted

Refer to the Web Catalog for details.

| l. | Model | | |
|----|-----------------------|---------------------|-----------|
| П | Piping specifications | Solenoid valve | Port size |
| П | Body ported | VK332 | M5 x 0.8 |
| П | body ported | For vacuum:VK332V * | M5 x 0.8 |
| П | Base mounted | VK334 | 1/8 |
| П | (With sub-plate) | For vacuum:VK334V * | 1/8 |

^{*} Vacuum specification: Operating pressure range –101.2 kPa to 0.1 MPa * Low wattage type (2 W DC) and long period energized type available.

3 Port Solenoid Valve VQZ100/200/300



Refer to the Web Catalog for details.

Model/Metal Seal, Rubber Seal

| Piping specifications | Solen | oid valve | Port size |
|----------------------------------|--------|-----------|-----------|
| | VQZ100 | VQZ115 | 1/8 |
| | | VQZ215 | |
| | VQZ | VQZ235 | 1/8, 1/4 |
| Base mounted (With sub-plate) | 200 | VQZ225 | 78, 74 |
| | | VQZ245 | |
| | | VQZ315 | |
| | VQZ | VQZ335 | 1/4, 3/8 |
| | 300 | VQZ325 | 74, 98 |
| | | VQZ345 | |

Compact 2 Port Solenoid Valve VX2 Series For Medium Vacuum





Refer to the Web Catalog for details.

Model

| Size | Port size | Orifice dia. (mm ø) | Model |
|------|------------|---------------------|-----------|
| | | 2 | |
| 1 | 1/8, 1/4 | 3 | VX214 |
| | | 5 | |
| 2 | 2 1/4, 3/8 | 4 | VX224 |
| 2 | | 7 | V A Z Z 4 |
| | | 5 | |
| 3 | 1/4,3/8 | 8 | VX234 |
| ³ | 10 | V A 2 3 4 | |
| | 1/2 | 10 | |

Compact 3 Port Solenoid Valve VX3 Series Options V & M For Medium Vacuum, Non Leakage



Refer to the Web Catalog for details.

Model

| Size | Port size | Orifice dia. (mm ø) | Model |
|------|-----------|---------------------|---------|
| | | 1.5 | |
| 1 | 1/8, 1/4 | 2.2 | VX31□□∜ |
| | | 3 | |
| | | 2.2 | |
| 2 | 1/4, 3/8 | 3 | VX32□□₩ |
| | | 4 | |
| | | 2.2 | |
| 3 | 1/4, 3/8 | 3 | VX33□□₩ |
| | | 1 | |

For Vacuum Pad

| Model | Port size | Orifice dia. (ø) | |
|----------|-----------|------------------|-------------|
| Iviouei | Rc | Pressurised side | Vacuum side |
| VXV313 □ | 1/8, 1/4 | 1.5 | 3 |
| VXV324□ | 1/. 3/- | 2.2 | 4 |
| VXV334□ | 1/4, 3/8 | 2.2 | 4 |

Directional Control Valve/Solenoid Valve/Vacuum System Peripherals

3 Port Solenoid Valve VT, VP







Refer to the Web Catalog for details.

Model/Rubber Seal

| Piping specifications | Solenoid valve | Port size |
|-----------------------|----------------|---------------|
| | VT325(V) | 1/4, 3/8 |
| Body ported | VT307(V)* | 1/8, 1/4 |
| | VT317(V)** | 1/4 |
| | VP342 | 1/8, 1/4 |
| Body ported | VP542 | 1/4, 3/8 |
| | VP742 | 3/8, 1/2 |
| | VP344 | 1/8, 1/4 |
| Base mounted | VP544 | 1/4, 3/8 |
| | VP744 | 3/8, 1/2 |
| | VP3145 | 3/8, 1/2, 3/4 |
| Body ported | VP3165 | 3/4, 1, 11/4 |
| | VP3185 | 11/4, 11/2, 2 |

- Low wattage (2 W DC) type and long period energized type available.

** Long period energized type available.

V: Vacuum specification: Operating pressure range –101.2 kPa to 0.1 MPa

3 Port Solenoid Valve VG342



Model/Rubber Seal

| Piping specifications | Solenoid valve | Port size |
|-----------------------|----------------------|------------|
| | VG342 | 1/2 to 3/4 |
| Dadi. aadad | VG342 | 1 |
| Body ported | For Vacuum: VG342R * | 1/2 to 3/4 |
| | ror vacuum: vus42n | 1 |

* Operating pressure range: -101.2 kPa to 0.9 MPa

Refer to the Web Catalog for details.

Vacuum Pilot 2 Port Valve **VNB**

It is used when the valve is to be operated by the main vacuum in the absence of pressurized air.

Refer to the Web Catalog for details.







Specifications (Vacuum pilot)

| Fluid | Vacuum | | |
|--------------------------|---|--|--|
| Operating pressure range | Vacuum -101 kPa to atmospheric pressure -101 to -47.9 kPa | | |
| Pilot pressure range | -101 to -47.9 kPa | | |

Model

| Model | Port size Screw-in | Orifice dia ø [mm] |
|---------------|-----------------------|-----------------------|
| VNB2□4□□□-10A | 3/8 | 11 |
| VNB2 | 9/8 | 15 |
| VNB2□4□□□-15A | 1/2 | 11 |
| VNB2□□□□□-15A | 72 | 15 |
| VNB3□4□□□-20A | 3/4 | 14 |
| VNB3□□□□□-20A | 74 | 20 |

| Model | Port | size | Orifice dia | |
|---------------|----------|--------|-------------|--|
| Wodei | Screw-in | Flange | ø [mm] | |
| VNB4□4□□□-25A | -1 | _ | 16 | |
| VNB4□□□□-25A | ' | | 25 | |
| VNB5□4□□□-32A | 11/4 | _ | 22 | |
| VNB5□□□□□-32A | . , , , | | 32 | |
| VNB5□4□□□-32F | | 32 | 22 | |
| VNB5□□□□□-32F | _ | 32 | 32 | |
| VNB6□4□□-40A | 11/2 | _ | 28 | |
| VNB6□□□□-40A | 1 / 2 | | 40 | |
| VNB6□4□□□-40F | _ | 40 | 28 | |
| VNB60000-40F | _ | 40 | 40 | |
| VNB7□4□□□-50A | 2 | | 33 | |
| VNB70000-50A | - | | 50 | |
| VNB7□4□□□-50F | | 50 | 33 | |
| VNB70000-50F | _ | 30 | 50 | |

3 Position Valve VEX3

Refer to the Web Catalog for details.




Vacuum suction and release

The 3 port, 3 position double solenoid that permits vacuum suction, release, and suspension (closed) is ideal for a system where many valves are used for a single circuit.

Model

| Мо | Port size | | | |
|--------------------|------------|-----|--|--|
| | VEX312□-01 | 1/8 | | |
| | VEX312□-02 | 1/4 | | |
| Pody ported | VEX332□-02 | 1/4 | | |
| Body ported | VEX332□-03 | 3/8 | | |
| | VEX332□-04 | 1/2 | | |
| | VEX350□-04 | 1/2 | | |
| | VEX322□-01 | 1/8 | | |
| Base mounted | VEX322□-02 | 1/4 | | |
| (With sub-plate) | VEX342□-02 | 1/4 | | |
| (vviiii sub-piate) | VEX342□-03 | 3/8 | | |
| | VEX342□-04 | 1/2 | | |

| Mo | Port size | |
|-------------|------------|------|
| | VEX350□-06 | 3/4 |
| Body ported | VEX350□-10 | 1 |
| | VEX370□-10 | 1 |
| | VEX370□-12 | 11/4 |
| | VEX390□-14 | 11/2 |
| | VEX390□-20 | 2 |



· Sequential switching operation prevents the inflow of pressurized air into the vacuum pump system.

△ Caution

• To maintain the vacuum of port A via the closed center, be aware that the vacuum could be decreased due to leakage from the vacuum pad and the piping. Furthermore, it cannot be used as an emergency cutoff valve.

Directional Control Valve/Solenoid Valve/Vacuum System Peripherals

3/4 Port Solenoid Valve VQD

Unprecedented high speed. with stable response times (ON: 4 ms, OFF: 2 ms. Dispersion accuracy ±1 ms) Available in vacuum applications (Up to -101.2 kPa)



VQD115

Base mounted

Body ported

Model Refer to the Web Catalog for details Piping specifications Solenoid valve Port size Body ported VQD1121 VQD1000 VQD1151 Base mounted M5 x 0.8 VQD1251 (With sub-plate)

Vacuum/Release Unit VQD1000-V

- Response speed
- 13 ms (at 500 mm*)/
- 18.5 ms (at 1000 mm*) * Distance from a unit to a workpiece
- (Piping I.D. ø2.5) Smooth removal of workpiece

without overshoot No blow off of workpiece by release air

 No need to adjust the timing for switch-over vacuum and positive pressure.

(Single signal control)

No need to set a restriction circuit for release air

Refer to the Web Catalog for details.

Vacuum Release Valve with Throttle Valve SJ3A6

2 spool valves included.

Possible to control vacuum adsorption and release by a valve.

- · Current consumption 0.15 W (With energy saving circuit)
- Width 10 mm

(Same as SJ3000 Series)

- With throttle valve that can control the flow rate of release air
- Replaceable filters are built in the vacuum side and release side respectively
- With a pressure detection port that enables users to connect a pressure switch, etc.
- Can be mounted with a 4 port solenoid valve SJ2000/3000 (Made to Order). (Please contact SMC for details.)
- Possible to switch pressure of two wiring systems by applying different positive pressures to 1 (P) port and 3/5 (E). (In this case, flow rate is adjustable only at the P port side.)



Refer to the Web Catalog for details

Vacuum Release Valve with Restrictor SY3A B/SY5A B

Vacuum suction and release can be controlled with a single valve!

 Can be mounted on the same manifold with the standard valve. *: When the individual EXH spacer is used.





Connector connecting base

Metal base

Refer to the Web Catalog for details.

Body Ported Vacuum Release Valve with Restrictor Made to Order SY5A2R

- Line for vacuum adsorption transfer
- Built-in restrictor in the vacuum release valve
- Single unit

External pilot type dual 2 port solenoid valve

Manifold

SS5Y5-20-type (Individual wiring type), SS5Y5-20P-type (Flat ribbon cable type) Manifold





VQD100 Operating pressure range: 0 to 0.7 MPa for standard products, -101.2 kPa to 0.7 MPa for vacuum specification

Vacuum System Peripherals: Vacuum Pressure Switch

Refer to the Web Catalog for details.

3-Screen Display High-Precision Digital Pressure Switch ZSE20(F)



3-Screen Display
High-Precision Digital Pressure Switch For General Fluids
ZSE20C(F)



Pressure Sensor PSE530



3-Screen Display
High-Precision Digital Pressure Switch
ZSE20A(F)



Air Checker Electronic Pressure Switch PS1100/1200



Compact Pneumatic Pressure Sensor **PSE540**



3-Screen Display
High-Precision Digital Pressure Switch
ZSE20B(F)



3-Screen Display Multi-channel Digital Sensor Monitor PSE200A



2-Color Indicator
Digital Flow Switch PF2M7



Compact Digital Pressure Switch ZSE10(F)



3-Screen Display Sensor Monitor PSE300A



Flow Sensor PFMV





Vacuum System Peripherals: Pressure Gauge for Vacuum: GZ46/GZ46E Series





Standard Specifications

| Model | | GZ46 | GZ46E | |
|-----------------------------|---------------------------------|--|--|--|
| Туре | | Back side thread | | |
| Port size (1) | | R 1/8, R 1/4 (Option: | M = M5 x with thread) | |
| Fluid (2) (5) | | Д | ir | |
| Indication precision (6) | | ±3 | 3% | |
| Fluid contact part cleaning | | I | Wetted parts degrease washing | |
| | Case (Surface treatment) | Rolled steel (Black melamine painted) | | |
| Material (4) | Clear cover (Surface treatment) | Polycarbonate Part no.: G46-00-00-3 | Polycarbonate (Hard coated) Part no.: G46-00-00-2 | |
| | Stud (Surface treatment) | Brass | Brass (Electroless nickel plated) (3) | |
| | Bourdon tube | Brass | | |
| Weight [kg] | | 0.078 | 0.08 | |
| Attachment: With cover | С | Part no.: 1305104-1A | | |
| ring assembly | C1 | Part no.: 1305104-3A | | |

Note 1) When mounting a pressure gauge, use caution not to tighten excessively. Excessive tightening will cause product failure. Use a pipe tape for sealing. Recommended tightening torque: R 1/8: Set between 7 to 9 N·m, R1/4: 12 to 14 N·m respectively Note 2) When using other fluids, please consult with SMC for fluid compatibility information concerning

corrosive potential. Note 3) Movable parts (gear and etc.) in the pressure gauge are made of brass

Note 4) X3 (wetted parts stainless steel) specifications are not available

Note 5) Avoid freezing as this may cause a malfunction. Note 6) The guaranteed temperature range is 23°C ±5°C.

⚠ Specific Product Precautions

Be sure to read this before han-I dling the products. Refer to page I I 33 for safety instructions.

Selection

⚠ Caution

- 1. Make sure that no direct impact or vibrations are applied to the body.
- 2. If operating under pressure pulsations or in high frequency operations, please contact SMC.

Mounting

∕ Caution

- 1. During transport and installation, do not apply shock to the product, such as by dropping doing so will affect its precision.
- 2. Regarding the installation posture, place it perpendicular to the ground, with the zero point on the reading of a pressure gauge facing down.
- 3. Do not install it in an area that is exposed to high temperature or humidity, because doing so will lead to improper operation.
- 4. To screw in the pressure gauge, make sure to turn the gauge by placing a wrench over the square wrench flats.

If the pressure gauge is screwed in by holding it on some other area, air leakage or damage may result.

Model (Standard)

| Model | Pressure range (1) kPa | Indica- tion unit | Connection thread | Note |
|-----------------------|---------------------------|-------------------------|-------------------------------|--------------------------|
| GZ46-K-01 to 02 | -100 to 0 | kPa | R 1/8,1/4 | _ |
| GZ46-K-01 to 02-C, C1 | -100 to 0 | kPa | R 1/8, 1/4 | With cover ring assembly |
| GZ46-K-01 to 02M | -100 to 0 | kPa | R 1/8, 1/4 M5 (Female thread) | _ |
| GZ46E-K-01 to 02M | -100 to 0 | kPa | R 1/8, 1/4 M5 (Female thread) | _ |
| GZ46-K2K-01 to 02 | -100 to 200 | kPa | R 1/8,1/4 | _ |
| GZ46-K2K-01 to 02 | -100 to 200 | kPa | R 1/8, 1/4 | |

Note 1) Do not apply more excessive pressure than max. pressure display. It will be a cause of malfunction.


Please consult with SMC for models other than shown below, Model (Made to Order)

| mean (maae te e | ac donvery amountary to extended. | | | | | |
|-------------------|-----------------------------------|---|-----------|------|--|--|
| Model | Pressure range (1) | sure range (1) Indication Connection thread | | Note | | |
| Model | kPa | | | Note | | |
| GZ46-K1K-01 to 02 | -100 to 100 | kPa | R 1/8,1/4 | _ | | |

Note 1) Do not apply more excessive pressure than max. pressure display. It will be a cause of malfunction.

Pressure Gauge for Vacuum/Vacuum System Peripherals

How to Order




Pressure unit for vacuum (kPa

| | | • Press | ure unit f | or vacuum (kPa | |
|---------------------------------------|--------|--------------------------------|----------------|--------------------------------------|--|
| | | | | 0 | |
| | Symbol | Description | Specifications | | |
| | Symbol | Description | GZ46 | GZ46E | |
| | | | _ | Oil-free, external parts copper-free | |
| | + | | | | |
| 2 Pressure unit for positive pressure | Nil | _ | • | • | |
| Pressure unit for positive pressure | K | kPa | • | • | |
| | + | | | | |
| _ | Nil | -100 to 0 kPa | • | • | |
| 3 Display pressure range | 1 | -100 to 100 kPa | • | • | |
| | 2 | -100 to 200 kPa | • | • | |
| + | | | | • | |
| Connection thread | 01 | R 1/8 | • | • | |
| Connection thread | 02 | R 1/4 | • | • | |
| | + | | | | |
| Option | Nil | _ | • | • | |
| Орион | M (1) | With M5 (Female thread) | • | • | |
| | + | | | | |
| | Nil | Without cover ring assembly | • | • | |
| | С | Clear cover has no protrusion. | | | |
| 6 Attachment Note 2) | | (Clear cover is irremovable.) | | • | |
| | C1 | Clear cover has protrusion. | | | |
| | CI | (Clear cover is removable.) | • | • | |


Note 1) To use the pressure gauge with M5 (female thread), attach the joint when piping the tube.

Note 2) For pressure gauges with the cover ring assembly, it is recommended to select the option M so as to perform the piping.


Dimensions



With cover ring assembly (For panel mounting) GZ46-□□-01 to 02 (M)-C GZ46E-□□-01 to 02 (M)-C




| Model | Α | D |
|-------------------|------|-------|
| GZ46-□□-01 (M)-C | 41.5 | R 1/8 |
| GZ46-□□-02 (M)-C | 45.5 | R 1/4 |
| GZ46E-□□-01 (M)-C | 41.5 | R 1/8 |
| GZ46F-□□-02 (M)-C | 45.5 | R 1/4 |



How to mount the cover ring assembly

- Remove the small screw (1 position) from the pressure gauge.
 Place the cover ring on the pressure gauge.
- Prace the cover ring on the pressure gauge.
 Using the small screw that is provided with the cover ring, install the cover ring. The installation torque is 0.6 to 0.7 N·m.
- For reinstallation, the tightening torque is 0.5 to 0.6 N·m.



GZ46-□□-01 to 02 (M)-C1

| Model | Α | =E | D |
|--------------------|------|----|-------|
| GZ46-□□-01 (M)-C1 | 41.5 | 6 | R 1/8 |
| GZ46-□□-02 (M)-C1 | 45.5 | 6 | R 1/4 |
| GZ46E-□□-01 (M)-C1 | 40.5 | 5 | R 1/8 |
| G746F 02 (M)-C1 | 44.5 | 5 | R 1/4 |





Vacuum System Peripherals: Flow Contorol Equipment

Refer to the Web Catalog for details.

Speed Controller: AS-X214


Possible to control vacuum release air

With One-touch fitting

The tubing can be removed and installed through One-touch operation.

The body can be screwed in directly to the equipment that you are using.

As a result, the piping labor can be dramatically reduced.



^{*}Flow rate: Same as controlled flow of the standard product.


Check Valve: AK

Large valve capacity Low cracking pressure/0.02 MPa



| Model | Port size Rc |
|--------|-----------------|
| AK2000 | 1/8, 1/4 |
| AK4000 | 1/4, 3/8, 1/2 |
| AK6000 | 3/4, 1 |

Check Valve with One-touch Fitting: AKH Straight type





Metric size

| Мо | del | Applicable tubing O.D. |
|-----|-------|------------------------|
| | 04-00 | ø4 |
| | 06-00 | ø6 |
| AKH | 08-00 | ø8 |
| | 10-00 | ø10 |
| | 12-00 | ø12 |

Inch size

| Мо | del | Applicable tubing O.D. 5/32 1/4 | |
|-----|-------|---------------------------------|--|
| | 03-00 | 5/32 | |
| | 07-00 | 1/4 | |
| AKH | 09-00 | 5/16 | |
| | 11-00 | 3/8 | |
| | 13-00 | 1/2 | |

Check Valve with One-touch Fitting: **AKH** Male connector type





Metric size

| Model | | Applicable | Port size R | | | | | | |
|-------|-----|-------------|-------------|-----|-----|-----|-----|--|--|
| IVIO | uei | tubing O.D. | M5 | 1/8 | 1/4 | 3/8 | 1/2 | | |
| | 04□ | ø4 | • | • | | | | | |
| | 06□ | ø6 | • | • | • | | | | |
| AKH | 08□ | ø8 | | • | • | • | Г | | |
| | 10□ | ø10 | | | • | • | • | | |
| | 12□ | ø12 | | | | • | • | | |
| | | | | | | | | | |

Inch size

| Model | | Applicable tubing O.D. | | Port size NPT | | | | | |
|-------|-----|------------------------|---|---------------|-----|-----|-----|--|--|
| | | | | 1/8 | 1/4 | 3/8 | 1/2 | | |
| | 03□ | ø5/32 | • | • | | | | | |
| | 07□ | ø1/4 | • | | • | | | | |
| AKH | 09□ | ø5/16 | | • | • | • | | | |
| | 11□ | ø3/8 | | | • | • | • | | |
| | 13□ | ø1/2 | | | | • | • | | |

Check Valve: AKB Bushing type

Can be used in applications with splashing coolant and spatter, etc.



R thread

| Model | | Female | Male thread R | | | | | |
|-------|-----|-----------|---------------|---|-----|---|--|--|
| IVIO | uei | thread Rc | 1/8 1/4 3/8 | | 1/2 | | | |
| AKB | 01□ | 1/8 | • | | | | | |
| | 02□ | 1/4 | | • | | | | |
| | 03□ | 3/8 | | | • | | | |
| | 04□ | 1/2 | | | | • | | |

NPT thread

| Model | | Female_ | Male thread NPT | | | | | |
|-------|-----|------------|-----------------|-----|-----|-----|--|--|
| | | thread NPT | 1/8 | 1/4 | 3/8 | 1/2 | | |
| AKB | 01□ | 1/8 | • | | | | | |
| | 02□ | 1/4 | | | | | | |
| | 03□ | 3/8 | | | • | | | |
| | 04□ | 1/2 | | | | • | | |

Vacuum System Peripherals: Made to Order



1 Vacuum Release Valve with Restrictor: SY5A2R

- · Line for vacuum adsorption transfer
- Built-in restrictor in the vacuum release valve
- Can be mounted on the SS5Y5-20-type (Individual wiring type) and SS5Y5-20P-type (Flat ribbon cable type) Manifold
- Valve effective area

| B port Port size Note 1) | Effective area: mm² | | | | |
|-----------------------------|---------------------|------|--|--|--|
| Port size Note 1) | EA→B Note 2) | B→EB | | | |
| C6 | 4.4 | 6.8 | | | |
| C8 | 4.5 | 7.0 | | | |

Note 1) Refer to the part numbers for the port size. Note 2) When the built-in restrictor is fully open.

| Symbol | | В | | |
|--------|--------|-------|----------|-------|
| SOL.a | EA (P) | √ | EB (Vac. | SOL.b |

Specifications

| Valve type | | External pilot type, 3 position 3 port valve | |
|-----------------------------|--|---|--|
| Type of actuation | | Normally closed | |
| Fluid | | Air | |
| | P (External pilot pressure) | 0.15 to 0.7 MPa | |
| Operating pressure range | 3 position 3 port valve Normally closed Air P (External pilot pressure) A (Vacuum release pressure) B (Vacuum) -100 kPa to 0 MPa ust method Pilot valve individual exhau | 0 to 0.7 MPa | |
| procoure range | | | |
| Pilot valve exh | naust method | Pilot valve individual exhaust | |
| Ambient and f | luid temperature | -10 to 50°C (No condensation) | |


Effective Area/Weight

| B port Port size Note 1) | Effective a | Weight (g) | | |
|-----------------------------|--------------|------------|-------------|--|
| | EA→B Note 2) | B→EB | vveigni (g) | |
| C6 | 4.4 | 6.8 | 94 | |
| C8 | 4.5 | 7.0 | 88 | |

Note 1) Refer to the part numbers for the port size. Note 2) When the built-in restrictor is fully open.


How to Order

Single unit: External pilot type 3 position 3 port valve



Manifold: Body ported bar stock (20/20P type)

* Specify the part numbers for valves and options together beneath the manifold base part number in order starting from the first station.




Note 4) Refer to the SY5000 series catalog. Note 5) 20P (Flat ribbon cable type): Max. 12 stations



Made to Order/Vacuum System Peripherals

1 Vacuum Release Valve with Restrictor/SY5A2R

Dimensions/Single Unit: SY5A2R



[Remarks for valves]




Note 1) Refer to the SY series in the **Web Catalog** for the details of electrical entry and electrical circuit with a light/surge voltage suppressor. Note 2) Diagrams above are compatible with SY5A2R=LLCIDCDCI_(F2). Note 3) When mounted with brackets, the product is mounted in a place specified with one dot chain lines.

Note 4) Applicable pilot valves are V111/V115-□□□.

Made to Order/Vacuum System Peripherals


Dimensions/Manitold: SS5Y5-20P-Stations - □ □ - □



|--|

| L: Dir | .: Dimensions: mm n: Stations | | | | | | | | | | | |
|---------------|-------------------------------|------|-----|-------|-----|-------|-----|-------|-----|-------|--|--|
| $\overline{}$ | 3 | 4 | 5 | 6 | 7 | 8 | 9 | 10 | 11 | 12 | | |
| Lı | 77 | 94.5 | 112 | 129.5 | 147 | 164.5 | 182 | 199.5 | 217 | 234.5 | | |
| L2 | 67 | 84.5 | 102 | 119.5 | 137 | 154.5 | 172 | 189.5 | 207 | 224.5 | | |
| | 03 | 04 | 05 | 06 | 07 | 08 | 09 | 10 | 11 | 12 | | |

^{*} Applicable blanking plate assembly part no.: SS5Y5-20
SY5000-26-20A (with screws and gaskets) SS5Y5-20P-II: SY5000-26-21A (with screws, gaskets and dust cap) * The product cannot be mounted with standard products SY5000/500 series on a manifold.







SS5Y5-20□-□-□ Series Specific Product Precautions

Be sure to read this before handling the products. Refer to page 33 for safety instructions.

How to Use Manifold


<20/20P Type>

A piping port is different from that for the standard product. When not connected properly, the product will not operate properly.

[P port: External pilot port, EA port: Vacuum release pressure port, EB port: Vacuum suction port]

<20P Type>


- If a large amount of drainage is included in the supply air, it may cause electrical trouble since a wiring unit is located in the place where exhaust from the PE port directly goes through. Be sure to control the supply air.
- For more than 10 stations, both poles of the common should be wired.
- When replacing a solenoid valve, etc., be sure to mount it by placing the solenoid a side on the connector (MIL type) side.
- 4. Terminal no. is not indicated on the connector.
- 5. The terminal no. indicated in the connection schematic of connector, as shown in the reference, means a correlation of 1, 2, 3...26 from the triangle mark side on the flat ribbon cable of connector. (Refer to the reference drawing.)



Made to Order/Vacuum System Peripherals

2 Vacuum Release Valve with Throttle Valve: SV1A4R-X8

- · For vacuum adsorption transfer
- With a throttle valve that can control the flow rate of release air (Slotted type is used to ensure safety.)
- Possible to block release air and vacuum at the same time (3 position function)
- Compatible with manifold SV1000 series




Specifications

| Common specifications | | |
|-------------------------------|-----------------------------|---|
| Type of actuation | | Internal pilot type 3 position, 3 port solenoid valve |
| Valve type | | Normally closed (N.C.) |
| Fluid | | Air |
| Operating pressure range | P (Vacuum release pressure) | 0.15 to 0.7 MPa |
| | EB (Vacuum pressure) | -100 kPa to 0 MPa (Atmospheric pressure) |
| Ambient and fluid temperature | | −10 to 50°C |
| Allowable voltage fluctuation | | -10 to +10% |
| Electrical entry | | Plug-in type |
| Weight | | 73 g |
| | | |

Note) Specifications other than the above are the same as SV1000 series (Standard).


How to Order Refer to How to Order SV1000 Series (Standard).




Note) Please contact SMC when the product is mounted with a standard 5 port solenoid valve on a manifold.

Dimensions

Dimensions other than the throttle valve for vacuum release are the same as the standard product (SV1000).





Note) Use the manifold that the product is mounted on after mounting a plug to the A port.

♠ For safe operation, be sure to read the Safety Instructions on page 33 before handling.

