

variations							
	Applicable	Rated flow range	Flow	Port size			
Туре	fluid	[L/min]	None	Flow adjustment valve	Temperature sensor	Flow adjustment valve + Temperature sensor	Rc, NPT, G
p. 11) Integrated		0.5 to 4					3/8
Remote	Water	2 to 16					3/8, 1/2
Sensor	Ethylene glycol	5 to 40					1/2, 3/4
Monitor Monitor	aqueous	10 to 100		_		—	3/4, 1
p. 31	solution	50 to 250					1 ¹ /4, 1 ¹ /2
PVC piping type Integrated	Deionized water	10 to 100	•	_	_	_	25A
Sensor Difference Monitor	Chemical liquids	30 to 250		_	_	_	30A




3-Color Display Digital Flow Switch for Water **PF3W Series**



3-Color Display Digital Flow Switch for Water **PF3W** Series

New Compatible with the analog 2-output type (flow rate + temperature)

Enables the monitoring of flow rate and temperature conditions not only at the installation site but also remotely



3-color display Digital flow monitor: The set value can be copied **0** flow monitors simultaneously. to up to

Copy

The set values of the monitor can be copied.

 Reduced setting labor Minimized risk of setting mistakes




8 88 @ @ @ destination → 1 unit

Copy









SMC

3-Screen Display 4-Channel Flow Monitor PFG200 Series

Up to **4** flow sensors can be connected!





It is possible to change the settings while checking the measured value.


Main screen	Measured value (Current flow value)
Sub screen	Left side Right side Label (Display item), Set value (Threshold value)

Input Range Selection

Visualization of Settings




Visualization of Settings




SMC

Easy Screen Switching

It is possible to change the settings while checking the measured value.







Simple 3-Step Setting


After selecting the channel, when the SET button is pressed and the set value (P_1) is displayed, the set value (threshold value) can be set.

When the SET button is pressed and the hysteresis (H_1) is being displayed, the hysteresis value can be set.






Centralized Control Saves Installation Space.




Accumulated Flow Measurement

A single product can manage the accumulated flow in four lines.



Input Range Selection (for Pressure/Flow rate)



The sensor input range can be set to the required value and displayed. (Voltage input: 1 to 5 V) Pressure switch/Flow switch can be displayed.

A is displayed for 1 V. B is displayed for 5 V.

The range can be set as required.

Refer to page 36 for the specification of the sensors which can be connected. For the individual specifications of each connectable sensor, refer to the **Web Catalog**.


■ For Pressure Sensor for General Fluids / PSE56□

	Α	В
PSE560	0.000	1.000
PSE561	0	-101
PSE562	0	101
PSE563	-101	101

Set A and B to the values shown in the table.



Connection and removal of wiring is easy.



Functions

Peak/Bottom value indication function

This function constantly detects and updates the max. (min.) flow when the power is supplied, and allows to hold the max. (min.) flow value.

Key-lock function

This function prevents operation errors such as accidentally changing setting values.

External input function

The accumulated value, peak value, and bottom value can be reset remotely.

Error display function

This function displays error location and content when a problem or error has occurred.

Delay time setting

The time from when the instantaneous flow reaches the set value to when the switch output operates can be set.

Zero-cut setting

When the flow display value is close to zero, this function forces the display to zero.

Selection of power-saving mode

Power-saving mode can be selected. It shifts to power-saving mode automatically when there is no button operation for 30 seconds.

Setting of security code

Users can select whether a security code must be entered to release the key lock.

Accumulated value hold

The accumulated value is not cleared even when the power supply is turned OFF.

Snap shot function

The current flow rate value can be stored to the switch output $\ensuremath{\mathsf{ON/OFF}}$ set point.

Output check function It is possible to check the switch output oper-

ation and process data value.

Channel to channel copy function The set values can be copied to other channel.

Channel select function

Flow value for the selected channel is displayed.

Channel scan function

Flow values for each channel are displayed in turn every 2 seconds.


Hub Function Converts analog signals to digital signals Fieldbus and supports IO-Link A currently used sensor can be used. 0 PLC * Supports analog voltage output 1-5 V **O**IO-Link 0 0 Process data IO-Link Master @ SMC DOW Ø **Field setting and** confirmation of measured Analog voltage 1 to 5 V Analog voltage 1 to 5 V values are possible. Or IO-Link hub (Commercially available)

Process Data

D'1 (()	70	70		70	75	74	70	70	74	70			07		05	0.1	
Bit offset	79	78	77	76	75	74	73	72	71	70	69	68	67	66	65	64	1
Item	CH1 measured value: 16-bit signed integer									-							
Bit offset	63	62	61	60	59	58	57	56	55	54	53	52	51	50	49	48	Measurement data of
Item					(CH2 me	easure	d value	: 16-bit	signed	l intege	er					sensors for 4 channels are
Bit offset	47	46	45	44	43	42	41	40	39	38	37	36	35	34	33	32	combined and cyclically
ltem					(CH3 me	easure	d value	: 16-bit	signed	l intege	er					sent as a process data.
Bit offset	31	30	29	28	27	26	25	24	23	22	21	20	19	18	17	16	
Item					(CH4 me	easure	d value	: 16-bit	signed	l intege	er					
Bit offset	15	14	13	12	11	10	9	8	7	6	5	4	3	2	1	0	
Item	Error	System error	Fixed output	Reservation	CH4 diagnosis	CH3 diagnosis	CH2 diagnosis	CH1 diagnosis	CH4 OUT2	CH4 OUT1	CH3 OUT2	CH3 OUT1	CH2 OUT2	CH2 OUT1	CH1 OUT2	CH1 OUT1	Each channel has 2 outputs*1.
Diagnosis item · Internal product malfunction · Outside of zero-clear range Diagnosis item · Display upper and lower limits are exceeded. · The accumulated flow upper and lower limits are exceeded.																	
Impleme	nt dia	gnost	ic bits	in the	e proc	ess da	ata.										

*1 During SIO mode, only CH1 has 2 switch outputs. CH2-4 has one output each.





*1 In IO-Link mode, the IO-Link indicator will be ON or flashing.

SIO mode

OFF




Ma

General switch output

CONTENTS

3-Color Display Digital Flow Switch for Water *PF3W* Series **3-Color Display** Digital Flow Switch for PVC Piping *PF3W Series* **3-Color Display** Digital Flow Monitor for Water *PF3W3* Series 3-Screen Display 4-Channel Flow Monitor PFG200 Series














		ater
I Flow Switch for Water PF3W Series		3-Color Display Digital Flow Switch for Water PF3W
I Flow Switch for PVC Piping <i>PF3W</i> Series		v Swite
I Flow Monitor for Water <i>PF3W3</i> Series		ital Flov PF3W
nnel Flow Monitor <i>PFG200</i> Series		lay Dig
3-Color Display Digital Flow Switch for Water PF3W Series		r Disp
How to Order Specifications (Integrated Display)		Colo
Specifications (Remote Sensor Unit)	p. 13	\geq
Temperature Sensor Specifications		ipir
Set Flow Range and Rated Flow Range		1 2
Analog Output		ъ Б
Operating Pressure and Proof Pressure Available Flow Range		3-Color Display Digital Flow Switch for PVC Piping <i>PF3 W</i>
Flow Rate Characteristics (Pressure Loss: Without Flow Adjustment Valve)		> Swit
Straight Piping Length and Accuracy (Reference Value)		NΘ
Flow Rate Characteristics of Flow Adjustment Valve		E E
Measurable Range for Ethylene Glycol Aqueous Solution (Reference Value)		Digit
Wetted Parts Construction	p. 16	ay [
Internal Circuits and Wiring Examples		lisp
Dimensions	p. 19	or
Made to Order	- 00	ပို
EPDM seal material (-X109)		\geq
Analog 4 to 20 mA 2-output type (-X128) Brass piping material specification (-X143)		ater
IO-Link compatible (-X445)		Š
		play Digital Flow Monitor for Water PF3W3
3-Color Display Digital Flow Switch for PVC Piping PF3W Series		nito
How to Order		Mo
Specifications (Integrated Display)		V3 M
Analog Output		13 H
Operating Pressure and Proof Pressure		P
Specifications (Remote Sensor Unit)		⊇ 2
Flow Rate Characteristics (Pressure Loss) Straight Piping Length and Accuracy (Reference Value)		spla
Wetted Parts Construction		ä
Internal Circuits and Wiring Examples		3-Color Di
Dimensions		5
Made to Order	P	\geq
EPDM seal material (-X109)	p. 30	ito
	·	Jon
3-Color Display Digital Flow Monitor for Water PF3W3 Series		N N
How to Order		문
Specifications		lei
Temperature Sensor Specifications		/ 4-Chanr PFG200
Internal Circuits and Wiring Examples		Ϋ́Ϋ́Υ
Dimensions	-	P 4
	P. 0 .	3-Screen Display 4-Channel Flow Monitor PFG200
3-Screen Display 4-Channel Flow Monitor PFG200 Series		ā
How to Order	•	leel
Specifications		ŞCI
Applicable Flow Sensors	•	ſΫ
Internal Circuits and Wiring Examples		<u>د</u>
		Function Details
PF3W Series Function Details	n. 41	Det
Applicable Fluids		رت
Safety Instructions		
	10 🛽	
SMC .		

Details

3-Color Display Digital Flow Switch for Water PF3W Series (E HA GRAGUS (RoHS)

How to Order



When only optional parts are required, order with the part numbers listed below

1									
	Description	Part no.	Qty.	N	ote				
1		ZS-40-K	1	For PF3W704/720/504/520	With 4 tapping screws (3 x 8)				
	Bracket*1	ZS-40-L	1	For PF3W740/540	With 4 tapping screws (3 x 8)				
		ZS-40-M	1	For PF3W711/511	With 4 tapping screws (4 x 10)				
	Lead wire with M8 connector	ZS-40-A	1	Lead wire length: 3 m					

*1 For units with a flow adjustment valve, 2 brackets are required.

SMC



Α

rate

X128

X143

With calibration

certificate

The certificate is written in

both Japanese and English. The integrated display type

with a temperature sensor

can only display the flow

2-output type*1

specification

X445 IO-Link compatible*2

type with a temperature sensor

*1 Applicable only for the remote

*2 Integrated display type only

(Refer to page 22.)

Brass piping material

3-Color Display Digital Flow Switch for Water **PF3W Series**

For flow switch precautions and specific product precautions, refer to the "Operation Manual" on the SMC website.

Specifications (Integrated Display)

M	odel		PF3W704	PF3W720	PF3W740	PF3W711	PF3W721			
Applicable fluid				nd ethylene glycol aqueo						
Detection metho			water a	id ethylefie giycol aquet	Karman vortex		1 1655)			
Rated flow rang			0.5 to 4 L/min	2 to 16 L/min	5 to 40 L/min	10 to 100 L/min	50 to 250 L/min			
			0.35 to 5.50 L/min	1.7 to 22.0 L/min	3.5 to 55.0 L/min	7 to 140 L/min	20 to 350 L/min			
Display flow rar	ige			(Flow under 1.7 L/min is displayed as "0.0.")						
Set flow range			0.35 to 5.50 L/min	1.7 to 22.0 L/min	3.5 to 55.0 L/min	7 to 140 L/min	20 to 350 L/min			
Smallest settab	le increm	ent	0.01 L/min		_/min	1 L/min	2 L/min			
Conversion of accumulate			0.05 L/pulse							
Fluid temperatu	<u> </u>			0 to 90°C (No freezi			0 to 70°C (No freezing or condensation			
Display unit					us flow: L/min, Accumu	lated flow: L	<u> </u>			
Accuracy					e: ±3% F.S. Analog outp					
Repeatability					±2% F.S.*2					
Temperature ch	aracteris	tics		<u>+</u>	5% F.S. (25°C standard	(k				
Operating press	sure rang	e *3			0 to 1 MPa					
Proof pressure ³					1.5 MPa					
Pressure loss (without	t flow adjus	tment valve)		45 kPa or less a	at the max. flow		60 kPa or less at the max. flow			
Accumulated flo		*4		999.9 L		999999999 L				
Accumulated fig	ow range	. 4	By 0.1 L	By 0.5 L		By 1 L				
Switch output				NPN	or PNP open collector of	output				
	Max. loa	d current			80 mA					
		lied voltage	28 VDC							
		oltage drop	NPN: 1 V or less (at load current of 80 mA) PNP: 1.5 V or less (at load current of 80 mA)							
		se time*2, 5	0.5 s/1 s/2 s							
		protection			Short-circuit protection					
		Flow rate								
		Temperature	Select from Hysteresis mode or Window comparator mode.							
		se time*6								
Analog output	Voltage		Voltage output: 1 to 5 V Output impedance: 1 kΩ							
	Current	output	Output current: 4 to 20 mA Max. load impedance: 300 Ω for 12 VDC, 600 Ω for 24 VDC							
Hysteresis			Variable							
External input			Voltage free input: 0.4 V or less (reed or solid state), input for 30 ms or longer							
Display method			2-screen display (Main screen: 4-digit, 7-segment, 2-color, Red/Green Sub screen: 6-digit, 11-segment, White) Display values updated 5 times per second							
Indicator light	-		Output 1, Output 2: Orange							
Power supply ve Current consum	Intion		12 to 24 VDC ±10% 50 mA or less							
Current consul	Enclosu				IP65					
		nperature range		0 to 50°	C (No freezing or conde	insation)				
Environment		umidity range								
Linnonnent		d voltage*7	Operation, Storage: 35 to 85% R.H. (No condensation) 1000 VAC for 1 min between terminals and housing							
		n resistance	×							
Standards and					/UKCA marking, UL (CS		nouoing			
					ainless steel 304, FKM,					
Wetted parts ma	aterial*8				Non-grease					
Piping port size	*9		3/8	3/8, 1/2	1/2, 3/4	3/4, 1	1 1/4, 1 1/2			
Without temperature ser		adjustment valve	210 g	260 g	410 g	720 g	890 g			
			285 g	335 g	530 g	860 g	1075 g			
Without temperature se			310 g	360 g	610 g					
With temperature sense Without temperature sense With temperature sense			385 g	435 g	730 g	_	_			
With lead win					+85 g		1.			
			thylong Glycol Agugous	Solution" graph on page 1	•	alo as long as the fluid do	as not corrodo the wetter			

*1 Refer to the "Measurable Range for Ethylene Glycol Aqueous Solution" graph on page 16. Measurement is possible as long as the fluid does not corrode the wetted parts and the viscosity is 3 mPa s (3 cP) or less. Be aware that water leakage may occur due to internal seal shrinkage or swelling depending on the type of fluid. If 0.5 s is selected for the response time of the switch output, the repeatability will be $\pm 3\%$ F.S. *2

*3 *4

If 0.5 s is selected for the response time of the switch output, the repeatability will be ±3% F.S.
The operating pressure range, proof pressure, and available flow range vary depending on the fluid temperature. Refer to the graphs on page 14.
It is cleared when the power supply is turned OFF. The hold function can be selected. (Intervals of 2 or 5 mins can be selected.)
If the 5-min interval is selected, the life of the memory element (electronic part) is limited to 1 million times. (If energized for 24 hours, life is calculated as 5 mins x 1 million = 5 million mins = about 9.5 years.) Therefore, if using the hold function, calculate the memory life for your operating conditions, and use within this life. The response time when the set value is 90% in relation to the step input (The response time is 7 s when it is output by the temperature sensor.)
When the temperature sensor is used, it will be 250 VAC.

*6 *7

*8 For details, refer to the "Wetted Parts Construction" on page 16.

*9 When the piping diameter or piping passage is restricted, the specifications may not be satisfied.
 * Products with tiny scratches, marks, or display color or brightness variations which do not affect the performance of the product are verified as conforming products.

Temperature Sensor Specifications

Rated temperature range	0 to 100°C*1
Set/Display temperature range	-10 to 110°C
Smallest settable increment	1°C
Display unit	O°
Display accuracy	±2°C
Analog output accuracy	±3% F.S.
Response time	7 s*2
Ambient temperature characteristics	±5% F.S.

*1 The rated temperature range refers solely to that of the temperature sensor. The fluid temperature range specification of the flow switch as a whole is 0 to 90°C

*2 The response time refers solely to that of the temperature sensor.

The output related to the temperature sensor is OUT2 only. Brown DC (+) Main circuit Black OUT1 OUT1 Switch output Flow rate detecting circuit White OUT2 OUT2 Switch output Temperature detecting circuit Analog output Blue DC (-)

OUT2 can output either the temperature or flow rate by button operation.

PF3W7

PFG200

Function Details

SMC

For flow switch precautions and specific product precautions refer to the "Operation Manual" on the SMC website.

Specifications (Remote Sensor Unit)

Refer to page 32 for monitor unit specifications.

conforming products.

	M	odel	PF3W504	PF3W520	PF3W540	PF3W511	PF3W521	*1	Refer to the "Measurable Range
Ann	licable fluid			ne glycol aqueous			for Ethylene Glycol Aqueous		
	ection metho		water and ethyle	ne giycol aqueous		Solution" graph on page 16.			
	ed flow rang		0.5 to 4 L/min		Measurement is possible as				
	d temperatu			2 to 16 L/min	5 to 40 L/min	10 to 100 L/min	50 to 250 L/min 0 to 70°C (No freezing or condensation)		long as the fluid does not
	uracy		01		±3% F.S.	511	to re o pro noozing or concorozion)		corrode the wetted parts and the viscosity is 3 mPa·s (3 cP) or
	eatability				±2% F.S.				less. Be aware that water
		aracteristics		+5%	F.S. (25°C stand	ard)			leakage may occur due to
		sure range*2			0 to 1 MPa*2				internal seal shrinkage or
	of pressure*				1.5 MPa				swelling depending on the type
		ut flow adjustment valve)		45 kPa or less a	at the max. flow		60 kPa or less at the max. flow	۰.	of fluid. The operating pressure range
	•	Response time*3			1 s			*2	and proof pressure may change
Ana	log output	Voltage output		Voltage output:	1 to 5 V Output in	mpedance: 1 kΩ			according to the fluid
		Current output	Output current: 4	to 20 mA Max. Ic		temperature. Refer to the graphs			
Indi	cator light		For power supply status	, flow rate indicator (Blir	_	on page 8.			
Pow	er supply v	oltage		1	*3	The response time until the set			
Cur	rent consun	nption			value reaches 90% in relation to the step input (The response				
		Enclosure			time is 7 s when it is analog				
		Operating temperature range			output by the temperature				
Env	ironment	Operating humidity range			sensor.)				
		Withstand voltage*4		*4	When the temperature sensor is				
		Insulation resistance	50 M Ω or more (used, it will be 250 VAC.				
Star	ndards and i	regulations		*5	For details, refer to the "Wetted Parts Construction" on page 16.				
Wot	ted narte m	atorial ^{*5}		*6	When the piping diameter or				
Wetted parts material*5					Non-grease			Ũ	piping passage is restricted, the
Piping port size ^{*6}		3/8	3/8, 1/2	1/2, 3/4	3/4, 1	1 1/4, 1 1/2		specifications may not be	
Without temperature sensor/Without flow adjustment valve		195 g	245 g	395 g	705 g	875 g		satisfied.	
With temperature sensor/Without flow adjustment valve Without temperature sensor/With flow adjustment valve		270 g	320 g	515 g	840 g	1060 g		Products with tiny scratches,	
Without temperature sensor/With flow adjustment valve		295 g	345 g	595 g	—	—		marks, or display color or brightness variations which do	
1 · -		sor/With flow adjustment valve	370 g 415 g 715 g — —						not affect the performance of the
V	Vith lead wir	re with connector			+85 g				product are verified as
									conforming products

Temperature Sensor Specifications

Rated temperature range	0 to 100°C*1
Analog output accuracy	±3% F.S.
Response time	7 s*2
Ambient temperature characteristics	±5% F.S.

*1 The rated temperature range refers solely to that of the temperature sensor. The fluid temperature range specification of the flow switch as a whole is 0 to 90°C. *2 The response time refers solely to that of the temperature sensor.

Set Flow Range and Rated Flow Range

▲Caution

Set the flow rate within the rated flow range.

The set flow range is the range of flow rate within which setting is possible.

The rated flow range is the range within which the sensor specifications (accuracy, etc.) are satisfied. It is possible to set a value outside of the rated flow range if it is within the set flow range. However, the satisfaction of the specifications cannot be guaranteed.

Sensor						Flow range				
Sensor	0.5 L	./min 2 L/	min 5 L/	min 20 L	/min 40 L	/min 10	00 L/min 1	40 L/min	250 L/min 350	L/min
PF3W704 PF3W504	0.5 L/min 0.35 L/min 0.35 L/min		4 L/	min 5.5 L/min 5.5 L/min	r 					
PF3W720 PF3W520		2 L/min L/min L/min		16 L	/min 22 L/min 22 L/min					
PF3W740 PF3W540			5 L/min L/min L/min			40 L/min 55 L/min 55 L/min				
PF3W711 PF3W511			10 7 L/m 7 L/m				100 L/mi	n 140 L/mi 140 L/mi	1	
PF3W721				20 L/min 20 L/min	50 L/n	in			250 L/min	350 L/min 350 L/min
PF3W521				20 L/min 20 L/min	50 L/n	hin L			250 L/min 280 L/m 280 L/m	


For the PF3W5 series, the display flow range and set flow range are the same as those of the flow monitor PF3W3 series.

Rated flow range Display flow range Set flow range




3-Color Display Digital Flow Switch for Water **PF3W Series**

Analog Output




Operating Pressure and Proof Pressure



Available Flow Range * For the analog current 2-output type (symbol: "KT") only (Includes the analog voltage 2-output type (symbol: "JT"), excludes other specifications)

PF3W704/720/740/711/721





* For the PF3W721, up to 70 [°C] of the operating fluid If the analog current 2-output type is installed in an environment with high temperatures, the temperature of the product may rise. In such a case, be sure to cool the product.


PF3W


Flow Rate Characteristics (Pressure Loss: Without Flow Adjustment Valve)

PF3W704/504













PF3W721/521



Straight Piping Length and Accuracy (Reference Value)







No data for 4 cm, or for under 5 cm, as these cannot be used due to piping dimensions.

4


Straight piping length [cm]


6

8

10

- The smaller the piping size, the more the product is affected by the straight piping length. · Fluid pressure has almost no affect. • Low flow rate lessens the effect of the straight piping length.
- Use a straight pipe that is 8 cm or longer in length to satisfy the ±3% F.S. specification.
- (11 cm or longer for 100 L/min and 250 L/min types)





0

2

P = 0.2 MPa

4

5

△P = 0.1 MPa

Flow Rate Characteristics of Flow Adjustment Valve

PF3W720S/520S

△P = 0.5 MPa

2

Number of rotations

 $\triangle P$: Pressure differential between the front and the rear of product

P = 0.4 MPa

∆P = 0.3 MPa

20.0

15.0


10.0

5.0


0

Flow rate [L/min]


PF3W704S/504S



Measurable Range for Ethylene Glycol Aqueous Solution (Reference Value)



Wetted Parts Construction




Component Parts

No.	Description	Material	Note
	· · · · · · · · · · · · · · · · · · ·	SCS13	Stainless steel 304 equivalent PF3W704/720/740/711/504/520/540/511
1	Attachment	Stainless steel 304	PF3W721/521
2	Seal	FKM	
3	Body	PPS	
4	Sensor	PPS	
5	Temperature sensor	Stainless steel 304	
6	Temperature sensor body	Stainless steel 304	
7	Flow adjustment valve body	PPS	
8	Flow adjustment valve cover	PPS	
9	Flow adjustment valve shaft	Stainless steel 304	
10	Shaft support	PPS	
11	Seal	FKM	
12	Seal	FKM	

SMC

PF3W740S/540S




Function Details


Internal Circuits and Wiring Examples

PF3W7□□


-A(T) NPN (2 outputs)




-B(T) PNP (2 outputs)




-C(T)/D(T) C(T): NPN + Analog voltage output D(T): NPN + Analog current output




-E(T)/F(T) E(T): PNP + Analog voltage output F(T): PNP + Analog current output




-G NPN + External input









-JT/KT

JT: Analog voltage output + Analog voltage output KT: Analog current output + Analog current output


	Brown DC(+)
circuit	 Black Analog output (Flow rate)
ain cir	White Analog output (Temperature)
M	 Blue DC(-)

Internal Circuits and Wiring Examples

Accumulated pulse output wiring examples


-A(T)/C(T)/D(T)/G A(T): NPN (2 outputs) C(T), D(T): NPN + Analog output G: NPN + External input






PF3W5

-1/2 1: Analog voltage output 2: Analog current output




-B(T)/E(T)/F(T)/H B(T): PNP (2 outputs) E(T), F(T): PNP + Analog output G: PNP + External input



-1T


1T: Analog voltage output + Analog voltage output



3-Color Display Digital Flow Switch for Water 3-Screen Display 4-Channel Flow Monitor 3-Color Display Digital Flow Monitor for Water 3-Color Display Digital Flow Switch for PVC Piping PF3W3

PF3W

Dimensions



54

76.6 71.6 28.5

31 52 39.5

33 54 41.5

35 56 43.5

25

27.5 ø3.5 depth 14

PF3W721/521

1 1/4, 1 1/2

G1 1/4

G1 1/2


104 74

108 76 56 91

112 78

Dimensions

PF3W704/720/740/711/721-D-DT Integrated display: With temperature sensor




		լոող
Model	A	AA
PF3W704/504-□-□T	81	50
PF3W720/520-□-□T	89	54
PF3W740/540-□-□T	109	71
PF3W711/511-□-□T	135	92
PF3W721/521-□-□T	115	74
PF3W721/521-F12-□T	119	76
PF3W721/521-F14-□T	123	78

PF3W704S/720S/740S Integrated display: With flow adjustment valve


Α D s Ť \oplus $\overline{\Phi}$ 0 0 0 0 $\left[\phi \right]$ (\oplus \oplus ĘΦ Q മ 1 | F=t=t ╘═╪╍╛╘╍╪═ず F=+=3 AA F


K	

PF3W504/520/540/511/521-□-□T Remote sensor unit: With temperature sensor



PF3W504S/520S/540S Remote sensor unit: With flow adjustment valve







[mm]																						
Model	•		В	DF	- -							V	E V	.			Р	N P	0	Q number	Bracket dimensions	
Woder	A	AA	Б		Г	r	L		F	Q	of rotations	S	Т									
PF3W704S/504S	104	50	63.6 (Max. 68.6)	70.2	34	58.5	18	13.6	ø2.7 depth 10	ø19	6	56.5	22									
PF3W720S/520S	112	54	63.6 (Max. 68.6)	74.2	34	62.5	18	13.6	ø2.7 depth 10	ø19	6	60.5	22									
PF3W740S/540S	142	71	75.25 (Max. 81)	94.5	44	79.0	28	16.8	ø2.7 depth 10	ø28	7	78.0	30									

SMC

Dimensions

PF3W704S/720S/740S-D-DT Integrated display: With temperature sensor and flow adjustment valve






-	К	

					[mm]
Model	A	AA	D	к	s
PF3W704S/504S-□-□T	115	50	81.2	69.5	67.5
PF3W720S/520S-□-□T	123	54	85.2	73.5	71.5
PF3W740S/540S-□-□T	153	71	105.5	90.0	89.0


ZS-40-A Lead wire with M8 connector




* 4-wire type lead wire with M8 connector used for the PF3W series

* For wiring, refer to the "Operation Manual" on the SMC website (https://www.smcworld.com).

PF3W504S/520S/540S-D-DT Remote sensor unit: With temperature sensor and flow adjustment valve






	К		
<u> </u>			 _
		F	
		l l'Ÿ	

Please contact SMC for detailed dimensions, specifications, and lead times.

PF3W Series

Made to Order



SMC

* Not compatible with units with a flow adjustment valve Please special-order separately. Surface treatment is not applied on piping.

Made to Order

4 10-Li	nk com	oatible
---------	--------	---------

Symbol -X445

sensor

Yes

Supports the IO-Link communication protocol How to Order PF3W 7 20 04 М X445 0 Integrated display 6 8 IO-Link compatible B Piping port size Output specification/Temperature sensor type Rc Applicable flow range Output specification Temperature Symbol Port size Symbol IPT 04 OUT1 OUT2 20 40 11 21 3*1 03 3/8 ۲ • LT IO-Link: Switch output (N/P) 04 1/2 • • ompliant 06 3/4 • • 10 • 1 12 1 1/4 • **14** 1 1/2 Lead wire (Option) Calibration certificate 6 Unit specification Bracket (Option) Symbol Instantaneous flow Accumulated flow Temperature (Only for flow rate) Nil With lead wire with M8 connector (3 m) Nil None Without lead wire with M8 connector Nil With bracket Ν gal/min gal °C R Nil None Q With M12-M8 conversion lead wire (0.1 m)*2 Μ L/min °C Α Yes *2 A cable (3 m) with an M12 connector is Under the New Measurement Act, units The certificate is written in also available separately. other than SI (symbol "M") cannot be used both Japanese and English. For details, refer to the Web Catalog. in Japan. The integrated display type * Reference: 1 [L/min] = 0.2642 [gal/min] with a temperature sensor 1 [gal/min] = 3.785 [L/min] can only display the flow rate. The temperature sensor is not calibrated. *1 It is cleared when the power supply is turned OFF. The hold function can be selected. If the 5-min

- interval is selected, the life of the memory element (electronic part) is limited to 3.7 million times. (If energized for 24 hours, life is calculated as 5 mins x access times (3.7 million) = 18.5 million mins = about 35 years.) Therefore, if using the hold function, calculate the memory life for your operating conditions, and use within this life. *2 Does not include the value of the digital filter
- *3 The response time until the set value reaches 90% in relation to the step input (The response time is 7 s when it is output by the temperature sensor.)

*1 The configuration file can be downloaded from the SMC website, https://www.smcworld.com

*2 The device ID differs according to each product type (flow range, whether or not a temperature sensor is provided, etc.).

U R	Rated flow range (Flow range)			ead
04	0.5 to 4 L/min		Nil	F
20	2 to 16 L/min		Ν	N
40	5 to 40 L/min		F	G
11	10 to 100 L/min		*1 ISO 2	28 co
21	50 to 250 L/min			


Specifications

	Model	PF3W704 PF3W720 PF3W740 PF3W711		PF3W721		
1	cumulated flow range*1	999999999.9 L		999999999 L		
Accumulated flow range ^{*1}		By C).1 L		By 1 L	
Ħ	Maximum applied voltage		30) V (NPN outpu	ut)	
output	Internal voltage drop		1.5 V or less	(at load curre	nt of 80 mA)	
	Delay time*2			3.5 ms		
ч	Delay time -		Variable from	0 to 60 s/0.01	s increments	
Switch	Output Flow rate	Select from Hysteresis, Window comparator, Accumulated output,				
Ś	mode	Accumulated pulse output, Error output, or Switch output OFF modes.				
^o ower supply voltage	When used as a switch output device	12 to 24 VDC, including ripple (p-p) 10%				
Power sup	When used as an IO-Link device	18 to 30 VDC, including ripple (p-p) 10%				
Digital filter*3 Select from 0.5 s, 1.0 s, 2.0 s, 5.0 s, 10.0 s, 15.0 s, 20.0 s) s, or 30.0 s.			
Envir	onment Withstand voltage	250 VAC for 1 min between external terminals and case				d case
Sta	indards and regulations		CE/UK	CA marking, U	L (CSA)	

Communication Specifications (IO-Link mode)

IO Link hung	Device				
IO-Link type	Device				
IO-Link version	V1.1				
Communication speed	COM2 (38.4 kbps)				
Configuration file	IODD file*1				
Minimum cycle time	3.5 ms				
Process data length	Input data: 6 bytes, Output data: 0 byte				
On request data communication	Yes				
Data storage function	Yes				
Event function	Yes				
Vendor ID	131 (0x0083)				
	PF3W704-□-LT□-M-X445: 330 (0x014A)				
	PF3W720-□-LT□-M-X445: 310 (0x0136)				
Device ID*2	PF3W740-□-LT□-M-X445: 317 (̀0x013D́)				
	PF3W711-□-LT□-M-X445: 331 (0x014B)				
	PF3W721-□-LT□-M-X445: 332 (̀0x014C)́				

Other specifications and dimensions that are not indicated are the same as those of the standard product. For details, refer to page 12 and later.




SMC

* For wiring, refer to the "Operation Manual" on the SMC website (https://www.smcworld.com).

3-Color Display Digital Flow Switch for PVC Piping **PF3W Series** (E LA CAUS RoHS)

How to Order



*∕∂*SMC

Options/Part Nos.

When only optional parts are required, order with the part numbers listed below.

Description	Part no.	Qty.	Note		
Bracket	ZS-40-M	1	For PF3W711/511	With 4 tapping screws (4 x 10)	
Lead wire with M8 connector	ZS-40-A	1	Lead wire length: 3 m		

24 ®

3-Color Display Digital Flow Switch for PVC Piping 3-Color Display Digital Flow Switch for Water

PF3W

3-Screen Display 4-Channel Flow Monitor | 3-Color Display Digital Flow Monitor for Water

PFG200

Function Details

PF3W3

For flow switch precautions and specific product precautions, refer to the "Operation Manual" on the SMC website.



Specifications (Integrated Display)

Μ	odel	PF3W711	PF3W721			
Applicable fluid	I	Water and ethylene glycol aqueous solution (with a viscosity of 3 mPa·s [3 cP] or less)*1				
Detection meth		Karman vortex				
Rated flow rang	je	10 to 100 L/min	30 to 250 L/min			
Diamlass flasss say		7 to 140 L/min	20 to 350 L/min			
Display flow rar	nge	(Flow under 7 L/min is displayed as "0.")	(Flow under 20 L/min is displayed as "0.")			
Set flow range		7 to 140 L/min	20 to 350 L/min			
Smallest settab	le increment	1 L/min	2 L/min			
Conversion of a	accumulated pulse	1 L/pulse	2 L/pulse			
Fluid temperatu	ire	0 to 70°C (No freezi				
Display unit		Instantaneous flow: L/min, Accumulated flow:				
Accuracy		Display value: ±3% F.S.	Analog output: ±3% F.S.			
Repeatability		±2% F				
Temperature ch		±5% F.S. (25				
Operating press		0 to 1				
Proof pressure	*3	1 M				
Pressure loss		45 kPa or less a				
Accumulated fl	ow range*4	999999				
	owrange	By 1 L				
Switch output		NPN or PNP open collector output				
	Max. load current	80 mA				
	Max. applied voltage	28 VDC				
	Internal voltage drop	NPN: 1 V or less (at load current of 80 mA) PNP: 1.5 V or less (at load current of 80 mA)				
	Response time*2, 5					
	Output protection	Short-circuit protection				
	Output mode Flow rate	Select from Hysteresis, Window comparator, Accum				
	Response time*6	0.5 s/1 s/2 s (linked w				
Analog output	Voltage output	Voltage output: 1 to 5 V Output impedance: 1 kΩ				
	Current output	Output current: 4 to 20 mA Max. load imped	· · · · · · · · · · · · · · · · · · ·			
Hysteresis		Variable				
External input		Voltage free input: 0.4 V or less (reed or solid state), input for 30 ms or longer				
Display method Indicator light		2-screen display (Main screen: 4-digit, 7-segment, 2-color, Red/Green Sub screen: 6-digit, 11-segment, White)				
Power supply v	oltage	Output 1, Output 2: Orange				
Current consur		12 to 24 VDC ±10% 50 mA or less				
Current consul	Enclosure					
	Operating temperature range	0 to 50°C (No freezi	-			
Environment	Operating humidity range	Operation, Storage: 35 to 8				
	Withstand voltage	1000 VAC for 1 min betwe				
	Insulation resistance					
Standards and		50 MΩ or more (500 VDC measured via megohmmeter) between terminals and housing CE/UKCA marking, UL (CSA)				
Wetted parts m	aterial*7	PPS, FKM, CPVC Non-grease				
Piping port size	*8	25A	30A			
	Without lead wire with connector	285 g	340 g			
Weight	With lead wire with connector	370 g	425 g			


*1 Refer to the "Measurable Range for Ethylene Glycol Aqueous Solution" graph on page 16. Measurement is possible as long as the fluid does not corrode the wetted parts and the viscosity is 3 mPa·s (3 cP) or less. Refer to the list of applicable fluids on page 44. Be aware that water leakage may occur due to internal seal shrinkage or swelling depending on the type of fluid.
*2 If 0.5 s is selected for the response time of the switch output, the repeatability will be ±3% F.S.
*3 The operating pressure range and proof pressure may change according to the fluid temperature. Refer to the graph below.
*4 It is cleared when the power supply is turned OFF. The hold function can be selected. (Intervals of 2 or 5 mins can be selected.) If the 5-min interval is selected, the life of the memory element (electronic part) is limited to 1 million times. (If energized for 24 hours, life is calculated as 5 mins x 1 million = 5 million mins = about 9.5 years.) Therefore, if using the hold function, calculate the memory life for your operating conditions, and use within this life.
*5 The response time when the set value is 90% in relation to the step input
*6 The response time until the set value reaches 90% in relation to the step input

250


*5 The response time until the set value is 90% in relation to the step input
*6 The response time until the set value reaches 90% in relation to the step input
*7 For details, refer to the "Wetted Parts Construction" on page 27.
*8 When the piping diameter or piping passage is restricted, the specifications may not be satisfied.
* Products with tiny scratches, marks, or display color or brightness variations which do not affect the performance of the product are verified as conforming products.


Analog Output

Flow rate/Analog output



30





Operating Pressure and Proof Pressure

PF3W721/521



3-Color Display Digital Flow Switch for PVC Piping *PF3W Series*

For flow switch precautions and specific product precautions,

Specifications (Remote Sensor Unit)

refer to the "Operation Manual" on the SMC website.


Refer to page 32 for monitor unit specifications.

М	odel	PF3W511	PF3W521				
Applicable fluid		Water and ethylene glycol aqueous solution (with a viscosity of 3 mPa s [3 cP] or less)*1					
Detection meth		Karman vortex					
Rated flow rand	le	10 to 100 L/min 30 to 250 L/min					
Fluid temperatu	ure	0 to 70°C (No freezi	ng or condensation)				
Accuracy		±3%	F.S.				
Repeatability		±2%	F.S.				
Temperature ch	naracteristics	±5% F.S. (25	°C standard)				
Operating press		0 to 1 l	MPa ^{*2}				
Proof pressure	*2	1 M	1Pa				
Pressure loss		45 kPa or less a	at the max. flow				
	Response time*3	1	-				
Analog output	Voltage output	Voltage output: 1 to 5 V Output impedance: 1 k Ω					
	Current output	Output current: 4 to 20 mA Max. load impedance: 300 Ω for 12 VDC, 600 Ω for 24 VDC					
Indicator light		For power supply status, flow rate indicator (Blinking speed changes in response to flow rate.), and other error indicator					
Power supply v		12 to 24 VDC ±10%					
Current consur		30 mA or less					
	Enclosure	IP65					
	Operating temperature range	0 to 50°C (No freezing or condensation)					
Environment	Operating humidity range	Operation, Storage: 35 to 85% R.H. (No condensation)					
	Withstand voltage	1000 VAC for 1 min betwe	V				
	Insulation resistance	50 M Ω or more (500 VDC measured via megohmmeter) between terminals and housing					
Standards and	regulations	CE/UKCA marking, UL (CSA)					
Wetted parts m	aterial*4	PPS, FKI	· · · · · · · · · · · · · · · · · · ·				
•		Non-g					
Piping port size		25A	30A				
Weight	Without lead wire with connector	270 g	325 g				
	With lead wire with connector	355 g	410 g				


1 Refer to the "Measurable Range for Ethylene Glycol Aqueous Solution" graph on page 16. Measurement is possible as long as the fluid does not corrode the wetted parts and the viscosity is 3 mPa·s (3 cP) or less. Refer to the list of applicable fluids on page 44.
2 The operating pressure range and proof pressure may change according to the fluid temperature. Refer to the graphs below.
*3 The response time until the set value reaches 90% in relation to the step input
*4 For details, refer to the "Wetted Parts Construction" on page 27.
*5 When the piping diameter or piping passage is restricted, the specifications may not be satisfied.
* Products with tiny scratches, marks, or display color or brightness variations which do not affect the performance of the product are verified as conforming products.

Flow Rate Characteristics (Pressure Loss)


PF3W711/511



PF3W721/521




Straight Piping Length and Accuracy (Reference Value)



• Fluid pressure has almost no effect.

• To maintain ±3% F.S. in the specifications, use a straight pipe that is 11 cm or longer in length.






PF3W5

3-Color Display Digital Flow Switch for PVC Piping 3-Color Display Digital Flow Switch for Water

PF3W



Wetted Parts Construction



Component Parts

No.	Description	Material	Note
1	PVC pipe	CPVC	
2	Seal	FKM	
3	Body	PPS	
4	Sensor	PPS	

Replacement Parts


No.	Description	Part no.	Qty.
	PVC pipe (25A)	ZS-40-U25	1
1	PVC pipe (30A)	ZS-40-U30	1
F	25A retaining plate (With two M5 x 80 hexagonal socket head cap screws)	ZS-40-U25-A	1
5	30A retaining plate (With two M5 x 65 hexagonal socket head cap screws)	ZS-40-U30-A	1

* Replacing the PVC pipe may cause accuracy to fluctuate by 1 to 2%.

Internal Circuits and Wiring Examples

Refer to pages 17 and 18.

3-Color Display Digital Flow Switch for PVC Piping *PF3W* Series



For wiring, refer to the "Operation Manual" on the SMC website (https://www.smcworld.com).

4


OUT1

Black


SMC

Dimensions


PF3W721-U30 Integrated display




Body side Connector pin number





Pin no.	Pin name
1	DC (+)
2	OUT2
3	DC (-)
4	OUT1







Flow direction









Body side Connector pin number








Made to Order Please contact SMC for detailed dimensions, specifications, and lead times.

1 EPDM seal material




PF3W Series

Made to Order

 Function
 3-Screen Display 4-Channel Flow Monitor
 3-Color Display Digital Flow Switch for Water
 3-Color Display Digital Flow Switch for Water

 Details
 PF3.00
 PF3.00
 PF3.00

 Symbol -X109



Under the New Measurement Act, units other than SI (symbol "M") cannot be used in Japan.

G, F, J: Made to order

Reference: 1 [L/min]↔0.2642 [gal/min] 1 [gal/min]↔3.785 [L/min] °F = 9/5°C + 32

Options/Part Nos.

When only optional parts are required, order with the part numbers listed below.

Description	Part no.	Note
Panel mount adapter	ZS-26-B	With waterproof seal and screws
Front protective cover + Panel mount adapter	ZS-26-C	With waterproof seal and screws
Front protective cover only	ZS-26-01	Separately order panel mount adapter, etc.
Power supply/output connection lead wire	ZS-40-W	Lead wire length: 2 m
Sensor connector (e-con)	ZS-28-CA-4	1 pc.
Lead wire with connector for copying	ZS-40-Y	Connect up to 10 copy destination units

SMC

3-Color Display Digital Flow Monitor for Water **PF3W3** Series

For flow switch precautions and specific product precautions, refer to the "Operation Manual" on the SMC website.

品を通 PF3W3

Specifications

ľ	Model			PF3W30□		
Display flow ra	ande	0.35 to 4.50 L/min	1.7 to 18.0 L/min	3.5 to 45.0 L/min	7 to 112 L/min	20 to 280 L/min
				(Flow under 3.5 L/min is displayed as "0.0.")		· · · /
Set flow range		0.35 to 4.50 L/min	1.7 to 18.0 L/min	3.5 to 45.0 L/min	7 to 112 L/min	20 to 280 L/min
Smallest setta	ble increment	0.01 L/min	0.1 l	_/min	1 L/min	2 L/min
	accumulated pulse	0.05 L/pulse	0.1 L/pulse	0.5 L/pulse	1 L/pulse	2 L/pulse
Display unit			Instantaneo	ous flow: L/min, Accumu	lated flow: L	
Accuracy			Display value:	±0.5% F.S. Analog out	put: ±0.5% F.S.	
Repeatability				±0.5% F.S.		
Temperature c	haracteristics			0.5% F.S. (25°C standar		
Accumulated f	flow range*1	999999	999.9 L		999999999 L	
		By 0.1 L	By 0.5 L		By 1 L	
Switch output			NPN	or PNP open collector of	output	
	Max. load current			80 mA		
	Max. applied voltage			28 VDC		
	Internal voltage drop	NPN: 1 V or less (at load current of 80 mA) PNP: 1.5 V or less (at load current of 80 mA)				
	Response time*2	1 s/2 s				
	Output protection					
	Output Flow rate	Select from Hysteresis, Window comparator, Accumulated output, or Accumulated pulse output modes.				
	mode Temperature					
	Response time*3	1 s/2 s (linked with the switch output)				
Analog output	Voltage output	Voltage output: 1 to 5 V Output impedance: 1 k Ω				
	Current output	Output current: 4 to 20 mA Max. load impedance: 300 Ω for 12 VDC, 600 Ω for 24 VDC				
Hysteresis		Variable				
External input		Vol	tage free input: 0.4 V or	r less (reed or solid state	e), input for 30 ms or lon	ger
Input/output				Input for copy mode		
Display metho	d	2-screen display (Main screen: 4-digit, 7-segment, 2-color, Red/Green Sub screen: 6-digit, 11-segment, White), Display values updated 5 times per second				
Indicator light		Output 1, Output 2: Orange				
Power supply		12 to 24 VDC ±10%				
Current consu	mption	50 mA or less				
Connection		Power supply output 5P connector, sensor connection 4P connector (e-con)				
	Enclosure	IP40 (Only front face o		n panel mount adapter a		otional parts are used.)
	Operating temperature range		0 to 50°	C (No freezing or conde	nsation)	
Environment	Operating humidity range			age: 35 to 85% R.H. (No		
[Withstand voltage		1000 VAC for	1 min between terminal	s and housing	
	Insulation resistance	Ç				
Standards and		CE/UKCA marking, UL (CSA)				
Weight Without pow	ver supply/output connection lead wire			50 g		
With power	supply/output connection lead wire	100 g				
			ation can be calested (Int	ervals of 2 or 5 mins can b	a calestad)	

*1 It is cleared when the power supply is turned OFF. The hold function can be selected. (Intervals of 2 or 5 mins can be selected.)

If the 5-min interval is selected, the life of the memory element (electronic part) is limited to 1 million times. (If energized for 24 hours, life is calculated as 5 mins x 1 million = 5 million mins = about 9.5 years.) Therefore, if using the hold function, calculate the memory life for your operating conditions, and use within this life. *2 The response time when the set value is 90% in relation to the step input (The response time is 7 s when it is output by the temperature sensor.)

*3 The response time until the set value reaches 90% in relation to the step input (The response time is 7 s when it is analog output by the temperature sensor.)

* Products with tiny scratches, marks, or display color or brightness variations which do not affect the performance of the product are verified as conforming products.

Temperature Sensor Specifications

Rated temperature range	0 to 100°C*1
Set/Display temperature range	–10 to 110°C
Smallest settable increment	1°C
Display unit	O°
Analog output accuracy	±3% F.S.
Response time	7 s*2
Ambient temperature characteristics	±5% F.S.


*1 The rated temperature range refers solely to that of the temperature sensor. The fluid temperature range specification of the flow switch as a whole is **0 to 90°C**. *2 The response time refers solely to that of the temperature sensor.


Analog Output

Flow rate/Analog output


	Α		С		
	A	04/20/40	11	21	U
Voltage output	1 V	1.5 V	1.4 V	1.5 V	5 V
Current output	4 mA	6 mA	5.6 mA	5.9 mA	20 mA
The values of B vary according to the range.					

	, ,			
Model	Flow rate [L/min]			
woder	Min.	Max.		
PF3W504	504 0.5			
PF3W520	2	16		
PF3W540	5	40		
PF3W511	10	100		
PF3W521	30	250		






OUT2 can output either the temperature or flow rate by button operation.




Internal Circuits and Wiring Examples

-A







-B PNP (2 outputs)



-C/D C: NPN + Analog voltage output D: NPN + Analog current output




-E/F E: PNP + Analog voltage output F: PNP + Analog current output




Accumulated pulse output wiring examples


-A/C/D/G A: NPN (2 outputs) C, D: NPN + Analog output G: NPN + External input




-G NPN + External input





-H **PNP + External input**



-J/K J: Analog voltage output K: Analog current output








ר ר

3-Color Display Digital Flow Monitor for Water **PF3W3** Series

Dimensions



SMC

 $\ast~$ For wiring, refer to the "Operation Manual" on the SMC website (https://www.smcworld.com).


3-Screen Display 4-Channel Flow Monitor

PFG200

Function Details

3-Color Display Digital Flow Monitor for Water 3-Color Display Digital Flow Switch for PVC Piping 3-Color Display Digital Flow Switch for Water PF3W

3-Screen Display 4-Channel Flow Monitor **PFG200 Series** (ССА Понь



* Options are not assembled, but shipped together.

Options/Part Nos.

When only optional parts are required, order with the part numbers listed below.

Description	Part no.	Note
Power supply/Output connection cable	ZS-26-L	Length: 2 m
For PF2W5□□, PF3W5□□ Sensor connector (e-CON)	ZS-28-CA-4	1 pc., Finished O.D.: ø1.15 to ø1.35, Cover color: Blue
Panel mount adapter	ZS-26-B	Mounting screw (M3 x 8 L, 2 pcs.), With waterproof seal
Panel mount adapter + Front protection cover	ZS-26-C	Mounting screw (M3 x 8 L, 2 pcs.), With waterproof seal
Front protection cover	ZS-26-01	_
Power supply with M12 connector cable (Made to Order)	ZS-26-LM12	For use when using an M12 connector for IO-Link communication

3-Screen Display 4-Channel Flow Monitor **PFG200** Series

Specifications

For flow switch precautions and specific product precautions, refer to the "Operation Manual" on the SMC website.

	Series	PFG20 Series							
Applicable SMC flow sensor		PF2(3)W504	PF2(3)W520	PF2(3)W540	PF2(3)W511	PF3W521			
Ra	ted flow range	0.5 to 4 L/min	2 to 16 L/min	5 to 40 L/min	10 to 100 L/min	50 to 250 L/min			
Inc	tantaneous flow rate	0.35 to 4.50 L/min	1.7 to 17.0 L/min	3.5 to 45.0 L/min	7 to 110 L/min	20 to 280 L/min			
	play/Set flow rate range			(Flow under 3.5 L/min is	(Flow under 7 L/min is	(Flow under 20 L/min i			
uic	play/oet new rate range	displayed as "0.00.")	displayed as "0.0.")	displayed as "0.0.")	displayed as "0.")	displayed as "0.")			
Insta	ntaneous flow rate display/Min. setting unit	0.05 L/min	0.1 L/min	0.5 L/min	1 L/min	2 L/min			
Acci	mulated flow display/Set flow rate range	0 to 99,999,999.9 L	0 to 999,999,999 L		0 to 999,999,999 L				
Acc	mulated flow display/Min. setting unit	0.1 L	1 L		1 L				
Acci	mulated pulse flow rate exchange value	0.05 L	0.1 L	0.5 L	1 L	2 L			
Un	it		L/min. ga	l/min (depends on selecte	ed range)	1			
	When used as a switch output device			C ±10% with 10% ripple (
Electrical	When used as a switch output device When used as an IO-Link device		18 to 30	VDC, including ripple (p-p	o) 10%*1				
Ele I	Current consumption			55 mA or less					
-	Protection			Polarity protection					
Ì	Power supply voltage for sensor*1		[P	ower supply voltage] -1.5	V				
ł	Power supply current for sensor*2	Max. 110 mA (However, the total n		ts is 440 mA or less, and the total po		IO-Link device is 200 mA or less			
2	Display accuracy (Linearity)			+5.0% F.S. Max.*4					
Accuracy	Repeatability			±3.0% F.S. Max.*4					
ខ	Temperature characteristics		10 5	% F.S. Max. (Reference: 2	5°C)				
					,				
(e)	Output type			NP open collector output:	•				
ĕ	Output mode	Hysteresis mode, Wind		ccumulated output, Accur		or output, Output OFF			
ō	Switch operation		Nor	rmal output, Reversed out	put				
s.	Max. load current			80 mA					
۶ĺ	Max. applied voltage (NPN only)			30 VDC					
đ	Internal voltage drop (Residual voltage)		1.5 V c	or less (at load current of 8	30 mA)				
° C	Delay time*3			ariable from 0 to 60 s/0.0	,				
ę	Hysteresis		0 110 01 1000, 1	Variable from 0*5					
Switch output (SIO mode)	Protection			Over current protection					
Analog input	Input type		<u> </u>	t: 1 to 5 VDC (Input imped	,	• •			
i B	Number of inputs	41	nputs (Check the "Interna	al Circuits and Wiring Exa	mples" on pages 37 to 3	9.)			
嵩	Connection method			e-CON					
	Protection			protection (up to a voltage					
Ex	ernal input ^{*8}		Voltage free input: 0.4	V or less (reed or solid sta	ate) for 30 ms or longer				
	Display type			LCD					
_[Number of screens		3-screen di	splay (Main screen, Sub	screen x 2)				
<u>a</u>	Display color		Main scree	en: Red/Green, Sub scree	en: Orange				
Display	Number of display	Main screen: 4 digits		en (Left): 4 digits (some d		segments for other)			
ā	digits								
	Indicator light	Sub screen (Right): 5 digits (some digits are 11-segments, 7 segments for other)							
יח	lital filter*6	Lights up when switch output is turned ON. OUT1, OUT2: Orange							
1		Variable from 0 to 30 s/0.01 s increments							
Environment	Enclosure	Front face: IP65 (when panel-mounted), Others: IP40 1000 VAC for 1 min between terminals and housing							
E	Withstand voltage								
ē	Insulation resistance	50 MΩ		sured via megohmmeter)		ousing			
Ξ	Operating temperature range			°C, Stored: -10 to 60°C (
	Operating humidity range		Operating/Sto	ored: 35 to 85% RH (No c	ondensation)				
	ndards		CE/UKCA marking						
Weight	Body		51 g (Exclu	ides power supply and ou	tput cable)				
eig	Power supply/Output cable			60 g					
Š	e-CON (1 pc.)			2 g					
-	IO-Link type			Device					
g	IO-Link version			V1.1					
ž	Communication speed			COM2 (38.4 kbps)					
<u>.</u>	Configuration file			IODD file*7					
ġ	¥			4.8 ms					
Ę	Minimum cycle time				0 hutaa				
atio	Process data length		Input da	ta: 10 bytes, Output data:	U DYTES				
j.	On request data communication			Yes					
Communication (IO-Link mode)	Data storage function			Yes					
ξ	Event function			Yes					
~ '	Venden ID			131 (0 x 0083)					
ຮື	Vendor ID		e power supply voltage range of the connected sensor. *6 The response time indicates when the set value is 90% in relation to the step input.						

*1 Check the power supply voltage range of the connected sensor. *2 Over current on DC (+) side and DC (-) side of the sensor input

*2 Over current on DC (+) side and DC (-) side of the sensor input connector results in breakage of the product.

*3 Value without digital filter (at 0 ms)

*4 The system accuracy when combined with an applicable flow sensor.

*5 If the applied pressure fluctuates around the set value, the hysteresis must be set to a value more than the amount of fluctuation, or chattering will occur. *6 The response time indicates when the set value is 90% in relation to the step input.
*7 The configuration file can be downloaded from the SMC website, https://www.smcworld.com

*8 This setting is only possible for the PFG200/PFG201.

 Products with tiny scratches, marks, or display color or brightness variations which do not affect the performance of the product are verified as conforming products. Function Details

3-Screen Display 4-Channel Flow Monitor 3-Color Display Digital Flow Monitor for Water 3-Color Display Digital Flow Switch for PVC Piping 3-Color Display Digital Flow Switch for Water *PFG200 PF3W PF3W PF3W*

PFG200 Series

Applicable Flow Sensors

Applicable SMC	Rated flow range [L/min]												
flow sensor	0.5	1	2	4	5	10	2	0 4	0	50	100	20	00 25
PF2(3)W504	0.5		į	4									
PF2(3)W520			2		ļ		16						
PF2(3)W540					5			40					
PF2(3)W511						1	0		:		100		
PF3W521										50			250


Internal Circuits and Wiring Examples



Input/Output specifications


0

· NPN open collector 5 outputs + External input




1

• PNP open collector 5 outputs + External input



Internal Circuits and Wiring Examples







2

· IO-Link/NPN open collector 1 output + NPN open collector 4 outputs

When used as an IO-Link device




When used as a switch output device



3-Screen Display 4-Channel Flow Monitor 3-Color Display Digital Flow Monitor for Water 3-Color Display Digital Flow Switch for PVC Piping 3-Color Display Digital Flow Switch for Water *PF3W* Function Details

PFG200 Series


Internal Circuits and Wiring Examples




3

· IO-Link/PNP open collector 1 output + PNP open collector 4 outputs


When used as an IO-Link device



When used as a switch output device



3-Screen Display 4-Channel Flow Monitor **PFG200** Series



Panel fitting dimensions Applicable panel thickness: 0.5 to 8 mm

SMC

PF3W Series Function Details

Integrated Display (PF3W7 series)/Remote Monitor Unit (PF3W3 series)

Output operation

The output operation can be selected from the following:

Output (hysteresis mode and window comparator mode) corresponding to instantaneous flow rate, output corresponding to accumulated flow, or accumulated pulse output.

* At the time of shipment from the factory, it is set to hysteresis mode and normal output.

When a temperature sensor is attached, the output to the temperature sensor is selectable only for OUT2.

(Refer to "How to Order" for details.)

Display color

The display color can be selected for each	Green for ON, Red for OFF
output condition. The selection of the dis-	
play color provides visual identification of	Red for ON, Green for OFF
abnormal values. (The display color de-	Red all the time
pends on OUT1 setting.)	Green all the time

Response time -

The response time can be selected to suit the application. (1 second for default setting)

Abnormalities can be detected more quickly by setting the response time to 0.5 seconds.

The effect of the pump fluctuation and flickering of the display can be reduced by setting the response time to 2 seconds.

* The temperature sensor output is fixed to 7 seconds.

Desmanas	Applicable model					
Response time	Integrated display PF3W7 series	Remote monitor unit PF3W3 series				
0.5 seconds	•	—				
1 second	•	•				
2 seconds	•					

Selection of display on sub screen

The display on the sub screen in measuring mode can be set.

External input function

This function can be used only when the optional external input is present. The accumulated flow, peak value, and bottom value can be reset remotely.

Accumulated value external reset: A function to reset the accumulated flow value when an external input signal is applied.

In accumulated increment mode, the accumulated value will reset to and increase from zero.

In accumulated decrement mode, the accumulated value will reset to and decrease from the set value.

* When the accumulated value is stored to memory, every time the accumulated value external reset is activated, the memory (EE-PROM) will be accessed. Take into consideration that the maximum number of times the memory can be accessed is 1 million times. The total number of external inputs and the accumulated value memorizing time interval should not exceed 1 million times.

Peak/Bottom value reset: Peak and bottom value are reset.

Forced output function

The output is turned on/off in a fixed state when starting the system or during maintenance. This enables the confirmation of wiring and prevents system errors due to unexpected output.

For the analog output type, when ON the output will be 5 V or 20 mA, and when OFF, it will be 1 V or 4 mA.

 Also, an increase or decrease of the flow and temperature will not change the on/off status of the output while the forced output function is activated.


Accumulated value hold

FLOW MONITO

The accumulated value is not cleared even when the power supply is turned off.

The accumulated value is memorized every 2 or 5 minutes during measurement and continues from the last memorized value when the power supply is turned on again.

The life time of the memory device is 1 million access times. Take this into consideration before using this function.



* The above are examples of integrated displays. (Same as remote monitor unit)

Power-saving mode

The display can be turned off to reduce power consumption.

In power-saving mode, only decimal points blink.

If any button is pressed during power-saving mode, the display is recovered for 30 seconds to check the flow, etc.

Setting of security code

The user can select whether a security code must be entered to release the key lock. At the time of shipment from the factory, it is set such that a security code is not required.

Peak/Bottom value display

The maximum (minimum) flow rate is detected and updated from when the power supply is turned on. In peak (bottom) value display mode, this maximum (minimum) flow rate is displayed.

Keylock function

Prevents operation errors such as accidentally changing setting values



Function Details **PF3W Series**

Integrated Display (PF3W7 series)/Remote Monitor Unit (PF3W3 series)

Analog output free range function

This function allows a flow that generates an output of 5 V or 20 mA to be changed. (This function is not available for the analog output to the temperature.) This function is available if the analog output type is used. The value can be changed between 10% of the maximum value of the rated flow and the maximum value of the display range.


■ Copy function (Remote monitor unit/PF3W3 series)

The set values of the monitor can be copied.

This can reduce setting labor and minimize the risk of setting mistakes.

The set value can be copied to up to 10 flow monitors simultaneously.

(Maximum transmission distance: 4 m)



Error display function

When an error or abnormality arises, the location and contents are displayed.

				Applicable model		
Display	Description	Contents	Action	Integrated display PF3W7 series	Remote monitor unit PF3W3 series	
Er l	OUT1 over current error	A load current of 80 mA or more is applied to the switch output (OUT1).	Eliminate the cause of the over current by turning off the power supply and	•	•	
Er2	OUT2 over current error	A load current of 80 mA or more is applied to the switch output (OUT2).	then turning it on again.	•	•	
ННН	Instantaneous flow error	The flow rate has exceeded the display flow range (rated flow x approx. 1.4).	Decrease the flow rate.	•	•	
LLL Unconnected sensor error		Remote sensor unit is not connected to the monitor unit. Or, sensor output is less than 0.6 V.	Connect the sensor or check the sensor output voltage.	_	•	
(Alternately displays) [999] and [999999]	Accumulated flow error	The flow rate exceeds the accumulated flow rate range. (Decimal points start blinking due to the flow range.)	Clear the accumulated flow rate. (This error is irrelevant when accumulated flow is not being used.)	•	•	
⊂HHH	Over upper limit of temperature	Fluid temperature exceeds 110°C.	Lower the fluid temperature.	•	•	
	Under lower limit of temperature	Fluid temperature is under -10°C.	Raise the fluid temperature.	•	•	
cLLL	Unconnected	Temperature sensor output wire is not connected.	Connect the temperature output wire.		•	
	temperature sensor error	Temperature sensor is not connected to the remote sensor unit.	Check if or not the remote sensor unit is connected to a temperature sensor.		•	
	Temperature sensor failure	If the above actions to correct the lower limit of fluid temperature and unconnected sensor are taken and error message still appears, the temperature sensor of the remote sensor unit may be damaged.	Please contact SMC for investigation.	_	•	
8r0						
8 ተ ዛ	System error	Internal data error	Turn the power off and then on again. If the error cannot be rectified, please			
Erb					-	
Er8			contact SMC for investigation.			
Er12	Temperature sensor failure	Temperature sensor may be damaged.		•	_	

If the error cannot be solved after the instructions above are performed, please contact SMC for investigation.

Function Details




Remote Sensor Unit (PF3W5 series)

■POWER indicator function

It is possible to check whether power supply is reaching the product. When power is supplied to the product, the indicator lights up green.

■FLOW indicator function

Status of the flow rate can be checked visually. When the flow rate increases, the green lamp blinks faster. When below the measurable lower limit of flow rate, the lamp turns off, when above the measurable upper limit of flow rate, red lamp turns on.



Error display function

When an error or abnormality arises, the location and contents are displayed.

LED display	Description	Contents	Action	
POWER Green Red FLOW FLOW indicator: Red ON	Over upper limit of flow rate	Flow is approximately 110% or more of the rated flow.	Decrease the flow rate.	
POWER Red- POWER indicator: Blinking red	Temperature measurement range error	Fluid temperature is either under -10°C or over 110°C.	Adjust the fluid temperature within the measurable temperature range.	
POWER Red FLOW POWER indicator: Blinking red FLOW indicator: Red ON	Over upper limit of flow rate and temperature measurement range error	Refer to above.	Refer to above.	
LED display	Description	Contents	Action	
POWER Red Red FLOW POWER indicator: Red ON Red R	System error	Internal data error or other errors occur.	Turn the power off and then on again If the error cannot be rectified, please contact SMC for investigation.	
POWER Red FLOW POWER indicator: Red ON FLOW indicator: OFF		Temperature sensor may be damaged.		

If the error cannot be solved after the above instructions are performed, please contact SMC for investigation.

Digital Flow Switch for PVC Piping *PF3W Series* Applicable Fluids

Material and Fluid Compatibility Check List (Guide)

Chemical					
Ammonium hydroxide					
	×*3				
	⊖*1, 2				
Concentration 30% or less	○*2				
Concentration 5% or less	0				
Concentration 10% or less	○*2				
	0				
Concentration 50% or less	×* ³				
Concentration 30% or less	0				
Concentration 50% or less	0				
	Concentration 30% or less Concentration 5% or less Concentration 10% or less Concentration 50% or less Concentration 30% or less				

The material and fluid compatibility check list provides reference values as a guide only, therefore we do not guarantee the application to our product.

*1 Since static electricity may be generated, implement suitable countermeasures.

*2 Fluid may pass through. Fluid that has passed through may have an impact on components made of different materials.

*3 Karman vortex measurement cannot be carried out due to high viscosity.

• SMC is not responsible for its accuracy and any damage happened because of this data.

Table symbols

Can be used Can be used under

certain conditions

x: Cannot be used

▲ Safety Instructions

These safety instructions are intended to prevent hazardous situations and/or equipment damage. These instructions indicate the level of potential hazard with the labels of "Caution," "Warning" or "Danger." They are all important notes for safety and must be followed in addition to International Standards (ISO/IEC)*1), and other safety regulations.

- **Danger**: Danger indicates a hazard with a high level of risk which, if not avoided, will result in death or serious injury.
- Warning: Warning indicates a hazard with a medium level of risk which, if not avoided, could result in death or serious injury.

Caution: Caution indicates a hazard with a low level of risk which, if not avoided, could result in minor or moderate injury.

A Warning

1. The compatibility of the product is the responsibility of the person who designs the equipment or decides its specifications.

Since the product specified here is used under various operating conditions, its compatibility with specific equipment must be decided by the person who designs the equipment or decides its specifications based on necessary analysis and test results. The expected performance and safety assurance of the equipment will be the responsibility of the person who has determined its compatibility with the product. This person should also continuously review all specifications of the product referring to its latest catalog information, with a view to giving due consideration to any possibility of equipment failure when configuring the equipment.

2. Only personnel with appropriate training should operate machinery and equipment.

The product specified here may become unsafe if handled incorrectly. The assembly, operation and maintenance of machines or equipment including our products must be performed by an operator who is appropriately trained and experienced.

- 3. Do not service or attempt to remove product and machinery/ equipment until safety is confirmed.
 - 1. The inspection and maintenance of machinery/equipment should only be performed after measures to prevent falling or runaway of the driven objects have been confirmed.
 - 2. When the product is to be removed, confirm that the safety measures as mentioned above are implemented and the power from any appropriate source is cut, and read and understand the specific product precautions of all relevant products carefully.
 - 3. Before machinery/equipment is restarted, take measures to prevent unexpected operation and malfunction.

4. Our products cannot be used beyond their specifications. Our products are not developed, designed, and manufactured to be used under the following conditions or environments. Use under such conditions or environments is not covered.

- 1. Conditions and environments outside of the given specifications, or use outdoors or in a place exposed to direct sunlight.
- 2. Use for nuclear power, railways, aviation, space equipment, ships, vehicles, military application, equipment affecting human life, body, and property, fuel equipment, entertainment equipment, emergency shut-off circuits, press clutches, brake circuits, safety equipment, etc., and use for applications that do not conform to standard specifications such as catalogs and operation manuals.
- 3. Use for interlock circuits, except for use with double interlock such as installing a mechanical protection function in case of failure. Please periodically inspect the product to confirm that the product is operating properly.

*1) ISO 4414: Pneumatic fluid power - General rules and safety requirements for systems and their components ISO 4413: Hydraulic fluid power - General rules and safety requirements for systems and their components IEC 60204-1: Safety of machinery - Electrical equipment of machines - Part 1: General requirements ISO 10218-1: Robots and robotic devices - Safety requirements for industrial robots - Part 1: Robots etc.

Caution

We develop, design, and manufacture our products to be used for automatic control equipment, and provide them for peaceful use in manufacturing industries.

Use in non-manufacturing industries is not covered.

Products we manufacture and sell cannot be used for the purpose of transactions or certification specified in the Measurement Act. The new Measurement Act prohibits use of any unit other than SI units in Japan.

Limited warranty and Disclaimer/ **Compliance Requirements**

The product used is subject to the following "Limited warranty and Disclaimer" and "Compliance Requirements".

Read and accept them before using the product.

Limited warranty and Disclaimer

- 1. The warranty period of the product is 1 year in service or 1.5 years after the product is delivered, whichever is first.*2) Also, the product may have specified durability, running distance or replacement parts. Please consult your nearest sales branch.
- 2. For any failure or damage reported within the warranty period which is clearly our responsibility, a replacement product or necessary parts will be provided. This limited warranty applies only to our product independently, and not to any other damage incurred due to the failure of the product.
- 3. Prior to using SMC products, please read and understand the warranty terms and disclaimers noted in the specified catalog for the particular products.

*2) Vacuum pads are excluded from this 1 year warranty. A vacuum pad is a consumable part, so it is warranted for a year after it is delivered. Also, even within the warranty period, the wear of a product due to the use of the vacuum pad or failure due to the deterioration of rubber material are not covered by the limited warranty.

Compliance Requirements

- 1. The use of SMC products with production equipment for the manufacture of weapons of mass destruction (WMD) or any other weapon is strictly prohibited.
- The exports of SMC products or technology from one country to another are governed by the relevant security laws and regulations of the countries involved in the transaction. Prior to the shipment of a SMC product to another country, assure that all local rules governing that export are known and followed.

Rev	visio	n History
Edition B * The remote type has been added. * Units with a flow adjustment valve have been added. * The 100 L/min type has been added. * The PVC piping type has been added. * Number of pages has been increased from 16 to 32.	PR	* Number of pages has been decreased from 32 to 28. Q Edition D * The PF3W7⊡-X445 has been added. * Number of pages has been increased from 28 to 36. W
Edition C * The 250 L/min type has been added. * The analog 4 to 20 mA 2-output type (-X128) has been added to made to order options. * The brass piping material specification (-X143) has been added to made to order options.		
A Safety Instructions Be sure to read the "Handling Pred	cauti	ons for SMC Products" (M-E03-3) and "Operation Manual" before us
SMC Corporation Akihabara UDX 15F, 4-14-1, Sotokanda, Chiyoda-ku, Tokyo 101-0021, JAPAN Phone: 03-5207-8249 Fax: 03-5298-5362 https://www.smcworld.com © 2023 SMC Corporation All Rights Reserved		
Specifications are subject to change without prior notice		D-G

and any obligation on the part of the manufacturer.