
# Fieldbus System (For Output)

### EX120/121/122 Series

#### **Compatible Protocols**

DeviceNet CC-Link CompoBus/S CompoNet\*

Made to Order S-Link V



**★**Compatible with a variety of communication networks


# **Manifold Solenoid Valves** VQ1000/2000 SY3000/5000/7000

EX121 Series

EX120 Series


SV1000/2000/3000/4000

SY3000/5000



EX122 Series

SY3000/5000



(€ CA

EX123/124/126

**EX500** 

**EX140** 

**EX510** 

ATEX

# CONTENTS

Type 1 Output type for solenoid valves

Fieldbus System (For Output) EX120/121/122 Series







| How to Order SI Unit ·····p. 1         | 79 |
|--|----|
| •                                      |    |
| Specifications ·····p. 1               | 74 |
| Dimensions/Parts Description ·····p. 1 | 75 |
| LED Indicator ·····p. 1                | 78 |
|  |    |

#### **Accessories**


| ① Communication Connector ······p.  | 179 |
|-------------------------------------|-----|
| 2 Power Supply Connector · · · · p. | 179 |

| viade to Order   |
|--|
| ① DeviceNet® PNP (Negative common) output,             |
| Occupied points: 16 inputs/16 outputs ····· p. 179     |
| ② DeviceNet® PNP (Negative common) output,             |
| Occupied points: 0 inputs/16 outputs p. 179            |
| 3 S-LINK V compatible NPN (Positive common) 16 outputs |
| p. 179   |
|  |
|  |

Specific Product Precautions .....p. 179

# Fieldbus System For Output EX120/121/122 Series ← CE

#### **How to Order SI Unit**



<sup>\*1</sup> DN1's occupied points are 16 inputs and 16 outputs, while DN1-X26 has 0 inputs and 16 outputs.



<sup>\*2</sup> A manifold part number is not specified for this model. Please contact SMC for the manifold integrated type.

#### **Specifications**

**Common Specifications** 

|                                     | opoomounomo                 |   | _ |
|-------------------------------------|-----------------------------|---|---|
| Communication                       | Terminating resistor        | Not provided  |   |
| Internal current consumption (Unit) |                             | 100 mA or less  |   |
|                                     | Enclosure                   | IP20  | 7 |
|                                     | Operating temperature range | 0 to 55°C (Valve 8 points ON)<br>0 to 50°C (Valve 16 points ON)                   |   |
| Environment                         | Operating humidity range    | 35 to 85%RH (No condensation)   | 1 |
|                                     | Withstand voltage           | 1500 VAC for 1 minute between whole external terminal and enclosure               |   |
|                                     | Insulation resistance       | $2\text{M}\Omega$ or more (500 VDC) between whole external terminal and enclosure |   |
|                                     |                             |   |   |

|               | Model                                | EX12□-SDN1   | EX12□-SDN1-X26                    | EX12□-SMJ1                                | EX12□-SCS1<br>EX12□-SCS2       |  |
|---------------|--------------------------------------|--|-----------------------------------|---|--------------------------------|--|
|               | Protocol                             | Devic  | DeviceNet®                        |   | OMRON Corp.:<br>CompoBus/S     |  |
|               | Version*1                            | Relea  | se 2.0                            | Ver. 1.10                                 | _                              |  |
| Communication | Communication speed                  | 125 k/250  | k/500 kbps                        | 156 k/625 kbps<br>2.5 M/5 M/10 Mbps       | 750 kbps                       |  |
|               | Configuration file*2                 | EDS  | 6 file                            | CSP+ file                                 | _                              |  |
|               | I/O occupation area (Inputs/Outputs) | 16/16  | 0/16                              | 32/32<br>(1 station, remote I/O stations) | SCS1: 0/16<br>SCS2: 0/8        |  |
| Power supply  | For control                          | 11 to 25 VDC   |                                   | 15 to 30 VDC                              | 14 to 26.4 VDC                 |  |
| voltage       | For valve                            |  | 24 VDC +10%/-5%                   |   |                                |  |
|               | Output type                          | Sink/NPN (Positive common)   |                                   |   |                                |  |
|               | Number of outputs                    |  |                                   | SCS1: 16 points<br>SCS2: 8 points         |                                |  |
| Output        | Load                                 | Solenoid valve with surge voltage suppressor 24 VDC, 2.1 W or less (SMC) |                                   |   |                                |  |
|               | Fail safe                            | CLEAR  | CLEAR HOLD/CLEAR (Switch setting) |   | HOLD/CLEAR<br>(Switch setting) |  |
| Standards     |                                      | CE/UKCA marking (EMC directive/RoHS directive)                           |                                   |   |                                |  |
| Weight        |                                      | EX120: 110 g or less, EX121: 140 g or less, EX122: 130 g or less         |                                   |   | ess                            |  |
| Accessory     |                                      | Communication connector 1 pc., Power supply connector 1 pc. —            |                                   |   | -                              |  |

st1 Please note that the version is subject to change.

<sup>\*2</sup> The setting file can be downloaded from the SMC website, http://www.smcworld.com

| Model         |                                      | EX12□-SCM1   | EX12□-SCM3                   |  |
|---------------|--------------------------------------|--|------------------------------|--|
|               | Protocol                             | CompoNet®  |                              |  |
|               | Communication speed                  | 93.75 kbps/1.5 M/3 M/4 Mbps  |                              |  |
| Communication | Configuration file                   | EDS  | file*1                       |  |
|               | I/O occupation area (Inputs/Outputs) | 0/16   |                              |  |
| Power supply  | For control                          | 14 to 26   | 6.4 VDC                      |  |
| voltage       | For valve                            | 24 VDC +10%/-5%  |                              |  |
|               | Output type                          | Sink/NPN (Positive common)   | Source/PNP (Negative common) |  |
| Outnut        | Number of outputs                    | 16 points  |                              |  |
| Output        | Load                                 | Solenoid valve with surge voltage suppressor 24 VDC, 2.1 W or less (SMC) |                              |  |
|               | Fail safe                            | HOLD/CLEAR (Setting via network)   |                              |  |
| Standards     |                                      | CE/UKCA marking (EMC directive/RoHS directive)                           |                              |  |
| Weight        |                                      | EX120: 100 g or less   |                              |  |
|               |                                      | EX121: 120 g or less   |                              |  |
|               |                                      | EX122: 110 g or less (including accessory)                               |                              |  |
| Accessory     |                                      | Power supply connector (EX9-CP2) 1 pc.*2                                 |                              |  |

<sup>\*1</sup> The setting file can be downloaded from the SMC website, http://www.smcworld.com

**SMC** 

6 EX260

X500 E

009X

EX245

1/122 EX2

lype 1

EX180

EX510


M8/M12


<sup>\*2</sup> Communication connector (for the opposite side) is not provided.

# EX120/121/122 Series


#### **Dimensions/Parts Description**


#### EX120 EX120-SDN1(-X26)







#### EX120-SMJ1, SCS□





#### EX120-SCM□






#### **Dimensions/Parts Description**

#### **EX121** EX121-SDN1(-X26) EX121-SMJ1, SCS□ Position indicator LED Position indicator LED Terminal block cover Terminal block cover 99999 MIL connector MIL connector Power supply connector (20 pins, socket) (20 pins, socket) (96 190 Communication connector Screw terminal block Tightening Tightening torque torque 0.6 N⋅m 0.6 N⋅m 8.09 60.8 $\otimes$ $\otimes$ $\overline{\Delta}$ $\otimes$ 10.2 28.8 9.5 28.8 DIN rail mounting bracket DIN rail mounting bracket EX121-SCM□ Position indicator LED Terminal block cover

PWR(V) MS NS



**EX260** 

EX123/124/126

**EX500** 

**EX600** 

**EX250** 

EX120/121/122

**EX140** 

EX180

**EX510** 

M8/M12


**ATEX** 


Type 2

# EX120/121/122 Series


#### **Dimensions/Parts Description**


#### EX122 EX122-SDN1(-X26)






#### EX122-SMJ1, SCS□






#### EX122-SCM□

**A** 177







# Fieldbus System For Output **EX120/121/122** Series

#### **LED Indicator**

#### EX12□-SDN1


#### EX12□-SMJ1






#### EX12□-SCS□

#### EX12□-SCM□





**SMC** 

126 EX260

0 EX123/124/126

EX600

EX245

EX250

EX140 EX120/121/122

EX180

Type 2 **EX510** 


M8/M12

### EX120/121/122 Series

#### Accessories (For EX12□-SCM□)


#### Communication Connector

Press-in connector for flat cables
Use this connector for the standard dedicated flat cable.
The communication connector does not come with this product.



Terminal block connector for round cables (VCTF)
Use this connector for the VCTF cable.


The communication connector does not come with this product.



#### Power Supply Connector


Straight type power supply connector This connector is supplied at the time of shipment.

EX9-CP2



T-branch type power supply connector This connector is not supplied at the time of shipment.

EX9-CP3




#### **Made to Order**

Please contact SMC for detailed specifications and lead times.

Prepare the SI unit and manifold valve (without SI unit) separately, and combine them before use.

1 DeviceNet® PNP (Negative common) output, Occupied points: 16 inputs/16 outputs



 $\bullet$  Dimensions are the same as those of the standard type.

② DeviceNet® PNP (Negative common) output, Occupied points: 0 inputs/16 outputs

•Valve interface

O Plug-in

1 Flat ribbon cable DIN rail mounting

Plug-in DIN rail mounting

Dimensions are the same as those of the standard type.

3 S-LINK V compatible NPN (Positive common) 16 outputs

EX120-SSL1-X99

• Dimensions are the same as those of the CC-Link (EX120-SMJ1).

# **▲ Specific Product Precautions**

Be sure to read this before handling the products. Refer to page 277 for safety instructions. For fieldbus system
 precautions, refer to pages 278 to 280 and the "Operation Manual" on the SMC website: http://www.smcworld.com

#### **Operating Environment**

#### **⚠Warning**

 Do not use this product in the presence of dust, particles, water, chemicals, and oil. Use around such materials is likely to cause a malfunction or breakage.

#### ■ Trademark

DeviceNet® is a registered trademark of ODVA, Inc. CompoNet® is a registered trademark of ODVA, Inc.



# Fieldbus System (For Output)

# EX124/126 Series

**Compatible Protocols** 

DeviceNet CC-Link CompoBus/S

Made to Order CompoNet


- **★Enclosure IP65 (EX124), IP67 (EX126)**
- **★**Maximum 16 outputs



**EX500** 

**EX140** 

**EX510** 



# CONTENTS

Type 1 Output type for solenoid valves

Fieldbus System (For Output) **EX124/126** Series






| LLD malcator  | p. 52                    |
|---|--------------------------|
| Accessories  • Replacement Fuse ·····  • Drip Proof Plug Assembly ·····   | -                        |
| Made to Order  ① DeviceNet® PNP (Negative common), Occupied points: 16 inputs/16 outputs ······ ② DeviceNet® PNP (Negative common), Occupied points: 0 inputs/16 outputs ····· ③ CompoNet® ····· ④ Signal Cut Block ····· | ···· p. 53<br>···· p. 53 |
| Specific Product Precautions ·····  | ····· p. 53<br>48 @      |

How to Order SI Unit ·····


Specifications ······ Dimensions/Parts Description .....p. 51

# Fieldbus System For Output EX124/126 Series (€ ८६)

#### **How to Order SI Unit**



<sup>\*1</sup> DN1's occupied points are 16 inputs and 16 outputs, while DN1-X26 has 0 inputs and 16 outputs.



#### **Specifications**

#### **Common Specifications**

| Communication                       | Terminating resistor     | Not provided  | ٦ |
|-------------------------------------|--------------------------|---|---|
| Internal current consumption (Unit) |                          | 100 mA or less  |   |
| Out-out                             | Output type              | Sink/NPN (Positive common)  |   |
| Output                              | Load                     | Solenoid valve with surge voltage suppressor 24 VDC, 2.1 W or less (SMC)          |   |
|                                     | Operating temperature    | 0 to 55°C (Valve 8 points ON)   |   |
| Fundanamental                       | range                    | 0 to 50°C (Valve 16 points OŃ)  |   |
| Environmental<br>resistance         | Operating humidity range | 35 to 85%RH (No condensation)   |   |
| 10313tall00                         | Withstand voltage        | 1500 VAC for 1 minute between whole external terminal and enclosure               |   |
|                                     | Insulation resistance    | $2\text{M}\Omega$ or more (500 VDC) between whole external terminal and enclosure |   |
| Weight                              |                          | 240 g or less   |   |
| Accessory                           |                          | 4 unit mounting screws (M4 x 10)  |   |

| Model             |                                      |           | EX124□-SDN1          | EX124□-SDN1-X26* <sup>3</sup> |
|-------------------|--------------------------------------|-----------|----------------------|-------------------------------|
|                   | Applicable                           | Protocol  | DeviceNet®           | DeviceNet <sup>®</sup>        |
|                   | system                               | Version*1 | Relea                | se 2.0                        |
| Communication     | Communication speed                  |           | 125 k/250            | k/500 kbps                    |
|                   | Configuration file*2                 |           | EDS                  | S file                        |
|                   | I/O occupation area (Inputs/Outputs) |           | 16/16                | 0/16                          |
| Power supply      | <u> </u>                             |           | 11 to 2              | 5 VDC                         |
| voltage           | For valve                            |           | 24 VDC +             | 10%/–5%                       |
| Number of outputs |                                      | f outputs | 16 p                 | oints                         |
| Output            | Fail safe                            |           | CLEAR                | HOLD/CLEAR (Switch setting)   |
| Environment       | nment Enclosure II                   |           | IP                   | 65                            |
| Standards         |                                      |           | CE/UKCA marking (EMC | directive/RoHS directive)     |

|  | Model                  |                       | EX124□-SMJ1                               | EX124□-SCS1<br>EX124□-SCS2        | EX126D-SMJ1                               |
|--|------------------------|-----------------------|---|-----------------------------------|---|
|  | Applicable             | Protocol              | CC-Link                                   | OMRON Corp.: CompoBus/S           | CC-Link                                   |
|  | system                 | Version*1             | Ver. 1.10                                 | <del>_</del>                      | Ver. 1.10                                 |
| Communication  | Communication spec     | cation speed          | 156 k/625 kbps<br>2.5 M/5 M/10 Mbps       | 750 kbps                          | 156 k/625 kbps<br>2.5 M/5 M/10 Mbps       |
|  | Configuration file*2   |                       | CSP+ file                                 | <del></del>                       | CSP+ file                                 |
|  | I/O occup<br>(Inputs/O | ation area<br>utputs) | 32/32<br>(1 station, remote I/O stations) | SCS1: 0/16<br>SCS2: 0/8           | 32/32<br>(1 station, remote I/O stations) |
| Power supply   | For contr              | ol                    | 15 to 30 VDC                              | 14 to 26.4 VDC                    | 15 to 30 VDC                              |
| voltage  | For valve              |                       | 24 VDC +10%/-5%                           |                                   |   |
| Output   | Number o               | of outputs            | 16 points                                 | SCS1: 16 points<br>SCS2: 8 points | 16 points                                 |
|  | Fail safe              |                       | CLEAR                                     | HOLD/CLEAR (Switch setting)       | CLEAR                                     |
| Environment  | Enclosure              | 9                     | IP65                                      |                                   | IP67                                      |
| Standards CE/UKCA marking (EMC directive/RoHS directive) |                        |                       | ective)                                   |                                   |   |

<sup>\*1</sup> Please note that the version is subject to change.

**SMC** 

**EX600** 

**EX140** 

EX510

<sup>\*2</sup> The setting file can be downloaded from the SMC website, http://www.smcworld.com


<sup>\*3</sup> Since this is a special product, a manifold part number is not specified. Please consult SMC for the manifold integrated type.


\* For detailed specifications other than the above, refer to the operation manual that can be downloaded from SMC website, http://www.smcworld.com

### **EX124/126** Series


#### **Dimensions/Parts Description**

#### **EX124**□-**S**□□□







#### Housing cover diagram





\* The housing cover of the EX124U/D-SMJ1 is the same as that of the EX126D-SMJ1.

#### EX126D-SMJ1











#### Housing cover diagram






#### **LED Indicator**


#### EX124□-SDN1




#### EX124□-SMJ1



#### EX124□-SCS□



#### EX126D-SMJ1



#### **Accessories**

#### Replacement Fuse

A replacement fuse for the EX126D-SMJ1

#### **EX9-FU20**

| Applicable model | EX126D-SMJ1 |
|------------------|-------------|
| Rated current    | 2.0 A       |



#### 2 Drip Proof Plug Assembly

Use when the wiring entry (G1/2) is not being used. Incorrect handling of the wiring entry may allow foreign matter to enter the SI unit, which will lead to a malfunction and damage to the SI unit.

#### AXT100-B04A

Type 1 EX123/124/126 **EX** 

EX500

EX600

EX245

EX120/121/122

**EX250** 

EX140 E

EX180

EX510

M8/M12

#### **Made to Order**

Please contact SMC for detailed specifications and lead times. Prepare the SI unit, signal cut block, and manifold valve (without SI unit) separately, and combine them before use.



#### 1) DeviceNet® PNP (Negative common), Occupied points: 16 inputs\*1/16 outputs

EX124 U -SDN1-X2

#### Mounting specifications

- Wount a unit to the U side of the manifoldMount a unit to the D side of the manifold
- Dimensions are the same as those of the standard type.

- \*1 The SI unit cannot be connected to an input device but occupies memory areas of 16 input points (2 bytes) as a mirror function of output data.
  - The mirror function is used to transmit output data received by the SI unit as input data exactly as it is.

#### ② DeviceNet® PNP (Negative common), Occupied points: 0 inputs/16 outputs

EX124 U -SDN1-X77

#### Mounting specifications

- U Mount a unit to the U side of the manifoldD Mount a unit to the D side of the manifold
- Dimensions are the same as those of the standard type.


#### 3 CompoNet®

• Please contact SMC for details.

#### 4 Signal cut block

#### **EX9-SC1-8**

- A switch unit that forcibly turns OFF the output signal to the valve by means
  of a toggle switch operation in double 1-station units
- Open the switch guard to prevent misoperation, and then carry out the operation.
- It comes with a safety mechanism which returns the switch to the normal position (AUTO) after the switch guard is closed.
- Enclosure: IP67



# Cover open Switch guard (Part no.: EX9-HCDSC1-X42) Connector connection Hook Switch guard (Part no.: EX9-HCDSC1-X42) Press the lever to open the switch guard, press the lever and attach the hook.

### 

Be sure to read this before handling the products. Refer to page 277 for safety instructions. For fieldbus system precautions, refer to pages 278 to 280 and the "Operation Manual" on the SMC website: http://www.smcworld.com

#### ■ Trademark

DeviceNet® is a registered trademark of ODVA, Inc. CompoNet® is a registered trademark of ODVA, Inc.

#### Operating Environment

#### 

1. Select the proper type of enclosure according to the operating environment.

IP65/67 is achieved when the following conditions are met.

- 1) Provide appropriate wiring between all units using electrical wiring cables and communication connectors cables.
- 2) For wiring, use a G1/2 cable gland.
- 3) Appropriately mount each unit and valve manifold.
- 4) Be sure to install a drip proof plug assembly (AXT100-B04A) on each unused connector. This is to prevent the risk of the SI unit malfunctioning or breaking down.

If using in an environment that is exposed to water splashes, please take measures such as using a cover.



# Fieldbus System (For Output)

# EX140 Series


**Compatible Protocols** 

**DeviceNet** CC-Link CompoBus/S



**EX500** 

- **★**Thinner unit with low height
- **★**Maximum 16 outputs



# CONTENTS

Type 1 Output type for solenoid valves

Fieldbus System (For Output)

EX140 Series



| How to Order SI Unit ·····p. 1          | 81 |
|---|----|
| Specifications ·····p. 1                | 81 |
| Dimensions/Parts Description ······p. 1 | 82 |
| _ED Indicator ·····p. 1                 | 83 |
| Specific Product Precautions ·····p. 1  | 83 |



**EX510** 

# Fieldbus System For Output EX140 Series (EXA

#### **How to Order SI Unit**

EX140-S DN1

#### Protocol

| DN1 | DeviceNet®                           |
|-----|--------------------------------------|
| MJ1 | CC-Link                              |
| CS1 | OMRON Corp.: CompoBus/S (16 outputs) |
| CS2 | OMRON Corp.: CompoBus/S (8 outputs)  |

#### **Specifications**

| Model                       |                                      |               | EX140-SDN1   | EX140-SMJ1                                | EX140-SCS1<br>EX140-SCS2   |  |  |
|-----------------------------|--------------------------------------|---------------|--|---|----------------------------|--|--|
| Communication               | Applicable system                    | Protocol      | DeviceNet®   | CC-Link                                   | OMRON Corp.:<br>CompoBus/S |  |  |
|                             | System                               | Version*1     | Release 2.0  | Ver. 1.10                                 | <del>_</del>               |  |  |
|                             | Communication speed                  |               | 125 k/250 k/500 kbps   | 156 k/625 kbps<br>2.5 M/5 M/10 Mbps       | 750 kbps                   |  |  |
| E                           | Configuration file*2                 |               | EDS file   | CSP+ file                                 | _                          |  |  |
| Cor                         | I/O occupation area (Inputs/Outputs) |               | 0/16   | 32/32<br>(1 station, remote I/O stations) | SCS1: 0/16<br>SCS2: 0/8    |  |  |
|                             | Terminating resistor                 |               | Not provided   |   |                            |  |  |
| Power supply                | For control                          |               | 11 to 25 VDC   | 15 to 30 VDC                              | 14 to 26.4 VDC             |  |  |
| voltage                     | voltage For valve                    |               | 24 VDC +10%/-5%  |   |                            |  |  |
| Internal c                  | Internal current consumption (Unit)  |               | 100 mA or less   |   |                            |  |  |
|                             | Output type                          |               | Sink/NPN (Positive common)   |   |                            |  |  |
| Output                      | Number of outputs                    |               | 16 ou  | SCS1: 16 outputs<br>SCS2: 8 outputs       |                            |  |  |
| Out                         | Load                                 |               | Solenoid valve with surge voltage suppressor 24 VDC, 2.1 W or less (SMC)           |   |                            |  |  |
|                             | Fail safe                            |               | HOLD/CLEAR<br>(Switch setting)   |   |                            |  |  |
| Environmental<br>resistance | Enclosure                            |               | IP20   |   |                            |  |  |
|                             | Operating to range                   | emperature    |  |   |                            |  |  |
|                             | Operating h                          | umidity range | 35 to 85%RH (No condensation)  |   |                            |  |  |
|                             | Withstand v                          | oltage        | 1500 VAC for 1 minute between whole external terminal and enclosure                |   |                            |  |  |
|                             | Insulation re                        | esistance     | $2~\text{M}\Omega$ or more (500 VDC) between whole external terminal and enclosure |   |                            |  |  |
| Standards                   |                                      |               | CE marking (EMC directive/RoHS directive)  |   |                            |  |  |
| Weight                      |                                      |               | 80 g or less   |   |                            |  |  |
| Accessory                   |                                      |               | Communication connector 1 pc.,<br>Power supply connector 1 pc.                     | _   |                            |  |  |

<sup>\*1</sup> Please note that the version is subject to change.


<sup>\*</sup> For detailed specifications other than the above, refer to the operation manual that can be downloaded from SMC website, http://www.smcworld.com





<sup>\*2</sup> The setting file can be downloaded from SMC website, http://www.smcworld.com

#### **Dimensions/Parts Description**


#### **EX140-SDN1**









#### EX140-SMJ1, SCS□







EX123/124/126

**EX600** 

EX120/121/122


# EX140 Series

#### **LED Indicator**


#### **EX140-SDN1**

# POWER: Power supply for control MOD/NET: Connection state MOD/NET: Connection state MOD/NET: Connection state SERIAL UNIT EX140-SDN1 DeviceNet Solemote Ex24V OV V-CANL FG (ANH V+ DeviceNet Solemote Ex22 D DEVICENET Ex22 D

#### **EX140-SMJ1**



#### EX140-SCS□



# **△ Specific Product Precautions**

Be sure to read this before handling the products. Refer to page 277 for safety instructions. For fieldbus system I precautions, refer to pages 278 to 280 and the "Operation Manual" on the SMC website: http://www.smcworld.com

#### **Operating Environment**

#### **∆**Warning

1. Do not use this product in the presence of dust, particles, water, chemicals, and oil. Use around such materials is likely to cause a malfunction or breakage.

#### **■** Trademark

DeviceNet® is a registered trademark of ODVA, Inc.



# Fieldbus System (For Output)

# EX180 Series

**Compatible Protocols** 

DeviceNet CC-Link


Made to Order AnyWireASLINK







- **★**Thinner unit with low height
- **★**Maximum 32 outputs



# CONTENTS

Type 1 Output type for solenoid valves

Fieldbus System (For Output)

EX180 Series



| Dimensions/Parts Descriptionp. 186 LED Indicator                 |
|--|
| Accessories  Ommunication Connector                              |
| Made to Order  ① AnyWireASLINK NPN (Positive common), 32 outputs |
| Specific Product Precautionsp. 188                               |

How to Order SI Unit ......p. 185

**Specifications** ......p. 185

24/126 EX3

0 EX123/

EX500

EX2

EX120/121/122

EX140

EX510

EX180


/M12

# Fieldbus System For Output EX180 Series





#### **How to Order SI Unit**



Communication and power supply connectors are included.

#### **Specifications**

| Model                       |                                      |                               | EX180-SDN3<br>EX180-SDN4                                       | EX180-SDN5<br>EX180-SDN6             | EX180-SMJ3  | EX180-SMJ5 |  |
|-----------------------------|--------------------------------------|-------------------------------|--|--------------------------------------|---|------------|--|
| Communication               | Applicable system                    | Protocol                      | DeviceNet®   |                                      | CC-Link   |            |  |
|                             |                                      | Version*1                     | Release 2.0  |                                      | Ver. 1.10   |            |  |
|                             | Communication speed                  |                               | 125 k/250 k/500 kbps   |                                      | 156 k/625 kbps<br>2.5 M/5 M/10 Mbps                       |            |  |
|                             | Configuration file*2                 |                               | EDS file   |                                      | CSP+ file   |            |  |
|                             | I/O occupation area (Inputs/Outputs) |                               | SDN3: 0/32<br>SDN4: 0/16                                       | SDN5: 0/32<br>SDN6: 0/16             | 32/32 (1 station)   |            |  |
|                             | Terminating resistor                 |                               | Not provided   |                                      | Built into the unit (Switch setting, 110 $\Omega$ )       |            |  |
| Power supply                | Power supply For control             |                               | 11 to 25 VDC   |                                      | 24 VDC ±10%   |            |  |
| voltage For valve           |                                      |                               | 24 VDC ±10%/-5%  |                                      |   |            |  |
| Internal cu                 | rrent consump                        | tion (Unit)                   | 0.1 A or less  |                                      |   |            |  |
|                             | Output type                          |                               | Sink/NPN (Positive common)                                     | Source/PNP (Negative common)         | Sink/NPN (Positive common)   Source/PNP (Negative common) |            |  |
| <b>5</b>                    | Number of outputs                    |                               | SDN3: 32 outputs<br>SDN4: 16 outputs                           | SDN5: 32 outputs<br>SDN6: 16 outputs | 32 outputs  |            |  |
| Output                      | Load                                 |                               | SY3000/5000/7000, SJ2000/3000, S0700 series<br>manifold valves |                                      |   |            |  |
|                             | Fail safe                            |                               | HOLD/CLEAR<br>(Switch setting)                                 |                                      |   |            |  |
| la (                        | Enclosure                            |                               |  | IP20                                 |   |            |  |
| Environmental<br>resistance | Operating ten                        | nperature range               |  | –10 to                               | 50°C  |            |  |
|                             | Operating hui                        | midity range                  | 35 to 85%RH (No condensation)                                  |                                      |   |            |  |
|                             | Withstand vol                        | Itage                         | 500 VAC for 1 minute between whole external terminal and FG    |                                      |   |            |  |
| 튭_                          | Insulation res                       | istance                       | 10 MΩ  | or more (500 VDC) between            | en whole external terminal and FG                         |            |  |
| Standards                   |                                      |                               | CE marking (EMC directive/RoHS directive), UL (CSA)            |                                      |   |            |  |
| Weight                      |                                      |                               | 110 g or less (including accessory)                            |                                      |   |            |  |
| Accessory                   |                                      | Communication Power supply of |  |                                      | n connector 1 pc.,<br>connector 2 pcs.                    |            |  |

<sup>\*1</sup> Please note that the version is subject to change.

<sup>\*</sup> The EX180-SMJ1□ cannot be mounted on the manifold for the EX180-SMJ3□/5□. Additionally, the EX180-SMJ3□/5□ cannot be mounted on the manifold for the EX180-SMJ1□.




<sup>\*2</sup> The setting file can be downloaded from SMC website, https://www.smcworld.com

<sup>\*</sup> For detailed specifications other than the above, refer to the operation manual that can be downloaded from SMC website, https://www.smcworld.com


<sup>\*</sup> The EX180-SDN1□/2□ cannot be mounted on the manifold for the EX180-SDN3□/4□/5□/6□. Additionally, the EX180-SDN3□/4□/5□/6□ cannot be mounted on the manifold for the EX180-SDN1□/2□.

#### **Dimensions/Parts Description**

#### EX180-SDN□



#### EX180-SMJ□



EX123/124/126 EX260

EX500

EX600

EX250 EX2

EX140 EX120/121/122

:X180

EX510

M8/M12


### EX180 Series

#### **LED Indicator**

# PWR(V): Power supply for valve PWR: Power supply for control PWR: Power supply for control MNS: Connection state

tovovovov


#### EX180-SMJ□




#### **Accessories**

#### **1** Communication Connector

Connector for the network cable This connector is supplied at the time of shipment.









EX180-C□□2

Power Supply Connector

Connector for power supply
This connector is supplied at the time of shipment.

**EX180-CP1** 




#### **Made to Order**

Please contact SMC for detailed specifications and lead times. Prepare the SI unit and manifold valve (without SI unit) separately, and combine them before use.

#### 1) AnyWireASLINK NPN (Positive common), 32 outputs

#### EX180-SAW1-X237



# **▲ Specific Product Precautions**

I Be sure to read this before handling the products. Refer to page 277 for safety instructions. For fieldbus system I precautions, refer to pages 278 to 280 and the "Operation Manual" on the SMC website: http://www.smcworld.com

#### **Operating Environment**

#### **≜**Warning

1. Do not use this product in the presence of dust, particles, water, chemicals, and oil. Use around such materials is likely to cause a malfunction or breakage.

#### **■** Trademark

DeviceNet® is a registered trademark of ODVA, Inc.

**SMC** 

ype 1 6 EX260

D EX123/124/

Type 2 EX500

EX600

EX24

EX250

EX120/121/122

140