Valve Mounted Cylinder

CV□ Series

Ø10, Ø16, Ø20, Ø25, Ø32, Ø40, Ø50, Ø63, Ø80, Ø100


Series Variations Standard variations Bore size Page Series Action Built-in cushion One-touch fitting auto switch CVJ5 series 10 P.1154 Double acting 16 CVJ3 series Single acting 10 P.1164 (Spring return) 16 (Spring extend) CVM5/CVM5K 20 series P.**1175** 25 Double acting 32 P.**1185** Nonrotating 40 rod CVM3/CVM3K Standard series Single acting P.1194 25 (Spring return) 32 P.1207 Non-(Spring extend) rotating 40 rod CV3/CV3K series 40 · 50 63 · 80 P.1216 Standard Double acting Non-40 · 50 P.**1228** rotating rod CVS1 series 40 · 50 63 · 80 P.1238 Double acting 100

Valve Mounted Cylinder Double Acting, Single Rod

CVJ5 Series

ø10, ø16

How to Order



		Electrical entry	ight			Load v	oltage		Auto swit	ch model		Lea	d wir	e ler	igth i	(m)																						
Туре	Special function			Indicator light	Wiring (Output)		DC	AC	Band m	ounting	Rail mo	ounting	0.5	1	3	5	None	Pre-wired connector	Applical	ble load																		
		Cilly	Indic	(Output)		DC	AC	Perpendicular	In-line	Perpendicular	In-line	(Nil)	(M)	(L)	(Z)	(N)	CONTRECTOR																					
				3-wire (NPN)				M9NV	M9N	_	_	•	•	lacksquare	0	I —	0																					
				3-WITE (INFIN)		5 V,		_	_	F7NV	F79	•		•	0	I —	0	IC circuit																				
		Grommet		3-wire (PNP)		12 V		M9PV	M9P	_	_	•	•	•	0	_	0	ic circuit																				
		Gionnine		3-WIE (FINE)				_	_	F7PV	F7P	•			0	_	0																					
_								M9BV	M9B	_	_	•	•	•	0	_	0																					
switch				2-wire		12 V		_	_	F7BV	J79	•	-	•	0	_	0	_																				
S		Connector						_	H7C	J79C	_	•		•	•	•																						
anto		1 1																				1	3-wire (NPN)				M9NWV	M9NW	_	_	•	•	•	0	_	0		Relay,
a	Diagnostic indication (2-color indicator)		Yes	Yes	Yes	Yes	Yes	Yes	Yes	Yes	Yes	Yes	Yes	Yes	Yes	Yes	Yes	Yes	o-wire (INPIN)	24 V	5 V,	_	_	_	F7NWV	F79W	•	-	•	0	_	0	IC circuit	PLC				
state				3-wire (PNP)	2.wiro (DND)	2-wiro (DND)	3-wire (PNP)		12 V		M9PWV	M9PW	_	_	•	•	•	0	-	0	IO CIICUII	. 20																
g							_		_	_	_	F7PW	•		•	0	-	0																				
Solid					l L											2-wire		12 V	M9BWV	M9BW	_	_	•	•	•	0	_	0										
0)																								_	_	F7BWV	J79W	•	_	•	0	_	0					
																								3-wire (NPN)		5 V,			M9NA*1	_	_	0	0	•	0	_	0	IC circuit
	Water resistant (2-color indicator)			3-wire (PNP)		12 V	M9PAV*1	M9PA*1	_	_	0	0	•	0	_	0	io circuit	1																				
	,,			2-wire		12 V		M9BAV*1	M9BA*1	_	_	0	0	•	0	_	0	_																				
	With diagnostic output (2-color indicator)			4-wire (NPN)		5 V, 12 V		_	H7NF	_	F79F	•	_	•	0	_	0	IC circuit																				
چ				3-wire (NPN equivalent)	_	5 V	_	A96V	A96	_	A76H	•	<u> </u>	•	_	_	_	IC circuit	_																			
switch		Grommet	Yes	Yes			_	200 V	_	_	A72	A72H	•	_	•	_	_																					
S		Gionnine					100 V	A93V*2	A93	A73	A73H	•	•	•	•	_	_																					
auto		1	No	2-wire		12 V	100 V or less	A90V	A90	A80	A80H	•	_	•	_	_	_	IC circuit	Relay,																			
a		Connector	Yes	2-WIIE	24 V	12 V	_		C73C	A73C	_	•	_	•	•	•	_	_	PLĊ																			
Reed			No				24 V or less	_	C80C	A80C	_	•	三	•	•	•	_	IC circuit]																			
ш.	Diagnostic indication (2-color indicator)	Grommet	Yes			_	_		_	A79W	_	•	I-	•	_	_		_																				

^{*} Lead wire length symbols: 0.5 m Nil (Example) M9NW (Example) M9NWM 1 m M (Example) M9NWL

- 5 m..... 7 (Example) M9NWZ * Solid state auto switches marked with "O" are produced upon receipt of order.
- * D-A9□/M9□/A7□□/A80□/F7□□/J7□□ auto switches are shipped together (not assembled). (For D-A9□/M9□, only auto switch mounting brackets are assembled before shipped.)

 ► D-C7□□/C80□/H7□□ auto switches are assembled at the time of shipment.
- * Order auto switch mounting brackets separately when D-A9\(\times \text{(V)/M9\(\times \text 1163 for details
- *1 Water resistant type auto switches can be mounted on the above models, but in such case SMC cannot guarantee water resistance. Consult with SMC regarding water resistant types with the above model number

^{*} Since there are other applicable auto switches than listed, refer to page 1163 for details. * For details about auto switches with pre-wired connector, refer to pages 1410 and 1411.


^{*2 1} m type lead wire is only applicable to D-A93.

Operation type can be changed to rod extended when energized or rod retracted when energized.

An auto switch cylinder with the switch installed can also be manufactured.



Symbol Double acting/Single rod, Rubber bumper





0 1 1	0 '' '
Symbol	Specifications
-XA□	Change of rod end shape

Specifications

Bore size (mm)	ø10	ø 16		
Action	tion Double acting, Single rod			
Fluid	А	ir		
Proof pressure	1.05	MPa		
Maximum operating pressure	0.7	MPa		
Minimum operating pressure	0.15 MPa			
Ambient and fluid temperature	perature -10 to 50°C (No freezing)			
Cushion	Rubber bumper Not required (Non-lube)			
Lubrication				
Stroke length tolerance	+ 1.0			
Port size	M5 x 0.8			
Mounting	Basic type, Axial foot type, Rod side flange ty			
Piston speed	50 to 750 mm/s	50 to 150 mm/s		
Allowable kinetic energy	0.035J	0.090J		

Solenoid Valve Specifications

Applicable solenoid val	ve mod	el	SYJ3190		
Electrical entry			Grommet (G), L plug connector (L), M plug connector (M)		
0-11		DC	24, 12, 6, 5, 3		
Coil rated voltage (V)	AC 50/60 Hz		100, 110, 200, 220		
Effective area of valve (Cv facto	or)	1.8 mm ² (0.1)		
Allowable voltage			±10% of the rated voltage*		
Power consumption (W) DC Standard		Standard	0.35 (With indicator light: 0.4)		
		100 V	0.78 (With indicator light: 0.81)		
*		110 V [115 V]	0.86 (With indicator light: 0.89) [0.94 (With indicator light: 0.97)]		
Apparent power (VA)*	AC	200 V	1.18 (With indicator light: 1.22)		
		220 V [230 V]	1.30 (With indicator light: 1.34) [1.42 (With indicator light: 1.46)]		
Surge voltage suppressor			Diode (Varistor for the non-polar type)		
Indicator light			LED		

- * 110 VAC and 115 VAC types and 220 VAC and 230 VAC types are common respectively.

 * For 115 VAC and 230 VAC, allowable voltage fluctuation is –15 to +5 % of the rated voltage.

 * For S and Z, the voltage will drop due to the internal circuit. Allowable voltage fluctuation must be in the
- range below. Types S, Z 24 VDC: -7 to 10 %, 12 VDC: -4 to 10 %

Standard Stroke

(m	m	١
١.		•••	7

	/·····
Bore size (mm)	Standard stroke
10	15, 30, 45, 60
16	15, 30, 45, 60

^{*} If types for more than the strokes indicated in the table above (61 strokes) are required, please ask SMC.

Mounting Type and Accessory/For details, refer to page 1159.

	Mounting	Basic type	Axial foot type	Rod side flange type
Standard equipment	Mounting nut	•	•	•
Stan	Rod end nut	•	•	•
Option	Single knuckle joint	0	0	0
g	Double knuckle joint (With pin)*	0	0	0

* Knuckle pin and retaining ring are shipped ... Supplied with the product. O---Please order senarately together

Weight					
Bore size (mm)	10	16			
Basic weight*	71	99			
Additional weight per each 15 mm of stroke	6.5	9.5			

19

13

5

Rod side flange type * Mounting nut and rod end nut are included in the basic weight.

Calculation: (Example) CVJ5L10-45-1G

Basic weight-----71 (g) (Ø10)

Axial foot type

- Additional weight -----6.5/15 stroke
- Cylinder stroket ······45 stroke
- · Weight of bracket7 (g) (Axial foot type)

 $71 + 6.5/15 \times 45 + 7 = 97.5 q$

Mounting Bracket Part No.

Mounting bracket	Bore size (mm)				
Woulding bracket	10	16			
Foot	CJ-L010C	CJ-L016C			
Flange	CJ-F010C	CJ-F016C			

Accessory (Option)

Refer to page 1159 for part numbers and dimensions of the single knuckle joint, double knuckle joint, knuckle pin, mounting nut, and rod end nut.

Changing between Rod Extended when Energized and Rod Retracted when Energized


<Step>

Mounting


bracket weight

This procedure is for changing the rod extended when energized to the rod retracted when energized.


1. Using a screwdriver, loosen the two small round head screws, and remove the plate and the solenoid valve. At this time, instead of removing the plate and the solenoid valve separately, remove them together, with the round head screws remaining inserted




2. Turn the pipe gasket at 180° and mount, showing the letter "B".




3.Install the solenoid valve and the plate, and tighten the small round head screws, with a screw driver. After tightening, press the manual button on the solenoid valve, check for any air leaks, and verify the operating conditions. When the cylinder is viewed from above, the position of the gasket is as shown in the figure below.





Manual Operation

Manual operation is possible by pushing the manual button indicated with the arrow.



Specific Product Precautions

Be sure to read this before handling the products. Refer to I page 9 for safety instructions, pages 10 to 19 for actuator I and auto switch precautions, and 3/4/5-port solenoid valve I I precautions on the SMC website:https://www.smcworld.com I

Handling Precautions

∕ Caution

1. During installation, secure the rod cover and tighten the mounting nut or the rod cover body by applying an appropriate tightening force.

If the head cover is secured or the head cover is tightened. the cover may rotate, leading to the deviation.

2. Tighten the mounting screws with an appropriate tightening torque within the range given below.

ø6: 2.1 to 2.5 N·m, ø10: 5.9 to 6.4 N·m ø16: 10.8 to 11.8 N·m

3. To remove and install the retaining ring for the knuckle pin or the clevis pin, use an appropriate pair of pliers (tool for installing a type C retaining ring).

In particular, use a pair of ultra-mini pliers for removing and installing the retaining rings on the ø10 cylinder.

4. For the auto switch mounting rail, do not remove the pre-equipped rail.

Since the mounting thread is drilled through inside the cylinder, it may cause air leakage.

∕∿Warninɑ


1. Confirm the specifications.

Products in this catalog are designed to be used for compressed air systems. If not operated within the designated pressure or temperature, it may damage the products or cause malfunction. (Refer to specifications.)

2. Energizing continuously for a long period of time

When the valve is continuously energized for a long period of time, the performance may deteriorate, shorten the service life or effect peripheral equipment adversely since temperature rises when coils generate heat.

Construction/(Not able to disassemble.)



Component Parts

No.	Description	Material	Note
1	Rod cover	Aluminum alloy	Clear anodized
2	Head cover	Aluminum alloy	Clear anodized
3	Cylinder tube	Stainless steel	
4	Piston rod	Stainless steel	
5	Piston	Aluminum alloy	Chromated
6	Mounting nut	Brass	Nickel plated
7	Rod end nut	Rolled steel	Zinc chromated
8	Bumper	Urethane	
9	Steel ball	Carbon steel	
10	Stud	Brass	Electroless nickel plated
11	Phillips screw	Rolled steel	Zinc chromated

No.	Description	Material	Note
12	Plate	Zinc alloy	
13	Solenoid valve	_	* Refer to the note below.
14	Pipe	Aluminum alloy	Clear anodized
15	Piston seal	NBR	
16	Rod seal	NBR	
17	Tube gasket	NBR	
18	Piston gasket	NBR	
19	Gasket	NBR + Stainless steel 304	
20	Pipe gasket	NBR	
21	Plate gasket	NBR	


^{*} How to order solenoid valves

SYJ3190 - .

Rated voltage Light/surge voltage suppressor Electrical entry

Basic Type (B)

CVJ5




*[]:	Denotes	the	values	of AC.
----	----	---------	-----	--------	--------

*[]: Denotes t	[]: Denotes the values of AC.													
Bore size	Α	В	С	D	F	Н	нх	MM	NA	NB	ND	NN	S	Z
10	15	12	14	4	8	28	35	M4 x 0.7	12.5	9.5	8 _0.022	M8 x 1	46	90 [91]
16	15	18	20	5	8	28	41	M5 x 0.8	12.5	9.5	10 _0.022	M10 x 1	47	91 [92]

CVJ5 Series

Axial Foot Type (L)

CVJ5L



Rod End Nut

Bore size (mm)	Вı	Нı		
10	7	3.2		
16	8	4		


*[]: Denotes the values of AC

0 | 8 | 4

[]. Donote	(IIIII												(111111)								
Bore size	Α	В	С	D	F	Н	LA	LC	LH	LT	LX	LY	LZ	MM	NA	NB	NN	S	Х	Υ	Z
10	15	12	14	4	8	28	38	4.5	9	1.6	24	16.5	32	M4 x 0.7	12.5	9.5	M8 x 1	46	5	7	90 [91]
16	15	18	20	5	8	28	46	5.5	14	2.3	33	25	42	M5 x 0.8	12.5	9.5	M10 x 1	47	6	9	91 [92]

Rod Side Flange Type (F)

CVJ5F



Rod End Nut

Bore size (mm)	B ₁	H ₁	
10	7	3.2	
16	8	4	

*[]: Denotes the values of AC.

[]	(1111)																	
Bore size	Α	В	С	D	F	FC	FT	FX	FY	FZ	Н	нх	MM	NA	NB	NN	S	Z
10	15	12	14	4	8	4.5	1.6	24	14	32	28	35	M4 x 0.7	12.5	9.5	M8 x 1	46	90 [91]
16	15	18	20	5	8	5.5	2.3	33	20	42	28	41	M5 x 0.8	12.5	9.5	M10 x 1	47	91 [92]

CVJ5 Series **Accessory Dimensions**

Single Knuckle Joint

(mm)

Knuckle Pin

(mm)





mt.	L ₁	tm	~
		7	용,
			ջ
		— J	9
#11			핥
V-		H.V	<u>~</u>

Material: Holled stee											
Part no.	Applicable bore size	Αı	Lı	мм	ND ^{H10}	NX	Rı	U ₁			
I-J010C	10	8	21	M4 x 0.7	3.3 +0.048	3.1	8	9			
I-J016C	16	8	25	M5 x 0.8	5 +0.048	6.4	12	14			

	Material: Stainless steel											
Part no.	Applicable bore size	Dd9	d	L	Lı	m	t	Applicable retaining ring				
IY-J010	10	3.3 -0.030	3	16.2	12.2	1.7	0.3	Type C 3.2				
IY-J015	16	5 -0.030 -0.060	4.8	16.6	12.2	1.5	0.7	Type C 5				

^{*} Retaining rings are included.


Mounting Nut

Double Knuckle Joint

(mm)



(mm)



	<u>d</u>
	1 A
	, H
В	• н

	Material: Rolled steel										
Part no.	Applicable bore size	A ₁	L	L ₁	ММ	NDde	ND _{H10}	NX	Rı	U ₁	
Y-J010C	10	8	16.2	21	M4 x 0.7	-0.000	3.3 +0.048	3.2	8	10	
Y-J016C	16	11	16.6	21	M5 x 0.8	5 -0.030 -0.060	5 ^{+0.048}	6.5	12	10	

^{*} Knuckle pin and retaining ring are shipped together.

Material: Brass

	Applicable bore size	В	С	d	н
SNJ-010C	10	11	12.7	M8 x 1.0	4
SNJ-016C	16	14	16.2	M10 x 1.0	4

Rod End Nut

(mm)




Material: Iron

Part no.	Applicable bore size	В	С	d	н
NTJ-010C	10	7	8.1	M4 x 0.7	3.2
NTJ-015C	16	8	9.2	M5 x 0.8	4


CVJ5 Series **Auto Switch Mounting 1**


Auto Switch Proper Mounting Position (Detection at Stroke End) and Its Mounting Height



SMC

Auto Switch Proper Mounting Position (Detection at Stroke End) and Its Mounting Height





Auto Switch Proper Mounting Position

\Auto switch	to switch Band mounting				Rail mounting															
model Bore size	D-AS		D-M9 D-M9 D-M9 D-M9 D-M9	□V □W □WV	D-C D-C D-C D-C	80 73C	D-H7 D-H7 D-H7	'C 'NF	D-AS		D-M9 D-M9 D-M9 D-M9 D-M9	□V □W □WV	D-4 D-4	\7□ \80	D-A7 H D-A73C, D-F7 J D-F7 V D-F7 V D-F79F/	/A80C J79 V/J79W V/F7□WV	D-F	7NT	D-A	79W
(mm)	Α	В	Α	В	Α	В	Α	В	Α	В	Α	В	Α	В	Α	В	Α	В	Α	В
10	2	2	6	6	2.5	2.5	1.5	1.5	0.5	0.5	4.5	4.5	3	3	3.5	3.5	8.5	8.5	0.5	0.5
16	2.5	2.5	6.5	6.5	3	3	2	2	1	1	4	4	3.5	3.5	4	4	9	9	1	1

Note) Adjust the auto switch after confirming the operating conditions in the actual setting.

Auto Switch Mounting Height

Auto Sw	Auto Switch Mounting height (mm)											
Auto switch	Band mounting					Rail mounting						
model Bore size	D-M9□	D-M9□WV D-M9□AV	D-C7□/C80 D-H7□/H7□W D-H7NF	D-C73C D-C80C	D-H7C	D-A9□/A9□V D-M9□/M9□V D-M9□W D-M9□WV	D-A7□ D-A80	D-A7□H/A80H D-F7□/J79 D-F7□W/J79W D-F79F		D-F7□V D-F7□WV	D-J79C	D-A79W
(mm)	Hs	Hs	Hs	Hs	Hs	Hs	Hs	Hs	Hs	Hs	Hs	Hs
10	17	18	17	19.5	20	17.5	16.5	17.5	23.5	20	23	19
16	20.5	21	20.5	23	23.5	21	19.5	20.5	26.5	23	26	22

CVJ5 Series **Auto Switch Mounting 2**

Minimum Auto Switch Mounting Stroke

			No	. of auto switches moun	tod	(mm)	
Auto switch mounting	Auto switch model		INO 2		n (n: No. of auto switches)		
Auto switch mounting	Auto Switch model	1	Different surfaces	Same surface	Different surfaces	Same surface	
	D-M9□/M9□W D-A9□/M9□A	10	15 Note 1)	45 Note 1)	$15 + 35 \frac{(n-2)}{2}$ $(n = 2, 4, 6)^{\text{Note 4}}$	45 + 15 (n-2) (n = 2, 3, 4, 5···)	
	D-M9□V	5	15 Note 1)	35	15 + 35 (n-2) (n = 2, 4, 6···) Note 4)	35 + 25 (n-2) (n = 2, 3, 4, 5···)	
	D-M9□WV D-M9□AV	10	15 Note 1)	35	15 + 35 (n-2) (n = 2, 4, 6···) Note 4)	35 + 25 (n-2) (n = 2, 3, 4, 5···)	
Band mounting	D-A9□V	5	10	35	$10 + 35 \frac{(n-2)}{2}$ $(n = 2, 4, 6)^{\text{Note 4}}$	35 + 25 (n-2) (n = 2, 3, 4, 5···)	
	D-C7□ D-C80	10	15	50	15 + 40 (n-2) (n = 2, 4, 6···) Note 4)	50 + 20 (n-2) (n = 2, 3, 4, 5···)	
	D-H7□ D-H7□W D-H7NF	10	15	60	$15 + 45 \frac{(n-2)}{2}$ $(n = 2, 4, 6 \cdots)^{\text{Note 4}}$	60 + 22.5 (n-2) (n = 2, 3, 4, 5···)	
	D-C73C D-C80C D-H7C	10	15	65 Note 2)	$15 + 50 \frac{\text{(n-2)}}{2}$ (n = 2, 4, 6···) Note 4)	50 + 27.5 (n-2) (n = 2, 3, 4, 5···)	
	D-M9□V	5	_	5	_	10 + 10 (n-2) (n = 4, 6···) Note 5)	
	D-A9□V	5	_	10	_	10 + 15 (n-2) (n = 4, 6···) Note 5)	
	D-M9□ D-A9□	10	_	10	_	15 + 15 (n-2) (n = 4, 6···) Note 5)	
	D-M9□WV D-M9□AV	10	_	15	_	15 + 15 (n-2) (n = 4, 6···) Note 5)	
	D-M9□W	15		15	_	20 + 15 (n-2) (n = 4, 6···) Note 5)	
	D-M9□A	15	-	20	_	20 + 15 (n-2) (n = 4, 6···) Note 5)	
Rail mounting	D-A7□/A80 D-A7□H/A80H D-A73C/A80C	5	_	10	_	15 + 10 (n-2) (n = 4, 6···) Note 5)	
	D-A7□H D-A80H	5	_	10	_	15 + 15 (n-2) (n = 4, 6···) Note 5)	
	D-A79W	10	_	15	-	10 + 15 (n-2) (n = 4, 6···) Note 5)	
	D-F7□ D-J79	5	_	5	_	15 + 15 (n-2) (n = 4, 6···) Note 5)	
	D-F7□V D-J79C	5		5	_	10 + 10 (n-2) (n = 4, 6···) Note 5)	
	D-F7□W/J79W D-F79F/F7NT	10	_	15	-	15 + 20 (n-2) $(n = 4, 6\cdots)^{\text{Note 5}}$	
	D-F7□WV	10	_	15	_	10 + 15 (n-2) (n = 4, 6···) Note 5)	

Note 4) When "n" is an odd number, an even number that is one larger than this odd number is used for the calculation. Note 5) When "n" is an odd number, an even number that is one larger than this odd number is used for the calculation. However, the minimum even number is 4. So, 4 is used for the calculation when "n" is 1 to 3.

Note 1) Auto switch mounting (The adjustment as shown in the figures below is required with the following stroke ranges.)								
	With 2 aut	o switches						
	Different surfaces Note 1)	Same surface Note 1)						
Auto switch model	Auto switch D-M9 (W) D-M9 (W) The proper auto switch mounting position is 5.5 mm inward from the switch holder edge.	The auto switch is mounted by slightly displacing it in a direction (cylinder tube circumferential exterior) so that the auto switch and lead wire do not interfere with each other.						
D-A93	ı	45 to less than 50 stroke						
D-M9□ D-M9□W	15 to less than 20 stroke	45 to less than 55 stroke						

Note 2) For the CDVJ5 series, note that 65 strokes cannot be manufactured.

Note 3) The dimension stated in () shows the minimum stroke for the auto switch mounting when the auto switch does not project from the end surface of the cylinder body and hinder the lead wire bending space. (Refer to the fligure below.)

These contents apply to the rail mounting with one or two auto switches.






Operating Range

			(mm)		
	Auto switch model	Bore size			
	Auto switch model	10	16		
Б	D-A9□(V)	6	7		
mounting	D-M9□(V) D-M9□W(V)/M9□A(V)	2.5	3		
	D-C7□/C80/C73C/C80C	7	7		
Band	D-H7□/H7□W/H7NF	4	4		
Ш	D-H7C	8	9		

Since the operating range is provided as a guideline including hysteresis, it cannot be guaranteed (assuming approximately ±30% dispersion). It may vary substantially depending on an ambient environment.

			(mm)		
	Auto switch model	Bore size			
	Auto switch model	10	16		
	D-A9□/A9□V	6	6.5		
Rail mounting	D-M9□/M9□V D-M9□W/M9□WV D-M9□A/M9□AV	3	3.5		
물	D-A7□/A80/A7H/A80H/A73C/A80C	8	9		
<u>=</u>	D-A79W	11	13		
l &	D-F7□/J79/F7□W/J79W D-F7□V/F7□WV/F79F/J79C D-F7NT	5	5		

Auto Switch Mounting Bracket: Part No.



- Note 1) Set part number which includes the auto switch mounting band (BJ2-□□□) and the holder kit (BJ5-1/Switch bracket: Transparent). Since the switch bracket (made from nylon) are affected in an environment where alcohol, chloroform, methylamines, hydrochloric acid or sulfuric acid is splashed over, so it cannot be used. Please consult SMC regarding other chemicals.
- Note 2) Set part number which includes the auto switch mounting band (BJ2-□□□S) and the holder kit (BJ4-1/Switch bracket: White).
- Note 3) For the D-M9□A (V) type auto switch, do not install the switch bracket on the indicator light.

Note 4) Only auto switch mounting brackets are assembled when cylinders are shipped.

Note 5) When a compact auto switch is mounted on the rail mounting type, the auto switch mounting brackets on the left are required. Order them separately from cylinders

Example order: CDJ2B10-60-A 1 unit D-M9BWV 2 pcs. BQ2-012 2 pcs.

Besides the models listed in How to Order, the following auto switches are applicable. Refer to pages 1341 to1435 for detailed specifications.

neier to pages 1341 to 1433 for detailed specifications.								
Auto switch type	Part no.	Electrical entry (Fetching direction)	Features					
Reed	D-C73, C76		_					
neeu	D-C80	Grommet (In-let)	Without indicator light					
Solid state	D-H7A1, H7A2, H7B	Grommet (m-iet)	_					
Solid State	D-H7NW, H7PW, H7BW		Diagnostic indication (2-color)					

* For solid state auto switches, auto switches with a pre-wired connector are also available. Refer to pages 1410 and 1411 for details.

* Normally closed (NC = b contact) solid state auto switches (D-M9□E(V)) are also available. Refer to page 1360 for details.




Valve Mounted Cylinder Single Acting, Spring Return/Extend

CVJ3 Series

ø10, ø16

How to Order



M9PWV M9PW

M9BWV M9BW

M9BAV*1 M9BA*

MQPA:

H7NF

A96

Δ93

A90

C73C

C80C

M9NAV*1

M9PAV*1

A96V

A93V*2

A90V

24 V or less *1 Water resistant type auto switches can be mounted on the above models, but in such case SMC cannot quarantee water resistance Consult with SMC regarding water resistant types with the above model numbers

200 V

100 V

100 V or less

*2 1 m type lead wire is only applicable to D-A93.

Grommet

* Lead wire length symbols: 0.5 m Nil (Example) M9NW 5 m ··

No

Yes No

(Example) M9NWM 1 m M

24 \

- (Example) M9NWI 3 m..... I
- * Since there are other applicable auto switches than listed, refer to page 1174 for details.

•

•

•

•

F7NWV

F7BWV

A72

A73

A80

A73C

A80C

A79W

F79W

F7PW

J79W

F79F

A76H

A72H

A73H

A80H Relay,

IC circuit PLC

IC circuit

IC circuit

IC circuit

IC circuit Relay,

IC circuit

PI C

- * For details about auto switches with pre-wired connector, refer to pages 1410 and 1411.
- (Example) M9NWZ * Solid state auto switches marked with "O" are produced upon receipt of order

3-wire (NPN)

3-wire (PNP)

2-wire

3-wire (NPN)

3-wire (PNP)

2-wire

4-wire (NPN)

2-wire

5 V, 12 V

12 V

5 V. 12 V

12 V

5 V. 12 V

5 V

12 V

- * D-A9 \(M9 \(A7 \) \(A80 \) \(F7 \) \(A9 \) \(A7 \) \(A80 \) \(A7 \) \(A80 \ are assembled before shipped.)
- * D-C7 \(\subset \)/C80 \(\subset /H7 \subset \subset \) auto switches are assembled at the time of shipment
- * Order auto switch mounting brackets separately when D-A9 (V)/M9 (V)/M9 (V)/M9 (A(V) are mounted on ø10 and ø16 of the rail mounting type. Refer to page 1174 for details.

state

Solid

Reed auto switch

Diagnostic indication

(2-color indicator)


Water resistant

(2-color indicator)


An auto switch cylinder with the switch installed can also be manufactured.



Symbol Single acting: Spring return, Rubber bumper



Single acting: Spring extend, Rubber bumper





Symbol	Specifications
-XA□	Change of rod end shape

Specifications

Bore size (mm)	ø10	ø16		
Action	Single acting, Single rod, Spring return/Spring e			
Fluid	Air			
Proof pressure	1.05	MPa		
Maximum operating pressure	0.7 MPa			
Minimum operating pressure	0.15 MPa			
Ambient and fluid temperature	-10 to 50°C (No freezing)			
Cushion	Rubber bumper			
Lubrication	Not required (Non-lube)			
Stroke length tolerance		1.0		
Port size	M5 x 0.8			
Mounting	Basic type, Axial foot ty	pe, Rod side flange type		
Piston speed	50 to 750 mm/s	50 to 350 mm/s		
Allowable kinetic energy	0.035 J	0.090 J		

Solenoid Valve Specifications

Applicable solenoid val	ve mod	el	SYJ319		
Electrical entry			Grommet (G), L plug connector (L), M plug connector (M)		
Call rated valtage (V)		DC	24, 12, 6, 5, 3		
Coil rated voltage (V)	AC	50/60 Hz	100, 110, 200, 220		
Effective area of valve (Cv factor)			1.8 mm² (0.1)		
Allowable voltage			±10% of the rated voltage*		
Power consumption (W)	DC Standard		0.35 (With indicator light: 0.4)		
		100 V	0.78 (With indicator light: 0.81)		
A		110 V [115 V]	0.86 (With indicator light: 0.89) [0.94 (With indicator light: 0.97)]		
Apparent power (VA)*	AC	200 V	1.18 (With indicator light: 1.22)		
		220 V [230 V]	1.30 (With indicator light: 1.34) [1.42 (With indicator light: 1.46)]		
Surge voltage suppressor			Diode (Varistor for the non-polar type)		
Indicator light			LED		

- * 110 VAC and 115 VAC types and 220 VAC and 230 VAC types are common respectively.

 For 115 VAC and 230 VAC, allowable voltage fluctuation is -15 to -5 % of the rated voltage.

 For S and Z, the voltage will drop due to the internal circuit. Allowable voltage fluctuation must be in the
- range below.
 Types S, Z 24 VDC: -7 to 10 %, 12 VDC: -4 to 10 %

Standard Stroke

(mm)

Bore size (mm)	Standard stroke
10	15, 30, 45, 60
16	15, 30, 45, 60

Spring Back Force

opining back i orce								
Bore size (mm)	Spring reaction force							
Bore Size (ITIIII)	Secondary	Primary						
10	6.9	3.5						
16	14.2	6.9						



Mounting Type and Accessory/For details, refer to page 1159.

		Mounting	Basic type	Axial foot type	Rod side flange type
Standard	ment	Mounting nut	•	•	•
Stan	equip	Rod end nut	•	•	•
1	Jption	Single knuckle joint	0	0	0
2	5	Double knuckle joint (With pin)*	0	0	0

Accessory

Accessories of the CVJ3 series are the same specifications as those of the CVJ5 series. Refer to page 1159.

Mounting Bracket Part No.

Mounting	Bore siz	ze (mm)
bracket	10	16
Foot	CJ-L010C	CJ-L016C
Flange	CJ-F010C	CJ-F016C

Accessory (Option)

Refer to page 1159 for part numbers and dimensions of the single knuckle joint, double knuckle joint, knuckle pin, mounting nut, and rod end nut.

Weight

Spring Return

-								
Boi	re size (mm)	10	16					
	15 stroke	79	116					
Basic weight*	30 stroke	87	135					
basic weight	45 stroke	97	159					
	60 stroke	109	184					
Mounting	Axial foot type	7	19					
bracket weight	Rod side flange type	5	13					

- * Mounting nut and rod end nut are included in the basic weight. Calculation: (Example) CVJ3L10-45S
 - Basic weight ------ 97 (g) (ø10-45 stroke)
 Mounting bracket weight ---- 7 (g) (Axial foot type)


97 + 7 = 104 g

Spring Exte	na		(g)
Boi	re size (mm)	10	16
	15 Stroke	75	111
Basic weight*	30 Stroke	82	129
basic weight	45 Stroke	93	151
	60 Stroke	103	175
Mounting	Axial foot type	7	19
bracket weight	Rod side flange type	5	13

- Mounting nut and rod end nut are included in the basic weight.
 Calculation: (Example) CVJ3L10-45T

Manual Operation

Manual operation is possible by pushing the manual button indicated with the arrow.



⚠ Specific Product Precautions

Be sure to read this before handling the products. Refer to page 9 for safety instructions, pages 10 to 19 for actuator and auto switch precautions, and 3/4/5-port solenoid valve precautions on the SMC website: https://www.smcworld.com

Handling Precautions

 During installation, secure the rod cover and tighten the mounting nut or the rod cover body by applying an appropriate tightening force.

If the head cover is secured or the head cover is tightened, the cover may rotate, leading to the deviation.

Tighten the mounting screws with an appropriate tightening torque within the range given below.

ø6: 2.1 to 2.5 N·m, ø10: 5.9 to 6.4 N·m ø16: 10.8 to 11.8 N·m

Do not operate the single acting cylinder in such a way that a load would be applied when retracting the piston rod of the spring return type or extending the piston rod of the spring extend type.

The spring that is built into the cylinder provides only enough force to retract the piston rod. If a load is applied, the piston rod will not be able to retract to the stroke end.

- 4. For the single acting cylinder, a breather hole is provided in the cover surface. Do not block this hole during installation. This may cause malfunction.
- To remove and install the retaining ring for the knuckle pin or the clevis pin, use an appropriate pair of pliers (tool for installing a type C retaining ring).

In particular, use a pair of ultra-mini pliers for removing and installing the retaining rings on the ø10 cylinder.

For the auto switch mounting rail, do not remove the pre-equipped rail.

Since the mounting thread is drilled through inside the cylinder, it may cause air leakage.

△Warning

1. Confirm the specifications.

Products in this catalog are designed to be used for compressed air systems. If not operated within the designated pressure or temperature, it may damage the products or cause malfunction. (Refer to specifications.)


2. Energizing continuously for a long period of time

When the valve is continuously energized for a long period of time, the performance may deteriorate, shorten the service life or effect peripheral equipment adversely since temperature rises when coils generate heat.


(a)

Construction/Component Parts

Single acting, Spring return



Single acting, Spring extend



Component Parts

No.	Description	Material	Note
1	Rod cover	Aluminum alloy	Clear anodized
2	Head cover	Aluminum alloy	Clear anodized
3	Cylinder tube	Stainless steel	
4	Piston rod	Stainless steel	
5	Piston A	Aluminum alloy	Chromated
6	Piston B	Aluminum alloy	Chromated
7	Return spring	Piano wire	
8	Spring seat	Brass	
9	Bumper	Urethane	
10	Mounting nut	Brass	Nickel plated
11	Rod end nut	Rolled steel	Zinc chromated
12	Steel ball	Carbon steel	

No.	Description	Material	Note							
13	Stud	Brass	Electroless nickel plated							
14	Phillips screw	Rolled steel	Nickel plated							
15	Plate	Zinc alloy								
16	Solenoid valve	_	Refer to "How to Order" below.*							
17	Pipe	Aluminum alloy	Clear anodized							
18	Piston seal	NBR								
19	Rod seal	NBR								
20	Tube gasket	NBR								
21	Piston gasket	NBR								
22	Gasket	NBR + Stainless steel 304								
23	Plate gasket	NBR								
* How to Order solenoid valves										


SYJ319 - | | |

Rated voltage Light/surge voltage suppressor Electrical entry




CVJ3 Series

Single Acting, Spring Return/Basic Type (B)



Single Acting, Spring Return/Axial Foot Type (L)




Rod End Nut Bore size (mm) B₁ H₁ 10 3.2 16 8 4

*[]: Denotes the values of AC.

*[]: Denote	[]: Denotes the values of AC.										((mm)																
Bore size	^	В	С	7	_			ı B			LT	ı v	ıv	17	мм	МА	NB	NN	х	v	5 to	15 st	16 to	30 st	31 to	45 st	46 to	60 st
bore size	^	P	•	ט	-	"	LA	ㅁ	LC	LΠ	-'		Lī	LZ	IVIIVI	INA	IND	ININ	^	ı ا	S	z	s	Z	S	Z	s	Z
10	15	12	14	4	8	28	37.5	15	4.5	9	1.6	24	16.5	32	M4 x 0.7	12.5	9.5	M8 x 1	5	7	52.5	96.5 [97.5]	60	104	72	116 [117]	84	128 [129]
16	15	18	20	5	8	28	45.5	23	5.5	14	2.3	33	25	42	M5 x 0.8	12.5	9.5	M10 x 1	6	9	52.5	96.5 [97.5]	61	105 [106]	73	117 [118]	85	129 [130]

Single Acting, Spring Return/Rod Side Flange Type (F)




Rod End N	lut	
Bore size (mm)	B ₁	Ηı
10	7	3.2
16	8	4

(mm)

Dave size	^	R	В	В	В	В	В	^	7	_	FC	FT	FX	FY	FZ	н	нх	ММ	NA	NB	NN	5 to	15 st	16 to	30 st	31 to	45 st	46 to	60 st
Bore size	Α.	В	C	ט	-	-	г	「^	FT	FZ	п	пл	IVIIVI	INA	IND	ININ	S	Z	S	Z	S	Z	S	Z					
10	15	12	14	4	8	4.5	1.6	24	14	32	28	34.5	M4 x 0.7	12.5	9.5	M8 x 1	52.5	96.5 [97.5]	60	104 [105]	72	116 [117]	84	128 [129] 129					
16	15	18	20	5	8	5.5	2.3	33	20	42	28	40.5	M5 x 0.8	12.5	9.5	M10 x 1	52.5	96.5 [97.5]	61	105 [106]	73	117 [118]	85	129 [130]					

Single Acting, Spring Extend/Basic Type (B)

CVJ3B Bore size - Stroke T




Rod End I	lut	
Bore size (mm)	Вı	Нı
10	7	3.2
16	0	4


* []: Denotes the values of AC.

* []: Denote	▼ []: Denotes the values of AC.												(mm)							
Di		В	_	2	_	н	нх	ММ	NA	NB	ND	NN	5 to	15 st	16 to	30 st	31 to	45 st	46 to	60 st
Bore size	A	P	·	ט	-	п	пх	IVIIVI	INA	IND	טא	ININ	S	Z	S	Z	S	Z	S	Z
10	15	12	14	4	8	28	34.5	M4 x 0.7	12.5	9.5	8 -0.022	M8 x 1	52.5	96.5 [97.5]	60	104 [105]	72	116 [117]	84	128 [129]
16	15	18	20	5	8	28	40.5	M5 x 0.8	12.5	9.5	10 -0.022	M10 x 1	52.5	96.5 [97.5]	61	105 [106]	73	117 [118]	85	129 [130]

Single Acting, Spring Extend/Axial Foot Type (L)

CVJ3L Bore size - Stroke T





₹od	End	Nut	
	/	.\ D	


Bore size (mm)	Вı	Hı
10	7	3.2
16	8	4

* []: Denotes the values of AC.

2	* []: Denotes the values of AC.														(mm)																								
	Bore size	^	В	_	D	_	ш		ı B			LT	ı v	ıv	17	Z NAMA NIA		7 8484 8		7 1/1/4 1	, NAMA I	NANA	NAMA I	DADA	, NANA I	MM NA NB		NN	NB NN	х	v	5 to	15 st	16 to	30 st	31 to	45 st	46 to	60 st
	Dore Size	^	•	٠	יי	「	п.	LA	LD		LΠ			Lī	ᄔ	IVIIVI	INA	IND	ININ	^	ı	s	Z	s	Z	s	Z	S	Z										
	10	15	12	14	4	8	28	37.5	15	4.5	9	1.6	24	16.5	32	M4 x 0.7	12.5	9.5	M8 x 1	5	7	52.5	96.5 [97.5]	60	104 [105]	72	116 [117]	84	128 [129]										
	16	15	18	20	5	8	28	45.5	23	5.5	14	2.3	33	25	42	M5 x 0.8	12.5	9.5	M10 x 1	6	9	52.5	96.5 [97.5]	61	105 [106]	73	117 [118]	85	129 [130]										

Single Acting, Spring Extend/Rod Side Flange Type (F)

CVJ3F Bore size - Stroke T



Rod End Nut


Bore size (mm)	Вı	Ηı
10	7	3.2
16	8	4


* []. Denotes the values of AC

· []. Denote	[]. Benotes the values of No.																							
Bore size	^	В	_	2	F FC FT FX FY FZ H HX MM NA NB NN		NA NB A		5 to	15 st	16 to	30 st	31 to	45 st	46 to	60 st								
Dore Size	4	ь		U	Г	FC	г	Γ^	ГТ	FZ	п	пл	IVIIVI	INA	IND	ININ	S	Z	S	Z	s	Z	ß	Z
10	15	12	14	4	8	4.5	1.6	24	14	32	28	34.5	M4 x 0.7	12.5	9.5	M8 x 1	52.5	96.5 [97.5]	60	104 [105]	72	116 [117]	84	128 [129]
16	15	18	20	5	8	5.5	2.3	33	20	42	28	40.5	M5 x 0.8	12.5	9.5	M10 x 1	52.5	96.5 [97.5]	61	105 [106]	73	117 [118]	85	129 [130]


CVJ3 Series **Auto Switch Mounting 1**


Auto Switch Proper Mounting Position (Detection at Stroke End) and Its Mounting Height







Auto Switch Proper Mounting Position (Detection at Stroke End) and Its Mounting Height









CVJ3 Series

Auto Switch Mounting 2

Auto Switch Proper Mounting Position (Detection at Stroke End) and Its Mounting Height: Single Acting, Spring Return (S) / Spring Extend (T)

	uto Switch Pi	Bore size	unting P		Spring F	eturn (5)	(m
	Auto switch model	(mm)	10 to 15 st	16 to 30 st	31 to 45 st	46 to 60 st	В
	D-A9□(V)	10	8.5	16	28	40	2
	D-A9□(V)	16	8	16.5	28.5	40.5	2.5
5	D-M9□(V) D-M9□W(V)	10	12.5	20	32	44	6
	D-M9□A(V)	16	12	20.5	32.5	44.5	6.5
Ę	D-C7□/C80	10	9	16.5	28.5	40.5	2.5
ğ	D-C73C/C80C	16	8.5	17	29	41	3
נ	D-H7□/H7C D-H7□W	10	8	15.5	27.5	39.5	1.5
	D-H7NF	16	7.5	16	28	40	2
	D-A9□	10	7	14.5	26.5	38.5	0.5
	D-A9□V	16	6.5	15	27	39	1
	D-M9□/M9□V	10	11	18.5	30.5	42.5	4.5
	D-M9 W/M9 WV	16	10.5	19	31	43	5
	D-A7□	10	9.5	17	29	41	3
20	D-A80	16	9	17.5	29.5	41.5	3.5
Rail mounting	D-A7□H/A80H D-A73C/A80C D-F7□/J79	10	10	17.5	29.5	41.5	3.5
	D-F7□W/J79W D-F7□V/F7□WV D-F79F/J79C	16	9.5	18	30	42	4
	D-F7NT	10	15	22.5	34.5	46.5	8.5

Note) Adjust the auto switch after confirming the operating conditions in the actual setting.

16

D-A79W

Auto Switch Proper Mounting Position / Spring Extend (T)

6.5

Bore size			Ď.						
	Α	Dimension B							
(mm)	A	10 to 15 st	16 to 30 st	31 to 45 st	46 to 60 st				
10	2	8.5	16	28	40				
16	2.5	8	16.5	28.5	40.5				
10	6	12.5	20	32	44				
16	6.5	12	20.5	32.5	44.5				
10	2.5	9	16.5	28.5	40.5				
16	3	8.5	17	29	41				
10	1.5	8	15.5	27.5	39.5				
16	2	7.5	16	28	40				
10	0.5	7	14.5	16.5	38.5				
16	1	6.5	15	27	39				
10	4.5	11	18.5	30.5	42.5				
16	5	10.5	19	31	43				
10	3	9.5	17	29	41				
16	3.5	9	17.5	29.5	41.5				
10	3.5	10	17.5	29.5	41.5				
16	4	9.5	18	30	42				
10	8.5	15	22.5	34.5	46.5				
16	9	14.5	23	35	47				
10	0.5	7	14.5	26.5	38.5				
16	1	6.5	15	27	39				
	16 10 16 10 16 10 16 10 16 10 16 10 16 10 16 10 16 10 16 10 16 10 16 10 16	16 2.5 10 6 16 6.5 10 2.5 16 3 10 1.5 16 2 10 0.5 16 1 10 4.5 16 5 10 3 16 3.5 10 3.5 10 3.5	10 2 8.5 16 2.5 8 10 6 12.5 16 6.5 12 10 2.5 9 16 3 8.5 10 1.5 8 16 2 7.5 10 0.5 7 16 1 6.5 10 4.5 11 10 4.5 11 10 3 9.5 10 3.5 9 10 3.5 10	10 2 8.5 16 16 2.5 8 16.5 10 6 12.5 20 16 6.5 12 20.5 10 2.5 9 16.5 16 3 8.5 17 10 1.5 8 15.5 16 2 7.5 16 10 0.5 7 14.5 16 1 6.5 15 10 4.5 11 18.5 16 5 10.5 19 10 3 9.5 17 16 3.5 9 17.5 10 3.5 10 17.5 16 4 9.5 18 10 8.5 15 22.5 16 9 14.5 23 10 0.5 7 14.5	10 2 8.5 16 28 16 2.5 8 16.5 28.5 10 6 12.5 20 32 16 6.5 12 20.5 32.5 10 2.5 9 16.5 28.5 16 3 8.5 17 29 10 1.5 8 15.5 27.5 16 2 7.5 16 28 10 0.5 7 14.5 16.5 16.5 16 1 6.5 15 27 10 4.5 11 18.5 30.5 30.5 16 30.5 19 31 10 3 9.5 17 29 16 3.5 9 17.5 29.5 10 3.5 10 17.5 29.5 10 16 4 9.5 18 30 10 10 3.5 10 14.5 23 34.5 16 16				

Note) Adjust the auto switch after confirming the operating conditions in the actual setting.

Auto	Switch	Mounting	Height

ľ	Auto switch		Ba	and mountir	ng		Rail mounting								
	model Bore size	D-A9□ D-M9□ D-M9□W	D-M9□WV D-M9□AV		D-C73C D-C80C	D-H7C	D-A9□/A9□V D-M9□ D-M9□V D-M9□W D-M9□WV	D-A7□ D-A80	D-A7□H/A80H D-F7□/J79 D-F7□W/J79W D-F79F D-F7NT	D-A73C	D-F7□V D-F7□WV	D-J79C	D-A79W		
1	(mm)	Hs	Hs	Hs	Hs	Hs	Hs	Hs	Hs	Hs	Hs	Hs	Hs		
	10	17	18	17	19.5	20	17.5	16.5	17.5	23.5	20	23	19		
Γ	16	20.5	21	20.5	23	23.5	21	19.5	20.5	26.5	23	26	22		

Minimum Auto Switch Mounting Stroke

Auto switch mounting Auto switch model 1 2	ntod	of outo quitabas ma	No			
D-M9□/M9□M 10 15 Note 1) 45 Note 1) 15 + 35	IIILEC				Auto switch model	Auto switch mounting
D-A9□V 5 15 Note 1) 35 15 + 35 (n-2) (n = 2, 4, 6) Note 4) (n = 2, 3)				1	Auto Switch model	Auto Switch mounting
D-M9□WV 10 15 Note 1) 35 15 + 35 (n-2) 2 35 + 21 (n = 2, 4, 6) Note 4) (n = 2, 3, 4, 6) Note 4) (n = 2, 4, 6) Note		45 Note 1)	15 Note 1)	10		
D-A9□V 5 10 35 10 + 35 (n-2) / (n = 2, 4, 6) 10 / (n = 2, 4, 6) 10 / (n = 2, 3)		35	15 Note 1)	5	D-M9□V	
D-A9□V 5 10 35 10 + 35 (n-2) / (n = 2, 4, 6) 10 / (n = 2, 4, 6) 10 / (n = 2, 3)		35	15 Note 1)	10		
D-C7 D-C80 10 15 50 15 + 40 (n-2) / 2 (n = 2, 4, 6) hote 4) (n = 2, 3)		35	10	5	D-A9□V	Band mounting
D-H7□		50	15	10		
D-H7C		60	15	10	D-H7□W	
D-M9□V 5 — 10 — 10+11 D-M9□V 5 — 10 — 10+11 D-M9□ 10 — 10 — 15+11 D-M9□WV 10 — 15 — 15 — 15+11 D-M9□WV 15 — 15 — 20+11 D-M9□W 15 — 20 — 20+11 D-M9□A 15 — 20 — 20+11 (n = 4, 6) D-A7□/A80 D-A7□/H/A80H 5 — 10 — (15+6)		65 Note 2)	15	10	D-C80C	
D-A9□		5	-	5	D-M9□V	
D-A9		10	_	5	D-A9□V	
D-M9□AV 10		10	_	10	D-A9□	
D-M9□W 15 — 15 — (n = 4, 6) D-M9□A 15 — 20 — 20+11 (n = 4, 6) D-A7□/A80 D-A7□/A80 D-A7□/A80H 5 — 10 — (n = 4, 6)		15	_	10		
D-M9⊟A 15 — 20 — (n = 4, 6 D-A7□/A80		15	_	15	D-M9□W	
Rail mounting D-A7 - H/A80H 5 - 10 - 15 + 10		20	_	15	D-M9□A	
		10	_	5	D-A7□H/A80H	Rail mounting
D-A7 □ H D-A80H 5 — 10 — 15 + 19 (n = 4, 6)		10	_	5		
D-A79W 10 — 15 — 10 + 15 (n = 4, 6		15	_	10	D-A79W	
D-F7 □ 5 — 5 — 15 + 15 (n = 4,6		5	_	5	D-J79	
D-F7 □ V D-J79C 5 — 5 — 10 + 10 (n = 4,6)		5	_	5	D-J79C	
D-F7□W/J79W D-F79F/F7NT 10 — 15 — 15 + 2l (n = 4,6		15	_	10		

Note 4) When "n" is an odd number, an even number that is one larger than this odd number is used for the calculation. Note 5) When "n" is an odd number, an even number that is one larger than this odd number is used for the calculation. However, the minimum even number is 4. So, 4 is used for the calculation when "n" is 1 to 3.

Note 1) Auto switch mounting (The adjustment as shown in the figures below is required with the following stroke ranges.)

Note 1) Auto Switch Hourit	ing (The adjustment as shown in the figures below is required with the follow	ing stoke ranges.)
	With 2 aut	o switches
	Different surfaces Note 1)	Same surface Note 1)
Auto switch model	Auto switch D-M9□W(V) D-M9□W(V) The proper auto switch mounting position is 5.5 mm inward from the switch holder edge.	The auto switch is mounted by slightly displacing it in a direction (cylinder tube circumferential exterior) so that the auto switch and lead wire do not interfere with each other.
D-A93	I	45 to less than 50 stroke
D-M9□ D-M9□W	15 to less than 20 stroke	45 to less than 55 stroke

Note 2) For the CDVJ3 series, note that 65 strokes cannot be manufactured.

D-F7□WV

Note 3) The dimension stated in () shows the minimum stroke for the auto switch mounting when the auto switch does not project from the end surface of the cylinder body and hinder the lead wire bending space. (Refer to the figure below.)

These contents apply to the rail mounting with one or two auto switches.



10 + 15 (n-2) (n = 4, 6···) Note 5)

CVJ3 Series Auto Switch Mounting 3


Operating Range

			(mm)			
	Auto switch model	Bore size				
	Auto switch model	10	16			
g	D-A9□(V)	6	7			
mounting	D-M9□(V) D-M9□W(V)/M9□A(V)	2.5	3			
E	D-C7□/C80/C73C/C80C	7	7			
Band	D-H7□/H7□W/H7NF	4	4			
ш	D-H7C	8	9			

Since the operating range is provided as a guideline including hysteresis, it cannot be guaranteed (assuming approximately ±30% dispersion). It may vary substantially depending on an ambient environment.

			(mm)			
	Auto switch model	Bore size				
	Auto switch model	10	16			
	D-A9□/A9□V	6	6.5			
mounting	D-M9□/M9□V D-M9□W/M9□WV D-M9□A/M9□AV	3	3.5			
물	D-A7□/A80/A7H/A80H/A73C/A80C	8	9			
۱Ę	D-A79W	11	13			
Rail	D-F7□/J79/F7□W/J79W D-F7□V/F7□WV/F79F/J79C D-F7NT	5	5			

Auto Switch Mounting Bracket: Part No.



- Note 1) Set part number which includes the auto switch mounting band (Bu2-□□□) and the holder kit (Bu5-1/Switch bracket: Transparent). Since the switch bracket (made from nylon) are affected in an environment where alcohol, chloroform, methylamines, hydrochloric acid or sulfuric acid is splashed over, so it cannot be used. Please consult SMC regarding other chemicals.

 Note 2) Set part number which includes the auto switch mounting the sulfurious control of the sulfurious control
- Note 2) Set part number which includes the auto switch mounting band (Bu2-□□□S) and the holder kit (BJ4-1/Switch bracket: White).
- Note 3) For the D-M9□A (V) type auto switch, do not install the switch bracket on the indicator light.

Note 4) Only auto switches are assembled when cylinders are shipped.

Note 5) When a compact auto switch is mounted on the rail mounting type, the auto switch mounting brackets on the left are required. Order them separately from cylinders.

Example order: CDJ2B10-60-A 1 unit D-M9BWV 2 pcs. BQ2-012 2 pcs.

Besides the models listed in How to Order, the following auto switches are applicable. Refer to pages 1341 to 1435 for detailed specifications.

		•	
Auto switch type	Part no.	Electrical entry (Fetching direction)	Features
Reed	D-C73, C76		_
need	D-C80	Grommet (In-let)	Without indicator light
Callelatata	D-H7A1, H7A2, H7B	Grommet (m-iet)	_
Solid state	D-H7NW, H7PW, H7BW		Diagnostic indication (2-color)


^{*} For solid state auto switches, auto switches with a pre-wired connector are also available. Refer to pages 1410 and 1411 for details.

* Normally closed (NC = b contact) solid state auto switches (D-M9□E(V)) are also available. Refer to page 1360 for details.

Valve Mounted Cylinder Double Acting, Single Rod

CVM5 Series

Ø20. Ø25. Ø32. Ø40



Applicable Auto Switch

Only in case of 2

position single

solenoid valve

App	Applicable Auto Switches/Refer to pages 1341 to 1435 for further information on auto switches.																									
		Electrical	dicator light	Wiring		Load vol	tage	Auto s		Lead	d wir	e ler	igth	(m)	Pre-wired											
Type	Special function	entry	cator	(Output)		DC	AC	mo		0.5	1	3	5	None	connector	Applica	ble load									
		,	Вĝ	(Output)			AO	Perpendicular	In-line	(Nil)	(M)	(L)	(Z)	(N)												
				3-wire (NPN)		5 V, 12 V		M9NV	M9N	•	•	•	0	_	0	IC										
=		Grommet		3-wire (PNP)		J V, 12 V		M9PV	M9P	•	•	•	0	_	0	circuit										
switch				2-wire		12 V		M9BV	M9B	•	•	•	0	_	0											
		Connector		Z-WITE		12 V		_	H7C	•	_	•	•	•	_											
anto	Diagnostic indication		1	3-wire (NPN)		5 V, 12 V		M9NWV	M9NW	•	•	•	0	_	0	IC	Relay,									
- F	(2-color indicator)				_	M9PWV	M9PW	•	•	•	0	_	0	circuit	PLC											
state				2-wire	12 V		M9BWV	M9BW	•	•	•	0	_	0	_											
	(2-color indicator)	or)	Grommet	Grommet		3-wire (NPN)		5 V, 12 V		M9NAV*1	M9NA*1	0	0	•	0	-	0	IC								
Solid																3-wire (PNP)	5 V, 12 V		M9PAV*1	M9PA*1	0	0	•	0	_	0
ဟ				2-wire		12 V		M9BAV*1	M9BA*1	0	0	•	0	-	0	_										
	With diagnostic output (2-color indicator)]		4-wire (NPN))	5 V, 12 V			H7NF	•	—	•	0	I —	0	IC circuit										
			Vac	3-wire (NPN equivalent)	_	5 V	_	A96V	A96	•	-	•	_	_	_	IC circuit	_									
switch			Yes				100 V	A93V*2	A93	•	•	•	•	-	_	_										
<u>×</u>		Grommet	None				100 V or less	A90V	A90	•	-	•	-	_	_	IC circuit										
		Yes None 2-wire 24 V 12 V 100 V, 200 V 200 V or less	_	B54	•	-	•	•	-	_		Relay,														
anto	Cor		2-wire	24 V	v 12 V	12 V 200	200 V or less		B64	•	-	•	-	_	_	l —	PLC									
		I Connector F	Yes				_	_	C73C	•	_	•	•	•	_		I LO									
Reed			None				24 V or less	_	C80C	•	-	•	•	•	_	IC circuit										
	Diagnostic indication (2-color indicator)	Grommet	Yes	1			_		B59W	•	I —	•	Ι=	<u> </u>	_	_	1									

switch

K | Heat resistant tarpaulin (Example) CDVM5B25-150-25GS

J Nylon tarpaulin

* Lead wire length symbols: 0.5 m · (Example) M9NW 1 m М (Example) M9NWM

(Refer to "Standard Stroke"

on page 1176.)

- ... L (Example) M9NWL 3 m ... 5 m (Example) M9NWZ
- * Solid state auto switches marked with "O" are produced upon receipt of order. *1 Water resistant type auto switches can be mounted on the above models, but in such case SMC cannot guarantee water resistance. Consult with SMC
- regarding water resistant types with the above model numbers. *2 1 m type lead wire is only applicable to D-A93.
- None ······ N (Example) H7CN * Since there are other applicable auto switches than listed, refer to page 1193 for details.
- * For details about auto switches with pre-wired connector, refer to pages 1410 and 1411.
 * D-A9□/M9□ auto switches are shipped together (not assembled). (Only auto switch mounting brackets are assembled before shipped.)



auto switches (D-C7
and H7
, etc.) (Nil)

s 1 pc.

n "n" pcs.


CVM5 Series

Operation type can be changed to rod extended when energized or rod retracted when energized.

An auto switch cylinder with the switch installed can also be manufactured.



Symbol Rubber bumper





Made to Order Specifications Click here for details

Symbol Specifications					
-XA□	Change of rod end shape				
-XC4	With heavy duty scraper				
-XC6	Made of stainless steel				

Refer to pages 1191 to 1193 for cylinders with auto switches.

- Proper auto switch mounting position
- (detection at stroke end) and mounting height

 Minimum auto switch mounting stroke
- · Operating range
- · Auto switch mounting bracket: Part no.

Specifications

Applicable	bore size (mm)	20 25 32 40							
Fluid		Air							
Action		Double acting, Single rod							
Cushion			Rubber	bumper					
Proof pressure			1.0	MPa					
Maximum oper	Maximum operating pressure			MPa					
Minimum opera	Minimum operating pressure			MPa					
Ambient and fl	Ambient and fluid temperature			-10 to 50°C (No freezing)					
Lubrication		Not required (Non-lube)							
Stroke length to	olerance	+ 1.4 0							
Port size	Screw-in type	Rc 1/8							
POIT SIZE	Built-in One-touch fitting	O.D.: ø6/l.D.: ø4							
Piston speed (r	mm/s) Note)	50 to 700*	50 to 650*	50 to 590*	50 to 420*				
Allowable kine	Allowable kinetic energy			0.27 J 0.4 J 0.65 J 1.2 J					
Mounting	Mounting			Basic type, Axial foot type, Rod side flange type, Head side flange type, Single clevis type, Double clevis type, Head side trunnion type, Rod side trunnion type					

Note) The figures marked with "*" represent the values of the cylinder with the silencer type exhaust throttle valve removed. To operate the cylinder at these values, prevent dust from entering by installing an AN120-M5 silencer on the EXH port.

Solenoid Valve Specifications

		SYJ5□90 series			
		Non-locking push type, Push-turn locking slotted type, Push-turn locking lever type			
		Pilot valve indiv	idual exh. Type		
nce (r	n/s²) Note 1)	150)/30		
		Dust	proof		
		Grommet (G), L plug connect	tor (L), M plug connector (M),		
		DIN terminal (D)			
		G, L, M	D		
Coil rated DC		24, 12, 6, 5, 3	24, 12		
AC	50/60 Hz	100, 110, 200, 220			
		±10% of the rated voltage*			
DC		0.35 (With light: 0.4 (DIN terminal with light: 0.45))			
	100 V	0.78 (With light: 0.81)	0.78 (With light: 0.87)		
	110 V	0.86 (With light: 0.89)	0.86 (With light: 0.97)		
۸.	[115 V]	[0.94 (With light: 0.97)]	[0.94 (With light: 1.07)]		
AC	200 V	1.18 (With light: 1.22)	1.15 (With light: 1.30)		
	220 V	1.30 (With light: 1.34)	1.27 (With light: 1.46)		
	[230 V]	[1.42 (With light: 1.46)]	[1.39 (With light: 1.60)]		
pre	ssor	Diode (DIN terminal, Varistor when non-polar types)			
		LED (Neon light when AC with DIN terminal)			
Pilot valve individual exh. Type 150/30 15					

- * Based on IEC60529
- * In common between 110 VAC and 115 VAC, and between 220 VAC and 230 VAC.
- * For 115 VAC and 230 VAC, the allowable voltage is –15% to +5% of rated voltage.

 Note 1) Impact resistance: No malfunction occurred when it is tested in the axial direction and at the right angles to the main valve

Vote 1) Impact resistance: No malfunction occurred when it is tested in the axial direction and at the right angles to the main valve and armature in both energized and de-energized states every once for each condition. (Values at the initial period)

Vibration resistance: No malfunction occurred in a one-sweep test between 45 and 2000 Hz. The test was performed at both energized and de-energized states in the sail direction and at the right angles to the main valve and armature. (Values at the initial period)

Note 2) At the rated voltage.

Standard Stroke

Stariuai	u Siloke	
Bore size (mm)	Standard stroke (mm) Note)	Maximum stroke (mm)
20		
25	25, 50, 75, 100,	1000
32	125, 150, 200, 250, 300	
40	200, 200, 300	

Note 1) Other intermediate strokes can be manufactured upon receipt of order.

Note 2) Applicable strokes should be confirmed according to the usage. For details, refer to the CM2 series of the "Air Cylinders Model Selection" in the Web Catalog. In addition, the products that exceed the standard stroke might not be able to fulfill the specifications due to the deflection etc.

Rod Boot Material

Symbol	Rod boot material	Maximum ambient temperature
J	Nylon tarpaulin	70°C
K	Heat resistant tarpaulin	110°C*

^{*} Maximum ambient temperature for the rod boot itself.



(ka)

Weight

	Bore size (mm)	20	25	32	40
	Basic type	0.22	0.29	0.36	0.64
	Axial foot type	0.37	0.45	0.52	0.91
Basic	Flange type	0.28	0.38	0.45	0.76
Weight	Single clevis type	0.26	0.33	0.40	0.73
	Double clevis type	0.27	0.35	0.41	0.77
	Trunnion type	0.26	0.36	0.42	0.74
Additiona	Additional weight per each 50 mm of stroke		0.07	0.09	0.14
Option	Single knuckle joint	0.06	0.06	0.06	0.23
bracket	Double knuckle joint (With pin)	0.07	0.07	0.07	0.20

Calculation: (Example) CVM5L32-100-11G

- Basic weight 0.52 (Axial foot type ø32) Additional weight 0.09/50 st
- Cylinder stroke 100 (st) $0.52 + 0.09 \times 100/50 = 0.70 \text{ kg}$
- Add 0.03 kg for the DIN terminal.
- Add 0.02 kg for the double solenoids.
- Add 0.03 kg for the closed center and exhaust center.

Mounting Type and Accessory

Accessory	Standard equipment			Option				
Mounting	Mounting nut	Rod end nut	Clevis pin	Single knuckle joint	Double knuckle joint	Pivot bracket	Pivot bracket pin	
Basic type	• (1 pc.)	•	_	•	•			
Axial foot type	• (2)	•	_	•	•			
Rod side flange type	• (1)	•	_	•	•	_	_	
Head side flange type	• (1)	•	_	•	•			
Single clevis type	— ⁽¹⁾	•	_	•	•	•	•	
Double clevis type (3)	— ⁽¹⁾	•	• (4)	•	•	_	_	
Head side trunnion type	• (1) (2)	•	_	•	•		_	
Rod side trunnion type	● (1) ⁽²⁾	•	_	•	•			

Note 1) Mounting nut is not equipped with single clevis type and double clevis type

Note 2) Trunnion nuts are equipped for head side trunnion and rod side trunnion.

Note 3) Pin and set ring are shipped together with double clevis and double knuckle joint.

Note 4) Retaining rings (cotter pins for ø40) are included in clevis pins.

Note 5) Pin and retaining ring are not included in pivot bracket. Note 6) Retaining rings are included in pivot bracket pin.

Mounting Bracket Part No.

Bore size (mm)	20 25		25 32		25 32		25 32		
Axial foot*	CM-L020B	CM-L032B		CM-L032B		CM-L032B CI		CM-L040B	
Flange	CM-F020B	CM-F	CM-F040B						
Single clevis	CM-C020B	CM-C	CM-C040B						
Double clevis**	CM-D020B	CM-D032B		CM-D040B					
Trunnion (With nut)	CM-T020B	CM-T032B		CM-T040B					

- * Two foot brackets and a mounting nut are attached.
- When ordering the foot bracket, order 2 pcs. per cylinder.
- * * Clevis pin and retaining ring (cotter pin for ø40) are packaged together.

Accessory (Option)

- Refer to page 1190 for part numbers and dimensions of the single knuckle joint, double knuckle joint, clevis pin, knuckle pin, rod end nut, mounting nut, and trunnion nut.
- Refer to page 255 of the CM2-Z series catalog for the part numbers and external dimensions of the pivot bracket and pivot bracket pin as well as for the dimensions when the cylinder is mounted.

Be sure to read this before handling the products. Refer to page 9 for safety instructions, pages 10 to 19 for actuator and auto switch precautions, and 3/4/5 I port solenoid valve precautions on the SMC website: https://www.smcworld.com

Mounting

⚠ Warning

1. Do not rotate the cover.

If a cover is rotated when installing a cylinder or screwing a fitting into the port, it is likely to damage the junction part with cover.

∕!\ Caution

1. Not able to disassemble.

Cover and cylinder tube are connected to each other by caulking method, thus making it impossible to disassemble. Therefore, internal parts of a cylinder other than rod seal are not replaceable.

2. Use caution to the popping of a retaining ring.

When replacing rod seals and removing and mounting a retaining ring, use a proper tool (retaining ring plier: tool for installing type C retaining ring). Even if a proper tool is used, it is likely to inflict damage to a human body or peripheral equipment, as a retaining ring may be flown out of the tip of a plier. Be much careful with the popping of a retaining ring. Besides, be certain that a retaining ring is placed firmly into the groove of rod cover before supplying air at the time of installment.

3. Do not touch the cylinder during operation. Use caution when handling a cylinder, which is

running at a high speed and a high frequency, because the surface of a cylinder tube could get so hot enough as to cause you get burns.

4. Do not use an air cylinder as an airhydro cylinder.

If it uses turbine oil in place of fluids for cylinder, it may result in oil leakage

5. Conjoin the rod end part, so that rod boot might not be twisted.

If a rod boot is installed with being twisted when installing a cylinder, it will cause a rod boot to fail during operation.

Model Selection

🗥 Warning

Confirm the specifications.

Products in this catalog are designed to be used for compressed air systems. If not operated within the designated pressure or temperature, it may damage the products or cause malfunction. (Refer to specifications.)

2. Energizing continuously for a long period of time

When the valve is continuously energized for a long period of time, the performance may deteriorate, shorten the service life or affect peripheral equipment adversely temperature rises when coils generate heat.



Built-in One-touch Fitting

CVM5 Mounting type Bore size F — For "How to Order", refer to page 1175.

Built-in One-touch fitting

One-touch fittings are installed on cylinders



Application/Tubing O.D.


Bore size (mm)	20	25	32	40			
Applicable tubing O.D. (mm)	ø6/4	ø6/4	ø6/4	ø6/4			
Applicable tubing material	Can be used for either nylon, soft nylor or polyurethane tube.						

Specifications

Specifications													
Action	D	ouble acting	g, Single ro	d									
Bore size (mm)		20, 25,	32, 40										
Maximum operating pressure		0.7	ИРа										
Minimum operating pressure		0.15	MPa										
Cushion	Rubber bumper												
Piping	Built-in One-touch fitting												
Piston speed	ø20	ø25	ø32	ø40									
(mm/s)	50 to 700	50 to 650	50 to 590	50 to 420									
Mounting	Head sid	de flange typ levis type, R	be, Rod side e, Single cle od side trunr runnion type	vis type, nion type,									

For the dimensions of mounting bracket, refer to pages 1181 to 1184.

Opening Range of Throttle Valve and Driving Speed



Measuring conditions: Operating pressure 0.5 MPa Mounting: horizontal Load: no load on the return side The speeds indicated above are for reference.

Manual Operation

Manual operation is possible by pushing the manual button indicated with the arrow.




Piston Speed Adjustment

- To slow down the piston speed, screw in the needle of the silencer type exhaust throttle valve clockwise, which reduces the amount of air that is discharged.
- To adjust the piston extension side, regulate the "R1" side silencer type exhaust throttle
 - To adjust the retraction side, regulate the "R2" side silencer exhaust throttle valve.
- The needle valve of the throttle valve can be fully opened by loosening it 8 turns from the fully closed position.
- The needle valve has a loosening prevention construction.


Changing between Rod Extended when Energized and Rod Retracted when Energized

Step [This procedure is for changing the rod extended when energized to the rod retracted when energized.]

 Using a tool, loosen the two hexagon socket bolts, and remove the plate and the solenoid valve. At this time, instead of removing the plate and the solenoid valve separately, remove them together, with the hexagon socket bolts remaining inserted.



2. A sub-plate gasket is inside the sub-plate. Invert this sub-plate gasket 180° and install it with its letter "B" visible. (A portion that protrudes is provided on the periphery of the sub-plate gasket, and the letter "B" is on one side of this protrusion.)



 Install the solenoid valve and the plate, and tighten the hexagon socket bolts with a tool. The tightening torque is between 0.6 and 0.8 N·m

After tightening, press the manual button on the solenoid valve, check for any air leaks, and verify the operating conditions. Distinction between rod extended when energized and rod retracted when energized can be determined from the outside, by looking through the small window in the sub-olate.




Convex position of sub-plate gasket




Rod retracted when energized


Construction







Built-in One-touch fitting



Component Parts

CUI	iiponeni Faris		
No.	Description	Material	Note
1	Rod cover	Aluminum alloy	Anodized
2	Head cover	Aluminum alloy	Anodized
3	Cylinder tube	Stainless steel	
4	Piston	Aluminum alloy	
5	Piston rod	Carbon steel	Hard chrome plated
6	Bushing	Bearing alloy	
7	Seal retainer	Stainless steel	
8	Retaining ring	Carbon steel	Phosphate coated
9	Pipe	Aluminum alloy	
10	Stud	Brass	Electroless nickel plated
11	Hex. socket head cap screw with spring washer	Stainless steel	
12	Hex. socket head cap screw with spring washer	Stainless steel	
13	Plate	Aluminum alloy	Metallic painted
14	Sub-plate	Aluminum alloy	Metallic painted
15	Solenoid valve	_	Refer to the "How to order" below.*
16	Bumper A	Urethane	
17	Bumper B	Urethane	


Component Parts

00.	iiponenti arts		
No.	Description	Material	Note
18	Retaining ring	Stainless steel	
19	Piston seal	NBR	
20	Piston gasket	NBR	
21	Gasket	Resin	
22	Pipe gasket	Urethane rubber	
23	Wear ring	Resin	
24	Head cover gasket	NBR	
25	Sub-plate gasket	NBR	
26	Gasket	NBR	
27	Spacer gasket	Resin	Except ø25
28	Exhaust throttle with silencer	_	ASN2-M5
29	Mounting nut	Carbon steel	Nickel plated
30	Rod end nut	Carbon steel	Zinc chromated
32	One-touch fitting	_	Port size: Ø6

Replacement Parts/Seal Kit

		,				
No.	Description	Material		Parl	no.	
NO.	Description	ivialeriai	20	25	32	40
31	Rod seal	NBR	CM220-PS	CM225-PS	CM232-PS	CM240-PS


^{*} Since the seal kit does not include a grease pack, order it separately. Grease pack part no.: GR-S-010 (10g)





CVM5 Series

Basic Type (B)



For DIN terminal and double solenoid, refer to page 1184.

						1																	(mm)
Bore size (mm)	Stroke range	Α	AL	Вı	B ₂	D	Eh₃	F	Q	QY	Н	Нı	H ₂	нх	- 1	K	KA	MM	N	NA	NN	s	ZZ
20	Up to 300	18	15.5	13	26	8	20-0.033	13	19.8	14	41	5	8	65.3	28	5	6	M8 x 1.25	15	24	M20 x 1.5	62	116
25	Up to 300	22	19.5	17	32	10	26-8.033	13	22	14	45	6	8	70.5	33.5	5.5	8	M10 x 1.25	15	30	M26 x 1.5	62	120
32	Up to 300	22	19.5	17	32	12	26-8.033	13	25.8	16	45	6	8	76.5	37.5	5.5	10	M10 x 1.25	15	34.5	M26 x 1.5	64	122
40	Up to 300	24	21	22	41	14	32-0.039	16	29.8	16	50	8	10	84.5	46.5	7	12	M14 x 1.5	21.5	42.5	M32 x 2	88	154

With Rod	Boot	t																	(mm)
Bore size (mm)	Вз	е	-				h							l				JH	JW
Dore Size (IIIII)	D3	-	'	1 to 50	51 to 100	101 to 150	151 to 200	201 to 300	301 to 400	401 to 500	1 to 50	51 to 100	101 to 150	151 to 200	201 to 300	301 to 400	401 to 500	(Reference)	(Reference)
20	30	36	18	68	81	93	106	131	156	181	12.5	25	37.5	50	75	100	125	23.5	10.5
25	32	36	18	72	85	97	110	135	160	185	12.5	25	37.5	50	75	100	125	23.5	10.5
32	32	36	18	72	85	97	110	135	160	185	12.5	25	37.5	50	75	100	125	23.5	10.5
40	41	46	20	77	90	102	115	140	165	190	12.5	25	37.5	50	75	100	125	27	10.5


Bore size (mm)				ZZ			
bole size (IIIII)	1 to 50	51 to 100	101 to 150	151 to 200	201 to 300	301 to 400	401 to 500
20	143	156	168	181	206	231	256
25	147	160	172	185	210	235	260
32	149	162	174	187	212	237	262
40	181	194	206	219	244	269	294

^{*} For short strokes, a solenoid valve may protrude from the rod cover end. Confirm S dimension and solenoid dimensions. * Long stroke type includes ones for strokes more than 301 mm.



Valve Mounted Cylinder CVM5 Series

Axial Foot Type (L)



																				()
Bore size (mm)	Stroke range	Α	AL	В	Вı	B ₂	D	F	Н	H₁	H ₂	1	K	KA	LC	LD	LH	LS	LT	LX
20	Up to 300	18	15.5	40	13	26	8	13	41	5	8	28	5	6	4	6.8	25	102	3.2	40
25	Up to 300	22	19.5	47	17	32	10	13	45	6	8	33.5	5.5	8	4	6.8	28	102	3.2	40
32	Up to 300	22	19.5	47	17	32	12	13	45	6	8	37.5	5.5	10	4	6.8	28	104	3.2	40
40	Up to 300	24	21	54	22	41	14	16	50	8	10	46.5	7	12	4	7	30	134	3.2	55


Bore size (mm)	LY	LZ	MM	N	NA	NN	S	Х	Y	Z	ZZ
20	70.5	55	M8 x 1.25	15	24	M20 x 1.5	62	20	8	21	131
25	76.5	55	M10 x 1.25	15	30	M26 x 1.5	62	20	8	25	135
32	78.8	55	M10 x 1.25	15	34.5	M26 x 1.5	64	20	8	25	137
40	84.8	75	M14 x 1.5	21.5	42.5	M32 x 2	88	23	10	27	171

* Brackets are packaged together.

(mm)

(mm)

Rod Side Flange Type (F)



																			/
Bore size (mm)	Stroke range	Α	AL	В	Вı	B ₂	C ₂	D	Eh₃	F	FD	FT	FX	FY	FZ	Н	H₁	H ₂	нх
20	Up to 300	18	15.5	34	13	26	30	8	20 -0.033	13	7	4	60	_	75	41	5	8	65.3
25	Up to 300	22	19.5	40	17	32	37	10	26-0.033	13	7	4	60	_	75	45	6	8	70.5
32	Up to 300	22	19.5	40	17	32	37	12	26-0.033	13	7	4	60	_	75	45	6	8	76.5
40	Up to 300	24	21	52	22	41	47.3	14	32 0 0 0 0 0 0	16	7	5	66	36	82	50	8	10	84.5

												(111111)
Bore size (mm)	ı	K	KA	MM	N	NA	NN	Q	QY	s	Z	ZZ
20	28	5	6	M8 x 1.25	15	24	M20 x 1.5	19.8	14	62	37	116
25	33.5	5.5	8	M10 x 1.25	15	30	M26 x 1.5	22	14	62	41	120
32	37.5	5.5	10	M10 x 1.25	15	34.5	M26 x 1.5	25.8	16	64	41	122
40	46.5	7	12	M14 x 1.5	21.5	42.5	M32 x 2	29.8	16	88	45	154


^{*} For short strokes, a solenoid valve may protrude from the rod cover end. Confirm S dimension and solenoid dimensions.



^{*} Brackets are packaged together.

CVM5 Series

Head Side Flange Type (G)




	ou one range	••																• • • •	
20	Up to 300	18	15.5	34	13	26	30	8	20-0.033	13	7	4	60	_	75	41	5	8	65.3
25	Up to 300	22	19.5	40	17	32	37	10	26-0.033	13	7	4	60	_	75	45	6	8	70.5
32	Up to 300	22	19.5	40	17	32	37	12	26-0.033	13	7	4	60	_	75	45	6	8	76.5
40	Up to 300	24	21	52	22	41	47.3	14	32 -0.039	16	7	5	66	36	82	50	8	10	84.5
												(m	m)						

Bore size (mm)	- 1	K	KA	MM	N	NA	NN	Q	QY	S	Z	Z
20	28	5	6	M8 x 1.25	15	24	M20 x 1.5	19.8	14	62	107	107
25	33.5	5.5	8	M10 x 1.25	15	30	M26 x 1.5	22	14	62	111	111
32	37.5	5.5	10	M10 x 1.25	15	34.5	M26 x 1.5	25.8	16	64	113	113
40	46.5	7	12	M14 x 1.5	21.5	42.5	M32 x 2	29.8	16	88	143	143

* Brackets are packaged together.


Single Clevis Type (C)



																		(111111)
Bore size (mm)	Stroke range	Α	AL	B₁	CD	CI	СХ	D	Eh₃	F	Н	H ₁	- 1	нх	K	KA	L	MM
20	Up to 300	18	15.5	13	9	24	10	8	20-0.033	13	41	5	28	65.3	5	6	30	M8 x 1.25
25	Up to 300	22	19.5	17	9	30	10	10	26 -0.033	13	45	6	33.5	70.5	5.5	8	30	M10 x 1.25
32	Up to 300	22	19.5	17	9	30	10	12	26 -0.033	13	45	6	37.5	76.5	5.5	10	30	M10 x 1.25
40	Up to 300	24	21	22	10	38	15	14	32 -0.039	16	50	8	46.5	84.5	7	12	39	M14 x 1.5
									(mr	n)								

Bore size (mm)	N	NA	NN	Q	QY	RR	S	U	Z	ZZ
20	15	24	M20 x 1.5	19.8	14	9	62	14	133	142
25	15	30	M26 x 1.5	22	14	9	62	14	137	146
32	15	34.5	M26 x 1.5	25.8	16	9	64	14	139	148
40	21.5	42.5	M32 x 2	29.8	16	11	88	18	177	188

Double Clevis Type (D)



Bore size (mm)	Stroke range	Α	AL	Вı	CD	CI	CL	СХ	CZ	D	Eh₃	F	Н	Нı	нх	ı	K	KA	L
20	Up to 300	18	15.5	13	9	24	25	10	19	8	20 -0.033	13	41	5	65.3	28	5	6	30
25	Up to 300	22	19.5	17	9	30	25	10	19	10	26-0.033	13	45	6	70.5	33.5	5.5	8	30
32	Up to 300	22	19.5	17	9	30	25	10	19	12	26-0.033	13	45	6	76.5	37.5	5.5	10	30
40	Up to 300	24	21	22	10	38	41.2	15	30	14	32-0.039	16	50	8	84.5	46.5	7	12	39


(mm)

Bore size (mm)	MM	N	NA	NN	Q	QY	RR	S	U	Z	ZZ
20	M8 x 1.25	15	24	M20 x 1.5	19.8	14	9	62	14	133	142
25	M10 x 1.25	15	30	M26 x 1.5	22	14	9	62	14	137	146
32	M10 x 1.25	15	34.5	M26 x 1.5	25.8	16	9	64	14	139	148
40	M14 x 1.5	21.5	42.5	M32 x 2	29.8	16	11	88	18	177	188

 Clevis pin and snap ring (cotter pin for ø40) are packaged together.

Rod Side Trunnion Type (U)






							-								•			(mm)
Bore size (mm)	Stroke range	Α	AL	Вı	B ₂	D	Eh₃	F	Н	Нı	нх	1	K	KA	MM	N	NA	NN
20	Up to 300	18	15.5	13	26	8	20 -0.033	13	41	5	65.3	28	5	6	M8 x 1.25	15	24	M20 x 1.5
25	Up to 300	22	19.5	17	32	10	26-0.033	13	45	6	70.5	33.5	5.5	8	M10 x 1.25	15	30	M26 x 1.5
32	Up to 300	22	19.5	17	32	12	26-0.033	13	45	6	76.5	37.5	5.5	10	M10 x 1.25	15	34.5	M26 x 1.5
40	Up to 300	24	21	22	41	14	32 0 0 0 0 0 0 0 0 0 0 0 0 0 0 0 0 0 0 0	16	50	8	84.5	46.5	7	12	M14 x 1.5	21.5	42.5	M32 x 2

										\·····
Bore size (mm)	Q	QY	S	TD	TT	TX	TY	TZ	Z	ZZ
20	19.8	14	62	8	10	32	32	52	36	116
25	22	14	62	9	10	40	40	60	40	120
32	25.8	16	64	9	10	40	40	60	40	122
40	29.8	16	88	10	11	53	53	77	44.5	154

^{*} Brackets are packaged together.

CVM5 Series

Head Side Trunnion Type (T)




																		(111111)
Bore size (mm)	Stroke range	Α	AL	B ₁	B ₂	D	Eh₃	F	Н	Нı	НХ	_	K	KA	MM	N	NA	NN
20	Up to 300	18	15.5	13	26	8	20 -0.033	13	41	5	65.3	28	5	6	M8 x 1.25	15	24	M20 x 1.5
25	Up to 300	22	19.5	17	32	10	26-0.033	13	45	6	70.5	33.5	5.5	8	M10 x 1.25	15	30	M26 x 1.5
32	Up to 300	22	19.5	17	32	12	26 0 0 0 0	13	45	6	76.5	37.5	5.5	10	M10 x 1.25	15	34.5	M26 x 1.5
40	Up to 300	24	21	22	41	14	32-0.039	16	50	8	84.5	46.5	7	12	M14 x 1.5	21.5	42.5	M32 x 2
								(mm)	1									

										()
Bore size (mm)	Q	QY	S	TD	TT	TX	TY	TZ	Z	ZZ
20	19.8	14	62	8	10	32	32	52	108	118
25	22	14	62	9	10	40	40	60	112	122
32	25.8	16	64	9	10	40	40	60	114	124
40	29.8	16	88	10	11	53	53	77	143.5	154

^{*} Brackets are packaged together.

DIN Terminal

Double Solenoid




For the mounting brackets of flange, single clevis, double clevis and head side trunnion type, the doule soleoid may not be used depending on the mounting conditions.

Valve Mounted Cylinder: Non-rotating Rod Type **Double Acting**

CVM5K Series

Ø20, Ø25, Ø32, Ø40





Applicable Auto Switches/Refer to pages 1341 to 1435 for further information on auto switches.

		Electrical	or light	NA E-si		Load volt	age	Auto s	switch	Lead	l wir	e ler	igth	(m)	Pre-wired		
Type	Special function	entry	ndicator	Wiring (Output)		DC	AC	mo	del	0.5	1	3	5	None	connector	Applica	ble load
		oy	Рá	(Output)			Λ0	Perpendicular	In-line	(Nil)	(M)	(L)	(Z)	(N)	00111100101		
				3-wire (NPN)		5 V, 12 V		M9NV	M9N	•	•	•	0	_	0	IC	
ڃ		Grommet		3-wire (PNP)		J V, 12 V		M9PV	M9P	•	•	•	0	_	0	circuit	
switch				2-wire		12 V		M9BV	M9B	•	•	•	0	_	0		
		Connector		Z-WIIG		12 4		_	H7C	•	_	•	•	•	_		
anto	Diagnostic indication			3-wire (NPN)		5 V, 12 V		M9NWV	M9NW	•	•	•	0	_	0	IC	Relay,
a a	(2-color indicator)		Yes	3-wire (PNP)	24 V	3 V, 12 V	_	M9PWV	M9PW	•	•	•	0	_	0	circuit	PLC
state	(=			2-wire		12 V		M9BWV	M9BW	•	•	•	0	_	0	_	
g	Water resistant	Grommet		3-wire (NPN)		5 V, 12 V		M9NAV*1	M9NA*1	0	0	•	0	_	0	IC	
Solid	(2-color indicator)			3-wire (PNP)		5 V, 12 V		M9PAV*1	M9PA*1	0	0	•	0	_	0	circuit	
S	,			2-wire		12 V		M9BAV*1	M9BA*1	0	0	•	0	_	0	_	
	With diagnostic output (2-color indicator)			4-wire (NPN)		5 V, 12 V		_	H7NF	•	_	•	0	_	0	IC circuit	
_			Yes	3-wire (NPN equivalent)		5 V	_	A96V	A96	•	_	•	二	_	_	IC circuit	_
switch			165				100 V	A93V*2	A93	•	•	•	•	_	_	_	
Š		Grommet	None				100 V or less	A90V	A90	•	_	•	_	_	_	IC circuit	
			Yes			12 V	100 V, 200 V	_	B54	•	_	•	•	_	_		Relay,
anto			None	2-wire	24 V	12 V	200 V or less	_	B64	•	_	•	上	<u> </u>		-	PLC
Reed		Connector	Yes				_	_	C73C	•	_	•	•	•	_		
- B			None				24 V or less	_	C80C	•	_	•	•	•	_	IC circuit	
	Diagnostic indication (2-color indicator)	Grommet	Yes			_	l —	_	B59W	•	l —		l —	l —	-	l —	

- * Lead wire length symbols: 0.5 m Nil (Example) M9NW
 - (Example) M9NWM 1 m M 3 m L (Example) M9NWL 5 m Z (Example) M9NWZ
- * Solid state auto switches marked with "O" are produced upon receipt of order. *1 Water resistant type auto switches can be mounted on the above models.
- but in such case SMC cannot guarantee water resistance. Consult with SMC regarding water resistant types with the above model numbers. *2 1 m type lead wire is only applicable to D-A93.
- None N (Example) H7CN * Since there are other applicable auto switches than listed, refer to page 1193 for details.
- For details about auto switches with pre-wired connector, refer to pages 1410 and 1411.
 D-A9□/M9□ auto switches are shipped together (not assembled). (Only auto switch mounting brackets are assembled before shipped.)



A hexagon shaped rod that does not rotate.

Non-rotating accuracy

 \emptyset **20**, \emptyset **25** $-\pm$ **0.7**°

 \emptyset 32, \emptyset 40 — \pm 0.5°


Can operate without lubrication.

Auto switches can also be mounted.

Can be installed with auto switches to facilitate the detection of the cylinder's stroke position.



Symbol Rubber bumper





Made to Order Specifications Click here for details

Symbol	Specifications
-XA□	Change of rod end shape

Refer to pages 1191 to 1193 for cylinders with auto switches.

- · Proper auto switch mounting position (detection at stroke end) and mounting height
- · Minimum auto switch mounting stroke
- · Operating range
- · Auto switch mounting bracket: Part no.

Specifications

Applicable	e bore size (mm)	20	25	32	40
Rod non-rota	ting accuracy	± 0	.7°	±().5°
Fluid			А	ir	
Action			Double actin	g, Single rod	
Proof pressur	re		1.01	MРа	
Maximum ope	erating pressure		0.7 [MРа	
Minimum ope	rating pressure		0.15	MPa	
Ambient and	fluid temperature		−10 to 50°C	(No freezing)	
Lubrication			Not required	i (Non-lube)	
Stroke length	tolerance		+1.	4	
Piston speed	(mm/s)	50 to 700 *	50 to 650*	50 to 590*	50 to 420*
Allowable kin	etic energy	0.27 J	0.4 J	0.65 J	1.2 J
Port size	Screw-in type		Rc	1/8	
FUIT SIZE	Built-in One-touch fitting		O.D.: ø6	/I.D.: ø4	
Mounting		Head s	ide flange typ levis type, He	oe, Rod side f e, Single clev ead side trunr unnion type	is type,

Note) The figures marked with "*" represent the values of the cylinder with the silencer type exhaust throttle valve removed. To operate the cylinder at these values, prevent dust from entering by installing an AN120-M5 silencer on the EXH port.

Solenoid Valve Specifications

Series			SYJ5□90 series		
Manual override			Non-locking push type, Push-turn locking slotted type, Push-turn locking lever type		
Pilot exhaust	t exhaust Pilot valve individual exh. Type			ridual exh. Type	
Impact/Vibration resista	nce (ı	n/s²) Note 1)	150)/30	
Enclosure			Dust	proof	
			Grommet (G), L plug connector (L), M plug connector (M		
Electrical entry			DIN tern	DIN terminal (D)	
			G, L, M	D	
Coil rated DC AC 50/60 Hz			24, 12, 6, 5, 3	24, 12	
		50/60 Hz	100, 110, 200, 220		
Allowable voltage	•		±10% of the r	rated voltage*	
Power consumption (W) Note 2)	DC		0.35 (With light: 0.4 (DIN	terminal with light: 0.45)}	
		100 V	0.78 (With light: 0.81)	0.78 (With light: 0.87)	
		110 V	0.86 (With light: 0.89)	0.86 (With light: 0.97)	
Apparent power	AC	[115 V]	[0.94 (With light: 0.97)]	[0.94 (With light: 1.07)]	
(VA) Note 2)	AC	200 V	1.18 (With light: 1.22)	1.15 (With light: 1.30)	
		220 V	1.30 (With light: 1.34)	1.27 (With light: 1.46)	
		[230 V]	[1.42 (With light: 1.46)]	[1.39 (With light: 1.60)]	
Surge voltage su	Surge voltage suppressor Diode (DIN terminal, Varistor when non-polar type			stor when non-polar types)	
Indicator light			LED (Neon light when AC with DIN terminal)		

- * Based on IEC60529
- * In common between 110 VAC and 115 VAC, and between 220 VAC and 230 VAC.

* For 115 VAC and 230 VAC, the allowable voltage is –15% to +5% of rated voltage.

Note 1) Impact resistance: No malfunction occurred when it is tested in the axial direction and at the right angles to the main valve and armature in both energized and de-energized states every once for each condition. (Values at the initial period)

Vibration resistance: No malfunction occurred in a one-sweep test between 45 and 2000 Hz. The test was performed at both energized and de-energized states in the axial direction and at the right angles to the main valve and armature. (Values at the initial period)

Note 2) At the rated voltage.

Standard Stroke

Stariuai	u Slioke
Bore size (mm)	Standard stroke (mm) Note)
20	
25	25, 50, 75, 100, 125, 150
32	200, 250, 300
40	

Rod Boot Material

Symbol	Rod boot material	Maximum ambient temperature
J	Nylon tarpaulin	70°C
K	Heat resistant tarpaulin	110°C *

^{*} Maximum ambient temperature for the rod boot itself.

Note) Other intermediate strokes can be manufactured upon receipt of order.

Although it is possible to make up to 1000 stroke length, when exceeding the standard stroke, there may be the case which cannot meet the specifications.



Valve Mounted Cylinder: Non-rotating Rod Type CVM5K Series

Weiaht

(kg) 20 25 32 40 Bore size (mm) Basic type 0.22 0.29 0.36 0.64 Axial foot type 0.37 0.45 0.52 0.91 Rasic Flange type 0.38 0.45 0.76 0.28 weiaht 0.26 0.33 0.40 0.73 Single clevis type Double clevis type 0.27 0.35 0.41 0.77 Trunnion type 0.74 0.26 0.36 0.42 Additional weight per each 50 mm of stroke 0.05 0.07 0.09 0 14 Single knuckle joint 0.06 0.06 0.06 0.23 Option bracket Double knuckle joint (with pin) 0.07 0.07 0.07 0.20

Calculation: (Example) CVM5KL32-100-11G

- .. 0.52 (Axial foot type ø32) Additional weight 0.09/50 st · Basic weight -
- Cylinder stroke ----- 100 (st)
- $0.52 + 0.09 \times 100/50 = 0.70 \text{ kg}$
- . Add 0.03 kg for the DIN terminal
- . Add 0.02 kg for the double solenoids
- . Add 0.03 kg for the closed center and exhaust center.

Mounting Bracket and Accessory

Accessory	Stan	Standard equipment			Option				
Mounting	Mounting nut	Rod end nut	Clevis pin	Single knuckle joint	Double (3) knuckle joint	Pivot ⁽⁵⁾ bracket	Pivot (6) bracket pin		
		1100	P				э		
Basic type	(1 pc.)	•	_	•	•				
Axial foot type	(2)	•	_	•	•	_	_		
Rod side flange type	• (1)	•	_	•	•				
Head side flange type	• (1)	•	_	•	•				
Single clevis type	— ⁽¹⁾	•	_	•	•	•	•		
Double clevis type (3)	— ⁽¹⁾	•	(4)	•	•	_	_		
Head side trunnion type	• (1) (2)	•	_	•	•				
Rod side trunnion type	• (1) (2)	•	_	•	•	•	_		
				•					

Mounting Bracket Part No.

Bore size (mm)	20	25 32	40	
Axial foot *	CM-L020B	CM-L032B	CM-L040B	
Flange	CM-F020B	CM-F032B	CM-F040B	
Single clevis	CM-C020B	CM-C032B	CM-C040B	
Double clevis **	CM-D020B	CM-D032B	CM-D040B	
Trunnion (With nut)	CM-T020B	CM-T032B	CM-T040B	

- * Two foot brackets and a mounting nut are attached. When ordering the foot bracket, order 2 pcs. per
- Clevis pin and snap ring (cotter pin for ø40) are packaged together.

- Note 1) Mounting nut is not equipped with single clevis type and double clevis type.
- Note 2) Trunnion nuts are equipped for head side trunnion and rod side trunnion.
- Note 3) Pin and set ring are shipped together with double clevis and double knuckle joint.
- Note 4) Retaining rings (cotter pins for ø40) are included in clevis pins.
- Note 5) Pin and retaining ring are not included in pivot bracket
- Note 6) Retaining rings are included in pivot bracke pin.

Accessory (Option)

- * Refer to page 1190 for part numbers and dimensions of the single knuckle joint, double knuckle joint, clevis pin, knuckle pin, rod end nut, mounting nut, and trunnion nut.
- * Refer to page 255 of the CM2-Z series catalog for the part numbers and external dimensions of the pivot bracket and pivot bracket pin as well as for the dimensions when the cylinder is mounted

Precautions

Be sure to read this before handling the products. Refer to page 9 for safety instructions, pages 10 to 19 for actuator I and auto switch precautions, and 3/4/5 port solenoid valve precautions on the SMC website: https://www.smcworld.com

Precautions

∧ Warning

1. Do not rotate the cover.

If a cover is rotated when installing a cylinder or screwing a fitting into the port, it is likely to damage the junction part with cover.

1. Avoid using the air cylinder in such a way that rotational torque would be applied to the piston rod.

If rotational torque is applied, the non-rotating guide will deform, causing a loss of non-rotating accuracy. Also, to screw a bracket or a nut onto the threaded portion at the end of the piston rod, make sure to retract the piston rod entirely, and place a wrench on the parallel sections of the rod that protrudes. To tighten, take precautions to prevent the tightening torque from being applied to the non-rotating guide

Allowable	ø 20	ø 25	ø 32	ø 40
rotational torque (N·m or less)	0.2	0.25	0.25	0.44



Disassembly/Replacement

1. When replacing rod seals, please contact SMC.

Air leakage may be happened, depending on the position in which a rod seal is fitted. Thus, please contact SMC when replacing them.

2. Not able to disassemble.

Since the cover and the cylinder tube are combined by crimping method, it is impossible to disassemble it. Therefore, the internal parts of a cylinder other than rod seal cannot be replaced at all.

3. Do not touch the cylinder during operation.

If the cylinder is operating at a high frequency, be aware that the cylinder tube surface could become very hot, creating the risk of burns.

4. Conjoin the rod end part, so that rod boot might not be twisted.

If a cylinder were installed with its rod boot being twisted, the rod boot could be damaged during operation.

Model Selection

1. Confirm the specifications.

Products in this catalog are designed to be used for compressed air systems. If not operated within the designated pressure or temperature, it may damage the products or cause malfunction. (Refer to specifications.)


2. Energizing continuously for a long period of time


When the valve is continuously energized for a long period of time, the performance may deteriorate, shorten the service life or affect peripheral equipment adversely since temperature rises when coils generate heat.




CVM5K Series

Construction







Component Parts

00.	iiponeni Faits		
No.	Description	Material	Note
1	Rod cover	Aluminum alloy	Anodized
2	Head cover	Aluminum alloy	Anodized
3	Cylinder tube	Stainless steel	
4	Piston	Aluminum alloy	
5	Piston rod	Stainless steel	
6	Non-rotating guide	Bearing alloy	
7	Seal retainer	Rolled steel	Nickel plated
8	Retaining ring	Carbon steel	Phosphate coated
9	Pipe	Aluminum alloy	
10	Stud	Brass	Electroless nickel plated
11	Hex. socket head cap screw with spring washer	Stainless steel	
12	Hex. socket head cap screw with spring washer	Stainless steel	
13	Plate	Aluminum alloy	Metallic painted
14	Sub-plate	Aluminum alloy	Metallic painted
15	Solenoid valve	_	Refer to the "How to order" below.*
16	Bumper A	Urethane	
17	Bumper B	Urethane	

How to order solenoid valves						
SYJ5 🗆 90 - 🗆 🗀		Nil	Valves other than those below			
Type of • Rated actuation voltage •	• Manual override	-Q	All valves with a DC rated voltage Valves with an AC rated voltage (DIN terminal only)			
Electrical entry • Light/Surge voltage suppressor						

Component Parts

Cor	omponent Parts					
No.	Description	Material	Note			
18	Retaining ring	Stainless steel				
19	Piston seal	NBR				
20	Piston gasket	NBR				
21	Gasket	Resin				
22	Pipe gasket	Urethane rubber				
23	Wear ring	Resin				
24	Head cover gasket	NBR				
25	Sub-plate gasket	NBR				
26	Gasket	NBR				
27	Spacer gasket	Resin	Except ø25			
28	Exhaust throttle with silencer	_	ASN2-M5			
29	Mounting nut	Carbon steel	Nickel plated			
30	Rod end nut	Carbon steel	Zinc chromated			
32	One-touch fitting	_	Port size: ø6			


Replacement Parts/Seal Kit

No.	Description	Matarial	Part no.			
NO.	Description	Material	20	25	32	40
31	Rod seal	NBB	CW3K3U-B6	CMOKOE-DC	CW3K33-DC	CW3K4U-B6

Since the seal kit does not include a grease pack, order it separately.
 Grease pack part no.: GR-S-010 (10g)

Valve Mounted Cylinder: Non-rotating Rod Type CVM5K Series

Basic Type (B): External Dimensions



For DIN terminal and double solenoid, refer to page 1184.

. 0. 5	imia ana ao	ub.0 0	0.00.	u, 1010	. то ро	.go o															(mm)
Bore size (mm)	Stroke range	Α	AL	Вı	B ₂	Eh₃	F	Q	QY	Н	H ₁	H ₂	нх	1	KA	MM	N	NA	NN	S	ZZ
20	Up to 300	18	15.5	13	26	20 -0.033	13	19.8	14	41	5	8	65.3	28	8.2	M8 x 1.25	15	24	M20 x 1.5	62	116
25	Up to 300	22	19.5	17	32	26 -0.033	13	22	14	45	6	8	70.5	33.5	10.2	M10 x 1.25	15	30	M26 x 1.5	62	120
32	Up to 300	22	19.5	17	32	26 -0.033	13	25.8	16	45	6	8	76.5	37.5	12.2	M10 x 1.25	15	34.5	M26 x 1.5	64	122
40	Up to 300	24	21	22	41	32 0000	16	29.8	16	50	8	10	84.5	46.5	142	M14 x 1 5	21.5	42.5	M32 x 2	88	154

	With Rod Boot													(mm)		
Bore size (mm) B ₃ e f							h					l			JH	JW
	Bore size (mm)	Вз	е	Т	1 to 50	51 to 100	101 to 150	151 to 200	201 to 300	1 to 50	51 to 100	101 to 150	151 to 200	201 to 300	(Reference)	(Reference)
	20	30	36	18	68	81	93	106	131	12.5	25	37.5	50	75	23.5	10.5
	25	32	36	18	72	85	97	110	135	12.5	25	37.5	50	75	23.5	10.5
	32	32	36	18	72	85	97	110	135	12.5	25	37.5	50	75	23.5	10.5
	40	41	46	20	77	90	102	115	140	12.5	25	37.5	50	75	27	10.5

					(mm)
D			ZZ		
Bore size (mm)	1 to 50	51 to 100	101 to 150	151 to 200	201 to 300
20	143	156	168	181	206
25	147	160	172	185	210
32	149	162	174	187	212
40	181	194	206	219	244


SMC

CVM5 Series

Accessory dimensions

Single Knuckle Joint Mounting


(mm)



Bore size	Α	Н	MM	ND _{H10}	NX ₁	U ₁	R2	Υ	Z
20	18	41	M8 x 1.25	9 +0.058	9 -0.1	14	10	11	66
25, 32	22	45	M10 x 1.25	9 +0.058	9 -0.1	14	10	14	69
40	24	50	M14 x 1.5	12 +0.070	16 =0.1	20	14	13	92

Double Knuckle Joint Mounting


(mm)



				_
9 +0.2	10	14	11	66
9 +0.2	10	14	14	69
16 +0.3	13	25	13	92
	9 +0.1 9 +0.2 +0.1	9 +0.1 10 9 +0.1 10	9 +0.1 10 14 9 +0.1 10 14	9 +0.1 10 14 11 9 +0.2 10 14 14 16 +0.3 12 25 12

Single Knuckle Joint


(mm)



Part no.	Applicable bore size	Α	A ₁	Εı	Lı	MM	ND _{H10}	NX	R₁	U ₁
I-020B	20	46	16	20	36	M8 x 1.25	9 +0.058	9 -0.1	10	14
I-032B	25, 32	48	18	20	38	M10 x 1.25	9 +0.058	9 -0.1	10	14
I-040B	40	69	22	24	55	M14 x 1.5	12 +0.070	16 -0.1	15.5	20

Double Knuckle Joint

(mm)



Part no.	bore size		A	Αı	E1	L	Li	IVIIVI	ND
Y-020B	20		46	16	20	25	36	M8 x 1.25	9
Y-032B	25, 32		48	18	20	25	38	M10 x 1.25	9
Y-040B	40		68	22	24	49.7	55	M14 x 1.5	12
Part no.	NX	NZ	R ₁	U ₁		cable pir ar no.	Reta Cotte	ining ring size	
Y-020B	9 +0.2	18	5	14	CI	DP-1	Тур	e C9 for shaft	
Y-032B	9 +0.2	18	5	14	CI	CDP-1		e C9 for shaft	
Y-040B	16 +0.3	38	13	25	CI	CDP-3		3 x 18 ℓ	

^{*} Knuckle pins and retaining rings (cotter pins for ø40) are included.

Double Clevis Pin/Material: Carbon steel

Bore size: Ø20, Ø25, Ø32 Bore size



Retaining ring: Type C9 for shaft * Retaining rings (cotter pins for ø40) are included.

Bore size: Ø40 CDP-2



(mm)

Cotter pins used

Double Knuckle Pin/Material: Carbon steel



Retaining ring: Type C9 for shaft

Retaining rings (cotter pins for ø40) are included.

Bore size: Ø40 CDP-3 2ר3 Drill through 888 4 41.7 49.7

Cotter pins used ø3 x 18 ℓ

Rod End Nut

Material: Carbon steel

(mm)



Part no.	Applicable bore size	В	С	D	d	Н
NT-02	20	13	15.0	12.5	M8 x 1.25	5
NT-03	25, 32	17	19.6	16.5	M10 x 1.25	6
NT-04	40	22	25.4	21.0	M14 x 1.5	8

Mounting Nut


Material: Carbon steel



Part no.	Applicable bore size	В	С	D	d	Н
SN-020B	20	26	30	25.5	M20 x 1.5	8
SN-032B	25, 32	32	37	31.5	M26 x 1.5	8
SN-040B	40	41	47.3	40.5	M32 x 2.0	10

Trunnion Nut

(mm)




Part no.	Applicable bore size	В	С	D	d	Н
TN-020B	20	26	28	25.5	M20 x 1.5	10
TN-032B	25, 32	32	34	31.5	M26 x 1.5	10
TN-040B	40	41	45	40.5	M32 x 2	10

CVM5 Series

Auto Switch Mounting 1

Auto Switch Proper Mounting Position (Detection at Stroke End) and Mounting Height



Auto Switch Proper Mounting Position (Detection at Stroke End) and Mounting Height

Auto Switch Proper Mounting Position (mm)														
			D-M9□(V) D-M9□W(V) D-A9□A(V)		D-B5□ D-B64		D-C7□ D-C80 D-C73C D-C80C		D-B59W		D-H7□ D-H7C D-H7□W D-H7NF		D-G5NT	
(mm)	Α	В	Α	В	Α	В	Α	В	Α	В	Α	В	Α	В
20	6.5	5.5	10.5	9.5	1	0	7	6	4	3	6	5	2.5	1.5
25	6.5	5.5	10.5	9.5	1	0	7	6	4	3	6	5	2.5	1.5
32	7.5	6.5	11.5	10.5	2	1	8	7	5	4	7	6	3.5	2.5
40	13.5	11.5	17.5	15.5	7	6	13	12	10	9	12	11	8.5	7.5

Note) Adjust the auto switch after confirming the operating conditions in the actual setting.

Auto Switch Mounting Height (mm)											
Auto switch model Bore size	D-A9□(V) D-M9□(V) D-M9□W(V) D-M9□A(V)	D-B5□ D-B64 D-B59W D-G5NT D-H7C	D-C7□ D-C80 D-H7□ D-H7□W D-H7NF	D-C73C D-C80C							
(mm)	Hs	Hs	Hs	Hs							
20	23	25.5	22.5	25							
25	25.5	28	25	27.5							
32	29	31.5	28.5	31							
40	33	35.5	32.5	35							

CVM5 Series Auto Switch Mounting 2


Minimum Auto Switch Mounting Stroke

					n: No. of auto switches (mm)	
A 1			No. of auto switch mounted			
Auto switch model	1	2	2	n		
model	'	Different surfaces	Same surface	Different surfaces	Same surface	
D-A9□ D-M9□ D-M9□W	10	15 Note 1)	45 Note 1)	$15 + 45 \frac{(n-2)}{2}$ $(n = 2, 4, 6)^{\text{Note 2}}$	45 + 45 (n - 2) (n = 2, 3, 4, 5···)	
D-M9□V	5	20	35	20 + 35	35 + 35 (n - 2) (n = 2, 3, 4, 5···)	
D-A9□V	5	15	25	$15 + 35 \frac{(n-2)}{2}$ $(n = 2, 4, 6) \text{ Note 2}$	25 + 35 (n - 2) (n = 2, 3, 4, 5···)	
D-M9□WV D-M9□AV	10	20	35	$20 + 35 \frac{(n-2)}{2}$ $(n = 2, 4, 6) \text{ Note 2}$	35 + 35 (n - 2) (n = 2, 3, 4, 5···)	
D-C7□ D-C80	10	15	50	$15 + 45 \frac{(n-2)}{2}$ $(n = 2, 4, 6)^{\text{Note 2}}$	50 + 45 (n - 2) (n = 2, 3, 4, 5···)	
D-H7□ D-H7□W D-H7NF	10	15	60	$15 + 45 \frac{(n-2)}{2}$ $(n = 2, 4, 6)^{\text{Note 2}}$	60 + 45 (n - 2) (n = 2, 3, 4, 5···)	
D-C73C D-C80C D-H7C	10	15	65	$15 + 50 \frac{(n-2)}{2}$ $(n = 2, 4, 6)^{\text{Note 2}}$	65 + 50 (n - 2) (n = 2, 3, 4, 5···)	
D-B5□/B64 D-G5NT	10	15	75	$15 + 50 \frac{(n-2)}{2}$ (n = 2, 4, 6) Note 2)	75 + 55 (n - 2) (n = 2, 3, 4, 5···)	
D-B59W	15	20	75	$20 + 50 \frac{(n-2)}{2}$ $(n = 2, 4, 6\cdots)^{\text{Note } 2)}$	75 + 55 (n - 2) (n = 2, 3, 4, 5···)	

Note 2) When "n" is an odd number, an even number that is one larger than this odd number is used for the calculation.

Note 1) Auto switch mounting (The adjustment as shown in the figures below is required with the following stroke ranges.)

With 2 auto switches



Operating Range

<u> </u>							
				(mm)			
Auto switch model	Bore size (mm)						
Auto switch model	20	25	32	40			
D-A9□(V)	6	6	6	6			
D-M9□(V)/M9□W(V) D-M9□A(V)	3.5	3	3.5	3			
D-C7□/C80 D-C73C/C80C	7	8	8	8			
D-B5□/B64	8	8	9	9			
D-B59W	12	12	13	13			
D-H7□/H7□W D-G5NT/H7NF	4	4	4.5	5			
D-H7C	7	8.5	9	10			

^{*} Since the operating range is provided as a guideline including hysteresis, it cannot be guaranteed (assuming approximately ±30% dispersion). It may vary substantially depending on an ambient environment.



Auto Switch Mounting Bracket: Part No.

A		Bore size (mm)							
Auto switch mounting	ø 20	ø 25	ø32	ø40					
D-M9□(V) D-M9□W(V) D-A9□(V)	Note 1) BM5-020 (A set of a, b, c, d)	Note 1) BM5-025 (A set of a, b, c, d)	Note 1) BM5-032 (A set of a, b, c, d)	Note 1) BM5-040 (A set of a, b, c, d)					
D-M9 □ A(V) Note 2)	BM5-020S (A set of b, c, e, f)	BM5-025S (A set of b, c, e, f)	BM5-032S (A set of b, c, e, f)	BM5-040S (A set of b, c, e, f)					
D-H7□ D-H7□W D-H7NF D-C7□/C80 D-C73C/C80C	BM2-020A (A set of c and d)	BM2-025A (A set of c and d)	BM2-032A (A set of c and d)	BM2-040A (A set of c and d)					
D-B5□/B64 D-B59W D-G5NT	BA2-020 (A set of c and d)	BA2-025 (A set of c and d)	BA2-032 (A set of c and d)	BA2-040 (A set of c and d)					


Note 1) Since the switch bracket (made from nylon) are affected in an environment where alcohol, chloroform, methylamines, hydrochloric acid or sulfuric acid is splashed over, so it cannot be used. Please consult SMC regarding other chemicals.

Note 2) When mounting a D-M9□A(V) type auto switch, if the switch bracket is mounted on the indicator light, it may damage the auto switch. Therefore, be sure to avoid mounting the switch bracket on the indicator

[Mounting screw set made of stainless steel]

The following set of mounting screws made of stainless steel is available. Use it in accordance with the operating environment. (Please order the auto switch mounting BBA4: For D-C7/C8/H7 types

Note) Refer to page 1440 for the details of BBA4.



* Band (c) is mounted so that the projected part is on the internal side (contact side with the tube).


Besides the models listed in How to Order, the following auto switches are applicable. Refer to pages 1341 to 1435 for detailed specifications.

Auto switch type	Part no.	Part no. Electrical entry (Fetching direction)		
Reed	D-B53, C73, C76		_	
	D-C80		Without indicator light	
	D-H7A1, H7A2, H7B	Grommet (In-let)	_	
Solid state	D-H7NW, H7PW, H7BW		Diagnostic indication (2-color	
	D-G5NT		With timer	

* For solid state auto switches, auto switches with a pre-wired connector are also available. Refer to pages 1410 and 1411 for details. * Normally closed (NC = b contact) solid state auto switches (D-M9□E(V)) are also available. Refer to page 1360 for details.

Valve Mounted Cylinder Single Acting, Spring Return/Extend CVM3 Series ø20, ø25, ø32, ø40

How to Order



		Electrical	Indicator light	145		Load vol	tage	Auto s	switch	Lea	d wir	e len	gth	(m)	Pre-wired				
Type	Special function	entry	cator	Wiring (Output)		DC	AC	mo	del	0.5	1	3	5	None	connector	Applica	ble load		
		,	Вĝ	(Output)			AO	Perpendicular	In-line	(Nil)	(M)	(L)	(Z)	(N)					
				3-wire (NPN)		5 V, 12 V		M9NV	M9N	•	•	•	0	_	0	IC			
ڃ		Grommet		3-wire (PNP)		3 V, 12 V]	M9PV	M9P	•	•	•	0	_	0	circuit			
switch				2-wire		12 V		M9BV	M9B	•	•	•	0	_	0	l _			
		Connector		Z-WIIG		12 4		_	H7C	•	_	•	•	•	_				
anto	Diagnostic indication			3-wire (NPN)		5 V, 12 V		M9NWV	M9NW	•	•	•	0	_	0	IC	Relay,		
9	(2-color indicator)		Yes	3-wire (PNP)	24 V	3 V, 12 V] —	M9PWV	M9PW	•	•	•	0	_	0	circuit	PLC		
state	(2 color iridicator)			2-wire		12 V	12 V	M9BWV	M9BW	•	•	•	0	_	0	_	. 20		
S	Water resistant	Grommet		3-wire (NPN)		E V 10 V	E V 10 V	5 V, 12 V		M9NAV*1	M9NA*1	0	0	•	0	_	0	IC	
Solid	(2-color indicator)			3-wire (PNP)		5 V, 12 V		M9PAV*1	M9PA*1	0	0	•	0	_	0	circuit			
S	. ,			2-wire		12 V		M9BAV*1	M9BA*1	0	0	•	0	_	0	_			
	With diagnostic output (2-color indicator)			4-wire (NPN)		5 V, 12 V		_	H7NF	•	_	•	0	-	0	IC circuit			
_			Yes	3-wire (NPN equivalent)	_	5 V	_	A96V	A96	•	_	•	_	_	_	IC circuit	_		
switch			res				100 V	A93V*2	A93	•	•	•	•	_	_	_			
Š		Grommet	None				100 V or less	A90V	A90	•	_	•	_	_	_	IC circuit			
			Yes			12 V	100 V, 200V	_	B54	•	_	•	•	_	_		Relay,		
an	anto —		None	2-wire	24 V	12 V	200 V or less	_	B64	•	_	•	_	_	_	-	PLC		
Reed		Connector	Yes	:			_	_	C73C	•	_	•	•	•	_				
æ			None				24 V or less	_	C80C	•	_	•	•	•	_	IC circuit			
	Diagnostic indication (2-color indicator)	Grommet	Yes			_	_		B59W	•	—	•	<u> — </u>	-	_	_			


- * Lead wire length symbols: 0.5 m Nil
 - (Example) M9NW (Example) M9NWM 1 m M 3 m L (Example) M9NWL
 - 5 m (Example) M9NWZ None (Example) H7CN
- * Solid state auto switches marked with "O" are produced upon receipt of order. *1 Water resistant type auto switches can be mounted on the above models but in such case SMC cannot guarantee water resistance. Consult with SMC
- regarding water resistant types with the above model numbers. *2 1 m type lead wire is only applicable to D-A93.
- * Since there are other applicable auto switches than listed, refer to page 1215 for details.
- * For details about auto switches with pre-wired connector, refer to pages 1410 and 1411.
- * D-A9 M9 auto switches are shipped together (not assembled). (Only auto switch mounting brackets are assembled before shipped.)


Valve Mounted Cylinder CVM3 Series Single Acting, Spring Return/Extend CVM3 Series

An auto switch cylinder with the switch installed can also be manufactured.



Symbol Rubber bumper







Made to Order Specifications Click here for details

Symbol	Specifications
-ХА□	Change of rod end shape

Refer to pages 1212 to 1215 for cylinders with auto switches.

- · Proper auto switch mounting position
- $(\mbox{detection at stroke end}) \ \mbox{and mounting height} \\ \cdot \mbox{Minimum auto switch mounting stroke}$
- Minimum auto switch
 Operating range
- · Auto switch mounting bracket: Part no.

Specifications

Applicable I	oore size (mm)	20 25 32 40					
Action		Single acting, Spring return/Spring extend					
Fluid			Д	ir			
Cushion			Rubber	bumper			
Proof pressure			1.0	MPa			
Maximum opera	ating pressure		0.7	MPa			
Minimum opera	Minimum operating pressure			0.23 MPa S	pring extend		
Ambient and flu	uid temperature		–10 to 50°C	(No freezing))		
Lubrication		Not required (Non-lube)					
Stroke length to	olerance	+1.4 0					
Piping	Screw-in type		Rc	1/8			
riping	Built-in One-touch fitting		O.D.: ø6	quired (Non-lube			
Manual overrid	е		Non locking	(Standard)			
Allowable kinet	Allowable kinetic energy		0.4 J	0.65 J	1.2 J		
Mounting			Basic type, Axial foot type, Rod side flange type, Head side flange type, Single clevis type, Double clevis type, Head side trunnion type, Rod side trunnion type				

Solenoid Valve Specifications

Series	1519					
Manual override			Non-locking push type, Push-turn locking slotted type, Push-turn locking lever type			
Pilot exhaust			Pilot valve indiv	ridual exh. Type		
Impact/Vibration resis	tance	e (m/s²) ^{Note 1)}	150)/30		
Enclosure			Dust	proof		
Electrical entry				lug connector (L), M), DIN terminal (D)		
-			G, L, M	D		
Coil rated voltage	e DC		24, 12, 6, 5, 3	24, 12		
(V)	AC	50/60 Hz	100, 110, 200, 220			
Allowable voltage			±10% of the r	ated voltage*		
Power consumption (W)Note 2	DC		0.35 (With light: 0.4 (DIN terminal with light: 0.45))			
		100 V	0.78 (With light: 0.81)	0.78 (With light: 0.87)		
		110 V	0.86 (With light: 0.89)	0.86 (With light: 0.97)		
Apparent power	AC	[115 V]	[0.94 (With light: 0.97)]	[0.94 (With light: 1.07)]		
(VA) Note 2)	AC	200 V	1.18 (With light: 1.22)	1.15 (With light: 1.30)		
		220 V	1.30 (With light: 1.34)	1.27 (With light: 1.46)		
		[230 V]	[1.42 (With light: 1.46)]	[1.39 (With light: 1.60)]		
Surge voltage supp	ress	or	Diode (DIN terminal, Varistor when non-polar types			
Indicator light			LED (Neon light when AC with DIN terminal)			

- * Based on IEC60529
- * In common between 110 VAC and 115 VAC, and between 220 VAC and 230 VAC.
- * For 115 VAC and 230 VAC, the allowable voltage is -15% to +5% of rated voltage.

Note 1) Impact resistance: No malfunction occurred when it is tested in the axial direction and at the right angles to the main valve and armature in both energized and de-energized states every once for each condition. (Values at the linitial period)

Vibration resistance: No malfunction occurred in a one-sweep test between 45 and 2000 Hz. The test was performed at both energized and de-energized states in the axial direction and at the right angles to the main valve and armature. (Values at the initial perior).

Note 2) At the rated voltage.

Standard Stroke

Standard Stroke							
Bore size (mm)	Standard stroke (mm) Note)						
20	25, 50, 75, 100, 125, 150 *						
25	25, 50, 75, 100, 125, 150 *						
32	25, 50, 75, 100, 125, 150, 200 *						
40	25, 50, 75, 100, 125, 150, 200, 250 *						

Note 1) Intermediate stroke except mentioned above is produced upon receipt of order.

upon receipt of order.

Note 2) Strokes marked with "*" are the maximum strokes which are available.

Theoretical Output

Refer to the Technical Data (Theoretical Output 1) in the Web Catalog.

Spring Reaction Force

Refer to the Technical Data (Table 2: Spring Reaction Force) in the Web Catalog.



Mounting Bracket and Accessory

wounting bracket and Accessory										
Accessory	Stan	dard equip	ment	Option						
Mounting	Mounting nut	Rod end nut	Clevis pin	Single knuckle joint	Double knuckle joint	Pivot bracket	Pivot bracket pin			
Basic type	• (1 pc.)	•	_	•	•					
Axial foot type	• (2)	•	_	•	•					
Rod side flange type	• (1)	•	_	•	•	_	_			
Head side flange type	• (1)	•	_	•	•					
Single clevis type	— ⁽¹⁾	•	_	•	•	•	•			
Double clevis type (3)	— ⁽¹⁾	•	● ⁽⁴⁾	•	•	_	_			
Head side trunnion type	• (1) (2)	•	_	•	•	_				
Rod side trunnion type	• (1) (2)	•	_	•	•	•	_			

Note 1) Mounting nut is not equipped with single clevis type and double clevis type.

Note 2) Trunnion nuts are equipped for head side trunnion and rod side trunnion.

Note 3) Pin and retaining ring are shipped together with double clevis and double knuckle joint.

Note 4) Retaining rings (cotter pins for ø40) are included in clevis pins.

Note 5) Pin and retaining ring are not included in pivot bracket. Note 6) Retaining rings are included in pivot bracket pin.

Accessory Bracket

Further information on accessories are the same specifications as these of the standard double acting single rod. Refer to page 1190.

Manual Operation

Manual operation is possible by pushing the manual button indicated with the arrow.



Weight

Sprin	ring Return/(): Denotes Spring Extend. (kg)									
	Bore size (mm)	20	25	32	40					
	25 stroke	0.27 (0.27)	0.37 (0.37)	0.49 (0.48)	0.84 (0.83)					
	50 stroke	0.29 (0.29)	0.40 (0.40)	0.53 (0.53)	0.91 (0.90)					
	75 stroke	0.34 (0.34)	0.49 (0.48)	0.65 (0.63)	1.10 (1.06)					
Basic	100 stroke	0.36 (0.36)	0.52 (0.51)	0.70 (0.67)	1.16 (1.13)					
weight	125 stroke	0.42 (0.41)	0.61 (0.58)	0.83 (0.79)	1.36 (1.30)					
	150 stroke	0.44 (0.43)	0.64 (0.61)	0.87 (0.83)	1.43 (1.37)					
	200 stroke	_	_	1.03 (0.99)	1.68 (1.60)					
	250 stroke	_	_	_	1.94 (1.82)					
	Axial foot	0.15 (0.15)	0.16 (0.16)	0.16 (0.16)	0.27 (0.27)					
Mounting	Flange	0.06 (0.06)	0.09 (0.09)	0.09 (0.09)	0.12 (0.12)					
bracket	Single clevis	0.04 (0.04)	0.04 (0.04)	0.04 (0.04)	0.09 (0.09)					
weight	Double clevis	0.05 (0.05)	0.06 (0.06)	0.06 (0.06)	0.13 (0.13)					
	Trunnion	0.04 (0.04)	0.07 (0.07)	0.07 (0.07)	0.10 (0.10)					
Option	Single knuckle joint	0.06 (0.06)	0.06 (0.06)	0.06 (0.06)	0.23 (0.23)					
bracket	Double knuckle (With pin)	0.07 (0.07)	0.07 (0.07)	0.07 (0.07)	0.20 (0.20)					

Calculation

(Example) CVM3L32-100S-1G

(ø32, 100 stroke, Spring return)

 Basic weight----....0.70 (kg) Weight of brackets-----0.16 (kg)

0.70 + 0.16 = 0.86 kg

• Add 0.03 kg for the DIN terminal.

∧Precautions

Be sure to read this before handling the products. Refer to page 9 for safety instructions, pages 10 to 19 for actuator and I auto switch precautions, and 3/4/5 port solenoid valve precautions on the SMC web site: https://www.smcworld.com

Operating Precautions

∕!\ Warning

1. Do not rotate the cover.

If a cover is rotated when installing a cylinder or screwing a fitting into port, it is likely to damage the junction part with cover.

∕!\ Caution

Not able to disassemble.

Cover and cylinder tube are connected to each other by caulking method, thus making it impossible to disassemble. Therefore, internal parts of a cylinder other than rod seal are not replaceable.

2. Use caution to the popping of a retaining ring.

When replacing rod seals and removing and mounting a retaining ring, use a proper tool (retaining ring plier: tool for installing type C retaining ring). Even if a proper tool is used, it is likely to inflict damage to a human body or peripheral equipment, as a retaining ring may be flown out of the tip of a plier. Be much careful with the popping of a retaining ring. Besides, be certain that a retaining ring is placed firmly into the groove of rod cover before supplying air at the time of installment.

∕!\ Caution

3. Do not touch the cylinder during operation.

Use caution when handling a cylinder, which is running at a high speed and a high frequency, because the surface of a cylinder tube could get so hot enough as to cause you get burned.

One-touch fitting cannot be replaced.

One-touch fitting is press-fit into the cover, thus cannot be replaced.

Model Selection

🗥 Warning

1. Confirm the specifications.

Products in this catalog are designed to be used for compressed air systems (including vacuum). If not operated within the designated pressure or temperature, it may damage the products or cause malfunction. (Refer to specifications.)

2. Energizing continuously for a long period of time

When the valve is continuously energized for a long period of time, the performance may deteriorate, shorten the service life or affect peripheral equipment adversely since temperature rises when coils generate heat

Valve Mounted Cylinder CVM3 Series

Built-in One-touch Fitting

CVM3 Mounting type Bore size F For "How to Order", refer to page 1194.

One-touch fittings are installed on cylinders.



For dimensions of each mounting bracket, refer to pages 1200 to 1206.

Specifications

Specifications						
Action	Single acting, Spring return Single acting, Spring exter					
Bore size (mm)	ø20, ø25, ø32, ø40					
Max. operating pressure		0.7	MPa			
Min. operating pressure	0.18	MPa	0.23	MPa		
Cushion	Rubber bumper					
Piping	Built-in One-touch fitting					
Piston speed	ø20	ø40				
(mm/s)	20, 925,	50 to 590	50 to 420			
Port size (Tube bore size)		O.D.: ø6	6/I.D.: ø4			
Applicable bore size						
Mounting	Head sid	le flange typ evis type, He	e, Single cle ad side trun	vis type,		

Mounting Bracket Part No.

Bore size (mm)	20	25	32	40
Axial foot *	CM-L020B	CM-L	.032B	CM-L040B
Flange	CM-F020B	CM-F	032B	CM-F040B
Single clevis	CM-C020B	CM-C	032B	CM-C040B
Double clevis **	CM-D020B	CM-E	032B	CM-D040B
Trunnion (with nut)	CM-T020B	CM-T	032B	CM-T040B

^{*} Two foot brackets and a mounting nut are attached.

SMC


When ordering the foot bracket, order 2 pcs. per cylinder.


^{**} Clevis pin and retaining ring (cotter pin for ø40) are packaged together.

CVM3 Series


Construction

Spring return






Spring extend



Nil Valves other than those below All valves with a DC rated voltage

Valves with an AC rated voltage

(DIN terminal only)



Component Parts

No.	Description	Material	Note
1	Rod cover	Aluminum alloy	Anodized
2	Head cover	Aluminum alloy	Anodized
3	Cylinder tube	Stainless steel	
4	Piston	Aluminum alloy	
5	Piston rod	Carbon steel	Hard chromium electroplated
6	Bushing	Bearing alloy	
7	Seal retainer	Stainless steel	
8	Return spring	Steel wire	Zinc chromated
9	Spring guide	Aluminum alloy	
10	Spring seat	Aluminum alloy	
11	Plug with fixed orifice	Alloy steel	Black dyed
12	Retaining ring	Carbon steel	Phosphate coated
13	Sub-plate	Aluminum alloy	Metallic painted
14	Hex. socket head cap screw with spring washer	Stainless steel	
15	Plate	Alloy	Metallic painted
16	Hex. socket head cap screw with spring washer	Stainless steel	
17	Solenoid valve		Refer to "How to order" below.*
18	Bumper	Urethane	
19	Bumper A	Urethane	
∗ Ho	w to order solenoid valves		

Manual override

voltage suppressor

Light/surge

-Q

Component Parts

COI	nponent Parts		
No.	Description	Material	Note
20	Bumper B	Urethane	
21	Retaining ring	Stainless steel	
22	Piston seal	NBR	
23	Piston gasket	NBR	
24	Wear ring	Resin	
25	Head cover gasket	NBR	
26	Sub-plate gasket	NBR	
27	Gasket	NBR	
28	Pipe gasket	Urethane rubber	
29	Gasket	Resin	
30	Spacer gasket	Resin	
31	Stud	Brass	Electroless nickel plated
32	Pipe	Aluminum alloy	
33	Mounting nut	Carbon steel	Nickel plated
34	Rod end nut	Carbon steel	Zinc chromated
36	One-touch fitting	_	Port size: ø6

Replacement Parts/Seal Kit

NI-	December			Parl	no.	
No.	Description	Material	20	25	32	40
35	Rod seal	NBR	CM220-PS	CM225-PS	CM232-PS	CM240-PS

^{*} Since the seal kit does not include a grease pack, order it separately. Grease pack part no.: GR-S-010 (10g)


Rated voltage


Electrical entry

SYJ519 - _ _ _ _


Basic Type (B)









Single acting, Spring extend: CVM3B Bore size Stroke T







(----)

																		(111111)
Bore size (mm)	Α	AL	Вı	B ₂	D	Eh₃	F	Н	Нı	H ₂	НХ	ı	K	KA	MM	N	NA	NN
20	18	15.5	13	26	8	20 -0.033	13	41	5	8	57.5	28	5	6	M8 x 1.25	15	24	M20 x 1.5
25	22	19.5	17	32	10	26 -0.033	13	45	6	8	63.5	33.5	5.5	8	M10 x 1.25	15	30	M26 x 1.5
32	22	19.5	17	32	12	26 -0.033	13	45	6	8	68	37.5	5.5	10	M10 x 1.25	15	34.5	M26 x 1.5
40	24	21	22	41	14	32 -0.039	16	50	8	10	76	46.5	7	12	M14 x 1.5	21.5	42.5	M32 x 2

Dimensions by Stroke (mm) 1 to 50 51 to 100 101 to 150 151 to 200 201 to 250 s ZZ s ZZ s ZZ s ΖZ s ZZ size (mm) 20 87 141 112 166 137 191 25 87 145 112 170 137 195 32 89 147 114 172 139 197 164 222 40 113 179 138 204 163 229 188 254 213 279


Single Actir	ıg/Sprii	ng Exte	nd (mm)
Bore size (mm)	нх	Q	QY
20	65.3	19.8	14
25	70.5	22	14
32	76.5	25.8	16
40	84.5	29.8	16




CVM3 Series

Axial Foot Type (L)

Single acting, Spring return: CVM3L Bore size - Stroke S







																							(mm)
Bore size (mm)	Α	AL	В	Вı	B ₂	D	F	Н	Нı	H ₂	ı	K	KA	LC	LD	LH	LT	LX	LY	LZ	MM	N	NA
20	18	15.5	40	13	26	8	13	41	5	8	28	5	6	4	6.8	25	3.2	40	70.5	55	M8 x 1.25	15	24
25	22	19.5	47	17	32	10	13	45	6	8	33.5	5.5	8	4	6.8	28	3.2	40	76.5	55	M10 x 1.25	15	30
32	22	19.5	47	17	32	12	13	45	6	8	37.5	5.5	10	4	6.8	28	3.2	40	78.8	55	M10 x 1.25	15	34.5
40	24	21	54	22	41	14	16	50	8	10	46.5	7	12	4	7	30	3.2	55	84.8	75	M14 x 1.5	21.5	42.5


				(mm)
Bore size (mm)	NN	х	Y	z
20	M20 x 1.5	20	8	21
25	M26 x 1.5	20	8	25
32	M26 x 1.5	20	8	25
40	M32 x 2	23	10	27

^{*} Brackets are packaged together.


Dimensi	ons	by	Str	oke											(mm)
Stroke Bore Symu	1	to 5	0	51	to 1	00	10	1 to 1	50	15	1 to 2	200	20	1 to 2	250
Bore Symbol size (mm)	s	LS	ZZ	s	LS	ZZ	S	LS	ZZ	s	LS	ZZ	S	LS	ZZ
20	87	127	156	112	152	181	137	177	206	_	_	_	-	_	_
25	87	127	160	112	152	185	137	177	210	_	_	_	_	_	_
32	89	129	162	114	154	187	139	179	212	164	204	237	_	_	_
40	113	150	196	138	184	221	163	200	246	188	234	271	213	259	296


Valve Mounted Cylinder CVM3 Series

Rod Side Flange Type (F)










																					(mm)
Bore size (mm)	Α	AL	В	Вı	B ₂	C ₂	D	Eh₃	F	FD	FT	FX	FY	FZ	Н	H₁	H2	нх	_	K	KA
20	18	15.5	34	13	26	30	8	20 0 -0.033	13	7	4	60	_	75	41	5	8	57.5	28	5	6
25	22	19.5	40	17	32	37	10	26 0 -0.033	13	7	4	60	_	75	45	6	8	63.5	33.5	5.5	8
32	22	19.5	40	17	32	37	12	26 0 0 0 0 0 0 0 0 0 0 0 0 0 0 0 0 0 0 0	13	7	4	60	_	75	45	6	8	68	37.5	5.5	10
40	24	21	52	22	41	47.3	14	32 0	16	7	5	66	36	82	50	8	10	76	46.5	7	12


					(mm)	Dimensi	ons	by	Str	oke)					(mm)	Single Acting	J/Sprin	g Exten	ıd (mm
Bore size	мм	N	NA	NN	z	Bore Symbol		50	51 to	100	101 t	o 150	151 t	o 200	201 t	o 250	Bore size	нх	Q	QY
(mm)		i	1		_	size (mm)	S	ZZ	S	ZZ	S	ZZ	S	ZZ	S	ZZ	(mm)		_ ~	۵.
20	M8 x 1.25	15	24	M20 x 1.5	37	20	87	141	112	166	137	191	—	—	—	_	20	65.3	19.8	14
25	M10 x 1.25	15	30	M26 x 1.5	41	25	87	145	112	170	137	195	_	_	_	_	25	70.5	22	14
32	M10 x 1.25	15	34.5	M26 x 1.5	41	32	89	147	114	172	139	197	164	222	_	_	32	76.5	25.8	16
40	M14 x 1.5	21.5	42.5	M32 x 2	45	40	113	179	138	204	163	229	188	254	213	279	40	84.5	29.8	16

^{*} Brackets are packaged together.

CVM3 Series

Head Side Flange Type (G)






																						(mm)
Bore size (mm)	Α	AL	В	Вı	B ₂	C ₂	D	Eh₃	F	FD	FT	FX	FY	FZ	Н	H ₁	H ₂	НХ	_	K	KA	MM
20	18	15.5	34	13	26	30	8	20 0 -0.033	13	7	4	60	_	75	41	5	8	57.5	28	5	6	M8 x 1.25
25	22	19.5	40	17	32	37	10	26 0 -0.033	13	7	4	60	_	75	45	6	8	63.5	33.5	5.5	8	M10 x 1.25
32	22	19.5	40	17	32	37	12	26 0 -0.033	13	7	4	60	_	75	45	6	8	68	37.5	5.5	10	M10 x 1.25
40	24	21	52	22	41	47.3	14	32 0	16	7	5	66	36	82	50	8	10	76	46.5	7	12	M14 x 1.5


			(mm)	Dimensi	ions	by	Stı	roke	•										(mm)	Single Actin	g/Sprir	g Exter	nd (mm)
Bore size	N	NA	NN	Bore Symp		to 5	0	51	to 1	00	10	1 to 1	150	15	1 to 2	200	20	1 to 2	50	Bore size	нх	0	QY
(mm)	"	IVA	IVIV	Bore Symbol size (mm)	S	Z	ZZ	s	Z	ZZ	S	Z	ZZ	S	Z	ZZ	S	Z	ZZ	(mm)	· · · ·	u	Q1
20	15	24	M20 x 1.5	20	87	132	141	112	157	166	137	182	191	_	_	_	_	_	_	20	65.3	19.8	14
25	15	30	M26 x 1.5	25	87	136	145	112	161	170	137	186	195	_	_	_	_	_	_	25	70.5	22	14
32	15	34.5	M26 x 1.5	32	89	138	147	114	163	172	139	188	197	164	213	222	_	_	_	32	76.5	25.8	16
40	21.5	42.5	M32 x 2	40	113	168	179	138	193	204	163	218	229	188	243	254	213	268	279	40	84.5	29.8	16

^{*} Brackets are packaged together.


Single Clevis Type (C)


Single acting, Spring return: CVM3C Bore size - Stroke S






Single acting, Spring extend: CVM3C Bore size - Stroke





(mm) CD CI D Ehs F нх KA MM NA NN U Bore size (mm) 20 15.5 13 9 10 8 13 5 57.5 5 6 M8 x 1.25 15 M20 x 1.5 14 20 22 19.5 17 9 30 10 10 26 13 45 6 63.5 33.5 5.5 8 30 M10 x 1.25 15 30 M26 x 1.5 9 14 M10 x 1.25 22 19.5 17 9 30 10 12 26 13 45 6 68 37.5 5.5 10 15 34.5 M26 x 1.5 9 14 40 21 22 10 38 15 14 32 -0.039 16 50 8 76 46.5 12 M14 x 1.5 21.5 42.5 M32 x 2 11 18


Dimensions	by S	Stro	ke												(mm)
Bore Stroke		1 to 50)	5	1 to 10	00	10	1 to 1	50	15	1 to 2	00	20	1 to 2	50
size (mm)	s	Z	ZZ	s	Z	ZZ	s	Z	ZZ	s	Z	ZZ	S	Z	ZZ
20	87	158	167	112	183	192	137	208	217	_	_	_	_	_	_
25	87	162	171	112	187	196	137	212	221	_	_	_	_	_	_
32	89	164	173	114	189	198	139	214	223	164	239	248	_	_	_
40	113	202	213	138	227	238	163	252	263	188	277	288	213	302	313




CVM3 Series


Double Clevis Type (D)

Single acting, Spring return: CVM3D Bore size Stroke



Single acting, Spring extend: CVM3D Bore size





																								(mm)
Bore size (mm)	Α	AL	Вı	CD	CI	CL	СХ	CZ	D	Eh₃	F	Н	Нı	нх		K	KA	L	MM	N	NA	NN	RR	U
20	18	15.5	13	9	24	25	10	19	8	20 -0.033	13	41	5	57.5	28	5	6	30	M8 x 1.25	15	24	M20 x 1.5	9	14
25	22	19.5	17	9	30	25	10	19	10	26-0.033	13	45	6	63.5	33.5	5.5	8	30	M10 x 1.25	15	30	M26 x 1.5	9	14
32	22	19.5	17	9	30	25	10	19	12	26-0.033	13	45	6	68	37.5	5.5	10	30	M10 x 1.25	15	34.5	M26 x 1.5	9	14
40	24	21	22	10	38	41.2	15	30	14	32 -0.039	16	50	8	76	46.5	7	12	39	M14 x 1.5	21.5	42.5	M32 x 2	11	18

Dimension	s by	Stroke

Dimension	s by	Str	oke												(mm)
Stroke Bore		1 to 50)	5	1 to 10	00	10	1 to 1	50	15	1 to 2	:00	20	1 to 2	50
size (mm)	S	Z	ZZ	s	Z	ZZ	S	Z	ZZ	S	Z	ZZ	S	Z	ZZ
20	87	158	167	112	183	192	137	208	217	_	_	_	_	_	_
25	87	162	171	112	187	196	137	212	221	_	_	_	_	_	_
32	89	164	173	114	189	198	139	214	223	164	239	248	_	_	_
40	113	202	213	138	227	238	163	252	263	188	277	288	213	302	313
* Clevis pin and	snap i	ring (c	otter p	in for	ø40)	is ship	ped to	ogethe	er.						


Single Acting/Spring Extend (mm)

<u> </u>	J		. ()
Bore size (mm)	нх	Q	QY
20	65.3	19.8	14
25	70.5	22	14
32	76.5	25.8	16
40	84.5	20.8	16


Valve Mounted Cylinder CVM3 Series


Rod Side Trunnion Type (U)

Single acting, Spring return: CVM3U Bore size - Stroke S



Single acting, Spring extend: CVM3U Bore size - Stroke T





																							(mm)
Bore size (mm)	Α	AL	Вı	B ₂	D	Eh₃	F	Н	Нı	НХ	Т	K	KA	MM	N	NA	NN	TD	TT	TX	TY	TZ	Z
20	18	15.5	13	26	8	20-0.033	13	41	5	57.5	28	5	6	M8 x 1.25	15	24	M20 x 1.5	8	10	32	32	52	36
25	22	19.5	17	32	10	26-0.033	13	45	6	63.5	33.5	5.5	8	M10 x 1.25	15	30	M26 x 1.5	9	10	40	40	60	40
32	22	19.5	17	32	12	26-0.033	13	45	6	68	37.5	5.5	10	M10 x 1.25	15	34.5	M26 x 1.5	9	10	40	40	60	40
40	24	21	22	41	14	32-0.039	16	50	8	76	46.5	7	12	M14 x 1.5	21.5	42.5	M32 x 2	10	11	53	53	77	44.5

Dimens	ions	s by	Str	oke						(mm)
Bore Symbol	1 to	50	51 to	100	101 t	0 150	151 t	o 200	201 t	250
Bore Symbol size (mm)	S	ZZ	S	ZZ	S	ZZ	S	ZZ	S	ZZ
20	87	141	112	166	137	191	_	_	_	_
25	87	145	112	170	137	195	_	-	_	_
32	89	147	114	172	139	197	164	222	_	
40	113	179	138	204	163	229	188	254	213	279


^{*} Brackets are packaged together.

Single Ac	ting/Spi	ring Exte	end (mm)
Bore size (mm)	нх	Q	QY
20	65.3	19.8	14
25	70.5	22	14
32	76.5	25.8	16
40	84.5	29.8	16


CVM3 Series

Head Side Trunnion Type (T)

Single acting, Spring return: CVM3T Bore size - Stroke S



Single acting, Spring extend: CVM3T Bore size - Stroke T





																						(mm)
Bore size (mm)	Α	AL	Вı	B ₂	D	Eh₃	F	Н	Ηı	НХ	ı	K	KA	MM	N	NA	NN	TD	TT	TX	TY	TZ
20	18	15.5	13	26	8	20 -0.033	13	41	5	57.5	28	5	6	M8 x 1.25	15	24	M20 x 1.5	8	10	32	32	52
25	22	19.5	17	32	10	26 -0.033	13	45	6	63.5	33.5	5.5	8	M10 x 1.25	15	30	M26 x 1.5	9	10	40	40	60
32	22	19.5	17	32	12	26 -0.033	13	45	6	68	37.5	5.5	10	M10 x 1.25	15	34.5	M26 x 1.5	9	10	40	40	60
40	24	21	22	41	14	32 -0.039	16	50	8	76	46.5	7	12	M14 x 1.5	21.5	42.5	M32 x 2	10	11	53	53	77

Dimensi	ons	by S	Strol	кe											(mm)
Stroke		1 to 50)	5	1 to 10	00	10	1 to 1	50	15	1 to 2	00	20	1 to 2	50
Bore Symbol size (mm)	S	Z	ZZ	S	Z	ZZ	S	Z	ZZ	S	Z	ZZ	S	Z	ZZ
20	87	133	143	112	158	168	137	183	193	_	_	_	_	_	_
25	87	137	147	112	162	172	137	187	197	_	_	_	-	_	_
32	89	139	149	114	164	174	139	189	199	164	214	224	_	_	_
40	113	168.5	179	138	193.5	204	163	218.5	229	188	243.5	254	213	268.5	279

^{*} Brackets are packaged together.


Single Ac	ting/Sp	ring Exte	end (mm)
Bore size (mm)	нх	Q	QY
20	65.3	19.8	14
25	70.5	22	14
32	76.5	25.8	16
40	84.5	29.8	16

Valve Mounted Cylinder: Non-rotating Rod Type Single Acting, Spring Return/Extend

CVM3K Series

ø20, ø25, ø32, ø40

How to Order



		Electrical	을			Luau vui	laye	Auto s	switch	Lead	ı vvii	e lei	igiii	(111)	Pre-wired								
Type	Special function	entry	ndicator lig	Wiring (Output)		DC	AC	mo		0.5	1	3		None	connector	Applica	ble load						
		,	İPİ	(Output)			AO	Perpendicular	In-line	(Nil)	(M)	(L)	(Z)	(N)									
				3-wire (NPN)		5 V, 12 V		M9NV	M9N	•	•	•	0	ı	0	IC							
ڃ		Grommet		3-wire (PNP)		5 V, 12 V		M9PV	M9P	•	•	•	0	_	0	circuit							
switch				2-wire		12 V		M9BV	M9B	•	•	•	0	_	0	_							
S		Connector		Z-WITE		12 V		_	H7C	•	l	•	•	•	_								
auto	Diagnostic indication			3-wire (NPN)		5 V, 12 V		M9NWV	M9NW	•	•	•	0	_	0	IC	Relay,						
	(2-color indicator)		Yes	3-wire (PNP)	24 V	J V, 12 V	_	M9PWV	M9PW	•	•	•	0	-	0	circuit	PLC						
state			2-wire		12 V		M9BWV	M9BW	•	•	•	0	ı	0	_]							
S	Water resistant (2-color indicator)		3-wire (NPN)	PN)	5 V, 12 V		M9NAV*1	M9NA*1	0	0	•	0	_	0	IC								
Solid		lor indicator) 3-wire (PNP) 2-wire	J V, 12 V		M9PAV*1	M9PA*1	0	0	•	0	-	0	circuit										
S									´	′ I		2-wire		12 V		M9BAV*1	M9BA*1	0	0	•	0	ı	0
	With diagnostic output (2-color indicator)			4-wire (NPN)		5 V, 12 V		_	H7NF	•	_	•	0	_	0	IC circuit							
_			Yes	3-wire (NPN equivalent)	_	5 V	_	A96V	A96	•	-	•	_	-	_	IC circuit	_						
switch			162				100 V	A93V*2	A93	•	•	•	•	ı	_	_							
<u>×</u>		Grommet	None				100 V or less	A90V	A90	•	_	•	_	_	_	IC circuit							
ő			Yes			12 V	100 V, 200 V	_	B54	•	-	•	•	-	_		Relay,						
auto		None 2-wire 24	24 V 12 V	200 V or less	_	B64	•	_	•	_	_	_		PLC									
Reed		Connector	Connector Ye	Yes					_	C73C	•	_	•	•	•	_] - = 0					
æ			None	e			24 V or less	_	C80C	•	_	•	•	•	_	IC circuit]						
	Diagnostic indication	Grommet	Yes			_	_	_	B59W	•	_	•	I —	_	_	_							

- * Lead wire length symbols: 0.5 m ··
 - 0.5 m ······· Nil (Example) M9NW
 1 m ······ M (Example) M9NWM
 - 3 m L (Example) M9NWL 5 m Z (Example) M9NWZ None N (Example) H7CN
- * Solid state auto switches marked with "O" are produced upon receipt of order.
- * D-A9□V□/M9□V□/M9□WV□/M9□A(V) types cannot be mounted.
 *1 Water resistant type auto switches can be mounted on the above models, but in such case SMC cannot guarantee water resistance. Consult with SMC regarding water resistant types with the above model numbers.
- *2 1 m type lead wire is only applicable to D-A93.
- * Since there are other applicable auto switches than listed, refer to page 1215 for details.
- * For details about auto switches with pre-wired connector, refer to pages 1410 and 1411.
- * D-A9□/M9□/M9□W auto switches are shipped together (not assembled). (Only auto switch mounting brackets are assembled before shipped.)

A hexagon shaped rod that does not rotate.

Non-rotating accuracy ø20, ø25 — ±0.7° Ø32. Ø40 — ±0.5°


Can operate without lubrication.


Auto switches can also be mounted.

Can be installed with auto switches to facilitate the detection of the cylinder's stroke position.



Symbol Rubber bumper







Symbol	Specifications
-ХА□	Change of rod end shape

Specifications

Applicable bore s	Applicable bore size (mm)			32	40			
Rod non-rotatin	g accuracy	±0	.7°	±0.5°				
Action		Single a	cting, Spring	return/Spring	g extend			
Fluid			Α	ir				
Cushion			Rubber	bumper				
Proof pressure			1.0	MPa				
Maximum opera	ting pressure			MPa				
Minimum operat	Minimum operating pressure			0.18 MPa spring return 0.23 MPa spring extend				
Ambient and flu	Ambient and fluid temperature			-10 to 50°C (No freezing)				
Lubrication	Lubrication			Not required (Non-lube)				
Stroke length to	Stroke length tolerance			+ 1.4 0				
Piping	Screw-in type	Rc 1/8						
pg	Built-in One-touch fitting							
Piston speed (m	m/s)	50 to 700	50 to 650	50 to 590	50 to 420			
Allowable kinetic energy		0.27 J	0.4 J	0.65 J	1.2 J			
Mounting		Basic type, Axial foot type, Rod side flange type, Head side flange type, Single clevis type, Double clevis type, Head side trunnion type, Rod side trunnion type						

Calanaid Value Cassifications

Series			SYJ519		
Manual override			Non-locking push type, Push-turn locking slotted type, Push-turn locking lever type		
Pilot exhaust			Pilot valve indiv	idual exh. Type	
Impact/Vibration resis	tance	e (m/s²) ^{Note 1)}	150)/30	
Enclosure			Dust	proof	
Electrical entry			Grommet (G), L plug connector (L), M plug connector (M), DIN terminal (D)		
		G, L, M	D		
Coil rated voltage DC		24, 12, 6, 5, 3	24, 12		
(V)	AC 50/60 Hz		100, 110, 200, 220		
Allowable voltage			±10% of the rated voltage*		
Power consumption (W)Note 2	DC		0.35 (With light: 0.4 (DIN terminal with light: 0.45))		
		100 V	0.78 (With light: 0.81)	0.78 (With light: 0.87)	
		110 V	0.86 (With light: 0.89)	0.86 (With light: 0.97)	
Apparent power	AC	[115 V]	[0.94 (With light: 0.97)]	[0.94 (With light: 1.07)]	
(VA) Note 2)	٦	200 V	1.18 (With light: 1.22)	1.15 (With light: 1.30)	
		220 V	1.30 (With light: 1.34)	1.27 (With light: 1.46)	
		[230 V]	[1.42 (With light: 1.46)]	[1.39 (With light: 1.60)]	
Surge voltage suppressor			Diode (DIN terminal, Varistor when non-polar types)		
Indicator light			LED (Neon light when AC with DIN terminal)		

- * Based on IEC60529
- * In common between 110 VAC and 115 VAC, and between 220 VAC and 230 VAC. * For 115 VAC and 230 VAC, the allowable voltage is -15% to +5% of rated voltage.

Note 1) Impact resistance: No malfunction occurred when it is tested in the axial direction and at the right angles to the main valve and armature in both energized and de-energized states every once for each condition. (Values at the initial period)

Vibration resistance: No malfunction occurred in a one-sweep test between 45 and 2000 Hz. The test was performed at both energized and de-energized states in the axial direction and at the right angles to the main valve and armature. (Values at the initial period)

Note 2) At the rated voltage

Standard Stroke

Bore size (mm)	Standard stroke (mm) Note)
20	25, 50, 75, 100, 125, 150 *
25	25, 50, 75, 100, 125, 150 *
32	25, 50, 75, 100, 125, 150, 200 *
40	25, 50, 75, 100, 125, 150, 200, 250 *

Note 1) Intermediate stroke other than above is manufactured upon receipt of order. Note 2) Strokes marked with "*" are the maximum strokes which are available.

Mounting Bracket Part No.

Bore size (mm)	20	25	32	40
Axial foot*	CM-L020B	CM-L	.032B	CM-L040B
Flange	CM-F020B	CM-F	032B	CM-F040B
Single clevis	CM-C020B	CM-C032B		CM-C040B
Double clevis**	CM-D020B	CM-E	032B	CM-D040B
Trunnion (With nut)	CM-T020B	CM-T	032B	CM-T040B

- * Two foot brackets and a mounting nut are attached
- When ordering the foot bracket, order 2 pcs. per cylinder.
- ** Clevis pin and retaining ring (cotter pin for ø40) are packaged together.

Refer to pages 1212 to 1215 for cylinders with auto switches.

- · Proper auto switch mounting position (detection at stroke end) and mounting height
- · Minimum auto switch mounting stroke
- · Operating range
- · Auto switch mounting bracket: Part no.

Theoretical Output

Refer to the Technical Data (Theoretical Output 1) in the Web Catalog.

Spring Reaction Force

Refer to the Technical Data (Table 2: Spring Reaction Force) in the Web Catalog.



Valve Mounted Cylinder: Non-rotating Rod Type Single Acting, Spring Return/Extend CVM3K Series

Mounting Bracket and Accessory

Accessory	Accessory Standard equipment			Option			
Mounting	Mounting nut	Rod end nut	Clevis pin	Single knuckle joint	Double knuckle joint	Pivot bracket	Pivot bracket pin
Basic type	• (1 pc.)	•	_	•	•		
Axial foot type	• (2)	•	_	•	•		
Rod side flange type	• (1)	•	_	•	•	_	_
Head side flange type	• (1)	•	_	•	•		
Single clevis type	— ⁽¹⁾	•	_	•	•	•	•
Double clevis type (3)	— ⁽¹⁾	•	• (4)	•	•	_	_
Head side trunnion type	• (1) (2)	•	_	•	•	_	
Rod side trunnion type	• (1) (2)	•	_	•	•	•	_

Note 1) Mounting nut is not equipped with single clevis type and double clevis type.

Note 2) Trunnion nuts are equipped for head side trunnion and rod side trunnion.

Note 3) Pin and retaining ring are shipped together with double clevis and double knuckle joint.

Note 3) Pin and retaining ring are shipped together with double clevis and double knuckle joint. Note 4) Retaining rings (cotter pins for ø40) are included in clevis pins.

Note 5) Pin and retaining ring are not included in pivot bracket.

Note 6) Retaining rings are included in pivot bracket pin.

Weight

Sprin	Spring Return/(): Denotes Spring Extend. (kg							
	Bore size (mm)	20	25	32	40			
	25 stroke	0.27 (0.27)	0.37 (0.37)	0.49 (0.48)	0.84 (0.83)			
	50 stroke	0.29 (0.29)	0.40 (0.40)	0.53 (0.53)	0.91 (0.90)			
	75 stroke	0.34 (0.34)	0.49 (0.48)	0.65 (0.63)	1.10 (1.06)			
Basic	100 stroke	0.36 (0.36)	0.52 (0.51)	0.70 (0.67)	1.16 (1.13)			
weight	125 stroke	0.42 (0.41)	0.61 (0.58)	0.83 (0.79)	1.36 (1.30)			
	150 stroke	0.44 (0.43)	0.64 (0.61)	0.87 (0.83)	1.43 (1.37)			
	200 stroke	_	_	1.03 (0.99)	1.68 (1.60)			
	250 stroke	_	_	_	1.94 (1.82)			
	Axial foot	0.15 (0.15)	0.16 (0.16)	0.16 (0.16)	0.27 (0.27)			
Mounting	Flange	0.06 (0.06)	0.09 (0.09)	0.09 (0.09)	0.12 (0.12)			
bracket weight	Single clevis	0.04 (0.04)	0.04 (0.04)	0.04 (0.04)	0.09 (0.09)			
weigni	Double clevis	0.05 (0.05)	0.06 (0.06)	0.06 (0.06)	0.13 (0.13)			
	Trunnion	0.04 (0.04)	0.07 (0.07)	0.07 (0.07)	0.10 (0.10)			
Option bracket weight	Single knuckle joint	0.06 (0.06)	0.06 (0.06)	0.06 (0.06)	0.23 (0.23)			
	Double knuckle (With pin)	0.07 (0.07)	0.07 (0.07)	0.07 (0.07)	0.20 (0.20)			

Calculation: (Example) CVM3KL32-100S-1G (ø32, 100 stroke, Spring return)

Weight of brackets------0.16 (kg)
 0.70 + 0.16 = 0.86 kg

Add 0.03 kg for the DIN terminal.

Manual Operation

Manual operation is possible by pushing the manual button indicated with the arrow.



↑ Precautions


Be sure to read this before handling the products. Refer to page 9 for safety instructions, pages 10 to 19 for actuator and auto switch precautions, and 3/4/5 port solenoid valve precautions on the SMC web site: https://www.smcworld.com

Operating Precautions

 Avoid using the air cylinder in such a way that rotational torque would be applied to the piston rod.

If rotational torque is applied, the non-rotating guide will deform, causing a loss of non-rotating accuracy. Also, to screw a bracket or a nut onto the threaded portion at the end of the piston rod, make sure to retract the piston rod entirely, and place a wrench on the parallel sections of the rod that protrudes. To tighten, take precautions to prevent the tightening torque from being applied to the non-rotating guide.

Allowable rotational torque	ø 20	ø 25	ø 32	ø 40
(N·m or less)	0.2	0.25	0.25	0.44



Disassembly/Replacement

When replacing rod seals, please contact
 SMC.

Air leakage may be happened, depending on the position in which a rod seal is fitted. Thus, please contact SMC when replacing them.

Model Selection

1. Confirm the specifications.

Products in this catalog are designed to be used for compressed air systems. If not operated within the designated pressure or temperature, it may damage the products or cause malfunction. (Refer to specifications.)


2. Energizing continuously for a long period of time

When the valve is continuously energized for a long period of time, the performance may deteriorate or affect peripheral equipment adversely since temperature rises when coils generate heat.



CVM3K Series

Construction



Component Parts

Description	Material	Note
Rod cover	Aluminum alloy	Anodized
Head cover	Aluminum alloy	Anodized
Cylinder tube	Stainless steel	
Piston	Aluminum alloy	
Piston rod	Stainless steel	
Non-rotating guide	Bearing alloy	
Seal retainer	Rolled steel	Nickel plated
Return spring	Steel wire	Zinc chromated
Spring guide	Aluminum alloy	
Spring seat	Aluminum alloy	
Plug with fixed orifice	Alloy steel	Black dyed
Retaining ring	Carbon steel	Phosphate coated
Sub-plate	Aluminum alloy	Metallic painted
Hex. socket head cap screw with spring washer	Stainless steel	
Plate	Aluminum alloy	Metallic painted
Hex. socket head cap screw with spring washer	Stainless steel	
Solenoid valve	_	Refer to the below.*
Bumper	Urethane	
Bumper A	Urethane	
	Rod cover Head cover Cylinder tube Piston Piston rod Non-rotating guide Seal retainer Return spring Spring guide Spring guide Spring seat Plug with fixed orifice Retaining ring Sub-plate Hex societ head cap screw with spring washer Plate Hex societ head cap screw with spring washer Solemoid valve Bumper	Rod cover Aluminum alloy Head cover Aluminum alloy Cylinder tube Stainless steel Piston Aluminum alloy Piston rod Stainless steel Non-rotating guide Bearing alloy Seal retainer Rolled steel Return spring Steel wire Spring guide Aluminum alloy Spring seat Aluminum alloy Plug with fixed orifice Alloy steel Retaining ring Carbon steel Sub-plate Aluminum alloy His. sociat head cap screw with spring washer Plate Aluminum alloy Stainless steel Solenoid valve Garbon steel Solenoid valve Urethane Urethane

SYJ519 -		N
Rated voltage •	Manual override	
Electrical entry		_
	voltage suppressor	

* How to order solenoid valves

Nii Valves other than those below
All valves with a DC rated voltage
Valves with an AC rated voltage
(DIN terminal only)

Component Parts


No.	Description	Material	Note
20	Bumper B	Urethane	
21	Retaining ring	Stainless steel	
22	Piston seal	NBR	
23	Piston gasket	NBR	
24	Wear ring	Resin	
25	Head cover gasket	NBR	
26	Sub-plate gasket	NBR	
27	Gasket	NBR	
28	Pipe gasket	Urethane rubber	
29	Gasket	Resin	
30	Spacer gasket	Resin	
31	Stud	Brass	Electroless nickel plated
32	Pipe	Aluminum alloy	
33	Mounting nut	Carbon steel	Nickel plated
34	Rod end nut	Carbon steel	Zinc chromated
36	One-touch fitting	_	Port size: ø6


Replacement Parts/Seal Kit


No.	Description	Material		Parl	no.	
INO.	Description	ivialeriai	20	25	32	40
35	Rod seal	NBR	CM2K20-PS	CM2K25-PS	CM2K32-PS	CM2K40-PS

^{*} Since the seal kit does not include a grease pack, order it separately. Grease pack part no.: GR-S-010 (10g)

Basic Type (B): External Dimensions







																(mm)
Bore size (mm)	Α	AL	B₁	B ₂	Eh₃	F	Н	Ηı	H ₂	НХ	ı	KA	MM	N	NA	NN
20	18	15.5	13	26	20 0 0 0 0	13	41	5	8	57.5	28	8.2	M8 x 1.25	15	24	M20 x 1.5
25	22	19.5	17	32	26 -0.033	13	45	6	8	63.5	33.5	10.2	M10 x 1.25	15	30	M26 x 1.5
32	22	19.5	17	32	26 0 0 0	13	45	6	8	68	37.5	12.2	M10 x 1.25	15	34.5	M26 x 1.5
40	24	21	22	41	32 0 0	16	50	8	10	76	46.5	14.2	M14 x 1.5	21.5	42.5	M32 x 2

Dimensi	Dimensions by Stroke (mm														
Bore Sympa	1 to	50	51 to	100	101 t	0 150	151 t	o 200	201 t	201 to 250					
Bore Symbol size (mm)	S	S ZZ		ZZ	S	ZZ	S ZZ		S	ZZ					
20	87	141	112	166	137	191	_	_	_	_					
25	87	145	112	170	137	195	_	_	_	_					
32	89	147	114	172	139	197	164	222	_						
40	113	179	138	204	163	229	188	254	213	279					

Single Actir	ıg/Sprir	ng Exte	nd (mm)
Bore size (mm)	нх	Q	QY
20	65.3	19.8	14
25	70.5	22	14
32	76.5	25.8	16
40	84.5	29.8	16


CVM3 Series

Auto Switch Mounting 1

Auto Switch Proper Mounting Position (Detection at Stroke End) and Its Mounting Height


Reed auto switch

D-A9□




(): For D-A96 type A and B are the dimensions from the end of the head cover/rod cover to the end of the auto switch.


D-C7/C8



D-B5/B6/B59W




D-C73C/C80C




Solid state auto switch


D-M9□




D-H7 - /H7 - W/H7NF



D-G5NT



D-H7C



(mm)

Auto Switch Proper Mounting Position (Detection at Stroke End) and Its Mounting Height: Single Acting, Spring Return (S)/Spring Extend (T)

Auto Switch Proper Mounting Position: Standard, Spring Return (S) Non-Rotating, Spring Return (S)

	A dimension												
Auto switch model	Bore size			A dimension			В						
riato omitar moder	DOTC SIZE	to 15st	51 to 100st	101 to 150st	151 to 200st	201 to 250st							
	20	31.5	56.5	81.5	_	_	5.5						
D-A9□(V)	25	31.5	56.5	81.5	_	_	5.5						
D-A9□(V)	32	32.5	57.5	82.5	107.5	_	6.5						
	40	38.5	63.5	88.5	113.5	138.5	11.5						
D-M9□(V)	20	35.5	60.5	60.5 85.5 —		_	9.5						
D-M9□W(V)	25	35.5	60.5 85.5 —		_	9.5							
D-M9□A(V)	32	36.5	61.5 86.5 111.5		_	10.5							
D-INI3 HA(V)	40	42.5	67.5	92.5	92.5 117.5 142.5		15.5						
	20	26	51	76	_	_	0						
D-B5□	25	26	51	76	_	_	0						
D-B64	32	27	52	77	102	_	1						
	40	32	57	82	107	132	6						
D-C7□	20	32	57	82	_	_	6						
D-C80	25	32	57	82	_	_	6						
D-C73C	32	33	58	83	108	_	7						
D-C80C	40	38	63	88	113	138	12						
	20	29	54	79	_	_	3						
D-B59W	25	29	54	79	_	_	3						
D-D39W	32	30	55	80	105	_	4						
	40	35	60	85	110	135	9						
D-H7□	20	31	56	81	_	_	5						
D-H7C	25	31	56	81	_	_	5						
D-H7□W	32	32	57	82	107	_	6						
D-H7NF	40	37	62	87	112	137	11						
	20	27.5	52.5	77.5	_	_	1.5						
D-G5NT	25	27.5	52.5	77.5	_	_	1.5						
	32	28.5	53.5	78.5	103.5	_	2.5						
	40	33.5	58.5	83.5	108.5	133.5	7.5						

Auto Switch Proper Mounting Position: Standard, Spring Extend (T)

Non-Rotating	g, Spring	Extend	(1)				(mm)	
Auto switch model	D	Α			B dimension			
Auto switch model	Bore size	_ ^	to 15st	51 to 100st	101 to 150st	151 to 200st	201 to 250st	
	20	6.5	30.5	55.5	80.5	_	_	
D-A9□(V)	25	6.5	30.5	55.5	80.5	_	_	
D-A9□(V)	32	7.5	31.5	56.5	81.5	106.5	_	
	40	13.5	36.5	61.5	86.5	111.5	136.5	
D MODAY	20	10.5	34.5			ı	_	
D-M9□(V) D-M9□W(V)	25	10.5	34.5	59.5 84.5			_	
D-M9□A(V)	32	11.5	35.5	60.5	85.5 110.5		_	
D-W3⊟A(V)	40	17.5	40.5	65.5	90.5	115.5	140.5	
	20	1	25 50 75 —		_	_		
D-B5□	25	1	25	50	75	_	_	
D-B64	32	2	26			101	_	
	40	7	31	56	81	106	131	
D-C7□	20	7	31	56	81	_	_	
D-C80	25	7	31 56 81 -			_		
D-C73C	32	8	32 57 82 107		107	_		
D-C80C	40	13	37	62	87	112	137	
	20	4	28	53	78		_	
D-B59W	25	4	28	53	78	_	_	
D-D3311	32	5	29	54	79	104	_	
	40	10	34	59	84	109	134	
D-H7□	20	6	30	55	80	_	_	
D-H7C	25	6	30	55	80		_	
	32	7	31	56	81	106	_	
D-H7NF	40	12	36	61	86	111	136	
D-H7□W D-H7NF D-G5NT	20	2.5	26.5	51.5	76.5		_	
	25	2.5	26.5	51.5	76.5		_	
	32	3.5	27.5	52.5	77.5	102.5	_	
	40	8.5	32.5	57.5	81.5	107.5	132.5	

Note) Adjust the auto switch after confirming the operating conditions in the actual setting.

CVM3 Series

Auto Switch Mounting 2

Auto Switch Proper Mounting Position (Detection at Stroke End) and Its Mounting Height

Auto Switch	Mounting Heig	ght		(mm)
Auto switch model Bore size	D-A9□(V) D-M9□(V) D-M9□W(V) D-M9□A(V)	D-B5□ D-B64 D-B59W D-G5NT D-H7C	D-C7□ D-C80 D-H7□ D-H7□W D-H7NF	D-C73C D-C80C
(mm)	Hs	Hs	Hs	Hs
20	23	25.5	22.5	25
25	25.5	28	25	27.5
32	29	31.5	28.5	31
40	33	35.5	32.5	35


Minimum Auto Switch Mounting Stroke

n: No of auto ewitches (mm

					n: No. of auto switches (mm)
Auto switch			No. of auto switch mounted		
model	1	2			1
		Different surfaces	Same surface	Different surfaces	Same surface
D-A9□		A = Note 1)	s = Note 1)	15 + 45 (n - 2)	45 + 45 (n - 2)
D-M9□ D-M9□W	10	15 Note 1)	45 Note 1)	(n = 2, 4, 6···) Note2)	(n = 2, 3, 4, 5···)
D-M9□V	5	20	35	20 + 35 (n - 2) 2	35 + 35 (n - 2)
				(n = 2, 4, 6···) Note2)	(n = 2, 3, 4, 5···)
D-A9□V	V 5		25	15 + 35 (n - 2)	25 + 35 (n - 2)
D-As-V	,	15	25	(n = 2, 4, 6···) Note2)	(n = 2, 3, 4, 5···)
D-M9□WV	10	00	05	20 + 35 (n - 2)	35 + 35 (n - 2)
D-M9□AV	10	20	35	(n = 2, 4, 6···) Note2)	(n = 2, 3, 4, 5···)
D-C7□	10	15	50	15 + 45 (n - 2)	50 + 45 (n - 2)
D-C80	10	15	50	(n = 2, 4, 6···) Note2)	(n = 2, 3, 4, 5···)
D-H7□ D-H7□W	10	15	60	15 + 45 (n - 2)	60 + 45 (n - 2)
D-H7□W D-H7NF	10	15	60	(n = 2, 4, 6···) Note2)	(n = 2, 3, 4, 5···)
D-C73C				15 + 50 (n - 2)	65 + 50 (n - 2)
D-C80C D-H7C	10	15	65	(n = 2, 4, 6···) Note2)	(n = 2, 3, 4, 5···)
D-B5□/B64	10	45		15 + 50 (n - 2)	75 + 55 (n - 2)
D-G5NT	10	15	75	(n = 2, 4, 6···) Note2)	(n = 2, 3, 4, 5···)
D Drow	4.5	00		20 + 50 (n - 2)	75 + 55 (n - 2)
D-B59W	15	20	75	(n = 2, 4, 6···) Note2)	(n = 2, 3, 4, 5···)

Note 2) When "n" is an odd number, an even number that is one larger than this odd number is used for the calculation.

Note 1) Auto switch mounting (The adjustment as shown in the figures below is required with the following stroke ranges.)



Operating Range

(mm)

				(111111)
		Bore	size	
Auto switch model	20	25	32	40
D-A9□(V)	6	6	6	6
D-M9□(V)/M9□W(V) D-M9□A(V)	3.5	3	3.5	3
D-C7□/C80 D-C73C/C80C	7	8	8	8
D-B5□/B64	8	8	9	9
D-B59W	12	12	13	13
D-H7□/H7□W D-G5NT/H7NF	4	4	4.5	5
D-H7C	7	8.5	9	10
* Since the operating range	is prov	ided as	s a guid	deline

Since the operating range is provided as a guideline including hysteresis, it cannot be guaranteed (assuming approximately ±30% dispersion).

[Mounting screw set made of stainless steel]

The following set of mounting screws made of stainless steel is available. Use it in accordance with the operating environment. (Please order the auto switch mounting bracket separately, since it is not included.)

BBA4: For D-C7/C8/H7 types

Note) Refer to page 1440 for the details of BBA4.


ı

Auto Switch Mounting Bracket: Part No.

A		Bore siz	ze (mm)	
Auto switch mounting	ø 20	ø 25	ø 32	ø 40
D-M9□(V) D-M9□W(V) D-A9□(V)	Note 1) BM5-020 (A set of a, b, c, d)	Note 1) BM5-025 (A set of a, b, c, d)	Note 1) BM5-032 (A set of a, b, c, d)	Note 1) BM5-040 (A set of a, b, c, d)
D-M9 □ A(V) Note 2)	BM5-020S (A set of b, c, e, f)	BM5-025S (A set of b, c, e, f)	BM5-032S (A set of b, c, e, f)	BM5-040S (A set of b, c, e, f)
D-H7□ D-H7□W D-H7NF D-C7□/C80 D-C73C/C80C	BM2-020A (A set of c and d)	BM2-025A (A set of c and d)	BM2-032A (A set of c and d)	BM2-040A (A set of c and d)
D-B5□/B64 D-B59W D-G5NT	BA2-020 (A set of c and d)	BA2-025 (A set of c and d)	BA2-032 (A set of c and d)	BA2-040 (A set of c and d)

Note 1) Since the switch bracket (made from nylon) are affected in an environment where alcohol, chloroform, methylamines, hydrochloric acid or sulfuric acid is splashed over, so it cannot be used. Please consult SMC regarding other chemicals.

Note 2) When mounting a D-MSILA(V) type auto switch, if the switch bracket is mounted on the indicator light, it may damage the auto switch. Therefore, be sure to avoid mounting the switch bracket on the indicator light.



* Band (c) is mounted so that the projected part is on the internal side (contact side with the tube).

Besides the models listed in How to Order, the following auto switches are applicable. Refer to pages 1341 to 1435 for detailed specifications.

Auto switch type	Part no.	Electrical entry (Fetching direction)	Features
Reed	D-B53, C73, C76		_
neeu	D-C80		Without indicator light
	D-H7A1, H7A2, H7B	Grommet (In-let)	_
Solid state	D-H7NW, H7PW, H7BW		Diagnostic indication (2-color)
	D-G5NT]	With timer

For solid state auto switches, auto switches with a pre-wired connector are also available. Refer to pages 1410 and 1411 for details.
 Normally closed (NC = b contact) solid state auto switches (D-M9□E(V)) are also available. Refer to page 1360 for details.


It may vary substantially depending on an ambient

Valve Mounted Cylinder Double Acting

CV3 Series

Ø40, Ø50, Ø63, Ø80, Ø100

How to Order



Applicable Auto Switches/Refer to pages 1341 to 1435 for further information on auto switches

T	0 11/ "	Electrical	ndætorigt	Wiring	L	oad volta	ge		ch model			ngth (n		Pre-wired A		licable
Type	Special function	entry	불	(Output)		C	AC	Tie-rod mounting	Band mounting	0.5 (Nil)	1 (M)	3 (L)	5 (Z)	connector		oad
				O suine (NIDNI)				M9N	_	•	•	•	0	0		
				3-wire (NPN)		5 V. 12 V			G59**	•		•	0	0	IC circuit	
		Grommet		3-wire (PNP)	24 V	J V, 12 V	_	M9P		•	•	•	0	0	IC CITCUIL	
		Grommet		o wile (i ivi)	24 *				G5P**		0	0				
				2-wire		12 V		M9B		•	•	•	0	0		
ᇷ		L	1						K59**	•	_	•	0	0	_	
₹		Terminal		3-wire (NPN)	4	12 V		G39C	G39	_	-	_	_			
S		conduit	1	2-wire				K39C	K39	=	=	=	=	-		
鱼			,	3-wire (NPN)				M9NW		-	_	-	0			Relay
a			Υes	O WIIC (IVI IV)		5 V. 12 V		_	G59W **	•	_	•	0	0	IC circuit	PLC
ate	Terminal conduit Diagnostic indication (2-color indicator)	ľ			J V, 12 V		M9PW	_	•	•	•	0	0		FLC	
1st				3-wire (PNP)			_	G5PW**	•	–	•	0	0		I	
Solid		Grommet			24 V		-	M9BW	_	•	•	•	0	0		İ
Ñ				2-wire		12 V		_	K59W **	•	<u>-</u>	•	0	0	-	
		1		3-wire (NPN)		5 V, 12 V		M9NA*1	_	0	0	•	0	0		İ
	Water resistant			3-wire (PNP)				M9PA*1	_	Ŏ	Ŏ	ě	Ŏ	Ŏ	IC circuit	
	(2-color indicator)			2-wire			1	M9BA*1	_	Ō	Ō	•	Ô	Ō	_	1
	With diagnostic output (2-color indicator)	1		4-wire (NPN)		5 V, 12 V		F59F	G59F**	•	_	•	0	0	IC circuit	
	,,		Yes	3-wire (NPN equivalent)	_	5 V	_	A96 [Z76] ***	_	•	Ι-	•	_	_	IC circuit	_
ᇷ							100 V	A93 [Z73] *2*	_	•	•	•	•	_	_	
switch		Grommet	2				100 V or less	A90 [Z80] ***	_	•	_	•	_	_	IC circuit	Relay,
	_	G. 0.1.11.10t	š				100 V, 200 V	A54	B54**	•	_	•	•	_		PLC
anto			ટ	2-wire	24 V	12 V	200 V or less	A64	B64**	•	_	•	_	_		
<u>a</u>		Terminal		Z-WIFE	2-7 V			A33C	A33		<u> </u>		_	_	l _	PLC
Reed		conduit	Yes				100 V. 200 V	A34C	A34		<u> </u>		_	_		Relay
	D:	DIN terminal	ļ٣				,	A44C	A44	<u> </u>	<u> </u>	<u> </u>	_			PLC
	Diagnostic indication (2-color indicator)	Grommet						A59W	B59W**		<u> </u>	_	-			

- *1 Water resistant type auto switches can be mounted on the above models, but in such case SMC cannot guarantee water resistance. Consult with SMC regarding water resistant types with the above model numbers.

- *Since there are other applicable auto switches than listed, refer to page 1236 for details.

 *For details about auto switches with pre-wired connector, refer to pages 1410 and 1411.

 *D-A9EJMBJMMSJMMSJMA auto switches are shipped together (not assembled). (Only auto switch mounting brackets are assembled before shipped.)
- * Solid state auto switches marked with "()" are produced upon receipt of order.
- ** D-B5\(\to /B64/G5/K5\) types are mountable only upon a receipt of order. (Not mountable after the time of shipment)
- *** D-A9 cannot be mounted on ø50. Select auto switches in brackets



- Operation type can be changed to rod extended when energized or rod retracted when energized.
- Ease of maintenance and inspection.

The solenoid valve can be separated easily and the cylinder can also be disassembled.

· A manual operation mechanism is provided as standard equipment (non-locking).



Symbol

Air cushion





Made to Order Specifications Click here for details

Symbol	Specifications			
-XA□	Change of rod end shape			
-XC4	With heavy duty scraper			
-XC15	Change of tie-rod length			
-XC29	Double knuckle joint with spring pin			
-XC65	Made of stainless steel (Combination of XC7 and XC68)			

Precautions

Minimum stroke for auto switch mounting

1. Each switch and mounting type of cylinder has different minimum mountable stroke. Be careful especially of the center trunnion type. (For details, refer to pages 1234 and 1235.)

Refer to pages 1232 to 1236 for cylinders with auto switches.

- · Proper auto switch mounting position (detection at stroke end) and mounting height
- . Minimum auto switch mounting stroke
- Operating range
- · Auto switch mounting bracket: Part no.

Specifications

opoomoa	poomoanomo							
Во	re size	(mm)	40	50	63	80	100	
Fluid			Air					
Action					Double acting	g		
Proof pressi	ure				1.35 MPa			
Maximum o	eratin	g pressure			0.9 MPa			
Ambient and fluid temperature				_	-10 to 50°C*	1		
Minimum operating pressure			0.15 MPa					
Piston speed			50 to 500 mm/s 50 to 350 mm					
Cushion			Air cushion					
Stroke lengt	h toler	ance	Up to 250 st: +1.0 251 to 1000 st: +1.4					
Lubrication			Not required (Non-lube)					
Mounting		Basic, Foot, Rod flange, Single clevis Double clevis, Center trunnion						
Port size			Rc1/4					
Allowable kinetic	Air	When activated	2.8	4.6	7.8	16	29	
energy (J)*2	cushion	When not activated	0.33	0.56	0.91	1.5	2.68	

^{*1} No freezing

Solenoid Valve Specifications

Applicable solenoid va	V3□08				
Applicable solenoid va	V3⊔08				
Coil rated voltage		Refer to	the solenoid	valve voltage shown below.	
Electrical entry		Grommet, DIN terminal			
Allowable voltage			-15 to 10% of the rated voltage		
Coil insulation		Class B or equivalent (130°C)			
		Inrush	50 Hz	8.5 VA	
Apparent power Note)	AC	IIIIusii	60 Hz	7.5 VA	
Apparent power ****	AC	11-1-6	50 Hz	7.0 VA	
	Hoic	Holding	60 Hz	5.5 VA	
Power consumption Note) DC		6 W			

Note) At the rated voltage.

Solenoid valve voltage

1 100 VAC (50/60 Hz) 2 200 VAC (50/60 Hz) 3 110 VAC (50/60 Hz) 4 220 VAC (50/60 Hz) 5 24 VDC 6 12 VDC 7 240 VAC (50/60 Hz) 8 48 VAC (50/60 Hz) B 24 VAC (50/60 Hz) P 100 VDC V 6 VDC Y 48 VDC Z 110 VDC	SOIL	illolu valve voltage
3 110 VAC (50/60 Hz) 4 220 VAC (50/60 Hz) 5 24 VDC 6 12 VDC 7 240 VAC (50/60 Hz) 8 48 VAC (50/60 Hz) B 24 VAC (50/60 Hz) P 100 VDC V 6 VDC Y 48 VDC	1	100 VAC (50/60 Hz)
4 220 VAC (50/60 Hz) 5 24 VDC 6 12 VDC 7 240 VAC (50/60 Hz) 8 48 VAC (50/60 Hz) B 24 VAC (50/60 Hz) P 100 VDC V 6 VDC Y 48 VDC	2	200 VAC (50/60 Hz)
5 24 VDC 6 12 VDC 7 240 VAC (50/60 Hz) 8 48 VAC (50/60 Hz) B 24 VAC (50/60 Hz) P 100 VDC V 6 VDC Y 48 VDC	3	110 VAC (50/60 Hz)
6 12 VDC 7 240 VAC (50/60 Hz) 8 48 VAC (50/60 Hz) B 24 VAC (50/60 Hz) P 100 VDC V 6 VDC Y 48 VDC	4	220 VAC (50/60 Hz)
7 240 VAC (50/60 Hz) 8 48 VAC (50/60 Hz) B 24 VAC (50/60 Hz) P 100 VDC V 6 VDC Y 48 VDC	5	24 VDC
8 48 VAC (50/60 Hz) B 24 VAC (50/60 Hz) P 100 VDC V 6 VDC Y 48 VDC	6	12 VDC
B 24 VAC (50/60 Hz) P 100 VDC V 6 VDC Y 48 VDC	7	240 VAC (50/60 Hz)
P 100 VDC V 6 VDC Y 48 VDC	8	48 VAC (50/60 Hz)
V 6 VDC Y 48 VDC	В	24 VAC (50/60 Hz)
Y 48 VDC	P	100 VDC
	٧	6 VDC
Z 110 VDC	Υ	48 VDC
	Z	110 VDC

Rod Boot Material

Symbol	Rod boot material	Maximum ambient temperature
J	Nylon tarpaulin	70°C
K Heat resistant tarpaulin		110°C*

^{*} Maximum ambient temperature for the rod boot itself.

* For other rated voltages, please contact SMC.

Standard Strokes

Jianuai	andard Strokes						
Bore size	Standard stroke						
DOI'R SIZE	Stroke range ①	Stroke range ②					
40	25, 50, 75, 100, 125, 150, 200, 250, 300, 350, 400, 450, 500						
50, 63	25, 50, 75, 100, 125, 150, 200, 250, 300, 350, 400, 450, 500, 600	Up to 1000					
80, 100	25, 50, 75, 100, 125, 150, 200, 250, 300, 350, 400, 450, 500, 600, 700						

Note 1) Intermediate strokes not listed above are produced upon receipt of order.

Note 2) Applicable strokes should be confirmed according to the usage. For details, refer to "Air Cylinders Model Selection" in the **Web Catalog**. In addition, the products that exceed the stroke range 1 might not be able to fulfill the specifications due to the deflection etc.


Note 3) Please consult with SMC for manufacturability and the part numbers when exceeding the stroke range (2).

Note 4) The minimum stroke length is different in the trunnion type and types with auto switch. Refer to pages 1234 and 1235.

^{*2} Activate the air cushion when operating the cylinder. If this is not done, the piston rod assembly or the tie-rods will be damaged when the allowable kinetic energy exceeds the values shown in the above table.

^{*} Refer to page 1226 for solenoid valve replacement methods and part numbers.

Opening Range of Throttle Valve and Driving Speed




Conditions: Operating pressure 0.5 MPa, Horizontal mounting, No load, Spring return side

· Driving speeds indicated above are for reference.

Piston Speed Adjustment

- 1. To slow down the piston speed, screw in the needle of the silencer exhaust throttle valve clockwise, to reduce the amount of air that is discharged.
- 2. The throttle valve needle opens fully when it is loosened 11 turns from its fully closed position.



3. After the specified speed has been set, secure the needle with the lock nut.

Weight

(kg) Bore size (mm) 40 50 63 80 100 Basic type 1.17 (1.27) 1.47 (1.60) 2.25 (2.45) 3.96 (4.27) 5.55 (5.95) Axial foot type 1.34 (1.44) 1.67 (1.80) 2.54 (2.74) 4.75 (5.06) 6.48 (6.88) Rod side flange type 1.43 (1.53) 1.88 (2.01) 2.87 (3.07) 5.06 (5.37) 6.94 (7.34) Basic weight Single clevis type 2.20 (2.33) 3.36 (3.56) 5.90 (6.21) 8.20 (8.60) 2.25 (2.38) 3.41 (3.61) 5.96 (6.27) 8.27 (8.67) Double clevis type Trunnion type 1.82 (1.97) 2.26 (3.35) 3.64 (4.00) 6.34 (6.79) 9.12 (9.71) 0.46 (0.70) 0.58 (0.87) Additional weight per each 50 mm of stroke 0.20 (0.28) 0.25 (0.35) 0.31 (0.43) Single knuckle 0.23 0.26 0.26 0.60 0.83 bracket 0.37 0.87 Double knuckle (with pin) 0.43 0.43 1 27

Calculation: (Example) CV3L40-100-1

- · Basic weight---··1.33 (kg)
- Additional weight-----0.20 (kg/50 st)
- Cylinder stroke-------100 (st) 1.33 + 0.20 x 100 ÷ 50 = 1.73 kg

*(): Steel tube type.

Accessory

Mounting		Basic type	Foot type	Rod side flange type	Single clevis type	Double* clevis type	Center trunnion type
Standard	Rod end nut	•	•	•	•	•	•
equipment	Clevis pin	_	_	_	_	•	_
Option	Single knuckle joint	•	•	•	•	•	•
	Double knuckle joint * (with pin)	•	•	•	•	•	•
	With rod boot	•	•	•	•	•	•

- * Pin, plain washer and cotter pin are packaged together with double clevis and double knuckle joint.
- * Refer to page 1225 for dimensions and part numbers of the option.

Refer to page 1220 for dimensions of the rod boot.

Mounting Bracket Part No.

Mounting Bracket Part No.

Bore size (mm)	40	50	63	80	100
Axial foot *	CA1-L04	CA1-L05	CA1-L06	CA1-L08	CA1-L10
Flange	CA1-F04	CA1-F05	CA1-F06	CA1-F08	CA1-F10
Single clevis	-	CV3-C05	CV3-C06	CV3-C08	CV3-C10
Double clevis **	-	CV3-D05	CV3-D06	CV3-D08	CV3-D10


* Order two foot brackets per cylinder.

Accessories for each mounting bracket are as follows.

Foot, Flange: Body mounting bolts, Spring washer Single clevis: Body mounting bolts, Nut, Spring washer

Double clevis: Body mounting bolts, Nut, Spring washer, Clevis pin, Flat washer, Cotter pin

Construction



Component Parts

No.	Description	Material	Q'ty	Note
1	Rod cover	Aluminum die-casted	1	Black painted
2	Head cover	Aluminum die-casted	1	Black painted
3	Cylinder tube	Aluminum alloy	1	Hard anodized
4	Piston rod	Carbon steel	1	Hard chrome plating
5	Piston	Aluminum alloy	1	
6	Cushion ring	Aluminum alloy	1	Anodized
7	Cushion ring B	Aluminum alloy	1	Anodized
8	Bushing	Special friction material	1	
9	Cushion valve	Steel wire	2	Trivalent zinc chromated
10	Retaining ring	Spring steel	2	Phosphate coating
11	Tie-rod	Carbon steel	4	Trivalent zinc chromated
12	Tie-rod nut	Rolled steel	6	Trivalent black zinc chromated
13	Spring washer	Steel wire	6	Trivalent black zinc chromated
14	Pipe	Carbon steel tube	1	Trivalent zinc chromated
15	Needle	Free-cutting steel	2	Electroless nickel plating
16	Lock nut	Carbon steel	2	Trivalent zinc chromated
17	Needle guide	Free-cutting steel	2	Electroless nickel plating
18	Plug	Chromium molybdenum steel	1	Trivalent black zinc chromated
19	Hex. socket head cap screw with SW	Carbon steel	2	Trivalent black zinc chromated
20	Rod seal	NBR	1	
21	Piston seal	NBR	1	

No.	Description No. of solenoids		Rod extended when energized	Rod retracted when energized
	Solenoid	Single	(1)	(2)
29	valve	Double	(;	3)

* How to order solenoid valves

Note 1) V3108-00 Voltage Electrical entry
Note 2) V3108-00 Voltage Electrical entry
Note 3) V3208-00 Voltage Electrical entry

Component Parts

No.	Description	Material	Q'ty	Note			
22	Cushion seal	Urethane	2				
23	Cylinder tube gasket	NBR	2				
24 [*]	Cushion valve seal	NBR	2				
25	Pipe gasket	NBR	2				
26	Head cover gasket	NBR	1				
27	Solenoid gasket	NBR	1	For single solenoid			
21	Soleliolu gasket		2	For double solenoid			
28	Wear ring	Resin	1				
30	Rod end nut	Rolled steel	1	Zinc chromated			
31	Magnet	_	(1)				

^{*} Not replaceable.

Replacement Parts: Seal Kit

Bore size (mm)	Kit no.	Contents
40	CV3N40-PS	
50	CV3N50-PS	Set of nos, above
63	CV3N63-PS	20, 21, 22, 23, 25, 26
80	CV3N80-PS	
100	CV3N100-PS	

* Seal kit includes ②, ②, ②, ②, ②, ③. Order the seal kit, based on each bore size.

(The parts indicated with number @ is not replaceable.)


* Seal kit includes a grease pack (ø40, ø50: 10 g, ø63, ø80: 20 g, ø100: 30 g). Order with the following part number when only the grease pack is needed. Grease pack part no.: GR-S-010 (10 g), GR-S-020 (20 g)

For the dimensions of DIN terminal, refer to page 1225.



CV3 Series

Basic Type: CV3B




																			(mm)
Bore size (mm)	Stroke range* (mm)	Α	AL	В	Вı	С	D	E	F	H ₁	1	L	K	KA	LL	ММ	N	Q	s
40	Up to 1000	30	27	60	22	44	16	32	10	8	18	M8 x 1.25	6	14	86	M14 x 1.5	27	38	84
50	Up to 1000	35	32	70	27	52	20	40	10	11	18	M8 x 1.25	7	18	83	M18 x 1.5	30	43.5	90
63	Up to 1000	35	32	85	27	64	20	40	10	11	18	M10 x 1.25	7	18	83	M18 x 1.5	31	49	98
80	Up to 1000	40	37	102	32	78	25	52	14	13	20	M12 x 1.75	10	22	84	M22 x 1.5	37	63	116
100	Up to 1000	40	37	116	41	92	30	52	14	16	20	M12 x 1.75	10	26	85	M26 x 1.5	40	73	126

Bore size	Without	rod boot				With ro	od boot	
(mm)	Н	ZZ	d	е	f	h	l	ZZ
40	51	221	56	43	11.2	59	1/4 stroke	229
50	58	231	64	52	11.2	66	1/4 stroke	239
63	58	239	64	52	11.2	66	1/4 stroke	247
80	71	271	76	65	12.5	80	1/4 stroke	280
100	72	283	76	65	14	81	1/4 stroke	292

^{*} The minimum stroke of the one with rod boot is 20 mm or more.

Axial Foot Type: CV3L




																				(mm)
Bore size	Stroke range*			В	B₁	С	_	_	_	Hı		v	L/A				LS			LY
(mm)	(mm)	А	AL	P	D 1	C	D		г	п	J	Λ.	NA	LD	LΠ	LL	LS	LI	LX	LY
40	Up to 1000	30	27	60	22	44	16	32	10	8	M8 x 1.25	6	14	9	40	86	138	3.2	42	70
50	Up to 1000	35	32	70	27	52	20	40	10	11	M8 x 1.25	7	18	9	45	83	144	3.2	50	80
63	Up to 1000	35	32	85	27	64	20	40	10	11	M10 x 1.25	7	18	11.5	50	83	166	3.2	59	93
80	Up to 1000	40	37	102	32	78	25	52	14	13	M12 x 1.75	10	22	13.5	65	84	204	4.5	76	116
100	Up to 1000	40	37	116	41	92	30	52	14	16	M12 x 1.75	10	26	13.5	75	85	212	6	92	133

Bore size		N	s	х	v	Without	rod boot			٧	Vith roo	d boot	
(mm)	MM	IN	3	^	T	Н	ZZ	d	е	f	h	e	ZZ
40	M14 x 1.5	27	84	27	13	51	221	56	43	11.2	59	1/4 stroke	229
50	M18 x 1.5	30	90	27	13	58	231	64	52	11.2	66	1/4 stroke	239
63	M18 x 1.5	31	98	34	16	58	239	64	52	11.2	66	1/4 stroke	247
80	M22 x 1.5	37	116	44	16	71	271	76	65	12.5	80	1/4 stroke	280
100	M26 x 1.5	40	126	43	17	72	283	76	65	14	81	1/4 stroke	292

The minimum stroke of the one with rod boot is 20 mm or more. * Long stroke



Rod Side Flange Type: CV3F



																				(mm)
Bore size (mm)	Stroke range* (mm)	Α	AL	В	B ₁	С	D	Е	FB	FD	FT	FV	FX	FY	FZ	Hı	1	J	K	KA
40	Up to 1000	30	27	60	22	44	16	32	71	9	12	60	80	42	100	8	18	M8 x 1.25	6	14
50	Up to 1000	35	32	70	27	52	20	40	81	9	12	70	90	50	110	11	18	M8 x 1.25	7	18
63	Up to 1000	35	32	85	27	64	20	40	101	11.5	15	86	105	59	130	11	18	M10 x 1.25	7	18
80	Up to 1000	40	37	102	32	78	25	52	119	13.5	18	102	130	76	160	13	20	M12 x 1.75	10	22
100	Up to 1000	40	37	116	41	92	30	52	133	13.5	18	116	150	92	180	16	20	M12 x 1.75	10	26

Bore size	LL	ММ	N	Q	-	Without	rod boot				With	rod boot	
(mm)	LL	IVIIVI	14	ų ų	3	Н	ZZ	★d	е	f	h	e	ZZ
40	86	M14 x 1.5	27	38	84	51	221	56	43	11.2	59	1/4 stroke	229
50	83	M18 x 1.5	30	43.5	90	58	231	64	52	11.2	66	1/4 stroke	239
63	83	M18 x 1.5	31	49	98	58	239	64	52	11.2	66	1/4 stroke	247
80	84	M22 x 1.5	37	63	116	71	271	76	65	12.5	80	1/4 stroke	280
100	85	M26 x 1.5	40	73	126	72	283	76	65	14	81	1/4 stroke	292


^{*} The minimum stroke of the one with rod boot is 20 mm or more. * When drilling holes to get through the rod boot for the purpose of mounting, make the holes larger


than the outer diameter (ød) of the rod boot mounting bracket.

CV3 Series

Single Clevis Type: CV3C

Bore size ø40 is not available.






** Bore siz	ze ø40 is not a	availab	le.															(mm)
Bore size** (mm)	* Stroke range* (mm)	Α	AL	В	B ₁	С	СДн10	сх	D	E	F	H ₁	ı	J	K	KA	L	LL
50	Up to 1000	35	32	70	27	52	12 +0.070	18 -0.1	20	40	10	11	18	M8 x 1.25	7	18	98	83
63	Up to 1000	35	32	85	27	64	16 +0.070	25 =0.1	20	40	10	11	18	M10 x 1.25	7	18	100	83
80	Up to 1000	40	37	102	32	78	20 +0.084	31.5 -0.1	25	52	14	13	20	M12 x 1.75	10	22	105	84
100	Up to 1000	40	37	116	41	92	25 +0.084	35.5 =0.1	30	52	14	16	20	M12 x 1.75	10	26	110	85


Bore size	ММ	N		DD.	_	With	out rod	boot				With ro	od boot	
(mm)	IVIIVI	N	Q	RR	S	Н	Z	ZZ	d	е	f	h	l	ZZ
50	M18 x 1.5	30	43.5	12	90	58	246	258	64	52	11.2	66	1/4 stroke	266
63	M18 x 1.5	31	49	16	98	58	256	272	64	52	11.2	66	1/4 stroke	280
80	M22 x 1.5	37	63	20	116	71	292	312	76	65	12.5	80	1/4 stroke	321
100	M26 x 1.5	40	73	25	126	72	308	333	76	65	14	81	1/4 stroke	342

^{*} The minimum stroke of the one with rod boot is 20 mm or more.

Double Clevis Type: CV3D

Bore size ø40 is not available.





** Bore size ø40 is not available.	
------------------------------------	--

** Bore Siz	ze ø40 is not a	avallab	ie.															(mm)
Bore size** (mm)	Stroke range* (mm)	A	AL	В	Bı	С	CD	сх	cz	D	E	F	H ₁	ı	J	к	KA	L
50	Up to 1000	35	32	70	27	52	12	18 +0.3	35.5	20	40	10	11	18	M8 x 1.25	7	18	98
63	Up to 1000	35	32	85	27	64	16	25 +0.3	50	20	40	10	11	18	M10 x 1.25	7	18	100
80	Up to 1000	40	37	102	32	78	20	31.5 +0.3	63	25	52	14	13	20	M12 x 1.75	10	22	105
100	Up to 1000	40	37	116	41	92	25	35.5 +0.3	71	30	52	14	16	20	M12 x 1.75	10	26	110


Bore size**	LL	ММ	N	_	Q RR		With	out rod	boot				With ro	d boot	
(mm)		IVIIVI	IN	l u	nn	3	Н	Z	ZZ	d	е	f	h	l	ZZ
50	83	M18 x 1.5	30	43.5	12	90	58	246	258	64	52	11.2	66	1/4 stroke	266
63	83	M18 x 1.5	31	49	16	98	58	256	272	64	52	11.2	66	1/4 stroke	280
80	84	M22 x 1.5	37	63	20	116	71	292	312	76	65	12.5	80	1/4 stroke	321
100	85	M26 x 1.5	40	73	25	126	72	308	333	76	65	14	81	1/4 stroke	342


^{*} Clevis pin, flat washer and cotter pin are shipped together. The minimum stroke with rod boot is 20 mm or more.


SMC

CV3 Series

Center Trunnion Type: CV3T









Bore size (mm)	Stroke range* (mm)	A	AL	В	Bı	С	D	Е	F	Hı	ı	J	K	KA	LL	ММ	N	Q
40	25 to 1000	30	27	60	22	44	16	32	10	8	18	M8 x 1.25	6	14	86	M14 x 1.5	27	38
50	25 to 1000	35	32	70	27	52	20	40	10	11	18	M8 x 1.25	7	18	83	M18 x 1.5	30	43.5
63	50 to 1000	35	32	85	27	64	20	40	10	11	18	M10 x 1.25	7	18	83	M18 x 1.5	31	49
80	50 to 1000	40	37	102	32	78	25	52	14	13	20	M12 x 1.75	10	22	84	M22 x 1.5	37	63
100	50 to 1000	40	37	116	41	92	30	52	14	16	20	M12 x 1.75	10	26	85	M26 x 1.5	40	73


Bore size	s	тв	Ø TD e8	TI	TQ	тт	тх	TY	TZ	Without rod boot			With rod boot					
(mm)										Н	Z	ZZ	d	е	f	h	e	ZZ
40	84	65	15 -0.032	20	45	23	85	77.5	115	51	93	221	56	43	11.2	59	1/4 stroke	229
50	90	75	15 -0.032	20	50	23	95	87.5	125	58	103	231	64	52	11.2	66	1/4 stroke	239
63	98	90	18 -0.032	20	57	28	110	102	146	58	107	239	64	52	11.2	66	1/4 stroke	247
80	116	110	25 -0.040	24	69.5	35	140	124.5	190	71	129	271	76	65	12.5	80	1/4 stroke	280
100	126	130	25 -0.040	24	79.5	43	162	144.5	212	72	135	283	76	65	14	81	1/4 stroke	292

^{*} The minimum stroke of the one with rod boot is 20 mm or more.

Electrical Entry: Dimensions for DIN Terminal








Bore size (mm)	LL	н٧	нү
40	95.5	55	64
50	92.5	60	69
63	92.5	68	77
80	93.5	76	85
100	94.5	83	92

Accessory Dimensions


I Type Single Knuckle Joint



Material: Free cutting sulfur steel (mm) Applicable bore size Αı øE1 MM U1 ØNDH10 NX I-04 40 69 M14 x 1.5 20 12+0.070 16 -0.1 22 24 55 15.5 16 -0.1 I-05 50. 63 74 27 28 60 M18 x 1.5 15.5 20 12+0.0 I-08 80 28 -0.1 91 37 36 71 M22 x 1.5 22.5 26 18+0.070

40 83 M26 x 1.5 24.5

Y Type Double Knuckle Joint




Materia	al: Cast ir	on									(mm)			
Part no.	Applicable bore size (mm)	A ₁	E1	Lı	ММ	R1	U1	ND	NX	NZ	L	Cotter pin size	Plain washer size	
Y-04D	40	22	24	55	M14 x 1.5	13	25	12	16 + 0.3	38	55.5	ø3 x 18 ℓ	Polished round 12	
Y-05D	50, 63	27	28	60	M18 x 1.5	15	27	12	16 + 0.3	38	55.5	ø3 x 18 ℓ	Polished round 12	
Y-08D	80	37	36	71	M22 x 1.5	19	28	18	28 + 0.3	55	76.5	ø4 x 25 ℓ	Polished round 18	
Y-10D	100	37	40	83	M26 x 1.5	21	38	20	30 + 0.3	61	83	ø4 x 30 €	Polished round 20	

^{*} Knuckle pin, cotter pin, and plain washer are shipped together.

Clevis Pin

105 37



I-10 100

Material: Carbon steel								
	Applicable bore size (mm)	ø Dd9	L	ø d	e	m	Applicable plain washer	Applicable cotter pin
CDP-3A	50	12 -0.050	55.5	3	47.5	4.0	Polished round 12	3 x 18
CVD-06	63	16 -0.050	75	4	65	5.0	Polished round 16	4 x 22
CVD-08	80	20 -0.065	94	5	79	7.5	Polished round 20	5 x 30
CVD-10	100	25 -0.065	105	5	90	7.5	Polished round 24	5 x 35

^{*} Cotter pins and flat washers are included.

Knuckle Pin

30 -0.1

28 20+0.084



-									
Materia		(mm)							
Part no.	Applicable bore size (mm)	øDd9	L	e	m	Ø d (Drill through)	Applicable cotter pin	Applicable plain washer	
CDP-3A	40, 50, 63	12 -0.050	55.5	47.5	4	3	ø3 x 18 L	Polished round 12	
CDP-5A	80	18 -0.050	76.5	66.5	5	4	ø4 x 25 L	Polished round 18	
CDP-6A	100	20 -0.065	83	73	5	4		Polished round 20	

^{*} Cotter pins and flat washers are included.

Rod End Nut




Material: Rolled steel (mm)								
Part no.	Applicable bore size (mm)	d	Н	В	С	D		
NT-04	40	M14 x 1.5	8	22	25.4	21		
NT-05	50, 63	M18 x 1.5	11	27	31.2	26		
NT-08	80	M22 x 1.5	13	32	37	31		
NT-10	100	M26 x 1.5	16	41	47.3	39		



CV3 Series


Manual Operation


Manual operation (non-locking) is possible by pushing the manual button about 3 mm.



Solenoid Valve Replacement and Order No.

(Single solenoid)





SSWO



CV3 Series Specific Product Precautions

Be sure to read this before handling the products. Refer to page 9 for safety instructions, pages 10 to 19 for actuator and auto switch precautions, and 3/4/5-port solenoid valve precautions on the SMC website: https://www.smcworld.com

Handling

1. Do not open the cushion valve beyond the stopper. A retaining ring is installed as a cushion valve retention mechanism. Do not open the cushion valve beyond it. If not operated in accordance with the above precautions, the cushion valve may be ejected from the cover when air pressure is supplied.

Bore size (mm)	Width across flats	Socket wrench
40, 50	2.5	JIS 4648 Hexagonal wrench key 2.5
63, 80, 100	4	JIS 4648 Hexagonal wrench key 4

2. Use the air cushion at the end of cylinder stroke.

Otherwise, the tie-rod or piston rod assembly will be damaged.

⚠ Caution

- Do not use a pneumatic type as an air-hydro cylinder. It can cause oil leak.
- Do not rotate the piston rod when the rod boot is fixed.

Before rotating the piston rod, loosen the band to avoid twisting the rod boot.

 Install the rod boot with the breathing hole facing downwards or in a direction suitable to prevent dust, moisture etc. from entering easily into the rod boot.

Selection

⚠ Warning

1. Confirm the specifications.

Products in this catalog are designed to be used for compressed air systems. If not operated within the designated pressure or temperature, it may damage the products or cause malfunction. (Refer to specifications.)

2. Energizing continuously for a long period of time

When the valve is continuously energized for a long period of time, the performance may deteriorate or effect peripheral equipment adversely since temperature rises when coils generate heat.

Disassembly/Replacement

⚠ Caution

1. Use a socket wrench when the bracket is replaced.

If other tools are used, the nut or other parts may be deformed or the work efficiency may decrease. For applicable sockets, refer to the table below.

Bore size (mm)	Nut	Width across flats		Tightening torque (N·m)	
40, 50	DA00180	13	JIS B4636	7.4	
40, 50	(M8 x 1.25, Hexagon nut 3 types)	13	+ Two-angle socket 13	7.4	
63	DA00008	17	JIS B4636	20	
03	(M10 x 1.25, Hexagon nut 3 types)	''	+ Two-angle socket 17		
80, 100	DA00013	19 JIS B4636		29	
ou, 100	(M12 x 1.75, Hexagon nut 3 types)	19	+ Two-angle socket 19	29	

2. Do not replace the bushing.

As the bushing is press-fit, replace the cover assembly when the bushing must be replaced.

When a seal is replaced, apply grease to the new seal before it is assembled.

Operation of the cylinder without greasing will result in extreme abrasion of the seal, causing premature air leakage.

Do not disassemble the trunnion type cylinder because the mounting precision is required.

It is difficult to align the axial center of the trunnion with the axial center of the cylinder. Thus, if this type of cylinder is disassembled and reassembled, the required dimensional accuracy cannot be attained, which may lead to malfunctions.




Valve Mounted Cylinder: Non-rotating Rod Type **Double Acting**

CV3K Series

ø40, ø50, ø63

How to Order



Applicable Auto Switches/Refer to pages 1341 to 1435 for further information on auto switches

Typo	Special function	Electrical	Indicator	Wiring	L	oad volta			itch model	Lead wi				Pre-wired	App	licable							
Type	Special function	entry	ğis	(Output)	D	C	AC		Band mounting	0.5 (Nil)	1 (M)	3 (L)	5 (Z)	connector	i ie	oad							
	Grommet ——			3-wire (NPN)		5 1/ 40 1/		M9N —	G59**		•	•	0	0	IC circuit								
		Grommet		3-wire (PNP)	24 V	5 V, 12 V	_	M9P	 G5P**	•	•	•	0	0	IIC CITCUIL								
등			2-wire		12 V		М9В	_		•	ě	ŏ	0										
swit			3-wire (NPN)		12 V		G39C	K59** G39	•	=	-	0	0	_									
2		conduit		2-wire		12 V		K39C	K39	-	-	=	_	_									
	Diagnostic indication	Yes	3-wire (NPN)				M9NW	G59W**		•	•	8	0	IC circuit	Relay, PLC								
state		Diagnostic indication	3-wire (PNP)			5 V, 12 V	5 V, 12 V		M9PW	_		•	ě	ŏ	Ö	I G GIIGGII	1 20						
ğ				o wile (i iti)			_	- MODW	G5PW**		=	•	0	0									
Solid		Grommet		2-wire	12 V		M9BW	K59W**		•	-	8	0	-									
	Water resistant			3-wire (NPN)	5 V 12] [ĺ			5 V, 12 V		M9NA*1	_	Ŏ	0	ě	ŏ	Ō	IC circuit			
	(2-color indicator)			3-wire (PNP) 2-wire		12 V		M9PA*1 M9BA*1		0	8	•	0	0	TO GITGUIL								
	With diagnostic output (2-color indicator)			4-wire (NPN)		5 V, 12 V		F59F	G59F**	ĕ	Ĭ	ě	ŏ		IC circuit								
_			8	3-wire (NPN equivalent)		5 V		A96 [Z76] ***		•		•	=	_	IC circuit	_							
호		A	╠				100 V	A93 [Z73] *2		•	•	•	•			Deless							
switch		Grommet	8				100 V or less 100 V, 200 V	A90 [Z80] *** A54	B54**		H	-	_		IC circuit	Relay, PLC							
ş	and and		No Yes			V 12 V	200 V or less	A64	B64**	-	⇇	-	_			1 LO							
an		Terminal		2-wire	24 V		_	A33C	A33		1-	Ť	—	_		PLC							
Reed		conduit	8				100 V. 200 V	A34C	A34		=		_	_	_	Relay,							
æ	Discussitie indication (O cales indicates)	DIN terminal Grommet	>	1									l —	100 1,200 1	A44C	A44		 -	=	_	_		PLC
	Diagnostic indication (2-color indicator)	Grornmet	ı	1		. – 1	_	A59W	B59W**		1-		1-	_	I	1							

- *1 Water resistant type auto switches can be mounted on the above models, but in such case SMC cannot guarantee water resistance. Consult with SMC regarding water resistant types with the above model numbers.

 *2 1 m type lead wire is only applicable to D-A93.

- (Example) M9NW (Example) M9NWM (Example) M9NWL * Lead wire length symbols: 0.5 m Nil 1 m..... M 3 m L 5 m Z (Example) M9NWZ
- * Since there are other applicable auto switches than listed, refer to page 1236 for details * For details about auto switches with pre-wired connector, refer to pages 1410 and 1411 * D-A9□/M9□/M9□W/M9□A auto switches are shipped together (not assembled). (Only auto switch mounting brackets are assembled before shipped.)
- *Solid state auto switches marked with "O" are produced upon receipt of order. **D-B5□/B64/G5/K5□ types are mountable only upon a receipt of order. (Not mountable after the time of shipment)
- ***D-A9 cannot be mounted on ø50. Select auto switches in brackets

Valve Mounted Cylinder: Non-rotating Rod Type Double Acting CV3K Series

Adjustable speed.

Built-in throttle valves are provided to enable speed adjustments in each direction.

Operation type can be changed to rod extended when energized or rod retracted when energized.

A manual operation mechanism is provided as standard equipment (non-locking).

An auto switch cylinder with the switch installed can also be manufactured.



Symbol Air cushion





Symbol	Specifications
-XA□	Change of rod end shape
-XC15	Change of tie-rod length

Refer to pages 1232 to 1236 for cylinders with auto switches.

- Proper auto switch mounting position (detection at stroke end) and mounting height
- Minimum auto switch mounting stroke
- Operating range
- Auto switch mounting bracket: Part no.

Specifications

Bo	ore size (mr	n)	40	50	63			
Fluid			Air					
Proof press	ure			1.35 MPa				
Maximum o	perating p	ressure		0.9 MPa				
Minimum o	perating pr	essure		0.15 MPa				
Ambient an	d fluid tem	perature	−10 to 50°C					
Piston spee	ed		50 to 500 mm/s					
Cushion			Air cushion					
Stroke leng	th tolerand	e	Up to 250 st:+ 1.0, 251 to 600 st:+ 1.4					
Rod non-ro	tating accu	ıracy	±0.8°					
Allowable re	otational to	orque	0.44 N·m or less					
Lubrication			Not required (Non-lube)					
Mounting			Basic, Axial foot, Rod flange, Single clevis Double clevis, Center trunnion					
Allowable kinetic energy (J)	Air	When activated	2.8	4.6	7.8			
	cushion	When not activated	0.33	0.56	0.91			

^{*} No freezing

Solenoid Valve Specifications

Applicable solenoid va	lve model		V3□08				
Coil rated voltage		Refer	Refer to the solenoid valve voltage shown below.				
Electrical entry			Grommet, DIN terminal				
Allowable voltage		-15 to 10% of the rated voltage					
Coil insulation		Class B or equivalent (130°C)					
		Inrush	50 Hz	8.5 VA			
A Noto	AC		60 Hz	7.5 VA			
Apparent power Note)	AC	Holding	50 Hz	7.0 VA			
		Holding	60 Hz	5.5 VA			
Power consumption Note)	DC	6 W					

Note) At the rated voltage.

Solenoid valve voltage

1	100 VAC (50/60 Hz)
2	200 VAC (50/60 Hz)
3	110 VAC (50/60 Hz)
4	220 VAC (50/60 Hz)
5	24 VDC
6	12 VDC
7	240 VAC (50/60 Hz)
8	48 VAC (50/60 Hz)
В	24 VAC (50/60 Hz)
Р	100 VDC
٧	6 VDC
Υ	48 VDC
Z	110 VDC

^{*} For other rated voltages, please contact SMC.

Rod Boot Material

Symbol	Rod boot material	Max. ambient temperature					
J	Nylon tarpaulin	70°C					
K	Heat resistant tarpaulin	110°C*					

Maximum ambient temperature for the rod boot itself.

Standard Stroke

Bore size (mm)	Standard stroke (mm)
40	25, 50, 75, 100, 125, 150, 200, 250, 300, 350, 400, 450, 500*
50, 63	25, 50, 75, 100, 125, 150, 200, 250, 300, 350, 400, 450, 500, 600*

Note) The cylinders with the standard strokes indicated above can be delivered in a short term.

- Intermediate stroke except mentioned above is manufactured upon receipt of order.
- When the auto switch is attached, the minimum stroke is going to be different. Refer to pages 1234 and 1235.

 The street of the stree


The minimum stroke length is different in the trunnion type. Refer to pages 1234 and 1235 for further information.

Please consult with SMC for longer strokes than the strokes marked with *.



CV3K Series

Opening Range of Throttle Valve and Driving Speed



Conditions: Operating pressure 0.5 MPa, Horizontal mounting, No load, Spring return side

. The speeds shown in the graph are for reference.

Weight				(kg)
	Bore size (mm)	40	50	63
	Basic type	1.20	1.52	2.36
	Axial foot type	1.37	1.72	2.65
Basic	Rod side flange type	1.46	1.93	2.98
weight	Single clevis type	_	2.25	3.47
	Double clevis type	_	2.30	3.52
	Trunnion type	1.85	2.31	3.75
Additional we	ight per each 50 mm of stroke	0.20	0.25	0.31
Accessory	Single knuckle	0.23	0.26	0.26
bracket	Double knuckle (with pin)	0.37	0.43	0.43

Calculation: (Example) CV3KL40-100-1

 Basic weight-----1.36 (kg) Additional weight-----0.20 (kg/50 st)

• Cylinder stroke------100 (st) 1.36 + 0.20 x 100 ÷ 50 = 1.76 kg

Accessory

	· • · · y						
	Mounting	Basic type	Foot type	Rod side flange type	Single clevis type	Double * clevis type	Center trunnion type
Standard	Rod end nut	•	•	•	•	•	•
equipment	Clevis pin	-	-	-	-	•	-
	Single knuckle joint	•	•	•	•	•	•
Option	Double knuckle joint * (with pin)	•	•	•	•	•	•
	With rod boot	•	•	•	•	•	•

- * Pin, plain washer and cotter pin are shipped together with double clevis and double knuckle joint.
- * Refer to page 1225 for dimensions and part numbers of the option.

Refer to page 1231 for dimensions of the rod boot.

Handling

- 1. Adjusting of the piston speed
- 2. Change of voltage specifications
- 3. Manual operation
- 4. Changing between rod extended when energized and rod retracted when energized.

Since the operations above 1. to 4. are the same as the CV3 series, refer to pages 1218 and 1226.



Precautions

Be sure to read this before handling the products. Refer to page 9 for safety instructions and pages 11261 to 1128 for common precautions. ----

Operating Precautions

1. Avoid using the air cylinder in such a way that rotational torque would be applied to the piston rod.

If rotational torque is applied, the non-rotating guide will become deformed, causing a loss of non-rotating accuracy. Also, to screw a bracket or a nut onto the threaded portion at the end of the piston rod, make sure the retract the piston rod entirely, and place a wrench on the parallel sections of the rod that protrudes. To tighten, take precautions to prevent the tightening torque from being applied to the non-rotating guide.





Disassembly/Replacement

1. When replacing rod seals, please contact SMC.

Air leakage may be happened, depending on the position in which a rod seal is fitted. Thus, please contact SMC when replacing them.

2. Do not replace the non-rotating guide. Since the non-rotating guide is press fitted, the entire cover assembly needs be replaced instead of a single part.

Selection


1. Confirm the specifications.

Products in this catalog are designed to be used for compressed air systems. If not operated within the designated pressure or temperature, it may damage the products or cause malfunction. (Refer to specifications.)

2. Energizing continuously for a long period of time

When the valve is continuously energized for a long period of time, the performance may deteriorate or effect peripheral equipment adversely since temperature rises when coils generate heat.

Construction



Component Parts

No.	Description	Material	Q'ty	Note
1	Rod cover	Aluminum die-casted	1	Black painted
2	Head cover	Aluminum die-casted	1	Black painted
3	Cylinder tube	Aluminum alloy	1	Hard anodized
4	Piston rod	Carbon steel	1	Hard chrome plated
5	Piston	Aluminum alloy	1	Trivalent chromated
6	Cushion ring A	Rolled steel	1	Trivalent zinc chromated
7	Cushion ring B	Rolled steel	1	Trivalent zinc chromated
8	Non-rotating guide	Special friction material	1	
9	Cushion valve	Steel wire	2	Trivalent zinc chromated
10	Retaining ring	Spring steel	2	Phosphate coating
11	Tie-rod	Carbon steel	4	Trivalent zinc chromated
12	Tie-rod nut	Rolled steel	6	Trivalent black zinc chromated
13	Spring washer	Steel wire	6	Trivalent black zinc chromated
14	Pipe	Caron steel tube	1	Trivalent zinc chromated
15	Needle	Free-cutting steel	2	Electroless nickel plated
16	Lock nut	Carbon steel	2	Trivalent zinc chromated
17	Needle guide	Free-cutting steel	2	Electroless nickel plated
18	Hex. socket head cap screw with SW	Carbon steel	2	Trivalent black zinc chromated

No.	Description	Material	Q'ty	Note
19	Plug	Chromium molybdenum steel	1	Trivalent black zinc chromated
20	Piston nut	Rolled steel	1	
21	Spring washer	Steel wire	1	
22	Cushion seal holder	Aluminum alloy	1	
23	Rod seal	NBR	1	
24	Piston seal	NBR	1	
25	Cushion seal	Urethane	2	
26	Cylinder tube gasket	NBR	2	
27*	Cushion valve seal	NBR	2	
28*	Piston gasket	NBR	1	
29	Pipe gasket	NBR	2	
30	Head cover gasket	NBR	1	
31	Solenoid	NBR	1	For single solenoid
31	gasket	INDI	2	For double solenoid
32	Wear ring	Resin	1	
33	Solenoid valve	-	1	
34	Rod end nut	Rolled steel	1	Zinc chromated
35	Magnet	_	(1)	

^{*} Not replaceable.

Replacement Parts: Seal Kit

Bore size (mm)	Kit no.	Contents
40	CV3K40-PS	Set of nos. above
50	CV3K50-PS	23, 24, 25,
63	CV3K63-PS	26, 29, 30

- * Seal kit includes ②, ②, ②, ②, ②, ②. Order the seal kit, based on each bore size.

 (The parts indicated with numbers ② and ⑳ are
- not replaceable.)


 * Seal kit includes a grease pack (ø40, ø50: 10 g,
- ø63 or more: 20 g). Order with the following part number when only

the grease pack is needed.

Grease pack part no.: GR-S-010 (10 g),

rease pack part no.: GR-S-010 (10 g), GR-S-020 (20 g)

Basic Type: CV3KB□



Bore size (mm)	Stroke range* (mm)	Α	AL	В	B ₁	С	D	E	F	H ₁	ı	J	KA	LL	ММ	N	Q	s
40	Up to 500	30	27	60	22	44	16	32	10	8	18	M8 x 1.25	14	86	M14 x 1.5	27	38	84
50	Up to 600	35	32	70	27	52	20	40	10	11	18	M8 x 1.25	18	83	M18 x 1.5	30	43.5	90
63	Up to 600	35	32	85	27	64	20	40	10	11	18	M10 x 1.25	18	83	M18 x 1.5	31	49	98

Bore size	Without	rod boot			٧	Vith roo	d boot	
(mm)	Н	ZZ	d	е	f	h	I	ZZ
40	51	221	56	43	11.2	59	1/4 stroke	229
50	58	231	64	52	11.2	66	1/4 stroke	239
63	63 58 23		64	52	11.2	66	1/4 stroke	247


- * The minimum stroke of the one with rod boot is 20 mm or more.
- ** For dimensions of DIN terminal, refer to page 1225.


External dimensions of each mounting bracket other than basic type are the same, except KA dimension. Refer to pages 1220 to 1225.
 For accessory, refer to page 1225.




CV3 Series Auto Switch Mounting


Auto Switch Proper Mounting Position (Detection at Stroke End) and Its Mounting Height








D-G5□/K59 D-G5□W/K59W D-G59F/G5NT





<Tie-rod mounting type>


D-A9□/A9□V D-Z7□/Z80 D-M9□/M9□V D-Y59□/Y69□/Y7P/Y7PV


D-M9\(\to\)W/M9\(\to\)WV



D-Y7 W/Y7 WV









D-F5□/J59 D-F5NT D-F5□W/J59W D-F59F

D-A44C





Auto Switch Proper Mounting Position (Detection at Stroke End) and Its Mounting Height

Auto Swi	tch P	roper	Mou	nting	Posit	ion												(mm)
Auto switch model	D-M9 D-M9 D-M9 D-M9 D-M9	□V □W □WV	D-A9□ D-A9□V		D-Y59□ D-Y69□ D-Y7P D-Y7PV D-Y7□W D-Y7□WV D-Y7BA D-B59W D-Z7□ D-Z80		D-G39 D-G39C D-K39 D-K39C D-A5□ D-A6□ D-A3□ D-A3□ D-A44 D-A44C		D-G5□ D-K59 D-G5NT D-G5□W D-K59W D-G5BA D-G59F		D-B5□ D-B64		D-F5□ D-J59 D-F59F D-F5□W D-J59W D-F5BA		D-F5NT		D-A59W	
Bore size \	Α	В	Α	В	Α	В	Α	В	Α	В	Α	В	Α	В	Α	В	Α	В
40	10	8	6	4	3.5	1.5	0	0	2	0	0.5	0	6.5	4.5	11.5	9.5	4	2
50	10	8	_	_	3.5	1.5	0	0	2	0	0.5	0	6.5	4.5	11.5	9.5	4	2
63	12.5	11.5	8.5	7.5	6	5	2.5	1.5	4.5	3.5	3	2	9	8	14	13	6.5	5.5
80	16 14 12 10 9.5 7.5 6 4		8	6	6.5	4.5	12.5	10.5	17.5	15.5	10	8						
100			9.5	8.5	8	7	14	13	19	18	11.5	10.5						

Note 1) D-B5□, D-G5□ and D-K5□ types are mountable only upon a receipt of order. (Not mountable after the time of shipment) Note 2) D-A9□ and D-A9□V types cannot be mounted on ø50

Note 3) Adjust the auto switch after confirming the operating conditions in the actual setting.

Auto Sw	tch	Μοι	ıntin	g H	eigh	t															(mm)
Auto switch model	switch model D-M9 D-M9 D-M9 D-M9 D-M9 D-M9		D-M9□V D-M9□WV D-M9□AV		D-A9□V		D-Y59□ D-Y7P D-Y7□W D-Y7BA D-Z7□ D-Z80		D-Y69□ D-Y7PV D-Y7□WV		D-G5 D-K59 D-G5 W D-K59W D-G59F D-G5BA D-G5NT D-B5 D-B64 D-B59W	D-G39 D-K39 D-A3□	D-A44	D-F5 D-J5 D-F5 D-F5 D-F5 D-F5	59 5⊒W 59W 59F 5BA	D-A: D-A: D-A:	6□	D-K	39C 39C 3⊡C	D-A	14C
Bore size \	Hs	Ht	Hs	Ht	Hs	Ht	Hs	Ht	Hs	Ht	Hs	Hs	Hs	Hs	Ht	Hs	Ht	Hs	Ht	Hs	Ht
40	30	30	34	30	31	30	30	30	30	30	37	71.5	81.5	38	31.5	38.5	31.5	73	69	81	69
50	34	34	38	34	_	_	34	34	34	34	42	76.5	86.5	42	35.5	42	35.5	78.5	77	86.5	77
63	41	41	44	41	41.5	41	41	41	41	41	49	83.5	93	47	43	46.5	43	85.5	91	93.5	91
80	49.5	49	52.5	49	50	49	49.5	49	49.5	49	57.5	92	102	53.5	51	53.5	51	94	107	102	107
100	56.5	56	61	56	58.5	56	58.5	55.5	57.5	55.5	68	102.5	112.5	61	57.5	61.5	57.5	104	121	112	121

^{*} D-A9□ and D-A9□V types cannot be mounted on ø50

CV3 Series

Minimum Stroke For Auto Switch Mounting

n: Number of auto switches (mm)

Auto quitob	NI-	of outo quitabas	Mounting brackets			Center trunnion	n. radinber	of auto switches (mm)		
Auto switch model	INC	o. of auto switches mounted	Mounting brackets other than center trunnion	ø 40	ø 50	ø 63	ø 80	ø100		
		Different surfaces, ame surface), 1	15	80		90	105	115		
D-A9□	Г		15 + 40 (n-2)	80 + 40 (n - 4)	1 -	$90 + 40 \frac{(n-4)}{2}$	$105 + 40\frac{(n-4)}{2}$	$115 + 40 \frac{(n-4)}{2}$		
		n		(n = 4, 8, 12, 16···) Note 2)			(n = 4, 8, 12, 16) Note 2)			
		Different surfaces, ame surface), 1	10	80		90	105	115		
D-A9□V		n	10 + 30 (n - 2) (n = 2, 4, 6, 8···) Note 1)	80 + 30 (n - 4) (n = 4, 8, 12, 16···) Note 2)	_	90 + 30 (n - 4) (n = 4 8 12 16) Note 2)	105 + 30 (n - 4) (n = 4, 8, 12, 16···) Note 2)	115 + 30 (n - 4) (n = 4, 8, 12, 16···) Note 2)		
D-M9 □	2 (Sa	Different surfaces, ame surface), 1	15		85	100	120			
D-M9□W D-M9□A	Г	n	15 + 40 (n - 2)	85 + 40		100 + 40 (n - 4)	115 + 40 (n - 4)	120 + 40 (n - 4)		
			(n = 2, 4, 6, 8···) Note 1)	(n = 4, 8, 12	2, 16···) Note 2)	(n = 4, 8, 12, 16···) Note 2)	(n = 4, 8, 12, 16···) Note 2)	(n = 4, 8, 12, 16···) NOTE 2)		
D-M9□V D-M9□WV		Different surfaces, ame surface), 1	10		85	100	115	120		
D-M9□AV		n	10 + 30 (n - 2)) (n - 4) 2	$100 + 30 \frac{(n-4)}{2}$	$115 + 30\frac{(n-4)}{2}$	$120 + 30 \frac{(n-4)}{2}$		
		**	(n = 2, 4, 6, 8···) Note 1)	(n = 4, 8, 12	2, 16···) Note 2)	(n = 4, 8, 12, 16···) Note 2)	(n = 4, 8, 12, 16···) Note 2)	(n = 4, 8, 12, 16···) Note 2)		
D-A5□/A6□ D-F5□/J59		Different surfaces, ime surface), 1	15		90	100	110	120		
D-F5□W/J59W D-F59F	n	(Same surface)	15 + 55 $\frac{(n-2)}{2}$ (n = 2, 4, 6, 8) Note 1)	90 + 55 (n - 4, 8, 13	5 (n - 4) 2, 16···) Note 2)	100 + 55 (n - 4) (n - 4 8 12 16) Note 2)	$110 + 55 \frac{(n-4)}{2}$ (n = 4, 8, 12, 16) Note 2)	120 + 55 (n - 4) (n = 4, 8, 12, 16···) Note 2)		
		(Different surfaces,	20		90	100	110	120		
D-A59W	Н	(Same surface)	20 + 55 (n - 2)	90 + 55		100 + 55 (n - 4)	110 + 55 (n - 4)	120 + 55 (n-4)		
	L	,	(n = 2, 4, 6, 8···) Note 1)		2, 16···) Note 2)		(n = 4, 8, 12, 16···) Note 2)			
		1	15		90	100	110	120		
D-F5NT		Different surfaces, ame surface), 1	25		10	120	130	140		
D-F3N1	n	(Same surface)	$25 + 55 \frac{(n-2)}{2}$ (n = 2, 4, 6, 8) Note 1)		55 (n - 4) 2, 16) Note 2)	120 + 55 (n - 4) (n = 4, 8, 12, 16) Note 2)	$130 + 55 \frac{(n-4)}{2}$ (n = 4, 8, 12, 16) Note 2)	140 + 55 (n - 4) (n = 4, 8, 12, 16) Note 2)		
		Different surfaces	15							
D-B5□/B64	2	Same surface	75		90	100	1	10		
D-G5□/K59		D:#t	$15 + 50 \frac{(n-2)}{2}$	90 + 5	$0\frac{(n-4)}{2}$	$100 + 50 \frac{(n-4)}{2}$	110 + 5	0 (n - 4)		
D-G5□W D-K59W	l _n	Different surfaces	(n = 2, 4, 6, 8) Note 1)		2, 16) Note 2)	(n = 4, 8, 12, 16) Note 2)		, 16) Note 2)		
D-G59F	Ι".	Same surface	75 + 50 (n - 2)	90 + 50) (n – 2)	100 + 50 (n - 2)	100 + 50 (n - 2) 110 + 50			
D-G5NT			(n = 2, 4, 6, 8···)		5, 8···) Note 1)	(n = 2, 4, 6, 8···) Note 1)		, 8···) Note 1)		
	⊢	1	10		90	100	1	10		
	2	Different surfaces Same surface	75		90	100	1.	10		
D Drow	r	Different surfaces	20 + 50 (n-2)		0 (n - 4)	100 + 50 (n - 4)	110 + 5			
D-B59W	n		(n = 2, 4, 6, 8···) Note 1)		2, 16···) Note 2)	(n = 4, 8, 12, 16···) Note 2)		2, 16···) Note 2)		
		Same surface	75 + 50 (n - 2) (n = 2, 3, 4, ···)	90 + 50 (n = 2, 4, 6	0 (n – 2) 5, 8) Note 1)	100 + 50 (n - 2) (n = 2, 4, 6, 8···) Note 1)	(n = 2, 4, 6	0 (n – 2) i, 8) ^{Note 1)}		
		1	15		90	100	1	10		
	2	Different surfaces	35	11	00	100	1:	10		
D-A3□	⊢	Same surface	100 35 + 30 (n – 2)	100 ± 3	0 (n – 2)	100 + 30 (n - 2)	110 ± 3	0 (n – 2)		
D-G39		Different surfaces	(n = 2, 3, 4, ···)		5, 8) Note 1)	(n = 2, 4, 6, 8···) Note 1)		i, 8) Note 1)		
D-K39	n	Same surface	100 + 100 (n - 2) (n = 2, 3, 4, ···)		100 + 100 (n - 2) (n = 2, 4, 6, 8···) Note 1		110 + 10	00 (n – 2) i, 8) Note 1)		
	Г	1	10		00	100		10		
	2	Different surfaces Same surface	35 55		90	100	1	10		
	Г		35 + 30 (n - 2)) (n – 2)	100 + 30 (n - 2)		0 (n – 2)		
D-A44	١.	Different surfaces	(n = 2, 3, 4, ···)	(n = 2, 4, 6	5, 8) Note 1)	(n = 2, 4, 6, 8···) Noté 1)	(n = 2, 4, 6	i, 8) Note 1)		
	Ľ	Same surface	55 + 50 (n - 2) (n = 2, 3, 4, ···)		0 (n – 2) 5, 8···) ^{Note 1)}	100 + 50 (n - 2) (n = 2, 4, 6, 8···) Note 1)	(n = 2, 4, 6	110 + 50 (n - 2) (n = 2, 4, 6, 8···) Note 1)		
		1	10		90	100		10		
loto 1) \Mbon "o" ;			even number that	in and laveau than th	sia add acceptace in co	and for the enlactest.				

Note 1) When "n" is an odd number, an even number that is one larger than this odd number is used for the calculation. Note 2) When "n" is an odd number, a multiple of 4 that is larger than this odd number is used for the calculation.



Minimum Stroke For Auto Switch Mounting

n: Number of auto switches (mm)

Auto switch	No	o. of auto switches	Mounting brackets						
model		mounted	other than center trunnion	ø 40 ø 50		ø 63	ø 80	ø100	
	2	Different surfaces	20	100		100	110		
	Ľ	Same surface	100	10	JU	100	110		
D-A3□C	Different surfaces		20 + 35 (n - 2)	100 + 3	5 (n – 2)	100 + 35 (n - 2)	110 + 35 (n - 2)		
D-G39C		Dillerent surfaces	(n = 2, 3, 4, ···)	(n = 2, 4, 6	i, 8) Note 1)	(n = 2, 4, 6, 8···) Note 1)	(n = 2, 4, 6, 8···) Note 1)		
D-K39C	n	Same surface	100 + 100 (n - 2)		100 + 100 (n - 2)		110 + 10	00 (n – 2)	
		Same surface	(n = 2, 3, 4, 5, ···)		(n = 2, 4, 6, 8···) Note 1)	(n = 2, 4, 6	i, 8···) Note 1)	
		1	10	10	00	100	11	10	
	2	Different surfaces	20		90	100	1:	10	
	Ľ	Same surface	55			100			
	Different surfaces		25 + 35 (n - 2)	90 + 35 (n – 2)		100 + 35 (n - 2)	110 + 35 (n - 2)		
D-A44C		Diliciciii suriuces	(n = 2, 3, 4, ···)	(n = 2, 4, 6, 8···) Note 1)		(n = 2, 4, 6, 8···) Note 1)			
	n	Same surface	55 + 50 (n - 2)	90 + 50 (n - 2)		100 + 35 (n - 2)	110 + 50 (n - 2)		
	_	Same surface	(n = 2, 3, 4, ···)	(n = 2, 4, 6, 8···) Note 1)		(n = 2, 4, 6, 8) Note 1)	(n = 2, 4, 6, 8···) Note 1)		
		1	10	90		100	110		
D-Z7□/Z80		Different surfaces, me surface), 1	15	80	85	90	95	105	
D-Y59□/Y7P D-Y7□W		n	15 + 40 (n-2)	$80 + 40 \frac{(n-4)}{2}$	85 + 40 (n - 4)	$90 + 40\frac{(n-4)}{2}$	95 + 40 (n - 4)	$105 + 40\frac{(n-4)}{2}$	
			(n = 2, 4, 6, 8···) Note 1)	(n = 4, 8, 12, 16···) Note 2)	(n = 4, 8, 12, 16···) Note 2)	(n = 4, 8, 12, 16···) Note 2)	(n = 4, 8, 12, 16···) Note 2)	(n = 4, 8, 12, 16) Note 2)	
D-Y69□/Y7PV	n		10		65	75	80	90	
D-Y7□WV			10 + 30 (n - 2)		$65 + 30 \frac{(n-4)}{2}$		80 + 30 (n - 4)	$90 + 30 \frac{(n-4)}{2}$	
			(n = 2, 4, 6, 8···) Note 1)	(n = 4, 8, 12	2, 16···) Note 2)	(n = 4, 8, 12, 16···) Note 2)	(n = 4, 8, 12, 16···) Note 2)	(n = 4, 8, 12, 16···) Note 2)	

Note 1) When "n" is an odd number, an even number that is one larger than this odd number is used for the calculation.

Note 2) When "n" is an odd number, a multiple of 4 that is larger than this odd number is used for the calculation.

Operating Range


					(mm)			
Auto switch model	Bore size							
Auto switch model	40	50	63	80	100			
D-A9□/A9□V	7	_	9	9	9			
D-M9□/M9□V D-M9□W/M9□WV D-M9□A/M9□AV	4.5	5	5.5	5	6			
D-Z7□/Z80	8	7	9	9.5	10.5			
D-A3□/A44 D-A3□C/A44C D-A5□/A6□	9	10	11	11	11			
D-B5□/B64	ĺ							
D-A59W	13	13	14	14	15			
D-B59W	14	14	17	16	18			
D-Y59□/Y69□ D-Y7P/Y7PV D-Y7□W/Y7□WV	8	7	5.5	6.5	6.5			
D-F5□/J59 D-F5□W/J59W D-F5NT/F59F	4	4	4.5	4.5	4.5			
D-G5□/K59 D-G5□W/K59W D-G5NT/G59F	5	6	6.5	6.5	7			
D-G39/K39 D-G39C/K39C	9	9	10	10	11			

^{*} D-A9 and D-A9 types cannot be mounted on ø50.
* Since this is a guideline including hysteresis, not meant

Auto Switch Mounting Bracket Part No.

<Tie-rod mounting type>

Auto switch model		Boi	re size (m	nm)	
Auto Switch model	40	50	63	80	100
D-M9□/M9□V D-M9□W/M9□WV D-M9□A/M9□AV D-A9□/A9□V	BA7-040	BA7-040	BA7-063	BA7-080	BA7-080
D-F5□/J59 D-F5□W/J59W D-F59F/F5NT D-A5□/A6□ D-A59W	BT-04	BT-04	BT-06	BT-08	BT-08
D-G39C/K39C D-A3□C/A44C	BA3-040	BA3-050	BA3-063	BA3-080	BA3-100
D-Y59□/Y69□ D-Y7P/Y7PV D-Y7□W/Y7□WV D-Y7BA D-Z7□/Z80	BA4-040	BA4-040	BA4-063	BA4-080	BA4-080



 Mounting example of D-M9□(V)/ M9□W(V)/M9□A(V)/A9□(V)

<Band mounting type>

<u> </u>									
Auto switch model	Bore size (mm)								
Auto Switch model	40	50	63	80	100				
D-G39/K39 D-A3□/A44	BD1-04M	BD1-05M	BD1-06M	BD1-08M	BD1-10M				
D-G5□/K59 D-G5□W/K59W D-G59F D-G5NT D-B5□/B64 D-B59W	BA-04	BA-05	BA-06	BA-08	BA-10				

Note) The auto switch mounting bracket is included in the D-A3\(\subseteq C/A44C/G39C/K39C\) types. Specify the part number as follows depending on the cylinder size when ordering. Ex.) \(\text{e}_1\) 0 40: D-A3\(\supseteq C-4\), \(\text{e}_3\) 0: D-A3\(\subseteq C-8\), \(\text{e}_1\) 00: D-A3\(\subseteq C-10\)

Other than the models listed in "How to Order", the following auto switches are applicable. For detailed specifications, refer to pages 1341 to 1435.

Auto switch type	Model	Electrical entry (Fetching direction)	Features
	D-A93V, A96V	Grommet	_
Reed	D-A90V	(Perpendicular)	Without indicator light
need	D-A53, A56, B53, Z73, Z76	Grommet (In-line)	_
	D-A67, Z80	Grommet (m-iine)	Without indicator light
	D-M9NV, M9PV, M9BV		
	D-Y69A, Y69B, Y7PV	0	_
	D-M9NWV, M9PWV, M9BWV	Grommet (Perpendicular)	Diagnostic indication
	D-Y7NWV, Y7PWV, Y7BWV	(Ferperialcular)	(2-color indicator)
Solid state	D-M9NAV, M9PAV, M9BAV		Water resistant (2-color indicator)
Solid State	D-Y59A, Y59B, Y7P		
	D-F59, F5P, J59		_
	D-Y7NW, Y7PW, Y7BW	Grommet (In-line)	Diagnostic indication
	D-F59W, F5PW, J59W		(2-color iindicator)
	D-F5NT, G5NT		With timer

^{*} With pre-wired connector is also available in solid state auto switches.

to be guaranteed. (Assuming approximately ±30% dispersion.)

There may be the case it will vary substantially depending on an ambient environment.

For details, refer to pages 1410 and 1411.


^{*} Normally closed (NC = b contact), solid state auto switches (D-M9□E(V)/Y7G/Y7H type) are also available. For details, refer to pages 1360 and 1362.



Valve Mounted Cylinder Double Acting

CVS1 Series

Ø40, Ø50, Ø63, Ø80, Ø100



* When specifying symbol more than one,

combine symbols alphabetically.

Nil With cushion on both ends Nil Without auto switch

For the applicable auto switch

model, refer to the table below.

* Solid state auto switches marked with "()" are produced upon receipt of order.

** D-B5□/G5□/K5□ types are mountable only upon a receipt of order. (Not

*** D-A9 cannot be mounted on ø50. Select auto switches in brackets

mountable after the time of shipment)

solenoid valve voltage.

Applicable Auto Switches/Refer to pages 1341 to 1435 for further information on auto switch

Гуре	Special function	Electrical	hácatrígit	Wiring	l	_oad volta	age	Auto switch model			wire le			Pre-wired		licable					
i ype	Special fullclion	entry	Páca	(Output)	D	DC AC Tie-ro		Tie-rod mounting	Band mounting	0.5 (Nil) 1 (M) 3 (L) 5 (Z		5 (Z)	connector		load						
				3-wire (NPN)				M9N	_	•	•	•	0	0							
				3-WITE (INFIN)		5 V 40 V	5 V. 12 V	_	G59**	•		•	0	0	IC circuit						
		Grommet		3-wire (PNP)	24 V	J V, 12 V		M9P	_	•	•	•		0	IC CIICUIL						
		Grommer		3-WIIE (FINF)	24 V		_	_	G5P**	•	_	•	0	0							
_				2-wire		12 V		M9B	_	•	•	•	0	0							
Solid state auto switch						12 V		_	K59**	•	_	•	0	0	—						
Š		Terminal		3-wire (NPN)		12 V		G39C	G39	_	_	-	_	_							
ő		conduit		2-wire		12 V		K39C	K39	_	_	-	—								
ä			Υes	Oive (NIDNI)				M9NW	_	•	•	•	0	0		Relay					
ţ.		gnostic indication	dication	n		~	3-wire (NPN)		5 V. 12 V		_	G59W**	•	_	•	0	0	IC circuit	PLC		
sta	Diagnostic indication								3-wire (PNP)		5 V, 12 V		M9PW	_	•	•	•	0	0		
≘∣	(2-color indicator)			24 V		_	_	G5PW**	•	_	•	0	0								
တ			Grommet	Grommet	Grommet	Grommet	Grommet	Grommet		2-wire		12 V		M9BW	_	•	•	•	0	0	
							_	K59W**	•	_	•	0	0								
	Water resistant			3-wire (NPN)	5 V, 12	5 V 12 I	5 V 12 V	5 V, 12 V		M9NA*1	_	0	0	•		0	IC circuit				
	(2-color indicator)			3-wire (PNP)		5 V, 12 V		M9PA*1	_	0	0	•	0	0	IC CIICUIL						
	,			2-wire		12 V		M9BA*1	_	0	0	•	0	0	—						
	With diagnostic output (2-color indicator)			4-wire (NPN)		5 V, 12 V		F59F	G59F**	•	_	•	0	0	IC circuit						
			Yes	3-wire (NPN equivalent)	_	5 V	_	A96 [Z76]***	_	•	_	•	_	_	IC circuit	_					
_			≥					A93 [Z73] ***	_	•	•	•	•		—						
뎔	Grommet 2	೭				100 V or less	A90 [Z80]***	_	•	_	•	_	_	IC circuit	Relay						
S.			No Yes No	1			100 V, 200 V	A54	B54**	•		•	•	_	PLC						
욘	_		ટ	2-wire	24 V	12 V	200 V or less	A64	B64**	•	_	•	—								
Reed auto switch		Terminal		Z-WIIE	2-7 V		_	A33C	A33	-		<u> —</u>	<u> </u>	_		PLC					
8		conduit	S S				100 V 000 V	A34C	A34		<u> </u>	1-	<u> </u>	_	_	Relay					
æ		DIN terminal]≍				100 V, 200 V	A44C	A44	_	-	-	_	_		PLC					
	Diagnostic indication (2-color indicator)	Grommet				_	_	A59W	B59W**	•	_	•	_			1.10					

^{*1} Water resistant type auto switches can be mounted on the above models, but in such case SMC cannot guarantee water resistance. Consult with SMC regarding water resistant types with the above model numbers.
*2 1 m type lead wire is only applicable to D-A93.

without an auto switch is required

(Éxample) CDVS1LN40-100-1

there is no need to enter the symbol for the auto switch

ØSMC

⁽Example) M9NW (Example) M9NWM (Example) M9NWL * Lead wire length symbols: 0.5 m Nil 1 m----- M 3 m----- L 5 m---- Z 5 m...

⁽Example) M9NWZ

^{*}Since there are other applicable auto switches than listed, refer to page 1251 for details.

For details about auto switches with pre-wired connector, refer to pages 1410 and 1411.

PAPI_MBI_MMS_WMMS_A auto switches are shipped together (not assembled). (Only auto switch mounting brackets are assembled before shipped.)

Speed controller installed Operation type can changed to rod extended when energized or rod

selection of solenoid valves is possible.


retracted when energized.

Single, double and 3 position solenoid valves are mountable.

An auto switch cylinder with the switch installed can also be manufactured.



Symbol Air cushion





Made to Order Specifications Click here for details

Symbol	Specifications
-XA□	Change of rod end shape
-XC4	With heavy duty scraper
-XC6	Made of stainless steel
-XC14	Change of trunnion bracket mounting position
-XC15	Change of tie-rod length

Refer to pages 1246 to 1251 for cylinders with auto switches.

- · Proper auto switch mounting position (detection at stroke end) and mounting height
- . Minimum auto switch mounting stroke
- Operating range
- · Auto switch mounting bracket: Part no.

Specifications

Bore size (mm)			40	50	63	80	100			
Fluid			Air							
Action				[Double acting	9				
Proof press	ure				1.5 MPa					
Maximum o	perating	pressure			1.0 MPa					
Ambient an	d fluid te	mperatures		_	-10 to 60°C *	1				
Minimum operating pressure					0.05 MPa					
Piston speed			50 to 500 mm/s *3							
Cushion			Air cushion or Rubber bumper							
Stroke leng	th tolera	nce	Up to 250 st. +1.0 , 251 to 1000 st. +1.4							
Lubrication			Not required (Non-lube)							
Mounting			Basic type, Foot type, Rod side flange type, Head side flange type, Single clevis type, Double clevis type, Center trunnion type							
Port size			Rc 1/4							
Allowable kinetic energy		When activated	2.8	4.6	7.8	16	29			
	Air cushion	When not activated	0.33	0.56	0.91	1.5	2.68			
(J) *2 Rub		er bumper	1.8	3.6	6.0	12.0	12.0			

- *1 No freezing
- *2 Activate the air cushion when operating the cylinder. If this is not done, the piston rod assembly or the tie-rods will be damaged when the allowable kinetic energy exceeds the values shown in the above table.
- *3 For operating piston speed for each size, refer to page 1240.

Solenoid Valve Specifications

Colonela vario opocinicationo									
Applicable solenoid va	VS4□24								
Coil rated voltage	Coil rated voltage			Refer to the solenoid valve voltage shown below.					
Electrical entry	Grommet, C	Grommet, Conduit terminal, DIN terminal, DIN terminal with indicator light, Conduit terminal with surge voltage suppressor							
Allowable voltage		-15 to 10% of the rated voltage							
Coil insulation		Class B or equivalent (130°C)							
		Inrush	50 Hz	100 VA					
Ammanant manuar Note)	AC		60 Hz	90 VA					
Apparent power Note)	AC	Holding	50 Hz	20 VA					
		Holding	60 Hz	14 VA					
Power consumption Note)	13.2 W								

Note) At the rated voltage.

Solenoid valve voltage

1	100 VAC (50/60 Hz)
2	200 VAC (50/60 Hz)
3	110 VAC (50/60 Hz)
4	220 VAC (50/60 Hz)
5	24 VDC
6	12 VDC
В	24 VAC (50/60 Hz)
Р	100 VDC
W	32 VDC
Υ	48 VDC
Z	110 VDC

For other rated voltages. please contact SMC

Standard Strokes

(mm)

		(
Bore size	Standard stroke	
DOI C SIZE	Stroke range ①	Stroke range ②
40	25, 50, 75, 100, 125, 150, 200, 250, 300, 350, 400, 450, 500	
50, 63	25, 50, 75, 100, 125, 150, 200, 250, 300, 350, 400, 450, 500, 600	Up to 1000
80, 100	25, 50, 75, 100, 125, 150, 200, 250, 300, 350, 400, 450, 500, 600, 700	

- Note 1) Intermediate strokes not listed above are produced upon receipt of order.
- Note 2) Applicable strokes should be confirmed according to the usage. For details, refer to "Air Cylinders Model Selection" in the Web Catalog. In addition, the products that exceed the stroke range ① might not be able to fulfill the specifications due to the deflection etc.
- Note 3) Please consult with SMC for manufacturability and the part numbers when exceeding the stroke range 2.
- Note 4) The minimum stroke length is different in the trunnion type and types with auto switch. Refer to pages 1248

Rod Boot Material

Symbol	Rod boot material	Max. ambient temperature
J	Nylon tarpaulin	70°C
K	Heat resistant tarpaulin	110°C*

* Maximum ambient temperature for the rod boot itself.



CVS1 Series

Accessory

	Mounting	Basic type	Axial foot type	Rod side flange type	Head side flange type	Single clevis type	Double* clevis type	Center trunnion type
Standard	Rod end nut	•	•	•	•	•	•	•
equipment	Clevis pin	_	_	_	-	-	•	_
	Single knuckle joint	•	•	•	•	•	•	•
Option	Double knuckle joint * (with pin)	•	•	•	•	•	•	•
	With rod boot	•	•	•	•	•	•	•

- * Pin, plain washer and cotter pin are packaged together with double clevis and double knuckle joint.
- Refer to page 1245 for dimensions and part numbers of the option. Refer to page 1242 for dimensions of the rod boot.

Weight						(kg)
	Bore size (mm)	40	50	63	80	100
	Basic type	2.32(2.42)	2.73(2.86)	3.67(3.88)	5.25(5.56)	6.81(7.21)
	Axial foot type	2.49(2.59)	2.93(3.06)	3.96(4.17)	6.04(6.35)	7.74(8.14)
Doolo	Rod side flange type	2.72(2.82)	3.33(3.46)	4.63(4.84)	7.09(7.40)	9.13(9.53)
Basic weight	Head side flange type	2.82(2.92)	3.47(3.60)	4.63(4.84)	7.09(7.40)	9.13(9.53)
g	Single clevis type	2.58(2.68)	3.17(3.30)	4.42(4.63)	6.63(6.94)	9.11(9.51)
	Double clevis type	2.57(2.67)	3.15(3.28)	4.44(4.65)	6.62(6.93)	9.13(9.53)
	Trunnion type	2.92(3.07)	3.47(3.66)	5.01(5.38)	7.58(8.03)	10.33(10.92)
Additional we	ight per each 50 mm of stroke	0.20(0.28)	0.25(0.35)	0.31(0.43)	0.46(0.70)	0.58(0.87)
Accessory	Single knuckle	0.23	0.26	0.26	0.60	0.83
bracket	Double knuckle (with pin)	0.37	0.43	0.43	0.87	1.27

Calculation: (Example) CVS1L40-100-1

-2.48 (kg) Basic weight------


Mounting Bracket Part No.

Bore size (mm)	40	50	63	80	100
Axial foot *	CA1-L04	CA1-L05	CA1-L06	CA1-L08	CA1-L10
Flange	CA1-F04	CA1-F05	CA1-F06	CA1-F08	CA1-F10
Single clevis	CA1-C04	CA1-C05	CA1-C06	CA1-C08	CA1-C10
Double clevis **	CA1-D04	CA1-D05	CA1-D06	CA1-D08	CA1-D10

- * Order two foot brackets per cylinder.
- ** Accessories for each mounting bracket are as follows. Foot, Flange, Single clevis: Body mounting bolts, Spring washer

Double clevis: Body mounting bolts, Spring washer, Clevis pin, Flat washer, Cotter pin.

Opening Range of Throttle Valve and Piston Speed




Conditions: Operating pressure 0.5 MPa,

- Horizontal mounting, No load, Extending stroke
- . The speed shown above are for reference.


Piston Speed Adjustment Procedure

- 1. To slow down the piston speed, screw in the speed controller needle clockwise, which reduces the amount of air that is discharged.
- 2. The speed controller needle opens fully when it is loosened 3 1/2 turns from its fully closed position. After the specified speed has been set, secure the needle with the lock nut.




Changing between Rod Extended when Energized and Rod Retracted when Energized

1. This is possible by reversing the SUP port and EXH port piping.



2. This is possible by inverting the solenoid valve direction 180



Manual Operation


Using a screwdriver or its equivalent, push the center of the rubber plug on the head of the solenoid cap of the solenoid valve.

(It is not necessary to remove the rubber plug.)



* (): Steel tube type

Construction



Component Parts

No.	Description	Material	Q'ty	Note
1	Rod cover	Aluminum die-casted	1	Black painted
2	Head cover	Aluminum alloy	1	Black painted
3	Cylinder tube	Aluminum alloy	1	Hard anodized
4	Piston rod	Carbon steel	1	Hard chrome plating
5	Piston	Aluminum alloy	1	
6	Cushion ring A	Aluminum alloy	1	Anodized
7	Cushion ring B	Aluminum alloy	1	Anodized
8*	Bushing	Bearing alloy	1	
9	Cushion valve	Steel wire	2	Trivalent zinc chromated
10	Retaining ring	Spring steel	2	Phosphate coating
11	Tie-rod	Carbon steel	4	Trivalent zinc chromated
12	Tie-rod nut	Rolled steel	8	Trivalent black zinc chromated
13	Spring washer	Steel wire	8	Trivalent black zinc chromated
14	Pipe	Carbon steel tube	1	Trivalent zinc chromated
15	Sub-plate	Aluminum die-casted	1	Platinum silver
16*	Guide tube fitting	Aluminum die-casted	1	Platinum silver
17*	Valve port	Rolled steel	2	Electroless nickel plating
18*	Check spring	Spring steel	2	Trivalent zinc chromated

Note) Add "-X46" to the end of the part numbers for single solenoid type.

			_	
No.	Description	Material	Q'ty	Note
19*	Check ball	Polyurethane rubber	2	Ball 9/32
20	Hex. socket head cap screw with SW	Chromium molybdenum steel	4	Trivalent zinc chromated
21	Needle guide	Carbon steel	2	Trivalent zinc chromated
22	Speed adjustment needle	Rolled steel	2	Electroless nickel plating
23	Lock nut	Carbon steel	2	Trivalent zinc chromated
24	Wear ring	Resin	1	
25	Rod seal	NBR	1	
26	Piston seal	NBR	1	
27*	Cushion seal	Urethane	2	
28	Cylinder tube gasket	NBR	2	
29*	Cushion valve seal	NBR	2	
30	Pipe gasket	NBR	2	
31	Gasket	NBR	1	
32	Speed adjustment needle seal	NBR	2	
33	Valve port gasket	NBR	4	
34	Magnet	_	(1)	
35	Rod end nut	Rolled steel	1	Trivalent zinc chromated
36	Solenoid valve	_	1	VS4124-00□-X46

Replacement Parts: Seal Kit

Bore size (mm)	Kit no.	Contents
40	CVS1N40-PS	
50	CVS1N50-PS	Set of nos. above
63	CVS1N63-PS	25, 26, 28, 30, 33
80	CVS1N80-PS	20, 20, 20, 30, 30
100	CVS1N100-PS	

^{*} Seal kit includes 🖄, 🚳, 🦓, ③, and ③. Order the seal kit based on each bore size. (The parts indicated with numbers ② and ③ are not replaceable.)

Grease pack part no.: GR-S-010 (10 g), GR-S-020 (20 g)


How to order solenoid valves/VS4□24-00 Voltage Electrical entry

^{*} Not replaceable.

^{*} Seal kit includes a grease pack (ø40, ø50: 10 g, ø63, ø80: 20 g, ø100: 30 g). Order with the following part number when only the grease pack is needed.

CVS1 Series

Basic Type: CVS1B




	(mm)	(mm)	Α	AL	В	Вı	С	D	E	F	H ₁	нх	J	K	KA	M	MM	N	S
Ξ	40	Up to 1000	30	27	60	22	44	16	32	10	8	150	M8 x 1.25	6	14	19.4	M14 x 1.5	27	130.6
	50	Up to 1000	35	32	70	27	52	20	40	10	11	160	M8 x 1.25	7	18	16.4	M18 x 1.5	30	133.6
Ξ	63	Up to 1000	35	32	85	27	64	20	40	10	11	175	M10 x 1.25	7	18	18.4	M18 x 1.5	31	140.6
	80	Up to 1000	40	37	102	32	78	25	52	14	13	192	M12 x 1.75	10	22	21.4	M22 x 1.5	37	152.6
Ξ	100	Up to 1000	40	37	116	41	92	30	52	14	16	206	M12 x 1.75	10	26	21.4	M26 x 1.5	40	159.6

Bore size	w	Without	rod boot	With rod boot									
(mm)	VV	Н	ZZ	d	е	f	h	l	ZZ				
40	8	51 201		56	43	11.2	59	1/4 stroke	209				
50	8	58 20		64	52	11.2	66	1/4 stroke	216				
63	8	8	8	58	217	64	52	11.2	66	1/4 stroke	225		
80	0	71 245 76 65		65	12.5	80	1/4 stroke	254					
100	0	72	253	76	65	14	81	1/4 stroke	262				

^{*} The minimum stroke of the one with rod boot is 20 mm or more.

Axial Foot Type: CVS1L




Bore size	Stroke* range (mm)	Α	AL	В	Вı	С	D	E	F	H ₁	J	K	KA	LD	LH	LS	LT	LX	LZ	ММ
40	Up to 1000	30	27	60	22	44	16	32	10	8	M8 x 1.25	6	14	9	40	184.6	3.2	42	160	M14 x 1.5
50	Up to 1000	35	32	70	27	52	20	40	10	11	M8 x 1.25	7	18	9	45	187.6	3.2	50	170	M18 x 1.5
63	Up to 1000	35	32	85	27	64	20	40	10	11	M10 x 1.25	7	18	11.5	50	208.6	3.2	59	182	M18 x 1.5
80	Up to 1000	40	37	102	32	78	25	52	14	13	M12 x 1.75	10	22	13.5	65	240.6	4.5	76	206	M22 x 1.5
100	Up to 1000	40	37	116	41	92	30	52	14	16	M12 x 1.75	10	26	13.5	75	245.6	6	92	223	M26 x 1.5
	Op 10 1000	70	0,	110	71	32	_ 50	_ JZ_	14	10	W112 X 1.70	10	20	10.0	/3	245.0		32	223	1VIZU X 1.5

Bore size	N	s	w	х	v	Without	rod boot	With rod boot							
(mm)	14	3	> W A		1	Н	ZZ	d	е	f	h	l	ZZ		
40	27	130.6	8	27	13	51	221.6	56	43	11.2	59	1/4 stroke	229.6	2	
50	30	133.6	8	27	13	58	231.6	64	52	11.2	66	1/4 stroke	239.6		
63	31	140.6	8	34	16	58	248.6	64	52	11.2	66	1/4 stroke	256.6		
80	37	152.6	0	44	16	71	283.6	76	65	12.5	80	1/4 stroke	292.6		
100	40	159.6	0	43	17	72	291.6	76	65	14	81	1/4 stroke	300.6		

^{*} The minimum stroke of the one with rod boot is 20 mm or more. ** Long stroke

Rod Side Flange Type: CVS1F




Bore size	ММ	N	s	w	Without	rod boot			W	/ith rod			
(mm)	(11111)		3	vv	Н	ZZ	d**	е	f	h	e	ZZ	
40	M14 x 1.5	27	130.6	8	51	201	52	43	15	59	1/4 stroke	209	
50	M18 x 1.5	30	133.6	8	58	208	58	52	15	66	1/4 stroke	216	
63	M18 x 1.5	31	140.6	8	58	217	58	52	17.5	66	1/4 stroke	225	
80	M22 x 1.5	37	152.6	0	71	245	80	65	21.5	80	1/4 stroke	254	
100	M26 x 1.5	40	159.6	0	72	253	80	65	21.5	81	1/4 stroke	262	

- * The minimum stroke of the one with rod boot is 20 mm or more.
- ** Long stroke

 *** Machine larger holes than the outside diameter ød of the mounting bracket for rod
 boot when mounting the rod boot part to

the through for mounting.

Head Side Flange Type: CVS1G




Bore size	1/ 4			_	147	Without rod boot			With rod boot						
(mm)	KA	MM	N	S	W	Н	ZZ	d	е	f	h	e	ZZ		
40	14	M14 x 1.5	27	130.6	8	51	197.6	56	43	11.2	59	1/4 stroke	205.6		
50	18	M18 x 1.5	30	133.6	8	58	207.6	64	52	11.2	66	1/4 stroke	215.6		
63	18	M18 x 1.5	31	140.6	8	58	213.6	64	52	11.2	66	1/4 stroke	221.6		
80	22	M22 x 1.5	37	152.6	0	71	241.6	76	65	12.5	80	1/4 stroke	250.6		
100	26	M26 x 1.5	40	159.6	0	72	249.6	76	65	14	81	1/4 stroke	258.6		

^{*} The minimum stroke of the one with rod boot is 20 mm or more.

CVS1 Series

Single Clevis Type: CVS1C



25 **Double Clevis Type: CVS1D**

159 6 36 0 71 271.6 291.6 76 65 12.5 80


0 72

80

100

37 20 152.6

40



76

65 14 81

289 6 314 6

1/4 stroke

1/4 stroke

280.6 300.6

298.6 323.6

Bore size (mm)	Stroke* range (mm)	Α	AL	В	B ₁	С	СДн10	сх	cz	D	E	F	H ₁	нх	J	к	KA	L
40	Up to 1000	30	27	60	22	44	10 + 0.058	15+0.3	29.5	16	32	10	8	150	M8 x 1.25	6	14	30
50	Up to 1000	35	32	70	27	52	12 + 0.070	18+0.3	38	20	40	10	11	160	M8 x 1.25	7	18	35
63	Up to 1000	35	32	85	27	64	16 + 0.070	25+0.3	49	20	40	10	11	175	M10 x 1.25	7	18	40
80	Up to 1000	40	37	102	32	78	20 + 0.084	31.5 + 0.3	61	25	52	14	13	192	M12 x 1.75	10	22	48
100	Up to 1000	40	37	116	41	92	25 + 0.084	35.5 + 0.3	64	30	52	14	16	206	M12 x 1.75	10	26	58


Bore size	BABA	N	DD.	- C	U	w	vvitn	out roc	1 DOOT				vvitn	roa boot		
(mm)	MM	IN	RR	>	U	W	Н	Z	ZZ	d	е	f	h	e	Z	ZZ
40	M14 x 1.5	27	10	130.6	16	8	51	211.6	221.6	56	43	11.2	59	1/4 stroke	219.5	229.6
50	M18 x 1.5	30	12	133.6	19	8	58	226.6	238.6	64	52	11.2	66	1/4 stroke	234.6	246.6
63	M18 x 1.5	31	16	140.6	23	8	58	238.6	254.6	64	52	11.2	66	1/4 stroke	246.6	262.6
80	M22 x 1.5	37	20	152.6	28	0	71	271.6	291.6	76	65	12.5	80	1/4 stroke	280.6	300.6
100	M26 x 1.5	40	25	159.6	36	0	72	289.6	314.6	76	65	14	81	1/4 stroke	298.6	323.6

^{*} The minimum stroke of the one with rod boot is 20 mm or more.

^{*} Clevis pin, flat washer and cotter pin are shipped together.

¹²⁴⁴

Center Trunnion Type: CVS1T



Bore size (mm)	Stroke* range (mm)	A	AL	В	Вı	С	D	E	F	Нı	нх	J	K	KA	М	ММ	N	s	TDe8
40	Up to 1000	30	27	60	22	44	16	32	10	8	150	M8 x 1.25	6	14	11.4	M14 x 1.5	27	130.6	15 -0.032
50	Up to 1000	35	32	70	27	52	20	40	10	11	160	M8 x 1.25	7	18	11.4	M18 x 1.5	30	133.6	15 -0.032
63	Up to 1000	35	32	85	27	64	20	40	10	11	175	M10 x 1.25	7	18	13.4	M18 x 1.5	31	140.6	18 -0.032
80	Up to 1000	40	37	102	32	78	25	52	14	13	192	M12 x 1.75	10	22	18.4	M22 x 1.5	37	152.6	25 -0.040
100	Up to 1000	40	37	116	41	92	30	52	14	16	206	M12 x 1.75	10	26	16.4	M26 x 1.5	40	159.6	25 -0.040


Dule Size	TT	TV	TV	TTT	34/	******	out roc	DOOL				*****	1100 0001			*
(mm)	11	1^	11	12	W	Н	Z	ZZ	d	е	f	h	l	Z	ZZ	,
40	22	85	62	117	8	51	93	193	56	43	11.2	59	1/4 stroke	101	201	
50	22	95	74	127	8	58	103	203	64	52	11.2	66	1/4 stroke	111	211	
63	28	110	90	148	8	58	107	212	64	52	11.2	66	1/4 stroke	115	220	
80	34	140	110	192	0	71	129	242	76	65	12.5	80	1/4 stroke	138	251	
100	40	162	130	214	0	72	135	248	76	65	14	81	1/4 stroke	144	257	

Without rod boot

The minimum stroke of the one with rod boot is 20 mm or more.

Accessory Dimensions

I Type Single Knuckle Joint



		ag	, ounc	0.0.						(
Part no.	Applicable bore size (mm)	A	A 1	øE1	L ₁	ММ	Rı	U₁	ø ND н10	NX
I-04	40	69	22	24	55	M14 x 1.5	15.5	20	12+0.070	16 -0.1
I-05	50, 63	74	27	28	60	M18 x 1.5	15.5	20	12+0.070	
I-08	80	91	37	36	71	M22 x 1.5	22.5	26	18+0.070	28 -0.1
I-10	100	105	37	40	83	M26 x 1.5	24.5	28	20 + 0.084	30 -0.1

Knuckle Pin, Clevis Pin




Material: C	Carbon ste	el						(mm)
Part no.	Applicable by	re size (mm)	øDd9	L	e	m	ød	Applicable
raitiio.	Clevis	Knuckle	bDu3	-	١,	l ''''	(Drill through)	cotter pin
CDP-2A	40		10-0.046	46	38	4	3	ø3 x 18ℓ
CDP-3A	50	40, 50, 63	12-0.050	55.5	47.5	4	3	ø3 x 18 ℓ
CDP-4A	63	_	16-0.050	71	61	5	4	ø4 x 25 ℓ
CDP-5A	_	80	18-0.050	76.5	66.5	5	4	ø4 x 25 ℓ
CDP-6A	80	100	20-0.065	83	73	5	4	ø4 x 30 ℓ
CDP-7A	100		25-0.065	88	78	6	4	ø4 x 36 ℓ

^{*} Cotter pin and plain washer are shipped together.

Y Type Double Knuckle Joint

 Knuckle pin, cotter pin and plain washer are shipped together.

With rod boot



Materi	al: Cast	iro	n							_			(mm)
Part no.	Applicable bore size (mm)	Αı	Εı	Lı	ММ	RR1	U₁	ND	NX	ΝZ	L	Cotter pin size	flat washer size
Y-04D	40	22	24	55	M14 x 1.5	13	25	12	16+0.3	38	55.5	ø3 x 18 L	Polished round 12
Y-05D	50, 63	27	28	60	M18 x 1.5	15	27	12	16+0.3	38	55.5	ø3 x 18 L	Polished round 12
Y-08D	80	37	36	71	M22 x 1.5	19	28	18	28 +0.3	55	76.5	ø4 x 25 L	Polished round 18
Y-10D	100	37	40	83	M26 x 1.5	21	38	20	30 +0.3	61	83	ø4 x 30 L	Polished round 20

Rod End Nut




į	Material: Ro	lled steel	H -	_ В	_
	Part no.	Applicable bore size (mm)	d	Н	В
	NT-04	40	M14 x 1.5	8	22

Part no.	bore size (mm)	a	п	P	١	D
NT-04	40	M14 x 1.5	8	22	25.4	21
NT-05	50, 63	M18 x 1.5	11	27	31.2	26
NT-08	80	M22 x 1.5	13	32	37	31
NT-10	100	M26 x 1.5	16	41	47.3	39

CVS1 Series Auto Switch Mounting

Auto Switch Proper Mounting Position (Detection at Stroke End) and Mounting Height



Auto Switch Proper Mounting position (Detection at Stroke End) and Mounting Height

Auto S	witch	Prop	er Mo	untin	g Pos	ition	(Stan	dard t	ype)									(mm)
Auto switch model	D-M9 D-M9 D-M9 D-M9 D-M9 D-M9	□V □W □WV □□A	D-A D-A		D-Y5 D-Y6 D-Y7 D-Y7 D-Y7 D-Y7 D-Z7 D-Z8 D-B5	9□ P PV □W □WV BA	D-F5 D-J5 D-F5 D-J5 D-F5	59 59F 5⊒W 59W	D-F	5NT	D-A	59W	D-G: D-K: D-K: D-A: D-A: D-A: D-A: D-A:	39C 39 39C 5□ 6□ 3□ 3□C	D-G! D-K! D-G! D-G! D-G! D-G!	59 5NT 5□W 59W 5BA	D-B D-B	
Bore size \	Α	В	Α	В	Α	В	Α	В	Α	В	Α	В	Α	В	Α	В	Α	В
40	9	9	5	5	2.5	2.5	5.5	5.5	10.5	10.5	3	3	0	0	1	1	0	0
50	9.5	8.5	5.5	4.5	3	2	6	5	11	10	3.5	2.5	0	0	1.5	0.5	0	0
63	12.5	11.5	8.5	7.5	6	5	9	8	14	13	6.5	5.5	2.5	1.5	4.5	3.5	3	2
80	16.5	13.5	12.5	9.5	10	7	13	10	18	15	10.5	7.5	6.5	3.5	8.5	5.5	7	4
100	18	16	14	12	11.5	9.5	14.5	12.5	19.5	17.5	12	10	8	6	10	8	8.5	6.5

Note 1) D-B5□ type, D-G5□ type, D-K5□ type are mountable only upon a receipt of order. (Not mountable after the time of shipment)
Note 2) Adjust the auto switch after confirming the operating conditions in the actual setting.

Auto Switch Mounting Height (Standard type)

•	auto o	WILC		Juiit	y	ı iciy	יו זייין	Juan	uait	a typ	,,,											(111111)
	Auto switch model	D-M9 D-M9 D-M9 D-A9	D□W D□A	D-M9 D-M9 D-M9	□wv	D-A	9□V	D-Y5 D-Y7 D-Y7 D-Y7 D-Z5	7P 7BA 7□W	D-Y6 D-Y7 D-Y7	PV	D-G5 D-K59 D-G5NT D-G5 DW D-K59W D-G5BA D-G59F D-B5 D-B64 D-B59W	D-G39 D-K39 D-A3□	D-A44	D-F5 D-J5 D-F5 D-F5 D-F5	9 i⊟W i9W iBA i9F	D-A D-A D-A	6□	D-G3 D-K3 D-A3	39C	D-A	14C
	Bore size \	Hs	Ht	Hs	Ht	Hs	Ht	Hs	Ht	Hs	Ht	Hs	Hs	Hs	Hs	Ht	Hs	Ht	Hs	Ht	Hs	Ht
	40	30	30	34	30	31	30	30	30	30	30	37	71.5	81.5	38	31.5	38.5	31.5	73	69	81	69
ſ	50	34	34	38	34	35	34	34	34	34	34	42	76.5	86.5	42	35.5	42	35.5	78.5	77	86.5	77
	63	41	41	44	41	41.5	41	41	41	41	41	49	83.5	93.5	47	43	46.5	43	85.5	91	93.5	91
	80	49.5	49	52.5	49	50	49	49.5	49	49.5	49	57.5	92	102	53.5	51	53.5	51	94	107	102	107
ſ	100	56.5	56	61	56	58.5	56	56.5	55.5	57.5	55.5	68	102.5	112.5	61	57.5	61.5	57.5	104	121	112	121

(mm)

CVS1 Series

Minimum Stroke for Auto Switch Mounting (Standard Type)

	n:	Number	of	auto	switches	(mm	١
--	----	--------	----	------	----------	-----	---

Auto switch	Number of	Brackets other than			Center trunnion		r auto switches (mm)
model	auto switches	center trunnion	ø 40	ø 50	ø 63	ø 80	ø100
	2 (Different surfaces and same surface) 1	15		30	85	90	95
D-M9□ D-M9□W	n	15 + 40 (n - 2) (n = 2, 4, 6, 8···) Note 1)	80 + 40 (n = 4, 8, 12		85 + 40 (n - 4) (n = 4, 8, 12, 16···) Note 2)	$90 + 40 \frac{(n-4)}{2}$ (n = 4, 8, 12, 16) Note 2)	
D MODV	2 (Different surfaces and same surface) 1	10	5	55	60	65	70
D-M9□V D-M9□WV	n	$10 + 30 \frac{(n-2)}{2}$ (n = 2, 4, 6, 8) Note 1)	55 + 30 (n = 4, 8, 12		60 + 30 (n - 4) 2 Note 2)	65 + 30 (n - 4) (n = 4, 8, 12, 16···) Note 2)	70 + 30 (n - 4) (n - 4 8 12 16) Note 2)
	2 (Different surfaces and same surface) 1	15		30	85	95	100
D-M9□A	n	15 + 40 (n - 2) (n = 2, 4, 6, 8···) Note 1)	80 + 40 (n = 4, 8, 12	~	85 + 40 (n - 4) (n = 4, 8, 12, 16) Note 2)	95 + 40 (n - 4) (n = 4, 8, 12, 16···) Note 2)	100 + 40 (n - 4) (n = 4, 8, 12, 16) Note 2)
	2 (Different surfaces and same surface) 1	10		60	65	70	75
D-M9□AV	n	$10 + 30 \frac{(n-2)}{2}$ (n = 2, 4, 6, 8) Note 1)	60 + 30 (n = 4, 8, 12		65 + 30 (n - 4) (n = 4, 8, 12, 16···) Note 2)	70 + 30 (n - 4) (n = 4, 8, 12, 16···) Note 2)	75 + 30 (n - 4) (n = 4, 8, 12, 16···) Note 2)
	2 (Different surfaces and same surface) 1	15		75	80	85	90
D-A9□	n	15 + 40 (n - 2) (n = 2, 4, 6, 8···) Note 1)	75 + 40 (n = 4, 8, 12		80 + 40 (n - 4) (n = 4, 8, 12, 16) Note 2)	85 + 40 (n - 4) (n = 4, 8, 12, 16···) Note 2)	90 + 40 (n - 4) (n = 4, 8, 12, 16) Note 2)
	2 (Different surfaces and same surface) 1	10		60	55	60	65
D-A9□V	n	10 + 30 (n - 2) (n = 2, 4, 6, 8···) Note 1)	50 + 30 (n = 4, 8, 12		55 + 30 (n - 4) (n = 4, 8, 12, 16···) Note 2)	60 + 30 (n - 4) (n = 4, 8, 12, 16···) Note 2)	65 + 30 (n - 4) (n = 4, 8, 12, 16···) Note 2)
D-F5□/J59 D-F5□W/J59W	2 (Different surfaces and same surface) 1	15		00	100	110	120
D-F5BA/F59F D-A5□/A6	n (Same surface)	15 + 55 (n - 2) (n = 2, 4, 6, 8···) Note 1)	90 + 55 (n = 4, 8, 12		100 + 55 (n - 4) (n = 4, 8, 12, 16···) Note 2)	110 + 55 $\frac{(n-4)}{2}$ (n = 4, 8, 12, 16···) Note 2)	$120 + 55 \frac{(n-4)}{2}$ (n = 4, 8, 12, 16) Note 2)
	2 (Different surfaces and same surface) 1	25	11	0	120	130	140
D-F5NT	n (Same surface)	25 + 55 (n - 2) (n = 2, 4, 6, 8···) Note 1)	110 + 5 (n = 4, 8, 12		120 + 55 (n - 4) (n = 4, 8, 12, 16···) Note 2)	130 + 55 (n - 4) (n = 4, 8, 12, 16···) Note 2)	
	2 (Different surfaces and same surface) 1	20	g	00	100	110	120
D-A59W	n (Same surface)	$20 + 55 \frac{(n-2)}{2}$ $(n = 2, 4, 6, 8 \cdot \cdot \cdot)$ Note 1)	90 + 55 (n = 4, 8, 12		100 + 55 (n - 4) (n = 4, 8, 12, 16···) Note 2)	110 + 55 $\frac{(n-4)}{2}$ (n = 4, 8, 12, 16···) Note 2)	$120 + 55 \frac{(n-4)}{2}$ (n = 4, 8, 12, 16···) Note 2)
	1	15	g	0	100	110	120
D-G5□/K59 D-G5□W	2 Different surfaces Same surface	15 75		00	100	1	
D-K59W D-G5BA	Different surfaces	15 + 50 (n - 2) (n = 2, 4, 6, 8···) Note 1)	90 + 50 (n = 4, 8, 12		100 + 50 (n - 4) (n = 4, 8, 12, 16···) Note 2)	110 + 5 (n = 4, 8, 12	
D-G59F D-G5NT D-B5□/B64	Same surface	75 + 50 (n - 2) (n = 2, 3, 4···)	90 + 50 (n = 2, 4, 6	(n – 2)	100 + 50 (n - 2) (n = 2, 4, 6, 8···) Note 1)		0 (n – 2)
D-D3L/D04	1	10	9	0	100	1	10
	2 Different surfaces Same surface	20 75	g	00	100	1	10
D-B59W	Different surfaces	20 + 50 (n - 2) (n = 2, 4, 6, 8···) Note 1)	90 + 50 (n = 4, 8, 12		100 + 50 (n - 4) (n = 4, 8, 12, 16···) Note 2)	110 + 5 (n = 4, 8, 12	-
	Same surface	75 + 50 (n - 2) (n = 2, 3, 4···)	90 + 50 (n = 2, 4, 6	(n – 2)	100 + 50 (n - 2) (n = 2, 4, 6, 8···) Note 1)		0 (n – 2)
Note 1) When "n" is	1	15		00	100	1	

Note 1) When "n" is an odd number, an even number that is one larger than this odd number is used for the calculation. Note 2) When "n" is an odd number, a multiple of 4 that is larger than this odd number is used for the calculation.

Minimum Stroke for Auto Switch Mounting (Standard Type)

							n: Number o	f auto switches (mm)	
Auto switch		Number of	Brackets other than			Center trunnion			
model		auto switches	center trunnion	ø 40	ø 50	ø 63	ø 80	ø100	
	2	Different surfaces	35		75	80		90	
	Ľ	Same surface	100	1	00	100	1	00	
D-G39 D-K39		Different surfaces	35 + 30 (n - 2)	75 + 30 (n - 2)		80 + 30 (n - 2)	90 + 30 (n - 2)		
	l_	Dilleterit Suriaces	(n = 2, 3, 4···)	4···) (n = 2, 4, 6, 8···) Note 1) (n =		(n = 2, 4, 6, 8···) Note 1)	(n = 2, 4, 6	, 8) Note 1)	
D-A3□	n	Same surface	100 + 100 (n - 2)			100 + 100 (n - 2)			
		Same surface	(n = 2, 3, 4···)			n = 2, 4, 6, 8···) Note 1)			
		1	10		75	80		90	
	2	Different surfaces	35		75	80		90	
	_ ا	Same surface	55		75	80		90	
		D.//	35 + 30 (n - 2)	75 + 30) (n – 2)	80 + 30 (n - 2)	90 + 30	(n – 2)	
D-A44	l _	Different surfaces	(n = 2, 3, 4···)	(n = 2, 4, 6	i, 8) Note 1)	(n = 2, 4, 6, 8···) Note 1)	(n = 2, 4, 6	, 8) Note 1)	
	n		55 + 50 (n - 2)	75 + 50) (n – 2)	80 + 50 (n - 2)	90 + 50	(n – 2)	
		Same surface	(n = 2, 3, 4···)	(n = 2, 4, 6	i, 8) Note 1)	(n = 2, 4, 6, 8···) Note 1)	(n = 2, 4, 6	, 8) Note 1)	
	П	1	10		75	80		90	
	_	Different surfaces	20		75	80		90	
	2	Same surface	100	1	00	100	100		
D-G39C		D.//	20 + 35 (n - 2)	75 + 35 (n - 2)		80 + 35 (n - 2)	90 + 35 (n - 2)		
D-K39C		Different surfaces	(n = 2, 3, 4···)	(n = 2, 4, 6, 8···) Note 1)		(n = 2, 4, 6, 8) Note 1)	Note 1) (n = 2, 4, 6, 8···) Note 1)		
D-A3□C	n		100 + 100 (n - 2)			100 + 100 (n - 2)			
		Same surface	(n = 2, 3, 4, 5···)			(n = 2, 4, 6, 8···) Note 1	n = 2, 4, 6, 8···) Note 1)		
	Г	1	10			80	90		
	_	Different surfaces	20	75				00	
	2	Same surface	55		/5	80		90	
		D.//	20 + 35 (n - 2)	75 + 35 (n - 2)		80 + 35 (n - 2)	90 + 35 (n - 2)		
D-A44C		Different surfaces	(n = 2, 3, 4···)	(n = 2, 4, 6, 8···) Note 1)		(n = 2, 4, 6, 8) Note 1)			
	n		55 + 50 (n - 2)	75 + 50) (n – 2)	80 + 50 (n - 2)	90 + 50) (n – 2)	
		Same surface	(n = 2, 3, 4···)	(n = 2, 4, 6	(n = 2, 4, 6, 8···) Note 1)		(n = 2, 4, 6	, 8) Note 1)	
		1	10		75	80		90	
D-Y59□/Y7P		Different surfaces d same surface) 1	15	80	85	90	95	105	
D-Y7□W	u	d suric suriace) i	(n – 2)	(n – 4)	(n – 4)	90 + 40 (n - 4)	(n – 4)	(n – 4)	
D-Z7□/Z80		n							
			(n = 2, 4, 6, 8···) Note 1)	(n = 4, 8, 12, 16···) Note 2)	(n = 4, 8, 12, 16···) Note 2)	(n = 4, 8, 12, 16···) Note 2)	(n = 4, 8, 12, 16···) Note 2)	(n = 4, 8, 12, 16···) Note 2)	
D-Y69□/Y7PV	2 (Different surfaces and same surface) 1		10		65	75	80	90	
D-103⊟/1/1V D-Y7□WV	Г		10 + 30 (n - 2)	65 + 3	n (n – 4)	75 ± 30 (n - 4)	80 + 30 (n - 4)	90 ± 30 (n - 4)	
2		n	(n = 2, 4, 6, 8···) Note 1)		2, 16) Note 2)		(n = 4, 8, 12, 16···) Note 2)		
	2 /	Different surfaces	(11 = 2, 4, 0, 0)	(11 = 4, 0, 12	, 10,		(11 = 4, 0, 12, 10)	(11 = 4, 0, 12, 10***)	
		d same surface) 1	20		95	100	105	110	
D-Y7BA		n	$20 + 45 \frac{(n-2)}{2}$	95 + 4	5 (n - 4)	100 + 45 (n - 4)	105 + 45 (n - 4)	$110 + 45 \frac{(n-4)}{2}$	
	n		(n = 2, 4, 6, 8) Note 1)	(n = 4, 8, 12	., 16···) Note 2)		(n = 4, 8, 12, 16) Note 2)		

Note 1) When "n" is an odd number, an even number that is one larger than this odd number is used for the calculation. Note 2) When "n" is an odd number, a multiple of 4 that is larger than this odd number is used for the calculation.

CVS1 Series

Operating Range

					(mm)	
Auto switch model	Bore size					
Auto Switch model	40	50	63	80	100	
D-M9□/M9□V D-M9□W/M9□WV D-M9□A/M9□AV	4.5	5	5.5	5	6	
D-A9□/A9□V	7	_	9	9	9	
D-Z7□/Z80	8	7	9	9.5	10.5	
D-A3□/A44 D-A3□C/A44C D-A5□/A6□	9	10	11	11	11	
D-B5□/B64						
D-A59W	13	13	14	14	15	
D-B59W	14	14	17	16	18	
D-Y59□/Y69□ D-Y7P/Y7PV D-Y7□W/Y7□WV	8	7	5.5	6.5	6.5	
D-F5□/J59 D-F5□W/J59W D-F5NT/F59F	4	4	4.5	4.5	4.5	
D-G5□/K59 D-G5□W/K59W D-G5NT/G59F	5	6	6.5	6.5	7	
D-G39/K39 D-G39C/K39C	9	9	10	10	11	

^{*} D-A9□ and D-A9□V types cannot be mounted on ø50

Auto Switch Mounting Bracket Part No.


<Tie-rod mounting type>

Auto switch	Bore size (mm)						
model	40	50	63	80	100		
D-M9□/M9□V D-M9□W/M9□WV D-M9□A/M9□AV D-A9□/A9□V	BA7-040	BA7-040	BA7-063	BA7-080	BA7-080		
D-F5□/J59 D-F5□W/J59W D-F59F/F5NT D-A5□/A6□ D-A59W	BT-04	BT-04	BT-06	BT-08	BT-08		
D-G39C/K39C D-A3□C/A44C	BA3-040	BA3-050	BA3-063	BA3-080	BA3-100		
D-Y59□/Y69□ D-Y7P/Y7PV D-Y7□W/Y7□WV D-Y7BA D-Z7□/Z80	BA4-040	BA4-040	BA4-063	BA4-080	BA4-080		

<Band mounting type>

Standard

Auto switch	Bore size (mm)					
model	40	50	63	80	100	
D-G39/K39 D-A3□/A44	BDS-04M	BDS-05M	BMB1-063	BMB1-080	BMB1-100	
D-G5□/K59 D-G5□W/K59W D-G59F D-G5NT D-B5□/B64 D-B59W	BH2-040	BA5-050	BAF-06	BAF-08	BAF-10	



• The figure shows the mounting example for the D-M9 \square (V)/M9 \square W(V)/M9 \square A(V)/A9 \square (V) types.

Note 1) Auto switch brackets are included in the D-A3\(\timec\)C/A44C/G39C/K39C types. Specify the part number as follows depending on the cylinder size when ordering. (Example) \(\tilde{\gamma}\)40: D-A3\(\tilde{\tilde{C}}\)C-4, \(\tilde{\gamma}\)50: D-A3\(\tilde{\tilde{C}}\)C-8, \(\tilde{\gamma}\)63: D-A3\(\tilde{\tilde{C}}\)C-8, \(\tilde{\gamma}\)100: D-A3\(\tilde{\tilde{C}}\)C-10

^{*} Since this is a guideline including hysteresis, not meant to be

guaranteed. (Assuming approximately ±30% dispersion.)
There may be the case it will vary substantially depending on an ambient environment.

Auto Switch Mounting CVS1 Series

Other than the models listed in "How to Order", the following auto switches are applicable. For detailed specifications, refer to pages 1341 to 1435.

Auto switch type	Model	Electrical entry (Fetching direction)	Features	
	D-A93V, A96V	Grommet	_	
Reed	D-A90V	(Perpendicular)	Without indicator light	
	D-A53, A56, B53, Z73, Z76	Crommet (In line)	_	
	D-A67, Z80	Grommet (In-line)	Without indicator light	
	D-M9NV, M9PV, M9BV		_	
	D-Y69A, Y69B, Y7PV	☐ <u>.</u> .		
	D-M9NWV, M9PWV, M9BWV	Grommet (Perpendicular)	Diagnostic indication	
	D-Y7NWV, Y7PWV, Y7BWV	(Ferperidicular)	(2-color indicator)	
Solid state	D-M9NAV, M9PAV, M9BAV		Water resistant (2-color indicato	
Solid State	D-Y59A, Y59B, Y7P		_	
	D-F59, F5P, J59			
	D-Y7NW, Y7PW, Y7BW	Grommet (In-line)	Diagnostic indication	
	D-F59W, F5PW, J59W		(2-color indicator)	
	D-F5NT, G5NT		With timer	

^{*} With pre-wired connector is also available in solid state auto switches. For details, refer to pages 1410 and 1411.

^{*} Normally closed (NC = b contact) solid state auto switches (D-M9□E(V)/Y7G/Y7H) are also available. For details, refer to pages 1360 and 1362.



CVS1 Series Specific Product Precautions

Be sure to read this before handling the products. Refer to page 9 for safety instructions, pages 10 to 19 for actuator and auto switch precautions, and 3/4/5-port solenoid valve precautions on the SMC website: https://www.smcworld.com

Selection

⚠ Warning

1. Confirm the specifications.

Products in this catalog are designed to be used for compressed air systems. If not operated within the designated pressure or temperature, it may damage the products or cause malfunction. (Refer to specifications.)

2. Energizing continuously for a long period of time When the valve is continuously energized for a long period of time, the performance may deteriorate or effect peripheral equipment adversely since temperature rises when coils generate heat.

3. Mounting orientation

Metal seal: For single solenoids, mounting orientation is flexible. For double solenoids and 3 position valves, mount a spool valve horizontally.

Handling

.↑Warning

1. Do not open the cushion valve beyond the stopper. A retaining ring is installed as a cushion valve retention mechanism. Do not open the cushion valve beyond it. If not operated in accordance with the above precautions, the cushion valve may be ejected from the cover when air pressure is supplied.

Bore size (mm)	Width across flats	Socket wrench
40, 50	2.5	JIS 4648 Hexagonal wrench key 2.5
63, 80, 100	4	JIS 4648 Hexagonal wrench key 4

Use the air cushion at the end of cylinder stroke. Otherwise, the tie-rod or piston rod assembly will be damaged.

Handling

↑ Caution

- Do not use a pneumatic type as an air-hydro cylinder. It can cause oil leak.
- Do not rotate the piston rod when the rod boot is fixed.

Before rotating the piston rod, loosen the band to avoid twisting the rod boot.

3. Install the rod boot with the breathing hole facing downwards or in a direction suitable to prevent dust, moisture etc. from entering easily into the rod boot.

Disassembly/Replacement

⚠ Caution

Use a socket wrench when the bracket is replaced.
 If other tools are used, the nut or other parts may be

If other tools are used, the nut or other parts may be deformed or the work efficiency may decrease. For applicable sockets, refer to the table below.

Bore size (mm)	Nut	Width across flats	Socket	Tightening torque (N·m)	
40, 50	DA00040	13	JIS B4636	7.4	
40, 50	(M8 x 1.25, Hexagon nut 3 types)	13	+ Two-angle socket 13		
63	DA00010	17	JIS B4636	20	
03	(M10 x 1.25, Hexagon nut 3 types)	17	+ Two-angle socket 17	20	
90 100	DA00131	19	JIS B4636	29	
00, 100	(M12 x 1.75, Hexagon nut 3 types)	19	+ Two-angle socket 19		

2. Do not replace the bushing.

As the bushing is press-fit, replace the cover assembly when the bushing must be replaced.

When a seal is replaced, apply grease to the new seal before it is assembled.

Operation of the cylinder without greasing will result in extreme abrasion of the seal, causing premature air leakage.

4. Do not disassemble the trunnion type cylinder because the mounting precision is required.

It is difficult to align the axial center of the trunnion with the axial center of the cylinder. Thus, if this type of cylinder is disassembled and reassembled, the required dimensional accuracy cannot be attained, which may lead to malfunctions.

