

Compact Manifold Regulator

ARM10/11 Series



Allows high degree of freedom in selection according to the installation conditions.

- Knob position: Top, Front, Bottom
- · Piping direction: Top ported, Bottom ported
- · One-touch fitting types: Straight, Elbow



Types and sizes of the One-touch fittings can be changed.



		Applic	cable tub	ing O.D	. (mm)
	Fitting type	4	6	8	10
IN side	Straight, Elbow				
OUT side	Straight, Elbow		0		

Also available in inch sizes.

Reverse flow function is equipped as a standard.

Can control thrust of the actuator.

Four types of supply blocks (for common supply)

The mounting position of the supply block can be selected from the right, left and both sides of the manifold.

Supply block	With 3-way pressure relief valve	With pressure switch	With 3-way pressure relief valve + Pressure switch

Mixed manifold

Common exhaust type and individual exhaust type can be mounted on the same manifold base.

(Available as Simple Specials)



Pressure gauge with limit indicator.

Opening and closing lens cover makes adjustment easy.

Compatible with units with a digital pressure switch

Individual lines can be controlled with electric signals.






Compact Manifold Regulator

Common Supply Type


ARM11A Series



How to Order



1. Knob Position



2. IN/OUT Piping Position

Position Symbol			OUT	side	IN side Top fitti	JT side ing
1 2	•		•		Elbow	Top)
3	•	•		•		
4		•	•			
					TELL CAR	IN side Bottom OUT side fitting
					Bottom	Straight Straight

3. Regulator Block Stations


Symbol	Stations
1	1 station
2	2 stations
3	3 stations
4	4 stations
5	5 stations
6	6 stations
7	7 stations
8	8 stations
9	9 stations
М	10 stations

4. IN/OUT Fitting Type (Refer to the figure below.)

Metric s	ize										ı	nch siz	е									
Mounting position			IN s	side				TUC	side	Э	ſ	Mounting position			IN s	side				OUT	side	•
Fitting type	S	traig	ht	E	Elbov	N	Stra	ight	Elbo	w Note)	N	Fitting type	S	traig	ht	E	Elbov	N	Stra	ight	Elbov	N N
Symbol	ø6	ø8	ø10	ø6	ø8	ø10	ø4	ø6	ø4	ø6		Symbol	ø1/4	ø5/16	ø3/8	ø1/4	ø5/16	ø3/8	ø5/32	ø1/4	ø5/32	ø1
07	•						•					57	•						•			
08	•							•				58	•							•		
09		•					•					59		•					•			
10		•						•				60		•						•		
11			•				•					61			•							
12			•					•				62			•					•		
19				•					•			69				•					•	
20				•						•		70				•						•
21									•			71					•				•	Γ
22					•					•		72					•					•
23						•			•			73						•			•	
24						•						74						•				•
26	•								•			76	•								•	
27	•									•		77	•									•
28		•							•			78		•							•	
29		•								•		79		•								•
30			•						•			80			•						•	
31			•							•		81			•							•
33				•			•					83				•			•			L
34				•				•				84				•				•		
35					•		•					85					•		•			
36					•			•				86					•			•		
37						•	•					87						•	•			
38		_	_	_	_	•		•		ΙП	J	88						•		•		(-

Note) When the knob and the OUT piping are located on the same side, the elbow fitting is directed to the rear side (DIN rail side). Use caution to ensure the connector is not disturbed, depending on piping direction, when choosing to attach a digital pressure switch.

Knob position: Top OUT piping position: Top



Knob position: Bottom OUT piping position: Bottom



Compact Manifold Regulator Common Supply Type ARM11A Series

5. Accessories

	Pressure dis	splay Note 1, 2)	Supply block type Note 3)			Supply block mounting po-			
Symbol	Without pressure display	With pressure display	Common supply block	Common supply block with pressure switch	3-way valve common supply block	3-way valve common supply block + Pressure switch block	L side (Left)	R side (Right)	B side (Both)
Nil	•		•				•		
Α	•			•			•		
В	•				•		<u> </u>		
С	•					•	•		
D	•		•					•	
E	•			•				•	
F	•				•			•	
G	•					•		•	
Н	•		•						•
J		•	•				•		
K		•		•			•		
L		•			•		•		
M		•				•	•		
N		•	•					•	
0		•		•				•	
P		•			•			•	
Q		•				•		•	
R		•	•						•

Note 1) Pressure display means a pressure gauge or digital pressure switch is attached.

When choosing to attach a digital pressure switch is chosen for attachment, be sure to enter the symbol, referring to table 8, "Digital Presure Switch Output Specifications". Otherwise, a pressure gauge will come with the regulator.

Note 2) Pressure gauges are not compatible with copper-free and fluorine-free specifications

Note 3) Pressure switches are not available with the oil-free specification.

6. Semi-standard 8. Digital Presure Switch Output Specifications Note

Symbol	None	0.35 MPa setting Note 1)	Non- relieving	Note 2) Oil-free
Nil	•			
1		•		
2			•	
3				•
4		•	•	
5		•		•
6			•	•
7		•	_	_

Note 1) A pressure gauge with a full span of 0.4 MPa is attached. Note 2) The oil-free specification is grease-free in the fluid contact area.

| Symbol | Details | Nil | None | N | NPN open collector | P | PNP open collector | Note) When a digital pressure switch is

attached, the "pressure display" in table 5
"Accessories" will be equipped.
The electrical entry is positioned on the side
opposite the knob.

Without pressure display pressure display With with digital

pressure

quage

Common supply block

Common supply block with pressure switch

pressure switch







3-way valve

common supply block 3-way valve common supply block +

Pressure switch block



7. Unit Representation

Symbol	Description
Nil	Display unit for product name plate and pressure gauge: MPa
Z Note 1, 2)	Display unit for product name plate and pressure gauge: psi
ZA ^{Note 1, 3)}	Digital pressure switch: with unit switching (MPa is initially set.)

Note 1) This option is available for use outside Japan only. (The SI unit has to be used in Japan.) Additionally, the pressure switch offers dual unit presentation in MPa and osi.

Note 2) The digital pressure switch is equipped with unit switching and initially set to psi.

Note 3) This option is available with the digital pressure switch. A lead wire with connector (2 m) is included

Symbol



Note) A standard model is equipped with a backflow function. Main valve opens when the inlet pressure is released, and then the outlet pressure backflows into the inlet side.

Specifications

Manifold (Regulator block, Common supply block, 3-way valve common supply block)

Regulator construction		Direct acting
Working principal		Diaphragm regulator
Relief mechanism	Standard	Relief type
neller illechanism	Optional	Non-relieving type
Backflow function Note 1)		Within (Unbalance type)
IN side tubing O.D.		ø6, ø8, ø10, ø1/4, ø5/16, ø3/8
OUT side tubing O.D.		ø4, ø6, ø5/32, ø1/4
Proof pressure		1.5 MPa
Maximum operating pressure		1.0 MPa
0-4	Standard	0.05 to 0.7 MPa
Set pressure range	Optional	0.05 to 0.35 MPa (Low pressure type)
Fluid		Air
Ambient and operating fluid temperature Note 2)		5 to 60°C

Note 1) 0.1 MPa or greater set pressure is required when used in the reverse flow.


Note 2) 5 to 50°C when the digital pressure switch will be used.


Refer to pages 1018 and 1020 for the digital pressure switch and pressure switch specifications.





ARM11A Series


Flow Rate Characteristics (Representative Values)

















Pressure Characteristics (Representative Values)





Construction



Component Parts

00	ipononii arto	
No.	Description	Material
1	Body for regulator block	PBT
2	Bonnet	PBT
3	Knob	POM
4	Valve seat	POM
5	Adjusting screw assembly	Reinforced steel
6	Adjustment spring	Steel wire
7	Regulator clip	Stainless steel
8	Manifold block	PBT
9	Blanking plate assembly	_
10	Square nut	Steel
11	Common exhaust bushing	POM

Replacement Parts

No.	Description	Material	Part no.	Note
Α.	Diaphragm	Weatherproof	136126A	Relieving type
^	assembly	NBR, POM	136126-1A	Non-relieving type
В	Valve	HNBR, Aluminum alloy	136127-30#1	
С	Valve spring	Stainless steel	136131	
D	Gasket	HNBR	136137-30	
E	O-ring	NBR	136146	Standard model
-	O-ring	HNBR	136146-30	Oil-free specification
F	O-ring	NBR	136147	Standard model
	O-ring	HNBR	136147-30	Oil-free specification
		NBR	136148	Standard model
G	O-ring	HNBR	136148-30	Oil-free specification
u	O-ring	NBR	KA01731	Standard model for digital pressure switch
		HNBR	KA01613	Oil-free spec. for digital pressure switch
н	O-ring	NBR	136149	Standard model
	O-ring	HNBR	136149-30	Oil-free specification
J	Fitting assembly	_	Refer to page 1021.	
K	Port plug	PBT/HNBR	Refer to page 1022.	

SMC


ARM11A Series


Dimensions

ARM11AA1-□12

Knob position: Top / Common supply block

For One-touch fittings part and manifold option dimensions, refer to pages 1015 to 1022.







Stations	DIN rail part no. (for L and R sides)	L2 dimension
1	AXT100-DR-9	123
2	AXT100-DR-11	148
3	AXT100-DR-13	173
4	AXT100-DR-16	210.5
5	AXT100-DR-18	235.5
6	AXT100-DR-20	260.5
7	AXT100-DR-22	285.5
8	AXT100-DR-25	323
9	AXT100-DR-27	348
М	AXT100-DR-29	373

ARM11AA1-□12-A

Knob position: Top / Common supply block with pressure switch





1 1 1 1 1 1 1 1 1 1 1 1 1 1 1 1 1 1 1		
---------------------------------------	--	--


Stations	DIN rail part no. (for L and R sides)	L2 dimension
1	AXT100-DR-9	123
2	AXT100-DR-11	148
3	AXT100-DR-13	173
4	AXT100-DR-16	210.5
5	AXT100-DR-18	235.5
6	AXT100-DR-20	260.5
7	AXT100-DR-22	285.5
8	AXT100-DR-25	323
9	AXT100-DR-27	348
М	AXT100-DR-29	373


Dimensions

ARM11AA1-□12-B

Knob position: Top / 3-way valve common supply block

For One-touch fittings part and manifold option dimensions, refer to pages 1015 to 1022.







Stations	DIN rail part no. (for L and R sides)	L2 dimension
1	AXT100-DR-9	123
2	AXT100-DR-11	148
3	AXT100-DR-13	173
4	AXT100-DR-16	210.5
5	AXT100-DR-18	235.5
6	AXT100-DR-20	260.5
7	AXT100-DR-22	285.5
8	AXT100-DR-25	323
9	AXT100-DR-27	348
М	AXT100-DR-29	373

ARM11AA1-□12-C

Knob position: Top / 3-way valve common supply block + Pressure switch block





Stations	DIN rail part no.	L2 dimension
1	AXT100-DR-11	148
2	AXT100-DR-13	173
3	AXT100-DR-15	198
4	AXT100-DR-17	223
5	AXT100-DR-19	248
6	AXT100-DR-22	285.5
7	AXT100-DR-24	310.5
8	AXT100-DR-26	335.5
9	AXT100-DR-28	360.5
M	AXT100-DR-31	398




ARM11A Series


Dimensions

ARM11AB1-□12

Knob position: Front / Common supply block

For One-touch fittings part and manifold option dimensions, refer to pages 1015 to 1022.








Stations	DIN rail part no.	L2 dimension
1	AXT100-DR-9	123
2	AXT100-DR-11	148
3	AXT100-DR-13	173
4	AXT100-DR-16	210.5
5	AXT100-DR-18	235.5
6	AXT100-DR-20	260.5
7	AXT100-DR-22	285.5
8	AXT100-DR-25	323
9	AXT100-DR-27	348
М	AXT100-DR-29	373

ARM11AB1-□12-A

Knob position: Front / Common supply block with pressure switch








AXT100-DR-9 AXT100-DR-11 AXT100-DR-13 AXT100-DR-16	123 148 173 210.5
AXT100-DR-13	173
AXT100-DR-16	210.5
	1 -10.0
AXT100-DR-18	235.5
AXT100-DR-20	260.5
AXT100-DR-22	285.5
AXT100-DR-25	323
AXT100-DR-27	348
AXT100-DR-29	373
	AXT100-DR-20 AXT100-DR-22 AXT100-DR-25 AXT100-DR-27


Dimensions

ARM11AB1-□12-B

Knob position: Front / 3-way valve common supply block

For One-touch fittings part and manifold option dimensions, refer to pages 1015 to 1022.







Stations	DIN rail part no.	L2 dimension
1	AXT100-DR-9	123
2	AXT100-DR-11	148
3	AXT100-DR-13	173
4	AXT100-DR-16	210.5
5	AXT100-DR-18	235.5
6	AXT100-DR-20	260.5
7	AXT100-DR-22	285.5
8	AXT100-DR-25	323
9	AXT100-DR-27	348
M	AXT100-DR-29	373

ARM11AB1-□12-C

Knob position: Front / 3-way valve common supply block + Pressure switch block





Stations	DIN rail part no.	L2 dimension
1	AXT100-DR-11	148
2	AXT100-DR-13	173
3	AXT100-DR-15	198
4	AXT100-DR-17	223
5	AXT100-DR-19	248
6	AXT100-DR-22	285.5
7	AXT100-DR-24	310.5
8	AXT100-DR-26	335.5
9	AXT100-DR-28	360.5
M	AXT100-DR-31	398




ARM11A Series


Dimensions

ARM11AC2-□12

Knob position: Bottom / Common supply block

For One-touch fittings part and manifold option dimensions, refer to pages 1015 to 1022.







53	18		O	Q		
	, 	or o	DÜT	100	N	

Stations	DIN rail part no.	L2 dimension
1	AXT100-DR-9	123
2	AXT100-DR-11	148
3	AXT100-DR-13	173
4	AXT100-DR-16	210.5
5	AXT100-DR-18	235.5
6	AXT100-DR-20	260.5
7	AXT100-DR-22	285.5
8	AXT100-DR-25	323
9	AXT100-DR-27	348
М	AXT100-DR-29	373

ARM11AC2-□12-A

Knob position: Bottom / Common supply block with pressure switch






Stations	DIN rail part no.	L2 dimension
1	AXT100-DR-9	123
2	AXT100-DR-11	148
3	AXT100-DR-13	173
4	AXT100-DR-16	210.5
5	AXT100-DR-18	235.5
6	AXT100-DR-20	260.5
7	AXT100-DR-22	285.5
8	AXT100-DR-25	323
9	AXT100-DR-27	348
M	AXT100-DR-29	373


Dimensions

ARM11AC2-□12-B

Knob position: Bottom / 3-way valve common supply block

For One-touch fittings part and manifold option dimensions, refer to pages 1015 to 1022.







Stations	DIN rail part no.	L2 dimension
1	AXT100-DR-9	123
2	AXT100-DR-11	148
3	AXT100-DR-13	173
4	AXT100-DR-16	210.5
5	AXT100-DR-18	235.5
6	AXT100-DR-20	260.5
7	AXT100-DR-22	285.5
8	AXT100-DR-25	323
9	AXT100-DR-27	348
M	AXT100-DR-29	373

ARM11AC2-□12-C

Knob position: Bottom / 3-way valve common supply block + Pressure switch block





22	_			•	•	9			e	
۵,	5	<u>φ</u>			@			33.5	Ď	

Stations	DIN rail part no.	L2 dimension
1	AXT100-DR-11	148
2	AXT100-DR-13	173
3	AXT100-DR-15	198
4	AXT100-DR-17	223
5	AXT100-DR-19	248
6	AXT100-DR-22	285.5
7	AXT100-DR-24	310.5
8	AXT100-DR-26	335.5
9	AXT100-DR-28	360.5
М	AXT100-DR-31	398

Compact Manifold Regulator

Individual Supply Type

ARM11B Series

How to Order






1. Knob Position

Symbol	Position	Top Front Bottom
Α	Тор	
В	Front	
С	Bottom	

2. IN/OUT Piping Position

Position			OUT side				
Symbol	Bottom	Top	Bottom	Top			
1	•		•				
2		•		•			
3	•			•			
4		•	•				



3. Regulator Block Stations

Symbol	Stations			
1	1 station			
2	2 stations			
3	3 stations			
4	4 stations			
5	5 stations			
6	6 stations			
7	7 stations			
8	8 stations			
9	9 stations			
M	10 stations			

4. IN/OUT Fitting Type (Refer to the figure below.)

Metric size									Inch siz	e							
Mounting position		IN:	side			OUT	side	,	Mounting position	ion IN side			OUT side				
Fitting type	Stra	ight	Elbov	N Note)	Stra	ight	Elbo	N Note)	Fitting type	Stra	ight	Elbov	v Note)	Stra	ight	Elbov	w Note)
Symbol	ø4	ø6	ø4	ø6	ø4	ø6	ø4	ø6	Symbol	ø5/32	ø1/4	ø5/32	ø 1/4	ø5/32	ø1/4	ø5/32	ø1/4
06	•				•				56	•				•			
07		•			•				57		•			•			
08		•				•			58		•				•		
18			•				•		68			•				•	
19				•			•		69				•			•	
20				•				•	70				•				•
25	•						•		75	•						•	
26		•					•		76		•					•	
27		•						•	77		•						•
32			•		•				82			•		•			
33				•	•				83				•	•			
34				•		•			84				•		•		

Note) When the knob and the OUT piping are located on the same side, the elbow fitting is directed to the rear side (DIN rail side). Use caution to ensure the connector is not disturbed, depending on piping direction, when choosing to attach a digital pressure switch.

Knob position: Top OUT piping position: Top OUT piping position: Top OUT piping position: Bottom OUT piping positi

Compact Manifold Regulator Individual Supply Type ARM11B Series

5. Accessory (Pressure Display)

Symbol	Accessory					
Nil	Without pressure display					
A Note 1, 2)	With pressure display					

Note 1) Pressure display means a pressure gauge or digital pressure switch is attached.

When choosing to attach a digital pressure switch is chosen for attachment, be sure to enter the symbol, referring to table 8, "Digital Presure Switch Output Specifications". Otherwise, a pressure gauge will come with the regulator.

Note 2) Pressure gauges are not compatible with copper-free and fluorine-free specifications.

Without pressure display







With digital With pressure pressure switch quage

With

pressure display

6. Semi-standard

Symbol	None	0.35 MPa setting Note 1)	Non- relieving	Note 2) Oil-free
Nil	•			
1		•		
2			•	
3				•
4		•	•	
5		•		•
6			•	•
7		•	•	•

Note 1) A pressure gauge with a full span of 0.4 MPa is attached.

Note 2) The oil-free specification is grease-free in the fluid contact area.

7. Unit Representation

Symbol	Description
Nil	Display unit for product name plate and pressure gauge: MPa
Z Note 1, 2)	Display unit for product name plate and pressure gauge: psi
ZA Note 1, 3)	Digital pressure switch: with unit switching (MPa is initially set.)

Note 1) This option is available for use outside Japan only. (The SI unit has to be used in Japan.)

Note 2) The digital pressure switch is equipped with unit switching and initially set to psi.

Note 3) This option is available with the digital pressure switch. A lead wire with connector (2 m) is included.

8. Digital Presure Switch Output Specifications Note)

Symbol	Details			
Nil	None			
N	NPN open collector PNP open collector			
P				

Note) When a digital pressure switch is attached, the "pressure display" in table 5 "Accessory" will be equipped.

The electrical entry is positioned on the side opposite the knob.

Specifications

Regulator construction		Direct acting		
Working principal		Diaphragm regulator		
Relief mechanism	Standard	Relief type		
neller illectianism	Optional	Non-relieving type		
Backflow function Note 1)		Within (Unbalance type)		
IN side tubing O.D.		ø4, ø6, ø5/32, ø1/4		
OUT side tubing O.D.		ø4, ø6, ø5/32, ø1/4		
Proof pressure		1.5 MPa		
Maximum operating pressure		1.0 MPa		
0-4	Standard	0.05 to 0.7 MPa		
Set pressure range	Optional	0.05 to 0.35 MPa (Low pressure type)		
Fluid		Air		
Ambient and operating fluid temper	rature Note 2)	5 to 60°C		

Note 1) 0.1 MPa or greater set pressure is required when used in the reverse flow. Note 2) 5 to 50°C when the digital pressure switch will be used

Refer to page 1018 for the digital pressure switch specifications.



Note) A standard model is equipped with a backflow function. Main valve opens when the inlet pressure is released, and then the outlet pressure backflows into the inlet side.

Specific Product Precautions

Be sure to read this before handling the products.

Refer to page 9 for safety instructions and pages 13 to 17 for precautions on

Maintenance


⚠ Warning

1. Make sure to perform a periodic inspection of the pressure gauge when the compact manifold regulator is installed between a solenoid valve and an actuator. Sudden pressure changes could happen and the durability of the product could be reduced. Using an electronic type pressure gauge is recommended, depending on the situation.



ARM11B Series

Construction




Component Parts


No.	Description	Material
1	Body for regulator block	PBT
2	Bonnet	PBT
3	Knob	POM
4	Valve seat	POM
5	Adjusting screw assembly	Reinforced steel
6	Adjustment spring	Steel wire
7	Regulator clip	Stainless steel
8	Manifold block	PBT
9	Blanking plate assembly	_
10	Square nut	Steel
11	Individual supply bushing	POM


Replacement Parts


No.	Description	Material	Part no.	Note
Α	Diaphragm	Weatherproof	136126A	Relieving type
Α.	assembly	NBR, POM	136126-1A	Non-relieving type
В	Valve	HNBR, Aluminum alloy	136127-30#1	
С	Valve spring	Stainless steel	136131	
D	Gasket	HNBR	136137-30	
E	O-ring	NBR	136146	Standard model
-	O-ring	HNBR	136146-30	Oil-free specification
F	O-ring	NBR	136147	Standard model
	O-ring	HNBR	136147-30	Oil-free specification
	O-ring	NBR	136148	Standard model
G		HNBR	136148-30	Oil-free specification
u		NBR	KA01731	Standard model for digital pressure switch
		HNBR	KA01613	Oil-free spec. for digital pressure switch
н	O-ring	NBR	136149	Standard model
	O-ring	HNBR	136149-30	Oil-free specification
J	Fitting assembly	_	Refer to page 1021.	
K	Port plug	PBT/HNBR	Refer to page 1022.	


Flow Rate Characteristics (Representative Values)
















Pressure Characteristics (Representative Values)








ARM11B Series


Dimensions

ARM11BA1-□08 Knob position: Top



Stations	DIN rail part no.	L2 dimension
Stations	DIN Tall part 110.	LZ UIIIICIISIUII
1	AXT100-DR-8	110.5
2	AXT100-DR-10	135.5
3	AXT100-DR-12	160.5
4	AXT100-DR-14	185.5
5	AXT100-DR-16	210.5
6	AXT100-DR-19	248
7	AXT100-DR-21	273
8	AXT100-DR-23	298
9	AXT100-DR-25	323
M	AXT100-DR-28	360.5


ARM11BB1-□**08**



Stations	DIN rail part no.	L2 dimension
1	AXT100-DR-8	110.5
2	AXT100-DR-10	135.5
3	AXT100-DR-12	160.5
4	AXT100-DR-14	185.5
5	AXT100-DR-16	210.5
6	AXT100-DR-19	248
7	AXT100-DR-21	273
8	AXT100-DR-23	298
9	9 AXT100-DR-25	
М	M AXT100-DR-28	

52.5


ARM11BC2-□08




Stations	DIN rail part no.	L2 dimension
1	AXT100-DR-8	110.5
2	AXT100-DR-10	135.5
3	AXT100-DR-12	160.5
4	AXT100-DR-14	185.5
5	AXT100-DR-16	210.5
6	AXT100-DR-19	248
7	AXT100-DR-21	273
8	AXT100-DR-23	298
9	AXT100-DR-25	323
М	AXT100-DR-28	360.5

Compact Manifold Regulator Options

Common Supply Type



Individual Supply Type




ARM11A/B Series

Regulator Block



1. Knob Position



2. OUT Piping Position 3. OUT

Symbol	Position
1	Bottom
2	Тор

3. OUT Fitting Type Metric size

Fitting type	Straight		Elbow	
Symbol	ø4 ø6		ø4	ø6
04	•			
05		•		
16			•	
17				•

Inch size

Straight		Elbow	
ø5/32 ø1/4		ø5/32	ø1/4
4 ●			
	•		
		•	
67			•

4. Accessory (Pressure Display)

Symbol	Accessory Without pressure display	
Nil		
A Note 1, 2)	With pressure display	

Note 1) Pressure display means a pressure gauge or digital pressure switch is attached. When choosing to attach a digital pressure switch is chosen for attachment, be sure to enter the symbol, referring to table 7, "Digital Presure Switch Output Specifications". Otherwise, a pressure gauge will come with the regulator.

Note 2) Pressure gauges are not compatible with copper-free and fluorine-free specifications.

5. Semi-standard

Symbol	None	0.35 MPa setting Note 1)	Non- relieving	Oil-free
Nil	•			
1		•		
2			•	
3				•
4		•	•	
5		•		•
6			•	•
7		•	•	•

Note 1) A pressure gauge with a full span of 0.4 MPa is attached. Note 2) The oil-free specification is grease-free in the fluid contact area.

6. Unit Representation

Symbol	Description
Nil	Display unit for product name plate and pressure gauge: MPa
Z Note 1, 2)	Display unit for product harne plate and pressure gauge, psi
ZA Note 1, 3)	Digital pressure switch: with unit switching (MPa is initially set.)

Note 1) This option is available for use outside Japan only. (The SI unit has to be used in Japan.) Additionally, the pressure switch offers dual unit presentation in MPa and psi.

Note 2) The digital pressure switch is equipped with unit switching and initially set to psi.

Note 3) This option is available with the digital pressure switch.

7. Digital Presure Switch Output Specifications Note)


Symbol	Details	
Nil	None	
N	NPN open collector	
Р	PNP open collector	

Note) When a digital pressure switch is attached, the "pressure display" in table 4 "Accessory" will be equipped.
The electrical entry is positioned on the side opposite the knob.

Regulator Block



1. Knob Position



2. IN/OUT Piping Position

Position	IN side		OUT side	
Symbol	Bottom Top		Bottom	Тор
1	•		•	
2		•		•
3	•			•
1				

3. IN/OUT Fitting Type

Metric size						Inch siz	e										
Mounting position		IN s	side			OUT side			Mounting position	IN side				OUT side			
Fitting type	Stra	ight	Elb	ow	Stra	ight	Elb	ow	Fitting type	Stra	ight	Elb	ow	Stra	ight	Elb	ow
Symbol	ø4	ø6	ø4	ø6	ø4	ø6	ø4	ø6	Symbol	05/32	ø1/4	ø5/32	ø1/4	ø5/32	ø1/4	05/32	ø1/4
06	•				•				56	•				•			
07		•			•				57		•						
08		•				•			58		•				•		
18			•				•		68			•				•	
19				•					69				•			•	
20				•				•	70				•				•
25	•						•		75	•						•	
26		•							76		•					•	
27		•						•	77		•						•
32			•		•				82			•		•			
33				•	•				83				•	•			
34				•		•			84				•		•		

4. Accessory (Pressure Display)

Symbol	Accessory
Nil	Without pressure display
A Note 1, 2)	With pressure display

Note 1) Pressure display means a pressure gauge or digital pressure switch is attached.

When choosing to attach a digital pressure switch is chosen for attachment, be sure to enter the symbol, referring to table 7, "Digital Pressure Switch Output Specifications".

Otherwise, a pressure gauge will come with

Note 2) Pressure gauges are not compatible with copper-free and fluorine-free specifications.

5. Semi-standard

Symbol	None	0.35 MPa setting Note 1)	Non- relieving	Oil-free
Nil	•			
1		•		
2			•	
3				•
4		•	•	
5		•		•
6			•	•
7		•	•	•

Note 1) A pressure gauge with a full span of 0.4 MPa is attached. Note 2) The oil-free specification is grease-free in the fluid contact area.

6. Unit Representation

the regulator

	Symbol	Description
	Nil	Display unit for product name plate and pressure gauge: MPa
	Z Note 1, 2)	Display unit for product name plate and pressure gauge: psi
ı	7 Δ Note 1, 3)	Digital pressure switch: with unit switching (MPa is initially set.)

Note 1) This option is available for use outside Japan only. (The SI unit has to be used in Japan.) Additionally, the pressure switch offers dual unit presentation in MPa and psi.

Note 2) The digital pressure switch is equipped with unit switching and initially set to psi.

Note 3) This option is available with the digital pressure switch.

7. Digital Presure Switch Output Specifications Note)

Symbol	Details
Nil	None
N	NPN open collector
P	PNP open collector

Note) When a digital pressure switch is attached, the "pressure display" in table 4 "Accessory" will be equipped. The electrical entry is positioned on the side opposite the knob.


ARM11A/B Series

Digital Pressure Switch



Specificati	ons					
Rated press	sure range	0 to 1 MPa				
Display/Set pressure range		-0.1 to 1 MPa				
Withstand pressure		1.5 MPa				
Display/Min	imum setting unit	0.01 MPa				
Applicable f	fluid	Air, Non-corrosive gas, Non-flammable gas				
Power supp		12 to 24 VDC ± 10%, Ripple (p-p) 10% or less (With power supply polarity protection)				
Current con	sumption	55 mA or less (at no load)				
Switch outp	ut	NPN or PNP open collector output: 1 output				
	Max. load current	80 mA				
	Max. applied voltage	30 V (With NPN output)				
	Residual voltage	1 V or less (With load current of 80 mA)				
	Response time	1 s (0.25, 0.5, 2, 3 selections)				
Short circui	t protection	Yes				
Repeatabilit	ty	±1% F.S.				
Hysteresis	Hysteresis mode	Adjustable (can be set from 0)				
nysteresis	Window comparator mode	Aujustable (carr be set from 0)				
Diaminu		3-digit, 7-segment indicator, 2-color display (Red / Green)				
Display		A switch can be operated simultaneously.				
Display acc	uracy	±2% F.S. ± 1 digit (at 25°C ± 3°C ambient temperature)				
Indicator light		Illuminates when output is ON. (Green)				
Environmental Enclosure		IP40				
resistance Operating temperature range		- 5 to 50°C (No freezing or condensation)				
Lead wire w	rith connector Note) (Option: L)	ø3.4 3-wire 25 AWG 2 m With connector cover				
Weight		Approx. 14g (body only)/Approx. 38g (including lead wire with connector)				
Standards		CE/UKCA marking, UL, CSA, RoHS				


Note) Refer to the Operation Manual in SMC's website (https://www.smcworld.com) for wiring.



SMC

Compact Manifold Regulator ARM11A/B Series

Common Supply Block



1. IN Piping Position

Symbol	Position
1	Bottom
2	Top

3. IN Fitting Type

Metri	ic size						Inch size							
Fitting type	S	traig	ht	Elbow			Eiting type	Straight		Elbow		/		
Symbol	ø6	ø8	ø10	ø6	ø8	ø10		Symbol	Ø1/4	Ø5/16	ø3/8	Ø1/4	ø5/16	ø3/8
01	•							51	•					
02		•						52		•				
03			•					53			•			
13				•				63				•		
14					•			64					•	
15						•		65						•

4. Option

Symbol	Description
Nil	None
3	Oil-free

Note) The oil-free type has non-greased fluid contact areas.

5. Accessory

Symbol	Description
Nil	Pressure switch lead wire length: 0.5 m
Α	Pressure switch lead wire length: 3.0 m

Note) Leave the field blank for types without pressure switch.

6. Unit Representation

Symbol	Description
Nil	Display unit for product name plate: MPa
Z Note)	Display unit for product name plate: psi


Note) This option is available for use outside Japan only. (The SI unit has to be used in Japan.) Additionally, the pressure switch offers dual unit presentation in MPa and psi.

2. Common Supply Block Type

Symbol	Description
S	Common supply block
P	Common supply block with pressure switch
٧	3-way valve common supply block
W	3-way valve common supply block + Pressure switch block

Note) The oil-free specification is not available for P and W types of common supply blocks (types with pressure switch).

Common supply block (S) Common supply block with pressure switch (P)



ARM11A/B Series

Pressure Switch Block




1. Accessory

Symbol	Description
Nil	Pressure switch lead wire length: 0.5 m
Α	Pressure switch lead wire length: 3.0 m

2. Unit Representation

Symbol	Description
Nil	Display unit for product name plate: MPa
Z Note)	Display unit for product name plate: psi

Note) This option is available for use outside Japan only. (The SI unit has to be used in Japan.) Additionally, the pressure switch offers dual unit presentation in MPa and psi.




Specifications


Pressure switch (Common supply block with pressure switch, 3-way valve common supply block plus pressure switch block)

Contact type	Reed type		
Contact construction	Reed switch type		
Contact component		1a	
Reed switch action	Pisto	on type (built-in mag	gnet)
Wiring specification		Grommet type	
Wiring length	0.	5 m (standard mode	el)
Proof pressure	1.0 MPa		
Maximum operating pressure	0.7 MPa		
Set pressure range	0.1 to 0.6 MPa		
Hysteresis	0.08 MPa or less		
Repeatability	±0.05 MPa		
Maximum contact capacity		AC 2 VA, DC 2 W	
Operating voltage AC, DC	24 V or less	48 V	100 V
Max. operating current and range	50 mA	40 mA	20 mA
Impact resistance	30 G		
Environmental resistance Enclosure	IP40		

Set Pressure Range



Electric Circuit



Compact Manifold Regulator ARM11A/B Series

DIN Rail


. When only DIN rail is required:

DIN rail part no.

AXT100-DR-7

L dimension

Select L dimension from the table below and enter an applicable symbol.








L Dimension L=12.5 x n+10.5 Symbol 2 3 4 8 9 10 23 35.5 48 60.5 73 85.5 98 110.5 123 135.5 Symbol 17 19 20 11 12 13 14 15 16 18 148 160.5 173 185.5 198 210.5 223 235.5 248 260.5 21 22 23 24 25 26 27 28 29 30 Symbol 273 285.5 298 310.5 323 335.5 348 360.5 373 385.5 Symbol 31 32 33 34 35 36 37 38 39 40 L 398 410.5 423 435.5 448 460.5 473 485.5 498 510.5

One-touch Fittings for Regulator Block

One-touch Fittings for Common Supply Block







	Ü	×	

Fitting size	Х
ø4, ø5/32	3
ø6	3
ø1/4	7


	6.5]
 Y		×

Elbow type

Fitting size	Х	Υ
ø4, ø5/32	11.5	19
ø6	11.5	19.5
ø1/4	11.5	22

Straight type


Fitting size	Х
ø6	5
ø8, ø5/16	5
ø10, ø3/8	5.5
ø1/4	5



Fitting size	Х	Y
ø6	19	20
ø8, ø5/16	20	23
ø10, ø3/8	22	26
ø1/4	19	20.5

ARM11A/B Series

End Block





Pressure Gauge


Part no.	Pressure gauge indication range	Indication unit
GC3-4A-X2101	0 to 0.4 MPa	MPa
GC3-10A-X2101	0 to 1.0 MPa	IVIFA
GC3-P4A-X2104	0 to 0.4 MPa (60 psi)	MPa/psi
GC3-P10A-X2104	0 to 1.0 MPa (150 psi)	ivir-a/psi

Specifications


	Display accuracy	±3%F.S. (Full Span)	
	Calibration angle	230°	
	Limit indicator	With limit indicator	








Port Plug



Bushing

Part no.	Description
136144-S	Common supply bushing
136144-K	Individual supply bushing




Regulator

Single Unit Type

ARM10 Series


How to Order



1. IN/OUT Fitting Type

Metric	size	•						
Mounting position		IN:	side			OUT	side	
Fitting type	Stra	ight	Elbov	N Note)	Straight		Elbow Note	
Symbol	ø4	ø6	ø4	ø6	ø4	ø6	ø4	ø6
06	•				•			
07		•			•			
08		•				•		
18			•				•	
19				•			•	
20				•				•
25	•						•	
26		•					•	
27		•						•
32			•		•			
33				•	•			
34				•		•		

Mounting position		IN s	side		OUT side			
Fitting type	Stra	ight	Elbov	N Note)	Stra	ight	Elbov	N Note)
Symbol	ø5/32	ø1/4	ø5/32	ø1/4	ø5/32	ø1/4	ø5/32	ø1/4
56	•				•			
57		•			•			
58		•				•		
68			•				•	
69				•			•	
70				•				•
75	•						•	
76		•					•	
77		•						•
82			•		•			
83				•	•			
84				•		•		





Note) Use caution to ensure the connector is not disturbed, depending on piping direction, when choosing to attach a digital pressure switch

2. Accessories

Symbol	None	Bracket	Note 2) Pressure gauge	Panel nut
Nil	•			
В		•		(●)
G			•	
Р				•
BG		•	•	(●)
GP			•	•
	, .			





Note 2) Pressure display means a pressure gauge or digital pressure switch is attached

When choosing to attach a digital pressure switch is chosen for attachment, be sure to enter the symbol, referring to table 5, "Digital Presure Switch Output Specifications". Otherwise, a pressure gauge will come with the regulator. Additionally, pressure gauges are not compatible with copper-free and fluorine-free specifications

3. Semi-standard

Symbol	None	0.35 MPa setting Note 1)	Non- relieving	Note 2) Oil-free
Nil	•	J J		
1		•		
2			•	
3				•
4		•	•	
5		•		•
6			•	•
7		•	•	•

Note 1) A pressure gauge with a full span of 0.4 MPa is attached. Note 2) The oil-free specification is grease-free in the fluid contact area

4. Unit Representation

Symbol	Description
Nil	Display unit for product name plate and pressure gauge: MPa
Z Note 1, 2)	Display unit for product name plate and pressure gauge: psi
7∆ Note 1, 3)	Digital pressure switch: with unit switching (MPa is initially set.)

Note 1) This option is available for use outside Japan only. (The SI unit has to be used in Japan.) Additionally, the pressure switch offers dual unit presentation in MPa and psi.

Note 2) The digital pressure switch is equipped with unit switching and initially set to

Note 3) This option is available with the digital pressure switch.

A lead wire with connector (2 m) is included.

5. Digital Presure Switch Output Specifications Notes

Symbol	Details
Nil	None
N	NPN open collector
P	PNP open collector


Note) When a digital pressure switch is attached, the "pressure display" in table 2 "Accessories" will be equipped. The electrical entry is positioned on the side opposite the knob.





How to Order











2. IN/OUT Fitting Type

Metric size

Mounting position	IN side			OUT side				
Fitting type	Stra	ight	Elbov	v Note)	Stra	ight	Elbov	v Note)
Symbol	ø4	ø6	ø4	ø6	ø4	ø6	ø4	ø6
06	•				•			
07		•			•			
08		•				•		
18			•				•	
19				•			•	
20				•				•
25	•						•	
26		•					•	
27		•						•
32			•		•			
33				•	•			
34				•		•		

Inch size

Inch Siz	e							
Mounting position	IN side					OUT		
Fitting type			Elbow Note)		Straight		Elbow Note	
Symbol	ø5/32	ø1/4	ø5/32	ø1/4	ø5/32	ø1/4	ø5/32	ø1/4
56	•				•			
57		•			•			
58		•				•		
68			•				•	
69				•			•	
70				•				•
75	•						•	
76		•					•	
77		•						•
82			•		•			
83				•	•			
84				•		•		

Note) Use caution to ensure the connector is not disturbed, depending on piping direction, when choosing to attach a digital pressure switch.

Panel nut

3. Accessories

Symbol	None	Bracket	Pressure display	Panel nut	Decorative cover
Nil	•				
В		•		(●)	
G			•		
BG		•	•	(●)	
GP			•	•	
GPC Note 4)			•	•	•

Note 1) In case of a type with bracket, the panel nut is included.

Note 2) Pressure display means a pressure gauge or digital pressure switch is attached.

When choosing to attach a digital pressure switch is


When choosing to attach a digital pressure switch is chosen for attachment, be sure to enter the symbol, referring to table 6, "Digital Presure Switch Output Specifications". Otherwise, a pressure gauge will come with the regulator.

Additionally, pressure gauges are not compatible with copper-free and fluorine-free specifications.

Note 3) Not attachable to a model with digital pressure switch.

Note 4) Please note that the dimensions will be bigger when GPC is selected.









4. Semi-standard

Symbol	None	0.35 MPa setting Note 1)	Non- relieving	Note 2) Oil-free
Nil	•			
1		•		
2			•	
3				•
4		•	•	
5		•		•
6			•	•
7		•	•	•

Note 1) A pressure gauge with a full span of 0.4 MPa is attached. Note 2) The oil-free specification is grease-free in the fluid contact area.

5. Unit Representation

Symbol	Description
Nil	Display unit for product name plate and pressure gauge: MPa
Z Note 1, 2)	Display unit for product name plate and pressure gauge: psi
ZA Note 1, 3)	Digital pressure switch: with unit switching (MPa is initially set.)

Note 1) This option is available for use outside Japan only. (The SI unit has to be used in Japan.)

Note 2) The digital pressure switch is equipped with unit switching and initially set to

Note 3) This option is available with the digital pressure switch.

A lead wire with connector (2 m) is included.


6. Digital Presure Switch Output Specifications Note)

Symbol	Details
Nil	None
N	NPN open collector
P	PNP open collector

Note) When a digital pressure switch is attached, the "pressure display" in table 3 "Accessories" will be equipped.

The electrical entry is positioned on the side opposite the knob.

Specifications



Note 1) 0.1 MPa or greater set pressure is required when used in the reverse flow. Note 2) 5 to 50°C when the digital pressure switch will be used.

Refer to page 1018 for the digital pressure switch specifications.

Symbol Relieving type Non-relieving type

Note) A standard model is equipped with a backflow function. Main valve opens when the inlet pressure is released, and then the outlet pressure backflows into the inlet side.

⚠ Specific Product Precautions

Be sure to read this before handling the products.

Refer to page 9 for safety instructions and pages 13 to 17 for precautions on every series.

Maintenance


⚠ Warning


1. Make sure to perform a periodic inspection of the pressure gauge when the compact manifold regulator is installed between a solenoid valve and an actuator. Sudden pressure changes could happen and the durability of the product could be reduced. Using an electronic type pressure gauge is recommended, depending on the situation.





ARM10 Series


Flow Rate Characteristics (Representative Values)

















Pressure Characteristics (Representative Values)






Regulator Single Unit Type **ARM10** Series

Construction





Component Parts


No.	Description	Material
1	Body	PBT
2	Bonnet	PBT
3	Knob	POM
4	Valve seat	POM
5	Adjusting screw assembly	Reinforced steel
6	Adjustment spring	Steel wire
7	Regulator clip	Stainless steel
8	Blanking plate assembly	_
9	Square nut	Steel

Replacement Parts

<u> </u>				
No.	Description	Material	Part no.	Note
Α	Diaphragm	Weatherproof	136126A	Relieving type
^	assembly	NBR, POM	136126-1A	Non-relieving type
В	Valve	HNBR, Aluminum alloy	136127-30#1	
С	Valve spring	Stainless steel	136131	
D	O-ring	NBR	136146	Standard model
U	O-ring	HNBR	136146-30	Oil-free specification
Е	O rime	NBR	136147	Standard model
-	O-ring	HNBR	136147-30	Oil-free specification
		NBR	136148	Standard model
F	O-rina	HNBR	136148-30	Oil-free specification
Г	O-ring	NBR	KA01731	Standard model for digital pressure switch
		HNBR	KA01613	Oil-free spec. for digital pressure switch
G	Fitting assembly	_	Refer to page 1029.	

Dimensions

 $ARM10-_{08}^{06}$




For dimensions and accessories of One-touch fittings, please refer to page 1029.

1027


ARM10 Series

Dimensions

ARM10F1- $^{06}_{08}$




ARM10F1-06GPC



Panel cutout dimensions

4 x R1 or less




Regulator/Single Unit Type Options


Pressure Gauge

Part no.	Pressure gauge indication range	Indication unit
GC3-4A-X2101	0 to 0.4 MPa	MPa
GC3-10A-X2101	0 to 1.0 MPa	IVIPA
GC3-P4A-X2104	0 to 0.4 MPa (60 psi)	MDa/asi
GC3-P10A-X2104	0 to 1.0 MPa (150 psi)	MPa/psi

Specifications

Display accuracy	±3% F.S. (Full Span)	
Calibration angle	230°	
Limit indicator	With limit indicator	
Weight	17 g	






Digital Pressure Switch

Refer to page 1018.

Panel Nut

Part no.	136133
Material	POM
Weight	1 g
	•




Decorative Cover


Part no.	136155
Material	PBT
Weight	0.5 g




One-touch Fittings for Regulator



ARM10



Fitting size	Х
ø4, ø5/32	2
ø6	2
ø1/4	6



Fitting size	Х	Υ
ø4, ø5/32	10.5	21.5
ø6	10.5	22
ø1/4	10.5	24.5

ARM10F

Straight type



Fitting size	Х
ø4, ø5/32	7
ø6	7
ø1/4	11


Elbow type



Fitting size	Х	Υ
ø4, ø5/32	15.5	21.5
ø6	15.5	22
ø1/4	15.5	24.5

Bracket

	136134#1
Material Ste	el band (Zinc chromated)
Weight	17 g



ARM10F Series

Made to Order Specifications:

contact SMC for detailed dimensions, specifications and lead times



Regulator Single Unit Front Knob Type/ For Manifold

Specifications

Regulator construction		Direct acting
Working principal		Diaphragm regulator
Relief mechanism	Standard	Relief type
neller illectialistii	Optional	Non-relieving type
Backflow function		Within (Unbalance type)
IN/OUT air passage diameter		ø4
IN/OUT gasket sealing O.D.		ø7
Proof pressure		1.5 MPa
Maximum operating pressure		1.0 MPa
Set pressure range	Standard	0.05 to 0.7 MPa
Set pressure range	Optional	0.05 to 0.35 MPa (Low pressure type)
Fluid		Air
Ambient and fluid temperature		5 to 60°C
Weight		73 g



Note 1) Two mounting bolts and two O-rings are attached.

Note 2) 0.1 MPa or greater set pressure is required when used in the reverse flow


Note 3) 5 to 50°C when the digital pressure switch will be used. Refer to page 1018 for the digital pressure switch

a digital pressure switch.

0.35 MPa setting Note 1) Non-relieving Oil-free Note 2)

•

How to Order



1. Accessory (Pressure Display)

Enter symbol for when the model requires			
Symbol	Accessory		
Nil	Without pressure display		
A With pressure displ			

Note 1) Pressure display means a pressure gauge or digital pressure switch is attached. When choosing to attach a digital pressure switch is chosen for attachment, be sure to enter the symbol, referring to table 4, "Digital Pressure Switch Output Specifications". Otherwise, a pressure gauge will come with the regulator.

Note 2) Pressure gauges are not compatible with copper-free and fluorine-free specifications.

Note 1) A pressure gauge with a full span of 0.4 MPa is attached Note 2) The oil-free type has non-greased fluid contact areas

3. Unit Representation

Symbol	Description
Nil	Display unit for product name plate and pressure gauge: MPa
Z Note 1, 2)	Display unit for product name plate and pressure gauge: psi
ZA Note 1, 3)	Digital pressure switch: with unit switching (MPa is initially set.)

Note 1) This option is available for use outside Japan only. (The SI unit has to be used in Japan.)

Note 2) The digital pressure switch is equipped with unit switching and initially set to psi.

Note 3) This option is available with the digital pressure switch.

Example



4. Digital Presure Switch Output Specifications Note)

Symbol	Details	
Nil	None	
N	NPN open collector	
Р	PNP open collector	

Note) When a digital pressure switch is attached, the "pressure display" in table 1 "Accessory" will be equipped.

The electrical entry is positioned on the side opposite the knob.

Dimensions


2. Semi-standard

Symbol Nil 2 3

4

5 6

1030









ARM10/11 Series Blocks/Specific Product Precautions 1

Be sure to read this before handling the products.

Refer to page 9 for safety instructions and pages 13 to 17 for precautions on every series.

Handling


⚠ Warning

Observe the proper screw tightening torque in installation.

Tightening beyond the proper tightening torque may damage the mounting screws, blocks or switches.

If the force is below the tightening torque range, the threaded joint can come loose.

 Tightening torque for fixing screws and panel nuts of a single unit regulator



2. Tightening torque for regulator assembly fixing screws on regulator block



3. Tightening torque for blanking plates and pressure gauge fixing screws on regulator block



 Tightening torque for pressure switch fixing screws on common supply block with pressure switch and pressure switch block



5. Tightening torque for DIN rail clamp screws on end block $$1.5\pm0.15~\text{N}{\cdot}\text{m}$$



Digital Pressure Switch

Mount it with the proper screw-tightening torque.


Overtightening may damage the regulator body or adaptor, etc. Meanwhile, insufficient tightening may loosen the connecting threads.

- 1. Attach an O-ring to the regulator O-ring slit.
- Attach the adaptor with the 2 set screws by positioning the adapter slot on the opposite side of the knob and keeping the 2 square nuts (right/left) attached.

Tightening torque: $0.32 \pm 0.03 \text{ N} \cdot \text{m}$

- 3. Attach the switch body.
- 4. Fully insert the locking pin into the adapter slot.

The switch body can be replaced by attaching/removing the locking pin.







ARM10/11 Series Blocks/Specific Product Precautions 2

Be sure to read this before handling the products.

Refer to page 9 for safety instructions and pages 13 to 17 for precautions on every series.

Handling

⚠ Warning

Mounting and Removal of Manifold with DIN Rail


Be sure to shut off the power and air supplies before disassembly. Furthermore, since air may remain inside the actuator, piping and manifold, confirm that the air is completely exhausted before performing any work.

When disassembly and assembly are performed, air leakage may result if connections between blocks and tightening of the end block's holding screw are inadequate.

Before supplying air, confirm that there are no gaps between blocks, and that manifold blocks are securely fastened to the DIN rail. Then supply air and confirm that there is no air leakage before operating.


Removing blocks from DIN rail

- Loosen the end plate clamping screws on the side until they turn freely. (The screws do not come out.)
- Remove it by sliding it to the side (in the direction of the arrow).




Mounting blocks on DIN rail

- Confirm that the clamping screws of the end block on one side are securely tightened.
- Install blocks sliding them from the side. Push the end plate on the opposite side so that there will be no gap between blocks.
- 3. Tighten the end plate clamping screws on the opposite side.



Confirming DIN rail clasp


Confirm that the DIN rail clasps are securely hooked into the DIN rail.



One-touch fitting replacement

For the ease of replacement, One-touch fittings are installed as the cassette type. One-touch fittings are retained with clips inserted from the directions illustrated blow. Remove the clips with a flat head screw driver to replace the One-touch fittings. When installing, insert each One-touch fitting deeply to the end and reinsert the clip to the specified position.

1. Single unit regulator



2. Regulator block




3. Various common supply blocks



Pressure supply of 3-way valve common supply block

Make sure that the knob is set at the OPEN or SHUT position in operation. The block cannot be used for the purpose of containing pressure because it allows a small amount of leakage.





ARM10/11 Series Blocks/Specific Product Precautions 3

Be sure to read this before handling the products. Refer to page 9 for safety instructions and pages 13 to 17 for precautions on every series.


Handling

 Digital Pressure Switch How to attach a connector

Insert the connector vertically onto the pins, pinching the lever and connector with your fingers. Insert the lever into the switch body slot until it is locked. Cover the connector with a cover.

How to remove a connector

Displace the cover and pull the lever straight forward by pushing its claw to remove it from the slot.



Adjustment

⚠ Caution


How to adjust indicator of the pressure gauge.

Make sure to follow the instruction when opening the lens cover to adjust the pressure gauge.

1. Open the lens cover to the arrow's direction with finger nail.



2. Adjust the gauge needle with for example, a flat head screw



Close the lens cover to the arrow's direction until it snaps on.





ARM10/11 Series Pressure Switch Blocks Specific Product Precautions

Be sure to read this before handling the products.

Refer to page 9 for safety instructions and pages 13 to 17 for precautions on every series.

Design & Selection

1. Operate the switch only within the specified voltage.

Use of the switch outside the range of the specified voltage can cause malfunction and damage to the switch, it may also increase the risks of electrical shocks or fire.

- Never apply a load above the maximum load capacity. It can damage the switch or shorten the service life.
- Be sure to observe the set pressure range and maximum operating pressure.

Use of the switch outside the set pressure range can cause failure and use beyond the maximum operating pressure can damage the switch.

 When operating at an inlet pressure lower than the inlet pressure used in the flow rate characteristics graph, the pressure drop on the outlet side may be greater. Therefore, be sure to conduct testing using the actual equipment.

For pressure control equipment selection, refer to the "Product Selection Guide."

Mounting

.⚠Warning

 Do not use the switch unless the equipment operates normally.

After installation, repair or reform, connect air and electricity and conduct appropriate function and leakage tests to confirm proper installation.

2. Do not apply a tensile force to a cord.

Be sure to hold the body to handle the product.

Applying a tensile force to a cord may cause damage to the product.

3. Do not drop or bump the product.

Dropping or bumping while handling may cause damage to the product.

Pressure Supply

1. Do not use the switch with corrosive gas or liquid.

Do not use the switch with corrosive gas or liquid. Such gas or fluid may cause damage to the switch.

2. Do not use the switch at a vacuum pressure.

If used in a vacuum pressure range, the switch will suction the outer air and become unable to operate.

Pressure Setting

⚠ Caution

- The switching setting indication scale shows the set value for pressure decrease.
- When the ON pressure signal is to be detected, the ON signal comes on at the pressure found by adding the hysteresis to the pressure set on the scale plate.
- The pressure indication on the scale plate is provided as a guideline. Use a pressure gauge to measure the precise settings.

Wiring

⚠ Warning

1. Connect the load


Be sure to connect the load to the pressure switch before connecting the power supply.

2. Use a contact protection box.

If the load driven by the pressure switch is an induction load or connected with a lead wire of 5 m or longer, use a contact protection box in the following table.

Contact protection box	Operating voltage	Lead wire length
CD-P11 100 VAC		Switch connection side: 0.5 m
CD-P12	24 VDC	Load connection side: 0.5 m

3. Contact protection box internal circuit



4. Contact protection box/Connection method

To connect the switch body and the contact protection box, connect the lead wire of the contact protection box on the side marked with "SWITCH" and the lead wire from the switch body. Connect the switch body and the contact protection box with a lead wire of 1 m or shorter and arrange them as close as possible.

5. Lead wire dimensions

Covering: ø3.4 Insulator: ø1.1 Conductor: ø0.64

Operating Environment

⚠ Warning

1. Never use in the presence of explosive gases.

These switches are not rated as explosion proof. Never use in the presence of an explosive gas as this may cause a serious explosion.

Do not use in an environment where a strong magnetic field is present.

The influence of the external magnetic filed may cause the switch to malfunction.

Do not use in an environment where the switch is exposed to water or oil splashes.

Because the switch has an open type construction, ingress of water or oil can corrode the electric circuit, resulting in malfunction and damage.

4. Do not apply vibration to the switch.

If vibration is applied, malfunction or setting errors may result.