Process Pump

PA3000/5000 Series

Automatically Operated Type (Internal Switching Type)/Air Operated Type (External Switching Type)



High abrasion resistance and low particle generation

Air operated type

No sliding parts in wetted areas.

Self-priming makes priming unnecessary

Exhausts the air inside the suction pipe to suck up liquid.

Automatically operated type

Compatible with a wide variety of fluids

PA3000: Max. discharge rate 20 L/min


PA5000: Max. discharge rate 45 L/min

• Easily control the discharge rate.


Control with external switching valve

makes constant cycling possible

- Easily adjust the flow with the external solenoid valve's ON/OFF cycle.
- Easy to operate, even for minute flow, low press operation or operation involving air.



Application Example




Process Pump Automatically Operated Type (Internal Switching Type) Air Operated Type (External Switching Type)

PA3000 Series



How to Order



Specifications

Model		PA3110	PA3120	PA3210	PA3220	PA3113	PA3213	
Actuation		Automatically operated				Air operated		
Port size		Rc, NPT, G, NPTF 3/8" Female thread						
FOILSIZE	Pilot air supply/exhaust port	Rc, NPT, G, NPTF 1/4" Female thread						
Body wetted areas		AD	C12	SC	S14	ADC12	SCS14	
Material	Diaphragm	PTFE	NBR	PTFE	NBR	PT	FE	
	Check valve			PTFE	, PFA			
Discharge	e rate		1 to 20) L/min		0.1 to 1	2 L/min	
Average of	discharge pressure		0 to 0.	6 MPa		0 to 0.	4 MPa	
Pilot air pressure			0.2 to 0	.7 MPa		0.1 to 0	.5 MPa	
Air consumption		Max. 200 L/min (ANR) or less				Max. 150 L/min (ANR) or less		
Suction ^{Note 1)}	Dry	1 m (Interior of pump dry))			
range	Wet		Up to 6 m (liquid inside pum			ıp)		
Noise		80 dB (A) or less (Option: with silencer, AN20)				72 dB (A) or less (excluding the noise from the quick exhaust and solenoid valve)		
Withstand	l pressure	1.05 MPa					MPa	
Diaphrag	m life	100 million times 50 million times 100 million times 50 million times 50 million times					on times	
Fluid tem	perature	0 to 60°C (No freezing)						
Ambient t	emperature	0 to 60°C (No freezing)						
Maximum	viscosity	1000 mPa·s						
Recommended operating cycle		_			1 to 7 Hz (0.2 to 1 Hz also possible depending on conditions) Note 2)			
Pilot air solenoid valve Note 3) recommended Cv factor		_			0.:	20		
Weight		1.7	kg	2.2	kg	1.7 kg	2.2 kg	
Mounting	orientation	Horizontal (with mounting foot at bottom)						
Packagin	g	General environment						
* Each of th	e values above are t	for normal temperatures and when the transferred fluid is fresh water.						

* Each of the values above are for normal temperatures and when the transferred fluid is fresh water.

* Refer to page 558 for maintenance parts.


* For related products, refer to pages 622 and 623.


Note 1) With cycles at 2 Hz or more

Note 2) After initial suction of liquid operating at 1 to 7 Hz, it can be used with operation at lower cycles.

Since a large quantity of liquid will be pumped out, use a suitable throttle in the discharge port if problems occur. Note 3) With a low number of operating cycles, even a valve with a small Cv factor can be operated.










Made to order specifications (For details, refer to pages 563 and 564)

Products complying with ATEX				
With air operated reset port Note)				
With operating cycle counting port Note)				

Note) For automatically operated type only.









PA3 0 Flow Bate Characteristics

Performance Curve: Automatically Operated Type

A new type of PA5000 with a polypropylene body is now available. Click here for details.



PA5 0 Flow Rate Characteristics



Selection from Flow Rate Characteristic Graph (PA3 0)

Required specifications example

Find the pilot air pressure and pilot air consumption for a discharge rate of 6 L/min and a discharge pressure of 0.25 MPa. <The transfer fluid is fresh water (viscosity 1 mPa·s, specific gravity 1.0).>

* If the total lifting height is required instead of the discharge pressure, a discharge pressure of 0.1 MPa corresponds to a total lift of 10 m.


Selection procedures:

1. First mark the intersection point for a discharge rate of 6 L/min and a discharge pressure of 0.25 MPa.

- 2. Find the pilot air pressure for the marked point. In this case, the point is between the discharge curves (solid lines) for SUP = 0.3 MPa and SUP = 0.4 MPa, and based on the proportional relationship to these lines, the pilot air pressure for this point is approximately 0.38 MPa.
- 3. Next find the air consumption rate. Since the marked point is below the curve for 50 L/min (ANR), the maximum rate will be about 50 L/min (ANR).

∆Caution

- 1. These flow rate characteristics are for fresh water (viscosity 1 mPa·s, specific gravity 1.0).
- The discharge rate differs greatly depending on properties (viscosity, specific gravity) of the fluid being transferred and operating conditions (lifting range, transfer distance), etc.
- Use 0.75 kW per 100 L/min of air consumption as a guide for the relationship of the air consumption to the compressor.



Viscosity Characteristics (Flow rate correction for viscous fluids)

Selection from Viscosity Characteristic Graph

Required specifications example:

Find the pilot air pressure and pilot air consumption for a discharge rate of 2.7 L/min, and a viscosity of 100 mPa s. Selection procedures:


- First find the ratio of the discharge rate for fresh water when viscosity is 100 mPa s from the graph below. It is determined to be 45%.
- Next, in the required specification example, the viscosity is 100 mPa.s and the discharge rate is 2.7 L/min. Since this is equivalent to 45% of the discharge rate for fresh water, 2.7 L/min + 0.45 = 6 L/min, indicating that a discharge rate of 6 L/min is required for fresh water.
- Finally, find the pilot air pressure and pilot air consumption based on selection from the flow characteristic graphs.

∆Caution

Viscosities up to 1000 mPa·s can be used. Dynamic viscosity ν = Viscosity $\mu/\text{Density }\rho.$




Performance Curve: Air Operated Type





PA3 13 Flow Rate Characteristics

PA3 13 Air Consumption



PA5 13 Air Consumption






Viscosity Characteristics (Flow rate correction for viscous fluids)

A new type of PA5000 with a polypropylene body is now available. Click here for details.

PA5 13 Flow Rate Characteristics



Selection from Flow Rate Characteristic Graph (PA3 13)

Required specification example: Find the pilot air pressure and pilot air consumption for a discharge rate of 6 L/min. < The transfer fluid is fresh water (viscosity 1 mPa·s, specific gravity 1.0).>

Note 1) If the total lifting height is required instead of the discharge pressure, a discharge pressure of 0.1 MPa corresponds to a total lift of 10 m.

- Selection procedures: 1. First mark the intersection point for a discharge rate of 6 L/min and a discharge pressure of 0.1 MPa
- 2. Find the pilot air pressure for the marked point. In this case, the point is between the discharge curves (solid lines) for SUP = 0.2 MPa and SUP = 0.3 MPa, and based on the proportional relationship to these lines, the pilot air pressure for this point is approximately 0.25 MPa.

- 1. These flow rate characteristics are for fresh water (viscosity 1 mPa·s, specific gravity 1.0).
- The discharge rate differs greatly depending on properties (viscosity, specific gravity) of the fluid being transferred and operating conditions (density, lifting range, transfer distance).

Calculating Air Consumption (PA3 13)

Find the air consumption for operation with a 4 Hz switching cycle and pilot air pressure of 0.3 MPa from the air consumption graph. Selection procedures:

1. Look up from the 4 Hz switching cycle to find the intersection with SUP = 0.3 MPa.

From the point just found, draw a line to the Y-axis to find the air consumption. The result is approximately 50 L/min (ANR).

Selection from Viscosity Characteristic Graph

Required specification example: Find the pilot air pressure and pilot air consumption for a discharge rate of 2.7 L/min, and a viscosity of 100 mPa-s.

Selection procedures:

- 1. First find the ratio of the discharge rate for fresh water when viscosity is 100 mPa-s from the graph below. It is determined to be 45%
- Next, in the required specification example, the viscosity is 100m Pa-s and the discharge rate is 2.7 L/min. Since this is equivalent to 45% of the discharge rate for fresh water, 2.7 L/min \div 0.45 = 6 L/min, indicating that a discharge rate of 6 L/min is required for fresh water.
- 3. Finally, find the pilot air pressure and pilot air consumption based on selection from the flow characteristic graphs.

∧ Caution


Viscosities up to 1000 mPa·s can be used. Dynamic viscosity $v = Viscosity \mu/Density \rho$. $v = \frac{\mu}{\rho}$

SMC

 $v(10^{-3} \text{ m}^2/\text{s}) = \mu(\text{mPa}\cdot\text{s})/\rho(\text{kg/m}^3)$

Working Principle






- 1. When air is supplied, it passes through the switching valve and enters drive chamber B.
- 2. Diaphragm B moves to the right, and at the same time diaphragm A also moves to the right pushing pilot valve A.
- When pilot valve A is pushed, air acts upon the switching valve, drive chamber A switches to a supply state, and the air which was in drive chamber B is exhausted to the outside.
- 4. When air enters drive chamber A, diaphragm B moves to the left pushing pilot valve B.
- 5. When pilot valve B is pushed, the air which was acting upon the switching valve is exhausted, and drive chamber B once again switches to a supply state. A continuous reciprocal motion is generated by this repetition.

Drive unit

- 1. When air enters drive chamber B, the fluid in pump chamber B is forced out, and at the same time fluid is sucked into pump chamber A.
- 2. When the diaphragm moves in the opposite direction, the fluid in pump chamber A is forced out, and fluid is sucked into pump chamber B.
- 3. Continuous suction and discharge is performed by the reciprocal motion of the diaphragm.



- 1. When air is supplied to P1 port, it enters drive chamber A.
- 2. Diaphragm A moves to the left, and at the same time diaphragm B also moves to the left.
- 3. The fluid in pump chamber A is forced out to the discharge port, and the fluid is sucked into pump chamber B from the suction port.
- 4. If air is supplied to the P2 port, the opposite will occur. Continuous suction and discharge of fluid is performed by repeating this process with the control of an external solenoid valve (5 port valve).

Maintenance Parts

• While it is not possible to disassemble this product without voiding the warranty, if disassembly is to be carried out anyway due to necessity, be sure to follow the maintenance procedures.
• When carrying out this work, wear appropriate protective equipment.

PA3000/5000 Series

Description		PA3000 series		PA5000 series		
Description	PA3□10	PA3□20	PA3□13	PA5□10	PA5□20	PA5□13
Diaphragm kit	KT-PA3-31	KT-PA3-32	KT-PA3-31	KT-PA5-31	KT-PA5-32	KT-PA5-31
Check valve kit	KT-PA3-36			KT-PA5-36		
Switching valve assembly kit	KT-PA3-37 Note) -			_		
Switching valve parts kit —		-		KT-P.	A5-37	—
Pilot valve kit	KT-PA5-38		—	KT-PA5-38 —		-
Manual cap assembly kit	KT-PA3-45		_	KT-PA5-45 —		_


Note) One of Nil, N, F or T is entered as a thread symbol.



Process Pump **PA** Series

Piping and Operation: Automatically Operated Type

A new type of PA5000 with a polypropylene body is now available. Click here for details.



▲ Caution

Mounting posture of the pump is set with the mounting bracket facing downward. Air to be supplied to the air supply port <AIR SUP> should be cleaned and filtered through AF filter, etc. Air with foreign matter or drainage etc. will have negative effects on the built-in directional control valve and will lead to malfunction. When air needs additional purification, use a filter (AF series), and a mist separator (AM series) together.

Maintain the proper tightening torque for fittings and mounting bolts, etc. Looseness can cause problems such as fluid and air leaks, while over tightening can cause damage to threads and parts, etc.

Operation

<Starting and Stopping> Refer to circuit example (1)

- 1. Connect air piping to the air supply port <AIR SUP> and connect piping for the fluid to be transferred to the suction port <FLUID IN> and the discharge port <FLUID OUT>.
- 2. Using a regulator, set the pilot air pressure within the range of 0.2 to 0.7 MPa. Then, the pump operates when power is applied to the 3 port solenoid valve of the air supply port <AIR SUP>, the sound of exhaust begins from the air exhaust port <AIR EXH> and fluid flows from the suction port <FLUID IN> to the discharge port <FLUID OUT>.


At this time, the throttle on the discharge side is in an open state. The pump performs suction with its own power even without priming. (Dry state suction lifting range: max. 1 m) To restrict exhaust noise, attach a silencer (AN20-02: option) to the air exhaust port <AIR EXH>.

3. To stop the pump, exhaust the air pressure being supplied to the pump by the 3 port solenoid valve of the air supply port <AIR SUP>. The pump will also stop if the throttle on the discharge side is closed.

<Discharge Flow Rate Adjustment>

- 1. To adjust the flow rate from the discharge port <FLUID OUT>, use the throttle connected to the discharge side. Refer to circuit example (1). Note that this product cannot be used as a fixed quantity liquid dispense pump.
- 2. When operating with a discharge flow rate below the specification range, provide a by-pass circuit from the discharge side to the suction side to ensure the minimum flow rate inside the process pump. With a discharge flow rate below the minimum flow rate, the process pump may stop due to unstable operation. Refer to circuit example (2). (Minimum flow rates: PA3000 1 L/min, PA5000 5 L/min) <Reset Button>


When the pump stops during operation, press the reset button. This makes it possible to restore operation in case the switching valve becomes clogged due to foreign matter in the supply air.





Piping and Operation: Air Operated Type

A new type of PA5000 with a polypropylene body is now available. Click here for details.




▲ Caution

Maintain the proper tightening torque for fittings and mounting bolts, etc. Looseness can cause problems such as fluid and air leaks, while over tightening can cause damage to threads and parts, etc.


Operation

<Starting and Stopping> Refer to circuit example


- Connect air piping Note 1) to the pilot air supply port <P1>, <P2> and connect piping for the fluid to be transferred to the suction port <FLUID IN> and the discharge port <FLUID OUT>.
- 2. Using a regulator, set the pilot air pressure within the range of 0.1 to 0.5 MPa. Then, the pump operates when power is applied to the solenoid valve ^{Note 2}) of the pilot air supply port and fluid flows from the suction port <FLUID IN> to the discharge port <FLUID OUT>. At this time, the throttle on the discharge side is in an open state. The pump performs suction with its own power even without priming. (Dry state suction lifting range: PA3 1 m, PA5 up to 0.5 m ^{Note 3}) To restrict exhaust noise, attach a silencer to the solenoid valve air exhaust port.
- 3. To stop the pump, exhaust the air pressure being supplied to the pump with the solenoid valve of the air supply port.
- Note 1) When used for highly permeable fluids, the solenoid valve may malfunction due to the gas contained in the exhaust. Implement measures to keep the exhaust from going to the solenoid valve side.
- Note 2) For the solenoid valve, use an exhaust center 5 port valve, or a combination of residual exhaust 3 port valve and a pump drive 4 port valve. If air in the drive chamber is not released when the pump is stopped, the diaphragm will be subjected to pressure and its life will be shortened.
- Note 3) When the pump is dry, operate the solenoid valve at a switching cycle of 1 to 7 Hz. If operated outside of this range, the suction lifting height may not reach the prescribed value.
- <Discharge Flow Rate Adjustment>
- 1. The flow rate from the discharge port <FLUID OUT> can be adjusted easily by changing the switching cycle of the solenoid valve on the air supply port.




Dimensions



PA3 13/Air Operated Type






SMC

PA3000/5000 Series Made to Order Specifications



Please contact SMC for detailed dimensions, specifications and lead times.



Cumbal	Disphysom motorial	Operating method		
Symbol	Diaphragm material Automatically operated		Air operated	
1	PTFE	•	•	
2	NBR	•	_	

* Dimensions are the same as those of the standard products.

	Actuation	•
Iodr	Actuation	

Symbol	Actuation
0	Automatic operation
3	Air operated

Thread type

03

04

06

3/8

1/2

3/4

.


.

.

Symbo	I Type
Nil	Rc
N	NPT
F	G
т	NPTF

PA3000/5000 Series

A new type of PA5000 with a polypropylene body is now available. Click here for details.




§ 564

⊘SMC

Process Pump PA(P)3000 Series Fluororesin Type



With the use of New PFA for body material,



Variations							
M	odel	Body material	Diaphragm material	Assembly environment	Discharge rate (L/min)	Option	
Automatically	PA3310			Standard	1 to 13*	•Foot	
operated type	PAP3310			Clean room	1 10 13	•Silencer	
Air pilot	PA3313	New PFA	PTFE	Standard	0.1 to 9	. Ea at	
operated type	PAP3313			Clean room	0.110.9	•Foot	

*With 3/8" inlet/outlet tube:1 to 12

high corrosion resistance is achieved!*

* Refer to the "Material and Fluid Compatibility Check List for Process Pumps" on page 624. It is your responsibility to check the suitability for your workpiece and equipment.

Clean

You can order your process pump assembled in a Clean room environment and double-packaged (Order number PAP331).


Side bodies and ports are molded to achieve a great reduction in dust generation.

PA
PA(P)
PAX
PB
PAF
PA□ PB

now a standard feature.

When the pump is used in an environment where manual reset is not possible, designing a circuit as the one shown below allows the use of air pressure for reset purposes.


With the use of an air pilot actuation reset circuit, resetting can be done by releasing the air pressure after supplying it to the reset port.



Air pilot actuation is standard.

External switching valve control makes constant cycling possible.

- · Discharge rate is easily controlled. The flow rate can be easily adjusted by the number of ON/OFF cycles of the external solenoid valve.
- · Stable operation is possible in spite of such conditions as a minimal flow rate, low pressure operation, or the entrainment of gasses.
- Can be used for operation with repetitive stopping.




Air pilot actuation reset is Compact & Lightweight (Without foot)







Process Pump Clean Room Automatically Operated Type (Internal Switching Type) Air Operated Type (External Switching Type) **PA(P)3000 Series** (RoHS)




Note 1) The port size of the pilot port is 1/4". Note 2) The thread type is applied to the pilot port thread and the female thread piping connection.



Automatically operated type



Process Pump Clean Room Automatically Operated Type/Air Operated Type **PA(P)3000** Series



Note 1) The port size of the pilot port is 1/4".

- Note 2) The thread type is applied to the pilot port thread and the female thread piping connection.
- Note 3) Refer to the pamphlet "High-Purity Fluoropolymer Fittings Hyper Fitting/LQ1, 2 series Work Procedure Instructions" (M-E05-1) for connecting tubing with special tools. (Downloadable from our website.)

PA(P)3000 Series

Specifications

Model		PA3310	PAP3310	PA3313	PAP3313		
Actuation		Automatica	ally operated	Air operated			
		Rc, NPT, G, NPTF 3/8" Female thread		Rc, NPT, G, NPTF 3/8" Female			
	Main fluid suction	Rc, NPT, G, NPTF 3/8"	3/8", 1/2" Tube extension	Rc, NPT, G, NPTF 3/8"	3/8", 1/2" Tube extension		
Port size	discharge port	Female thread	With nut (size 3, 4, 5)	Female thread	With nut (size 3, 4, 5)		
			3/8", 1/2" Integrated fitting type		3/8", 1/2" Integrated fitting type		
	Pilot air supply/exhaust port		Rc, NPT, G, NPTF	1/4" Female thread			
	Body wetted areas		New	PFA			
Material	Diaphragm		PT	FE			
	Check valve		PTFE, N	ew PFA			
Discharge	rate	1 to 13 l	_/min ^{Note)}	0.1 to 9	9 L/min		
Average discharge pressure		0 to 0.4 MPa					
Pilot air pr	essure	0.2 to 0.5 MPa					
Pilot air co	onsumption	140 L/min (ANR) or less					
Suction	Dry	0.5 m (Interior of pump dry)					
lifting range	Wet	Up to 4 m (liquid inside pump)					
Noise		80 dB (A) or less (Option: with silencer, AN20) 75 dB (A) or less (excluding the noise from the quick exhaust and solenoid values of the second secon					
Withstand	pressure	0.75 MPa					
Diaphragm	n life	50 million times					
Fluid temp	erature	0 to 100°C (No freezing, heat cycle not applied)					
Ambient te	emperature	0 to 100°C (No freezing, heat cycle not applied)					
Maximum	viscosity	1000 mPa·s					
Recommend	ded operating cycle	— 2 to 4 Hz					
Weight		2.1 kg (without foot)					
Mounting of	orientation	Horizontal (with mounting foot at bottom)					
Packaging		General environment	Clean double packaging	General environment	Clean double packaging		

* Each value of above represents at normal temperatures with fresh water.

* For related products, refer to pages 622 and 623 Note) The discharge rates for PAP3310-P11, PAP3310S-IIS11, PAP3310S-IIS1113, PAP3310S-IIS111, PAP3310-S11 are between 1 to 12 L/min.

Maintenance Parts


•While it is not possible to disassemble this product without voiding the warranty, if disassembly is to be carried out Ŵ anyway due to necessity, be sure to follow the maintenance procedures. OWhen carrying out this work, wear appropriate protective equipment.

PA(P)3000 Series

Description	PA(P)3000 series					
Description	PA3310	PA3313	PAP3310	PAP3313		
Diaphragm kit	KT-PA3-531		KT-PAP3-531			
Check valve kit	KT-PA3-536#1		KT-PAP3-536#1			
Pilot valve kit	КТ-РАЗ-538 —		KT-PA3-538	—		
Manual cap assembly kit	KT-PA3-545		KT-PA3-545			
Foot kit	KT-PA3-40		KT-PAP3-40			

* The maintenance procedure is to be distributed individually. Please contact your SMC sales representative for details. Note) One of Nil, N, F or T is entered as a thread symbol.

Performance Curve: Automatically Operated Type



Selection from Flow Rate Characteristic Graph (PAP3310)

Required specifications example:

Find the pilot air pressure and pilot air consumption for a discharge rate of 6 L/min and a discharge pressure of 0.25 MPa. <The transfer fluid is fresh water (viscosity 1 mPa·s, specific gravity 1.0).

* If the total lifting height is required instead of the discharge pressure, a discharge pressure of 0.1 MPa corresponds to a total lift of 10 m.


Selection procedures:

1. First mark the intersection point for a discharge rate of 6 L/min and a discharge pressure of 0.25 MPa.

- 2. Find the pilot air pressure for the marked point. In this case, the point is between the discharge curves (solid lines) for SUP = 0.4 MPa and SUP = 0.5 MPa, and based on the proportional relationship to these lines, the pilot air pressure for this point is approximately 0.43 MPa.
- Next find the air consumption rate. Find the intersection point for a discharge rate of 6 L/min and a discharge curve (solid line) for SUP = 0.43 MP a. Draw a line from this point to the Y axis to determine the air consumption rate. The result should be approx. 58 L/min (ANR).

∆Caution

- 1. These flow rate characteristics are for fresh water (viscosity 1 mPa·s, specific gravity 1.0).
- The discharge rate differs greatly depending on properties (viscosity, specific gravity) of the fluid being transferred and operating conditions (lifting range, transfer distance), etc.
- Use 0.75 kW per 100 L/min of air consumption as a guide for the relationship of the air consumption to the compressor.



Viscosity Characteristics (Flow rate correction for viscous fluids)

Selection from Viscosity Characteristic Graph

Required specifications example:

Find the pilot air pressure and pilot air consumption for a discharge rate of 2.7 L/min, and a viscosity of 100 mPa·s. Selection procedures:

- First find the ratio of the discharge rate for fresh water when viscosity is 100 mPa s from the graph below. It is determined to be 45%.
- 2. Next, in the required specification example, the viscosity is 100 mPa·s and the discharge rate is 2.7 L/min. Since this is equivalent to 45% of the discharge rate for fresh water, 2.7 L/min \div 0.45 = 6 L/min, indicating that a discharge rate of 6 L/min is required for fresh water.
- **3**. Finally, find the pilot air pressure and pilot air consumption based on selection from the flow characteristic graphs.

∆Caution

Viscosities up to 1000 mPa·s can be used. Dynamic viscosity ν = Viscosity $\mu/\text{Density}~\rho.$


$$\begin{split} \nu &= \frac{\mu}{\rho} \\ \nu(10^{-3}\,m^2/s) &= \mu(mPa{\cdot}s)/\rho(kg/m^3) \end{split}$$




PA(P)3000 Series

Performance Curve: Air Operated Type


PAP3313 Flow Rate Characteristics



PAP3313 Air Consumption (2 Hz)



PAP3313 Air Consumption (3 Hz)



Viscosity Characteristics (Flow rate correction for viscous fluids)


Selection from Flow Rate Characteristic Graph (PAP3313)

Required specification example: Find the pilot air pressure for a discharge rate of 6 L/min, a discharge pressure of 0.25 MPa, and a cycle of 4 Hz. <The transfer fluid is fresh water (viscosity 1 mPa·s, specific gravity 1.0).>

Note) If the total lifting height is required instead of the discharge pressure, a discharge pressure of 0.1 MPa corresponds to a total lift of 10 m. Selection procedures:

- First mark the intersection point for a discharge rate of 6 L/min and a discharge pressure of 0.25 MPa.
- Find the pilot air pressure for the marked point. In this case, the point is between the discharge curves (solid lines) for SUP = 0.4 MPa and SUP = 0.5 MPa, and based on the proportional relationship to these lines, the pilot air pressure for this point is approximately 0.45 MPa.

PAP3313 Air Consumption (4 Hz)



Calculating Air Consumption (PAP3313)

Required specifications example:

Find the pilot air consumption for a discharge rate of 6 L/min, a cycle of 4 Hz and a pilot air pressure of 0.25 MPa.

Selection procedures:

- 1. In the graph for air consumption (4 Hz), start at a discharge rate of 6 L/min.
- Mark where this point intersects with the air consumption rate. Based on the proportional relationship between these lines, the intersection point will be between the discharge curves SUP = 0.2 MPa and SUP = 0.3 MPa.
- From the point just found, draw a line to the Y-axis to find the air consumption. The result is approximately 70 L/min (ANR).

∆Caution

- 1. These flow rate characteristics are for fresh water (viscosity 1 mPa·s, specific gravity 1.0).
- The discharge rate differs greatly depending on properties (viscosity, specific gravity) of the fluid being transferred and operating conditions (density, lifting range, transfer distance).

Selection from Viscosity Characteristic Graph

Required specification example: Find the pilot air pressure for a discharge rate of 2.7 L/min, discharge pressure of 0.25 MPa and a viscosity of 100 mPa·s.

Selection procedures:


- First find the ratio of the discharge rate for fresh water when viscosity is 100 mPa s from the graph below. It is determined to be 45%.
- 2. Next, in the required specification example, the viscosity is 100m Pa-s and the discharge rate is 2.7 L/min. Since this is equivalent to 45% of the discharge rate for fresh water, 2.7 L/min + 0.45 = 6 L/min, indicating that a discharge rate of 6 L/min is required for fresh water.
- Finally, find the pilot air pressure and pilot air consumption based on selection from the flow characteristic graphs.

▲Caution

Viscosities up to 1000 mPa-s can be used.

- Dynamic viscosity ν = Viscosity μ /Density ρ .
- $v = \frac{\mu}{\rho}$
- $v(10^{-3} \text{ m}^2/\text{s}) = \mu(\text{mPa}\cdot\text{s})/\rho(\text{kg/m}^3)$

Process Pump Clean Room Automatically Operated Type/Air Operated Type **PA(P)3000** Series



SMC

Process Pump

PAX1000 Series


Automatically Operated Type, Built-in Pulsation Attenuator (Internal Switching Type)

RoHS




Prevents spraying of discharge and foaming in tank

· Space-saving design eliminates separate piping with built-in pulsation attenuator





Process Pump Automatically Operated Type, Built-in Pulsation Attenuator (Internal Switching Type) **PAX1000 Series** (RoHS)



Specifications

N	Nodel	PAX1112	PAX1212	
Actuation		Automatic operation		
Port size	Main fluid suction discharge port	Rc, NPT, G, NPTF 1/4	F, 3/8" Female thread	
Port size	Pilot air supply/ exhaust port	Rc, NPT, G, NPTF	1/4" Female thread	
	Body wetted areas	ADC12	SCS14	
Material	Diaphragm	PT	FE	
	Check valve	PTFE,	SCS14	
Discharge rate		0.5 to 1	0 L/min	
Average disch	arge pressure	0 to 0.	6 MPa	
Pilot air pressu	ire	0.2 to 0.7 MPa		
Air consumption	on	Max. 150 L/min (ANR)		
Suction lifting	Dry	Up to 2 m (Interior of pump dry)		
range	Wet	Up to 6 m (Liquid inside pump)		
Noise		84 dB(A) or less (Option: with silencer, AN20)		
Withstand pres	ssure	1.05	MPa	
Diaphragm life		50 million cycl	es (For water)	
Fluid temperat	ure	0 to 60°C (N	lo freezing)	
Ambient tempe	erature	0 to 60°C (No freezing)		
Maximum visc	osity	1000 mPa·s		
Weight		2.0 kg	3.5 kg	
Mounting posi	tion	Horizontal (Bottom facing down)		
Packaging		General environment		

* Each of the values above are for normal temperatures and when the transferred fluid is fresh water.


* Refer to page 577 for maintenance parts.

* Refer to pages 622 and 623 for related products.




PAX1000 Series

Performance Curve: Automatically Operated Type, Built-in Pulsation Attenuator



Viscosity Characteristics (Flow rate correction for viscous fluids)



Pulsation Attenuating Capacity



Required specification example:

Find the pilot air pressure and pilot air consumption for a discharge rate of 6 L/min and a discharge pressure of 0.25 MPa. <The transfer fluid is fresh water (viscosity 1 mPa·s, specific gravity 1.0).>

- * If the total lifting height is required instead of the discharge pressure. a discharge pressure of 0.1 MPa corresponds to a total lift of 10 m.
- 1. First mark the intersection point for a discharge rate of 6 L/min and a discharge pressure of 0.25 MPa.
- 2. Find the pilot air pressure for the marked point. In this case, the point is between the discharge curves (solid lines) for SUP = 0.2 MPa and SUP = 0.5 MPa, and based on the proportional relationship to these lines, the pilot air pressure for this point is approximately 0.45 MPa.
- 3. Next find the air consumption. Since the marked point is below the curve for 50 L/min (ANR), the maximum rate will be about 45 L/min (ANR).

Caution

- 1. These flow rate characteristics are for fresh water (viscosity 1 mPa·s, specific gravity 1.0).
- 2. The discharge rate differs greatly depending on properties (viscosity, specific gravity) of the fluid being transferred and operating conditions (lifting range, transfer distance), etc.
- 3. Use 0.75 kW per 100 L/min of air consumption as a guide for the relationship of the air consumption to the compressor.

Selection from Viscosity Characteristic Graph

Required specification example

Find the pilot air pressure and pilot air consumption for a discharge rate of 2.7 L/min, a discharge pressure of 0.25 MPa, and a viscosity of 100 mPa-s

Selection procedures


- 1. First find the ratio of the discharge rate for fresh water when viscosity is 100 mPa.s from the graph below. It is determined to be 45%.
- 2. Next, in the required specification example, the viscosity is 100 mPa s and the discharge rate is 2.7 L/min. Since this is equivalent to 45% of the discharge rate for fresh water, 2.7 L/min \div 0.45 = 6 L/min, indicating that a discharge rate of 6 L/min is required for fresh water
- 3. Finally, find the pilot air pressure and pilot air consumption based on selection from the flow characteristic graphs.

A Caution

Viscosities up to 1000 mPa-s can be used. Dynamic viscosity $v = Viscosity \mu/Density \rho$.


$$v = \frac{\mu}{\rho}$$

 $v(10^{-3}m^2/s) = \mu(mPa \cdot s)/\rho(kg/m^3)$



The process pump generates pulsation because it discharges a liquid using two diaphragms. The pulsation attenuator absorbs pressure when discharge pressure increases, and compensates the pressure when discharge pressure decreases. By this means pulsation is controlled. @SMC





Working Principle: Automatically Operated Type, Built-in Pulsation Attenuator

Control unit

- 1. When air is supplied, it passes through the switching valve and enters drive chamber B.
- 2. Diaphragm B moves to the right, and at the same time diaphragm A also moves to the right pushing pilot valve A.
- When pilot valve A is pushed, air acts upon the switching valve, drive chamber A switches to a supply state, and the air which was in drive chamber B is exhausted to the outside.
- 4. When air enters drive chamber A, diaphragm B moves to the left pushing pilot valve B.
- 5. When pilot valve B is pushed, the air which was acting upon the switching valve is exhausted, and drive chamber B once again switches to a supply state. A continuous reciprocal motion is generated by this repetition.

Drive unit

- 1. When air enters drive chamber B, the fluid in pump chamber B is forced out, and at the same time fluid is sucked into pump chamber A.
- 2. When the diaphragm moves in the opposite direction, the fluid in pump chamber A is forced out, and fluid is sucked into pump chamber B.
- 3. The pressure of the fluid that is forced out of the pump chamber is adjusted in the pulsation attenuation chamber and is then exhausted.

4. Continuous suction/discharge is performed by the reciprocal motion of the diaphragm.

Pulsation attenuation chamber

- 1. Pulsation is attenuated by the elastic force of the diaphragm and air in the pulsation attenuation chamber.
- When the pressure in the pulsation attenuation chamber rises, the change lever presses the pulsation attenuator intake valve, and air enters the pulsation attenuator air chamber.
- 3. Conversely, when pressure drops, the change lever presses the pulsation attenuator exhaust valve, exhausting the air from the air chamber and keeping the diaphragm in a constant position. Note that some time is required for the pulsation attenuator to operate normally.

Maintenance Parts


•While it is not possible to disassemble this product without voiding the warranty, if disassembly is to be carried out anyway due to necessity, be sure to follow the maintenance procedures. •When carrying out this work, wear appropriate protective equipment.

PAX1000 Series

Description	PAX1000 series
	PAX1□12
Diaphragm kit	KT-PAX1-31
Check valve kit	KT-PAX1-36
Switching valve parts kit	KT-PAX1-37#1
Pilot valve kit	KT-PA5-38
Pulsation attenuator control valve kit	KT-PAX1-39

PAX1000 Series

Piping: Automatically Operated Type, Built-in Pulsation Attenuator



A Caution

Mounting posture of the pump is set with the bottom surface at the bottom. Air to be supplied to the AIR SUP port should be cleaned and filtered through AF filter, etc. Air with foreign matter or drainage etc. will have negative effects on the built-in switching valve and will lead to malfunction. When air needs additional purification, use a filter (AF series), and a mist separator (AM series) together. Maintain the proper tightening torque for fittings and mounting botts, etc. Looseness can cause problems such as fluid and air leaks, while over tightening can cause damage to threads and parts, etc.

Operation

<Starting and Stopping> Refer to circuit example (1)


- Connect air piping to the air supply port <AIR SUR> and connect piping for the fluid to be transferred to the suction port <FLUID IN> and the discharge port <FLUID OUT>.
- 2. Using a regulator, set the pilot air pressure within the range of 0.2 to 0.7 MPa. Then, the pump operates when power is applied to the 3 port solenoid valve of the air supply port <AIR SUP>, the sound of exhaust begins from the air exhaust port <AIR EXH> and fluid flows from the suction port <FLUID IN> to the discharge port <FLUID OUT>.

At this time, the throttle on the discharge side is in an open state. The pump performs suction with its own power even without priming. (Dry state suction lifting range: max. 2 m) To restrict exhaust noise, attach a silencer (AN20-02: option) to the air exhaust port <AIR EXH>.

3. To stop the pump, exhaust the air pressure being supplied to the pump by the 3 port solenoid valve of the air supply port <AIR SUP>. The pump will also stop if the throttle on the discharge side is closed.

<Discharge Flow Rate Adjustment>

- 1. To adjust the flow rate from the discharge port <FLUID OUT>, use the throttle connected to the discharge side. Refer to circuit example (1). Note that this product cannot be used as a fixed quantity liquid dispense pump.
- 2. When operating with a discharge flow rate below the specification range, provide a by-pass circuit from the discharge side to the suction side to ensure the minimum flow rate inside the process pump. With a discharge flow rate below the minimum flow rate, the process pump may stop due to unstable operation. Refer to circuit example (2). (Minimum flow rates: PAX1000 0.5 L/min) <Reset Button>
- 1. When the pump stops during operation, press the reset button. This makes it possible to restore operation in case the switching valve becomes clogged due to foreign matter in the supply air. Maintenance is necessary if the reset button needs to be pressed frequently.



Process Pump Automatically Operated Type, Built-in Pulsation Attenuator **PAX1000 Series**

Dimensions

