
Type 3Integrated input-output type

Fieldbus System (For Input/Output)

EX250 Series




CONTENTS


Type 3 Integrated input-output type

Fieldbus System (For Input/Output) *EX250 Series*









	arts Structure ······p. I Unit	
	How to Orderp.	148
	Specificationsp.	149
	Dimensions/Parts Descriptionp.	150
	LED Indicator ·····p.	152
In	nput Block	
	How to Orderp.	153
	Specificationsp.	153
	Dimensions/Parts Descriptionp.	154
	LED Indicator ······p.	155
	Internal Circuit ······p.	155

Accessories

Example of Connectionsp. 156
Replacement Fuse
2 End Plate (Input side)p. 157
Output Block ······p. 158
Power Block
Send Plate (Output side)p. 161
Communication Cablep. 162
Field-wireable Communication Connector
3 Power Supply Cable (For SI unit/For power block) p. 164
Power Supply Cable (For SI unit)
Cable for Output Entryp. 165
() Seal Cap (10 pcs.) p. 165
Power Supply Cable
(For connecting the SI unit to the power block) ···· p. 166
AS-Interface Power Supply Cablep. 166


Made to Order

⊚ SMC

SMC

①DeviceNet [®] , 7/8 inch connector,	
Occupied points: 48 inputs/32 outputs ······ p. 16	7
Communication Cable p. 16	7
Power Supply Cable p. 16	8

Specific Product Precautionsp. 170



SMC

The EX250-SPR1 PROFIBUS DP compatible SI unit is to be discontinued as of November 2022. As a substitute, please consider the use of an EX600 series product. However, keep in mind that the product specifications, external appearance, etc., differ. For details, please contact your SMC sales representative.

Specifications

Model		EX250-SDN1	EX250-SDN1-X102	EX250-9	SPR1	EX250-SCA1A	EX250-SEN1	EX250-SAS3/5	EX250-SAS7/9	
		Protocol	Devic	eNet®	PROFIBL	JS DP	CANopen	EtherNet/IP™	AS-Int	erface
	Applicable system Version*2 Communication speed		Release 2.0 DP-V0 CiA DS-301 V4.02 CiA DS-401 Rel		Release 1.0	Ver. 2.11 (Standard Address Mode)				
Communication			125 k/250	k/500 kbps	9.6 k/19 45.45 k/9 187.5 k/5 1.5 M/3 N 12 Mb	3.75 k/ 500 k/ //6 M/	10 k/20 k/50 k/ 125 k/250 k/ 500 k/800 k/ 1 Mbps	10 M/100 Mbps	167	kbps
i mo	Configurat	tion file*3	EDS	S file	GSD	file	EDS file	EDS file	_	—
Ō	I/O occupa (Inputs/Ou		32/32	48/32	32/3	2	32/32	48/32	SAS3: 8/8 (2 slave units) SAS5: 4/4	SAS7: 8/8 (2 slave units) SAS9: 4/4
	Applicable	function	QuickCo	onnect™	—		—	—	—	—
	Terminatin	g resistor		Not pr	ovided			Not p	provided (Not req	uired)
Power supply			(Supp	25 VDC lied by et [®] circuit)	24 VDC	±20%	18 V to 30 VDC (Supplied by CANopen circuit)	24 VDC ±20%	26.5 to 31.6 VDC (Supplied by	*4 26.5 to 31.6 VDC
voltage	For sensor	rs	24 VD0	C ±20%			24 VDC±20%		AS-i circuit)	
	For valve				24	VDC +	-10%/–5%		1	AS-i circuit)
Internal current consumption (Unit)		100 mA or less					SAS3: 100 mA or less SAS5: 65 mA or less	SAS7: 100 mA or less SAS9: 65 mA or less		
t	Number of inputs			32 inputs (Based on input block connection)					SAS3: 8 inputs SAS5: 4 inputs	SAS7: 8 inputs SAS9: 4 inputs
Input	Supply voltage Supply current		24 VDC						-	
-			1.0 A or less					SAS3: 240 mA or less SAS5: 120 mA or less	*5	
	Output typ	e	Source/PNP (Negative common)							
	Number of	outputs	32 outputs SAS3: 8 outputs SAS5: 4 outputs						SAS7: 8 outputs SAS9: 4 outputs	
Output	Load		Solenoid valve with surge voltage suppressor 24 VDC, 1.5 W or less (SMC) Output block Power block							
	Supply vol	tage	24 VDC							
	Supply cu	Supply current							SAS3: 500 mA or less SAS5: 250 mA or less	*5
	Fail safe		HOLD/CLEAR (Switch setting) CLEAR (Switch setting)							
व	Enclosure						IP67			
Environmental resistance	Operating ter	nperature range		5 to +45°C			-10 to +50°C		5 to +45°C	
onn stal	Operating h	numidity range			3	5 to 85	5%RH (No conde	nsation)		
lv ir c	Withstand	voltage	500 VAC for 1 minute between whole external terminal and FG							
<u>ы</u> –	Insulation	resistance		10 MΩ o	r more (50	00 VDC	c) between whole	external termina	al and FG	
Standards			CE/UKCA marking (EMC directive/RoHS directive), UL (CSA)							
Weight							250 g			
Accesso	ry*6			Tie-rod 2 pcs.						

*1 This is a specification to transmit the diagnostic information of voltage drop of the valve power supply and input block fuse blowout as an input data to the master. The EX250-SDN1 becomes I/O connection time out when the diagnostic information is detected, but not EX250-SDN1-X102.

Since this is a special product, a manifold part number is not specified. Please consult SMC for the manifold integrated type.

*2 Please note that the version is subject to change.

*3 The setting file can be downloaded from SMC website, http://www.smcworld.com

*4 Since the EX250-SAS7/9 is compatible with the 1 power supply system, the power supply for units is divided into two: the power supply for sensors and for valves.
 *5 Since the EX250-SAS7/9 is compatible with the 1 power supply system, the power supply must be divided in accordance with the values below. (Refer to page 170 for details.)

EX250-SAS7 ··· Max. 240 mA, EX250-SAS9 ··· Max. 120 mA


*6 When the SI unit is mounted to the manifold when shipped, accessories are shipped together with it.


*7 For detailed specifications other than the above, refer to the operation manual that can be downloaded from SMC website, http://www.smcworld.com



Dimensions/Parts Description

EX250-SDN1 (DeviceNet®)







EX260

EX123/124/126

EX500


EX600

Type 2


Type.

Dimensions/Parts Description


EX250-SCA1A (CANopen)




EX250-SEN1 (EtherNet/IP™)




EX250-SAS7/9 (AS-Interface 1 power supply system)



Communication connector (M12, 4 pins, A-coded, plug)




EX250-SAS3/5 (AS-Interface 2 power supply systems)




LED Indicator


EX250-SDN1 (DeviceNet®)




EX250-SPR1 (PROFIBUS DP)




EX250-SCA1A (CANopen)




EX250-SEN1 (EtherNet/IP™)



EX250-SAS7/9 (AS-Interface 1 power supply system)




EX250-SAS3/5 (AS-Interface 2 power supply systems) PWR: Power supply for control Overcurrent detection



EX260 Type EX123/124/126 EX500 Type 2 EX600 EX245 Fype 3 EX250 EX120/121/122 EX140 Type EX180 EX510 Type 2 M8/M12

ATEX



Specifications


	Model	EX250-IE1	EX250-IE2	EX250-IE3			
	Input type	PNP/NPN sensor input (switched using a switch)					
	Number of inputs	2 inputs 4 inputs					
Input	Input device supply voltage		24 VDC				
	Input device supply current		Max. 30 mA/Point*1				
	Rated input current	Approx. 8 mA					
	Enclosure	IP67					
	Operating temperature range	-10 to +50°C					
Environmental resistance	Operating humidity range	35 to 85%RH (No condensation)					
resistance	Withstand voltage	500 VAC for 1 minute between whole external terminal and FG					
	Insulation resistance	10 M Ω or more (500 VDC) between whole external terminal and FG					
Standards		CE/UKCA marking, UL (CSA)					
Weight		90 g					
Accessory*2		Tie-rod 2 pcs.					

*1 When the maximum inputs to the SI unit is reached by adding an input block, pay attention not to exceed the supply current for the SI unit input.
 *2 When the SI unit is integrated into manifold, its tie-rod is also incorporated at the time of shipment.
 * For detailed specifications other than the above, refer to the operation manual that can be downloaded from SMC website, http://www.smcworld.com

Fieldbus System For Input/Output **EX250** Series

Dimensions/Parts Description







*1 Fuse for overcurrent protection If addressing the possible cause of a problem, even when the fuse is blown, it can be reinstated by replacing with a fuse as shown in options, page 157

SMC

LED Indicator




EX250-IE3




Internal Circuit


EX250-IE1



EX250-IE3





EX250-IE2






Example of Connections











^{*} The SI unit pictured above is compatible with PROFIBUS DP.

Connection example of an SI unit compatible with AS-Interface





EX260

EX123/124/126

EX500

EX600


Replacement Fuse

Replacement fuse required when the fuse for the input block (EX250-IED) overcurrent protection is blown.

EX9-FU05


Model	EX9-FU05	Fuse
Applicable model	EX250-IE	
Rated current	0.5 A	
Rated insulation capacity	48 VAC/DC 50 A	
Fuse resistance value	0.36 Ω	


2 End Plate (Input side)




EX250-EA1


EX250-EA2







Output Block



• Output specification

Source/PNP (Negative common) Sink/NPN (Positive common)

Power supply type

T Internal power supply method (for low-wattage load) P Integrated power supply method (for high-wattage load)*1 *1 Required to connect with a power block

SI Unit/Part Nos.

SI unit part no.	Output	Applicable model
EX250-SDN1 EX250-SPR1 EX250-SAS EX250-SCA1A EX250-SEN1	Source/PNP (Negative common)	EX9-OET1 EX9-OEP1

Option/Part Nos.

Description	Part no.		le model OEP□	Note
Seal cap	EX9-AWTS	0	0	Refer to page 165. Order separately: 10 pcs. included
Cable for output entry	EX9-AC□-7	0	0	Refer to page 165. Order separately.
Power block	EX9-PE1		0	Refer to page 159. Order separately.

- Able to retrofit to the valve manifold, using the unused points
- 2-output (M12 connector)
- Positive/Negative common available as standard
- Able to drive by 0.5 A per point

You are requested to connect it to an SI unit and a valve manifold. For detailed specifications, refer to the operation manual that can be downloaded from SMC website, http://www.smcworld.com

4 Power Block





Option/Part Nos.

•			
Description	Part no.	Note	
Seal cap	EX9-AWTS	Refer to page 165. Order separately: 10 pcs. included	
Power supply cable (For SI unit/For power block)	EX9-AC□-1	Refer to page 164. Order separately.	
Power supply cable (For connecting the SI unit to the power block)	EX9-AC002-2 EX9-AC002-3 EX9-AC002-4	Refer to page 166. Order separately.	
AS-Interface power supply cable	EX9-AC□-5	Refer to page 166. Order separately.	

EX600 EX245 lype 3 EX250 EX120/121/122 EX140 Type EX180 EX510 Type 2

EX260

EX123/124/126

EX500

lype 2

Type

ATEX

③Output Block/**④** Power Block

Output Block Specifications


•						
	Model	EX9-OET1	EX9-OET2	EX9-OEP1	EX9-OEP2	
Output connect	tor	M12 connector (5 pins)				
Internal current consumption			40 mA	or less		
	Output type	Source/PNP (Negative common)	Sink/NPN (Positive common)	Source/PNP (Negative common)	Sink/NPN (Positive common)	
	Number of outputs		2 ou	tputs		
Output	Power supply method	Internal power	supply method	Integrated power supply method (P	ower block: supplied from EX9-PE1)	
	Output device supply voltage		24 \	VDC		
	Output device supply current	Max. 62 mA/Poi	int (1.5 W/Point)	Max. 0.5 A/Point (12 W/Point)		
	Enclosure	IP67				
	Operating temperature range	−10 to +50°C				
Environmental resistance	Operating humidity range	35 to 85%RH (No condensation)				
resistance	Withstand voltage	1500 VAC for 1 minute between whole external terminal and FG				
	Insulation resistance	10 $M\Omega$ or more (500 VDC) between whole external terminal and FG				
Standards		CE/UKCA marking, UL (CSA)				
Weight		120 g				
Accessory Tie-rod		2 pcs.				

Power Block Specifications

Model			EX9-PE1		
Connection block			Output block (EX9-OEP□)		
Connection block stations			Output block: Max. 9 stations (excluding input blocks)*1		
Power supply fo		Power supply voltage	22.8 to 26.4 VDC		
output and inter control	rnai	Internal power consumption	20 mA or less		
Supply current			Max. 3.1 A (When using with 3.0 to 3.1 A, the ambient temperature should not exceed 40°C, and do not bundle the cable.)		
	Enclosure		IP67		
	Ope	rating temperature range	−10 to +50°C		
Environmental resistance	Ope	rating humidity range	35 to 85%RH (No condensation)		
resistance	With	stand voltage	1500 VAC for 1 minute between whole external terminal and FG		
	Insu	lation resistance	10 M Ω or more (500 VDC) between whole external terminal and FG		
Standards			CE/UKCA marking, UL (CSA)		
Weight			120 g		
		Tie-rod	2 pcs.		
Accessory	Seal cap (for M12 connector socket)		1 pc. (EX9-AWTS)		

*1 The total number of connectable input/output/power block to the EX250 series SI unit (except for AS-Interface compliant) is 10 stations at the maximum.
 * For detailed specifications other than the above, refer to the operation manual that can be downloaded from SMC website, http://www.smcworld.com

Output Block Dimensions/Parts Description




SMC

Power Block Dimensions/Parts Description


③ Output Block/**④** Power Block


Circuit Diagram

EX9-OET1



EX9-OEP1





Output block


EX9-OET2

Valve power supply 24 V

SI unit

EX9-PE1

Power block



* When the valve which supplies power to the SI unit is turned OFF, the output of the output block (EX9-OE⁽¹⁾) remains OFF.

ATEX

EX250

EX120/121/122

EX140

EX180

Type


G End Plate (Output side)


Use the end plate when a valve manifold is not connected.




EX9-EA04


EX9-EA03








66 M4 Clamping screw Tightening torque 0.4 to 0.6 N·m











G Communication Cable



EX9-AC 005 DN-SSPS (With connector on both sides (Socket/Plug))


4	• Cable length (L)							
	005	500 mm						
	010	1000 mm						
	020	2000 mm						
	030	3000 mm						
	050	5000 mm						
	100	10000 mm						



Item		Specifications	
Cable O.D.		ø6.7 mm	
Conductor nominal Power pair		0.34 mm ² /AWG22	
cross section	Data pair	0.25 mm ² /AWG24	
Wire O.D. Power pair		1.4 mm	
(Including insulator)	Data pair	2.05 mm	
Min. bending radius (Fixed)		67 mm	

SMC

GCommunication Cable



EX9-AC 005 EN-PSPS (With connector on both sides (Plug/Plug))

le length (L)	∞ ▼ 47.3 L	47.3	Ø 14.8
500 mm			
1000 mm	│ —┦┛┛┝╒══╸╫┥╴┍┞╼╼═┼╸╼═┈╸╶╶╦══	───-┦-╢-::=	⋺∔ ⋳ ⋒⋎⊢
2000 mm			
3000 mm	Metal parts vo	Metal parts	
5000 mm	<u>M12</u>	M12	, ,
10000 mm	SPEEDCON	SPEEDCON	
	Plug connector pin arrangement D-coded Connections (Straight of the section of th	2 White RD- 3 Orange TD- 4 Blue RD- V Plue Plue Metal parts pin	² ³ ⁴ ¹ ¹ ¹ ² ³ ⁴ ¹ ¹ ¹ ¹ ² ³ ⁴ ¹ ¹ ¹ ¹ ¹ ¹ ¹ ¹
		Item	Specifications
	C	Cable O.D.	ø6.5 mm

Min. bending radius (Fixed)

Conductor nominal cross section

Wire O.D. (Including insulator)

Min. bending radius (Fixed)

26 mm

0.34 mm²/AWG22


1.55 mm

19.5 mm




Accessories **EX250** Series

Field-wireable Communication Connector




164 ©

Over Supply Cable (For SI unit)



Cable for Output Entry




Connects the output block to the output device

Seal Cap (10 pcs.)

Use this on ports that are not being used for an M8 or M12 connector (socket). Use of this seal cap maintains the integrity of the enclosure. (Seal caps are packed together with each unit.)

 $\ast~$ Tighten the seal caps with the prescribed tightening torque. (For M8: 0.05 N·m, For M12: 0.1 N·m)






Accessories **EX250** Series

166 ®

D Power Supply Cable (For connecting the SI unit to the power block)

Connects between the power supply connector for the power block and the SI unit power supply connector, bridging the external power supply, which is supplied with the power block, to the SI unit.



SMC




SI Unit

Prepare the SI unit, each type of block, and the manifold valve (without SI unit) separately, and combine them before use.

1) DeviceNet®, 7/8 inch connector, 32 inputs/32 outputs (Occupied points: 48 inputs (32 inputs + diagnostic 16 inputs)/32 outputs)

EX250-SDN1-X122



Power supply connector

_		
1 3	1	24 VDC +10%/-5% (For valve)
$(\circ \circ)^3$	2	Unused
20_04	3	FE
	4	0 VDC (For valve)

Communication connector

$\begin{array}{c} 3\\ 4 \bigcirc \bigcirc \bigcirc \\ 5 \bigcirc \bigcirc \bigcirc \\ 1 \end{array}$	1	DRAIN
	2	V+
	3	V-
	4	CAN H
Ŷ	5	CAN L

Communication Cable


1 With connector on one side (Socket) Cable length: 10000 mm

For DeviceNet®

EX9-AC100 DN-X12

Applicable protocol

DN DeviceNet® * When connecting to a VQC4000 series model, use a VVQC4000-3A-3, etc., D side end plate. The VVQC4000-3A-2 D side end plate used by the standard EX250-SDN1 model cannot be used as it will come into contact with the EX250-SDN1-X122.



Connections

F _							
°~~~~~~~~~~~~~~~~~~~~~~~~~~~~~~~~~~~~~	Terminal no.	Core wire color: Signal name (DeviceNet®)	Item		Specifications		
1 (Õ * 0 0)3	1	Shield: DRAIN	Cable O.D.		ø6.7 mm		
•	2	Red: V+	Conductor nominal	Power pair	0.34 mm ² /AWG22		
4	3	Black: V-	cross section	Data pair	0.25 mm ² /AWG24		
Socket connector	4	White: CAN H	Wire O.D.	Power pair	1.4 mm		
pin arrangement	5	Blue: CAN L	(Including insulator)	Data pair	2.05 mm		
A-coded (Normal key)			Min. bending radius (Fixed)	67 mm		








Power Supply Cable

② With connector on one side (Socket) Cable length: 10000 mm



Straight connector type

EX500-AP100-S-X1



Specifications	
ø6 mm	
0.3 mm ² /AWG22	
1.5 mm	
40 mm	



EX250 Series Specific Product Precautions

Be sure to read this before handling the products. Refer to page 277 for safety instructions. For fieldbus system precautions, refer to pages 278 to 280 and the "Operation Manual" on the SMC website: http://www.smcworld.com

When one AS-Interface power supply system is used **Caution**

		EX250-SAS7	EX250-SAS9	
Powe	er supply voltage	Supplied from AS-Interface circuit, 26.5 to 31.6 VDC*		
Internal current consumption Max. 100 mA Max. 65 mA		Max. 65 mA		
u t	Number of inputs	8	4	
outp	Number of outputs	8	4	
out/	Number of inputs Number of outputs Supply voltage Supply current*2	24 VDC		
ang Spe	Supply current*2	Max. 240 mA	Max. 120 mA	

*1 For communication power supply, use a power supply dedicated to AS-Interface. For details, please refer to operation manuals provided by the respective manufacturers.

*2 The AS-Interface circuit provides current to the internal parts of the SI unit and all connected equipment.

Since there is a limit on the possible supply current to all connected equipment, select the equipment connected to the input/output device to stay within the possible supply current.

Example) When EX250-SAS9 is used

Valve: VQC1100NY - 5 (low-wattage type of 0.5 W) x 4 pcs. 0.5 [W] ÷ 24 [V] x 4 [pcs.]

= 84 [mA] (4 outputs simultaneously ON)

The maximum possible supply current of EX250-SAS9 is 120 mA. Therefore, the possible supply current to the sensor is

120 [mA] – 84 [mA] = 36 [mA]

Use of low-wattage type valves by minimizing the maximum number of simultaneous outputs, and low current consumption sensors (2-wire sensor, etc.) is recommended.

Maximum number of AS-Interface compatible input blocks

SI unit specifications		Input block type		Input block maximum stations
AS-Interfa	AS-Interface 8in/8out	1	M12/2 inputs	4 stations
EX250-SAS3	31 Slave Mode, 2 power	2	M12/4 inputs	2 stations
	supply systems	3	M8/4 inputs	2 stations
	EX250-SAS5 AS-Interface 4in/4out 31 Slave Mode, 2 power supply systems	1	M12/2 inputs	2 stations
EX250-SAS5		2	M12/4 inputs	1 station
		3	M8/4 inputs	1 station
EX250-SAS7	AS-Interface 8in/8out 31 Slave Mode, 1 power supply system	1	M12/2 inputs	4 stations
		2	M12/4 inputs	2 stations
		3	M8/4 inputs	2 stations
EX250-SAS9	AS-Interface 4in/4out 31 Slave Mode, 1 power supply system	1	M12/2 inputs	2 stations
		2	M12/4 inputs	1 station
		3	M8/4 inputs	1 station

Operating Environment

\land Caution

- 1. Select the proper type of enclosure according to the environment of operation.
 - IP65 is achieved when the following conditions are met.
 - Provide appropriate wiring between all units using electrical wiring cables, communication connectors and cables with M12 connectors.
 - 2) Suitable mounting of each unit and valve manifold.
 - Be sure to mount a seal cap on any unused connectors.
 If using in an environment that is exposed to water splashes, please take measures such as using a cover.

EX260

EX123/124/126

EX500

EX600

EX245

EX250

EX120/121/122

EX140

Type

M8/M12

ATEX

Trademark

Modbus[®] is a registered trademark of Schneider Electric, licensed to the Modbus Organization, Inc. DeviceNet[®] is a registered trademark of ODVA, Inc.

EtherNet/IP® is a registered trademark of ODVA, Inc.

QuickConnect[™] is a trademark of ODVA.

