5 Port Solenoid Valve Series VQC

VQC


SQ

VQ0

VQ4

VQ5

VQZ



Be sure to read before handling. For Safety Instructions and Solenoid Valve Precautions, refer to page 2-9-2.

Manual Override


⚠ Warning

Since connected equipment will operate when the manual override is activated, confirm that conditions are safe prior to activation.

The non-locking push type (tool required) is standard, and the slotted locking type (tool required) is optional.

■ VQC1000/2000


Non-locking push type (Tool required)



Push down the manual override button with a small screwdriver, etc., until it stops.


The manual override will return when released.

Slotted locking type (Tool required) <Option>




Push down the manual override button with a small flat head screwdriver until it stops, and turn it clockwise 90° to lock it. Turn it counterclockwise to release it.

Locking type (Manual) <Option>





Push down the manual override button with a small flat head screwdriver or with your finger until it stops, and turn it clockwise 90° to lock it. Turn it counterclockwise to release it.

Slide locking type (Manual) <Option>




Slide the manual override button with a small flat head screwdriver or with your finger until it stops at the pilot valve side (ON side) to lock it. Slide it to the fitting side (OFF side) to release it. It can also be used as a type using a screwdriver, etc., of ø1.7 or less in case of VQC1000, ø2 or less in the case of VQC2000.





Locking type (Manual) <Optional> d>




Push down the manual override button with a small screwdriver until it stops.

The manual override will return when released.

Push down the manual override button with a small flat head screwdriver until it stops, and turn it clockwise 90° to lock it. Turn it counterclockwise to release it.



Solenoid Valve Removal and Mounting (VQC1000/2000)



Removal steps

- 1. Loosen the clamp screws until they turn freely. (The screws do not come out.)
- 2. Remove the solenoid valve from clamp B by lifting the coil side of the valve while pushing on the screw top.

If pushing down on the screw is difficult, you can alternately press down on the valve gently in the area near the manual override.

Mounting steps

- 1. Push the clamp screws. Clamp A opens. Now insert the end plate hook of the valve into clamp B from an angle.
- 2. Push the valve down into place. (When you release the screws, the valve will be locked into clamp A.)
- 3. Tighten the clamp screws with a tightening torque of 0.25 to 0.35 N·m for VQC1000 and 0.5 to 0.7 N·m for VQC2000.


⚠Caution

Do not let foreign matter stick on the seal side of the gasket and solenoid, as this will cause air leakage.

Valve Mounting (VQC4000)

∕!\ Caution

After confirming that the gasket is installed correctly, securely tighten the mounting screws according to the tightening torque shown below.



♠ Precautions 2

Be sure to read before handling. For Safety Instructions and Solenoid Valve Precautions, refer to page 2-9-2.

Replacing One-touch Fittings


⚠ Caution

Cylinder port fittings are available in cassette type and can be replaced easily.


Fittings are secured with a retaining clip that is inserted from the top side of the valve. After removing the valve, remove the clip with a flat head screw driver to replace the fittings.

To mount a fitting, insert the fitting assembly until it stops and reinsert the retaining clip to its designated position.

■ VQC1000/2000



Anniharbia tuba O.D.	Fitting assembly part no.					
Applicable tube O.D.	VQC1000	VQC2000				
ø 3.2	VVQ1000-50A-C3	_				
ø 4	VVQ1000-50A-C4	VVQ1000-51A-C4				
ø 6	VVQ1000-50A-C6	VVQ1000-51A-C6				
ø 8	_	VVQ1000-51A-C8 —				
M5	VVQ1000-50A-M5					
ø 1/8 "	VVQ1000-50A-N1	_				
ø 5/32 "	VVQ1000-50A-N3	VVQ1000-51A-N3				
ø 1/4 "	VVQ1000-50A-N7	VVQ1000-51A-N7				
ø 5/16 "	_	VVQ1000-51A-N9				




Applicable tube O.D.	Fitting assembly part no.
Applicable tube O.D.	VQC4000
ø 8	VVQ4000-50B-C8
ø 10	VVQ4000-50B-C10
ø12	VVQ4000-50B-C12
ø 1/4 "	VVQ4000-50B-N7
ø 5/16 "	VVQ4000-50B-N9
ø 3/8 "	VVQ4000-50B-N11

Light/Surge Voltage Suppressor (VQC1000/2000)


⚠ Caution

Indicator lights are all positioned on one side for both single solenoid and double solenoid type valves.

For double solenoid type, 2 colours that are same as the manual override are used to indicate the energization of Aside or B-side.





(For VQC1000)



Internal Wiring Specifications (VQC4000)

⚠ Caution





How to Calculate the Flow Rate

Refer to pages 2-1-8 to 2-1-11.

SQ

VQC

VQ4

VQ5

VQZ

Precautions 3

Be sure to read before handling. For Safety Instructions and Solenoid Valve Precautions, refer to page 2-9-2.

Serial Wiring EX500/EX250/EX240/EX126 Precautions

△Warning

1. These products are intended for use in general factory automation equipment.

Avoid using these products in machinery/equipment which affects human safety, and in cases where malfunction or failure can result in extensive damage.

- 2. Do not use in explosive environments, in the presence of inflammable gases, or in corrosive environments. This can cause injury or fire.
- 3. Work such as transporting, installing, piping, wiring, operation, control and maintenance should be performed by knowledgable and qualified personnel only. As handling involves the risk of a danger of electrocution, injury or fire.
- 4. Install an external emergency stop circuit that can promptly stop operation and shut off the power supply.
- 5. Do not modify these products. Modifications done to these products carry the risk of injury and damage.

△Caution

- 1. Read the instruction manual carefully, strictly observe the precautions and operate within the range of the specifications.
- 2. Do not drop these products or submit them to strong impacts. This can cause damage, failure or malfunction.
- 3. In locations with poor electrical conditions, take steps to ensure a steady flow of the rated power supply. Use of a voltage outside of the specifications can cause malfunction, damage to the unit, electrocution or fire.
- 4. Do not touch connector terminals or internal circuit elements when current is being supplied. There is a danger of malfunction, damage to the unit or electrocution if connector terminals or internal circuit elements are touched when current is being supplied.

Be sure that the power supply is OFF when adding or removing manifold valves or input blocks or when connecting or disconnecting connectors.

5. Operate at an ambient temperature that is within the specifications. Even when the ambient temperature range is within the specifications, do not use in locations where there are rapid temperature changes.

⚠ Caution

- 6. Keep wire scraps and other extraneous materials from getting inside these products. This can cause fire, failure or malfunction.
- 7. Give consideration to the operating environment depending on the type of enclosure being used.

To achieve IP65 and IP67 protection, provide appropriate wiring between all units using electrical wiring cables, communication connectors and cables with M12 connectors. Also, provide waterproof caps when there are unused ports, and perform proper mounting of input units, input blocks, SI units and manifold valves. Provide a cover or other protection for applications in which there is constant exposure to water.

8. Use the proper tightening torques.

There is a possibility of damaging threads if tightening exceeds the tightening torque range.

9. Adjustment and operation.

Use a sharp-ended watchmakers screw driver to set the dip switches and rotary switches.

- 10. Provide adequate protection when operating in locations such as the following:
 - Where noise is generated by static electricity
 - Where there is a strong electric field
 - Where there is a danger of exposure to radiation
 - When in close proximity to power supply lines
- 11. When these products are installed in equipment, provide adequate protection against noise by using noise filters.
- 12. Since these products are components whose end usage is obtained after installation in other equipment, the customer should confirm conformity to EMC directives for the finished product.
- 13. Do not remove the name plate.
- 14. Perform periodic inspections and confirm normal operation, otherwise it may be impossible to guarantee safety due to unexpected malfunction or erroneous operation.

⚠ Precautions 4

Be sure to read before handling. For Safety Instructions and Solenoid Valve Precautions, refer to page 2-9-2.

When one AS-i power supply system is used

⚠ Caution

		TCW	SDTC	TDW	SDTD	
Pow	er supply voltage	Supplied fro	m AS-i circui	t, 26.5 to 31.6	S VDC Note 1)	
	Current consumption Note 2) Max. 100 mA Max. 65 mA					
ut	Number of inputs Number of outputs Valve supply voltage Possible supply current Note 3)	8	3	4	1	
outp	Number of outputs	8	3	4		
out/e	Valve supply voltage		24 VDC	C ± 10%		
lul	Possible supply current Note 3)	Max. 240 mA Max. 120 mA				

Note 1) For communication power supply, use a power supply dedicated to AS-i. For details, please refer to instruction manuals provided by the respective manufacturers.

Note 2) Current consumption of SI unit internal power supply Note 3) The AS-i circuit provides current to the internal parts of

the SI unit and all connected equipment.
Since there is a limit on the possible supply current to all connected equipment, select the equipment connected to the input block, such as sensors and valves, to stay within the possible supply current.

Example) When SDTD type is used

Valve: VQC1100NY – 5 (low wattage type of 0.5 W) \times 4 pcs.

 $0.5 \text{ [W]} \div 24 \text{ [V]} \times 4 \text{ [pcs.]} = 84 \text{ [mA]} (4 \text{ outputs simultaneously ON)}$

The maximum possible supply current of SDTD is 120 mA. Therefore, the possible supply current to the sensor connected to the input block is

120 [mA] - 84 [mA] = 36 [mA].

Use of low wattage type valves by minimizing the maximum number of simultaneous outputs, and low current consumption sensors (2-wire sensor, etc.) connected to the input block is recommended.

Power Supply Safety Instructions

△ Caution

- Operation is possible with a single power supply or a separate power supply. However, be sure to provide two wiring systems (one for solenoid valves, and one for input and control units).
- 2. Use the following UL approved products for DC power supply combinations.
 - (1) Controlled voltage current circuit conforming to UL508 Circuit uses the secondary coil of an isolated transformer as the power supply, satisfying the following conditions.
 - Max. voltage (with no load): 30 Vrms (42.4 V peak) or less
 - Max. current: 1 8 A or less (including shorts), and
 - When controlled by a circuit protector (fuse) with the following ratings:

No-load voltage (V peak)	Max. current rating
0 to 20 [V]	5.0
Over 20 [1/] and up to 20 [1/]	100
Over 20 [V] and up to 30 [V]	Peak voltage value

(2) A circuit (class 2 circuit) with maximum 30 Vrms (42.4 V peak) or less, and a power supply consisting of a class 2 power supply unit conforming to UL1310, or a class 2 transformer conforming to UL1585.

Cable Safety Instructions

- 1. Avoid miswiring, as this can cause malfunction, damage and fire in the unit.
- 2. Do not conduct wiring work while the cables are energized.

The SI unit may be damaged or malfunction.

- 3. To prevent noise and surge in signal lines, keep all wiring separate from power lines and high voltage lines. Otherwise, this can cause a malfunction.
- 4. Check wiring insulation, as defective insulation can cause damage to the unit when excessive voltage or current is applied.
- Do not bend or pull cables repeatedly, and do not place heavy objects on them or allow them to be pinched. This can cause broken lines.

VQC

SQ

VQ0

VQ4

VQ5

VQZ

Connector Type Manifold

Series VQC1000/2000/4000

Outstanding response times and long service life

(Metal seal: Single type with light/surge voltage suppressor)

VQC1100: 10 ms ±2 ms; 200 million cycles VQC2100: 20 ms ±2 ms; 200 million cycles VQC4100: 17 ms ±3 ms; 100 million cycles


Compact and large flow

T		F	Flow characteristics Note)						
Type (Sorios)	Manifold	Metal	seal		Rubber	Rubber seal			
(Series)	pitch (mm)	C[dm³/(s·bar)]	b	Cv	C[dm ³ /(s·bar)]	b	Cv	cylinder size (mm)	
VQC1000	10.5	0.72		0.18	1.0	0.30	0.25	to ø50	
VQC2000	16	2.6	0.15	0.60	3.2	0.30	0.80	to ø80	
VQC4000	25	6.9	0.17	1.7	7.3	0.38	2.0	to ø140	

Connecto

Note) Values for 2 position single from 4 to 5 and from 2 to 3. (From A to R1 and from B to R2) **Connector entry direction** can be changed with a single push (F, P kit)

The connector entry direction can be changed from the top to the side by simply pressing the manual release button. It is not necessary to use the manual release button when



Input blocks

Replaceable One-touch fittings

Single mounting screw, clamp construction

SI unit for I/O

(DeviceNet, PROFIBUS-DP,

CANopen, AS-i, etc.)


Accommodates gateway type serial wiring

- · Because just one gateway unit controls up to 4 branch lines, it offers much more freedom in choosing valve mounting locations in comparison to other
- A single cable from the gateway provides both signal and power to each branch, thus eliminating the need for separate power connections for each manifold valve and input block.
- · The use of a multi-connector for input blocks makes manifold station expansion or reduction a breeze.




EX250

A wide variety of prepackaged wiring configurations



- · Our six standard wiring packages bring a world of ease to wiring and maintenance work, while the protective enclosures of four of them conform to IP67 standards.
- The S Kit is compatible with a combined I/O unit. (If used with Gateway unit, SI must be output only.)

Conforming to IP67 for protection from dust and moisture



(Refer to the connector wiring diagram.)

Printed circuit board patterns between connectors are shifted at every station. This allows for viable connections to take place without necessarily specifying whether the manifold station is double, single, or mixed wiring.

Dual 3 port valves, 4 positions VQC1000/2000 (Rubber seal type only)


- Two 3 port valves built into one body.
- The 3 port valves on the A and B sides can operate independently.
- When used as 3 port valves, only half the number of stations is required.
- Can also be used as a 4 position, 5 port type valve.

Exhaust center: VQC1A01

VQC2A01

Pressure center: VQC1B01

VQC2B01



Model	A side	B side	JIS Symbol
VQC1A01	N.C.	N.C.	(A) (B) (B) (B1) (B2) (B2)
VQC2A01	valve	valve	
VQC1B01	N.O.	N.O.	(A) (B) (B) (B1) (B2) (B2)
VQC2B01	valve	valve	
VQC1C01	N.C.	N.O.	(A) (B)
VQC2C01	valve	valve	(B) (B) (B1) (B2)

VQC

SQ

VQ0

VQ4

VQ5

VQZ

Base Mounted: Variations

		So Condu	nic ctance			S	Kit				
			C[dm³/(s·bar)] (Values of CYL to EXH (From 4 to 5 and from 2 to 3)/			Serial transmission					
					. 6666 .		ore size	Gateway application Compatible network Remote I/O DeviceNet PROFIBUS-DP CC-LINK	Compatible network • DeviceNet • PROFIBUS-DP • CC-LINK • AS-i	Compatible network • DeviceNet • PROFIBUS-DP	Compatible network • CC-LINK Output
6:65:666		Single/Double	3 position (Closed center)	Applicable bore size	Gateway application requires a gateway unit and communication cable separately. Please contact SMC for more details. Serial unit: EX500 IP67 compliant	• CANopen I/O Serial unit: EX250 IP67 compliant	Serial unit: EX240 IP67 compliant	Serial unit: EX126 IP67 compliant			
Series	Wetal seal		0.72	0.72	to a50						
VQC1000	Rubber seal	VQC1□01	1.0	0.65	to ø50		O				
Series	Metal seal	VQC2□00	2.6	2.0	h. 200						
VQC2000			3.2	2.2	to ø80						
Series	Metal seal	VQC4□00	6.9	6.3	to ø140						
VQC4000	Rubber seal	VQC4□01	7.3	6.4	10 Ø 140						


F Kit	P Kit	Kit T Kit L		M Kit	Port	size
D-sub connector D-sub connector Compatible with D-sub connector that complies with MIL standard.	Flat ribbon cable Flat ribbon cable Compatible with flat ribbon cable connector that complies with MIL standard.	Terminal block box (Terminal blocks) Terminals are concentrated in compact clusters within the terminal block box. IP67 compliant	Lead wire IP67 enclosure with use of multiple wire cable with sheath and waterproof connector 25 core cable	Multiple connector Multiple connector IP67 enclosure with use of waterproof multiple connector 26 pins IP67 compliant	SUP EXH port 1, 3 (P, R)	Cylinder port 2, 4 (A, B)
0	0	0	0	0	C8 (for ø8) N9 (ø5/16")	C3 (For ø3.2) C4 (For ø4) C6 (For ø6) M5 (M5 thread) N1 (ø1/8") N3 (ø5/32") N7 (ø1/4")
0	0	0	0	0	C10 (for ø10) N11 (ø3/8") In case of branch type C12 (for ø12) N13 (ø1/2")	C4 (For Ø4) C6 (For Ø6) C8 (For Ø8) N3 (Ø5/32") N7 (Ø1/4") N9 (Ø5/16")
0		0	0	0	^{Rc 1/2 (NPT, NPTF, G) <exh port=""> Rc 3/4 (NPT, NPTF, G)</exh>}	C8 (For Ø8) C10 (For Ø10) C12 (For Ø12) N7 (Ø1/4") N9 (Ø5/16") N11 (Ø3/8") Rc 1/4 Rc 3/8 Rc 1/4 (Bottom ported) (NPT, NPTF, G)

VQC

SQ

Cylinder Average Speed

This chart is provided as guidelines only. For performance under various conditions, use SMC's Model Selection Program before making a judgment.



* Values at extension of a directly coupled cylinder when meter-out speed controllers are used with the needle full open.

* The average speed of the cylinder is obtained by dividing the stroke by the total stroke time.

* The load ratio is obtained by the following formula: ((Load weight x 9.8)/Theoretical output) x 100%

Conditions


Conditions								
Base	Series CJ2	Series CM2	Series MB, CA	Series CS1				
	Tube x Length	7	Г0604 x 1n	1				
VQC1000	Speed controller	A	S3001F-0	6	_			
	Silencer	ļ	N200-KM	8				
	Tube x Length	T0604 x 1 m	T0806	3 x 1 m				
VQC2000	Speed controller	AS3001F-06	AS300	01F-08	_			
	Silencer	Α	N200-KM1	0	_			
	Tube x Length	T0604 x 1 m	T1075 x 1 m	T1209	x 1 m			
VQC4000	Speed controller	AS3001F-06	AS4001F-10	AS400)1F-12			
	Silencer	-	AN400-04		AN400-04			

Conditions (With SGP (Stainless steel gas piping))

Direc	et piping	Series MB, CA Series CS1		
	Tube x Length	SGP10A x 1 m		
VQC4000	Speed controller	AS42	20-03	
	Silencer	AN40	00-04	




Series VQC1000 Base Mounted Plug-in Unit




8

With 8 input blocks

How to Order Valves




Kit Designation/Electrical Entry/Cable Length




Plug-in Unit Series VQC1000

Manifold Option


Blanking plate assembly VVQ1000-10A-1



SUP block plate VVQ1000-16A




Dual flow fitting assembly VVQ1000-52A-C8



Individual SUP spacer VVQ1000-P-1-C6






Elbow fitting assembly VVQ1000-F-L□

Port plug VVQ0000-58A

Electrical wiring specifications [-K]



 \circ

VQZ

Terminal n SOL. A_O 1

SOL. A_O 14

SOL A 2

SOL. B SOL. B 16

SOL. A

SOL. B 17 SOL. A_O 5 SOL. B_O 18

Connector terminal no.

VQC


SQ


VQ0

VQ4

VQ5

Individual EXH spacer VVQ1000-R-1-C6








Back pressure check valve assembly [-B] VVQ1000-18A




Standard manifolds are for double wiring, but mixed wiring (single and double wiring) can be specified as options.


Name plate [-N] VVQ1000-N-Stations (1 to max. no. of stations)









Series VQC2000 Base Mounted Plug-in Unit



How to Order Valves




Kit Designation/Electrical Entry/Cable Length




Plug-in Unit Series VQC2000

Manifold Option


Blanking plate assembly VVQ2000-10A-1



SUP block plate VVQ2000-16A




Perfect block VVQ2000-FPG-□□




Dual flow fitting assembly VVQ2000-52A-C10



Individual SUP spacer VVQ2000-P-1-C8




Elbow fitting assembly VVQ2000-F-L□




Port plug VVQ1000-58A




Individual EXH spacer



EXH block plate VVQ2000-19A



Electrical wiring specifications [-K]




Connector terminal no.

DIN rail mounting bracket [-D] VVQC2000-57A for {F, L, M, P, S (EX500) kit} VVQC2000-57A-S


for {S (EX250) kit} VVQC2000-57A-T for {T, S (EX126) kit}




Silencer (for EXH port) AN200-KM10



Back pressure check valve assembly [-B] VVQ2000-18A



Name plate [-N] VVQ2000-N-Stations (1 to max. no. of stations)




Standard manifolds are for double wiring, but mixed wiring (single and double wiring) can be specified as options.

Direct EXH outlet with built-in silencer [-S]



Blanking plug KQ2P-□



VQC SQ

VQ0


VQ4

VQ5


VQZ


VQZ

Series VQC4000 Base Mounted Plug-in Unit



How to Order Valves






LD2 Lead wire kit 3.0 m lead wire


Plug-in Unit Series VQC4000

Manifold Option


Blanking plate assembly VVQ4000-10A-1




Individual SUP spacer VVQ4000-P-1-02



Individual EXH spacer VVQ4000-R-1-02



SUP/EXH block plate VVQ4000-16A



VQC

SQ

VQ0


VQ4

VQ5


VQZ

VQD


Throttle valve spacer VVQ4000-20A-1




Residual pressure release valve perfect spacer VVQ4000-25A-1 Note 1)



SUP stop valve spacer VVQ4000-37A-1



Interface regulator ARBQ4000-00- ARBQ400-00- AR





Note 1) Perfect spacers with residual pressure release valve cannot be combined with external pilot specifications.

Series VQC **Base Mounted Plug-in Unit**



JIS Symbol

2 position single



2 position double (metal)



2 position double (rubber)



3 position closed center



3 position exhaust center



3 position pressure center




3 position exhaust center with pressure release valves (A) (B)




4 position dual 3 port valve (A)



4 position dual 3 port valve (B)



4 position dual 3 port valve (C)



2-2-22

Model

(0						Flov	v char	acteristics			Response	Note 2) time (ms)	
Series	0.	No. of olenoids	Mode	el	1 → 4, 2 ($P \rightarrow A$, B)	4, 2 → 5, 3 (A,	$B \rightarrow F$	R1, R2)	Standard:	Low	Weight
S	S	Dieriolas			C[dm ³ /(s•bar)]	b	Cv	C[dm3/(s•bar)]	b	Cv	1 W	wattage	(g)
	_	Cinala	Metal seal	VQC1100	0.70	0.15	0.16	0.72	0.25	0.18	12 or less	15 or less	64
	position	Single	Rubber seal	VQC1101	0.85	0.20	0.21	1.0	0.30	0.25	15 or less	20 or less	04
	2 po	Double	Metal seal	VQC1200	0.70	0.15	0.16	0.72	0.25	0.18	10 or less	13 or less	
	•	Double	Rubber seal	VQC1201	0.85	0.20	0.21	1.0	0.30	0.25	15 or less	20 or less	
0		Closed	Metal seal	VQC1300	0.68	0.15	0.16	0.72	0.25	0.18	20 or less	26 or less	
VQC1000		center	Rubber seal	VQC1301	0.70	0.20	0.16	0.65	0.42	0.18	25 or less	33 or less	
õ	position	Exhaust	Metal seal	VQC1400	0.68	0.15	0.16	0.72	0.25	0.18	20 or less	26 or less	78
>		center	Rubber seal	VQC1401	0.70	0.20	0.16	1.0	0.30	0.25	25 or less	33 or less	′°
	3	Pressure	Metal seal	VQC1500	0.70	0.15	0.16	0.72	0.25	0.18	20 or less	26 or less	
		center	Rubber seal	VQC1501	0.85	0.20	0.21	0.65	0.42	0.18	25 or less	33 or less	
	4 position	Dual 3 port valve	Rubber seal	VQC1B01	0.70	0.20	0.16	0.70	0.20	0.16	25 or less	33 or less	
		0: 1	Metal seal	VQC2100	2.0	0.15	0.46	2.6	0.15	0.60	22 or less	29 or less	00
	position	Single	Rubber seal	VQC2101	2.2	0.28	0.55	3.2	0.30	0.80	24 or less	31 or less	90
	sod :	Б	Metal seal	VQC2200	2.0	0.15	0.46	2.6	0.15	0.60	15 or less	20 or less	
	2	Double	Rubber seal	VQC2201	2.2	0.28	0.55	3.2	0.30	0.80	20 or less	26 or less	
0		Closed	Metal seal	VQC2300	2.0	0.15	0.46	2.0	0.18	0.46	29 or less	38 or less	
VQC2000		center	Rubber seal	VQC2301	2.0	0.28	0.49	2.2	0.31	0.60	34 or less	44 or less	
Ö	position	Exhaust	Metal seal	VQC2400	2.0	0.15	0.46	2.6	0.15	0.60	29 or less	38 or less	
>		center	Rubber seal	VQC2401	2.0	0.28	0.49	3.2	0.30	0.80	34 or less	44 or less	110
	3	Pressure	Metal seal	VQC2500	2.4	0.17	0.57	2.0	0.18	0.46	29 or less	38 or less	
		center	Rubber seal	VQC2501	3.2	0.28	0.80	2.2	0.31	0.60	34 or less	44 or less	
	4 position	Dual 3 port valve	Rubber seal	VQC2B01	1.8	0.28	0.46	1.8	0.28	0.46	34 or less	44 or less	
	_	Cinalo	Metal seal	VQC4100	6.2	0.19	1.5	6.9	0.17	1.7	20 or less	22 or less	230
	position	Single	Rubber seal	VQC4101	7.2	0.43	2.1	7.3	0.38	2.0	25 or less	27 or less	230
	2 pos	Daubla	Metal seal	VQC4200	6.2	0.19	1.5	6.9	0.17	1.7	12 or less	12 or less	260
	7	Double	Rubber seal	VQC4201	7.2	0.43	2.1	7.3	0.38	2.0	15 or less	15 or less	200
0		Closed	Metal seal	VQC4300	5.9	0.23	1.5	6.3	0.18	1.6	45 or less	47 or less	
400		center	Rubber seal	VQC4301	7.0	0.34	1.9	6.4	0.42	1.9	50 or less	52 or less	
VQC4000	_	Exhaust	Metal seal	VQC4400	6.2	0.18	1.5	6.9	0.17	1.7	45 or less	47 or less	280
>	position	center	Rubber seal	VQC4401	7.0	0.38	1.9	7.3	0.38	2.0	50 or less	52 or less	200
	3 pos	Pressure	Metal seal	VQC4500	6.2	0.18	1.9	6.4	0.18	1.6	45 or less	47 or less	
	(-)	center	Rubber seal	VQC4501	7.0	0.38	1.9	7.1	0.38	2.0	50 or less	52 or less	
		Porfoot	Metal seal	VQC4600	2.7	_	_	3.7	_	_	55 or less	57 or less	E00
		Perfect	Rubber seal	VQC4601	2.8			3.9			62 or less	64 or less	500
	N	Note 1) Values represented in this column are in the following conditions:											

VQC1000: Cylinder port size C6 without a back pressure check valve

VQC2000: Cylinder port size C8 without a back pressure check valve VQC4000: Cylinder port size Rc 3/8

Note 2) Values represented in this column are based on JIS B 8375-1981 (operating with clean air and a supply pressure of 0.5 MPa. Equipped with light/surge voltage suppressor. Values vary depending on the pressure as well as the air quality.) Values for double types are when the switch is ON.

VQC

SQ

VQ0

VQ4

VQ5

VQZ

VQD

Standard Specifications

	Valve Configuration				Metal seal	Rubber seal			
	Fluid			Air/Inert gas					
	00	Max. operating p	ressu	re	0.7 MPa (High pressur	e type: 1.0 MPa) Note 4)			
	/20		Singl	е	0.1 MPa	0.15 MPa			
	000	Min. operating	Doub	ole	0.11	MPa			
	VQC1000/2000	pressure	3 pos	sition	0.1 MPa	0.2 MPa			
ions)/		4 pos	sition	_	0.15 MPa			
ficat	0	Max. operating p	ressur	e Note 3)	1.0 MPa (0.7 MPa)			
Valve specifications	VQC4000	Min. operating	Singl	е	0.15 MPa	0.2 MPa			
ve s	Ø	pressure	Doub	ole	0.15	MPa			
Val	١_		3 pos	sition	0.15 MPa	0.2 MPa			
	Pr	oof pressure			1.5 MPa				
	An	nbient and fluid te	mpera	ature	-10 to 50°C Note 1)				
	Lu	brication			Not re	quired			
	Ma	anual override			Push type/Locking type (tool required)/Locking typ	e (Manual override) Note 5)/Slide locking type Note 5)			
	Im	pact resistance/Vibra	tion res	sistance	150/30 m	/S ² Note 2)			
	En	nclosure			Dust proof (IP	67 compliant)			
S	Rated coil voltage				24 \	/DC			
Sal	Allowable voltage fluctuation		ion	±10% of rated voltage					
Electrical specifications	Coil insulation type			Equivalent to B type					
Spec		ower consumption		24 VDC	1 W DC (42 mA), (0.5 W DC (21 mA)			
	" (Current) 12 VDC		12 VDC	1 W DC (83 mA), 0.5 W DC (42 mA)					

Note 1) Use dry air to prevent condensation at low temperatures.

Note 2) Impact resistance: No malfunction resulted from the impact test using a drop impact tester. The test was performed one time each in the axial and right angle directions of the main valve and armature, for both energized and de-energized states.

Vibration resistance: No malfunction occurred in a one-sweep test between 45 and 2000Hz. Test was performed in the axial and right angle directions of the main valve and armature for both energized and de-energized states.

Note 3) Values in () are for the low wattage (0.5 W) specification.

Note 4) Metal seal type only.

Note 5) Only for VQC1000/2000.

Manifold Specifications

				Piping specificat	ions	Note 2)	Applicable	5 station
Series	Base model	Connection type	Port	Port siz	ze Note 1)	Applicable stations	solenoid	weight
			direction	1, 3 (P, R)	2, 4 (A, B)	Stations	valves	(g)
VQC1000	VV5QC11-□□□	■ F Kit: D-sub connector ■ P Kit: Flat cable ■ T Kit: Terminal block box ■ S Kit: Serial transmission ■ L Kit: Lead wire ■ M Kit: Multiple connector	Side	C8 (For ø8) Options Direct outlet with built-in silencer	C3 (For ø3.2) C4 (For ø4) C6 (For ø6) M5 (M5 threads)	(F, L, M and P kits) 1 to 12 stations) (T kit 1 to 10 stations)	, / VQC1□00-5	628 (Single) 759 (Double, 3P)
VQC2000	VV5QC21-□□□		Side	C10 (For ø10) Options Direct outlet with built-in silencer Branch type C12 (for ø12)	C4 (For ø4) C6 (For ø6) C8 (For ø8)	S kit 1 to 8 stations: EX500 1 to 12 stations: EX250 1 to 8 stations: EX126	VQC2□00-5 VQC2□01-5	1051 (Single) 1144 (Double, 3P)
VQC4000	VV5QC41-□□□		Side	P: Rc 1/2 R: Rc 3/4	C8 (For Ø8) C10 (For Ø10) C12 (For Ø12) Rc 1/4 Rc 3/8	(F, L, M and P kits 1 to 12 stations) T kit 1 to 10 stations) S kit 1 to 12 stations: EX240, EX250	/	4150 • S kit (without unit) • Solenoid weight is not included.
			Bottom		Rc 1/4	1 to 8 stations: EX500 1 to 8 stations: EX126		

Note 1) One-touch fittings in inch sizes are also available.

Note 2) An optional specification for special wiring is available to increase the maximum number of stations.



Series VQC

VQC1000/2000/4000 Kit (Serial transmission kit) Decentralized Serial Wiring

Gateway type serial transmission system

 Since wiring is "prepackaged" into one multi-connector type cable, wiring work is not only made easier, but much more accurate.

S kit can be used by connecting to gateway unit.

Gateway (GW) Unit IP65 compliant



How to Order

EX500-G DN1

Communication protocol


DN1	DeviceNet	AB1-X1	Remote I/O (RIO)
PR1A	PROFIBUS-DP	MJ1	CC-LINK

Specifications

Model	EX500-GAB1-X1	EX500-GDN1	EX500-GPR1A	EX500-GMJ1			
Applicable PLC/ Communication protocol	Rockwell Automation PLC	DeviceNet Release 2.0	PROFIBUS-DP (EN50170)	CC-LINK Ver. 1.10			
Communication speed	57.6/115.2/ 230.4 kbit/sec	125/250/500 kbit/sec	9.6/19.2/45.45/93.75/ 187.5/500 kbit/sec 1.5/3/6/12 Mbit/sec	156/625 kbit/sec 2.5/5/10 Mbit/sec			
Rated voltage		24 VD0	C				
Power supply		,	24 VDC ± 10% -5% (with power drop wa	arning at approx. 20 V)			
voltage range	_	Communication power supply for DeviceNet 11 to 25 VDC					
Command	200 mA or less (Single GW unit)						
Current consumption	_	Communication power supply for DeviceNet 50 mA or less	_	_			
Number of inputs/outputs		Maximum 64 in	puts/64 outputs				
Number of input/ output branches	4 b	ranches (16 inputs/	16 outputs per brar	nch)			
Branch cable		8 core heav	y duty cable				
Branch cable length	5	m or less (total ext	tension 10 m or less	s)			
Communication connector		M12 connector	(8 pins, socket)				
Power connector	M12 connector (5 pins, plug)						
Ambient operating temperature/humidity	+5 to +45°C at 35% to 85% RH (No condensation)						
Enclosure	IP65						
Applicable standard		UL, CS	SA, CE				
Weight (g)		47	70				

Input Block IP67 compliant


How to Order Input Manifold





Note) When ordering an input block manifold, enter the [Input manifold part no.]+ [Input block part no.] together. The input block, end block and DIN rail are included in the input manifold.

How to Order Input Block



Applicable GW unit Nil DeviceNet PROFIBUS-DP -X1 Remote I/O (RIO)

Input Unit Specifications

Connection block	Current source type input block (PNP input block) or Current sink type input block (NPN input block)				
Communication connector	M12 connector (8 pins, plug)				
Number of connection blocks	Maximum 8 blocks				
Block supply voltage	24 VDC				
Block supply current	0.65 A maximum				
Current consumption	100 mA or less (at rated voltage)				
Short circuit protection	Operates at 1A Typ. (power supply cut) GW unit reset by turning power OFF and back ON.				
Enclosure	IP65				
Weight (g) Note)	100 (Input unit + end block)				

Note) Not including the DIN rail weight.

Input Block Specifications

par = room opcomoanom					
Applicable sensor	Current source type (PNP output) or Current sink type (NPN output)				
Sensor connector	M8 connector (3 pins) or, M12 connector (4 pins)				
Number of inputs	2 inputs/8 inputs (M8 only)				
Rated voltage	24 VDC				
Indication	Green LED				
Insulation	None				
Sensor supply current	Maximum 30 mA/Sensor				
Enclosure	IP65				
Weight (g)	[For M8: 20] [For M12: 40] [8 point integrated type, for M8: 55]				





VQC

SQ

VQ0

VQ4


VQ5

VQZ

VQD

SI Unit

How to Order




Specifications


Connection block	Solenoid valve (single, double) Relay output module (1 output, 2 outputs)
Communication connector	M12 connector (8 pins, plug, socket)
Number of connection block stations	Double solenoid valve Relay output module (2 points): Maximum 8 stations Single solenoid valve Relay output module (1 point): Maximum 16 stations
Block supply voltage	24 VDC
Block supply current	0.65 A maximum
Current consumption	100 mA or less (at rated voltage)
Weight (g)	115


Cable

How to Order Cable with M12 Connector




How to Order Power Cable with Connector





Socket connector Connections pin arrangement

Plug connector pin arrangement




Socket connector Connections pin arrangement

Series VQC



VV5QC11 SA1 Kit (Serial transmission kit: EX500)



Formulas

L1 = 10.5n + 45 (Maximum 16 single wiring stations) n: Stations 2 3 4 5 6 8 10 12 13 15 16 L1 55.5 66 76.5 87 97.5 108 118.5 129 139.5 150 160.5 171 181.5 192 202.5 213 114.5 L2 104 125 135.5 146 156.5 167 177.5 188 198.5 209 219.5 230 240.5 251 261.5 125 137.5 150 162.5 187.5 200 212.5 225 237.5 250 250 262.5 275 287.5 L3 175 187.5 135.5 148 160.5 185.5 210.5 223 235.5 248 260.5 260.5 273 285.5 298 L4 173 198

^{*} With signal cut block, L4 is obtained by adding approximately 30 mm to L2.

VQC

SQ

VQ0


VQ4

VQ5

VQZ

VQD

VV5QC21 SA1 Kit (Serial transmission kit: EX500)



Formulas L1 = 16n + 57 (Maximum 16 single wiring stations)


n. Stations

										1011 1 07	(IVIGAIITIGII	i io sirigio	, wiring sic	ations)		ii. Otaliolis
Ln	1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16
L1	73	89	105	121	137	153	169	185	201	217	233	249	265	281	297	313
L2	118	134	150	166	182	198	214	230	246	262	278	294	310	326	342	358
L3	137.5	150	175	187.5	200	212.5	237.5	250	262.5	287.5	300	312.5	337.5	350	362.5	375
L4	148	160.5	185.5	198	210.5	223	248	260.5	273	298	310.5	323	348	360.5	373	385.5

^{*} With signal cut block, L4 is obtained by adding approximately 30 mm to L2.

Series VQC

VV5QC41 SA1 Kit (Serial transmission kit: EX500)



Formulas L1 = 25n + 106 (Maximum 16 single wiring stations)

n: Stations

L	1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16
L1	131	156	181	206	231	256	281	306	331	356	381	406	431	456	481	506
L2	177	202	227	252	277	302	327	352	377	402	427	452	477	502	527	552



Series VQC

VQC1000/2000/4000 Kit (Serial Transmission Kit) for I/O IP67 compliant

Compatible network

DeviceNet/PROFIBUS-DP/CC-Link

• The serial transmission system greatly reduces connection work, minimizes wiring, and saves space.

SI unit for DeviceNet/PROFIBUS-DP/CC-LINK

As a DeviceNet/PROFIBUS-DP/CC-LINK slave unit, this kit is capable of up to 32 points of solenoid valve ON and OFF control.

Furthermore, by connecting an input block, a maximum 32 sensor signal inputs are possible.

SI unit for AS-i

As a AS-i slave unit, this kit is capable of up to 4 or 8 points of solenoid valve ON and OFF control.


Furthermore, by connecting an inmput block, a maximun 4 or 8 sensor signal inputs are possible.

Input block

This expansion block connects to the SI unit and allows for sensor input to the auto switches.

Each input block can receive input from up to two or four sensors, and the common can be matched to the sensor by an NPN/PNP selector switch. Input connectors are available in both M8 and M12 types.

Connector Details



Circuit diagram Input module (EX250-IE*)

Input connection: M12 ... 5 pins (Socket)
Example for the cable side connection: OMRON Corporation XS2G; Karl Lumberg GmbH: Series RST5; Franz Binder GmbH: Series 713,763



Pos.	Description	Function
1	SW+	Sensor power supply +
2	N.C (SIGNAL)	Open*
3	SW-	Sensor power supply –
4	SIGNAL	Sensor input signal
5	E	Sensor ground connection

 \ast In the 4 input type unit (EX250-IE2), this is the input signal from the second sensor connected

Communication connector

CANopen: Female connector cable: M12 female 5 pins cable with shield (according to ISO11898).

ition	Function
HLD S	Shield
+ F	Power supply +
ND F	Power supply –
В	Bus line (dominant High)
В	Bus line (dominant Low)
	HLD S '+ F AND F



 $\label{eq:decomposition} \textbf{DeviceNet:} \ \ \text{M12...5 pins (Plug) Example for a cable set with plug / socket:} \\ \text{OMRON Corporation DCA1-5CN05F1. Karl Lumberg GmbH: 0935 253 103/...M, RSC RKC 57}^*$ Accessories, bus branch Y: Karl Lumberg GmbH: 0906 UTP 101, Hans Turck GmbH: VB2-FKM-FSM57. Accessories terminating socket with resistor: Hans Turck GmbH: RSE57-TR2, Karl Lumberg GmbH: 0939 CXT 101.

Pos.	Description	Function
1	Drain	Drain / shield
2	V+	Circuit power supply +
3	V-	Circuit power supply -
4	CAN_H	Signal H
5	CAN_L	Signal L



PROFIBUS-DP: M12... 5 pins reserve-keyed (Socket). Example for the corresponding cable sets with plug / socket: Hans Turck GmbH: RSSW-RKSW456...M; Karl Lumberg GmbH: 0975 254 101/...M Accessories Bus branch Y: Hans Turck GmbH: VB2/FSW/FKW/FSW45

Accessories terminating resistor: Hans Turck GmbH: RSS4.5-PDP-TR; Karl Lumberg GmbH: 0979PTX101


Pos.	Description	Function
1	VP	Power supply for terminating resistor
2	A-N	Negative for data transfer/reception
3	DGND	Ground for terminating resistor
4	B-P	Positive for data transfer/reception
5	SHIELD	Shield



Power supply

DeviceNet:: M12 ... 5 pins reserve-keyed (Plug) (The configuration of the connection surface area differs from that of the transmission plug)

Example of the cable set with socket: Hans Turck GmbH: WAKW4.5T-2, Franz Binder GmbH: 79-4449-..-05




os.	Description	Function
1	SV24V	+24 V solenoid valve
2	SV0V	0V solenoid valve
3	SW24V	+24 V SI and input blocks
4	SW0V	0 V SI and input blocks
5	E	Ground connection
	1 2 3 4	1 SV24V 2 SV0V 3 SW24V 4 SW0V



PROFIBUS-DP: M12...5 pins (Plug) Example of the cable set with socket SMC: EX500-AP...S (See page 2-2-25.)

Pos.	Description	Function
1	SV24V	+24 V solenoid valve
2	SV0V	0 V solenoid valve
3	SW24V	+24 V SI and input blocks
4	SW0V	0 V SI and input blocks
-5	Е	Ground connection





Input connection: M8 ... 3 pins (Socket)
Example for cable side connection: Franz Binder GmbH Series 718, 768 Karl Lumberg GmbH: Series RSMV3



_			
1	Pos.	Description	Function
Ī	1	SW+	Sensor power supply +
	3	SW-	Sensor power supply -
	4	SIGNAL	Sensor input signal



VQC

SQ

VQ0

VQ4

VQ5

VQZ

VQD

Plug-in Unit Series VQC

AS-i EX250-SAS7 / EX250-SAS9

Communication connector: M12 male 4 pins




Pos.	Description	Function
1	AS-i +	Positive AS-Interface line
2	RESERVE	RESERVE
3	AS-i –	Negative AS-Interface line
4	RESERVE	RESERVE



Connection example

EX250-SAS7

BUS



AS-i EX250-SAS3 / EX250-SAS5

Communication connector: M12 male 4 pins




Pos.	Description	Function	
1	AS-i +	Positive AS-Interface line	
2	OV	Negative output equipment power line	\leftarrow
3	AS-i –	Negative AS-Interface line	
4	24V	Positive output equipment power line	\leftarrow


Output equipment power connector: M12 male 4 pins



Pos.	Description	Function	
1	24V	Positive output equipment power line	\Box
2	NC	Not connected	
3	0V	Negative output equipment power line	
4	NC	Not connected	-
		0	-

^{*} Connected inside the SI unit.









Indicator Unit (LED) Description and Its Function

■ SI unit DeviceNet (EX250-SDN1)




Name	Function		
PWR(V)	ON when solenoid valve power supply is turned ON.		
PWR	ON when DeviceNet circuit power supply input is turned ON.		
	OFF: Power supply off, off line, or when checking duplication of MAC_ID.		
	GREEN BLINKING: Waiting for connection (on line).		
MOD/NET	GREEN ON: Connection established (on line).		
INIOD/INET	RED BLINKING: Connection time out (minor communication abnormality).		
	RED ON: MAC_ID duplication error, or BUSOFF error (major communication abnormality).		

■ PROFIBUS-DP (EX250-SPR1)



Name	Function	
DMD()	GREEN ON when solenoid valve power supply is turned ON.	
PWR(V)	GREEN OFF when the power supply voltage is less than 19 V.	
RUN	GREEN ON when operating (SI unit power supply is ON).	
DIA	RED ON when self diagnosis device detects abnormality.	
BF	RED ON for BUS abnormality.	

■ Input block (EX250-IE1/2/3)



Description	Function
PWR	ON when sensor power is turned ON.
0 to 1(3)	ON when each sensor input goes ON.



* Please contact your SMC representative for specifications and handling precautions.

■ CC-Link (EX250-SMJ2)



Name	Function	
PW	ON: Input and control unit power supply ON. OFF: Input and control unit power supply OFF.	
PW(V)	ON: Solenoid valve power supply ON. OFF: Solenoid valve power supply voltage is less than 19 V.	
L RUN	ON: Normal traffic OFF: Traffic disconnected (Timeover error)	
L ERR	ON: Traffic error BLINKING: Station or baud rate switch is set while the power supply is ON. OFF: Normal traffic	

When the data link is normal, PW, PW (V) and L RUN are ON.

■ AS-i (EX250-SAS□)



Name	LED Condition	Contents
PWR	PWR Green Light In time of power supply for AS-Interface line is turned on.	
AUX	Green Light	In time of auxiliary power supply for output equipment is turned on.
IN-ERR Red Light In time of input power is detected over current. (Lights off at normal condition)		
COM- ERR	Red Light	In time of communication error. (Lights off at normal condition)
	Red Blink	In time of peripheral equipment error. (Over current of input power, blowing the fuse etc.)

■ SI unit CANopen (EX250-SCA1)



Name	LED Condition	Contents
PWR(V)	Green Light	Illuminates when power for solenoid valves is supplied
PVVH(V)	Green Light	Illuminates when power for CANopen line is supplied
PWR	Green Light	Illuminates when SI unit is in the Operational state
	Green Light (Blinking)	SI unit is in the Pre-operational state
	Green Light (Single flash)	Single flash when SI unit is in Stopped state
0.441	Red Light (Single flash)	Single flash when CAN controller error occurs
CAN	Red Light (Double flash)	Double flash when Error Control Event occurs
	Green/Red Light	Flickering when SI unit is in Configuration mode
	(flickering)	(LSS services)
	Red Light	Red Light SI unit is in "Bus OFF" state

VQC

SQ

VQ₀


VQ4


VQ5

VQZ

VQD

Plug-in Unit Series VQC





16 17 18

335.5 346

362.5 375

223.5 234

385.5 398

202.5 213

360.5 373

314.5 325

337.5 350

19 20

387.5 387.5 400

398

356.5 367

244.5 255

410.5 423

Formulas

L1

12

L3

L1 = 10.5n + 45 (Maximum 24 single wiring stations)

76.5 87

235.5 248

2 3

66

188.5 199

212.5 225

55.5

178

* L2: For one input block. Add 21 mm for each additional input block 4

209.5 220

237.5 250

n: Stations 21 22 23 24 286.5 297 265.5 276 419.5 377.5 388 398.5 409 412.5 425 437.5 450

> 435.5 448 448

5

97.5 108

6

250

230.5 241

8

251.5 262

285.5 298

118.5 129

262.5 275

9

139.5 150

287.5 300

10 11

272.5 283

310.2 323

12

293.5 304

160.5 171

312.5 325


13 14 15

181.5 192

325

335.5 335.5 348

VV5QC21 S Kit (Serial transmission kit: EX250)



L1 = 16n + 57 (Maximum 24 single wiring stations)

 * L2: For one input block. Add 21 mm for each additional input block 4 5 8 10 11 12 13 14 15 16 17 18 19 20 21 22 23 24 3 6 73 89 105 121 137 153 169 185 201 217 233 249 265 281 297 313 329 345 361 377 393 409 425 441 L1 L2 192 208 224 240 256 272 288 304 320 336 352 368 384 400 416 432 448 464 480 496 512 528 544 560 L3 212.5 237.5 250 262.5 275 287.5 312.5 325 337.5 362.5 375 387.5 400 425 437.5 450 462.5 487.5 500 512.5 537.5 550 562.5 587.5 248 260.5 273 285.5 298 323 335.5 348 373 385.5 398 410.5 435.5 448 460.5 473 498 510.5 523 548 560.5 573 | 598

n: Stations


^{260.5 260.5 273} * With signal cut block, L4 is obtained by adding approximately 30 mm to L2.


^{*} With signal cut block, L4 is obtained by adding approximately 30 mm to L2.

Series VQC



VV5QC41 S Kit (Serial transmission kit: EX250)





Formulas

L1 = 25n + 106 (Maximum 16 single wiring stations)

* L2: For one input block. Add 21 mm for each additional input block.

n: Stations

L	1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16
L1	131	156	181	206	231	256	281	306	331	356	381	406	431	456	481	506
L2	230	255	280	305	330	355	380	405	430	455	480	505	530	555	580	605





Compatible network | DeviceNet/PROFIBUS-DP

The serial transmission system greatly reduces connection work, minimizes wiring, and saves space.

DeviceNet/PROFIBUS-DP compatible SI unit

As a DeviceNet/PROFIBUS-DP slave unit, this kit is capable of solenoid valve ON and OFF control up to 32 points.

Furthermore, by connecting an input block, up to 32 sensor signal inputs

Input block

This expansion block connects to the SI unit and allows for sensor input to the auto switches.

Each input block can receive input from up to 8 sensors, and the common can be matched to the sensor by an NPN/PNP selector switch.

Connector Details

SI unit (PROFIBUS-DP) Input block SI unit (DeviceNet) Communication connector Input connector Power connector

• Communication connector (PROFIBUS-DP): CONINVERS GmbH RC-2RS1N12, 12 pins

Cable side connector example: Siemens AG 6ES5 760-2CB11



No.	Description	Function
1	M5V	GND Terminal
2	Α	Signal –N
4	В	Signal –P
6	+5V	Terminal +5V
9	SHIELD	Shield ground
12	RTS	Optical fiber (reserve)

- Pin no. 3, 5, 7, 8, 10 and 11 marked with "●" are open.
- * The connector configuration and the pin arrangement are compatible with Siemens AG ET200C
- Input connector: M12, 5 pins (OMRON Corporation XS2F compatible) x 8 pcs.

Cable side connector example: OMRON Corporation XS2G



	No.	Description	Function
	1	SW +	(+) Sensor power supply
	2	N.C.	Open*
3	3	SW -	(-) Sensor power supply
	4	SIGNAL	Sensor input signal
	5	PE	Protective sensor ground

* The second pin of the connector with input no. 0, 2, 4, 6 (the connector at the right side of the input block) is connected internally to the fourth pin (sensor input no.) of the connector with input no. 1, 3, 5, 7. This makes it possible to directly input two inputs that are combined together by the common connector.

Connector:	Input no	. 0, 2, 4, 6	Inpu	ut no. 1, 3,	5,
SW+		1	}	1	
SIGNAL -n + 1		2		2	
SW-		3		3	
SIGNAL -n		4		4	
PF		5		5	

* DIN type 5 pins

No.	Description	Function
1	SV24V	For solenoid valve +24V
2	SV0V	For solenoid valve +0V
3	PE	Protective ground
4	SW24V	For solenoid valve +24V
5	SW0V	For solenoid valve +0V
	1 2 3 4	1 SV24V 2 SV0V 3 PE 4 SW24V

 Power connector: Franz Binder GmbH Series 723. 5 pins (72309-0115-80-05) Cable side connector example: Franz Binder GmbH 72309-0114-70-15, etc.

 Communication connector (DeviceNet): M12, 5 pins (for DeviceNet only) Example of corresponding cable assemblies with connector: OMRON Corporation DCA1-5CN05F1, Karl Lumberg GmbH & Co. KG RKT5-56.



No.	Description	Function
1	Drain	Drain/Shield
2	V +	(+) Circuit power supply
3	V –	(-) Circuit power supply
4	CAN_H	Signal H
5	CAN L	Signal L


Compatible with DeviceNet specification Micro

When IP65 or equivalent enclosures are required, install a waterproof cover on the input connector that is not being used. Order waterproof covers separately.

Example: OMRON Corporation XS2Z-12


Indicator Unit (LED) Description and Its Function

■ SI unit (DeviceNet)



Description	Function			
PWR(V) ON when solenoid valve power supply is turned ON.				
PWR	ON when DeviceNet circuit power supply input is turned ON.			
	OFF: Power supply off, off line, or when checking duplication of MAC_ID.			
	GREEN BLINKING: Waiting for connection (on line).			
MOD/NET	GREEN ON: Connection established (on line).			
	RED BLINKING: Connection time out (minor communication abnormality).			
	RED ON: MAC_ID duplication error, or BUSOFF error			
	(major communication abnormality).			

■ SI unit (PROFIBUS-DP)



Description	Function
DIME (1.0	ON when solenoid valve power supply is turned ON.
PWR(V)	OFF when the power supply voltage is less than 19V.
RUN	ON when operating (SI unit power supply is ON).
DIA	ON when self diagnosis device detects abnormality.
BF	ON for BUS abnormality.

Input block



Description	Function
PWR	ON when sensor power is turned ON. OFF when short circuit protection is working.
0 to 7	ON when each sensor input goes ON.

SQ

VQ0


VQ4


VQ5

VQZ

VQD

VV5QC41 S Kit (Serial transmission kit: EX240)





 $Formulas: L1 = 25n + 106, L2 = 25n + 241 \ (For \ 1 \ input \ block. For \ each \ additional \ input \ block, \ add \ 54 \ mm.) \ n: \ Stations \ (Maximum \ 16 \ stations)$

L	1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16
L1	131	156	181	206	231	256	281	306	331	356	381	406	431	456	481	506
L2	266	291	316	341	366	391	416	441	466	491	516	541	566	591	616	641


VQC1000/2000/4000 Kit (Serial transmission kit) for I/O IP67 compliant

Compatible network


CC-Link

• The serial transmission system greatly reduces connection work, minimizes wiring, and saves space.

Terminal Block Connection



Step 2. Wire the cables according to the terminal block specifications below. Pay attention to the wire bound positions.



Step 3. How to replace the terminal block cover


Securely tighten the screws to the torque shown in the table below, after confirming that the gasket is installed correctly.

Proper tightening torque (N·m)	
0.7 to 1.2	

- Applicable crimp terminal (fork tongue type): 1.25-3S, 1.25Y-3 1.25Y-3N, 1.25Y-3.5
- * For detailed specifications and handling, refer to the operation manual provided by SMC.


Terminal Block Details

• Terminal block LED descriptions



Description	Function
PW	ON when transmission power supply is ON. OFF when transmission power supply is OFF.
L RUN	ON when normal data is received.
SD	ON when data is sent.
RD	ON when data is received.
L ERR.	ON for transmission error and incorrect settings. BLINKING for change in station or transmission speed settings.

Cable wiring



Note

 CC-LINK System Master unit: AJ61BT11 Master unit: A1SJ61BT11 Master unit: AJ61QBT11 Master unit: A1SJ61QBT11

• 16 outputs

SQ

VQ0


VQ4


VQ5

VQZ

VQD

VV5QC11 S Kit (Serial transmission kit: EX126)





Formulas

L1 = 10.5n + 45 (Maximum 16 single wiring stations) L2 = 10.5n + 154.5


L n	1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16
L1	55.5	66	76.5	87	97.5	108	118.5	129	139.5	150	160.5	171	181.5	192	202.5	213
L2	165	175.5	186	196.5	207	217.5	228	238.5	249	259.5	270	280.5	291	301.5	312	322.5
L3	187.5	200	212.5	212.5	225	237.5	250	262.5	275	275	287.5	300	312.5	325	337.5	337.5
L4	198	210.5	223	223	235.5	248	260.5	273	285.5	285.5	298	310.5	323	335.5	348	348

^{*} With signal cut block, L4 is obtained by adding approximately 30 mm to L2.

2-2-39



VV5QC21 S Kit (Serial transmission kit: EX126)



Formulas

L1 = 16n + 57 (Maximum 16 single wiring stations) L2 = 16n + 163

L	1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16
L1	73	89	105	121	137	153	169	185	201	217	233	249	265	281	297	313
L2	179	195	211	227	243	259	275	291	307	323	339	355	371	387	403	419
L3	200	212.5	237.5	237.5	262.5	262.5	287.5	312.5	325	371	362.5	375	408.5	412.5	425	437.5
L4	210.5	223	248	248	273	273	298	323	335.5	360.5	373	385.5	398	423	435.5	448

^{*} With signal cut block, L4 is obtained by adding approximately 30 mm to L2.

SQ

VQ0


VQ4


VQ5

VQZ

VQD

VV5QC41 S Kit (Serial transmission kit: EX126)





Formulas L1 = 25n + 106 (Maximum 16 single wiring stations)


L2 = 25n + 192														1	n: Stations	
L	1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16
L1	131	156	181	206	231	256	281	306	331	356	381	406	431	456	481	506
L2	217	242	267	292	317	342	367	392	417	442	467	492	517	542	567	592

VQC1000/2000/4000 Kit (D-sub connector kit)

IP40 compliant

- Using our D-sub connector for electrical connections greatly reduces labour, while it also minimizes wiring and saves space.
- We use a D-sub connector (25P) that conforms to MIL standards and is therefore widely compatible with many standard commercial models.
- Top or side entry for the connector can be changed freely, allowing for changes even after mounting, to meet any changing needs for space.


Electrical Wiring Specifications



Lead wire colours according to The colour code is according to SOL. A ·o 1 DIN47100 SOL. B ○ 14 Station 1 (-)(+)Pin no. Cable colour Identification SOL. A 2 (-) white (+) Station 2 brown (-)(+) SOL. A o 3 3 green (+) (-)Station 3 SOL. B ○ 16 yellow (-)(+) SOL. A_O 4 grey (-) (+) pink SOL. B ○ 17 Station 4 (-)(+) blue SOL. A_O 5 (-)(+) 8 red Station 5 SOL. B 0 18 9 black (-)(+) SOL. A 10 violet (-) (+) SOL. B 0 19 Station 6 grey (+) SOL. A 12 blue red (-)(+) Station 7 SOL. B 0 20 13 white green (-) (+) 14 brown green SOL. A 15 white yellow (+) Station 8 < SOL. B ○ 21 16 vellow brown (-)(+) SOL. A 9 white grey (-) (+) Station 9 SOL. B o 22 18 grey brown (+) pink 19 white SOL. A 0 10 (-)(+) Station 10 < 20 pink brown SOL. B 0 23 (-)(+) SOL. A_O 11 (-)(+) 22 brown blue Station 11 SOL. B 0 24 (+) 23 white red SOL. A 0 12 24 brown red (-)(+)Station 12 < SOL. B o 25 25 white black (+) COM ○ 13 Note) When using the negative COM specification for VQC1000/2000, use valves for negative COM.

Special Wiring Specifications (Option)

COM



Mixed single and double wiring are available as options. The maximum number of manifold stations is determined by the number of solenoids. Count one point for a single solenoid type and two points for a double solenoid type. The total number of solenoids (points) must not exceed 24.

Cable Assembly

■ D-sub connector cable assembly (25 pins)


GVVZS3000-21A-□

D-sub connector/cable

Cable length (L)	Part no.	Plug type
1 m	GVVZS3000-21A-160	60° outlet
3 m	GVVZS3000-21A-260	60° outlet
5 m	GVVZS3000-21A-360	60° outlet
8 m	GVVZS3000-21A-460	60° outlet
3 m	GVVZS3000-21A-2	Standard
5 m	GVVZS3000-21A-3	Standard
8 m	GVVZS3000-21A-4	Standard

Shielded cable

Cable length (L)	Part no.	Cable type
1 m	GVVZS3000-21A-1S	shielded
3 m	GVVZS3000-21A-2S	shielded
5 m	GVVZS3000-21A-3S	shielded
8 m	GVVZS3000-21A-4S	shielded
20 m	GVVZS3000-21A-5S	on demand




Electrical characteristics

orial actor lotiot	
Item	Charac- teristics
Conductor resistence Ω /km, 20°C	57 or less
Electric strength V, 5min, AC	1500
Insulation resistence MΩ/km	20

Standard version

(See also AXT100-DS25-050 which conforms to colour code MIL-C24308)

* For detailed specifications and handling, please contact SMC.



Formulas

L1 = 10.5n + 45 (Maximum 24 single wiring stations)

L2 = 10.5n + 102


n.	Stations

L_n	1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24
	55.5	66	76.5	87	97.5	108	118.5	129	139.5	150	160.5	171	181.5	192	202.5	213	223.5	234	244.5	255	265.5	276	286.5	297
L2	112.5	123	133.5	144	154.5	165	175.5	186	196.5	207	217.5	228	238.5	249	259.5	270	280.5	291	301.5	312	322.5	333	343.5	354
L3	137.5	150	162.5	175	175	187.5	200	212.5	225	237.5	237.5	250	262.5	275	287.5	300	300	312.5	325	337.5	350	362.5	375	375
L4	148	160.5	173	185.5	185.5	198	210.5	223	235.5	248	248	260.5	273	285.5	298	310.5	310.5	323	335.5	348	360.5	373	385.5	385.5

^{*} With signal cut block, L4 is obtained by adding approximately 30 mm to L2.



VV5QC21



Formulas

L1 = 16n + 57 (Maximum 24 single wiring stations)

L2 = 16n + 110.5

n: Stations

(Conforms to MIL-C-24308)

L	1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24
L1	73	89	105	121	137	153	169	185	201	217	233	249	265	281	297	313	329	345	361	377	393	409	425	441
L2	126.5	142.5	158.5	174.5	190.5	206.5	222.5	238.5	254.5	270.5	286.5	302.5	318.5	334.5	350.5	366.5	382.5	398.5	414.5	430.5	446.5	462.5	478.5	494.5
L3	150	162.5	187.5	200	212.5	237.5	250	262.5	275	300	312.5	325	350	362.5	375	387.5	412.5	425	437.5	450	475	487.5	500	525
L4	160.5	173	198	210.5	223	248	260.5	273	285.5	310.5	323	335.5	360.5	373	385.5	398	423	435.5	448	460.5	485.5	498	510.5	535.5

^{*} With signal cut block, L4 is obtained by adding approximately 30 mm to L2.

SQ


VQ0

VQ4

VQ5

VQZ

VQD



2 3

156 181

206 231

L1

131

Formulas L1 = 25n + 106 (Maximum 16 single wiring stations) L2 = 25n + 139.5


164.5 189.5 214.5 239.5 264.5 289.5 314.5 339.5 364.5 389.5 414.5 439.5 464.5 489.5 514.5 539.5




VQC1000/2000/4000 Kit (Flat ribbon cable kit) IP40 compliant

- Using our flat ribbon cable for electrical connections greatly reduces labour, while it also minimizes wiring and saves space.
- We use flat ribbon cables whose connectors (26P and 20P) conform to MIL standards, and are therefore widely compatible with many standard commercial models.
- Top or side entry for the connector can be changed freely, allowing for changes even after mounting, to meet any changing needs for space.

Electrical Wiring Specifications






Cable Assembly

AXT100-FC 20 - 2

Type 26P flat ribbon cable connector assemblies can be ordered with manifolds. Refer to manifold ordering.



Flat ribbon cable connector assemblies (Option)


Cable	Part	no.
length (L)	26P	20P
1.5 m	AXT100-FC26-1	AXT100-FC20-1
3 m	AXT100-FC26-2	AXT100-FC20-2
5 m	AXT100-FC26-3	AXT100-FC20-3

- * When using a standard commercial connector, use a type 26P connector conforming to MIL-C-83503 or a type 20P with strain relief.
- * Cannot be used for transfer wiring.

Connector Manufacturers Example:


- Hirose Electric CO., Ltd.
- Sumitomo/3-M Limited
- Fujitsu, Ltd.
- Japan Aviation Electronics Industry, Ltd.
- J.S.T. Mfg. Co., Ltd.
- Oki Electric Cable Co., Ltd.

Special Wiring Specifications (Option)



Mixed single and double wiring are available as options. The maximum number of manifold stations is determined by the number of solenoids. Count one point for a single solenoid type and two points for a double solenoid type. The total number of solenoids (points) must not exceed 24.

VV5QC11



Formulas

L1 = 10.5n + 45 (Maximum 24 single wiring stations)

														10.5n +	- 102	axiiiiai	11 2 7 3	ingic w	iiiig st	allons)			n: S	tations
L	1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24
L1	55.5	66	76.5	87	97.5	108	118.5	129	139.5	150	160.5	171	181.5	192	202.5	213	223.5	234	244.5	255	265.5	276	286.5	297
L2	112.5	123	133.5	144	154.5	165	175.5	186	196.5	207	217.5	228	238.5	249	259.5	270	280.5	291	301.5	312	322.5	333	343.5	354
L3	137.5	150	162.5	175	175	187.5	200	212.5	225	237.5	237.5	250	262.5	275	287.5	300	300	312.5	325	337.5	350	362.5	375	375
L4	148	160.5	173	185.5	185.5	198	210.5	223	235.5	248	248	260.5	273	285.5	298	310.5	310.5	323	335.5	348	360.5	373	385.5	385.5

^{*} With signal cut block, L4 is obtained by adding approximately 30 mm to L2.

VQC


SQ

VQ0


VQ4

VQZ

VQD



VV5QC21



Formulas

L1 = 16n + 57 (Maximum 24 single wiring stations) L2 = 16n + 110.5

L	1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24
L1	73	89	105	121	137	153	169	185	201	217	233	249	265	281	297	313	329	345	361	377	393	409	425	441
L2	126.5	142.5	158.5	174.5	190.5	206.5	222.5	238.5	254.5	270.5	286.5	302.5	318.5	334.5	350.5	366.5	382.5	398.5	414.5	430.5	446.5	462.5	478.5	494.5
L3	150	162.5	187.5	200	212.5	237.5	250	262.5	275	300	312.5	325	350	362.5	375	387.5	412.5	425	437.5	450	475	487.5	500	525
L4	160.5	173	198	210.5	223	248	260.5	273	285.5	310.5	323	335.5	360.5	373	385.5	398	423	435.5	448	460.5	485.5	498	510.5	535.5

^{*} With signal cut block, L4 is obtained by adding approximately 30 mm to L2.

SQ

VQ0


VQ4

VQ5

VQZ

VQD

VV5QC41



_ n

131

L1

2

156

3


181

Formulas L1 = 25n + 106 (Maximum 16 single wiring stations)

 $L2 = 25n + 139.\dot{5}$ n: Stations 15 16 5 6 9 10 12 13 14 8 11 281 331 456 206 256 306 356 381 406 431 481 506 231 164.5 189.5 214.5 239.5 264.5 289.5 314.5 339.5 364.5 389.5 414.5 439.5 464.5 489.5 514.5 539.5




• This kit has a small terminal block inside a junction box. The provision of a G 3/4 electrical entry allows connection of conduit fittings.



Terminal Block Connection

Step 1. How to remove terminal block cover

Loosen the 4 mounting screws (M4) and remove the terminal block cover.




Step 3. How to replace the terminal block cover

Securely tighten the screws to the torque shown in the table below, after confirming that the gasket is installed correctly.

Proper tightening torque (N·m) 0.7 to 1.2


Step 2. The diagram below shows the terminal block wiring. All stations are provided with double wiring regardless of the valves which are mounted.

Connect each wire to the power supply side, according to the markings provided inside the terminal block.



• Applicable crimp terminal (fork tongue type): 1.25-3S, 1.25Y-3 1.25Y-3N, 1.25Y-3.5

Electrical Wiring Specifications (Conforms to IP67)



Special Wiring Specifications (Option)


Mixed single and double wiring are available as options. The maximum number of manifold stations is determined by the number of solenoids. Count one point for a single solenoid type and two points for a double solenoid type. The total number of solenoids (points) must not exceed 20.

1. How to order

Indicate option symbol "-K" in the manifold part number and be sure to specify station positions for single or double wiring on the manifold specification

2. Wiring specifications

Connector terminal numbers are connected from solenoid station 1 on the A side in the order indicated by the arrows without skipping any terminal numbers.





SQ

VQ0


VQ4

VQ5

VQZ

VQD

VV5QC11



Formulas


L1 = 10.5n + 45 (Maximum 20 single wiring stations) L2 = 10.5n + 154.5

											LZ - 10	J.511 1 10	54.5						11.	Glations
L_n	1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20
L1	55.5	66	76.5	87	97.5	108	118.5	129	139.5	150	160.5	171	181.5	192	202.5	213	223.5	234	244.5	255
L2	165	175.5	186	196.5	207	217.5	228	238.5	249	259.5	270	280.5	291	301.5	312	322.5	333	343.5	354	364.5
L3	187.5	200	212.5	212.5	225	237.5	250	262.5	275	275	287.5	300	312.5	325	337.5	337.5	350	362.5	375	387.5
14	198	210.5	223	223	235.5	248	260.5	273	285.5	285.5	298	310.5	323	335.5	348	348	360.5	373	385.5	398

^{*} With signal cut block, L4 is obtained by adding approximately 30 mm to L2.



VV5QC21



Formulas L1 = 16n + 57 (Maximum 20 single wiring stations) L2 = 16n + 163

Ln	1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20
L1	73	89	105	121	137	153	169	185	201	217	233	249	265	281	297	313	329	345	361	377
L2	179	195	211	227	243	259	275	291	307	323	339	355	371	387	403	419	435	451	467	483
L3	200	212.5	237.5	237.5	262.5	262.5	287.5	312.5	325	371	362.5	375	408.5	412.5	425	437.5	462.5	496	487.5	500
L4	210.5	223	248	248	273	273	298	323	335.5	360.5	373	385.5	398	423	435.5	448	473	485.5	498	510.5

^{*} With signal cut block, L4 is obtained by adding approximately 30 mm to L2.

SQ


VQ0

VQ4

VQ5

VQZ

VQD




Formulas

L1 = 25n + 106 (Maximum 16 single wiring stations)

							L2 =	25n + 1	92			3 -			n:	Stations
L	1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16
L1	131	156	181	206	231	256	281	306	331	356	381	406	431	456	481	506
L2	217	242	267	292	317	342	367	392	417	442	467	492	517	542	567	592



- Direct electrical entry type.
- IP67 enclosure is available with use of cables with sheath and waterproof connectors.



Electrical Wiring Specifications

Lead wire specifications Lead wire 0.3 mm² × 25 core

As the standard electrical wiring specification used is for 12 stations or less, double wiring (connected to SOL. A and SOL. B) is used for the internal wiring of each station regardless of valve and option types. Mixed single and double wiring are available as options.

Refer to special wiring specifications (options) below.

Lead wire

Dot

Sheath
Colour: Urban white

Terminal

		no.	ıaı	rolatily L	colour	marking
0	SOL.	<u>A</u> ○ 1	(-)	(+)	Black	None
Station 1	SOL.	<u>B</u> ○ 14	(-)	(+)	Yellow	Black
Station 2	SOL.	A 2	(-)	(+)	Brown	None
Station 2	SOL.	<u>B</u> ⊙ 15	(-)	(+)	Pink	Black
Station 3	SOL.	A ₀ 3	(-)	(+)	Red	None
Stations	SOL.	<u>B</u> ○ 16	(-)	(+)	Blue	White
Station 4	SOL.	<u>A</u> 0 4	(-)	(+)	Orange	None
Station 4	SOL.	<u>B</u> ○ 17	(-)	(+)	Purple	None
Station 5	SOL.	<u>A</u> o 5	(-)	(+)	Yellow	None
Otation 5	SOL.	<u>B</u> ○ 18	(-)	(+)	Grey	None
Station 6	SOL.	<u>A</u> 0 6	(-)	(+)	Pink	None
Cianon o (SOL.	<u>B</u> ○ 19	(-)	(+)	Orange	Black
Station 7	SOL.	A 7	(-)	(+)	Blue	None
J. C.	30L.	B ○ 20	(-)	(+)	Red	White
Station 8	SOL.	8 0 <u>A</u>	(-)	(+)	Purple	White
J. Station C.	30L.	<u>B</u> ○ 21	(-)	(+)	Brown	White
Station 9	SOL.	<u>A</u> o 9	(-)	(+)	Grey	Black
	30L.	<u>B</u> ○ 22	(-)	(+)	Pink	Red
Station 10 √	SOL.	A 0 10	(-)	(+)	White	Black
[30L.	<u>B</u> ○ 23	(-)	(+)	Grey	Red
Station 11	SOL.	A 11	(-)	(+)	White	Red
(SOL.	B ₀ 24	(-)	(+)	Black	White
Station 12 √	301.	A 0 12	(-)	(+)	Yellow	Red
ί.		<u>B</u> ○ 25	(–)	(+)	White	None
	COM	l○ 13	(+)	(-) Note)	Orange	Red
			Positiv	ve Negative		
			spec			
Note)					ation for V	'QC1000/2000,
الشرخ ا	use valves	tor neg	ative (СОМ.		

Polarity

Lead wire length


VV5QC11-08 C6 LD 0

Lead wire length

0	0.6 m
1	1.5 m
2	3.0 m

Electrical characteristics


Item	Characteristic
Conductor resistance Ω/km, 20°C	65 or less
Withstand pressure V, 1 minute, AC	1000
Insulation resistance MΩ/km, 20°C	5 or more




Special Wiring Specifications (Option)

Mixed single and double wiring are available as options. The maximum number of manifold stations is determined by the number of solenoids. Count one point for a single solenoid type and two points for a double solenoid type. The total number of solenoids (points) must not exceed 24.

VV5QC11





Formulas

L1 = 10.5n + 45 (Maximum 24 single wiring stations) L2 = 10.5n + 102

n: Stations

L	1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24
L1	55.5	66	76.5	87	97.5	108	118.5	129	139.5	150	160.5	171	181.5	192	202.5	213	223.5	234	244.5	255	265.5	276	286.5	297
L2	112.5	123	133.5	144	154.5	165	175.5	186	196.5	207	217.5	228	238.5	249	259.5	270	280.5	291	301.5	312	322.5	333	343.5	354
L3	137.5	150	162.5	175	175	187.5	200	212.5	225	237.5	237.5	250	262.5	275	287.5	300	300	312.5	325	337.5	350	362.5	375	375
L4	148	160.5	173	185.5	185.5	198	210.5	223	235.5	248	248	260.5	273	285.5	298	310.5	310.5	323	335.5	348	360.5	373	385.5	385.5

^{*} With signal cut block, L4 is obtained by adding approximately 30 mm to L2.



SQ

VQC

VQ4


VQ5

VQZ

VQD



VV5QC21




Formulas L1 = 16n + 57 (Maximum 24 single wiring stations) L2 = 16n + 110.5

																,	Allilaili	24 3111	gic wii	ii ig sta	110113)			_	
														L2 =	16n +	110.5								n: S	tations
Ī	L	1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24
	L1	73	89	105	121	137	153	169	185	201	217	233	249	265	281	297	313	329	345	361	377	393	409	425	441
	L2	126.5	142.5	158.5	174.5	190.5	206.5	222.5	238.5	254.5	270.5	286.5	302.5	318.5	334.5	350.5	366.5	382.5	398.5	414.5	430.5	446.5	462.5	478.5	494.5
	L3	150	162.5	187.5	200	212.5	237.5	250	262.5	275	300	312.5	325	350	362.5	375	387.5	412.5	425	437.5	450	475	487.5	500	525
1	L4	160.5	173	198	210.5	223	248	260.5	273	285.5	310.5	323	335.5	360.5	373	385.5	398	423	435.5	448	460.5	485.5	498	510.5	535.5


D-side (Stations) - (1) - (2) - (3) - (4) - (5) - (6) - (7) - (8) - (n) | U-side

^{*} With signal cut block, L4 is obtained by adding approximately 30 mm to L2.





- Use of multiple connectors helps streamline wiring procedure to save labor.
- IP67 enclosure is available with use of waterproof multiple connectors.




Electrical Wiring Specifications

Multiple connector



Double wiring (connected to SOL.A and SOL.B) is used for the internal wiring of each staion regardless of valve and option types. Mixed single and double wiring are available as options. Refer to special wiring specifications (options) below.

Terminal Polarity no.



Note) When using the negative COM specification for VQC1000/2000, use valves for negative COM.

GAXT100 – MC26 – □

•	Port cable length				
	Part no.	L dimension			
	GAXT100-MC26-015	1.5 m			
‡	GAXT100-MC26-030	3 m			
7	GAXT100-MC26-050	5 m			

Lead wire colors according to pin numbers

The color code is according to

Pin no.	Cable color	Identification				
1	white	_				
2	brown	_				
3	green	_				
4	yellow	-				
5	grey	_				
6 7	pink	_				
	blue	_				
8	red	_				
9	black	_				
10	violet	_				
11	grey	pink				
12	red	blue				
13	white	green				
14	brown	green				
15	white	yellow				
16	yellow	brown				
17	white	grey				
18	grey	brown				
19	white	pink				
20	pink	brown				
21	white	blue				
22	brown	blue				
23	white	red				
24	brown	red				
25	white	black				
26 *	bridg	ed to pin 25				

* only for circular connectors

	Part no.	L dimension
	GAXT100-MC26-015	1.5 m
_	GAXT100-MC26-030	3 m
Ī	GAXT100-MC26-050	5 m

DIN47100.

Connector pin number (Arrangement as seen from the cable's port side)



Electrical characteristics

Item	Charac- teristics							
Conductor resistence Ω /km, 20°C	57 or less							
Electric strength V, 5min, AC	1500							
Insulation resistence ${\rm M}\Omega/{\rm km}$	20							

(See also AXT100-MC26-036) which conforms to colour code MIL-C24308)

* For detailed specifications and handling, please contact SMC.

Special Wiring Specifications (Option)

Mixed single and double wiring are available as an option. The maximum number of manifold stations is determined by the number of solenoids. Count one point for a single solenoid type and two points for a double solenoid type. The total number of solenoids (points) must not exceed 24.



SQ

VQ0


VQ4

VQ5

VQZ

VQD

VV5QC11




Formulas L1 = 10.5n + 45 (Maximum 24 single wiring stations) L2 = 10.5n + 102

L	1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24
L1	55.5	66	76.5	87	97.5	108	118.5	129	139.5	150	160.5	171	181.5	192	202.5	213	223.5	234	244.5	255	265.5	276	286.5	297
L2	112.5	123	133.5	144	154.5	165	175.5	186	196.5	207	217.5	228	238.5	249	259.5	270	280.5	291	301.5	312	322.5	333	343.5	354
L3	137.5	150	162.5	175	175	187.5	200	212.5	225	237.5	237.5	250	262.5	275	287.5	300	300	312.5	325	337.5	350	362.5	375	375
L4	148	160.5	173	185.5	185.5	198	210.5	223	235.5	248	248	260.5	273	285.5	298	310.5	310.5	323	335.5	348	360.5	373	385.5	385.5

^{*} With signal cut block, L4 is obtained by adding approximately 30 mm to L2.





Formulas L1 = 16n + 57 (Maximum 24 single wiring stations) L2 = 16n + 110.5

														LZ -	1011 +	110.5								11. 0	tations
	n	1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24
	L1	73	89	105	121	137	153	169	185	201	217	233	249	265	281	297	313	329	345	361	377	393	409	425	441
Ī	L2	126.5	142.5	158.5	174.5	190.5	206.5	222.5	238.5	254.5	270.5	286.5	302.5	318.5	334.5	350.5	366.5	382.5	398.5	414.5	430.5	446.5	462.5	478.5	494.5
	L3	150	162.5	187.5	200	212.5	237.5	250	262.5	275	300	312.5	325	350	362.5	375	387.5	412.5	425	437.5	450	475	487.5	500	525
	L4	160.5	173	198	210.5	223	248	260.5	273	285.5	310.5	323	335.5	360.5	373	385.5	398	423	435.5	448	460.5	485.5	498	510.5	535.5

^{*} With signal cut block, L4 is obtained by adding approximately 30 mm to L2.

SQ

VQ0


VQ4

VQ5

VQZ

VQD


Plug-in Unit Series VQC



Formulas L1 = 25n + 106 (Maximum 16 single wiring stations) L2 = 25n + 160.5

n: Stations __n 2 3 5 6 9 12 13 14 15 16 1 10 11 206 256 306 356 381 406 431 456 506 L1 131 156 181 231 281 331 481 L2 185.5 210.5 235.5 260.5 285.5 310.5 335.5 360.5 385.5 410.5 435.5 460.5 485.5 510.5 535.5 560.5

Exploded View of Manifold




Manifold Assembly Part No.

Housing Assembly and SI Unit/Input Block

No.	Description	Part no.	Note	Applicable model						
NO.	Description	rait iio.	Note	VQC1000	VQC2000	VQC4000				
		EX250-SPR1	PROFIBUS-DP (-COM.)	•	•	•				
		EX250-SAS□	AS-i (-COM.)	•	•	•				
1	SI unit	EX250-SMJ	CC-LINK (+COM.)	•	•	•				
		EX250-SDN1	DeviceNet (-COM.)	•	•	•				
		EX250-SCA1	CANopen (-COM.)	•	•	•				
		EX250-IE1	M12, 2 inputs	•	•	•				
2	Input block	EX250-IE2	M12, 4 inputs	•	•	•				
		EX250-IE3	M8, 4 inputs	•	•	•				
3)	End plate assembly	EX250-EA1	Standard	•	•	•				
3)	End plate assembly	EX250-EA2	DIN rail mounting	•	•	_				
		EX500-Q001	DeviceNet (+COM.)	_	_	_				
<u>4</u>)	SI unit	EX500-Q001-X1	Remote I/O (+COM.)	•	•	•				
4)		EX500-Q101	DeviceNet / PROFIBUS-DP (-COM.)	_	_	_				
		EX500-Q101-X1	Remote I/O (-COM.)	•	•	•				
	SI unit	EX240-SDN2	DeviceNet (+COM.)	_	_	•				
5)	Siunii	EX240-SPR1	PROFIBUS-DP (-COM.)	_	_	•				
6)	Input block	EX240-IE1	M12, 8 inputs	_	_	•				
7)	End cover cocombly	EX240-EA2	For manifold with input block			_				
D)	End cover assembly	EX240-EA4	For manifold without input block		_	•				
8)	SI unit	EX126D-SMJ1	CC-LINK (+COM.)	•	•	•				
9)	Terminal plate	VVQC1000-74A-2	For EX126 SI unit mounting	•	•	•				
10)	D-sub connector housing assembly	VVQC1000-F25-1	F kit, 25 pins	•	•	•				
 (1)	Flat vibban ashla bayaing assambly	VVQC1000-P26-1	P kit, 26 pins	_	_	_				
U	Flat ribbon cable housing assembly	VVQC1000-P20-1	P kit, 20 pins	•	•	•				
12)	Terminal block box housing assembly	VVQC1000-T0-1	T kit	•	•	•				
		VVQC1000-L25-0-1	L kit with 0.6 m lead wire							
13	Lead wire housing assembly	VVQC1000-L25-1-1	L kit with 1.5 m lead wire	•	•	•				
		VVQC1000-L25-2-1	L kit with 3.0 m lead wire							
14)	Multiple connector housing assembly	VVQC1000-M26-1	M kit 26 pins	•	•	•				
<u> </u>	Signal out blook	EX9-SC1-8	Double wiring of 1st to 8th stations	•	•	•				
15	Signal cut block	EX9-SC2-4	Double wiring of 9th to 12th stations	•	•	•				

D-side end plate assembly

16 D-side end plate assembly part no. VQC1000/2000




VQC4000 VVQC4000-3A-1 Kit type Thread type 1 S (EX240) kit 2 F, P, T, S (EX250) kit 3 L, M, S (EX500) kit Ro NPT/NPTF

U-side end plate assembly

VVQC4000-2A-1

18 U-side end plate assembly part no.




Thread type Nil

Ro G NPT/NPTF

Manifold block assembly

17 Manifold block assembly part no.



Port size

Symbol	Port size	VQC1000	VQC2000	VQC4000
C3	For ø3.2 One-touch fitting	•		
C4	For ø4 One-touch fitting	•	•	
C6	For ø6	•	•	
C8	For ø8		•	•
C10	For ø10			•
C12	For ø12			•
N1	For ø1/8"	•		
N3	For ø5/32"	•	•	
N7	For ø1/4"	•	•	•
N9	For ø5/16"		•	•
N11	For ø3/8"			•
M5	For M5 thread	•		
02	Rc 1/4"			•
03	Rc 3/8"			•
В	Rc 1/4" bottom ported			•
C0	Without One-touch fitting	•	•	•



VQC

SQ VQ0

VQ4


VQ5

VQZ

VQD

Series VQC1000: Base Mounted/Plug-in Unit

How to order manifold



1 Stations

01	1 station
÷	:

The maximum number of stations differs depending on the electrical entry. Refer to 3

(2) Cylinder port size

\bigcirc	yiiilder port size						
СЗ	With ø3.2 One-touch fitting						
C4	With ø4 One-touch fitting						
C6	With ø6 One-touch fitting						
M5	M5 thread						
CM	Mixed sizes and with port plug						
L3	Top ported elbow Wtih ø3.2 One-touch fitting						
L4	Top ported elbow With ø4 One-touch fitting						
L6	Top ported elbow With ø6 One-touch fitting						
L5	M5 thread						
В3	Bottom ported elbow With ø3.2 One-touch fitting						
B4	Bottom ported elbow With ø4 One-touch fitting						
В6	Bottom ported elbow With ø6 One-touch fitting						
B5	M5 thread						
LM	Elbow port, mixed sizes						
Note 1) Indicate the size in the							

Note 1) Indicate the size in the specification sheet in the case of CM and LM.

Note 2) Symbols for inch sizes are as follows:

<For One-touch fittings>

N1: ø1/8 N3: ø5/32"

N7: ø1/4" NM: Mixed

The top ported elbow is LN \square and the bottom ported elbow is BN \square .

3 Electrical entry/Cable length

FD0 D-sub connector kit (25P) without cable FD1 D-sub connector kit (25P) with 1.5 m cable FD2 D-sub connector kit (25P) with 3.0 m cable FD3 D-sub connector kit (25P) with 5.0 m cable PD0 Flat ribbon cable kit (26P) with 1.5 m cable PD1 Flat ribbon cable kit (26P) with 1.5 m cable PD2 Flat ribbon cable kit (26P) with 3.0 m cable PD3 Flat ribbon cable kit (26P) with 5.0 m cable PD4 Flat ribbon cable kit (20P) with 5.0 m cable PD5 Flat ribbon cable kit (20P) without cable PD6 Flat ribbon cable kit (20P) without cable PD7 Flat ribbon cable kit (20P) without cable PD8 Flat ribbon cable kit (20P) without cable PD9 Flat ribbon cable kit (25 core) 0.6 m lead wire LD0 Lead wire kit (25 core) 1.5 m lead wire LD1 Lead wire kit (25 core) 3.0 m lead wire MD0 Multiple connector kit (26P) without cable MD1 Multiple connector kit (26P) with 3.0 m cable MD2 Multiple connector kit (27P) with 3.0 m cable MD3 Multiple connector kit (27P) with 3.0 m cable Decentralized wiring serial kit (EX500) SD0A Serial kit without SI unit SDA1 Serial kit for Remote I/O SDA2 Serial kit for DeviceNet/PROFIBUS-DP/CC-LINK Input/Output serial kit (EX250) SD0 Serial kit without SI unit SDQ Serial kit without SI unit SDQ Serial kit to PoviceNet compatible SDN Serial kit DeviceNet compatible SDN Serial kit CC-LINK compatible SDN Serial kit CANopen compatible SDTA AS-i, 8 in/8 out, 31 slave modes, 2 power supply 1 to 4 (8)	\simeq		,,					
FD1 D-sub connector kit (25P) with 1.5 m cable FD2 D-sub connector kit (25P) with 3.0 m cable FD3 D-sub connector kit (25P) with 5.0 m cable PD0 Flat ribbon cable kit (26P) without cable PD1 Flat ribbon cable kit (26P) with 1.5 m cable PD2 Flat ribbon cable kit (26P) with 3.0 m cable PD3 Flat ribbon cable kit (26P) with 3.0 m cable PD6 Flat ribbon cable kit (26P) with 5.0 m cable PD7 Flat ribbon cable kit (26P) with 5.0 m cable PD8 Flat ribbon cable kit (26P) with 5.0 m cable PD9 Flat ribbon cable kit (20P) without cable PD9 Flat ribbon cable kit (20P) without cable PD0 Flat ribbon cable kit (20P) without cable PD1 Flat ribbon cable kit (20P) without cable PD2 Flat ribbon cable kit (20P) without cable PD3 Flat ribbon cable kit (20P) without cable PD0 Flat ribbon cable kit (20P) without cable ND1 Lead wire kit (25 core) 3.0 m lead wire ID9 Lead wire kit (25 core) 3.0 m lead wire ID9 Lead wire kit (25 core) 3.0 m lead wire MD0 Multiple connector kit (26P) without cable MD1 Multiple connector kit (27P) with 1.5 m cable MD2 Multiple connector kit (27P) with 5.0 m cable Decentralized wiring serial kit (EX500) SD0A Serial kit without SI unit SD0A1 Serial kit for DeviceNet/PROFIBUS-DP/CC-LINK Input/Output serial kit (EX250) SD0 Serial kit without SI unit SD0 Serial kit without SI unit SD0 Serial kit without SI unit SD0 Serial kit toviceNet compatible SDN Serial kit CC-LINK compatible SDN Serial kit CC-LINK compatible SDY Serial kit CANopen compatible SDTA AS-i, 8 in/8 out, 31 slave modes, 2 power supply 1 to 4 (8)			Kit, Cable length	Stations Note 2)				
FD2 D-sub connector kit (25P) with 3.0 m cable FD3 D-sub connector kit (25P) with 5.0 m cable PD0 Flat ribbon cable kit (26P) without cable PD1 Flat ribbon cable kit (26P) with 1.5 m cable PD2 Flat ribbon cable kit (26P) with 3.0 m cable PD3 Flat ribbon cable kit (26P) with 5.0 m cable PD6 Flat ribbon cable kit (26P) with 5.0 m cable PD7 Flat ribbon cable kit (26P) with 5.0 m cable PD7 Flat ribbon cable kit (20P) without cable PD8 Flat ribbon cable kit (20P) without cable PD9 Flat ribbon cable kit (25 core) 0.6 m lead wire LD0 Lead wire kit (25 core) 1.5 m lead wire LD1 Lead wire kit (25 core) 1.5 m lead wire LD2 Lead wire kit (25 core) 3.0 m lead wire LD2 Lead wire kit (25 core) 3.0 m lead wire LD2 Lead wire kit (25P) without cable MD0 Multiple connector kit (27P) with 1.5 m cable MD1 Multiple connector kit (27P) with 1.5 m cable MD2 Multiple connector kit (27P) with 5.0 m cable Decentralized wiring serial kit (EX500) SD0A Serial kit without SI unit SDA1 Serial kit for Remote I/O SDA2 Serial kit for DeviceNet/PROFIBUS-DP/CC-LINK Input/Output serial kit (EX250) SD0 Serial kit DeviceNet compatible SDN Serial kit PROFIBUS-DP compatible SDN Serial kit CC-LINK compatible SDV Serial kit CANopen compatible SDTA AS-i, 8 in/8 out, 31 slave modes, 2 power supply 1 to 4 (8)		FD0	D-sub connector kit (25P) without cable					
FD2 D-sub connector kit (25P) with 3.0 m cable FD3 D-sub connector kit (25P) with 5.0 m cable PD0 Flat ribbon cable kit (26P) with 1.5 m cable PD1 Flat ribbon cable kit (26P) with 3.0 m cable PD2 Flat ribbon cable kit (26P) with 3.0 m cable PD3 Flat ribbon cable kit (26P) with 5.0 m cable PD6 Flat ribbon cable kit (26P) with 5.0 m cable PD7 Flat ribbon cable kit (20P) without cable Note 1) TD8 Terminal block box kit 1 to 10 (20 LD9 Lead wire kit (25 core) 0.6 m lead wire LD1 Lead wire kit (25 core) 1.5 m lead wire LD2 Lead wire kit (25 core) 3.0 m lead wire MD0 Multiple connector kit (26P) with 1.5 m cable MD1 Multiple connector kit (27P) with 1.5 m cable MD2 Multiple connector kit (27P) with 3.0 m cable MD3 Multiple connector kit (27P) with 5.0 m cable Decentralized wiring serial kit (EX500) SD0A Serial kit without SI unit SDA1 Serial kit for Remote I/O SDA2 Serial kit for DeviceNet/PROFIBUS-DP/CC-LINK Input/Output serial kit (EX250) SD0 Serial kit without SI unit SDQ Serial kit without SI unit SDQ Serial kit DeviceNet compatible SDN Serial kit PROFIBUS-DP compatible SDN Serial kit CC-LINK compatible SDV Serial kit CANopen compatible SDTA AS-i, 8 in/8 out, 31 slave modes, 2 power supply 1 to 4 (8)	Ħ	FD1	D-sub connector kit (25P) with 1.5 m cable	1 +0 12 (24)				
PD0 Flat ribbon cable kit (26P) without cable PD1 Flat ribbon cable kit (26P) with 1.5 m cable PD2 Flat ribbon cable kit (26P) with 3.0 m cable PD3 Flat ribbon cable kit (26P) with 5.0 m cable PDC Flat ribbon cable kit (20P) without cable Note 1) 1 to 9 (18) TD0 Terminal block box kit 1 to 10 (20) LD0 Lead wire kit (25 core) 0.6 m lead wire LD1 Lead wire kit (25 core) 1.5 m lead wire LD2 Lead wire kit (25 core) 3.0 m lead wire MD0 Multiple connector kit (26P) without cable MD1 Multiple connector kit (27P) with 1.5 m cable MD2 Multiple connector kit (27P) with 3.0 m cable MD3 Multiple connector kit (27P) with 5.0 m cable Decentralized wiring serial kit (EX500) SD0A Serial kit without SI unit SDA1 Serial kit for DeviceNet/PROFIBUS-DP/CC-LINK Input/Output serial kit (EX250) SD0 Serial kit without SI unit SDQ Serial kit DeviceNet compatible SDN Serial kit PROFIBUS-DP compatible SDN Serial kit CC-LINK compatible SDV Serial kit CANopen compatible SDTA AS-i, 8 in/8 out, 31 slave modes, 2 power supply 1 to 4 (8)		FD2	D-sub connector kit (25P) with 3.0 m cable	1 10 12 (24)				
PD1 Flat ribbon cable kit (26P) with 1.5 m cable PD2 Flat ribbon cable kit (26P) with 3.0 m cable PD3 Flat ribbon cable kit (26P) with 5.0 m cable PDC Flat ribbon cable kit (20P) without cable Note 1) Terminal block box kit 1 to 10 (20) Terminal block box kit LD0 Lead wire kit (25 core) 0.6 m lead wire LD1 Lead wire kit (25 core) 1.5 m lead wire LD2 Lead wire kit (25 core) 3.0 m lead wire MD0 Multiple connector kit (26P) without cable MD1 Multiple connector kit (27P) with 1.5 m cable MD2 Multiple connector kit (27P) with 3.0 m cable MD3 Multiple connector kit (27P) with 5.0 m cable MD3 Multiple connector kit (27P) with 5.0 m cable Decentralized wiring serial kit (EX500) SD0A Serial kit without SI unit SDA1 Serial kit for Remote I/O SDA2 Serial kit for DeviceNet/PROFIBUS-DP/CC-LINK Input/Output serial kit (EX250) SD0 Serial kit without SI unit SDQ Serial kit DeviceNet compatible SDN Serial kit PROFIBUS-DP compatible SDN Serial kit CC-LINK compatible SDV Serial kit CANopen compatible SDTA AS-i, 8 in/8 out, 31 slave modes, 2 power supply 1 to 4 (8)		FD3	D-sub connector kit (25P) with 5.0 m cable]				
PD2 Flat ribbon cable kit (26P) with 3.0 m cable PD3 Flat ribbon cable kit (26P) with 5.0 m cable PDC Flat ribbon cable kit (20P) without cable Note 1) Terminal block box kit LD0 Lead wire kit (25 core) 0.6 m lead wire LD1 Lead wire kit (25 core) 1.5 m lead wire LD2 Lead wire kit (25 core) 3.0 m lead wire MD0 Multiple connector kit (26P) without cable MD1 Multiple connector kit (27P) with 1.5 m cable MD2 Multiple connector kit (27P) with 3.0 m cable MD3 Multiple connector kit (27P) with 3.0 m cable MD3 Multiple connector kit (27P) with 5.0 m cable Decentralized wiring serial kit (EX500) SD0A Serial kit without SI unit SDA1 Serial kit for Remote I/O SDA2 Serial kit for DeviceNet/PROFIBUS-DP/CC-LINK Input/Output serial kit (EX250) SD0 Serial kit without SI unit SDQ Serial kit DeviceNet compatible SDN Serial kit PROFIBUS-DP compatible SDN Serial kit CC-LINK compatible SDV Serial kit CANopen compatible SDTA AS-i, 8 in/8 out, 31 slave modes, 2 power supply 1 to 4 (8)		PD0	Flat ribbon cable kit (26P) without cable					
FIAT ribbon cable kit (26P) with 3.0 m cable PD3 Flat ribbon cable kit (26P) with 5.0 m cable PDC Flat ribbon cable kit (20P) without cable Note 1) TD0 Terminal block box kit 1 to 10 (20 LD1 Lead wire kit (25 core) 0.6 m lead wire LD1 Lead wire kit (25 core) 1.5 m lead wire LD2 Lead wire kit (25 core) 3.0 m lead wire MD0 Multiple connector kit (26P) without cable MD1 Multiple connector kit (26P) with 1.5 m cable MD2 Multiple connector kit (27P) with 3.0 m cable MD3 Multiple connector kit (27P) with 5.0 m cable Decentralized wiring serial kit (EX500) SD0A Serial kit without SI unit SDA1 Serial kit for Remote I/O SDA2 Serial kit for DeviceNet/PROFIBUS-DP/CC-LINK Input/Output serial kit (EX250) SD0 Serial kit without SI unit SDQ Serial kit without SI unit SDQ Serial kit DeviceNet compatible SDN Serial kit PROFIBUS-DP compatible SDV Serial kit CC-LINK compatible SDV Serial kit CANopen compatible SDTA AS-i, 8 in/8 out, 31 slave modes, 2 power supply 1 to 4 (8)		PD1	Flat ribbon cable kit (26P) with 1.5 m cable	1 to 12 (24)				
PD3 Flat ribbon cable kit (26P) with 5.0 m cable PDC Flat ribbon cable kit (20P) without cable Note 1) 1 to 9 (18) TD0 Terminal block box kit 1 to 10 (20) LD0 Lead wire kit (25 core) 0.6 m lead wire LD1 Lead wire kit (25 core) 1.5 m lead wire LD2 Lead wire kit (25 core) 3.0 m lead wire MD0 Multiple connector kit (26P) without cable MD1 Multiple connector kit (27P) with 1.5 m cable MD2 Multiple connector kit (27P) with 3.0 m cable MD3 Multiple connector kit (27P) with 5.0 m cable Decentralized wiring serial kit (EX500) SD0A Serial kit without SI unit SDA1 Serial kit for Remote I/O SDA2 Serial kit for DeviceNet/PROFIBUS-DP/CC-LINK Input/Output serial kit (EX250) SD0 Serial kit without SI unit SDQ Serial kit vithout SI unit SDQ Serial kit vithout SI unit SDQ Serial kit PROFIBUS-DP compatible SDN Serial kit PROFIBUS-DP compatible SDV Serial kit CC-LINK compatible SDV Serial kit CANopen compatible SDTA AS-i, 8 in/8 out, 31 slave modes, 2 power supply 1 to 4 (8)	Ż	PD2	Flat ribbon cable kit (26P) with 3.0 m cable	1 10 12 (24)				
TD0 Terminal block box kit 1 to 10 (20 LD1 Lead wire kit (25 core) 0.6 m lead wire LD1 Lead wire kit (25 core) 1.5 m lead wire LD2 Lead wire kit (25 core) 3.0 m lead wire MD0 Multiple connector kit (26P) without cable MD1 Multiple connector kit (27P) with 1.5 m cable MD2 Multiple connector kit (27P) with 3.0 m cable MD3 Multiple connector kit (27P) with 5.0 m cable Decentralized wiring serial kit (EX500) SD0A Serial kit without SI unit SDA1 Serial kit for Remote I/O SDA2 Serial kit for DeviceNet/PROFIBUS-DP/CC-LINK Input/Output serial kit (EX250) SD0 Serial kit without SI unit SDQ Serial kit without SI unit SDQ Serial kit PROFIBUS-DP compatible SDN Serial kit PROFIBUS-DP compatible SDV Serial kit CC-LINK compatible SDY Serial kit CANopen compatible SDTA AS-i, 8 in/8 out, 31 slave modes, 2 power supply 1 to 4 (8)	а.	PD3]					
LD0 Lead wire kit (25 core) 0.6 m lead wire LD1 Lead wire kit (25 core) 1.5 m lead wire LD2 Lead wire kit (25 core) 3.0 m lead wire MD0 Multiple connector kit (26P) without cable MD1 Multiple connector kit (27P) with 1.5 m cable MD2 Multiple connector kit (27P) with 3.0 m cable MD3 Multiple connector kit (27P) with 5.0 m cable MD3 Multiple connector kit (27P) with 5.0 m cable Decentralized wiring serial kit (EX500) SD0A Serial kit without SI unit SDA1 Serial kit for Remote I/O SDA2 Serial kit for DeviceNet/PROFIBUS-DP/CC-LINK Input/Output serial kit (EX250) SD0 Serial kit without SI unit SDQ Serial kit DeviceNet compatible SDN Serial kit PROFIBUS-DP compatible SDV Serial kit CC-LINK compatible SDY Serial kit CANopen compatible SDTA AS-i, 8 in/8 out, 31 slave modes, 2 power supply 1 to 4 (8)		PDC	Flat ribbon cable kit (20P) without cable Note 1)	1 to 9 (18)				
LD1 Lead wire kit (25 core) 1.5 m lead wire LD2 Lead wire kit (25 core) 3.0 m lead wire MD0 Multiple connector kit (26P) without cable MD1 Multiple connector kit (27P) with 1.5 m cable MD2 Multiple connector kit (27P) with 3.0 m cable MD3 Multiple connector kit (27P) with 5.0 m cable MD3 Multiple connector kit (27P) with 5.0 m cable Decentralized wiring serial kit (EX500) SD0A Serial kit without SI unit SDA1 Serial kit for Remote I/O SDA2 Serial kit for DeviceNet/PROFIBUS-DP/CC-LINK Input/Output serial kit (EX250) SD0 Serial kit without SI unit SDQ Serial kit DeviceNet compatible SDN Serial kit PROFIBUS-DP compatible SDV Serial kit CC-LINK compatible SDV Serial kit CANopen compatible SDTA AS-i, 8 in/8 out, 31 slave modes, 2 power supply 1 to 4 (8)		TD0	Terminal block box kit	1 to 10 (20)				
LD2 Lead wire kit (25 core) 3.0 m lead wire MD0 Multiple connector kit (26P) without cable MD1 Multiple connector kit (27P) with 1.5 m cable MD2 Multiple connector kit (27P) with 3.0 m cable MD3 Multiple connector kit (27P) with 5.0 m cable Decentralized wiring serial kit (EX500) SD0A Serial kit without SI unit SDA1 Serial kit for Remote I/O SDA2 Serial kit for DeviceNet/PROFIBUS-DP/CC-LINK Input/Output serial kit (EX250) SD0 Serial kit without SI unit SDQ Serial kit PROFIBUS-DP compatible SDN Serial kit PROFIBUS-DP compatible SDV Serial kit CC-LINK compatible SDY Serial kit CANopen compatible SDTA AS-i, 8 in/8 out, 31 slave modes, 2 power supply 1 to 4 (8)		LD0	Lead wire kit (25 core) 0.6 m lead wire					
LD2 Lead wire kit (25 core) 3.0 m lead wire MD0 Multiple connector kit (26P) without cable MD1 Multiple connector kit (27P) with 1.5 m cable MD2 Multiple connector kit (27P) with 3.0 m cable MD3 Multiple connector kit (27P) with 5.0 m cable Decentralized wiring serial kit (EX500) SD0A Serial kit without SI unit SDA1 Serial kit for Remote I/O SDA2 Serial kit for DeviceNet/PROFIBUS-DP/CC-LINK Input/Output serial kit (EX250) SD0 Serial kit without SI unit SDQ Serial kit DeviceNet compatible SDN Serial kit PROFIBUS-DP compatible SDV Serial kit CC-LINK compatible SDY Serial kit CANopen compatible SDTA AS-i, 8 in/8 out, 31 slave modes, 2 power supply 1 to 4 (8)		LD1	Lead wire kit (25 core) 1.5 m lead wire	1 to 12 (24)				
MD1 Multiple connector kit (27P) with 1.5 m cable MD2 Multiple connector kit (27P) with 3.0 m cable MD3 Multiple connector kit (27P) with 5.0 m cable Decentralized wiring serial kit (EX500) SD0A Serial kit without SI unit SDA1 Serial kit for Remote I/O SDA2 Serial kit for DeviceNet/PROFIBUS-DP/CC-LINK Input/Output serial kit (EX250) SD0 Serial kit without SI unit SDQ Serial kit DeviceNet compatible SDN Serial kit PROFIBUS-DP compatible SDV Serial kit CC-LINK compatible SDV Serial kit CANopen compatible SDTA AS-i, 8 in/8 out, 31 slave modes, 2 power supply 1 to 4 (8)	_	LD2	Lead wire kit (25 core) 3.0 m lead wire					
MD2 Multiple connector kit (27P) with 3.0 m cable MD3 Multiple connector kit (27P) with 5.0 m cable Decentralized wiring serial kit (EX500) SD0A Serial kit without SI unit SDA1 Serial kit for Remote I/O SDA2 Serial kit for DeviceNet/PROFIBUS-DP/CC-LINK Input/Output serial kit (EX250) SD0 Serial kit without SI unit SDQ Serial kit DeviceNet compatible SDN Serial kit PROFIBUS-DP compatible SDN Serial kit CC-LINK compatible SDV Serial kit CANopen compatible SDY Serial kit CANopen compatible SDTA AS-i, 8 in/8 out, 31 slave modes, 2 power supply 1 to 4 (8)		MD0	Multiple connector kit (26P) without cable					
MD2 Multiple connector kit (27P) with 3.0 m cable MD3 Multiple connector kit (27P) with 5.0 m cable Decentralized wiring serial kit (EX500) SD0A Serial kit without SI unit SDA1 Serial kit for Remote I/O SDA2 Serial kit for DeviceNet/PROFIBUS-DP/CC-LINK Input/Output serial kit (EX250) SD0 Serial kit without SI unit SDQ Serial kit DeviceNet compatible SDN Serial kit PROFIBUS-DP compatible SDN Serial kit CC-LINK compatible SDV Serial kit CANopen compatible SDY Serial kit CANopen compatible SDTA AS-i, 8 in/8 out, 31 slave modes, 2 power supply 1 to 4 (8)	Ħ	MD1	Multiple connector kit (27P) with 1.5 m cable	1 to 12 (24)				
Decentralized wiring serial kit (EX500) SD0A Serial kit without SI unit SDA1 Serial kit for Remote I/O SDA2 Serial kit for DeviceNet/PROFIBUS-DP/CC-LINK Input/Output serial kit (EX250) SD0 Serial kit without SI unit SDQ Serial kit DeviceNet compatible SDN Serial kit PROFIBUS-DP compatible SDV Serial kit CC-LINK compatible SDV Serial kit CANopen compatible SDTA AS-i, 8 in/8 out, 31 slave modes, 2 power supply 1 to 4 (8)		MD2	Multiple connector kit (27P) with 3.0 m cable	1 10 12 (24)				
SD0A Serial kit without SI unit SDA1 Serial kit for Remote I/O SDA2 Serial kit for DeviceNet/PROFIBUS-DP/CC-LINK Input/Output serial kit (EX250) SD0 Serial kit without SI unit SDQ Serial kit DeviceNet compatible SDN Serial kit PROFIBUS-DP compatible SDV Serial kit CC-LINK compatible SDY Serial kit CANopen compatible SDTA AS-i, 8 in/8 out, 31 slave modes, 2 power supply 1 to 4 (8)		MD3	Multiple connector kit (27P) with 5.0 m cable]				
SDA1 Serial kit for Remote I/O SDA2 Serial kit for DeviceNet/PROFIBUS-DP/CC-LINK Input/Output serial kit (EX250) SD0 Serial kit without SI unit SDQ Serial kit DeviceNet compatible SDN Serial kit PROFIBUS-DP compatible SDV Serial kit CC-LINK compatible SDY Serial kit CANopen compatible SDTA AS-i, 8 in/8 out, 31 slave modes, 2 power supply 1 to 4 (8)			Decentralized wiring serial kit (EX500)					
SDA1 Serial kit for Remote I/O SDA2 Serial kit for DeviceNet/PROFIBUS-DP/CC-LINK Input/Output serial kit (EX250) SD0 Serial kit without SI unit SDQ Serial kit DeviceNet compatible SDN Serial kit PROFIBUS-DP compatible SDV Serial kit CC-LINK compatible SDY Serial kit CANopen compatible SDTA AS-i, 8 in/8 out, 31 slave modes, 2 power supply 1 to 4 (8)		SD0A	00A Serial kit without SI unit					
Input/Output serial kit (EX250) SD0 Serial kit without SI unit SDQ Serial kit DeviceNet compatible SDN Serial kit PROFIBUS-DP compatible SDV Serial kit CC-LINK compatible SDY Serial kit CANopen compatible SDTA AS-i, 8 in/8 out, 31 slave modes, 2 power supply 1 to 4 (8)		SDA1	Serial kit for Remote I/O	1 10 8 (16)				
SD0 Serial kit without SI unit SDQ Serial kit DeviceNet compatible SDN Serial kit PROFIBUS-DP compatible SDV Serial kit CC-LINK compatible SDY Serial kit CANopen compatible SDTA AS-i, 8 in/8 out, 31 slave modes, 2 power supply 1 to 4 (8)		SDA2	Serial kit for DeviceNet/PROFIBUS-DP/CC-LINK]				
SDQ Serial kit DeviceNet compatible SDN Serial kit PROFIBUS-DP compatible SDV Serial kit CC-LINK compatible SDV Serial kit CANopen compatible SDTA AS-i, 8 in/8 out, 31 slave modes, 2 power supply 1 to 4 (8)			Input/Output serial kit (EX250)					
SDN Serial kit PROFIBUS-DP compatible SDV Serial kit CC-LINK compatible SDY Serial kit CANopen compatible SDTA AS-i, 8 in/8 out, 31 slave modes, 2 power supply 1 to 4 (8)		SD0	Serial kit without SI unit]				
SDV Serial kit CC-LINK compatible SDY Serial kit CANopen compatible SDTA AS-i, 8 in/8 out, 31 slave modes, 2 power supply 1 to 4 (8)		SDQ	Serial kit DeviceNet compatible]				
SDV Serial kit CC-LINK compatible SDY Serial kit CANopen compatible SDTA AS-i, 8 in/8 out, 31 slave modes, 2 power supply 1 to 4 (8)		SDN	Serial kit PROFIBUS-DP compatible	1 to 12 (24)				
SDTA AS-i, 8 in/8 out, 31 slave modes, 2 power supply 1 to 4 (8)	S	SDV	Serial kit CC-LINK compatible					
		SDY	Serial kit CANopen compatible	1				
SDTB AS-i, 4 in/4 out, 31 slave modes, 2 power supply 1 to 2 (4)		SDTA						
		SDTB	AS-i, 4 in/4 out, 31 slave modes, 2 power supply	1 to 2 (4)				
SDTC AS-i, 8 in/8 out, 31 slave modes, 1 power supply 1 to 4 (8)		SDTC	AS-i, 8 in/8 out, 31 slave modes, 1 power supply	1 to 4 (8)				
SDTD AS-i, 4 in/4 out, 31 slave modes, 1 power supply 1 to 2 (4)		SDTD	AS-i, 4 in/4 out, 31 slave modes, 1 power supply	1 to 2 (4)				
Output serial transmission kit (EX126)			Output serial transmission kit (EX126)	1 to 9 (10)				
SDVB Serial kit CC-LINK compatible		SDVB	Serial kit CC-LINK compatible	1 to 8 (16)				
Note 1) P Kit: Order the cable assembly separately for the type 20P.		,	* * * *					

Note 2) Numbers inside () indicate the maximum number of solenoids for mixed single and double wiring. The maximum number of stations is determined by the total number of solenoids. In the case of mixed wiring, use the option symbol "-K".

4 SI unit COM.

CL	# COM		Е	X250				EX500								
SI unit COM		DeviceNet	PROFIBUS-DP	CC-LINK	AS-i	CANopen	DeviceNet	PROFIBUS-DP	CC-LINK	Remote I/O	CC-LINK					
Nil	+COM	_	_	0	_	_	0	0	0	0	0					
N	-СОМ	0	0	_	0	0	0	0	0	0						

Note) Leave the box blank for the SI unit COM without SI unit (SD0).

5 Input block (Fill out for I/O unit only)

Nil	Without SI unit/input block (SD0)
0	Without input block
1	With 1 input block
8	With 8 input blocks

6 Input block type (Fill out for I/O unit only)

_ `		
Nil	Without input block	
1	M12, 2 inputs	
2	M12, 4 inputs	
3	M8, 4 inputs (3 pins)	

7 Input block COM. (Fill out for I/O unit only)

	• •
Nil	PNP (+) or without SI unit/input block
N	NPN (–)

(9) Option

Nil	None
В	All stations with back pressure check valve Note 1)
D	With DIN rail (Rail length: standard)
D□	With DIN rail (Rail length: special) Note 2)
K	Special wiring specifications Note 3) (Except double wiring)
N	With name plate
R	External pilot Note 4)
S	Direct exhaust with built-in silencer Note 5)

When specifying more than one option, enter symbols in alphabetical order. Example: -BRS

Note 1) When using the back pressure check valve for the necessary stations only, enter the back pressure check valve part no. and indicate the number of manifold stations in the specification sheet.

Note 2) For special DIN rail length indicate "DD"

Note 2) For special DIN rail length, indicate "D□." (Enter the number of stations inside □.)

Example: -D08
In this case, stations will be mounted on a DIN rail for 8 stations regardless of the actual number of manifold stations.

The specified number of stations must be larger than the number of stations on the manifold.


Indicate "-D0" for the option without DIN rail.

Note 3) Be sure to indicate the wiring specifications in the specification sheet.

For external pilot option, "-R", indicate the external pilot specification "R" for the applicable valves as well.

Note 5) The built-in silencer type does not satisfy the IP67 standard.

2 How to order applicable valves



(A) Type of actuation

1	2 position single
2	2 position double
3	3 position closed center
4	3 position exhaust center
5	3 position pressure center
A Note)	Dual 3 port valve (N.C. + N.C.)
B Note)	Dual 3 port valve (N.O. + N.O.)
C Note)	Dual 3 port valve (N.C. + N.O.)

Note) Available for the rubber seal type only.

(B) Seal type

\sim	71
0	Metal seal
1	Rubber seal

© Function

<u> </u>	.00.011
Nil	Standard type (1 W)
K Note 1)	High voltage type (1.0 MPa)
N	Negative COM.
R Note 2)	External pilot
Υ	Low wattage type (0.5 W)

* When specifying more than one option, enter symbols in alphabetical order

Note 1) Available for the metal seal type only Note 2) Not applicable to dual 3 port valve.

(D) Coil voltage


5	24 VDC Note)
6	12 VDC
,	S kit is only available for 24 VDC.

(E) Light/Surge voltage

suppressor

Nil	With					
E	Without Note)					

Note) Not applicable to S kit.



D-side Stations---1---2----3---4---5---6---7---8----Stations are numbered in ascending order from the D-side.

(F) Manual override

\sim	
Nil	Non-locking push type (Tool required)
В	Slotted locking type (Tool required)
С	Locking type (Manual)
D	Slide locking type (Manual)



Series VQC1000/Plug-in Unit

lanifold model																							Date	:	/	/
F, L, M, P, T kit>													Cu	stom	er na	me										
′V5QC <u>1</u> <u>1</u> −[$\exists \Box$		—				$\dashv \Gamma$		1	Co	ntact	pers	on										
				– – Fil	l out f	or S I	Kit on	ly		_		_	Sp	ecific	ation	shee	t no.									
S kit>	———	—		$\neg \vdash$		$\vec{\neg}$	- -	- - - -		. –		٦ .	Pu	rchas	se ord	ler no).									
V5QC	_	<u> </u>		⅃ᄔ	⅃L	IJL	IJL	⅃L		ЛL	_	J	Eq	uipm	ent na	ame										
Bas	e mounte	d nlu	ا ا a-in	Kit ty	ре						•0	ptio	n Qu	antity	,				Se	et(s)	Req	uired o	date			
	VQC1000		9																							
ecifications		\leftarrow	D-sid	de							* Ind	icate	real	ıirəd	etat	ione	with	a "C) II					U-	side	_
scription/Model	Sta	ations	1		3	4	5	6	7	8	9	10	11	12		14	1	16		18	19	20	21	22	23	24
Single		<u> </u>																								
Double	(Ří)(Þ)((A)(B) (Rí)(P)(
Closed center	(A)(B) (A)(B)																									
Exhaust center Pressure center	(A)(B)			L																		<u> </u>				
	(A) (B)		\perp																		<u> </u>				
Dual 3 port valve (A)	(A) (B	R ₂₎ N.C.		igdash																		<u> </u>				
Dual 3 port valve (B) Dual 3 port valve	(R1) 1 (N.O. (P) (B) (B) (B) (B) (B) (B) (B) (B) (B) (B	R2) N.O.		<u> </u>																		<u> </u>				
(C) Blanking plate	(R1) 1 (N.C. (P)	N.O. N.O.		_																		_				L
VVQ1000-10A-1 Individual SUP space VVQ1000-P-1-C0 SUP shutoff position	6	eitione	- 7 -	 	<u> </u>	L- _F -	L.,.	L .,				.,	.,	· - _T -		L . _F .	L-,-	L .,								<u> </u>
Individual EVII anac	er 6		- 7 -	Ī.,.	Ι.,.	I.,.	[<u> </u>	L	L .,]	J.,	[_ ₁		I . , .	L . , .	L- ₁ -	L - ₁ -		J	J.,.]	I.,.	I.,	I - _F -	Ι.,
VVQ1000-R-1-C EXH shutoff position SUP block plate VVQ1000-16A EXH shutoff position	Note 1)				4																					+
When using EXI VVQC1000-19A	I block base	•		\perp	\perp																	\dashv	\perp			\perp
Port plug Note 2)			АВ	A B	АВ	АВ	АВ	АВ	АВ	АВ	АВ	АВ	АВ	АВ	АВ	АВ	АВ	АВ	АВ	АВ	AB	АВ	АВ	АВ	АВ	AI
With ø3.2 (ø1/8")	Side ported	C3 (N1)	,=		,-			,=		,-	,=		,-			,-								,-		
With ø4 (ø5/32") One-touch fitting	Side ported	C4 (N3)																								
With ø4 (ø5/32") One-touch fitting With ø6 (ø1/4") One-touch fitting With ø6 (ø1/4") One-touch fitting	Side ported	C6 (N7)																								
M5 thread	Side ported	M5		\perp																		\perp				
out in c																										
Dual flow fitting VVQ1000-52A-C	:8																					\top				
pecial wiring Note 4)	Single w	iring	Ľ	Ľ	Ľ	Ľ	Ľ	Ľ	Ľ	Ľ	Ľ					Ľ	Ľ			Ľ	Ľ	Ľ	Ľ	Ľ		Ľ
ecifications	Double w	iring																								
scription/Model	Sta	ations	1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24
Note 1) Indicate to Note 2) When usi	ng port plug	s, circle	port	ts to s	specif	fy.						_														
Note 3) When mo	e of single v	viring o	r mix													e A-s	ide so	olenoi	d of	statio	n 1 a	nd co	ntinu	e in o	rder	
without s	kip ping any	remin	aıs.																							
									~ ~ ~ .	$\sim 10^{-1}$		only														

	Part no.	Qty.

	Part no.	Qty.

Order no.	
Clerk (code no.)	
Dept. code	



VQC

SQ

VQ0

VQ4


VQ5

VQZ

VQD

Series VQC2000: Base Mounted/Plug-in Unit

How to order manifold



1) Stations

01	1 station
:	:

The maximum number of stations differs depending on the electrical entry. Refer to 3

(2) Cylinder nort size

<u> </u>	yiiildei port size
C4	With ø4 One-touch fitting
C6	With ø6 One-touch fitting
C8	With ø8 One-touch fitting
СМ	Mixed or with port plug
L4	Top ported elbow With ø4 One-touch fitting
L6	Top ported elbow With ø6 One-touch fitting
L8	Top ported elbow With ø8 One-touch fitting
B4	Bottom ported elbow With ø4 One-touch fitting
В6	Bottom ported elbow With ø6 One-touch fitting
В8	Bottom ported elbow With ø8 One-touch fitting
LM	Elbow port, mixed sizes

Note 1) Indicate the size in the specification sheet in the case of CM and LM.

Note 2) Symbols for inch sizes are as follows:

<For One-touch fittings>

N3: ø5/32^t

N7: ø1/4"

N9: ø5/16

NM: Mixed

The top ported elbow is LN \square and the bottom ported elbow is BN□.

3 Electrical entry/Cable length

	D-side entry	Kit, Cable length	Stations Note 2)
FKit	FD0	D-sub connector kit (25P) without cable	
	FD1	D-sub connector kit (25P) with 1.5 m cable	1 to 10 (04)
	FD2	D-sub connector kit (25P) with 3.0 m cable	1 to 12 (24)
	FD3	D-sub connector kit (25P) with 5.0 m cable	
	PD0	Flat ribbon cable kit (26P) without cable	
	PD1	Flat ribbon cable kit (26P) with 1.5 m cable	1 +0 10 (04)
Σ	PD2	Flat ribbon cable kit (26P) with 3.0 m cable	1 to 12 (24)
Ф	PD3	Flat ribbon cable kit (26P) with 5.0 m cable	
	PDC	Flat ribbon cable kit (20P) without cable Note 1)	1 to 9 (18)
T Kit	TD0	Terminal block box kit	1 to 10 (20)
	LD0	Lead wire kit (25 core) 0.6 m lead wire	
Σ	LD1	Lead wire kit (25 core) 1.5 m lead wire	1 to 12 (24)
_	LD2	Lead wire kit (25 core) 3.0 m lead wire	
	MD0	Multiple connector kit (26P) without cable	
포	MD1	Multiple connector kit (27P) with 1.5 m cable	1 to 10 (04)
Ξ	MD2	Multiple connector kit (27P) with 3.0 m cable	1 to 12 (24)
	MD3	Multiple connector kit (27P) with 5.0 m cable	
		Decentralized wiring serial kit (EX500)	
	SD0A	Serial kit without SI unit	1 to 8 (16)
	SDA1	Serial kit for Remote I/O	1 10 6 (16)
	SDA2	Serial kit for DeviceNet/PROFIBUS-DP/CC-LINK	
		Input/Output serial kit (EX250)	
	SD0	Serial kit without SI unit	
	SDQ	Serial kit DeviceNet compatible	
조	SDN	Serial kit PROFIBUS-DP compatible	1 to 12 (24)
S	SDV	Serial kit CC-LINK compatible	
	SDY	Serial kit CANopen compatible	
	SDTA	AS-i, 8 in/8 out, 31 slave modes, 2 power supply	1 to 4 (8)
	SDTB	AS-i, 4 in/4 out, 31 slave modes, 2 power supply	1 to 2 (4)
	SDTC	AS-i, 8 in/8 out, 31 slave modes, 1 power supply	1 to 4 (8)
	SDTD	AS-i, 4 in/4 out, 31 slave modes, 1 power supply	1 to 2 (4)
		Output serial transmission kit (EX126)	1 to 9 (16)
	SDVB	Serial kit CC-LINK compatible	1 to 8 (16)
Note	1) P Kit: Ord	der the cable assembly separately for the type 20P.	

Note 2) Numbers inside () indicate the maximum number of solenoids for mixed single and double wiring. The maximum number of stations is determined by the total number of solenoids. In the case of mixed wiring, use the option symbol "-K".

(4) SI unit COM.

OI	:: 00M		Е	X250				EX	500		EX126
Si ui	nit COM	DeviceNet	PROFIBUS-DP	CC-LINK	AS-i	CANopen	DeviceNet	PROFIBUS-DP	CC-LINK	Remote I/O	CC-LINK
Nil	+COM	_	_	0	_	_	0	0	0	0	0
N	-COM	0	0	_	0	0	0	0	0	0	_

Note) Leave the box blank for the SI unit COM without SI unit (SD0)

5 Input block (Fill out for I/O unit only)

Nil	Without SI unit/input block (SD0)		
0	Without input block		
1	With 1 input block		
8	With 8 input blocks		

6 Input block type (Fill out for I/O unit only)

٠.	(i iii dut idi iid diiit diiiy)			
Nil	Without input block			
1	M12, 2 inputs			
2	M12, 4 inputs			
3	M8, 4 inputs (3 pins)			

7 Input block COM. (Fill out for I/O unit only)

Nil	PNP (+) or without SI unit/input block
N	NPN (-)

(9) Option

	•		
Nil	None		
В	All stations with back pressure check valve Note 1)		
D	With DIN rail (Rail length: standard)		
D□	With DIN rail (Rail length: special) Note 2)		
К	Special wiring specifications Note 3) (Except double wiring)		
N	With name plate		
R	External pilot Note 4)		
S	Direct exhaust with built-in silencer Note 5)		
Т	Branched P and R ports on U side Note 6)		
* When specifying more than one option, enter symbols			

When specifying more than one option, enter symbols in alphabetical order. Example: -BRS

Note 1) When using the back pressure check valve for the necessary stations only, enter the back pressure check valve part no. and indicate the number of manifold stations on the specification sheet.

Note 2) For special DIN rail length, indicate "D□." (Enter the number of stations inside □.) Example: -D08

In this case, stations will be mounted on a DIN rail for 8 stations regardless of the actual number of manifold stations.

The specified number of stations must be larger than the number of stations on the manifold. Indicate "-D0" for the option without DIN rail.

Note 3) Be sure to indicate the wiring specifications on the specification sheet.

Note 4) For external pilot option, "-R", indicate the external pilot specification "R" for the applicable valves as well.


Note 5) The built-in silencer type does not satisfy the IPS7.

well.
Note 5) The built-in silencer type does not satisfy the IP67

Note 3) The bunking standard.

Note 6) The SUP and EXH ports on U side are branched (toward the cylinder port and coil) with ø12 one-touch fittings for connection.

How to order applicable valves



A Type of actuation

1	2 position single
2	2 position double
3	3 position closed center
4	3 position exhaust center
5	3 position pressure center
A Note)	Dual 3 port valve (N.C. + N.C.)
B Note)	Dual 3 port valve (N.O. + N.O.)
C Note)	Dual 3 ,port valve (N.C. + N.O.)

Note) Available for the rubber seal type only.

(B) Seal type

0	Metal seal
1	Rubber seal

© Function

Nil Standard type (1 W)						
K Note 1)	High voltage type (1.0 MPa)					
	Negative COM.					
R Note 2)	External pilot					
Υ	Low wattage type (0.5 W)					

* When specifying more than one option, enter symbols in alphabetical order. Note 1) Available for the metal seal type only. Note 2) Not applicable to Dual 3 port valve.

D Coil voltage


5	24 VDC Note)					
6	12 VDC					
Note) S kit is only available for						

24 VDC.

E Light/Surge voltage suppressor

Nil	With				
Е	Without Note)				
Natal Nat applicable to Chit					

Note) Not applicable to S kit.



D-side Stations---1---2---3----4---5----6---7---8---n U-side


Stations are numbered in ascending order

(F) Manual override

O manual eventus									
Nil	Non-locking push type (Tool required)								
В	Slotted locking type (Tool required)								
С	Locking type (Manual)								
D	Slide locking type (Manual)								



Series VQC2000/Plug-in Unit



pec	cifications	•		-side	Э						2	* Ind	icate	requ	uired	stati	ions	with	a "O)".					U-	side]—
escrip	otion/Model	Sta	ations	1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	2
	Single	(4)(B) (A)(B) (A)(B)(B)																									
	Double	(A)(B)	₩																								
	Closed center	(A)(B) 11 11 11 (R1)(P)(R2)																									
valves	Exhaust center	(A)(B) 1 1 3 (R1)(P)(R2)																									
2	Pressure center	(A)(B) T (B1)(P)(R2)	Ī																								
	Dual 3 port valve (A)	(A) (B) (A) (B) (B) (B) (B) (B) (B) (B) (B) (B) (B) R2) N.C.																								
	Dual 3 port valve (B)	(Å) (B) (P) (N.O. (P)) 																								
	Dual 3 port valve (C)	(A) (B) (P) (N.C. (P) (P)	<u>1</u> 17⊒az)																								
	Blanking plate VVQ2000-10A-1	14.0.	14.0.																								T
Options	Individual SUP space VVQ2000-P-1-C8 SUP shutoff position		sitions.	-1-	I - _T -	l . _r .	l . _r .	l.,.	Ĺ.,.			- 1-	J ₋₁	.,.	I - _T -	l . , .	١.,.	- ۲-]	J _{- 1}		l _{-,-} .	1-,-	l - _[-	
	Individual EXH space VVQ2000-R-1-C8 EXH shutoff position		sitions.	-1-	l _{-,-}	l.,.	L- ₁ -	L.,.	L	l _.	ļ ₁]	J ₋₁	1-1-	I	l.,.	L.,.	L- _F -	L -		I _.]	I.,	I.,	l.,.	I.,.	
	SUP block plate VVQ2000-16A																										_
	EXH block plate VVQ2000-19A																										
	Port plug Note 1)	0.1	T	АВ	АВ	AB	АВ	АВ	АВ	АВ	АВ	АВ	АВ	АВ	АВ	AB	AB	АВ	АВ	АВ	AB	AB	АВ	AB	AB	АВ	1
<u>.</u>	With ø4 (ø5/32") One-touch fitting	Side ported	C4 (N3)																								
M/LM/N	With ø6 (ø1/4") One-touch fitting	Side ported	C6 (N7)																								
in case of mixed sizes (CM/LM/NM).	With ø8 (ø5/16") One-touch fitting	Side ported	C8 (N9)																								
Fill out in case of r																											+
	ial wiring ^{Note 2)}	Single wi	iring																								1
	fications	Double w	riring																								
scri	ption/Model	Statio	ns	1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	1

Applicable valves and options

	Part no.	Qty.

order without skipping any terminals.

Part no.	Qty.

Order no.	
Clerk (code no.)	
Dept. code	



Note 2) In the case of single wiring or mixed wiring, connections to the connector terminals start from the A-side solenoid of station 1 and continue in

For SMC use only ---

VQC

SQ

VQ0

VQ4


VQ5

VQZ

VQD

Series VQC4000: Base Mounted/Plug-in Unit

How to order manifold



1) Stations

01	1 station
:	

The maximum number of stations differs depending on the electrical entry. Refer to 3

2 Cylinder port size

C8	With ø8 One-touch fitting
C10	With ø10 One-touch fitting
C12	With ø12 One-touch fitting
02	Rc 1/4
03	Rc 3/8
В	Bottom ported Rc 1/4
СМ	Mixed

Note 1) Indicate the size in the specification order sheet in the case of CM.

Note 2) Symbols for inch sizes are as follows:

<For One-touch fittings>

N7: ø1/4" N9: ø5/16" N11: ø3/8 NM: Mixed

<For threads> P, R, A, B port

V	V5QC	41-08	303	TE
			П.	

Cylinder port Thread type

Nil	Rc
F	G
Т	NPT/NPTF

Note) P and R ports use the same type of threads.

3 Electrical entry

	D-side entry	Kit, Cable length	Stations Note 2)			
FKit	FD0	D-sub connector kit (25P) without cable				
	FD1	D-sub connector kit (25P) with 1.5 m cable	1 to 12 (24)			
	FD2	D-sub connector kit (25P) with 3.0 m cable	1 10 12 (24)			
	FD3	D-sub connector kit (25P) with 5.0 m cable				
	PD0	Flat ribbon cable kit (26P) without cable				
<u></u>	PD1	Flat ribbon cable kit (26P) with 1.5 m cable	1 to 12 (24)			
P Kit	PD2	Flat ribbon cable kit (26P) with 3.0 m cable	1 10 12 (24)			
-	PD3	Flat ribbon cable kit (26P) with 5.0 m cable				
	PDC	Flat ribbon cable kit (20P) without cable Note 1)	1 to 9 (18)			
⊤Kit	TD0	Terminal block box kit	1 to 10 (20)			
	LD0	Lead wire kit (25 core) 0.6 m lead wire				
Ξ	LD1	Lead wire kit (25 core) 1.5 m lead wire	1 to 12 (24)			
_	LD2	Lead wire kit (25 core) 3.0 m lead wire				
	MD0	Multiple connector kit (26P) without cable				
포	MD1	Multiple connector kit (27P) with 1.5 m cable	1 to 12 (24)			
≥	MD2	Multiple connector kit (27P) with 3.0 m cable	1 10 12 (24)			
	MD3	Multiple connector kit (27P) with 5.0 m cable				
		Decentralized wiring serial kit (EX500)				
	SD0A	Serial kit without SI unit				
	SDA1	Serial kit for Remote I/O	1 to 8 (16)			
	SDA2	Serial kit for DeviceNet/PROFIBUS-DP/CC-LINK				
		Input/Output serial kit (EX250)				
	SD0	Serial kit without SI unit				
	SDQ	Serial kit DeviceNet compatible				
	SDN	Serial kit PROFIBUS-DP compatible	1 to 12 (24)			
	SDV	Serial kit CC-LINK compatible				
	SDY	Serial kit CANopen compatible put/Output serial transmission kit (EX240)				
포						
S	SD0W	Serial kit without SI unit				
	SDQW	Serial kit DeviceNet compatible	1 to 12 (16)			
	SDNW	Serial kit PROFIBUS-DP compatible				
	SDVW	Serial kit CC-LINK compatible				
	SDTA	AS-i, 8 in/8 out, 31 slave modes, 2 power supply	1 to 4 (8)			
	SDTB	AS-i, 4 in/4 out, 31 slave modes, 2 power supply	1 to 2 (4)			
	SDTC	AS-i, 8 in/8 out, 31 slave modes, 1 power supply	1 to 4 (8)			
	SDTD	AS-i, 4 in/4 out, 31 slave modes, 1 power supply	1 to 2 (4)			
		Output serial transmission kit (EX126)				
	SDVB	Serial kit CC-LINK compatible	1 to 8 (16)			
Note 1) P Kit: Order the cable assembly separately for the type 20P. Note 2) Numbers inside () indicate the maximum number of solenoids for mixed single and						

Notifices inside () indicate the inaximal infinites of solerions of infined single and double wiring. The maximum number of stations is determined by the total number of solenoids. In the case of mixed wiring, use the option symbol "-K".

(4) SI unit COM.

<u> </u>													
CI.	ınit COM	EX	240		Е	X250				EX:	500		EX126
311	JIIII COM	DeviceNet	PROFIBUS-DP	DeviceNet	PROFIBUS-DP	CC-LINK	AS-i	CANopen	DeviceNet	PROFIBUS-DP	CC-LINK	Remote I/O	CC-LINK
Ni	I +COM	0	_	_	_	0	_	_	0	0	0	0	0
N	-COM	0	0	0	0	_	0	0	0	0	0	0	_

Note) Leave the box blank for the SI unit COM. without SI unit (SD0).

2 How to order applicable valves

VQC 4 1 0 0 Y-5 EB Series VQC4000

(A) Type of actuation

1	2 position single	
2	2 position double	
3	3 position closed center	
4 3 position exhaust center		
5	3 position pressure center	
6	3 position perfect	

(D) Coil voltage

<u> </u>				
5	24 VDC Note)			
6	12 VDC			

Note) S kit is only available for 24 VDC.

(B) Seal type

0	Metal seal
1	Rubber seal

ELight/Surge voltage suppressor

© Function

Nil	Standard type (1 W)
R	External pilot
Υ	Low wattage type (0.5 W)

* When specifying more than one option, enter symbols in alphabetical order.

Without indicator light, with surge voltage supressor (F) Manual override

With

Nil	Non-locking push type (Tool required)
В	Slotted locking type (Tool required)

5 Input block (Fill out for I/O unit only)

Nil	Without SI unit/input block [SD0(W)]			
0	Without input block			
1	With 1 input block			
8	With 8 input blocks			

Note) Max. 4 for EX240 and max 8 for EX250.

6 Input block type (Fill out for I/O unit only)

Nil	Without input block
1	M12, 8 inputs (EX240)
2	M12, 2 inputs (EX250)
3	M12, 4 inputs (EX250)
4	M8, 4 inputs (EX250)

7 Input block COM. (Fill out for I/O unit only)


	• • • • • • • • • • • • • • • • • • • •
Nil	PNP (+) or without SI unit/input block
N	NPN (–)

(9) Options

Nil	None
K	Special wiring specifications Note 1) (Except double wiring)
N	With name plate Note 2) (available for T Kit only)

* When specifying more than one option, enter symbols in alphabetical order. Example: -KN Note 1) Be sure to indicate the wiring specifications in the specification order sheet.

Note 2) The mounting position of the name plate is on the top face of the cover for the terminal block box.



* Stations are numbered in ascending order from the D-side.





Series VQC4000/Plug-in Unit

Series VQC4000

Manifold model Date: Customer name Fill out for S Kit only Contact person VV5QC 4 1-Specification sheet no. Purchase order no. Kit type Equipment name Base mounted, plug-in set(s) Required date

Quantity

/Model gle	Sta	ations	1			* Indicate required stations with a "O".																				
			'	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24
	T\ 1 1 T 5 1 3 1 1 1 1 1 1 1 1																									
uble	(A)(B) 4 2 (R1)(P)(R																									
sed center	(A)(B)																									
naust center	4 2 (R1)(P)(R2)																									
essure center	(R1)(P)(R2)																									
Perfect (\$\\\\\\\\\\\\\\\\\\\\\\\\\\\\\\\\\\\\																										
Blanking plate VVQ4000-10A-1																										
Individual SUP spacer VVQ4000-P-1-02/03																										
Individual EXH spacer VVQ4000-P-1-02/03																										
Throttle valve spacer VVQ4000-20A-1																										
Perfect spacer with residual pressure release valve VVQ4000-25A-1																										
Interface regulator (A regulator) ARBQ4000-00-A-1																										
Interface regulator (B regulator) ARBQ4000-00-B-1																										
Interface regulator (P regulator) ARBQ4000-00-P-1																										
																					<u> </u>					
SUP/EXH block plate VVQ4000-16A R1			-	+	+	+		+	+	+	+	+	- -	+		-	+	+	+	+		+	-	+	- -	
		R2			i			i		i		i	i					i	1	, i			i		i	
Rc 1/4		02																								
Rc 3/8		03																								
		C8 (N7)																								
With ø10 (ø5/16") C10		C10																								
With ø12 (ø3/8") C10		. ,																								
Bottom ported Rc 1/4																										
viring Note 1)	ote 1) Single wiring																									
specifications Double wirin		riring																								
/Model	Sta	itions	1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18	19	20	21	22	23	24
f and diverge extension of the second of the	inking plate Q4000-10A-1 ividual SUP sp Q4000-P-1-02/ ividual EXH sp Q4000-P-1-02/ ividual EXH sp Q4000-20A-1 erface regulator BQ4000-00-A- erface regulator BQ4000-00-P- P/EXH block pl Q4000-16A 1/4 3/8 th ø8 (ø1/4") le-touch fitting th ø12 (ø3/8") le-touch fitting ttom ported Rc iring Note 1)	fect fect fect fect fect Application fect Ap	Sasure center	fect Comparison of the property of the prop	fect Comparison Comparison	Sasure center	fect Comparison Comparison	Sasure center	ssure center	Saure center	Saure center Saur	Saure center Saure Saure	Saure center	Saure center Simple Single wiring Model Stations 1 2 3 4 5 6 7 8 9 10 111	Saure center Section Section	Saure center	Signature Sign	Signature Sign	Saure center	Saure center	Saure center	seure center	Saure center	seure center Company Company	Seure center	seure center Company

Applicable valves and options

	Part no.	Qty.

without skipping any terminals.

	Part no.	Qty.

Note 1) In the case of single wiring or mixed wiring, connections to the connector terminals start from the A-side solenoid of station 1 and continue in order

For SMC use only --

Order no.	
Clerk (code no.)	
Dept. code	



VQC

SQ

VQ0

VQ4

VQ5

VQZ

VQD